

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P691088

Luminaire Tested: **CRTK2-C013-5TLD-U-T5R-7040-U0**

Issue Date: 6/13/2023

Test Information

Test Method: LM-79-08
Report Number: P691088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)
Test Lab: INNOVATION CENTER
Issue Date: 6/13/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CRTK2-C013-5TLD-U-T5R-7040-U0
Description: CARETAKER AREA AND ROADWAY LUMINAIRE
(1) 70 CRI, 4000K LED WITH TYPE V ROUND OPTIC AND U0 SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3742 lumens
Efficiency: N/A
Efficacy: 161.3 lumens/watt
Luminous Opening: Circular (Dia: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B2 - U0 - G1

Input Watts (W): 23.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P691088

CATALOG NUMBER: CRTK2-C013-5TLD-U-T5R-7040-U0

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 0.6 fc
 Type V - Short - N/A

REPORT NUMBER: P691088

CATALOG NUMBER: CRTK2-C013-5TLD-U-T5R-7040-U0

Luminous Intensity Polar Plot



REPORT NUMBER: P691088

CATALOG NUMBER: CRTK2-C013-5TLD-U-T5R-7040-U0


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1871.0	0.0	1871.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1871.0	0.0	1871.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	3742.0	0.0	3742.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.6	0.9
10°-20°	88.3	2.4
20°-30°	152.2	4.1
30°-40°	258.4	6.9
40°-50°	455.9	12.2
50°-60°	777.0	20.8
60°-70°	1117.6	29.9
70°-80°	812.7	21.7
80°-90°	47.4	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3742.0	100.0
0°-180°	3742.0	100.0

Coefficient of Utilization



REPORT NUMBER: P691088


CATALOG NUMBER: CRTK2-C013-5TLD-U-T5R-7040-U0

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	136.5	3.6			
FM	(30°-60°)	745.6	19.9			
FH	(60°-80°)	965.1	25.8			G1/1800
FVH	(80°-90°)	23.7	0.6			G1/100
BL	(0°-30°)	136.5	3.6	B1/500		
BM	(30°-60°)	745.6	19.9	B1/1000		
BH	(60°-80°)	965.1	25.8	B2/1000		G1/1800
BVH	(80°-90°)	23.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short



REPORT NUMBER: P691088

CATALOG NUMBER: CRTK2-C013-5TLD-U-T5R-7040-U0

CANDELA DISTRIBUTION (FULL):

0°	
0°	363.9
2.5°	358.0
5°	350.9
7.5°	337.9
10°	323.8
12.5°	314.3
15°	309.6
17.5°	308.4
20°	309.6
22.5°	315.5
25°	324.9
27.5°	337.9
30°	353.3
32.5°	374.6
35°	404.1
37.5°	440.7
40°	478.6
42.5°	524.6
45°	579.0
47.5°	642.8
50°	712.5
52.5°	787.0
55°	864.9
57.5°	938.2
60°	1012.6
62.5°	1081.2
65°	1161.5
67.5°	1194.6
70°	1111.9
72.5°	984.3
75°	820.0
77.5°	592.0
80°	264.7
82.5°	34.3
85°	7.1
87.5°	1.2
90°	0.0

(END OF REPORT)