

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P690996

Luminaire Tested: **CRTK2-C01-D-U-T5R-7040-U0**

Issue Date: 6/13/2023

Test Information

Test Method: LM-79-08
Report Number: P690996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)
Test Lab: INNOVATION CENTER
Issue Date: 6/13/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CRTK2-C01-D-U-T5R-7040-U0
Description: CARETAKER AREA AND ROADWAY LUMINAIRE
(1) 70 CRI, 4000K LED WITH TYPE V ROUND OPTIC AND U0 SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9130 lumens
Efficiency: N/A
Efficacy: 149.7 lumens/watt
Luminous Opening: Circular (Dia: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P690996
 CATALOG NUMBER: CRTK2-C01-D-U-T5R-7040-U0

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.4 fc
 Type V - Short - N/A

REPORT NUMBER: P690996
CATALOG NUMBER: CRTK2-C01-D-U-T5R-7040-U0

Luminous Intensity Polar Plot



REPORT NUMBER: P690996

CATALOG NUMBER: CRTK2-C01-D-U-T5R-7040-U0


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4565.0	0.0	4565.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4565.0	0.0	4565.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	9130.0	0.0	9130.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	0.9
10°-20°	215.5	2.4
20°-30°	371.3	4.1
30°-40°	630.4	6.9
40°-50°	1112.3	12.2
50°-60°	1895.7	20.8
60°-70°	2726.7	29.9
70°-80°	1982.8	21.7
80°-90°	115.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9130.0	100.0
0°-180°	9130.0	100.0

Coefficient of Utilization



REPORT NUMBER: P690996


CATALOG NUMBER: CRTK2-C01-D-U-T5R-7040-U0

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	333.1	3.6			
FM	(30°-60°)	1819.3	19.9			
FH	(60°-80°)	2354.8	25.8			G2/5000
FVH	(80°-90°)	57.9	0.6			G1/100
BL	(0°-30°)	333.1	3.6	B1/500		
BM	(30°-60°)	1819.3	19.9	B2/2500		
BH	(60°-80°)	2354.8	25.8	B3/2500		G2/5000
BVH	(80°-90°)	57.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short



REPORT NUMBER: P690996
CATALOG NUMBER: CRTK2-C01-D-U-T5R-7040-U0

CANDELA DISTRIBUTION (FULL):

	0°
0°	888.0
2.5°	873.5
5°	856.2
7.5°	824.5
10°	789.9
12.5°	766.9
15°	755.3
17.5°	752.5
20°	755.3
22.5°	769.8
25°	792.8
27.5°	824.5
30°	862.0
32.5°	913.9
35°	986.0
37.5°	1075.3
40°	1167.6
42.5°	1280.0
45°	1412.7
47.5°	1568.3
50°	1738.4
52.5°	1920.1
55°	2110.3
57.5°	2289.1
60°	2470.7
62.5°	2637.9
65°	2834.0
67.5°	2914.7
70°	2712.9
72.5°	2401.5
75°	2000.8
77.5°	1444.4
80°	645.8
82.5°	83.6
85°	17.3
87.5°	2.9
90°	0.0

(END OF REPORT)