

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P691916

Luminaire Tested: **CRTK2-C01H-D-U-T5R-7040-U0**

Issue Date: 6/13/2023

Test Information

Test Method: LM-79-08
Report Number: P691916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)
Test Lab: INNOVATION CENTER
Issue Date: 6/13/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CRTK2-C01H-D-U-T5R-7040-U0
Description: CARETAKER AREA AND ROADWAY LUMINAIRE
(1) 70 CRI, 4000K LED WITH TYPE V ROUND OPTIC AND U0 SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10230 lumens
Efficiency: N/A
Efficacy: 145.7 lumens/watt
Luminous Opening: Circular (Dia: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G2

Input Watts (W): 70.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P691916

CATALOG NUMBER: CRTK2-C01H-D-U-T5R-7040-U0

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 1.6 fc
 Type V - Short - N/A

REPORT NUMBER: P691916

CATALOG NUMBER: CRTK2-C01H-D-U-T5R-7040-U0

Luminous Intensity Polar Plot



REPORT NUMBER: P691916

CATALOG NUMBER: CRTK2-C01H-D-U-T5R-7040-U0


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5115.0	0.0	5115.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5115.0	0.0	5115.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	10230.0	0.0	10230.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.1	0.9
10°-20°	241.4	2.4
20°-30°	416.0	4.1
30°-40°	706.4	6.9
40°-50°	1246.4	12.2
50°-60°	2124.1	20.8
60°-70°	3055.2	29.9
70°-80°	2221.7	21.7
80°-90°	129.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10230.0	100.0
0°-180°	10230.0	100.0

Coefficient of Utilization



REPORT NUMBER: P691916


CATALOG NUMBER: CRTK2-C01H-D-U-T5R-7040-U0

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	373.3	3.6			
FM	(30°-60°)	2038.5	19.9			
FH	(60°-80°)	2638.4	25.8			G2/5000
FVH	(80°-90°)	64.8	0.6			G1/100
BL	(0°-30°)	373.3	3.6	B1/500		
BM	(30°-60°)	2038.5	19.9	B2/2500		
BH	(60°-80°)	2638.4	25.8	B4/5000		G2/5000
BVH	(80°-90°)	64.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short



REPORT NUMBER: P691916

CATALOG NUMBER: CRTK2-C01H-D-U-T5R-7040-U0

CANDELA DISTRIBUTION (FULL):

	0°
0°	994.9
2.5°	978.8
5°	959.4
7.5°	923.9
10°	885.1
12.5°	859.3
15°	846.3
17.5°	843.1
20°	846.3
22.5°	862.5
25°	888.3
27.5°	923.9
30°	965.9
32.5°	1024.0
35°	1104.8
37.5°	1204.9
40°	1308.3
42.5°	1434.3
45°	1582.9
47.5°	1757.3
50°	1947.9
52.5°	2151.4
55°	2364.6
57.5°	2564.9
60°	2768.4
62.5°	2955.7
65°	3175.4
67.5°	3265.9
70°	3039.7
72.5°	2690.9
75°	2241.8
77.5°	1618.4
80°	723.6
82.5°	93.7
85°	19.4
87.5°	3.2
90°	0.0

(END OF REPORT)