

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P690897

Luminaire Tested: **CRTK2-C01-5TLD-U-T5R-7030-U0**

Issue Date: 6/13/2023

Test Information

Test Method: LM-79-08
Report Number: P690897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)
Test Lab: INNOVATION CENTER
Issue Date: 6/13/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CRTK2-C01-5TLD-U-T5R-7030-U0
Description: CARETAKER AREA AND ROADWAY LUMINAIRE
(1) 70 CRI, 3000K LED WITH TYPE V ROUND OPTIC AND U0 SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8862 lumens
Efficiency: N/A
Efficacy: 147.7 lumens/watt
Luminous Opening: Circular (Dia: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 60
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P690897

CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7030-U0

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd


--- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.4 fc
 Type V - Short - N/A

REPORT NUMBER: P690897
CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7030-U0

Luminous Intensity Polar Plot



REPORT NUMBER: P690897

CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7030-U0


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4431.0	0.0	4431.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4431.0	0.0	4431.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	8862.0	0.0	8862.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	0.9
10°-20°	209.2	2.4
20°-30°	360.4	4.1
30°-40°	611.9	6.9
40°-50°	1079.7	12.2
50°-60°	1840.1	20.8
60°-70°	2646.7	29.9
70°-80°	1924.6	21.7
80°-90°	112.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8862.0	100.0
0°-180°	8862.0	100.0

Coefficient of Utilization



REPORT NUMBER: P690897


CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7030-U0

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	323.4	3.6			
FM	(30°-60°)	1765.9	19.9			
FH	(60°-80°)	2285.6	25.8			G2/5000
FVH	(80°-90°)	56.2	0.6			G1/100
BL	(0°-30°)	323.4	3.6	B1/500		
BM	(30°-60°)	1765.9	19.9	B2/2500		
BH	(60°-80°)	2285.6	25.8	B3/2500		G2/5000
BVH	(80°-90°)	56.2	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short



REPORT NUMBER: P690897
CATALOG NUMBER: CRTK2-C01-5TLD-U-T5R-7030-U0

CANDELA DISTRIBUTION (FULL):

0°	
0°	861.9
2.5°	847.9
5°	831.1
7.5°	800.3
10°	766.7
12.5°	744.4
15°	733.2
17.5°	730.4
20°	733.2
22.5°	747.2
25°	769.5
27.5°	800.3
30°	836.7
32.5°	887.1
35°	957.0
37.5°	1043.8
40°	1133.3
42.5°	1242.5
45°	1371.2
47.5°	1522.3
50°	1687.4
52.5°	1863.7
55°	2048.4
57.5°	2221.9
60°	2398.2
62.5°	2560.5
65°	2750.8
67.5°	2829.1
70°	2633.2
72.5°	2331.0
75°	1942.1
77.5°	1402.0
80°	626.8
82.5°	81.2
85°	16.8
87.5°	2.8
90°	0.0

(END OF REPORT)