

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P691725

Luminaire Tested: **CRTK2-C018-D-U-T5R-7030-U0**

Issue Date: 6/13/2023

Test Information

Test Method: LM-79-08
Report Number: P691725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)
Test Lab: INNOVATION CENTER
Issue Date: 6/13/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CRTK2-C018-D-U-T5R-7030-U0
Description: CARETAKER AREA AND ROADWAY LUMINAIRE
(1) 70 CRI, 3000K LED WITH TYPE V ROUND OPTIC AND U0 SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7025 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Luminous Opening: Circular (Dia: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 50.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P691725

CATALOG NUMBER: CRTK2-C018-D-U-T5R-7030-U0

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.1 fc
 Type V - Short - N/A

REPORT NUMBER: P691725
CATALOG NUMBER: CRTK2-C018-D-U-T5R-7030-U0

Luminous Intensity Polar Plot



REPORT NUMBER: P691725

CATALOG NUMBER: CRTK2-C018-D-U-T5R-7030-U0


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3512.5	0.0	3512.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3512.5	0.0	3512.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	7025.0	0.0	7025.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	0.9
10°-20°	165.8	2.4
20°-30°	285.7	4.1
30°-40°	485.1	6.9
40°-50°	855.9	12.2
50°-60°	1458.7	20.8
60°-70°	2098.0	29.9
70°-80°	1525.6	21.7
80°-90°	89.0	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7025.0	100.0
0°-180°	7025.0	100.0

Coefficient of Utilization



REPORT NUMBER: P691725


CATALOG NUMBER: CRTK2-C018-D-U-T5R-7030-U0

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	256.3	3.6			
FM	(30°-60°)	1399.8	19.9			
FH	(60°-80°)	1811.8	25.8			G2/5000
FVH	(80°-90°)	44.5	0.6			G1/100
BL	(0°-30°)	256.3	3.6	B1/500		
BM	(30°-60°)	1399.8	19.9	B2/2500		
BH	(60°-80°)	1811.8	25.8	B3/2500		G2/5000
BVH	(80°-90°)	44.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short



REPORT NUMBER: P691725

CATALOG NUMBER: CRTK2-C018-D-U-T5R-7030-U0

CANDELA DISTRIBUTION (FULL):

0°	
0°	683.2
2.5°	672.1
5°	658.8
7.5°	634.4
10°	607.8
12.5°	590.1
15°	581.2
17.5°	579.0
20°	581.2
22.5°	592.3
25°	610.0
27.5°	634.4
30°	663.3
32.5°	703.2
35°	758.7
37.5°	827.4
40°	898.4
42.5°	984.9
45°	1087.0
47.5°	1206.7
50°	1337.6
52.5°	1477.4
55°	1623.8
57.5°	1761.3
60°	1901.1
62.5°	2029.7
65°	2180.6
67.5°	2242.7
70°	2087.4
72.5°	1847.8
75°	1539.5
77.5°	1111.4
80°	496.9
82.5°	64.3
85°	13.3
87.5°	2.2
90°	0.0

(END OF REPORT)