

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P691562

Luminaire Tested: **CRTK2-C016-D-U-T5R-8027-U0**

Issue Date: 6/13/2023

Test Information

Test Method: LM-79-08
Report Number: P691562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)
Test Lab: INNOVATION CENTER
Issue Date: 6/13/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CRTK2-C016-D-U-T5R-8027-U0
Description: CARETAKER AREA AND ROADWAY LUMINAIRE
(1) 80 CRI, 2700K LED WITH TYPE V ROUND OPTIC AND U0 SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5445 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Luminous Opening: Circular (Dia: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G1

Input Watts (W): 41.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P691562

CATALOG NUMBER: CRTK2-C016-D-U-T5R-8027-U0

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.8 fc
 Type V - Short - N/A

REPORT NUMBER: P691562
CATALOG NUMBER: CRTK2-C016-D-U-T5R-8027-U0

Luminous Intensity Polar Plot



REPORT NUMBER: P691562

CATALOG NUMBER: CRTK2-C016-D-U-T5R-8027-U0


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2722.5	0.0	2722.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2722.5	0.0	2722.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	5445.0	0.0	5445.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	0.9
10°-20°	128.5	2.4
20°-30°	221.4	4.1
30°-40°	376.0	6.9
40°-50°	663.4	12.2
50°-60°	1130.6	20.8
60°-70°	1626.2	29.9
70°-80°	1182.5	21.7
80°-90°	69.0	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5445.0	100.0
0°-180°	5445.0	100.0

Coefficient of Utilization



REPORT NUMBER: P691562


CATALOG NUMBER: CRTK2-C016-D-U-T5R-8027-U0

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	198.7	3.6			
FM	(30°-60°)	1085.0	19.9			
FH	(60°-80°)	1404.3	25.8			G1/1800
FVH	(80°-90°)	34.5	0.6			G1/100
BL	(0°-30°)	198.7	3.6	B1/500		
BM	(30°-60°)	1085.0	19.9	B2/2500		
BH	(60°-80°)	1404.3	25.8	B3/2500		G1/1800
BVH	(80°-90°)	34.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short



REPORT NUMBER: P691562

CATALOG NUMBER: CRTK2-C016-D-U-T5R-8027-U0

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.6
2.5°	521.0
5°	510.7
7.5°	491.7
10°	471.1
12.5°	457.4
15°	450.5
17.5°	448.8
20°	450.5
22.5°	459.1
25°	472.8
27.5°	491.7
30°	514.1
32.5°	545.0
35°	588.0
37.5°	641.3
40°	696.3
42.5°	763.4
45°	842.5
47.5°	935.3
50°	1036.8
52.5°	1145.1
55°	1258.6
57.5°	1365.2
60°	1473.5
62.5°	1573.2
65°	1690.1
67.5°	1738.3
70°	1617.9
72.5°	1432.2
75°	1193.2
77.5°	861.4
80°	385.1
82.5°	49.9
85°	10.3
87.5°	1.7
90°	0.0

(END OF REPORT)