

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P319856

Luminaire Tested: **GAN-SA2D-830-U-SL3**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P319856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA2D-830-U-SL3
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(2) 80 CRI, 3000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
SPILL LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12617 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 129
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P319856
 CATALOG NUMBER: GAN-SA2D-830-U-SL3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P319856
CATALOG NUMBER: GAN-SA2D-830-U-SL3

Luminous Intensity Polar Plot



REPORT NUMBER: P319856

CATALOG NUMBER: GAN-SA2D-830-U-SL3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1886.3	0.0	1886.3
	% Fixture	15.0	0.0	15.0
Street Side	Lumens	10730.7	0.0	10730.7
	% Fixture	85.0	0.0	85.0
Total	Lumens	12617.0	0.0	12617.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.6	2.4
10°-20°	670.6	5.3
20°-30°	852.3	6.8
30°-40°	1085.6	8.6
40°-50°	1539.4	12.2
50°-60°	2382.3	18.9
60°-70°	3243.3	25.7
70°-80°	2163.6	17.1
80°-90°	378.3	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12617.0	100.0
0°-180°	12617.0	100.0

Coefficient of Utilization



REPORT NUMBER: P319856


CATALOG NUMBER: GAN-SA2D-830-U-SL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1209.5	9.6			
FM	(30°-60°)	4315.6	34.2			
FH	(60°-80°)	4858.7	38.5			G2/5000
FVH	(80°-90°)	346.8	2.7			G3/500
BL	(0°-30°)	614.9	4.9	B2/1000		
BM	(30°-60°)	691.8	5.5	B1/1000		
BH	(60°-80°)	548.2	4.3	B2/1000		G2/1000
BVH	(80°-90°)	31.4	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type III Medium





REPORT NUMBER: P319856

CATALOG NUMBER: GAN-SA2D-830-U-SL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	58°	65°	75°	85°
0°	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8
2.5°	3588.5	3583.7	3585.4	3581.9	3573.5	3565.2	3552.9	3555.1	3537.9	3512.5	3480.8
5°	3520.8	3519.0	3532.2	3539.7	3545.9	3541.0	3537.5	3541.9	3516.8	3481.7	3426.8
7.5°	3378.8	3359.5	3376.2	3401.3	3425.0	3443.0	3466.7	3469.8	3454.0	3417.1	3345.0
10°	3177.1	3158.7	3183.3	3222.4	3269.9	3312.9	3360.8	3369.6	3372.7	3339.3	3251.8
12.5°	2967.9	2953.9	2978.5	3033.4	3112.1	3178.4	3254.9	3268.1	3295.3	3272.9	3165.7
15°	2780.7	2775.4	2805.3	2859.4	2949.9	3051.4	3161.7	3185.9	3232.1	3224.6	3098.4
17.5°	2619.0	2617.6	2640.5	2697.2	2797.4	2925.7	3069.0	3109.9	3178.4	3187.2	3043.1
20°	2498.5	2495.9	2511.7	2553.5	2656.8	2802.2	2968.8	3025.1	3123.9	3154.7	2985.9
22.5°	2433.9	2433.5	2433.9	2453.7	2538.1	2673.5	2871.2	2939.8	3070.8	3128.8	2922.6
25°	2422.9	2421.6	2412.0	2409.8	2457.7	2565.8	2774.5	2850.1	3020.2	3110.8	2862.4
27.5°	2451.5	2453.3	2440.5	2419.9	2429.5	2495.0	2690.6	2771.5	2979.8	3107.2	2820.7
30°	2510.8	2510.0	2499.0	2477.4	2458.5	2468.6	2630.8	2711.7	2952.5	3122.6	2792.1
32.5°	2576.3	2581.2	2579.0	2567.1	2539.0	2498.5	2612.8	2691.9	2944.6	3159.5	2779.8
35°	2655.0	2660.3	2676.1	2685.3	2652.4	2587.3	2651.5	2720.0	2967.5	3229.0	2799.6
37.5°	2729.7	2743.3	2787.7	2826.8	2798.7	2726.2	2754.3	2803.1	3038.2	3338.4	2852.8
40°	2815.9	2827.7	2900.2	2983.3	2978.9	2903.8	2920.0	2952.5	3163.1	3495.3	2949.0
42.5°	2900.7	2924.4	3029.4	3147.2	3181.1	3114.7	3140.6	3157.8	3338.9	3703.2	3116.9
45°	3013.6	3039.1	3185.0	3327.0	3406.1	3368.7	3410.1	3416.6	3559.9	3986.2	3360.8
47.5°	3184.6	3213.6	3383.7	3532.7	3653.5	3657.5	3725.6	3723.0	3835.9	4310.1	3668.0
50°	3450.9	3492.7	3632.0	3771.3	3918.1	3999.9	4090.8	4078.1	4166.9	4655.1	4021.8
52.5°	3799.9	3819.2	3922.5	4025.3	4207.7	4391.0	4521.5	4510.1	4542.2	5009.8	4423.5
55°	4161.6	4176.1	4218.7	4275.0	4520.2	4819.1	5095.1	5077.1	4995.8	5378.1	4820.4
57.5°	4486.8	4516.3	4545.7	4569.0	4834.9	5266.5	5681.8	5683.1	5488.0	5775.4	5230.4
60°	4537.4	4563.3	4758.0	4941.7	5373.3	5863.3	6309.8	6296.7	5997.4	6206.6	5687.5
62.5°	4010.8	4069.3	4394.5	4883.2	5891.9	6955.0	7111.0	7094.8	6606.5	6737.9	6219.7
65°	2874.3	2940.7	3333.1	4067.5	5640.5	8157.9	8557.0	8338.1	7437.2	7391.4	6843.0
67.5°	1658.2	1674.0	1844.1	2433.9	4294.8	8220.8	10762.8	10456.5	8727.1	8132.9	7148.0
70°	1226.2	1225.8	1266.2	1497.8	2324.1	6709.3	11811.9	12086.6	10085.1	8376.8	6716.8
71°	1108.8	1110.2	1155.4	1363.3	1840.6	5615.9	11589.1	12190.3	10442.9	8256.4	6404.8
72.5°	948.4	952.8	1015.7	1222.7	1548.3	3872.8	10629.2	11568.0	10612.5	7959.3	5916.5
75°	719.5	729.6	816.6	1030.6	1415.2	1964.1	7801.1	9237.3	9427.6	7023.1	4396.3
77.5°	513.3	524.8	623.2	866.7	1345.3	1480.2	5224.3	6737.9	6937.9	4500.9	1983.0
80°	324.3	338.0	412.2	689.6	1264.0	1405.5	3283.0	4529.0	3783.2	1440.2	504.5
82.5°	190.3	200.8	255.8	450.5	1032.4	1353.6	1931.6	2510.4	1472.3	435.1	229.4
85°	110.3	115.1	159.5	287.0	749.8	1277.6	1419.1	1403.3	639.0	212.7	108.6
87.5°	51.4	57.1	94.5	149.9	416.2	926.0	1121.6	969.1	397.3	99.8	51.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P319856

CATALOG NUMBER: GAN-SA2D-830-U-SL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8	3495.8
2.5°	3465.4	3458.0	3426.8	3399.1	3370.1	3332.3	3290.5	3285.2	3259.7	3264.6	3255.8
5°	3396.9	3378.0	3302.8	3234.7	3154.3	3082.2	3004.0	2967.9	2916.1	2912.5	2899.4
7.5°	3298.9	3263.7	3147.2	3018.0	2888.8	2765.7	2644.0	2564.0	2482.3	2447.6	2444.5
10°	3188.5	3128.8	2957.4	2766.2	2579.8	2400.1	2226.0	2097.3	1981.2	1926.3	1924.1
12.5°	3083.9	2995.6	2760.5	2500.3	2245.4	2012.5	1773.8	1604.6	1459.1	1410.3	1389.7
15°	2995.2	2870.8	2568.9	2236.2	1926.8	1603.3	1331.7	1153.7	1019.2	972.6	963.8
17.5°	2909.0	2749.0	2372.4	1969.4	1595.4	1239.8	967.8	835.5	763.8	744.9	744.5
20°	2823.3	2623.8	2167.2	1696.5	1275.0	927.3	744.1	684.7	660.6	658.4	654.8
22.5°	2726.2	2491.1	1951.4	1422.6	995.0	729.1	632.4	608.7	605.6	613.5	613.5
25°	2635.2	2359.2	1732.5	1154.6	774.0	608.3	564.8	559.9	568.3	582.3	583.7
27.5°	2550.4	2232.2	1518.9	916.3	620.1	535.7	517.7	523.4	538.4	554.6	555.1
30°	2480.5	2112.2	1311.5	722.1	523.9	481.7	478.6	490.0	506.3	519.0	522.1
32.5°	2426.5	2009.8	1111.0	580.6	461.0	441.3	443.9	453.6	463.7	470.7	475.5
35°	2401.4	1921.9	926.0	489.6	421.0	410.0	413.6	418.8	423.2	428.5	432.5
37.5°	2405.8	1853.8	760.8	432.9	394.2	388.5	388.5	388.5	388.5	391.2	391.6
40°	2446.7	1814.7	626.3	396.9	376.2	370.1	365.2	360.8	357.3	359.1	358.2
42.5°	2551.3	1811.2	527.8	374.0	361.7	351.6	341.9	335.8	331.4	333.1	334.0
45°	2728.8	1855.1	461.5	357.7	348.1	332.7	320.4	313.8	310.7	316.4	317.3
47.5°	2958.7	1950.9	421.0	345.9	335.3	315.1	301.9	295.8	296.7	305.0	307.2
50°	3254.9	2106.5	401.7	338.4	326.5	300.2	286.6	281.3	283.9	295.8	298.4
52.5°	3580.1	2330.6	403.9	336.2	320.8	289.2	274.7	268.5	272.9	283.9	286.1
55°	3955.5	2600.1	440.4	339.3	312.5	282.2	265.0	254.5	258.0	268.1	269.9
57.5°	4372.5	2908.6	513.8	338.4	301.9	275.6	254.9	239.1	241.7	247.9	249.6
60°	4806.8	3281.3	627.6	341.0	297.1	267.7	241.3	221.5	220.6	225.9	226.8
62.5°	5328.0	3712.4	757.7	342.8	300.2	257.5	223.3	203.9	201.3	202.6	203.5
65°	5865.1	4024.5	708.9	335.8	309.8	249.2	207.4	186.8	182.0	181.1	181.5
67.5°	5881.8	3690.0	497.1	321.7	313.8	244.8	195.6	172.3	164.4	161.3	160.9
70°	5274.8	2997.8	387.2	306.8	298.0	237.8	184.6	160.4	148.5	143.7	143.3
71°	4978.6	2759.6	367.0	299.3	286.1	230.7	179.8	155.1	142.8	137.6	136.7
72.5°	4514.1	2473.9	342.4	287.4	263.3	212.7	170.5	147.7	134.9	128.8	127.5
75°	3239.5	1617.8	294.0	256.2	218.0	169.6	149.4	132.7	121.7	114.3	113.4
77.5°	1248.2	643.9	222.4	213.2	167.0	132.7	123.1	114.7	106.8	99.3	98.9
80°	385.9	287.9	162.2	160.4	120.9	98.9	95.8	93.6	90.5	82.6	80.9
82.5°	206.1	165.3	111.6	103.7	79.1	65.9	69.4	70.3	70.8	62.4	61.5
85°	98.4	87.5	62.8	58.9	46.1	36.9	42.6	46.1	46.6	38.2	35.6
87.5°	47.0	45.7	29.4	22.4	17.1	12.3	14.9	18.5	20.2	14.5	12.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)