

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P318245

Luminaire Tested: **GAN-SA1C-830-U-T2**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA1C-830-U-T2
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(1) 80 CRI, 3000K, 1050mA LIGHTSQUARE WITH 16 LEDS AND TYPE II OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5775 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 59
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318245
 CATALOG NUMBER: GAN-SA1C-830-U-T2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P318245
CATALOG NUMBER: GAN-SA1C-830-U-T2

Luminous Intensity Polar Plot



REPORT NUMBER: P318245

CATALOG NUMBER: GAN-SA1C-830-U-T2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1071.3	0.0	1071.3
	% Fixture	18.6	0.0	18.6
Street Side	Lumens	4703.7	0.0	4703.7
	% Fixture	81.4	0.0	81.4
Total	Lumens	5775.0	0.0	5775.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.2	1.2
10°-20°	230.1	4.0
20°-30°	403.1	7.0
30°-40°	597.7	10.4
40°-50°	874.2	15.1
50°-60°	1202.9	20.8
60°-70°	1339.2	23.2
70°-80°	907.4	15.7
80°-90°	149.2	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5775.0	100.0
0°-180°	5775.0	100.0

Coefficient of Utilization



REPORT NUMBER: P318245


CATALOG NUMBER: GAN-SA1C-830-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	453.9	7.9			
FM	(30°-60°)	2207.9	38.2			
FH	(60°-80°)	1936.7	33.5			G2/5000
FVH	(80°-90°)	105.2	1.8			G2/225
BL	(0°-30°)	250.4	4.3	B1/500		
BM	(30°-60°)	467.0	8.1	B1/1000		
BH	(60°-80°)	309.9	5.4	B1/500		G1/500
BVH	(80°-90°)	43.9	0.8			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type III Medium





REPORT NUMBER: P318245

CATALOG NUMBER: GAN-SA1C-830-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	72°	75°	85°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	784.8	783.7	779.5	779.5	771.5	764.8	752.0	743.5	733.3	729.8	717.8
5°	860.8	861.2	856.0	852.5	840.7	826.4	804.7	785.0	765.4	757.4	732.9
7.5°	924.6	923.8	922.4	919.5	908.5	893.8	864.6	835.4	806.3	794.4	752.2
10°	965.6	967.4	968.6	970.0	965.4	954.9	927.2	891.6	853.6	837.3	775.3
12.5°	986.3	989.5	995.0	1004.6	1012.1	1010.9	990.8	953.1	907.9	887.4	804.1
15°	998.4	1002.6	1011.3	1028.4	1049.7	1061.8	1056.5	1022.3	972.0	946.7	839.3
17.5°	1006.0	1009.3	1022.9	1045.7	1077.3	1109.6	1123.7	1095.0	1044.3	1015.5	879.7
20°	1011.1	1013.7	1030.6	1057.5	1098.4	1149.7	1189.1	1181.9	1124.1	1086.7	921.8
22.5°	1022.7	1024.9	1041.0	1068.0	1113.3	1179.6	1252.1	1262.9	1208.2	1165.8	967.0
25°	1054.9	1054.9	1068.4	1087.3	1129.8	1205.4	1305.4	1352.9	1294.1	1244.8	1008.7
27.5°	1116.3	1115.7	1120.7	1127.3	1159.5	1231.7	1352.9	1432.5	1383.2	1329.3	1049.3
30°	1189.1	1193.1	1193.7	1190.5	1205.6	1264.5	1396.9	1516.4	1472.9	1414.8	1090.9
32.5°	1282.8	1285.3	1282.4	1271.8	1269.6	1311.0	1440.0	1604.3	1569.9	1504.1	1128.8
35°	1401.7	1396.7	1387.3	1365.9	1345.4	1373.2	1489.4	1692.2	1678.9	1612.0	1181.1
37.5°	1529.1	1529.3	1517.8	1469.1	1440.8	1452.8	1557.4	1791.8	1810.7	1740.5	1248.2
40°	1631.3	1636.7	1643.9	1579.8	1543.2	1559.7	1643.9	1907.3	1966.6	1892.8	1335.4
42.5°	1702.7	1708.9	1729.2	1689.0	1651.0	1681.6	1745.7	2030.6	2141.6	2068.6	1437.7
45°	1778.3	1781.7	1796.0	1778.7	1754.4	1823.4	1860.4	2158.3	2326.7	2255.9	1552.0
47.5°	1857.8	1861.4	1876.1	1864.6	1851.8	1955.8	1980.1	2278.6	2504.1	2461.7	1674.1
50°	1956.0	1958.4	1972.4	1951.5	1955.4	2055.7	2087.1	2388.9	2690.0	2646.6	1796.6
52.5°	2090.1	2090.7	2110.0	2091.1	2072.4	2128.8	2179.1	2492.9	2835.7	2815.3	1919.1
55°	2195.1	2201.4	2264.7	2260.7	2249.9	2195.3	2256.1	2592.0	2965.8	2975.5	2049.1
57.5°	2128.0	2152.9	2281.0	2371.2	2459.1	2360.5	2360.1	2703.5	3086.7	3132.8	2192.1
60°	1863.8	1897.6	2086.3	2286.5	2561.5	2648.0	2576.0	2839.7	3208.8	3288.7	2371.2
62.5°	1331.1	1386.7	1642.5	1962.2	2421.1	2838.5	3015.5	3055.9	3374.8	3469.3	2604.1
65°	672.9	715.0	929.4	1314.6	1934.4	2714.0	3493.1	3529.1	3663.3	3747.2	2962.6
67.5°	408.8	424.7	529.3	731.2	1185.9	2114.1	3649.0	4317.9	4221.7	4266.2	3473.8
70°	301.3	313.0	378.2	485.6	682.0	1240.6	3170.6	4880.9	4817.6	4812.7	3851.6
72°	234.6	243.2	300.9	392.3	498.7	744.3	2298.1	4673.1	4988.2	4963.2	3817.0
72.5°	222.5	230.1	282.6	369.3	471.3	674.7	2066.2	4532.9	4975.9	4964.6	3772.3
75°	175.2	180.6	209.2	285.5	368.9	382.8	1132.2	3512.8	4414.2	4597.7	3392.9
77.5°	145.0	145.8	160.9	207.8	287.5	270.6	556.2	2437.3	3160.9	3362.7	2403.4
80°	118.1	119.1	126.3	145.8	217.5	200.2	264.1	1401.5	1769.7	1771.9	1143.0
82.5°	94.1	94.3	102.2	106.6	156.3	143.2	151.3	658.0	773.3	743.9	410.8
85°	66.2	64.8	99.8	87.5	102.2	91.9	83.5	260.5	319.7	305.8	128.7
87.5°	22.1	22.9	44.3	56.7	59.7	52.1	37.2	99.8	120.7	119.7	40.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P318245

CATALOG NUMBER: GAN-SA1C-830-U-T2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	714.1	707.7	698.3	688.0	679.9	671.5	665.3	662.2	658.6	655.6	659.2
5°	721.6	709.7	689.8	670.3	656.0	643.3	634.1	629.3	625.0	622.0	622.4
7.5°	733.9	714.7	681.2	652.8	632.9	619.2	609.9	606.7	603.9	603.1	604.1
10°	747.1	718.6	669.9	632.1	609.5	598.1	594.0	596.1	598.1	599.9	601.9
12.5°	762.0	722.2	653.4	607.9	588.6	584.2	588.4	597.9	604.9	609.1	611.6
15°	781.5	725.4	634.3	583.6	570.7	575.7	589.8	606.3	618.4	626.2	627.4
17.5°	799.4	725.2	609.9	559.2	556.2	570.7	592.0	615.2	631.5	642.5	644.7
20°	817.9	719.8	581.4	535.3	541.5	565.3	593.0	621.0	640.7	653.4	656.4
22.5°	835.2	710.5	550.2	513.6	529.1	558.2	589.2	617.6	637.3	647.6	650.8
25°	846.9	694.2	518.6	495.3	518.2	549.4	576.9	599.7	614.4	619.6	620.4
27.5°	852.8	672.9	488.8	479.4	506.9	535.1	554.0	565.3	569.5	569.1	568.3
30°	853.6	644.9	463.1	466.5	493.7	514.0	523.0	520.8	515.4	506.3	507.1
32.5°	851.1	613.2	441.6	454.2	477.0	488.4	488.8	478.2	463.9	449.4	445.4
35°	851.9	582.2	422.7	440.2	456.7	461.7	457.1	441.6	422.1	403.5	399.5
37.5°	860.6	555.2	406.4	424.1	434.3	435.5	428.9	412.6	398.3	380.0	378.4
40°	881.5	535.9	390.9	406.0	411.8	412.4	403.1	391.5	392.7	383.0	382.8
42.5°	919.1	527.5	377.2	387.2	390.7	391.9	384.8	377.4	387.7	381.4	379.2
45°	967.6	529.5	365.7	368.7	375.2	380.8	376.4	367.5	371.4	343.8	334.7
47.5°	1023.7	542.3	356.5	352.8	364.1	374.6	367.9	354.3	340.2	312.8	307.6
50°	1089.3	561.9	348.2	337.0	352.0	366.3	359.5	340.2	318.9	305.6	303.8
52.5°	1157.7	586.0	339.8	319.7	336.6	359.9	356.5	337.0	310.8	297.7	295.3
55°	1235.2	610.3	329.3	299.7	320.1	356.9	355.1	325.5	304.6	297.3	295.5
57.5°	1331.7	637.9	315.4	278.8	304.6	346.2	340.6	318.6	298.3	292.7	292.1
60°	1457.3	678.7	295.3	256.5	285.7	329.7	328.5	308.4	288.1	284.2	283.4
62.5°	1645.8	746.1	267.6	234.2	264.7	301.6	312.6	294.7	277.4	277.2	277.6
65°	1938.1	847.5	237.6	214.8	243.4	278.0	294.1	280.6	266.5	270.4	271.0
67.5°	2277.0	931.6	208.2	195.7	221.7	255.5	277.4	266.5	251.9	262.3	262.5
70°	2389.7	856.4	182.3	176.8	199.2	233.8	259.3	250.9	236.2	246.6	245.6
72°	2223.9	691.4	165.6	162.5	182.3	215.9	243.2	236.4	221.9	228.9	226.3
72.5°	2171.6	659.2	161.5	158.9	177.8	211.4	239.0	232.8	218.3	224.3	221.9
75°	1937.2	572.5	138.8	139.4	155.1	189.1	215.5	213.6	198.6	199.2	198.4
77.5°	1405.0	419.8	116.9	120.9	132.0	166.2	191.9	190.7	174.4	171.4	170.8
80°	652.0	214.2	95.2	97.0	108.6	139.0	163.7	162.1	148.9	145.2	143.0
82.5°	223.3	101.8	71.6	72.8	84.1	112.0	142.0	141.0	130.0	122.7	118.1
85°	79.7	50.7	50.1	48.9	60.1	88.1	123.7	118.3	102.2	87.1	86.7
87.5°	25.8	21.7	25.8	25.7	35.0	59.7	89.9	76.6	74.2	61.6	60.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)