

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P321775

Luminaire Tested: **GAN-SA1D-830-U-T3R-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P321775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA1D-830-U-T3R-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(1) 80 CRI, 3000K, 1200mA LIGHTSQUARE WITH 16 LEDS AND TYPE III ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4965 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 67
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P321775
 CATALOG NUMBER: GAN-SA1D-830-U-T3R-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P321775
CATALOG NUMBER: GAN-SA1D-830-U-T3R-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P321775

CATALOG NUMBER: GAN-SA1D-830-U-T3R-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	393.1	0.0	393.1
	% Fixture	7.9	0.0	7.9
Street Side	Lumens	4571.9	0.0	4571.9
	% Fixture	92.1	0.0	92.1
Total	Lumens	4965.0	0.0	4965.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.6
10°-20°	184.3	3.7
20°-30°	296.2	6.0
30°-40°	503.2	10.1
40°-50°	781.1	15.7
50°-60°	1050.2	21.2
60°-70°	1284.7	25.9
70°-80°	751.1	15.1
80°-90°	32.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4965.0	100.0
0°-180°	4965.0	100.0

Coefficient of Utilization



REPORT NUMBER: P321775


CATALOG NUMBER: GAN-SA1D-830-U-T3R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	385.2	7.8			
FM	(30°-60°)	2171.5	43.7			
FH	(60°-80°)	1983.2	39.9			G2/5000
FVH	(80°-90°)	32.0	0.6			G1/100
BL	(0°-30°)	176.9	3.6	B1/500		
BM	(30°-60°)	163.0	3.3	B0/220		
BH	(60°-80°)	52.7	1.1	B0/110		G0/110
BVH	(80°-90°)	0.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type III Medium





REPORT NUMBER: P321775

CATALOG NUMBER: GAN-SA1D-830-U-T3R-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	54°	55°	65°	75°	85°
0°	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5
2.5°	929.4	930.5	934.6	936.3	940.6	947.7	951.3	951.5	957.3	959.5	961.3
5°	863.7	870.3	877.0	884.2	897.1	914.3	931.2	932.8	951.5	965.3	972.7
7.5°	807.0	813.1	821.1	832.4	850.7	877.7	906.0	909.4	944.8	976.2	992.7
10°	748.8	753.8	765.3	782.1	807.3	843.4	881.5	887.1	938.8	991.0	1019.9
12.5°	686.6	689.5	703.6	727.7	764.7	810.6	860.8	868.1	935.0	1007.9	1052.0
15°	639.4	640.7	654.1	679.1	721.4	781.2	844.7	853.6	935.9	1028.2	1087.0
17.5°	627.3	628.0	635.1	652.3	689.8	754.9	832.0	842.9	938.6	1048.0	1122.3
20°	676.2	671.5	664.1	661.5	677.5	739.0	824.4	836.7	942.1	1065.6	1153.9
22.5°	810.2	796.3	765.8	725.0	700.2	740.2	826.4	838.7	953.5	1087.3	1190.5
25°	1009.0	989.8	937.9	857.6	780.5	772.3	843.2	855.6	975.6	1113.1	1225.5
27.5°	1235.3	1216.3	1152.8	1038.2	906.7	835.8	881.5	893.1	1008.3	1136.1	1252.2
30°	1452.0	1446.6	1371.7	1241.5	1065.4	938.8	931.0	940.8	1032.6	1149.9	1273.4
32.5°	1635.7	1627.2	1567.0	1440.4	1247.1	1062.5	989.2	992.1	1050.9	1167.7	1301.1
35°	1806.0	1795.5	1742.7	1623.0	1433.5	1213.7	1078.8	1074.6	1090.8	1203.6	1341.2
37.5°	1954.7	1964.3	1905.7	1791.8	1600.7	1370.8	1199.6	1186.9	1153.3	1262.1	1399.4
40°	2079.1	2079.1	2048.6	1953.6	1781.3	1533.4	1336.3	1319.6	1247.1	1352.1	1473.2
42.5°	2123.9	2133.5	2144.9	2091.2	1942.9	1702.4	1488.6	1471.2	1379.3	1479.9	1566.4
45°	2126.6	2141.8	2200.0	2199.7	2088.9	1870.2	1660.2	1652.0	1548.7	1643.9	1681.8
47.5°	2088.9	2107.9	2203.7	2258.1	2204.6	2026.5	1847.9	1837.7	1747.8	1845.0	1802.7
50°	2030.7	2051.7	2163.2	2281.1	2283.3	2162.5	2045.7	2030.3	1967.0	2074.9	1927.5
52.5°	1926.6	1967.2	2126.8	2286.5	2335.1	2280.0	2233.8	2227.1	2212.2	2296.3	2027.0
55°	1703.9	1748.9	2035.6	2288.2	2383.0	2384.1	2410.2	2412.0	2442.1	2503.1	2101.0
57.5°	1598.7	1624.1	1876.5	2296.7	2454.1	2502.3	2589.9	2603.7	2650.3	2699.6	2185.5
60°	1532.5	1562.6	1798.0	2285.1	2565.8	2657.2	2756.4	2761.1	2811.0	2902.2	2299.8
62.5°	1479.6	1509.3	1748.5	2240.5	2691.3	2843.6	2919.1	2919.6	2957.0	3143.6	2429.8
65°	1349.2	1374.2	1648.4	2190.4	2774.2	3027.9	3108.2	3105.3	3135.8	3398.2	2580.7
67.5°	1160.6	1179.8	1444.0	2000.2	2743.0	3195.6	3393.6	3384.0	3347.0	3618.3	2640.0
70°	897.3	904.2	1138.1	1666.9	2450.5	3260.0	3669.3	3664.4	3476.5	3578.8	2422.7
71°	741.7	764.5	1003.0	1471.2	2254.6	3200.5	3696.1	3699.0	3443.9	3471.4	2273.1
72.5°	430.7	450.1	727.0	1129.8	1914.1	2952.1	3557.4	3578.4	3291.9	3157.5	1941.6
75°	92.3	98.8	269.5	546.9	1052.9	2069.1	2807.9	2882.6	2683.1	2148.0	1170.2
77.5°	64.2	69.3	115.5	248.1	348.0	1022.4	1744.3	1828.5	1602.9	807.3	374.5
80°	50.8	56.6	90.1	122.6	94.1	329.7	817.1	868.6	534.6	180.1	63.1
82.5°	28.3	33.7	70.2	66.2	36.1	62.6	228.7	258.6	107.0	36.3	14.9
85°	8.2	10.0	45.3	48.2	15.4	12.0	39.0	48.4	20.3	9.6	6.7
87.5°	0.0	0.0	21.8	18.5	4.5	1.8	3.6	4.0	4.0	4.0	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P321775

CATALOG NUMBER: GAN-SA1D-830-U-T3R-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5
2.5°	961.3	962.9	957.3	949.9	942.1	932.5	922.5	914.7	914.5	910.7	906.9
5°	973.1	972.2	956.8	933.4	905.8	877.0	849.6	818.6	808.4	795.7	791.4
7.5°	995.0	988.7	956.2	904.9	844.3	784.1	721.9	659.2	632.5	608.4	604.2
10°	1022.4	1010.6	951.9	862.1	750.9	639.8	546.0	460.8	423.4	394.6	393.3
12.5°	1050.9	1032.9	940.1	797.4	628.5	472.4	364.3	280.5	249.2	229.2	231.0
15°	1080.8	1053.8	914.7	710.3	489.1	320.6	223.8	174.6	162.1	156.9	158.3
17.5°	1111.3	1068.3	879.3	605.3	351.6	206.9	154.9	141.1	141.1	142.2	142.7
20°	1137.9	1076.1	827.1	487.6	238.3	150.7	135.5	133.5	134.7	136.4	136.7
22.5°	1164.2	1076.6	759.1	368.3	166.8	132.0	129.1	128.2	128.9	130.9	131.1
25°	1185.6	1071.2	673.9	262.0	133.1	124.4	123.1	122.6	123.1	125.5	125.5
27.5°	1194.3	1051.8	570.1	184.1	119.3	115.9	115.5	115.9	116.6	118.4	118.6
30°	1195.2	1017.9	456.8	133.3	108.1	104.6	105.4	107.0	106.3	105.9	106.3
32.5°	1197.4	978.7	346.4	109.7	98.8	93.2	92.1	92.1	89.4	87.8	86.9
35°	1204.8	932.5	251.3	98.5	89.2	82.7	78.5	73.6	68.4	65.8	65.1
37.5°	1216.3	884.2	179.9	91.2	80.7	73.3	65.3	56.6	49.3	47.3	47.3
40°	1237.5	834.2	133.1	85.4	74.0	64.9	52.8	41.5	34.8	33.7	33.7
42.5°	1271.0	781.6	106.1	80.3	68.2	56.2	40.4	30.1	25.2	24.5	24.3
45°	1305.7	723.7	92.7	75.4	62.0	46.1	29.9	22.3	19.4	18.7	18.7
47.5°	1340.5	661.9	86.3	70.7	56.0	35.9	22.3	17.6	16.3	16.3	16.5
50°	1370.0	597.5	81.6	65.5	48.2	27.2	17.6	14.9	14.5	15.4	15.6
52.5°	1377.3	534.2	75.8	59.1	38.6	20.7	14.5	13.2	13.2	13.2	13.2
55°	1372.9	485.1	68.2	51.1	28.5	16.5	12.5	11.6	11.4	11.4	11.4
57.5°	1388.0	456.1	54.6	39.7	20.5	13.4	10.9	10.3	9.8	9.6	9.6
60°	1418.6	437.2	39.0	28.5	15.4	11.1	9.4	8.7	8.0	7.6	7.6
62.5°	1459.1	420.7	29.0	21.2	11.8	8.9	7.8	7.1	6.2	5.8	5.8
65°	1490.3	391.3	22.1	15.8	8.9	7.1	6.0	5.8	4.5	4.0	3.8
67.5°	1442.6	326.6	17.8	11.6	6.7	5.6	4.7	4.5	2.7	2.2	2.2
70°	1237.3	227.4	14.3	8.5	4.9	4.5	3.8	2.9	2.0	1.8	1.8
71°	1122.0	189.9	12.9	7.1	4.2	4.2	3.6	2.5	1.8	1.6	1.6
72.5°	932.1	134.9	10.9	5.6	3.8	4.5	3.8	2.2	1.8	1.6	1.3
75°	541.1	56.4	7.6	3.8	2.9	5.4	4.9	2.0	1.3	1.1	1.1
77.5°	162.7	20.7	4.2	2.5	2.2	4.7	5.6	1.8	0.7	0.2	0.2
80°	29.7	8.9	2.7	1.6	1.6	2.9	4.2	0.9	0.0	0.0	0.0
82.5°	10.5	4.5	1.6	0.9	0.7	1.3	2.0	0.0	0.0	0.0	0.0
85°	6.0	3.1	0.9	0.4	0.0	0.2	0.4	0.0	0.0	0.0	0.0
87.5°	4.0	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)