

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P323688

Luminaire Tested: **GAN-SA4C-830-U-SL3-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P323688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-23)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA4C-830-U-SL3-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(4) 80 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19369 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G4


Input Watts (W): 225
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P323688
 CATALOG NUMBER: GAN-SA4C-830-U-SL3-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.3 fc
 Type III - Medium - N/A

REPORT NUMBER: P323688
CATALOG NUMBER: GAN-SA4C-830-U-SL3-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P323688

CATALOG NUMBER: GAN-SA4C-830-U-SL3-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1657.6	0.0	1657.6
	% Fixture	8.6	0.0	8.6
Street Side	Lumens	17711.4	0.0	17711.4
	% Fixture	91.4	0.0	91.4
Total	Lumens	19369.0	0.0	19369.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	467.9	2.4
10°-20°	982.0	5.1
20°-30°	1290.9	6.7
30°-40°	1709.7	8.8
40°-50°	2555.5	13.2
50°-60°	4093.8	21.1
60°-70°	5160.1	26.6
70°-80°	2783.4	14.4
80°-90°	325.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19369.0	100.0
0°-180°	19369.0	100.0

Coefficient of Utilization



REPORT NUMBER: P323688


CATALOG NUMBER: GAN-SA4C-830-U-SL3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2074.8	10.7			
FM	(30°-60°)	7726.6	39.9			
FH	(60°-80°)	7587.0	39.2			G4/12000
FVH	(80°-90°)	323.0	1.7			G3/500
BL	(0°-30°)	665.9	3.4	B2/1000		
BM	(30°-60°)	632.3	3.3	B1/1000		
BH	(60°-80°)	356.5	1.8	B1/500		G1/500
BVH	(80°-90°)	2.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4

Type III Medium



REPORT NUMBER: P323688

CATALOG NUMBER: GAN-SA4C-830-U-SL3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	58°	65°	75°	85°
0°	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5
2.5°	6195.9	6180.6	6174.9	6165.3	6128.2	6092.0	6020.3	6000.2	5955.1	5848.0	5734.4
5°	6200.7	6199.9	6216.8	6212.8	6199.9	6183.0	6131.5	6104.9	6028.4	5875.3	5667.5
7.5°	5901.9	5917.2	5955.1	5985.7	6021.1	6067.0	6073.5	6047.7	5984.9	5819.8	5544.3
10°	5500.8	5525.0	5578.2	5638.6	5731.2	5823.0	5905.1	5901.9	5880.2	5717.5	5396.1
12.5°	5098.9	5127.1	5188.3	5277.7	5409.0	5558.8	5705.4	5725.5	5761.8	5625.7	5259.2
15°	4747.0	4771.1	4831.6	4941.1	5103.8	5305.1	5520.2	5557.2	5650.6	5554.0	5144.8
17.5°	4448.2	4463.5	4507.8	4629.4	4817.9	5061.9	5341.4	5413.9	5553.2	5497.6	5045.8
20°	4239.6	4242.0	4271.0	4356.4	4544.8	4817.9	5156.1	5260.0	5450.1	5449.3	4943.5
22.5°	4136.5	4128.4	4134.1	4183.2	4321.7	4585.1	4970.9	5094.1	5357.5	5408.2	4839.6
25°	4117.2	4110.7	4094.6	4101.1	4184.8	4381.3	4784.0	4926.6	5276.1	5383.2	4749.4
27.5°	4177.6	4184.0	4156.6	4127.6	4134.1	4249.3	4618.1	4783.2	5210.1	5383.2	4685.8
30°	4299.2	4302.4	4282.3	4244.4	4193.7	4212.2	4503.0	4668.1	5177.1	5420.3	4645.5
32.5°	4433.7	4451.4	4449.0	4418.4	4345.9	4271.0	4475.6	4626.2	5174.6	5502.4	4641.5
35°	4600.4	4620.5	4654.4	4647.9	4572.2	4449.0	4569.0	4687.4	5222.2	5637.8	4685.0
37.5°	4777.6	4808.2	4880.7	4915.3	4866.2	4726.9	4778.4	4863.0	5349.4	5856.8	4795.3
40°	4949.1	4983.8	5115.9	5252.0	5214.9	5071.6	5095.7	5163.4	5575.7	6171.7	5004.7
42.5°	5117.5	5169.0	5363.1	5587.0	5631.3	5516.9	5529.8	5583.8	5911.6	6605.0	5347.0
45°	5318.8	5376.8	5664.3	5940.6	6059.0	6009.0	6063.8	6099.2	6350.5	7177.7	5808.5
47.5°	5614.4	5681.2	6034.0	6348.9	6556.7	6588.9	6699.3	6722.6	6905.4	7844.5	6410.1
50°	6191.1	6209.6	6528.5	6814.4	7114.0	7307.3	7433.0	7450.7	7577.1	8573.4	7161.6
52.5°	6916.7	6928.8	7109.2	7300.9	7641.6	8036.2	8330.2	8355.1	8381.7	9283.8	7903.3
55°	7637.5	7635.9	7755.1	7867.9	8257.7	8831.1	9469.0	9484.3	9293.4	9957.9	8470.3
57.5°	8087.8	8131.2	8312.5	8457.4	9001.9	9737.2	10622.3	10678.7	10251.0	10457.2	9030.9
60°	7944.4	7965.3	8367.2	8903.6	9928.9	11025.0	11789.3	11803.8	10971.1	10955.8	9739.6
62.5°	6768.5	6779.8	7411.2	8517.0	10398.4	12695.4	13197.2	12961.2	11799.0	11647.6	10587.7
65°	4639.1	4712.4	5239.9	6606.6	9535.9	13743.2	15376.6	14985.9	13061.1	12644.7	11354.4
67.5°	2731.9	2716.6	2977.5	3984.3	7003.7	13047.4	18133.4	17745.2	14782.2	13312.3	11129.7
70°	1866.1	1855.6	1955.5	2412.2	3953.7	10121.4	19000.8	19784.5	16302.0	12862.9	9578.5
72.5°	1332.1	1337.8	1485.1	1874.1	2482.2	5897.1	16339.8	18194.6	15826.0	11213.5	7280.8
75°	904.5	919.8	1130.8	1537.5	2176.2	3000.1	11595.2	13831.0	12887.1	8149.8	4184.8
77.5°	486.5	503.4	752.2	1238.7	1967.6	2084.4	7458.7	9518.9	8095.0	3663.7	1212.9
80°	203.0	212.6	352.0	900.4	1700.2	1830.7	4388.6	5772.3	3449.5	722.4	270.6
82.5°	87.8	92.6	146.6	537.2	1270.9	1545.5	2323.6	2777.0	1045.4	158.7	136.1
85°	16.9	17.7	60.4	284.3	811.0	872.2	1506.1	1476.3	469.5	68.5	99.1
87.5°	0.0	0.0	14.5	89.4	238.4	475.2	919.0	907.7	159.5	33.0	37.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P323688

CATALOG NUMBER: GAN-SA4C-830-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5	5721.5
2.5°	5676.4	5620.8	5504.1	5359.9	5249.6	5127.9	5031.3	4908.9	4855.7	4858.1	4829.1
5°	5549.2	5434.8	5176.3	4850.1	4598.8	4339.5	4116.4	3894.1	3762.8	3720.1	3679.8
7.5°	5367.1	5185.9	4773.6	4271.0	3845.8	3430.2	3068.5	2750.4	2549.1	2450.8	2414.6
10°	5161.8	4907.3	4310.5	3648.4	3041.2	2479.0	2010.3	1602.7	1440.0	1329.7	1301.5
12.5°	4981.4	4636.6	3857.8	3009.8	2288.9	1610.8	1163.8	910.1	799.8	756.3	749.0
15°	4811.4	4383.8	3422.1	2431.5	1585.0	991.4	740.2	654.0	628.2	621.0	621.0
17.5°	4651.1	4142.9	2996.1	1862.1	1048.6	695.1	612.9	593.6	585.5	584.7	585.5
20°	4483.6	3902.1	2577.3	1364.3	732.1	588.7	566.2	555.7	553.3	553.3	553.3
22.5°	4323.3	3661.3	2169.7	974.5	587.1	537.2	525.9	518.7	516.3	515.5	513.8
25°	4169.5	3432.6	1771.9	688.6	515.5	492.1	482.4	472.8	465.5	461.5	459.1
27.5°	4043.1	3228.8	1401.4	552.5	465.5	445.4	433.3	418.8	401.1	393.0	389.8
30°	3942.4	3042.8	1080.0	466.3	418.8	398.7	380.1	355.2	329.4	315.7	314.9
32.5°	3863.5	2860.0	819.9	412.4	376.9	352.0	325.4	294.0	264.2	248.9	248.1
35°	3824.8	2698.9	626.6	372.9	339.9	308.5	275.4	240.8	211.8	197.3	195.7
37.5°	3850.6	2562.8	488.9	339.9	308.5	272.2	233.6	197.3	171.5	158.7	157.9
40°	3944.8	2475.8	397.1	311.7	281.9	237.6	195.7	161.9	140.1	129.7	128.9
42.5°	4145.4	2443.6	339.1	288.3	256.1	205.4	162.7	133.7	113.6	106.3	104.7
45°	4480.4	2491.1	299.6	265.8	229.5	174.8	134.5	109.5	91.8	86.2	85.4
47.5°	4926.6	2615.9	271.4	244.0	205.4	147.4	111.9	88.6	74.9	69.3	68.5
50°	5501.6	2814.0	248.1	222.3	182.8	124.8	92.6	70.1	58.0	54.0	54.0
52.5°	6127.4	3050.0	227.1	202.2	160.3	103.9	74.9	54.0	45.9	41.1	41.1
55°	6644.5	3256.2	204.6	186.9	132.9	86.2	57.2	41.1	33.8	31.4	31.4
57.5°	7160.7	3476.1	178.8	160.3	106.3	70.1	43.5	30.6	25.0	23.4	23.4
60°	7830.0	3745.1	153.8	130.5	83.8	53.2	32.2	21.7	18.5	17.7	17.7
62.5°	8566.2	3902.9	131.3	104.7	65.2	39.5	23.4	14.5	13.7	13.7	12.9
65°	9016.4	3679.8	110.3	83.8	50.7	29.8	15.3	10.5	12.1	11.3	9.7
67.5°	8442.1	2880.9	90.2	65.2	39.5	22.6	9.7	7.2	12.9	10.5	8.1
70°	6990.0	2016.7	70.1	45.9	31.4	19.3	6.4	4.8	13.7	10.5	6.4
72.5°	5231.0	1349.8	55.6	30.6	23.4	16.9	5.6	2.4	12.1	8.9	5.6
75°	2858.3	543.6	44.3	19.3	14.5	12.1	4.0	1.6	8.1	6.4	4.0
77.5°	752.2	143.4	32.2	12.9	8.1	4.8	2.4	0.8	4.0	3.2	1.6
80°	191.7	55.6	20.9	8.9	5.6	2.4	0.0	0.0	0.8	0.0	0.0
82.5°	102.3	23.4	12.9	6.4	3.2	0.0	0.0	0.0	0.0	0.0	0.0
85°	77.3	15.3	7.2	4.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	29.8	4.8	2.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)