

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P321749

Luminaire Tested: **GAN-SA5A-830-U-T3R-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P321749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA5A-830-U-T3R-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 80 CRI, 3000K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14234 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 162
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P321749
 CATALOG NUMBER: GAN-SA5A-830-U-T3R-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.5 fc
 Type III - Medium - N/A

REPORT NUMBER: P321749
CATALOG NUMBER: GAN-SA5A-830-U-T3R-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P321749

CATALOG NUMBER: GAN-SA5A-830-U-T3R-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1126.9	0.0	1126.9
	% Fixture	7.9	0.0	7.9
Street Side	Lumens	13107.1	0.0	13107.1
	% Fixture	92.1	0.0	92.1
Total	Lumens	14234.0	0.0	14234.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.1	1.6
10°-20°	528.4	3.7
20°-30°	849.2	6.0
30°-40°	1442.7	10.1
40°-50°	2239.3	15.7
50°-60°	3010.7	21.2
60°-70°	3683.1	25.9
70°-80°	2153.4	15.1
80°-90°	93.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14234.0	100.0
0°-180°	14234.0	100.0

Coefficient of Utilization



REPORT NUMBER: P321749


CATALOG NUMBER: GAN-SA5A-830-U-T3R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1104.4	7.8			
FM	(30°-60°)	6225.5	43.7			
FH	(60°-80°)	5685.5	39.9			G3/7500
FVH	(80°-90°)	91.6	0.6			G1/100
BL	(0°-30°)	507.2	3.6	B2/1000		
BM	(30°-60°)	467.3	3.3	B1/1000		
BH	(60°-80°)	151.0	1.1	B1/500		G1/500
BVH	(80°-90°)	1.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type III Medium





REPORT NUMBER: P321749

CATALOG NUMBER: GAN-SA5A-830-U-T3R-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	54°	55°	65°	75°	85°
0°	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1
2.5°	2664.5	2667.7	2679.2	2684.4	2696.5	2717.0	2727.2	2727.8	2744.4	2750.8	2755.9
5°	2476.0	2495.2	2514.4	2534.8	2571.9	2621.1	2669.7	2674.1	2727.8	2767.4	2788.5
7.5°	2313.7	2330.9	2353.9	2386.5	2438.9	2516.3	2597.4	2607.0	2708.6	2798.8	2846.1
10°	2146.8	2160.9	2194.1	2242.1	2314.3	2417.8	2527.1	2543.1	2691.4	2840.9	2924.0
12.5°	1968.5	1976.8	2017.1	2086.1	2192.2	2323.9	2467.7	2488.8	2680.5	2889.5	3016.1
15°	1833.0	1836.9	1875.2	1946.8	2068.2	2239.5	2421.7	2447.2	2683.1	2947.7	3116.4
17.5°	1798.5	1800.4	1820.9	1870.1	1977.5	2164.1	2385.2	2416.6	2690.8	3004.6	3217.4
20°	1938.5	1925.1	1904.0	1896.3	1942.3	2118.7	2363.5	2398.7	2701.0	3055.1	3308.2
22.5°	2322.6	2283.0	2195.4	2078.5	2007.5	2121.9	2369.3	2404.4	2733.6	3117.1	3413.0
25°	2892.7	2837.8	2688.8	2458.7	2237.6	2214.0	2417.2	2453.0	2796.8	3191.2	3513.3
27.5°	3541.4	3487.1	3305.0	2976.4	2599.4	2396.1	2527.1	2560.4	2890.8	3257.0	3590.0
30°	4162.7	4147.3	3932.6	3559.3	3054.4	2691.4	2669.0	2697.1	2960.5	3296.7	3650.7
32.5°	4689.3	4665.0	4492.5	4129.4	3575.3	3046.1	2835.8	2844.1	3012.9	3347.8	3730.0
35°	5177.6	5147.6	4996.1	4652.9	4109.6	3479.4	3092.8	3080.6	3127.3	3450.7	3845.0
37.5°	5603.9	5631.4	5463.3	5136.7	4589.0	3930.0	3439.2	3402.7	3306.2	3618.1	4011.8
40°	5960.6	5960.6	5873.0	5600.7	5106.7	4396.0	3831.0	3783.0	3575.3	3876.3	4223.4
42.5°	6089.0	6116.5	6149.1	5995.1	5570.0	4880.4	4267.5	4217.6	3954.3	4242.6	4490.6
45°	6096.7	6140.2	6307.0	6306.3	5988.7	5361.7	4759.6	4736.0	4440.1	4713.0	4821.6
47.5°	5988.7	6043.0	6317.8	6473.8	6320.4	5809.7	5297.8	5268.4	5010.8	5289.5	5168.0
50°	5821.9	5881.9	6201.5	6539.6	6546.0	6199.6	5864.7	5820.6	5639.1	5948.4	5525.9
52.5°	5523.4	5639.7	6097.3	6555.0	6694.3	6536.4	6404.1	6384.9	6342.1	6583.1	5811.0
55°	4884.9	5014.0	5835.9	6560.1	6831.7	6834.9	6909.7	6914.8	7001.1	7176.2	6023.2
57.5°	4583.2	4656.1	5379.6	6584.4	7035.6	7173.6	7424.8	7464.4	7598.0	7739.3	6265.4
60°	4393.4	4479.7	5154.6	6551.1	7355.8	7617.8	7902.2	7915.7	8058.8	8320.2	6593.3
62.5°	4241.9	4326.9	5012.7	6423.3	7715.6	8152.1	8368.8	8370.1	8477.5	9012.4	6965.9
65°	3868.0	3939.6	4725.8	6279.5	7953.4	8680.7	8910.8	8902.5	8990.1	9742.3	7398.6
67.5°	3327.3	3382.3	4139.7	5734.3	7863.9	9161.3	9728.9	9701.4	9595.3	10373.1	7568.6
70°	2572.5	2592.3	3262.8	4778.8	7025.4	9346.0	10519.5	10505.4	9966.6	10260.0	6945.5
71°	2126.4	2191.6	2875.5	4217.6	6463.6	9175.4	10596.2	10604.5	9873.3	9951.9	6516.6
72.5°	1234.8	1290.4	2084.2	3239.1	5487.6	8463.4	10198.7	10258.7	9437.4	9052.0	5566.2
75°	264.6	283.1	772.7	1567.8	3018.6	5931.8	8049.9	8264.0	7692.0	6158.1	3354.8
77.5°	184.1	198.8	331.1	711.4	997.7	2931.1	5000.6	5242.2	4595.4	2314.3	1073.7
80°	145.7	162.3	258.2	351.5	269.7	945.3	2342.4	2490.1	1532.6	516.4	180.9
82.5°	81.2	96.5	201.3	189.8	103.5	179.6	655.8	741.4	306.8	104.2	42.8
85°	23.6	28.8	129.7	138.1	44.1	34.5	111.8	138.7	58.2	27.5	19.2
87.5°	0.0	0.0	62.6	53.0	12.8	5.1	10.2	11.5	11.5	11.5	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P321749

CATALOG NUMBER: GAN-SA5A-830-U-T3R-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1	2745.1
2.5°	2755.9	2760.4	2744.4	2723.3	2701.0	2673.5	2644.7	2622.4	2621.7	2610.9	2600.0
5°	2789.8	2787.3	2743.2	2676.1	2596.8	2514.4	2435.7	2346.9	2317.5	2281.1	2268.9
7.5°	2852.5	2834.6	2741.2	2594.2	2420.4	2247.8	2069.5	1889.9	1813.2	1744.2	1732.1
10°	2931.1	2897.2	2729.1	2471.5	2152.6	1834.3	1565.2	1321.1	1213.7	1131.3	1127.4
12.5°	3012.9	2961.1	2695.2	2286.2	1801.7	1354.3	1044.3	804.0	714.6	657.0	662.1
15°	3098.5	3021.2	2622.4	2036.3	1402.3	919.1	641.7	500.4	464.6	449.9	453.8
17.5°	3186.1	3062.7	2520.7	1735.2	1007.9	593.1	444.2	404.6	404.6	407.8	409.0
20°	3262.1	3085.1	2371.2	1397.8	683.2	432.1	388.6	382.8	386.0	391.1	391.8
22.5°	3337.6	3086.4	2176.2	1055.8	478.1	378.4	370.1	367.5	369.4	375.2	375.8
25°	3398.9	3071.0	1932.1	751.0	381.6	356.6	352.8	351.5	352.8	359.8	359.8
27.5°	3423.8	3015.4	1634.3	527.9	341.9	332.3	331.1	332.3	334.3	339.4	340.0
30°	3426.4	2918.3	1309.6	382.2	310.0	299.8	302.3	306.8	304.9	303.6	304.9
32.5°	3432.8	2805.8	993.2	314.5	283.1	267.2	264.0	264.0	256.3	251.8	249.3
35°	3453.9	2673.5	720.3	282.5	255.7	237.1	225.0	210.9	196.2	188.5	186.6
37.5°	3487.1	2534.8	515.8	261.4	231.4	210.3	187.3	162.3	141.2	135.5	135.5
40°	3547.8	2391.6	381.6	244.8	212.2	186.0	151.5	118.9	99.7	96.5	96.5
42.5°	3643.7	2240.8	304.2	230.1	195.6	161.1	115.7	86.3	72.2	70.3	69.7
45°	3743.4	2074.6	265.9	216.0	177.7	132.3	85.6	63.9	55.6	53.7	53.7
47.5°	3843.1	1897.6	247.3	202.6	160.4	102.9	63.9	50.5	46.7	46.7	47.3
50°	3927.5	1712.9	233.9	187.9	138.1	78.0	50.5	42.8	41.5	44.1	44.7
52.5°	3948.6	1531.4	217.3	169.4	110.6	59.4	41.5	37.7	37.7	37.7	37.7
55°	3935.8	1390.8	195.6	146.4	81.8	47.3	35.8	33.2	32.6	32.6	32.6
57.5°	3979.2	1307.7	156.6	113.8	58.8	38.3	31.3	29.4	28.1	27.5	27.5
60°	4066.8	1253.3	111.8	81.8	44.1	32.0	26.8	24.9	23.0	21.7	21.7
62.5°	4183.1	1206.0	83.1	60.7	33.9	25.6	22.4	20.5	17.9	16.6	16.6
65°	4272.6	1121.7	63.3	45.4	25.6	20.5	17.3	16.6	12.8	11.5	10.9
67.5°	4135.8	936.3	51.1	33.2	19.2	16.0	13.4	12.8	7.7	6.4	6.4
70°	3547.2	651.9	40.9	24.3	14.1	12.8	10.9	8.3	5.8	5.1	5.1
71°	3216.8	544.5	37.1	20.5	12.1	12.1	10.2	7.0	5.1	4.5	4.5
72.5°	2672.2	386.7	31.3	16.0	10.9	12.8	10.9	6.4	5.1	4.5	3.8
75°	1551.2	161.7	21.7	10.9	8.3	15.3	14.1	5.8	3.8	3.2	3.2
77.5°	466.6	59.4	12.1	7.0	6.4	13.4	16.0	5.1	1.9	0.6	0.6
80°	85.0	25.6	7.7	4.5	4.5	8.3	12.1	2.6	0.0	0.0	0.0
82.5°	30.0	12.8	4.5	2.6	1.9	3.8	5.8	0.0	0.0	0.0	0.0
85°	17.3	8.9	2.6	1.3	0.0	0.6	1.3	0.0	0.0	0.0	0.0
87.5°	11.5	2.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)