

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P322077

Luminaire Tested: **GAN-SA3B-830-U-T2-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P322077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-13)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA3B-830-U-T2-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(3) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II
OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9863 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G2

Input Watts (W): 124
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P322077

CATALOG NUMBER: GAN-SA3B-830-U-T2-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3 fc
 Type II - Medium - N/A

REPORT NUMBER: P322077
CATALOG NUMBER: GAN-SA3B-830-U-T2-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P322077

CATALOG NUMBER: GAN-SA3B-830-U-T2-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	591.6	0.0	591.6
	% Fixture	6.0	0.0	6.0
Street Side	Lumens	9271.4	0.0	9271.4
	% Fixture	94.0	0.0	94.0
Total	Lumens	9863.0	0.0	9863.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	1.1
10°-20°	322.9	3.3
20°-30°	562.3	5.7
30°-40°	986.6	10.0
40°-50°	1651.4	16.7
50°-60°	2427.3	24.6
60°-70°	2492.3	25.3
70°-80°	1230.4	12.5
80°-90°	81.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9863.0	100.0
0°-180°	9863.0	100.0

Coefficient of Utilization



REPORT NUMBER: P322077


CATALOG NUMBER: GAN-SA3B-830-U-T2-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	795.8	8.1			
FM	(30°-60°)	4829.4	49.0			
FH	(60°-80°)	3566.7	36.2			G2/5000
FVH	(80°-90°)	79.4	0.8			G1/100
BL	(0°-30°)	197.9	2.0	B1/500		
BM	(30°-60°)	235.9	2.4	B1/1000		
BH	(60°-80°)	155.9	1.6	B1/500		G1/500
BVH	(80°-90°)	2.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type II Medium



REPORT NUMBER: P322077

CATALOG NUMBER: GAN-SA3B-830-U-T2-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4
2.5°	1321.1	1315.4	1313.1	1302.8	1285.0	1271.4	1245.2	1214.7	1209.1	1179.6	1143.5
5°	1492.5	1487.8	1484.6	1470.0	1451.8	1417.6	1369.8	1313.1	1302.3	1246.1	1174.0
7.5°	1612.0	1620.4	1620.4	1611.0	1588.1	1562.3	1503.8	1426.5	1412.9	1326.7	1214.7
10°	1681.8	1692.1	1700.1	1708.0	1704.7	1694.4	1639.2	1552.0	1535.6	1421.3	1262.0
12.5°	1688.3	1698.7	1721.1	1754.4	1786.7	1810.1	1775.5	1691.2	1672.4	1530.9	1318.3
15°	1651.8	1662.6	1697.2	1761.9	1840.1	1908.5	1919.8	1845.3	1826.1	1661.6	1388.5
17.5°	1588.1	1595.1	1644.8	1734.3	1857.0	1982.5	2050.5	2010.6	1992.8	1811.1	1466.8
20°	1540.8	1545.9	1589.5	1685.5	1846.7	2028.9	2174.1	2186.3	2167.6	1971.3	1551.6
22.5°	1621.8	1631.2	1632.6	1678.0	1818.6	2051.9	2282.8	2359.2	2345.1	2141.4	1634.9
25°	1843.4	1854.2	1818.6	1790.5	1842.5	2062.2	2376.1	2536.3	2525.0	2324.5	1718.8
27.5°	2136.2	2147.4	2101.5	2017.7	1967.6	2101.1	2459.0	2716.2	2715.7	2518.5	1809.2
30°	2423.8	2435.1	2388.2	2304.4	2189.1	2211.2	2530.6	2904.5	2907.3	2718.5	1905.2
32.5°	2725.5	2739.6	2691.3	2583.6	2463.2	2401.3	2631.4	3093.7	3109.7	2950.4	2013.5
35°	3068.4	3070.3	3002.4	2889.5	2750.8	2655.7	2793.0	3306.0	3343.9	3237.6	2150.7
37.5°	3404.8	3418.4	3362.6	3184.6	3057.2	2949.5	3033.3	3571.1	3625.0	3588.4	2330.1
40°	3654.0	3682.6	3674.6	3482.6	3361.7	3284.9	3331.7	3886.4	3954.8	3996.9	2556.4
42.5°	3810.5	3832.0	3868.6	3752.9	3643.2	3655.9	3684.0	4253.7	4338.0	4462.6	2816.4
45°	3989.9	4000.2	4030.7	3979.6	3905.6	4033.0	4057.8	4667.3	4755.9	4963.4	3105.0
47.5°	4209.2	4233.5	4241.9	4195.1	4161.4	4366.6	4418.1	5043.5	5167.6	5499.8	3410.4
50°	4488.4	4494.9	4509.4	4479.0	4445.3	4653.3	4741.3	5438.4	5551.3	6038.0	3711.6
52.5°	4761.5	4784.9	4835.5	4816.3	4802.7	4897.3	5029.4	5794.4	5920.5	6486.8	4012.4
55°	4840.2	4860.3	5035.1	5154.5	5265.1	5198.1	5304.9	6113.5	6249.8	6887.8	4301.9
57.5°	4525.8	4566.6	4869.2	5180.3	5638.9	5665.6	5683.4	6440.9	6563.2	7195.1	4603.1
60°	3731.3	3739.3	4235.9	4769.4	5577.1	6073.6	6236.2	6792.7	6895.3	7481.4	4963.9
62.5°	2373.2	2454.3	2999.1	3752.4	4923.1	6014.6	6904.7	7324.9	7362.4	7824.8	5481.0
65°	1130.4	1182.9	1575.4	2318.4	3566.0	5259.0	7366.1	8287.6	8304.5	8505.4	6172.0
67.5°	625.9	651.2	838.1	1248.0	2084.7	3719.1	7179.7	9427.8	9443.8	9200.6	6778.2
69°	489.5	511.1	658.2	940.7	1413.4	2673.1	6497.1	9761.9	9809.2	9399.7	6799.8
70°	415.5	436.6	566.8	794.5	1136.5	2065.5	5783.2	9678.9	9729.1	9381.0	6639.1
72.5°	254.4	266.6	377.6	559.3	761.7	1039.1	3566.4	8185.5	8270.3	8605.2	5705.9
75°	171.5	178.0	236.1	386.0	544.8	535.0	1852.8	5769.6	5953.2	6693.9	4214.3
77.5°	122.7	128.8	158.3	249.7	381.8	353.2	839.0	3585.6	3625.0	4014.7	2298.3
80°	69.8	75.4	112.0	148.5	259.1	235.6	333.5	1712.7	1732.4	1721.6	767.3
82.5°	36.5	41.2	61.4	97.9	166.3	154.1	138.7	573.4	576.2	479.2	168.2
85°	7.0	8.4	30.5	67.0	85.7	67.0	56.7	134.4	137.3	121.3	41.7
87.5°	0.0	0.5	12.2	15.0	16.9	17.3	18.3	26.2	28.1	37.9	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P322077

CATALOG NUMBER: GAN-SA3B-830-U-T2-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4	1122.4
2.5°	1127.6	1110.7	1078.4	1040.9	1011.9	983.3	960.8	937.4	929.0	924.7	924.3
5°	1138.8	1103.2	1034.8	964.6	906.9	852.6	813.7	776.7	759.4	751.4	748.1
7.5°	1157.6	1100.4	990.3	883.1	800.1	732.2	678.3	638.0	617.9	609.5	606.2
10°	1179.6	1096.7	938.3	796.9	691.0	620.7	567.3	527.5	505.5	496.1	491.4
12.5°	1205.4	1090.1	878.4	709.7	597.8	527.5	462.8	413.7	388.4	377.6	372.4
15°	1237.2	1083.6	815.6	627.7	515.8	430.1	359.3	326.1	320.9	319.0	319.5
17.5°	1268.6	1073.3	747.2	546.7	429.6	335.9	299.8	297.9	298.9	298.9	298.9
20°	1296.7	1049.8	672.7	477.4	347.6	283.4	275.9	272.6	270.3	268.4	266.1
22.5°	1318.7	1018.4	601.0	408.5	283.9	259.5	247.8	237.5	229.1	223.5	220.6
25°	1333.7	976.7	535.5	342.4	255.3	236.1	215.0	197.7	184.6	176.6	173.3
27.5°	1345.0	931.8	476.9	286.7	235.6	208.9	181.3	160.7	147.1	140.1	137.3
30°	1352.9	880.7	425.4	252.0	213.6	180.4	150.8	130.7	120.9	117.1	115.2
32.5°	1360.4	824.0	376.6	235.6	193.0	154.1	126.5	111.0	104.9	100.3	98.8
35°	1379.2	771.6	330.3	218.3	171.9	131.6	108.7	97.4	91.4	88.5	87.6
37.5°	1423.7	732.7	285.8	200.5	150.8	113.8	95.1	87.1	81.5	78.7	77.8
40°	1495.3	713.0	248.3	181.3	130.2	100.3	86.2	78.7	72.6	68.4	67.5
42.5°	1600.7	715.8	222.1	162.1	113.8	89.5	77.8	68.9	62.3	58.6	57.6
45°	1728.6	736.4	203.8	143.4	100.3	81.0	68.4	59.0	52.9	49.7	48.7
47.5°	1867.3	769.7	188.8	126.5	89.5	73.1	59.0	49.2	44.0	41.2	40.8
50°	2013.5	802.0	173.3	110.1	80.1	65.1	49.7	40.8	36.5	34.2	33.3
52.5°	2161.5	839.5	159.3	95.1	72.1	55.7	41.2	33.3	30.0	28.1	27.2
55°	2320.8	867.6	145.7	83.4	64.2	47.3	34.2	27.6	24.8	22.5	22.0
57.5°	2508.2	911.2	131.6	72.1	54.8	39.4	28.1	22.0	19.7	17.3	16.9
60°	2761.1	962.2	116.6	63.7	45.0	32.3	23.0	17.8	15.0	13.1	12.6
62.5°	3094.7	1018.9	97.9	55.7	36.5	26.2	18.3	14.1	10.8	8.4	8.4
65°	3517.7	1111.2	80.1	46.8	30.0	21.5	14.1	10.3	6.1	3.7	3.7
67.5°	3764.6	1127.1	64.6	38.4	24.4	18.3	11.7	7.0	1.9	0.5	0.0
69°	3685.4	1034.8	54.8	32.8	21.1	17.3	10.8	5.2	0.9	0.0	0.0
70°	3536.4	946.3	48.3	29.0	19.2	16.4	10.3	3.7	0.9	0.0	0.0
72.5°	2922.3	673.7	36.5	21.5	14.1	14.5	9.4	2.3	0.9	0.0	0.0
75°	2128.7	409.4	26.2	15.0	8.9	10.8	6.6	0.9	0.5	0.0	0.0
77.5°	1184.3	193.0	16.4	8.4	5.6	6.6	3.3	0.0	0.0	0.0	0.0
80°	384.6	52.5	7.5	4.7	3.3	3.7	1.4	0.0	0.0	0.0	0.0
82.5°	71.2	15.0	4.2	2.3	0.9	0.9	0.0	0.0	0.0	0.0	0.0
85°	15.5	6.1	2.3	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.2	1.9	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)