

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P319848

Luminaire Tested: **GAN-SA4C-830-U-SL3**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P319848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA4C-830-U-SL3
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(4) 80 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
SPILL LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 22674 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B3 - U0 - G4


Input Watts (W): 225
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P319848
 CATALOG NUMBER: GAN-SA4C-830-U-SL3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.1 fc
 Type III - Medium - N/A

REPORT NUMBER: P319848
CATALOG NUMBER: GAN-SA4C-830-U-SL3

Luminous Intensity Polar Plot



REPORT NUMBER: P319848

CATALOG NUMBER: GAN-SA4C-830-U-SL3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3389.9	0.0	3389.9
	% Fixture	15.0	0.0	15.0
Street Side	Lumens	19284.1	0.0	19284.1
	% Fixture	85.0	0.0	85.0
Total	Lumens	22674.0	0.0	22674.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	542.0	2.4
10°-20°	1205.1	5.3
20°-30°	1531.6	6.8
30°-40°	1950.9	8.6
40°-50°	2766.5	12.2
50°-60°	4281.3	18.9
60°-70°	5828.5	25.7
70°-80°	3888.3	17.1
80°-90°	679.8	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	22674.0	100.0
0°-180°	22674.0	100.0

Coefficient of Utilization



REPORT NUMBER: P319848


CATALOG NUMBER: GAN-SA4C-830-U-SL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2173.7	9.6			
FM	(30°-60°)	7755.6	34.2			
FH	(60°-80°)	8731.5	38.5			G4/12000
FVH	(80°-90°)	623.3	2.7			G4/750
BL	(0°-30°)	1105.0	4.9	B3/2500		
BM	(30°-60°)	1243.2	5.5	B2/2500		
BH	(60°-80°)	985.2	4.3	B2/1000		G2/1000
BVH	(80°-90°)	56.5	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type III Medium





REPORT NUMBER: P319848

CATALOG NUMBER: GAN-SA4C-830-U-SL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	58°	65°	75°	85°
0°	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2
2.5°	6448.9	6440.2	6443.3	6437.0	6422.0	6407.0	6384.9	6388.8	6358.0	6312.2	6255.4
5°	6327.2	6324.1	6347.8	6361.2	6372.3	6363.6	6357.2	6365.1	6320.1	6256.9	6158.2
7.5°	6072.1	6037.4	6067.4	6112.4	6155.1	6187.4	6230.1	6235.6	6207.2	6140.8	6011.3
10°	5709.6	5676.4	5720.7	5790.9	5876.2	5953.6	6039.7	6055.5	6061.1	6001.0	5843.9
12.5°	5333.6	5308.4	5352.6	5451.3	5592.7	5712.0	5849.4	5873.1	5922.1	5881.8	5689.1
15°	4997.2	4987.7	5041.4	5138.6	5301.3	5483.7	5682.0	5725.4	5808.3	5794.9	5568.2
17.5°	4706.5	4704.2	4745.2	4847.1	5027.2	5257.8	5515.3	5588.8	5712.0	5727.8	5468.7
20°	4490.1	4485.4	4513.8	4588.8	4774.5	5035.9	5335.2	5436.3	5614.0	5669.3	5366.0
22.5°	4374.0	4373.2	4374.0	4409.6	4561.2	4804.5	5159.9	5283.1	5518.5	5622.7	5252.3
25°	4354.3	4351.9	4334.5	4330.6	4416.7	4611.0	4986.1	5122.0	5427.6	5590.3	5144.1
27.5°	4405.6	4408.8	4385.9	4348.7	4366.1	4483.8	4835.3	4980.6	5355.0	5584.0	5069.1
30°	4512.2	4510.7	4490.9	4452.2	4418.2	4436.4	4727.9	4873.2	5306.0	5611.7	5017.7
32.5°	4629.9	4638.6	4634.7	4613.3	4562.8	4490.1	4695.5	4837.6	5291.8	5678.0	4995.6
35°	4771.3	4780.8	4809.2	4825.8	4766.6	4649.7	4765.0	4888.2	5332.9	5802.8	5031.1
37.5°	4905.6	4930.0	5009.8	5080.1	5029.6	4899.2	4949.8	5037.5	5460.0	5999.5	5126.7
40°	5060.4	5081.7	5212.0	5361.3	5353.4	5218.3	5247.6	5306.0	5684.3	6281.4	5299.7
42.5°	5212.8	5255.5	5444.2	5655.9	5716.7	5597.4	5644.0	5674.8	6000.2	6655.0	5601.4
45°	5415.8	5461.6	5723.8	5978.9	6121.1	6054.0	6128.2	6140.0	6397.5	7163.7	6039.7
47.5°	5723.0	5775.2	6080.8	6348.6	6565.8	6572.9	6695.3	6690.5	6893.5	7745.7	6591.8
50°	6201.7	6276.7	6527.1	6777.4	7041.2	7188.1	7351.6	7328.7	7488.3	8365.8	7227.6
52.5°	6828.8	6863.5	7049.1	7233.9	7561.7	7891.1	8125.6	8105.1	8162.8	9003.1	7949.5
55°	7478.8	7504.9	7581.5	7682.6	8123.3	8660.4	9156.4	9124.0	8977.9	9665.0	8662.7
57.5°	8063.3	8116.2	8169.1	8210.9	8688.8	9464.4	10210.8	10213.1	9862.5	10379.0	9399.6
60°	8154.1	8200.7	8550.6	8880.7	9656.3	10537.0	11339.4	11315.7	10777.9	11153.8	10221.0
62.5°	7207.9	7312.9	7897.4	8775.7	10588.3	12498.9	12779.3	12750.0	11872.5	12108.7	11177.5
65°	5165.4	5284.7	5990.0	7309.8	10136.5	14660.6	15377.8	14984.4	13365.3	13283.2	12297.5
67.5°	2980.0	3008.4	3314.1	4374.0	7718.1	14773.5	19341.9	18791.4	15683.4	14615.6	12845.6
70°	2203.6	2202.8	2275.5	2691.7	4176.6	12057.4	21227.2	21720.8	18124.0	15053.9	12070.8
71°	1992.7	1995.1	2076.4	2450.0	3307.8	10092.3	20826.7	21907.2	18766.9	14837.5	11510.0
72.5°	1704.4	1712.3	1825.3	2197.3	2782.5	6959.9	19101.8	20788.8	19071.7	14303.6	10632.5
75°	1292.9	1311.1	1467.5	1852.1	2543.2	3529.7	14019.3	16600.4	16942.4	12621.3	7900.6
77.5°	922.5	943.0	1120.0	1557.5	2417.6	2660.1	9388.6	12108.7	12468.1	8088.5	3563.7
80°	582.9	607.4	740.8	1239.2	2271.5	2525.8	5899.9	8139.1	6798.8	2588.2	906.7
82.5°	342.0	360.9	459.7	809.6	1855.3	2432.6	3471.3	4511.4	2645.9	781.9	412.3
85°	198.2	206.9	286.7	515.8	1347.4	2296.0	2550.3	2521.9	1148.4	382.3	195.1
87.5°	92.4	102.7	169.8	269.3	748.0	1664.1	2015.6	1741.5	714.0	179.3	91.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P319848

CATALOG NUMBER: GAN-SA4C-830-U-SL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2	6282.2
2.5°	6227.7	6214.3	6158.2	6108.5	6056.3	5988.4	5913.4	5903.9	5858.1	5866.8	5851.0
5°	6104.5	6070.5	5935.5	5813.1	5668.5	5539.0	5398.4	5333.6	5240.4	5234.1	5210.4
7.5°	5928.4	5865.2	5655.9	5423.7	5191.5	4970.3	4751.5	4607.8	4460.9	4398.5	4393.0
10°	5730.1	5622.7	5314.7	4971.1	4636.2	4313.2	4000.4	3769.0	3560.5	3461.8	3457.8
12.5°	5542.2	5383.4	4960.8	4493.3	4035.2	3616.6	3187.7	2883.6	2622.2	2534.5	2497.4
15°	5382.6	5159.1	4616.5	4018.6	3462.6	2881.3	2393.1	2073.3	1831.6	1747.9	1732.1
17.5°	5227.8	4940.3	4263.4	3539.2	2867.0	2228.1	1739.2	1501.4	1372.7	1338.7	1338.0
20°	5073.8	4715.2	3894.6	3048.7	2291.3	1666.5	1337.2	1230.5	1187.1	1183.1	1176.8
22.5°	4899.2	4476.7	3506.8	2556.6	1788.1	1310.3	1136.5	1093.9	1088.4	1102.6	1102.6
25°	4735.7	4239.7	3113.5	2074.9	1390.9	1093.1	1014.9	1006.2	1021.2	1046.5	1048.9
27.5°	4583.3	4011.5	2729.6	1646.8	1114.4	962.8	930.4	940.7	967.5	996.8	997.5
30°	4457.7	3795.9	2356.8	1297.7	941.5	865.6	860.1	880.6	909.9	932.8	938.3
32.5°	4360.6	3611.8	1996.7	1043.3	828.5	793.0	797.7	815.1	833.3	845.9	854.6
35°	4315.6	3453.9	1664.1	879.9	756.6	736.9	743.2	752.7	760.6	770.1	777.2
37.5°	4323.5	3331.5	1367.2	778.0	708.5	698.2	698.2	698.2	698.2	702.9	703.7
40°	4396.9	3261.2	1125.5	713.2	676.1	665.0	656.3	648.4	642.1	645.3	643.7
42.5°	4584.9	3254.8	948.6	672.1	650.0	631.9	614.5	603.4	595.5	598.7	600.3
45°	4904.0	3333.8	829.3	642.9	625.5	597.9	575.8	563.9	558.4	568.7	570.2
47.5°	5317.1	3506.0	756.6	621.6	602.6	566.3	542.6	531.5	533.1	548.1	552.1
50°	5849.4	3785.6	721.9	608.2	586.8	539.4	515.0	505.5	510.2	531.5	536.3
52.5°	6433.9	4188.4	725.8	604.2	576.6	519.7	493.6	482.6	490.5	510.2	514.2
55°	7108.4	4672.6	791.4	609.7	561.6	507.1	476.3	457.3	463.6	481.8	484.9
57.5°	7857.9	5227.0	923.3	608.2	542.6	495.2	458.1	429.7	434.4	445.5	448.6
60°	8638.2	5896.8	1127.9	612.9	533.9	481.0	433.6	398.1	396.5	406.0	407.5
62.5°	9575.0	6671.6	1361.6	616.1	539.4	462.8	401.2	366.5	361.7	364.1	365.7
65°	10540.1	7232.4	1274.0	603.4	556.8	447.8	372.8	335.7	327.0	325.4	326.2
67.5°	10570.1	6631.3	893.3	578.1	563.9	439.9	351.5	309.6	295.4	289.9	289.1
70°	9479.4	5387.3	695.8	551.3	535.5	427.3	331.7	288.3	267.0	258.3	257.5
71°	8947.1	4959.3	659.5	537.9	514.2	414.7	323.0	278.8	256.7	247.2	245.6
72.5°	8112.2	4445.9	615.3	516.5	473.1	382.3	306.4	265.4	242.5	231.4	229.0
75°	5821.7	2907.3	528.4	460.5	391.7	304.9	268.5	238.5	218.8	205.4	203.8
77.5°	2243.1	1157.1	399.6	383.1	300.1	238.5	221.1	206.1	191.9	178.5	177.7
80°	693.5	517.3	291.4	288.3	217.2	177.7	172.2	168.2	162.7	148.5	145.3
82.5°	370.4	297.0	200.6	186.4	142.2	118.5	124.8	126.4	127.2	112.2	110.6
85°	176.9	157.2	112.9	105.8	82.9	66.3	76.6	82.9	83.7	68.7	64.0
87.5°	84.5	82.1	52.9	40.3	30.8	22.1	26.9	33.2	36.3	26.1	22.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)