

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P324949

Luminaire Tested: **GAN-SA5A-830-U-AFL-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P324949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA5A-830-U-AFL-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 80 CRI, 3000K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE
FRONTLINE OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15151 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 162
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P324949
 CATALOG NUMBER: GAN-SA5A-830-U-AFL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.3 fc
 Type II - Short - N/A

REPORT NUMBER: P324949
CATALOG NUMBER: GAN-SA5A-830-U-AFL-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P324949

CATALOG NUMBER: GAN-SA5A-830-U-AFL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	755.9	0.0	755.9
	% Fixture	5.0	0.0	5.0
Street Side	Lumens	14395.1	0.0	14395.1
	% Fixture	95.0	0.0	95.0
Total	Lumens	15151.0	0.0	15151.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.5	2.1
10°-20°	857.0	5.7
20°-30°	1463.1	9.7
30°-40°	2348.1	15.5
40°-50°	3752.3	24.8
50°-60°	4020.7	26.5
60°-70°	2064.3	13.6
70°-80°	312.7	2.1
80°-90°	20.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15151.0	100.0
0°-180°	15151.0	100.0

Coefficient of Utilization



REPORT NUMBER: P324949


CATALOG NUMBER: GAN-SA5A-830-U-AFL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2264.8	14.9			
FM	(30°-60°)	9803.4	64.7			
FH	(60°-80°)	2307.4	15.2			G2/5000
FVH	(80°-90°)	19.5	0.1			G1/100
BL	(0°-30°)	367.8	2.4	B1/500		
BM	(30°-60°)	317.7	2.1	B1/1000		
BH	(60°-80°)	69.7	0.5	B0/110		G0/110
BVH	(80°-90°)	0.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type II Short





REPORT NUMBER: P324949

CATALOG NUMBER: GAN-SA5A-830-U-AFL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	54°	55°	65°	75°	85°
0°	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2
2.5°	4258.2	4194.7	4196.7	4167.9	4062.6	3980.1	3894.4	3874.1	3740.7	3600.6	3465.8
5°	4994.3	4947.8	4936.7	4881.1	4734.5	4579.5	4413.3	4374.7	4113.6	3827.0	3545.0
7.5°	5372.5	5373.1	5364.0	5343.7	5252.1	5101.6	4898.8	4858.2	4502.9	4073.0	3627.5
10°	5262.6	5287.4	5338.5	5405.9	5475.9	5456.9	5304.4	5267.8	4881.8	4333.4	3719.1
12.5°	5006.1	5009.3	5066.3	5176.8	5378.4	5585.1	5587.7	5575.3	5243.6	4605.6	3819.8
15°	4878.5	4890.9	4911.9	4983.2	5174.2	5505.3	5742.2	5759.8	5575.3	4894.8	3927.1
17.5°	4962.2	4979.9	4962.2	4970.7	5081.3	5379.0	5769.0	5814.1	5865.2	5180.8	4028.5
20°	5189.3	5205.6	5174.2	5139.6	5161.1	5342.4	5750.0	5810.9	6092.2	5434.6	4113.6
22.5°	5495.5	5502.0	5454.3	5397.3	5381.6	5466.7	5765.7	5828.5	6274.1	5664.3	4167.3
25°	5832.5	5838.3	5778.8	5713.4	5676.1	5710.8	5894.6	5941.7	6434.4	5883.5	4198.0
27.5°	6199.5	6204.8	6130.2	6049.7	6006.5	6007.8	6107.3	6157.6	6605.2	6133.4	4222.9
30°	6587.5	6584.9	6516.2	6404.3	6349.4	6348.0	6413.5	6464.5	6852.5	6454.0	4256.9
32.5°	7023.3	7018.1	6920.6	6781.9	6719.7	6728.9	6787.1	6816.5	7159.4	6795.6	4317.7
35°	7597.1	7582.1	7434.8	7262.8	7148.3	7145.0	7194.1	7217.6	7550.7	7209.1	4419.2
37.5°	8341.7	8328.0	8128.4	7878.5	7717.5	7657.3	7715.5	7745.6	8108.8	7739.8	4582.1
40°	9075.8	9062.1	8943.7	8714.7	8466.7	8322.1	8367.9	8399.9	8805.6	8383.6	4787.5
42.5°	9582.3	9594.0	9635.3	9654.2	9422.0	9118.4	9139.3	9172.7	9537.8	9071.9	5022.4
45°	9715.7	9741.3	9974.2	10431.6	10518.6	10281.7	10062.5	10080.8	10281.7	9760.2	5257.3
47.5°	9314.7	9361.8	9811.3	10661.9	11398.6	11566.1	11151.3	11127.1	10995.6	10317.1	5424.2
50°	8403.2	8446.4	9028.7	10287.0	11665.6	12792.3	12456.0	12384.6	11621.7	10650.1	5483.1
52.5°	7084.1	7136.5	7609.5	9106.6	11162.4	13339.3	13691.3	13631.8	12081.1	10676.3	5492.9
55°	5002.8	5066.3	5566.8	6979.5	9567.9	12904.2	14129.0	14111.4	12462.5	10606.9	5513.8
57.5°	2811.5	2857.3	3397.1	4474.1	7007.6	11239.6	13671.7	13788.8	12692.8	10486.5	5545.2
60°	1248.4	1260.8	1540.2	2227.2	4102.5	8589.7	12362.4	12560.0	12495.2	10325.6	5598.2
62.5°	692.3	681.8	681.8	925.8	1783.0	5317.5	10080.8	10407.3	11651.8	10135.2	5600.8
65°	542.4	532.6	504.5	508.4	679.2	2360.1	6980.8	7561.1	10050.1	9577.0	5412.4
67.5°	460.0	451.5	423.3	412.2	422.0	778.6	3835.5	4438.1	7625.9	8126.4	4688.1
70°	388.7	382.8	368.4	354.6	329.8	384.7	1467.6	1877.2	4699.2	5405.9	3200.2
72.5°	312.8	310.1	315.4	303.6	273.5	256.5	501.9	607.8	2110.8	2412.4	1318.4
75°	269.6	268.3	270.9	259.1	225.1	178.6	255.2	278.7	595.4	590.2	267.0
77.5°	175.4	177.3	224.4	219.2	193.7	119.1	132.2	142.6	180.6	135.4	81.1
80°	111.9	110.6	113.8	181.9	174.0	90.9	66.1	69.4	87.0	66.7	39.3
82.5°	68.0	66.7	74.6	85.1	87.7	63.5	40.6	41.2	54.3	43.2	20.9
85°	5.9	7.9	45.1	41.9	30.1	19.6	19.6	20.9	28.8	25.5	11.8
87.5°	0.0	0.0	7.9	11.8	6.5	7.2	7.2	7.9	11.1	11.1	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P324949

CATALOG NUMBER: GAN-SA5A-830-U-AFL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2	3393.2
2.5°	3395.8	3327.8	3190.4	3058.2	2946.3	2838.4	2715.4	2593.7	2536.7	2513.8	2490.3
5°	3401.7	3261.7	2978.4	2693.1	2397.4	2131.1	1904.0	1671.1	1554.6	1503.6	1480.0
7.5°	3409.6	3196.3	2738.3	2259.3	1783.0	1421.8	1106.4	903.6	815.9	802.2	768.2
10°	3410.9	3117.1	2459.5	1780.4	1195.4	857.1	659.5	554.8	516.2	509.7	498.6
12.5°	3413.5	3023.5	2150.0	1318.4	796.9	573.2	477.0	442.3	431.8	431.2	431.2
15°	3421.4	2925.4	1828.8	950.0	572.5	454.1	418.8	405.0	401.1	403.1	402.4
17.5°	3421.4	2809.6	1513.4	708.0	462.6	408.3	388.7	379.5	378.2	380.2	380.8
20°	3396.5	2668.9	1224.2	550.9	410.2	378.8	361.2	352.7	349.4	350.7	351.4
22.5°	3336.9	2496.2	988.7	456.0	375.6	352.0	333.0	320.0	314.7	315.4	315.4
25°	3244.0	2291.4	773.4	394.5	347.4	323.2	301.0	285.9	282.7	282.0	283.3
27.5°	3125.0	2065.0	615.7	347.4	314.1	291.2	268.9	256.5	253.9	254.5	255.2
30°	3007.8	1830.1	485.5	307.5	276.8	255.2	238.2	232.3	232.3	234.2	234.9
32.5°	2900.5	1604.4	384.1	272.8	243.4	223.8	214.0	213.3	216.6	217.9	218.5
35°	2808.3	1395.6	318.0	246.0	217.2	200.2	196.9	199.6	203.5	206.1	206.8
37.5°	2742.8	1209.2	278.1	223.8	196.9	183.2	182.6	187.8	193.0	198.9	200.2
40°	2715.4	1051.5	250.6	204.1	180.6	170.1	168.2	175.4	185.2	193.7	195.0
42.5°	2692.5	922.6	227.0	185.2	167.5	152.5	151.8	161.0	172.7	181.2	183.2
45°	2672.8	819.2	205.5	164.9	150.5	130.9	132.8	144.6	153.8	162.9	164.9
47.5°	2632.3	734.1	181.9	143.3	124.3	111.9	115.8	126.3	133.5	147.2	149.2
50°	2559.6	664.8	157.7	117.1	101.4	96.8	102.7	109.9	119.1	130.9	132.2
52.5°	2510.6	612.4	136.7	98.1	83.8	85.1	90.9	93.6	98.8	103.4	102.1
55°	2482.4	583.6	119.7	85.1	71.3	75.2	76.6	73.3	70.7	66.1	64.1
57.5°	2479.2	557.5	106.7	73.9	62.8	64.8	60.2	49.1	39.9	34.7	33.4
60°	2473.9	525.4	96.2	62.2	55.6	53.0	43.2	26.8	19.0	17.7	17.7
62.5°	2417.0	475.7	88.3	52.3	47.1	39.9	24.9	12.4	10.5	11.1	11.1
65°	2235.8	406.3	80.5	42.5	37.3	28.8	12.4	7.2	3.9	4.6	4.6
67.5°	1900.8	323.9	72.0	32.7	28.1	18.3	7.2	3.3	0.0	0.0	0.0
70°	1272.6	200.9	60.9	22.9	18.3	11.1	5.2	0.7	0.0	0.0	0.0
72.5°	488.1	108.6	49.1	13.7	11.8	7.9	3.3	0.0	0.0	0.0	0.0
75°	109.9	71.3	34.0	9.8	8.5	5.2	1.3	0.0	0.0	0.0	0.0
77.5°	41.9	51.7	19.6	6.5	5.9	3.3	0.0	0.0	0.0	0.0	0.0
80°	20.3	30.8	9.2	3.9	3.3	1.3	0.0	0.0	0.0	0.0	0.0
82.5°	10.5	11.8	3.9	2.0	1.3	0.0	0.0	0.0	0.0	0.0	0.0
85°	5.9	5.9	2.0	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	3.3	2.0	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)