

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P318893

Luminaire Tested: **GAN-SA9C-830-U-T4FT**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA9C-830-U-T4FT
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(9) 80 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV
FORWARD THROW OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 50550 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 501
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318893
 CATALOG NUMBER: GAN-SA9C-830-U-T4FT

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 12.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P318893
CATALOG NUMBER: GAN-SA9C-830-U-T4FT

Luminous Intensity Polar Plot



REPORT NUMBER: P318893

CATALOG NUMBER: GAN-SA9C-830-U-T4FT


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10854.4	0.0	10854.4
	% Fixture	21.5	0.0	21.5
Street Side	Lumens	39695.6	0.0	39695.6
	% Fixture	78.5	0.0	78.5
Total	Lumens	50550.0	0.0	50550.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	714.6	1.4
10°-20°	1935.3	3.8
20°-30°	3160.7	6.3
30°-40°	4707.0	9.3
40°-50°	6751.2	13.4
50°-60°	9268.3	18.3
60°-70°	11603.5	23.0
70°-80°	10497.2	20.8
80°-90°	1912.1	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	50550.0	100.0
0°-180°	50550.0	100.0

Coefficient of Utilization



REPORT NUMBER: P318893


CATALOG NUMBER: GAN-SA9C-830-U-T4FT

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2903.3	5.7			
FM	(30°-60°)	15502.6	30.7			
FH	(60°-80°)	19766.8	39.1			G5
FVH	(80°-90°)	1522.8	3.0			G5
BL	(0°-30°)	2907.3	5.8	B4/5000		
BM	(30°-60°)	5223.9	10.3	B4/8500		
BH	(60°-80°)	2333.9	4.6	B3/2500		G3/2500
BVH	(80°-90°)	389.3	0.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5

Type IV Short





REPORT NUMBER: P318893

CATALOG NUMBER: GAN-SA9C-830-U-T4FT

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2
2.5°	7337.2	7309.3	7361.7	7368.7	7414.1	7431.5	7494.4	7592.2	7672.5	7765.1	7848.9
5°	6672.0	6652.8	6726.1	6778.5	6878.0	6919.9	7068.3	7276.1	7461.2	7670.8	7861.1
7.5°	6039.9	6029.4	6111.5	6230.2	6345.4	6403.1	6659.7	6961.8	7270.9	7609.6	7901.2
10°	5507.3	5503.8	5582.4	5699.4	5868.8	5933.4	6265.1	6663.2	7096.3	7562.5	7969.3
12.5°	5208.7	5220.9	5257.6	5355.4	5512.5	5577.1	5945.6	6413.5	6949.6	7546.8	8068.9
15°	5282.1	5301.3	5238.4	5234.9	5346.7	5397.3	5743.0	6235.4	6844.8	7573.0	8213.8
17.5°	5594.6	5598.1	5432.2	5327.4	5395.5	5421.7	5680.2	6134.2	6783.7	7632.3	8395.4
20°	6034.6	6025.9	5732.6	5557.9	5594.6	5601.6	5769.2	6135.9	6778.5	7735.4	8631.1
22.5°	6617.8	6553.2	6158.6	5921.1	5912.4	5901.9	5998.0	6265.1	6855.3	7903.0	8912.3
25°	7379.2	7318.0	6775.0	6450.2	6380.4	6354.2	6368.1	6541.0	7007.2	8082.8	9226.6
27.5°	8226.0	8119.5	7595.7	7136.4	6991.5	6954.8	6871.0	6930.4	7173.1	8255.7	9600.2
30°	8935.0	8877.3	8419.8	7875.1	7703.9	7651.6	7431.5	7366.9	7412.3	8491.4	10071.7
32.5°	9331.3	9292.9	9015.3	8575.3	8416.4	8343.0	8032.2	7903.0	7796.5	8863.4	10710.8
35°	9811.5	9787.1	9619.4	9299.9	9064.2	8987.3	8746.4	8611.9	8337.8	9375.0	11536.7
37.5°	10422.7	10396.5	10400.0	10141.5	9860.4	9788.8	9629.9	9488.5	9039.7	10047.2	12434.2
40°	11114.1	11063.5	11044.3	11032.1	10854.0	10813.8	10730.0	10537.9	9919.8	10850.5	13319.5
42.5°	12154.8	11975.0	11590.8	11735.8	11912.1	11891.2	11959.3	11683.4	10897.6	11800.4	14183.8
45°	13158.9	12863.8	12200.2	12231.7	12617.6	12734.5	13244.4	13048.8	11957.5	12841.1	15077.9
47.5°	13616.3	13392.8	12828.8	12830.6	13213.0	13455.7	14573.2	14433.5	13071.5	14023.2	16169.2
50°	14128.0	13904.5	13398.1	13588.4	13921.9	14180.3	15856.6	15785.0	14131.4	15317.1	17477.0
52.5°	14686.7	14307.8	13986.5	14327.0	14795.0	15095.3	17141.8	16946.2	15104.0	16619.7	18980.5
55°	14693.7	14590.7	14835.1	15084.8	15785.0	16153.5	18488.0	17971.2	15896.8	17899.6	20204.5
57.5°	15530.1	15362.5	15881.1	15996.3	16911.3	17326.9	19827.3	18863.5	16703.5	18880.9	20864.5
60°	16637.1	16494.0	16918.3	17222.1	18304.7	18860.0	21257.4	19780.2	17337.3	19621.3	20833.1
62.5°	18549.2	18386.8	18381.5	18807.6	20265.6	20911.7	22862.1	20679.4	17588.8	19768.0	19944.3
65°	21348.2	21089.8	20602.6	20805.2	22973.9	23618.2	24655.4	21330.8	17257.0	18982.2	17655.1
67.5°	24072.2	24063.4	23464.5	23880.1	26549.9	27066.8	26698.4	21395.4	16221.6	16246.0	13593.6
70°	26787.4	26822.3	26721.1	28166.9	31381.5	31919.3	28874.0	20527.5	13894.0	11732.3	8144.0
72.5°	28938.6	28929.9	29439.8	33167.8	37651.8	37531.4	30707.5	17897.9	9975.7	6333.2	3892.1
75°	27545.2	27241.4	28760.5	35643.8	41306.5	40718.1	29148.2	12484.8	5177.3	2882.9	2095.4
77.5°	17966.0	18254.1	20483.9	29445.0	36131.0	35415.1	21384.9	5825.1	2439.3	1891.1	1519.1
80°	6506.1	6809.9	9591.5	16679.1	24892.9	24775.9	10530.9	2393.9	1650.1	1428.3	1107.0
82.5°	2238.5	2350.3	3783.9	7407.1	14054.6	14578.5	3962.0	1360.2	1199.6	1012.8	757.8
85°	878.3	1005.8	1730.4	3563.9	7089.3	7141.7	1604.7	813.7	834.7	663.5	415.6
87.5°	333.5	405.1	827.7	1655.3	3237.3	2973.7	574.5	387.6	474.9	394.6	197.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P318893

CATALOG NUMBER: GAN-SA9C-830-U-T4FT

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2	7901.2
2.5°	7913.5	7950.1	8027.0	8079.4	8135.2	8150.9	8157.9	8171.9	8185.9	8180.6	8182.4
5°	7962.4	8034.0	8157.9	8210.3	8234.8	8206.8	8152.7	8109.0	8077.6	8060.1	8054.9
7.5°	8042.7	8144.0	8276.7	8267.9	8212.1	8088.1	7948.4	7843.6	7756.3	7724.9	7707.4
10°	8149.2	8267.9	8360.5	8261.0	8098.6	7883.8	7674.3	7511.9	7380.9	7330.3	7321.5
12.5°	8285.4	8405.9	8423.3	8212.1	7943.2	7649.8	7365.2	7150.4	6954.8	6892.0	6878.0
15°	8461.8	8575.3	8467.0	8126.5	7751.1	7356.5	6988.0	6696.4	6490.4	6413.5	6385.6
17.5°	8646.8	8755.1	8475.7	7985.1	7499.6	7009.0	6546.2	6247.7	6011.9	5922.9	5912.4
20°	8868.6	8917.5	8439.1	7782.5	7153.9	6558.5	6071.3	5790.2	5664.5	5601.6	5594.6
22.5°	9142.7	9090.4	8355.2	7508.4	6715.6	6038.1	5641.8	5510.8	5479.4	5465.4	5470.6
25°	9432.6	9272.0	8231.3	7150.4	6162.1	5517.8	5327.4	5364.1	5406.0	5400.8	5400.8
27.5°	9752.1	9457.1	8040.9	6675.5	5549.2	5091.7	5114.4	5248.9	5311.7	5310.0	5308.2
30°	10162.5	9666.6	7798.2	6104.5	4976.5	4791.4	4929.3	5093.5	5179.0	5175.5	5177.3
32.5°	10667.1	9897.1	7468.2	5467.1	4562.6	4569.6	4728.5	4890.9	4990.4	4981.7	4983.5
35°	11257.3	10155.5	7021.2	4838.5	4288.5	4393.3	4519.0	4632.5	4726.8	4714.6	4702.3
37.5°	11899.9	10408.7	6427.5	4276.3	4065.0	4229.1	4333.9	4353.1	4396.8	4365.3	4342.6
40°	12511.0	10602.5	5662.7	3815.3	3839.7	4089.4	4157.5	4080.7	4002.1	3991.7	3960.2
42.5°	13043.6	10667.1	4889.2	3446.9	3602.3	3942.8	3984.7	3824.0	3682.6	3616.2	3588.3
45°	13605.9	10689.8	4168.0	3137.8	3373.5	3811.8	3857.2	3642.4	3443.4	3300.2	3253.0
47.5°	14341.0	10854.0	3607.5	2909.1	3198.9	3724.5	3789.1	3497.5	3239.1	3034.8	2991.1
50°	15303.1	11178.7	3151.8	2734.4	3085.4	3666.9	3740.2	3356.1	3071.4	2825.2	2781.6
52.5°	16371.7	11477.3	2783.3	2593.0	2975.4	3565.6	3677.4	3254.8	2914.3	2631.4	2584.3
55°	17119.1	11248.6	2486.5	2446.3	2832.2	3420.7	3590.0	3169.2	2689.0	2442.8	2400.9
57.5°	17262.3	10466.3	2261.2	2294.4	2659.4	3239.1	3455.6	2978.9	2566.8	2360.8	2317.1
60°	16871.1	9376.7	2093.6	2154.7	2474.3	3010.3	3204.2	2844.4	2449.8	2273.5	2236.8
62.5°	15888.1	8261.0	1969.6	2029.0	2301.4	2778.1	3047.0	2703.0	2331.1	2173.9	2137.3
65°	13902.7	6935.6	1850.9	1917.3	2140.8	2577.3	2905.6	2572.1	2214.1	2093.6	2058.7
67.5°	10494.3	5194.7	1739.1	1798.5	1997.6	2402.7	2751.9	2442.8	2100.6	2023.8	1981.9
70°	6179.6	3253.0	1611.7	1674.5	1847.4	2221.1	2587.8	2301.4	1959.2	1924.2	1870.1
72.5°	2875.9	1957.4	1466.8	1527.9	1658.8	1978.4	2376.5	2116.3	1791.5	1714.7	1641.4
75°	1716.4	1431.8	1295.6	1349.8	1442.3	1719.9	2111.1	1927.7	1632.6	1531.4	1454.5
77.5°	1283.4	1094.8	1107.0	1164.7	1239.8	1505.2	1870.1	1779.3	1510.4	1431.8	1379.4
80°	923.7	831.2	902.8	965.6	1044.2	1369.0	1791.5	1644.9	1365.5	1260.7	1211.8
82.5°	616.4	597.2	679.2	743.9	820.7	1197.8	1683.3	1440.6	1166.4	1033.7	925.5
85°	340.5	359.7	457.5	485.4	551.8	843.4	1379.4	1157.7	878.3	707.2	675.8
87.5°	141.4	165.9	246.2	237.5	293.4	502.9	908.0	698.5	558.8	417.3	324.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)