

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P323361

Luminaire Tested: **GAN-SA7B-830-U-SL2-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P323361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-21)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA7B-830-U-SL2-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(7) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26605 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B3 - U0 - G4


Input Watts (W): 295
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P323361
 CATALOG NUMBER: GAN-SA7B-830-U-SL2-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.8 fc
 Type III - Medium - N/A

REPORT NUMBER: P323361
CATALOG NUMBER: GAN-SA7B-830-U-SL2-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P323361

CATALOG NUMBER: GAN-SA7B-830-U-SL2-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3136.1	0.0	3136.1
	% Fixture	11.8	0.0	11.8
Street Side	Lumens	23468.9	0.0	23468.9
	% Fixture	88.2	0.0	88.2
Total	Lumens	26605.0	0.0	26605.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	562.2	2.1
10°-20°	1230.7	4.6
20°-30°	1704.5	6.4
30°-40°	2376.6	8.9
40°-50°	3694.1	13.9
50°-60°	5930.4	22.3
60°-70°	6708.3	25.2
70°-80°	3939.9	14.8
80°-90°	458.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26605.0	100.0
0°-180°	26605.0	100.0

Coefficient of Utilization



REPORT NUMBER: P323361


CATALOG NUMBER: GAN-SA7B-830-U-SL2-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2424.3	9.1			
FM	(30°-60°)	10864.7	40.8			
FH	(60°-80°)	9731.8	36.6			G4/12000
FVH	(80°-90°)	448.0	1.7			G3/500
BL	(0°-30°)	1073.0	4.0	B3/2500		
BM	(30°-60°)	1136.4	4.3	B2/2500		
BH	(60°-80°)	916.3	3.4	B2/1000		G2/1000
BVH	(80°-90°)	10.3	0.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type III Medium



REPORT NUMBER: P323361

CATALOG NUMBER: GAN-SA7B-830-U-SL2-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1
2.5°	6782.8	6765.9	6779.4	6808.7	6823.3	6823.3	6834.6	6821.1	6825.6	6792.9	6745.6
5°	6358.4	6332.5	6369.6	6451.8	6553.1	6639.8	6768.2	6835.7	6842.5	6843.6	6788.4
7.5°	5901.3	5877.7	5932.8	6029.7	6160.2	6321.2	6545.3	6741.1	6752.4	6858.2	6817.7
10°	5529.8	5512.9	5577.1	5680.7	5833.8	6013.9	6288.6	6561.0	6593.7	6827.8	6813.2
12.5°	5234.9	5221.3	5282.1	5401.5	5558.0	5757.2	6044.3	6360.6	6404.5	6759.2	6790.7
15°	5019.8	5017.6	5068.2	5183.1	5356.4	5542.2	5836.0	6174.9	6225.5	6684.9	6787.3
17.5°	4907.3	4910.6	4947.8	5045.7	5194.3	5379.0	5660.4	6018.4	6073.6	6618.4	6804.2
20°	4896.0	4899.4	4919.6	4974.8	5095.3	5258.5	5517.4	5886.7	5944.1	6568.9	6831.2
22.5°	4995.1	4992.8	4998.4	4992.8	5060.4	5184.2	5422.9	5785.4	5851.8	6536.3	6852.6
25°	5185.3	5181.9	5179.7	5138.0	5093.0	5159.4	5383.5	5727.9	5791.0	6512.6	6865.0
27.5°	5449.9	5447.6	5444.2	5375.6	5240.5	5198.8	5388.0	5706.6	5759.5	6493.5	6862.7
30°	5797.7	5813.5	5809.0	5713.3	5502.8	5319.3	5435.2	5695.3	5741.5	6456.3	6839.1
32.5°	6206.4	6237.9	6262.7	6160.2	5896.8	5558.0	5544.4	5707.7	5741.5	6428.2	6796.3
35°	6630.8	6671.3	6762.5	6726.5	6379.8	5917.1	5732.4	5782.0	5810.1	6443.9	6776.0
37.5°	7048.5	7096.9	7295.0	7399.7	7012.5	6392.2	6025.1	5965.5	5980.1	6539.6	6798.6
40°	7533.7	7606.9	7907.4	8076.3	7767.8	7028.2	6463.1	6280.7	6286.3	6750.1	6903.3
42.5°	8170.9	8246.3	8571.7	8836.2	8618.9	7832.0	7057.5	6762.5	6756.9	7144.2	7149.8
45°	8947.7	9026.5	9363.1	9656.9	9559.0	8784.4	7818.5	7466.1	7459.4	7765.6	7617.0
47.5°	9828.0	9905.7	10206.3	10509.1	10614.9	9896.7	8787.8	8426.4	8410.7	8629.1	8338.6
50°	10583.4	10634.1	10911.0	11318.5	11795.9	11263.4	9993.5	9645.6	9628.8	9776.2	9398.0
52.5°	10858.1	10887.4	11168.8	11739.6	12930.7	13114.2	11577.5	11129.4	11117.0	11181.2	10808.6
55°	10302.0	10354.9	10700.5	11547.1	13545.3	15205.8	13576.9	12966.7	12873.2	12734.8	12283.3
57.5°	8786.7	8871.1	9242.6	10368.4	13258.3	16865.2	16515.1	15044.9	14907.5	14060.9	13482.3
60°	6583.5	6687.1	6995.6	8210.3	11726.1	17456.3	19725.8	17360.6	17051.0	15116.9	14584.4
62.5°	4517.7	4569.5	4778.9	5570.3	8635.8	16488.1	22411.9	20462.1	19897.0	16265.2	15776.6
65°	3450.5	3468.5	3554.1	3826.5	5142.5	13393.3	23480.3	24554.3	23870.9	17638.6	17013.8
67.5°	2780.7	2766.0	2884.2	3273.8	3443.7	8170.9	22234.1	28425.8	28106.1	19474.8	18258.9
69°	2451.9	2431.7	2552.1	3004.7	3234.4	5401.5	19876.7	29305.1	29325.3	20444.1	18344.5
70°	2206.5	2220.0	2339.4	2844.8	3163.4	4239.7	17625.1	29081.0	29240.9	20806.6	17831.2
72.5°	1473.6	1509.7	1749.5	2361.9	3041.8	3208.5	10642.0	24955.1	25569.7	19990.4	15298.2
75°	830.8	857.8	1142.7	1781.0	2866.2	3055.4	5621.0	18385.0	18979.4	16716.6	11797.0
77.5°	407.5	422.2	646.2	1149.4	2396.8	2911.3	3188.2	12488.2	13167.1	10911.0	6672.5
80°	172.2	180.1	323.1	709.2	1713.4	2778.4	2367.5	7685.7	7770.1	4274.6	1777.6
82.5°	66.4	68.7	136.2	442.4	1088.6	2166.0	1980.2	3644.1	3556.3	804.9	405.3
85°	7.9	9.0	49.5	265.7	605.7	1114.5	1608.7	1570.5	1453.4	159.9	208.3
87.5°	0.0	0.0	3.4	81.1	180.1	522.4	836.5	651.8	587.7	51.8	108.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P323361

CATALOG NUMBER: GAN-SA7B-830-U-SL2-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1	6723.1
2.5°	6706.2	6695.0	6634.2	6546.4	6463.1	6359.5	6260.4	6200.8	6153.5	6122.0	6159.1
5°	6724.3	6674.7	6490.1	6253.7	6021.8	5760.6	5517.4	5311.4	5230.4	5140.3	5180.8
7.5°	6718.6	6625.2	6293.1	5872.0	5446.5	5006.3	4589.8	4268.9	4102.3	3939.1	3980.7
10°	6690.5	6532.9	6029.7	5406.0	4768.8	4136.1	3545.1	3095.9	2844.8	2617.4	2650.1
12.5°	6628.6	6409.0	5718.9	4872.4	4020.1	3185.9	2493.6	1918.3	1609.9	1473.6	1490.5
15°	6591.4	6288.6	5390.2	4332.0	3220.8	2218.9	1524.3	1133.7	992.9	947.9	953.5
17.5°	6573.4	6172.6	5050.2	3713.9	2403.5	1412.8	985.1	869.1	838.7	830.8	833.1
20°	6555.4	6055.5	4700.1	3102.6	1656.0	950.2	809.4	775.7	764.4	754.3	756.5
22.5°	6525.0	5943.0	4324.1	2483.5	1116.8	771.2	729.5	696.9	673.2	660.8	663.1
25°	6487.8	5824.8	3940.2	1849.6	815.1	687.8	648.4	602.3	574.1	551.6	552.8
27.5°	6428.2	5679.5	3543.9	1346.4	684.5	615.8	562.9	512.2	464.9	439.1	439.1
30°	6344.9	5515.2	3103.8	963.7	613.5	544.9	480.7	417.7	367.0	343.4	341.1
32.5°	6252.6	5344.1	2659.1	730.6	557.3	478.5	405.3	338.9	293.8	274.7	273.6
35°	6173.8	5159.4	2215.5	612.4	501.0	414.3	334.4	278.1	242.0	226.3	225.2
37.5°	6123.1	4974.8	1783.2	547.1	450.3	354.6	280.3	229.7	203.8	191.4	190.3
40°	6115.2	4837.5	1388.1	497.6	403.0	301.7	234.2	194.8	171.1	157.6	156.5
42.5°	6217.7	4758.7	1065.0	455.9	354.6	255.6	199.3	166.6	141.8	128.3	127.2
45°	6486.7	4783.4	819.6	418.8	306.2	216.1	168.9	138.5	116.0	105.8	103.6
47.5°	6977.6	4954.5	651.8	381.6	260.1	183.5	144.1	114.8	95.7	85.6	84.4
50°	7851.2	5356.4	544.9	341.1	217.3	156.5	119.3	93.4	77.7	68.7	67.5
52.5°	9010.7	6072.4	486.3	301.7	180.1	132.8	97.9	74.3	60.8	54.0	52.9
55°	10289.6	6939.3	448.1	258.9	147.5	110.3	77.7	58.5	47.3	41.7	39.4
57.5°	11538.1	7690.2	412.0	217.3	122.7	90.1	61.9	46.2	37.2	31.5	30.4
60°	12685.2	8380.3	370.4	174.5	100.2	70.9	48.4	36.0	29.3	23.6	23.6
62.5°	13913.5	8913.9	313.0	136.2	82.2	54.0	39.4	32.6	23.6	20.3	19.1
65°	15214.9	9310.2	245.4	105.8	64.2	40.5	32.6	33.8	19.1	14.6	13.5
67.5°	16176.3	9231.4	181.2	83.3	49.5	31.5	31.5	36.0	16.9	11.3	10.1
69°	15964.6	8590.8	152.0	72.0	42.8	27.0	29.3	36.0	15.8	10.1	9.0
70°	15351.1	7881.6	134.0	64.2	38.3	24.8	28.1	34.9	14.6	10.1	9.0
72.5°	12784.3	5936.2	104.7	48.4	30.4	20.3	23.6	30.4	14.6	10.1	7.9
75°	9616.4	3799.5	79.9	34.9	22.5	15.8	18.0	22.5	14.6	9.0	7.9
77.5°	5232.6	1370.1	57.4	23.6	15.8	12.4	12.4	16.9	13.5	6.8	4.5
80°	1345.3	344.5	36.0	15.8	12.4	9.0	7.9	11.3	7.9	1.1	0.0
82.5°	332.1	77.7	19.1	11.3	9.0	3.4	3.4	5.6	3.4	0.0	0.0
85°	182.4	38.3	12.4	7.9	4.5	0.0	0.0	1.1	0.0	0.0	0.0
87.5°	93.4	11.3	3.4	2.3	1.1	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)