

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P323041

Luminaire Tested: **GAN-SA7B-830-U-T4W-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P323041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-19)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA7B-830-U-T4W-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(7) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23281 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 295
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P323041
 CATALOG NUMBER: GAN-SA7B-830-U-T4W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P323041
CATALOG NUMBER: GAN-SA7B-830-U-T4W-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P323041

CATALOG NUMBER: GAN-SA7B-830-U-T4W-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2389.3	0.0	2389.3
	% Fixture	10.3	0.0	10.3
Street Side	Lumens	20891.7	0.0	20891.7
	% Fixture	89.7	0.0	89.7
Total	Lumens	23281.0	0.0	23281.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.2	1.0
10°-20°	704.4	3.0
20°-30°	1107.8	4.8
30°-40°	1588.5	6.8
40°-50°	2745.6	11.8
50°-60°	5424.1	23.3
60°-70°	7580.7	32.6
70°-80°	3662.3	15.7
80°-90°	235.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23281.0	100.0
0°-180°	23281.0	100.0

Coefficient of Utilization



REPORT NUMBER: P323041


CATALOG NUMBER: GAN-SA7B-830-U-T4W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1414.6	6.1			
FM	(30°-60°)	8560.9	36.8			
FH	(60°-80°)	10682.8	45.9			G4/12000
FVH	(80°-90°)	233.4	1.0			G3/500
BL	(0°-30°)	629.7	2.7	B2/1000		
BM	(30°-60°)	1197.3	5.1	B2/2500		
BH	(60°-80°)	560.2	2.4	B2/1000		G2/1000
BVH	(80°-90°)	2.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4

Type IV Short





REPORT NUMBER: P323041

CATALOG NUMBER: GAN-SA7B-830-U-T4W-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	46°	55°	65°	75°	85°
0°	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7
2.5°	2591.4	2588.1	2572.8	2566.3	2529.2	2507.3	2498.6	2471.3	2432.0	2392.7	2349.0
5°	2886.1	2885.0	2856.6	2829.3	2759.5	2694.0	2682.0	2618.7	2530.2	2447.3	2364.3
7.5°	3187.4	3173.2	3144.8	3092.4	2990.9	2886.1	2876.3	2786.8	2661.2	2541.2	2422.2
10°	3442.8	3434.1	3396.9	3317.3	3198.3	3079.3	3067.3	2957.0	2815.1	2667.8	2516.1
12.5°	3641.5	3634.9	3585.8	3486.5	3359.8	3236.5	3220.1	3121.9	2970.1	2805.3	2626.3
15°	3762.6	3759.3	3699.3	3593.4	3469.0	3362.0	3347.8	3261.6	3120.8	2948.3	2746.4
17.5°	3791.0	3792.1	3729.9	3622.9	3520.3	3443.9	3433.0	3367.5	3249.6	3078.2	2866.4
20°	3727.7	3740.8	3685.1	3592.3	3529.0	3488.6	3479.9	3440.6	3341.3	3179.7	2962.5
22.5°	3638.2	3644.7	3606.5	3544.3	3518.1	3525.7	3521.4	3499.5	3415.5	3267.0	3057.5
25°	3583.6	3583.6	3560.7	3508.3	3525.7	3572.7	3573.8	3569.4	3502.8	3374.0	3173.2
27.5°	3581.4	3574.9	3548.7	3509.4	3557.4	3629.4	3633.8	3663.3	3621.8	3503.9	3317.3
30°	3668.7	3661.1	3605.4	3554.1	3615.3	3692.8	3703.7	3768.1	3747.3	3644.7	3477.7
32.5°	3872.9	3845.6	3722.2	3638.2	3684.0	3776.8	3791.0	3893.6	3926.4	3818.3	3632.7
35°	4152.3	4066.1	3888.1	3797.5	3801.9	3899.1	3912.2	4062.8	4159.9	3977.7	3752.8
37.5°	4537.6	4495.1	4205.8	3963.5	3983.1	4130.5	4168.7	4332.4	4305.1	4065.0	3889.2
40°	5382.5	5315.9	5008.1	4428.5	4156.7	4318.2	4330.2	4417.6	4419.7	4262.6	4173.0
42.5°	6533.0	6505.7	6181.5	5272.2	4498.3	4443.8	4465.6	4612.9	4777.8	4679.5	4675.2
45°	7806.9	7792.7	7448.8	6392.2	5189.3	4855.3	4882.6	5080.1	5395.6	5417.4	5556.1
47.5°	8831.8	8825.3	8627.7	7642.0	6247.0	5552.8	5561.5	5771.1	6325.6	6599.6	6821.2
50°	9766.2	9797.9	9641.8	8994.5	7687.9	6645.4	6624.7	6764.4	7655.1	8103.8	8378.8
52.5°	11065.2	11109.9	10672.2	10256.3	9199.7	8001.2	7984.8	8131.0	9253.2	9589.4	9638.5
55°	12212.4	12136.0	11790.0	11669.9	11043.3	9675.6	9671.2	9800.0	10798.8	10941.8	11032.4
57.5°	12718.9	12689.4	12856.4	13131.5	12974.3	11654.6	11644.8	11546.5	12181.8	12197.1	12475.5
60°	13038.7	13074.7	13586.7	14434.8	14826.7	13784.3	13720.9	13121.7	13502.6	13468.8	13766.8
62.5°	12798.6	12869.5	13790.8	15204.4	16213.0	15643.2	15553.7	14564.7	14631.3	14514.5	14791.8
65°	11523.6	11633.9	13143.5	15059.2	16900.7	17096.1	17005.5	15838.6	15527.5	15335.4	15181.5
67.5°	9356.9	9422.4	10998.6	13796.3	16590.7	17962.8	17944.2	16955.2	16204.2	15196.7	14002.6
69°	7732.6	7797.0	9314.3	12466.7	15908.4	18148.3	18184.3	17313.3	16075.4	14354.0	12406.7
70°	6549.4	6618.1	8031.7	11327.1	15117.0	18062.1	18126.5	17279.4	15706.5	13378.2	11006.2
72.5°	3435.1	3494.1	4944.8	7803.6	12323.7	16585.2	16780.6	15818.9	13313.8	9716.0	6507.9
75°	1079.6	1113.4	1931.0	4079.2	8437.8	12895.7	12940.5	12408.9	9454.0	5344.3	2710.3
77.5°	411.5	401.7	642.9	1503.1	4265.8	8120.1	8394.1	7754.5	4961.2	1889.5	625.5
80°	221.6	222.7	334.0	622.2	1825.1	4173.0	4404.5	3758.2	1762.9	589.4	144.1
82.5°	96.1	100.4	187.7	329.7	838.3	1539.1	1654.8	1377.6	673.5	396.2	53.5
85°	20.7	22.9	90.6	179.0	341.7	432.3	453.0	446.4	429.0	307.8	20.7
87.5°	0.0	0.0	40.4	64.4	86.2	98.2	86.2	112.4	236.9	207.4	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P323041

CATALOG NUMBER: GAN-SA7B-830-U-T4W-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7	2332.7
2.5°	2334.9	2315.2	2281.4	2244.3	2218.1	2190.8	2168.9	2159.1	2148.2	2140.6	2150.4
5°	2330.5	2292.3	2226.8	2163.5	2117.6	2080.5	2050.0	2037.9	2025.9	2017.2	2016.1
7.5°	2368.7	2315.2	2214.8	2122.0	2051.0	2000.8	1959.4	1941.9	1927.7	1921.2	1915.7
10°	2441.8	2373.1	2238.8	2117.6	2025.9	1940.8	1851.3	1782.5	1737.8	1717.0	1709.4
12.5°	2536.8	2450.6	2284.6	2140.6	2007.4	1843.6	1653.7	1490.0	1384.1	1349.2	1328.4
15°	2648.1	2541.2	2344.7	2170.0	1939.7	1640.6	1318.6	1104.7	1006.4	986.8	964.9
17.5°	2755.1	2637.2	2416.7	2175.5	1791.3	1311.0	966.0	820.9	782.7	795.7	799.0
20°	2849.0	2732.2	2487.7	2127.5	1521.6	983.5	747.7	711.7	725.9	751.0	755.4
22.5°	2943.9	2823.9	2553.2	2000.8	1176.7	746.6	673.5	682.2	696.4	721.5	725.9
25°	3059.6	2935.2	2614.3	1768.3	883.1	635.3	639.7	652.8	666.9	689.9	692.1
27.5°	3192.8	3076.0	2654.7	1466.0	654.9	584.0	598.2	617.8	632.0	653.8	658.2
30°	3369.7	3261.6	2667.8	1152.7	549.1	538.1	544.7	568.7	589.4	609.1	612.4
32.5°	3535.6	3445.0	2624.1	870.0	508.7	495.6	495.6	509.8	533.8	552.3	556.7
35°	3688.4	3629.4	2484.4	636.4	478.1	456.3	445.4	445.4	460.6	475.9	480.3
37.5°	3890.3	3888.1	2258.4	507.6	448.6	423.5	400.6	383.1	377.7	381.0	383.1
40°	4236.4	4239.6	1963.7	455.2	423.5	389.7	354.8	323.1	293.6	283.8	282.7
42.5°	4776.7	4727.6	1654.8	430.1	401.7	354.8	302.4	259.8	213.9	199.8	198.7
45°	5634.6	5343.2	1327.3	407.2	378.8	315.5	250.0	192.1	155.0	144.1	144.1
47.5°	6884.5	6152.0	1028.3	382.0	348.2	270.7	188.8	138.6	113.5	108.1	109.2
50°	8176.9	6944.5	788.1	350.4	311.1	223.8	139.7	100.4	86.2	86.2	87.3
52.5°	9323.0	7525.2	614.5	316.6	265.2	175.7	105.9	78.6	72.0	71.0	72.0
55°	10396.0	7899.6	470.5	277.3	210.7	131.0	80.8	64.4	60.0	57.9	56.8
57.5°	11430.8	8085.2	352.6	223.8	152.8	95.0	64.4	54.6	50.2	46.9	45.8
60°	12119.6	7934.6	242.3	164.8	105.9	68.8	53.5	46.9	41.5	38.2	37.1
62.5°	12508.2	7523.0	156.1	119.0	75.3	51.3	42.6	39.3	31.7	28.4	28.4
65°	12351.0	6844.1	109.2	85.1	54.6	38.2	31.7	31.7	22.9	18.6	17.5
67.5°	10945.1	5782.0	83.0	63.3	39.3	28.4	24.0	27.3	14.2	8.7	8.7
69°	9416.9	4792.0	71.0	52.4	32.7	22.9	20.7	25.1	9.8	6.5	5.5
70°	8184.5	4133.7	64.4	45.8	27.3	19.6	18.6	24.0	9.8	5.5	4.4
72.5°	4896.7	2305.4	49.1	32.7	17.5	15.3	15.3	27.3	9.8	5.5	4.4
75°	1979.0	812.1	36.0	22.9	13.1	13.1	18.6	34.9	8.7	4.4	3.3
77.5°	448.6	177.9	20.7	14.2	8.7	13.1	21.8	27.3	5.5	2.2	0.0
80°	109.2	43.7	13.1	8.7	5.5	9.8	16.4	15.3	1.1	0.0	0.0
82.5°	36.0	15.3	5.5	4.4	1.1	3.3	7.6	4.4	0.0	0.0	0.0
85°	15.3	8.7	2.2	1.1	0.0	0.0	1.1	0.0	0.0	0.0	0.0
87.5°	9.8	3.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)