

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057434

Luminaire Tested: **GAP-SA2C-722-U-T3BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1057434  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAP-SA2C-722-U-T3BC  
Description: GALLEON PEDESTRAIAN COMPANION 1050mA 2xLight Square PACKAGE 70CRI  
2200K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL  
Light Source: (28) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8330.4 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Luminous Opening: Rectangular (W 1.33' x L: 0.67' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 94.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1057434

CATALOG NUMBER: GAP-SA2C-722-U-T3BC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1057434

CATALOG NUMBER: GAP-SA2C-722-U-T3BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1057434

CATALOG NUMBER: GAP-SA2C-722-U-T3BC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 22.6     | 0.0    | 22.6   |
|                    | % Fixture | 0.3      | 0.0    | 0.3    |
| <b>Street Side</b> | Lumens    | 8307.8   | 0.0    | 8307.8 |
|                    | % Fixture | 99.7     | 0.0    | 99.7   |
| <b>Total</b>       | Lumens    | 8330.4   | 0.0    | 8330.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 8.1    | 0.1       |
| 10°-20°   | 96.4   | 1.2       |
| 20°-30°   | 341.0  | 4.1       |
| 30°-40°   | 785.9  | 9.4       |
| 40°-50°   | 1325.8 | 15.9      |
| 50°-60°   | 2185.8 | 26.2      |
| 60°-70°   | 2483.1 | 29.8      |
| 70°-80°   | 1021.0 | 12.3      |
| 80°-90°   | 83.1   | 1.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 8330.4 | 100.0     |
| 0°-180°   | 8330.4 | 100.0     |



REPORT NUMBER: P1057434


CATALOG NUMBER: GAP-SA2C-722-U-T3BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 440.8  | 5.3       |                         |      |         |
| FM   | (30°-60°)   | 4293.3 | 51.5      |                         |      |         |
| FH   | (60°-80°)   | 3491.2 | 41.9      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 82.5   | 1.0       |                         |      | G1/100  |
| BL   | (0°-30°)    | 4.8    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 4.3    | 0.1       | B0/220                  |      |         |
| BH   | (60°-80°)   | 12.9   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.6    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short





REPORT NUMBER: P1057434

CATALOG NUMBER: GAP-SA2C-722-U-T3BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 44°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   | 46.6   |
| 2.5°  | 62.2   | 62.9   | 62.2   | 61.5   | 58.8   | 56.1   | 56.1   | 54.1   | 52.0   | 50.0   | 48.0   |
| 5°    | 109.5  | 106.8  | 104.1  | 98.0   | 86.5   | 76.4   | 75.0   | 66.2   | 58.8   | 53.4   | 48.7   |
| 7.5°  | 277.8  | 270.4  | 244.7  | 214.3  | 162.9  | 125.0  | 123.7  | 94.0   | 71.0   | 58.1   | 49.3   |
| 10°   | 579.9  | 559.6  | 520.4  | 455.6  | 352.1  | 257.5  | 237.2  | 144.6  | 93.3   | 64.2   | 50.0   |
| 12.5° | 881.4  | 882.1  | 844.9  | 756.3  | 629.9  | 477.9  | 451.5  | 261.6  | 133.2  | 75.0   | 50.7   |
| 15°   | 1146.3 | 1139.6 | 1107.1 | 1044.3 | 907.7  | 732.0  | 708.3  | 449.5  | 201.4  | 89.9   | 52.0   |
| 17.5° | 1349.1 | 1339.6 | 1320.0 | 1277.5 | 1177.4 | 1004.4 | 979.4  | 677.9  | 312.3  | 109.5  | 52.7   |
| 20°   | 1587.0 | 1580.3 | 1555.3 | 1496.4 | 1405.2 | 1267.3 | 1231.5 | 928.0  | 475.8  | 141.9  | 54.1   |
| 22.5° | 1881.7 | 1862.1 | 1831.7 | 1756.7 | 1643.8 | 1495.8 | 1483.6 | 1182.2 | 676.6  | 192.6  | 56.8   |
| 25°   | 2222.4 | 2194.7 | 2158.8 | 2064.2 | 1925.0 | 1745.2 | 1730.3 | 1431.6 | 892.9  | 269.0  | 60.8   |
| 27.5° | 2635.3 | 2609.7 | 2545.4 | 2423.1 | 2256.2 | 2041.2 | 2024.3 | 1686.4 | 1132.8 | 373.1  | 66.2   |
| 30°   | 3082.8 | 3049.7 | 2943.6 | 2784.7 | 2625.9 | 2371.7 | 2331.2 | 1947.3 | 1372.8 | 502.9  | 73.7   |
| 32.5° | 3499.8 | 3457.2 | 3326.1 | 3138.2 | 2971.9 | 2703.6 | 2667.8 | 2242.0 | 1624.9 | 657.7  | 85.2   |
| 35°   | 3869.5 | 3819.5 | 3637.7 | 3432.9 | 3266.0 | 3029.4 | 2996.9 | 2528.5 | 1869.5 | 833.4  | 99.4   |
| 37.5° | 4163.6 | 4130.4 | 3879.0 | 3647.8 | 3512.0 | 3302.5 | 3280.8 | 2836.1 | 2141.9 | 1036.2 | 119.0  |
| 40°   | 4467.0 | 4423.1 | 4127.7 | 3836.4 | 3682.3 | 3507.9 | 3482.2 | 3083.5 | 2403.5 | 1255.1 | 143.3  |
| 42.5° | 4723.9 | 4682.6 | 4404.9 | 4096.0 | 3855.3 | 3647.8 | 3631.6 | 3291.0 | 2657.0 | 1482.9 | 175.1  |
| 45°   | 4995.6 | 4958.4 | 4709.7 | 4467.7 | 4106.8 | 3787.1 | 3759.4 | 3462.6 | 2904.4 | 1749.2 | 217.0  |
| 47.5° | 5368.7 | 5319.3 | 5082.1 | 4896.2 | 4483.3 | 4001.3 | 3970.2 | 3630.9 | 3155.1 | 2027.7 | 275.1  |
| 50°   | 5835.7 | 5799.9 | 5628.2 | 5480.2 | 5042.2 | 4392.0 | 4325.8 | 3849.3 | 3393.0 | 2346.7 | 350.8  |
| 52.5° | 6289.3 | 6277.1 | 6289.3 | 6236.5 | 5903.3 | 5069.9 | 4940.8 | 4216.3 | 3695.8 | 2680.0 | 449.5  |
| 55°   | 6346.0 | 6383.2 | 6529.9 | 6698.9 | 6643.4 | 6041.2 | 5932.4 | 4775.2 | 4070.3 | 3100.4 | 600.2  |
| 57.5° | 6140.6 | 6161.5 | 6348.7 | 6646.8 | 6825.9 | 6734.0 | 6720.5 | 5700.6 | 4598.8 | 3599.9 | 826.6  |
| 59°   | 5930.4 | 5971.6 | 6121.0 | 6425.1 | 6682.0 | 6833.4 | 6844.2 | 6287.9 | 5001.0 | 3910.8 | 1013.2 |
| 60°   | 5813.4 | 5826.3 | 5941.9 | 6241.3 | 6517.0 | 6756.3 | 6787.4 | 6588.7 | 5318.0 | 4145.3 | 1180.1 |
| 62.5° | 5444.4 | 5451.1 | 5513.3 | 5749.2 | 5993.2 | 6213.6 | 6279.1 | 6771.9 | 6198.0 | 4733.3 | 1770.2 |
| 65°   | 4961.8 | 4970.6 | 5064.5 | 5291.0 | 5523.5 | 5671.5 | 5699.2 | 6258.2 | 6661.7 | 5345.7 | 2594.1 |
| 67.5° | 4091.9 | 4141.3 | 4260.9 | 4617.8 | 4944.9 | 5122.0 | 5142.3 | 5352.5 | 6408.2 | 5760.0 | 3030.1 |
| 70°   | 2770.5 | 2723.9 | 3020.6 | 3517.4 | 4108.8 | 4375.1 | 4376.5 | 4468.4 | 5455.2 | 5658.0 | 2526.5 |
| 72.5° | 1209.9 | 1284.2 | 1500.5 | 1937.8 | 2654.3 | 3296.4 | 3282.9 | 3595.1 | 4350.8 | 4807.0 | 1878.3 |
| 75°   | 531.3  | 548.2  | 639.4  | 871.2  | 1207.2 | 1790.5 | 1996.6 | 2886.1 | 3274.7 | 3143.6 | 1366.0 |
| 77.5° | 285.9  | 290.0  | 314.3  | 364.3  | 461.6  | 845.6  | 892.9  | 1828.3 | 2321.7 | 1812.1 | 882.7  |
| 80°   | 108.8  | 108.8  | 113.6  | 130.4  | 192.6  | 330.5  | 354.8  | 826.0  | 1601.9 | 926.0  | 446.1  |
| 82.5° | 68.3   | 66.9   | 67.6   | 68.3   | 78.4   | 112.9  | 120.3  | 328.5  | 756.3  | 456.9  | 117.6  |
| 85°   | 34.5   | 35.8   | 39.9   | 48.0   | 56.8   | 69.6   | 71.6   | 102.7  | 229.8  | 106.8  | 30.4   |
| 87.5° | 22.3   | 23.0   | 25.0   | 32.4   | 39.9   | 50.7   | 52.0   | 71.6   | 91.2   | 75.0   | 6.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1057434

CATALOG NUMBER: GAP-SA2C-722-U-T3BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°   | 95°  | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|------|------|------|------|------|------|------|------|------|------|
| 0°    | 46.6  | 46.6 | 46.6 | 46.6 | 46.6 | 46.6 | 46.6 | 46.6 | 46.6 | 46.6 | 46.6 |
| 2.5°  | 47.3  | 46.0 | 43.9 | 41.9 | 39.9 | 36.5 | 33.8 | 32.4 | 31.8 | 31.1 | 31.1 |
| 5°    | 46.6  | 44.6 | 40.6 | 37.2 | 33.8 | 29.7 | 26.4 | 24.3 | 23.7 | 23.0 | 23.0 |
| 7.5°  | 46.0  | 42.6 | 37.9 | 33.1 | 28.4 | 23.7 | 19.6 | 17.6 | 16.9 | 16.2 | 15.5 |
| 10°   | 45.3  | 41.2 | 34.5 | 29.1 | 23.7 | 18.2 | 14.2 | 11.5 | 10.8 | 10.1 | 10.1 |
| 12.5° | 44.6  | 39.2 | 31.8 | 25.7 | 18.9 | 12.8 | 9.5  | 6.8  | 5.4  | 4.7  | 4.7  |
| 15°   | 43.9  | 37.2 | 29.7 | 21.6 | 14.2 | 8.1  | 4.1  | 2.0  | 0.7  | 0.7  | 0.7  |
| 17.5° | 41.9  | 35.1 | 26.4 | 16.9 | 9.5  | 4.1  | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  |
| 20°   | 40.6  | 33.1 | 23.0 | 12.8 | 5.4  | 2.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 22.5° | 39.9  | 31.8 | 19.6 | 8.8  | 4.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 25°   | 39.9  | 30.4 | 16.2 | 6.8  | 2.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 27.5° | 40.6  | 29.1 | 12.8 | 4.7  | 0.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 30°   | 39.2  | 27.7 | 9.5  | 3.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 32.5° | 39.2  | 25.0 | 6.8  | 2.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 35°   | 39.9  | 21.6 | 5.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 37.5° | 41.9  | 18.9 | 4.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 40°   | 45.3  | 17.6 | 3.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 42.5° | 50.0  | 16.9 | 2.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 45°   | 55.4  | 16.9 | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 47.5° | 63.5  | 17.6 | 0.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 50°   | 73.0  | 18.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 52.5° | 83.8  | 18.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 55°   | 95.3  | 18.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 57.5° | 110.8 | 17.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 59°   | 127.1 | 16.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 60°   | 144.0 | 14.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 62.5° | 232.5 | 13.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 65°   | 456.2 | 12.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 67.5° | 780.0 | 12.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 70°   | 828.7 | 12.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.5° | 544.1 | 10.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 75°   | 277.1 | 10.8 | 0.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 77.5° | 124.4 | 10.8 | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 80°   | 50.0  | 6.1  | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 82.5° | 20.3  | 4.1  | 2.0  | 0.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 85°   | 8.1   | 4.1  | 2.7  | 1.4  | 0.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 87.5° | 5.4   | 4.1  | 3.4  | 2.7  | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 90°   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ


Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-722-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 2200K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 2160     | CRI (Ra): | 71.9 |      |       |
| CIE u':                   | 0.2927   | R1:       | 68.7 | R9:  | -17.8 |
| CIE v':                   | 0.5388   | R2:       | 82.6 | R10: | 60.5  |
| Duv:                      | 0.0015   | R3:       | 95.5 | R11: | 60.2  |
| CIE x:                    | 0.5130   | R4:       | 66.4 | R12: | 48.2  |
| CIE y:                    | 0.4197   | R5:       | 65.4 | R13: | 70.7  |
| CIE z:                    | 0.0674   | R6:       | 75.9 | R14: | 96.8  |
| Peak Wavelength (nm):     | 609      | R7:       | 77.2 | R15: | 61.8  |
| Dominant Wavelength (nm): | 587      | R8:       | 43.5 |      |       |
| Purity:                   | 79.96089 |           |      |      |       |
| Rf:                       | 70.6     |           |      |      |       |
| Rg:                       | 97.6     |           |      |      |       |



### Test Conditions


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-2

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.8

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.21


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 27                                     | NR                             | 620               | 966                                    | NR                             | 750               | 46                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 42                                     | NR                             | 625               | 930                                    | NR                             | 755               | 39                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 67                                     | NR                             | 630               | 888                                    | NR                             | 760               | 34                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 101                                    | NR                             | 635               | 835                                    | NR                             | 765               | 30                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 139                                    | NR                             | 640               | 778                                    | NR                             | 770               | 26                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 183                                    | NR                             | 645               | 717                                    | NR                             | 775               | 22                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 224                                    | NR                             | 650               | 656                                    | NR                             | 780               | 19                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 262                                    | NR                             | 655               | 595                                    | NR                             | 785               | 17                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 1                                      | NR                             | 530               | 299                                    | NR                             | 660               | 536                                    | NR                             | 790               | 15                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 3                                      | NR                             | 535               | 332                                    | NR                             | 665               | 480                                    | NR                             | 795               | 13                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 7                                      | NR                             | 540               | 365                                    | NR                             | 670               | 425                                    | NR                             | 800               | 11                                     | NR                             | 930               | 1                                      | NR                             |
| 415               | 17                                     | NR                             | 545               | 400                                    | NR                             | 675               | 376                                    | NR                             | 805               | 10                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 36                                     | NR                             | 550               | 437                                    | NR                             | 680               | 332                                    | NR                             | 810               | 8                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 67                                     | NR                             | 555               | 479                                    | NR                             | 685               | 291                                    | NR                             | 815               | 8                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 105                                    | NR                             | 560               | 525                                    | NR                             | 690               | 255                                    | NR                             | 820               | 7                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 141                                    | NR                             | 565               | 579                                    | NR                             | 695               | 221                                    | NR                             | 825               | 6                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 169                                    | NR                             | 570               | 639                                    | NR                             | 700               | 192                                    | NR                             | 830               | 5                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 173                                    | NR                             | 575               | 703                                    | NR                             | 705               | 167                                    | NR                             | 835               | 4                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 136                                    | NR                             | 580               | 769                                    | NR                             | 710               | 144                                    | NR                             | 840               | 4                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 80                                     | NR                             | 585               | 832                                    | NR                             | 715               | 125                                    | NR                             | 845               | 3                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 45                                     | NR                             | 590               | 890                                    | NR                             | 720               | 109                                    | NR                             | 850               | 3                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 32                                     | NR                             | 595               | 937                                    | NR                             | 725               | 94                                     | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 23                                     | NR                             | 600               | 972                                    | NR                             | 730               | 81                                     | NR                             | 860               | 2                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 18                                     | NR                             | 605               | 992                                    | NR                             | 735               | 70                                     | NR                             | 865               | 2                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 18                                     | NR                             | 610               | 998                                    | NR                             | 740               | 61                                     | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 20                                     | NR                             | 615               | 990                                    | NR                             | 745               | 53                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-2





TM-30-18

### Summary

$R_f = 70.6$   
 $R_g = 97.6$   
 $CIE\ R_a = 71.9$   
 $R_g = -17.8$




### Color Vector Graphics








Individual Sample Fidelity Index ( $R_{f,i}$ )



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)