

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057482

Luminaire Tested: **GAP-SA2C-760-U-T3BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1057482  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAP-SA2C-760-U-T3BC  
Description: GALLEON PEDESTRAIAN COMPANION 1050mA 2xLight Square PACKAGE 70CRI  
5700K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL  
Light Source: (28) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11333.9 lumens  
Efficiency: N/A  
Efficacy: 119.4 lumens/watt  
Luminous Opening: Rectangular (W 1.33' x L: 0.67' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 94.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1057482

CATALOG NUMBER: GAP-SA2C-760-U-T3BC

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 12.7 fc  
 Type III - Short - N/A

REPORT NUMBER: P1057482

CATALOG NUMBER: GAP-SA2C-760-U-T3BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1057482

CATALOG NUMBER: GAP-SA2C-760-U-T3BC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 30.7     | 0.0    | 30.7    |
|                    | % Fixture | 0.3      | 0.0    | 0.3     |
| <b>Street Side</b> | Lumens    | 11303.1  | 0.0    | 11303.1 |
|                    | % Fixture | 99.7     | 0.0    | 99.7    |
| <b>Total</b>       | Lumens    | 11333.9  | 0.0    | 11333.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 11.1    | 0.1       |
| 10°-20°   | 131.2   | 1.2       |
| 20°-30°   | 463.9   | 4.1       |
| 30°-40°   | 1069.3  | 9.4       |
| 40°-50°   | 1803.9  | 15.9      |
| 50°-60°   | 2973.9  | 26.2      |
| 60°-70°   | 3378.4  | 29.8      |
| 70°-80°   | 1389.1  | 12.3      |
| 80°-90°   | 113.1   | 1.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 11333.9 | 100.0     |
| 0°-180°   | 11333.9 | 100.0     |



REPORT NUMBER: P1057482


CATALOG NUMBER: GAP-SA2C-760-U-T3BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 599.8  | 5.3       |                         |      |         |
| FM   | (30°-60°)   | 5841.2 | 51.5      |                         |      |         |
| FH   | (60°-80°)   | 4749.9 | 41.9      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 112.3  | 1.0       |                         |      | G2/225  |
| BL   | (0°-30°)    | 6.5    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 5.9    | 0.1       | B0/220                  |      |         |
| BH   | (60°-80°)   | 17.5   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.9    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1057482

CATALOG NUMBER: GAP-SA2C-760-U-T3BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 44°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   | 63.5   |
| 2.5°  | 84.6   | 85.5   | 84.6   | 83.7   | 80.0   | 76.3   | 76.3   | 73.6   | 70.8   | 68.0   | 65.3   |
| 5°    | 149.0  | 145.3  | 141.6  | 133.3  | 117.7  | 103.9  | 102.1  | 90.1   | 80.0   | 72.6   | 66.2   |
| 7.5°  | 378.0  | 367.8  | 332.9  | 291.5  | 221.6  | 170.1  | 168.3  | 127.8  | 96.6   | 79.1   | 67.1   |
| 10°   | 789.0  | 761.4  | 708.1  | 619.8  | 479.1  | 350.4  | 322.8  | 196.8  | 126.9  | 87.4   | 68.0   |
| 12.5° | 1199.2 | 1200.1 | 1149.5 | 1029.0 | 857.1  | 650.2  | 614.3  | 355.9  | 181.2  | 102.1  | 69.0   |
| 15°   | 1559.6 | 1550.4 | 1506.3 | 1420.8 | 1235.0 | 995.9  | 963.7  | 611.5  | 274.0  | 122.3  | 70.8   |
| 17.5° | 1835.5 | 1822.6 | 1796.0 | 1738.0 | 1601.9 | 1366.5 | 1332.5 | 922.4  | 424.9  | 149.0  | 71.7   |
| 20°   | 2159.2 | 2150.0 | 2116.0 | 2036.0 | 1911.8 | 1724.2 | 1675.5 | 1262.6 | 647.4  | 193.1  | 73.6   |
| 22.5° | 2560.2 | 2533.5 | 2492.1 | 2390.0 | 2236.5 | 2035.1 | 2018.5 | 1608.4 | 920.5  | 262.1  | 77.2   |
| 25°   | 3023.6 | 2985.9 | 2937.2 | 2808.4 | 2619.0 | 2374.4 | 2354.2 | 1947.7 | 1214.8 | 366.0  | 82.8   |
| 27.5° | 3585.5 | 3550.6 | 3463.2 | 3296.7 | 3069.6 | 2777.2 | 2754.2 | 2294.4 | 1541.2 | 507.6  | 90.1   |
| 30°   | 4194.3 | 4149.2 | 4004.8 | 3788.7 | 3572.6 | 3226.9 | 3171.7 | 2649.4 | 1867.7 | 684.2  | 100.2  |
| 32.5° | 4761.7 | 4703.7 | 4525.3 | 4269.7 | 4043.5 | 3678.4 | 3629.6 | 3050.3 | 2210.7 | 894.8  | 115.9  |
| 35°   | 5264.7 | 5196.6 | 4949.3 | 4670.6 | 4443.5 | 4121.6 | 4077.5 | 3440.2 | 2543.6 | 1133.9 | 135.2  |
| 37.5° | 5664.7 | 5619.6 | 5277.6 | 4963.1 | 4778.2 | 4493.1 | 4463.7 | 3858.6 | 2914.2 | 1409.7 | 161.8  |
| 40°   | 6077.6 | 6017.8 | 5616.0 | 5219.6 | 5009.9 | 4772.7 | 4737.7 | 4195.2 | 3270.1 | 1707.7 | 195.0  |
| 42.5° | 6427.0 | 6370.9 | 5993.0 | 5572.7 | 5245.4 | 4963.1 | 4941.0 | 4477.5 | 3614.9 | 2017.6 | 238.2  |
| 45°   | 6796.7 | 6746.1 | 6407.7 | 6078.5 | 5587.5 | 5152.5 | 5114.8 | 4711.1 | 3951.5 | 2379.9 | 295.2  |
| 47.5° | 7304.3 | 7237.2 | 6914.4 | 6661.5 | 6099.7 | 5444.0 | 5401.7 | 4940.1 | 4292.7 | 2758.8 | 374.3  |
| 50°   | 7939.8 | 7891.0 | 7657.5 | 7456.1 | 6860.2 | 5975.5 | 5885.4 | 5237.1 | 4616.4 | 3192.8 | 477.3  |
| 52.5° | 8556.8 | 8540.3 | 8556.8 | 8485.1 | 8031.7 | 6897.9 | 6722.2 | 5736.4 | 5028.3 | 3646.2 | 611.5  |
| 55°   | 8634.1 | 8684.6 | 8884.2 | 9114.1 | 9038.7 | 8219.3 | 8071.3 | 6496.9 | 5537.8 | 4218.2 | 816.6  |
| 57.5° | 8354.5 | 8383.0 | 8637.7 | 9043.3 | 9287.0 | 9161.9 | 9143.5 | 7755.9 | 6256.9 | 4897.8 | 1124.7 |
| 59°   | 8068.5 | 8124.6 | 8327.8 | 8741.7 | 9091.1 | 9297.1 | 9311.8 | 8555.0 | 6804.1 | 5320.8 | 1378.5 |
| 60°   | 7909.4 | 7926.9 | 8084.2 | 8491.5 | 8866.7 | 9192.3 | 9234.6 | 8964.2 | 7235.4 | 5639.9 | 1605.6 |
| 62.5° | 7407.3 | 7416.5 | 7501.1 | 7822.1 | 8154.0 | 8453.8 | 8543.0 | 9213.4 | 8432.7 | 6439.9 | 2408.4 |
| 65°   | 6750.7 | 6762.7 | 6890.5 | 7198.6 | 7514.9 | 7716.3 | 7754.0 | 8514.5 | 9063.5 | 7273.1 | 3529.4 |
| 67.5° | 5567.2 | 5634.4 | 5797.1 | 6282.7 | 6727.8 | 6968.7 | 6996.3 | 7282.3 | 8718.7 | 7836.8 | 4122.5 |
| 70°   | 3769.4 | 3706.0 | 4109.7 | 4785.6 | 5590.2 | 5952.5 | 5954.4 | 6079.4 | 7422.0 | 7697.9 | 3437.4 |
| 72.5° | 1646.1 | 1747.2 | 2041.5 | 2636.5 | 3611.2 | 4484.9 | 4466.5 | 4891.3 | 5919.4 | 6540.2 | 2555.6 |
| 75°   | 722.8  | 745.8  | 869.9  | 1185.4 | 1642.4 | 2436.0 | 2716.5 | 3926.7 | 4455.4 | 4277.0 | 1858.5 |
| 77.5° | 389.0  | 394.5  | 427.6  | 495.7  | 628.1  | 1150.4 | 1214.8 | 2487.5 | 3158.8 | 2465.4 | 1201.0 |
| 80°   | 148.1  | 148.1  | 154.5  | 177.5  | 262.1  | 449.7  | 482.8  | 1123.7 | 2179.4 | 1259.8 | 606.9  |
| 82.5° | 92.9   | 91.0   | 92.0   | 92.9   | 106.7  | 153.6  | 163.7  | 446.9  | 1029.0 | 621.6  | 160.0  |
| 85°   | 46.9   | 48.7   | 54.3   | 65.3   | 77.2   | 94.7   | 97.5   | 139.8  | 312.7  | 145.3  | 41.4   |
| 87.5° | 30.3   | 31.3   | 34.0   | 44.1   | 54.3   | 69.0   | 70.8   | 97.5   | 124.1  | 102.1  | 8.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P1057482

CATALOG NUMBER: GAP-SA2C-760-U-T3BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°  | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|------|------|------|------|------|------|------|------|------|------|
| 0°    | 63.5   | 63.5 | 63.5 | 63.5 | 63.5 | 63.5 | 63.5 | 63.5 | 63.5 | 63.5 | 63.5 |
| 2.5°  | 64.4   | 62.5 | 59.8 | 57.0 | 54.3 | 49.7 | 46.0 | 44.1 | 43.2 | 42.3 | 42.3 |
| 5°    | 63.5   | 60.7 | 55.2 | 50.6 | 46.0 | 40.5 | 35.9 | 33.1 | 32.2 | 31.3 | 31.3 |
| 7.5°  | 62.5   | 57.9 | 51.5 | 45.1 | 38.6 | 32.2 | 26.7 | 23.9 | 23.0 | 22.1 | 21.2 |
| 10°   | 61.6   | 56.1 | 46.9 | 39.5 | 32.2 | 24.8 | 19.3 | 15.6 | 14.7 | 13.8 | 13.8 |
| 12.5° | 60.7   | 53.3 | 43.2 | 34.9 | 25.7 | 17.5 | 12.9 | 9.2  | 7.4  | 6.4  | 6.4  |
| 15°   | 59.8   | 50.6 | 40.5 | 29.4 | 19.3 | 11.0 | 5.5  | 2.8  | 0.9  | 0.9  | 0.9  |
| 17.5° | 57.0   | 47.8 | 35.9 | 23.0 | 12.9 | 5.5  | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  |
| 20°   | 55.2   | 45.1 | 31.3 | 17.5 | 7.4  | 2.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 22.5° | 54.3   | 43.2 | 26.7 | 12.0 | 5.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 25°   | 54.3   | 41.4 | 22.1 | 9.2  | 2.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 27.5° | 55.2   | 39.5 | 17.5 | 6.4  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 30°   | 53.3   | 37.7 | 12.9 | 4.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 32.5° | 53.3   | 34.0 | 9.2  | 2.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 35°   | 54.3   | 29.4 | 7.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 37.5° | 57.0   | 25.7 | 5.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 40°   | 61.6   | 23.9 | 4.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 42.5° | 68.0   | 23.0 | 3.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 45°   | 75.4   | 23.0 | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 47.5° | 86.4   | 23.9 | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 50°   | 99.3   | 24.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 52.5° | 114.0  | 25.7 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 55°   | 129.7  | 24.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 57.5° | 150.8  | 23.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 59°   | 172.9  | 22.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 60°   | 195.9  | 20.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 62.5° | 316.3  | 18.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 65°   | 620.7  | 16.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 67.5° | 1061.2 | 17.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 70°   | 1127.4 | 16.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.5° | 740.3  | 13.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 75°   | 377.0  | 14.7 | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 77.5° | 169.2  | 14.7 | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 80°   | 68.0   | 8.3  | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 82.5° | 27.6   | 5.5  | 2.8  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 85°   | 11.0   | 5.5  | 3.7  | 1.8  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 87.5° | 7.4    | 5.5  | 4.6  | 3.7  | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 90°   | 0.0    | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-757-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5700K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 5571     | CRI (Ra): | 69.9 |      |       |
| CIE u':                   | 0.2033   | R1:       | 68.8 | R9:  | -35.4 |
| CIE v':                   | 0.4806   | R2:       | 72.5 | R10: | 36.7  |
| Duv:                      | 0.0041   | R3:       | 76.8 | R11: | 73.9  |
| CIE x:                    | 0.3308   | R4:       | 72.0 | R12: | 47.8  |
| CIE y:                    | 0.3476   | R5:       | 70.9 | R13: | 68.0  |
| CIE z:                    | 0.3216   | R6:       | 65.6 | R14: | 87.0  |
| Peak Wavelength (nm):     | 442      | R7:       | 75.5 | R15: | 59.8  |
| Dominant Wavelength (nm): | 544      | R8:       | 56.8 |      |       |
| Purity:                   | 3.635698 |           |      |      |       |
| Rf:                       | 70.4     |           |      |      |       |
| Rg:                       | 97.1     |           |      |      |       |



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2407-184-7

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 120                         | NR               | 620       | 298                         | NR               | 750       | 9                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 167                         | NR               | 625       | 270                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 222                         | NR               | 630       | 245                         | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 279                         | NR               | 635       | 219                         | NR               | 765       | 6                           | NR               | 895       | 0                           | NR               |
| 380       | 1                           | NR               | 510       | 329                         | NR               | 640       | 196                         | NR               | 770       | 5                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 371                         | NR               | 645       | 173                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 403                         | NR               | 650       | 153                         | NR               | 780       | 4                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 424                         | NR               | 655       | 135                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 439                         | NR               | 660       | 117                         | NR               | 790       | 3                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 449                         | NR               | 665       | 103                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 28                          | NR               | 540       | 454                         | NR               | 670       | 89                          | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 459                         | NR               | 675       | 77                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 118                         | NR               | 550       | 463                         | NR               | 680       | 67                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 237                         | NR               | 555       | 466                         | NR               | 685       | 58                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 420                         | NR               | 560       | 467                         | NR               | 690       | 50                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 677                         | NR               | 565       | 469                         | NR               | 695       | 43                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 962                         | NR               | 570       | 469                         | NR               | 700       | 37                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 894                         | NR               | 575       | 466                         | NR               | 705       | 32                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 472                         | NR               | 580       | 461                         | NR               | 710       | 28                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 275                         | NR               | 585       | 450                         | NR               | 715       | 24                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 180                         | NR               | 590       | 437                         | NR               | 720       | 21                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 107                         | NR               | 595       | 420                         | NR               | 725       | 18                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 76                          | NR               | 600       | 400                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 68                          | NR               | 605       | 376                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 69                          | NR               | 610       | 352                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 325                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-7

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 120                      | NR            | 620    | 298                      | NR            | 750    | 9                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 167                      | NR            | 625    | 270                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 222                      | NR            | 630    | 245                      | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 279                      | NR            | 635    | 219                      | NR            | 765    | 6                        | NR            | 895    | 0                        | NR            |
| 380    | 1                        | NR            | 510    | 329                      | NR            | 640    | 196                      | NR            | 770    | 5                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 371                      | NR            | 645    | 173                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 403                      | NR            | 650    | 153                      | NR            | 780    | 4                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 424                      | NR            | 655    | 135                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 439                      | NR            | 660    | 117                      | NR            | 790    | 3                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 449                      | NR            | 665    | 103                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 28                       | NR            | 540    | 454                      | NR            | 670    | 89                       | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 459                      | NR            | 675    | 77                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 118                      | NR            | 550    | 463                      | NR            | 680    | 67                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 237                      | NR            | 555    | 466                      | NR            | 685    | 58                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 420                      | NR            | 560    | 467                      | NR            | 690    | 50                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 677                      | NR            | 565    | 469                      | NR            | 695    | 43                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 962                      | NR            | 570    | 469                      | NR            | 700    | 37                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 894                      | NR            | 575    | 466                      | NR            | 705    | 32                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 472                      | NR            | 580    | 461                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 275                      | NR            | 585    | 450                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 180                      | NR            | 590    | 437                      | NR            | 720    | 21                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 420                      | NR            | 725    | 18                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 76                       | NR            | 600    | 400                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 68                       | NR            | 605    | 376                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 69                       | NR            | 610    | 352                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 325                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-7

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.71**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 120                                  | NR                             | 620               | 298                                  | NR                             | 750               | 9                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 167                                  | NR                             | 625               | 270                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 222                                  | NR                             | 630               | 245                                  | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 279                                  | NR                             | 635               | 219                                  | NR                             | 765               | 6                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 1                                    | NR                             | 510               | 329                                  | NR                             | 640               | 196                                  | NR                             | 770               | 5                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 2                                    | NR                             | 515               | 371                                  | NR                             | 645               | 173                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 4                                    | NR                             | 520               | 403                                  | NR                             | 650               | 153                                  | NR                             | 780               | 4                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 6                                    | NR                             | 525               | 424                                  | NR                             | 655               | 135                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 9                                    | NR                             | 530               | 439                                  | NR                             | 660               | 117                                  | NR                             | 790               | 3                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 14                                   | NR                             | 535               | 449                                  | NR                             | 665               | 103                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 28                                   | NR                             | 540               | 454                                  | NR                             | 670               | 89                                   | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 55                                   | NR                             | 545               | 459                                  | NR                             | 675               | 77                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 118                                  | NR                             | 550               | 463                                  | NR                             | 680               | 67                                   | NR                             | 810               | 2                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 237                                  | NR                             | 555               | 466                                  | NR                             | 685               | 58                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 420                                  | NR                             | 560               | 467                                  | NR                             | 690               | 50                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 677                                  | NR                             | 565               | 469                                  | NR                             | 695               | 43                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 962                                  | NR                             | 570               | 469                                  | NR                             | 700               | 37                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 894                                  | NR                             | 575               | 466                                  | NR                             | 705               | 32                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 472                                  | NR                             | 580               | 461                                  | NR                             | 710               | 28                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 275                                  | NR                             | 585               | 450                                  | NR                             | 715               | 24                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 180                                  | NR                             | 590               | 437                                  | NR                             | 720               | 21                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 107                                  | NR                             | 595               | 420                                  | NR                             | 725               | 18                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 76                                   | NR                             | 600               | 400                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 68                                   | NR                             | 605               | 376                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 69                                   | NR                             | 610               | 352                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 86                                   | NR                             | 615               | 325                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-7





TM-30-18

### Summary

$R_f = 70.4$   
 $R_g = 97.1$   
 $CIE R_a = 69.9$   
 $R_g = -35.4$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 52 | CES51 = 87 | CES76 = 40 |
| CES02 = 59 | CES27 = 77 | CES52 = 88 | CES77 = 62 |
| CES03 = 30 | CES28 = 76 | CES53 = 74 | CES78 = 43 |
| CES04 = 68 | CES29 = 46 | CES54 = 79 | CES79 = 72 |
| CES05 = 45 | CES30 = 54 | CES55 = 78 | CES80 = 68 |
| CES06 = 49 | CES31 = 52 | CES56 = 67 | CES81 = 70 |
| CES07 = 38 | CES32 = 49 | CES57 = 64 | CES82 = 87 |
| CES08 = 37 | CES33 = 59 | CES58 = 66 | CES83 = 81 |
| CES09 = 29 | CES34 = 61 | CES59 = 87 | CES84 = 87 |
| CES10 = 72 | CES35 = 78 | CES60 = 91 | CES85 = 83 |
| CES11 = 55 | CES36 = 88 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 71 | CES62 = 77 | CES87 = 74 |
| CES13 = 41 | CES38 = 64 | CES63 = 74 | CES88 = 76 |
| CES14 = 74 | CES39 = 90 | CES64 = 71 | CES89 = 75 |
| CES15 = 70 | CES40 = 81 | CES65 = 63 | CES90 = 73 |
| CES16 = 46 | CES41 = 82 | CES66 = 66 | CES91 = 93 |
| CES17 = 48 | CES42 = 69 | CES67 = 63 | CES92 = 69 |
| CES18 = 55 | CES43 = 67 | CES68 = 71 | CES93 = 82 |
| CES19 = 70 | CES44 = 98 | CES69 = 81 | CES94 = 58 |
| CES20 = 63 | CES45 = 77 | CES70 = 57 | CES95 = 72 |
| CES21 = 85 | CES46 = 76 | CES71 = 54 | CES96 = 78 |
| CES22 = 77 | CES47 = 73 | CES72 = 84 | CES97 = 82 |
| CES23 = 91 | CES48 = 65 | CES73 = 45 | CES98 = 70 |
| CES24 = 90 | CES49 = 77 | CES74 = 92 | CES99 = 59 |
| CES25 = 71 | CES50 = 85 | CES75 = 49 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)