

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057512

Luminaire Tested: **GAP-SA1A-727-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1057512
Test Lab: INNOVATION CENTER(G1)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAP-SA1A-727-U-T2BC
Description: GALLEON PEDESTRAIAN COMPANION 615mA 1xLight Square PACKAGE 70CRI
2700K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (14) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2966 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G1

Input Watts (W): 29.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1057512

CATALOG NUMBER: GAP-SA1A-727-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.3 fc
 Type II - Short - N/A

REPORT NUMBER: P1057512

CATALOG NUMBER: GAP-SA1A-727-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1057512

CATALOG NUMBER: GAP-SA1A-727-U-T2BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	13.2	0.0	13.2
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	2952.8	0.0	2952.8
	% Fixture	99.6	0.0	99.6
Total	Lumens	2966.0	0.0	2966.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3.9	0.1
10°-20°	32.8	1.1
20°-30°	100.4	3.4
30°-40°	260.9	8.8
40°-50°	656.8	22.1
50°-60°	952.1	32.1
60°-70°	734.4	24.8
70°-80°	202.6	6.8
80°-90°	22.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2966.0	100.0
0°-180°	2966.0	100.0



REPORT NUMBER: P1057512


CATALOG NUMBER: GAP-SA1A-727-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	134.6	4.5			
FM	(30°-60°)	1865.5	62.9			
FH	(60°-80°)	931.0	31.4			G1/1800
FVH	(80°-90°)	21.6	0.7			G1/100
BL	(0°-30°)	2.4	0.1	B0/110		
BM	(30°-60°)	4.3	0.1	B0/220		
BH	(60°-80°)	5.9	0.2	B0/110		G0/110
BVH	(80°-90°)	0.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type II Short



REPORT NUMBER: P1057512

CATALOG NUMBER: GAP-SA1A-727-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3
2.5°	34.2	34.2	33.6	32.5	29.7	28.0	26.3	24.7	24.1	23.0	21.9
5°	62.2	61.1	60.5	54.9	49.3	42.6	35.9	30.3	29.7	25.8	22.4
7.5°	130.6	130.6	119.4	105.9	90.8	70.1	51.6	39.8	38.1	29.7	23.0
10°	213.5	214.1	206.8	185.5	158.1	123.3	83.5	51.6	50.4	34.7	23.5
12.5°	288.1	287.5	280.2	265.1	234.8	191.1	131.2	74.5	70.1	40.4	23.5
15°	335.7	335.7	334.6	326.8	305.5	260.6	194.5	109.3	104.2	48.8	24.1
17.5°	382.2	385.1	381.1	377.8	362.1	328.4	260.6	157.5	147.4	62.2	25.2
20°	438.3	441.1	439.4	434.4	414.8	385.1	326.8	213.0	202.9	84.6	27.5
22.5°	503.3	505.6	502.2	500.5	475.8	438.3	387.9	279.7	264.5	113.2	30.3
25°	583.5	581.8	580.7	571.1	547.0	506.1	445.6	341.3	329.6	151.3	34.2
27.5°	677.6	675.4	668.1	655.8	620.5	575.6	507.2	406.9	395.7	197.3	39.8
30°	804.9	791.4	780.8	753.3	706.2	646.8	576.2	471.4	459.0	252.2	46.0
32.5°	984.2	980.3	938.8	867.1	799.2	728.1	653.0	539.7	526.9	308.8	54.4
35°	1305.9	1287.4	1215.1	1034.6	907.4	830.1	730.9	608.1	594.7	374.4	65.6
37.5°	1667.4	1651.2	1581.1	1363.7	1071.6	935.4	817.7	685.5	670.9	446.1	79.6
40°	2030.1	2025.0	1998.7	1824.9	1404.6	1076.1	932.6	784.1	767.3	518.4	99.2
42.5°	2438.1	2423.5	2406.7	2347.9	1979.6	1358.0	1092.4	896.8	882.2	607.6	127.2
45°	2567.6	2562.0	2582.1	2638.7	2582.1	1948.8	1340.1	1050.3	1035.8	721.9	167.6
47.5°	2523.8	2518.2	2573.7	2666.8	2796.2	2657.8	1724.0	1270.6	1243.7	858.7	227.6
50°	2303.0	2305.3	2403.3	2589.4	2774.9	2940.3	2365.2	1563.7	1545.2	1053.1	308.3
52.5°	2094.0	2097.9	2220.6	2458.8	2662.8	2950.9	2976.7	1990.3	1910.7	1291.3	408.0
55°	1890.5	1884.9	1977.9	2336.6	2642.7	2805.2	3169.0	2490.8	2438.7	1600.2	506.1
57.5°	1675.3	1668.6	1717.3	1984.1	2600.6	2825.4	3118.5	3079.8	3017.6	1955.0	585.1
60°	1285.2	1270.1	1366.5	1570.5	2276.1	2850.0	3018.8	3296.2	3292.3	2430.2	624.9
62.5°	616.0	640.6	771.2	992.6	1521.7	2631.5	3057.4	3216.0	3223.9	2849.5	716.9
65°	314.4	320.0	387.3	542.0	805.4	1891.6	2945.9	3105.1	3093.3	2767.7	955.1
67.5°	211.9	214.7	246.1	327.9	467.4	792.5	2289.0	2905.5	2897.1	2359.1	1096.9
70°	187.8	188.9	196.7	223.1	280.2	349.2	1048.1	2438.1	2500.9	1801.9	1001.6
72.5°	183.8	183.8	182.7	184.4	181.0	189.4	367.7	1467.9	1559.3	1258.8	811.6
75°	179.9	180.5	178.8	173.2	140.7	118.3	134.5	618.2	685.5	828.4	608.1
77.5°	168.1	169.3	174.3	160.3	127.8	83.5	76.8	196.2	229.2	529.1	445.6
80°	63.3	63.3	63.3	58.3	85.2	63.3	55.5	80.1	85.2	298.2	274.1
82.5°	46.5	46.0	43.7	40.4	34.2	31.9	45.4	60.5	60.5	139.6	104.2
85°	13.5	13.5	15.1	20.2	25.2	28.0	34.7	46.5	48.2	53.2	15.7
87.5°	6.2	6.2	7.8	10.1	13.5	20.2	29.1	39.8	40.4	44.3	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1057512

CATALOG NUMBER: GAP-SA1A-727-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3
2.5°	21.3	20.7	20.2	19.6	18.5	17.4	15.7	15.1	14.6	14.6	14.6
5°	21.3	20.2	18.5	16.8	15.7	14.0	12.9	12.3	11.8	11.2	11.2
7.5°	20.7	19.1	16.8	15.1	14.0	12.3	10.6	10.1	9.5	9.5	9.5
10°	20.7	18.5	15.7	14.0	12.3	10.1	8.4	7.8	7.3	6.7	6.7
12.5°	19.6	17.4	14.6	12.3	10.1	7.8	6.2	5.0	4.5	4.5	4.5
15°	19.1	16.8	13.5	10.6	7.8	5.6	3.9	2.8	2.2	2.8	2.8
17.5°	18.5	15.1	12.3	8.4	5.6	3.4	1.7	0.6	0.6	0.6	0.6
20°	18.5	14.6	10.6	6.7	3.9	1.7	0.6	0.0	0.0	0.0	0.0
22.5°	19.1	14.6	9.5	5.6	2.2	1.1	0.0	0.0	0.0	0.0	0.0
25°	19.6	14.0	8.4	3.9	1.7	0.6	0.0	0.0	0.0	0.0	0.0
27.5°	20.2	13.5	7.3	2.8	1.1	0.0	0.0	0.0	0.0	0.0	0.0
30°	21.3	12.9	6.2	2.2	0.6	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	23.0	12.3	5.0	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	24.7	11.2	3.4	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	26.9	11.2	2.2	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	30.3	11.2	2.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	35.9	11.8	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	46.5	15.1	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	66.1	23.0	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	93.6	33.1	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	117.1	34.7	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	121.6	24.7	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	104.8	20.2	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	90.2	13.5	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	108.7	11.2	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	173.2	10.6	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	269.6	10.6	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	302.1	10.6	1.7	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	233.7	8.4	1.7	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	146.8	6.7	1.7	1.1	0.6	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	80.1	4.5	1.7	1.1	0.6	0.0	0.0	0.0	0.0	0.0	0.0
80°	30.3	3.4	1.7	1.1	1.1	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	10.6	2.8	2.2	1.7	1.1	0.6	0.0	0.0	0.0	0.0	0.0
85°	3.9	2.2	2.2	1.7	1.7	0.6	0.0	0.0	0.0	0.0	0.0
87.5°	2.2	2.2	2.2	2.2	1.7	0.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ


Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-727-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672	CRI (Ra):	71.1		
CIE u':	0.2638	R1:	68.3	R9:	-27.8
CIE v':	0.5276	R2:	79.8	R10:	54.4
Duv:	-0.0002	R3:	91.2	R11:	65.8
CIE x:	0.4619	R4:	69.4	R12:	45.6
CIE y:	0.4106	R5:	66.5	R13:	69.8
CIE z:	0.1275	R6:	72.6	R14:	94.5
Peak Wavelength (nm):	601	R7:	77.0	R15:	60.1
Dominant Wavelength (nm):	584	R8:	44.1		
Purity:	61.88407				
Rf:	67.9				
Rg:	98.6				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.02

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.71

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18





Summary

$R_f = 67.9$
 $R_g = 98.6$
 $CIE R_a = 71.1$
 $R_g = -27.8$

Spectral Power Distribution Comparison







Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)