

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057591

Luminaire Tested: **GAP-SA1B-730-U-T4BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1057591  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAP-SA1B-730-U-T4BC  
Description: GALLEON PEDESTRAIAN COMPANION 800mA 1xLight Square PACKAGE 70CRI  
3000K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL  
Light Source: (14) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4080 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 38.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1057591

CATALOG NUMBER: GAP-SA1B-730-U-T4BC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P1057591

CATALOG NUMBER: GAP-SA1B-730-U-T4BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1057591

CATALOG NUMBER: GAP-SA1B-730-U-T4BC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 17.9     | 0.0    | 17.9   |
|                    | % Fixture | 0.4      | 0.0    | 0.4    |
| <b>Street Side</b> | Lumens    | 4062.1   | 0.0    | 4062.1 |
|                    | % Fixture | 99.6     | 0.0    | 99.6   |
| <b>Total</b>       | Lumens    | 4080.0   | 0.0    | 4080.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 8.6    | 0.2       |
| 10°-20°   | 65.2   | 1.6       |
| 20°-30°   | 196.2  | 4.8       |
| 30°-40°   | 432.1  | 10.6      |
| 40°-50°   | 664.0  | 16.3      |
| 50°-60°   | 817.7  | 20.0      |
| 60°-70°   | 1032.3 | 25.3      |
| 70°-80°   | 794.0  | 19.5      |
| 80°-90°   | 69.8   | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4080.0 | 100.0     |
| 0°-180°   | 4080.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P1057591


CATALOG NUMBER: GAP-SA1B-730-U-T4BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 267.0  | 6.5       |                         |      |         |
| FM   | (30°-60°)   | 1909.4 | 46.8      |                         |      |         |
| FH   | (60°-80°)   | 1816.1 | 44.5      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 69.6   | 1.7       |                         |      | G1/100  |
| BL   | (0°-30°)    | 3.0    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 4.4    | 0.1       | B0/220                  |      |         |
| BH   | (60°-80°)   | 10.3   | 0.3       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.2    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type IV Short



REPORT NUMBER: P1057591

CATALOG NUMBER: GAP-SA1B-730-U-T4BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 40°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   | 29.8   |
| 2.5°  | 66.6   | 65.8   | 62.8   | 58.9   | 55.9   | 53.6   | 50.5   | 45.9   | 41.3   | 36.0   | 32.1   |
| 5°    | 174.5  | 173.7  | 161.5  | 146.2  | 125.5  | 111.7  | 98.0   | 75.8   | 57.4   | 44.4   | 33.7   |
| 7.5°  | 322.9  | 320.7  | 309.2  | 285.4  | 241.8  | 218.1  | 192.8  | 135.5  | 88.0   | 55.1   | 36.0   |
| 10°   | 469.9  | 468.3  | 453.8  | 419.4  | 371.9  | 348.2  | 314.5  | 231.1  | 138.5  | 71.9   | 39.0   |
| 12.5° | 556.4  | 560.2  | 549.5  | 533.4  | 492.8  | 470.6  | 432.4  | 336.0  | 212.7  | 98.7   | 42.9   |
| 15°   | 627.5  | 629.1  | 619.1  | 609.2  | 587.0  | 568.6  | 536.5  | 447.7  | 301.5  | 134.7  | 47.4   |
| 17.5° | 715.5  | 713.2  | 702.5  | 691.0  | 666.6  | 652.8  | 632.1  | 551.0  | 396.4  | 186.0  | 53.6   |
| 20°   | 827.3  | 821.1  | 808.9  | 789.0  | 762.2  | 745.4  | 724.0  | 656.6  | 491.3  | 242.6  | 61.2   |
| 22.5° | 970.4  | 962.7  | 949.7  | 931.3  | 883.9  | 857.9  | 830.3  | 746.9  | 596.2  | 314.5  | 71.2   |
| 25°   | 1135.7 | 1131.8 | 1118.1 | 1092.1 | 1041.5 | 1007.1 | 962.7  | 852.5  | 700.2  | 391.1  | 83.4   |
| 27.5° | 1330.1 | 1323.2 | 1304.8 | 1274.2 | 1219.9 | 1174.7 | 1119.6 | 968.8  | 799.7  | 472.2  | 98.7   |
| 30°   | 1547.4 | 1532.1 | 1494.6 | 1467.8 | 1404.3 | 1359.9 | 1295.6 | 1123.4 | 902.3  | 557.1  | 114.8  |
| 32.5° | 1749.4 | 1729.5 | 1675.2 | 1638.5 | 1579.5 | 1539.7 | 1480.8 | 1279.5 | 1017.8 | 645.9  | 135.5  |
| 35°   | 1932.3 | 1910.9 | 1822.9 | 1767.0 | 1737.2 | 1703.5 | 1643.8 | 1457.9 | 1142.6 | 740.8  | 159.2  |
| 37.5° | 2086.9 | 2065.5 | 1952.2 | 1864.2 | 1845.8 | 1834.4 | 1786.2 | 1608.6 | 1284.1 | 847.9  | 186.7  |
| 40°   | 2173.4 | 2159.6 | 2061.7 | 1962.2 | 1927.0 | 1913.2 | 1878.0 | 1734.9 | 1441.8 | 955.1  | 218.9  |
| 42.5° | 2200.2 | 2191.8 | 2112.2 | 2063.2 | 1998.9 | 1971.4 | 1929.3 | 1831.3 | 1577.2 | 1075.2 | 255.6  |
| 45°   | 2185.6 | 2176.4 | 2118.3 | 2129.8 | 2076.2 | 2022.6 | 1965.2 | 1897.1 | 1691.3 | 1216.8 | 301.5  |
| 47.5° | 2123.6 | 2120.6 | 2080.8 | 2145.8 | 2139.7 | 2078.5 | 2007.3 | 1940.7 | 1789.2 | 1353.8 | 358.9  |
| 50°   | 1972.1 | 1970.6 | 1989.0 | 2123.6 | 2181.8 | 2124.4 | 2053.2 | 1979.8 | 1867.3 | 1490.8 | 432.4  |
| 52.5° | 1767.8 | 1778.5 | 1871.1 | 2082.3 | 2194.1 | 2160.4 | 2099.2 | 2024.2 | 1931.6 | 1627.7 | 531.1  |
| 55°   | 1659.9 | 1669.1 | 1790.7 | 2037.2 | 2191.8 | 2181.8 | 2145.8 | 2067.0 | 1990.5 | 1740.2 | 662.7  |
| 57.5° | 1741.8 | 1731.8 | 1787.7 | 2031.0 | 2181.8 | 2200.2 | 2179.5 | 2100.7 | 2044.1 | 1839.7 | 844.9  |
| 60°   | 1897.1 | 1894.1 | 1900.9 | 2074.7 | 2202.5 | 2230.0 | 2215.5 | 2123.6 | 2096.9 | 1915.5 | 1045.4 |
| 62.5° | 2054.0 | 2045.6 | 2052.5 | 2194.8 | 2274.4 | 2293.5 | 2275.9 | 2161.1 | 2138.2 | 1970.6 | 1262.7 |
| 65°   | 2132.1 | 2125.9 | 2158.1 | 2315.7 | 2377.0 | 2390.0 | 2367.0 | 2221.6 | 2145.1 | 1998.9 | 1399.7 |
| 67.5° | 2122.1 | 2120.6 | 2195.6 | 2400.7 | 2462.7 | 2470.3 | 2451.2 | 2282.1 | 2116.0 | 1998.1 | 1414.2 |
| 69°   | 2075.4 | 2072.4 | 2171.1 | 2409.1 | 2490.2 | 2495.6 | 2464.2 | 2251.4 | 2042.5 | 1946.9 | 1310.9 |
| 70°   | 2020.3 | 2023.4 | 2135.1 | 2393.8 | 2491.0 | 2483.3 | 2410.6 | 2207.8 | 1986.7 | 1887.9 | 1179.3 |
| 72.5° | 1815.2 | 1834.4 | 1987.4 | 2293.5 | 2386.1 | 2300.4 | 2205.5 | 2064.7 | 1880.3 | 1609.4 | 823.4  |
| 75°   | 1518.3 | 1545.1 | 1742.5 | 2085.4 | 2051.7 | 2008.9 | 1997.4 | 1890.2 | 1703.5 | 1069.1 | 585.4  |
| 77.5° | 742.3  | 831.1  | 1236.7 | 1601.7 | 1683.6 | 1727.2 | 1711.2 | 1562.7 | 1369.1 | 525.0  | 381.9  |
| 80°   | 39.0   | 40.6   | 65.0   | 153.1  | 779.8  | 991.8  | 1219.9 | 1193.1 | 1036.2 | 239.5  | 201.3  |
| 82.5° | 20.7   | 20.7   | 23.0   | 26.8   | 31.4   | 37.5   | 99.5   | 683.4  | 616.0  | 123.2  | 75.0   |
| 85°   | 11.5   | 11.5   | 13.8   | 18.4   | 23.7   | 27.5   | 31.4   | 41.3   | 132.4  | 44.4   | 12.2   |
| 87.5° | 5.4    | 6.9    | 9.2    | 13.0   | 16.8   | 21.4   | 24.5   | 30.6   | 39.0   | 37.5   | 2.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1057591

CATALOG NUMBER: GAP-SA1B-730-U-T4BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°   | 95°  | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|------|------|------|------|------|------|------|------|------|------|
| 0°    | 29.8  | 29.8 | 29.8 | 29.8 | 29.8 | 29.8 | 29.8 | 29.8 | 29.8 | 29.8 | 29.8 |
| 2.5°  | 29.8  | 28.3 | 26.0 | 24.5 | 23.7 | 22.2 | 20.7 | 19.9 | 19.1 | 18.4 | 19.1 |
| 5°    | 29.8  | 27.5 | 23.7 | 21.4 | 19.9 | 17.6 | 16.1 | 15.3 | 14.5 | 13.8 | 13.8 |
| 7.5°  | 29.8  | 26.0 | 21.4 | 18.4 | 16.1 | 14.5 | 12.2 | 11.5 | 10.7 | 9.9  | 9.9  |
| 10°   | 30.6  | 24.5 | 19.1 | 16.1 | 13.8 | 11.5 | 9.9  | 8.4  | 7.7  | 7.7  | 7.7  |
| 12.5° | 30.6  | 23.0 | 16.8 | 13.8 | 11.5 | 9.2  | 6.9  | 5.4  | 4.6  | 4.6  | 4.6  |
| 15°   | 30.6  | 21.4 | 15.3 | 11.5 | 9.2  | 6.9  | 3.8  | 2.3  | 1.5  | 1.5  | 0.8  |
| 17.5° | 31.4  | 20.7 | 13.8 | 9.9  | 6.9  | 3.8  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  |
| 20°   | 32.9  | 19.9 | 12.2 | 8.4  | 4.6  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 22.5° | 34.4  | 19.1 | 10.7 | 6.1  | 2.3  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 25°   | 37.5  | 19.1 | 9.9  | 5.4  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 27.5° | 40.6  | 19.1 | 7.7  | 3.1  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 30°   | 42.9  | 19.1 | 6.9  | 2.3  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 32.5° | 45.9  | 19.1 | 6.1  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 35°   | 48.2  | 18.4 | 4.6  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 37.5° | 50.5  | 17.6 | 3.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 40°   | 53.6  | 16.8 | 3.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 42.5° | 56.6  | 15.3 | 2.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 45°   | 60.5  | 14.5 | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 47.5° | 65.8  | 13.8 | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 50°   | 73.5  | 13.8 | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 52.5° | 86.5  | 13.8 | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 55°   | 107.9 | 13.8 | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 57.5° | 145.4 | 13.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 60°   | 218.9 | 13.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 62.5° | 338.3 | 15.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 65°   | 517.3 | 18.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 67.5° | 655.8 | 22.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 69°   | 592.3 | 20.7 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 70°   | 502.0 | 16.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.5° | 279.3 | 8.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 75°   | 145.4 | 3.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 77.5° | 62.0  | 2.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 80°   | 18.4  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 82.5° | 6.1   | 1.5  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 85°   | 2.3   | 1.5  | 0.8  | 0.8  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 87.5° | 1.5   | 0.8  | 0.8  | 0.8  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 90°   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 3000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 2985  
 CIE  $u'$ : 0.2504  
 CIE  $v'$ : 0.5243  
 Duv: 0.0019  
 CIE x: 0.4408  
 CIE y: 0.4101  
 CIE z: 0.1491  
 Peak Wavelength (nm): 595  
 Dominant Wavelength (nm): 582  
 Purity: 55.41818  
 R<sub>f</sub>: 73.8  
 R<sub>g</sub>: 94.4

CRI (Ra): 70.8  
 R1: 66.3  
 R2: 80.6  
 R3: 94.5  
 R4: 68.2  
 R5: 66.5  
 R6: 74.7  
 R7: 76.2  
 R8: 39.6  
 R9: -43.2  
 R10: 57.6  
 R11: 64.8  
 R12: 53.5  
 R13: 68.7  
 R14: 97.0  
 R15: 56.4



### Test Conditions


Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-4

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 142                                  | NR                             | 620               | 803                                  | NR                             | 750               | 17                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 189                                  | NR                             | 625               | 734                                  | NR                             | 755               | 15                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 240                                  | NR                             | 630               | 670                                  | NR                             | 760               | 13                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 290                                  | NR                             | 635               | 600                                  | NR                             | 765               | 11                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 335                                  | NR                             | 640               | 535                                  | NR                             | 770               | 9                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 375                                  | NR                             | 645               | 473                                  | NR                             | 775               | 8                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 408                                  | NR                             | 650               | 415                                  | NR                             | 780               | 7                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 434                                  | NR                             | 655               | 362                                  | NR                             | 785               | 6                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 461                                  | NR                             | 660               | 313                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 8                                    | NR                             | 535               | 486                                  | NR                             | 665               | 271                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 16                                   | NR                             | 540               | 514                                  | NR                             | 670               | 231                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 33                                   | NR                             | 545               | 549                                  | NR                             | 675               | 198                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 69                                   | NR                             | 550               | 591                                  | NR                             | 680               | 169                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 131                                  | NR                             | 555               | 640                                  | NR                             | 685               | 144                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 227                                  | NR                             | 560               | 695                                  | NR                             | 690               | 123                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 369                                  | NR                             | 565               | 757                                  | NR                             | 695               | 104                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 517                                  | NR                             | 570               | 822                                  | NR                             | 700               | 88                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 498                                  | NR                             | 575               | 882                                  | NR                             | 705               | 75                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 315                                  | NR                             | 580               | 935                                  | NR                             | 710               | 63                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 204                                  | NR                             | 585               | 972                                  | NR                             | 715               | 54                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 145                                  | NR                             | 590               | 996                                  | NR                             | 720               | 46                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 100                                  | NR                             | 595               | 1000                                 | NR                             | 725               | 39                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 78                                   | NR                             | 600               | 989                                  | NR                             | 730               | 33                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 76                                   | NR                             | 605               | 960                                  | NR                             | 735               | 28                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 83                                   | NR                             | 610               | 918                                  | NR                             | 740               | 24                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 105                                  | NR                             | 615               | 864                                  | NR                             | 745               | 20                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-4

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.19

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 142                         | NR               | 620       | 803                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 189                         | NR               | 625       | 734                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 240                         | NR               | 630       | 670                         | NR               | 760       | 13                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 290                         | NR               | 635       | 600                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 335                         | NR               | 640       | 535                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 375                         | NR               | 645       | 473                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 408                         | NR               | 650       | 415                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 434                         | NR               | 655       | 362                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 461                         | NR               | 660       | 313                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 8                           | NR               | 535       | 486                         | NR               | 665       | 271                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 16                          | NR               | 540       | 514                         | NR               | 670       | 231                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 33                          | NR               | 545       | 549                         | NR               | 675       | 198                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 69                          | NR               | 550       | 591                         | NR               | 680       | 169                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 131                         | NR               | 555       | 640                         | NR               | 685       | 144                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 227                         | NR               | 560       | 695                         | NR               | 690       | 123                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 369                         | NR               | 565       | 757                         | NR               | 695       | 104                         | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 517                         | NR               | 570       | 822                         | NR               | 700       | 88                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 498                         | NR               | 575       | 882                         | NR               | 705       | 75                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 315                         | NR               | 580       | 935                         | NR               | 710       | 63                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 204                         | NR               | 585       | 972                         | NR               | 715       | 54                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 145                         | NR               | 590       | 996                         | NR               | 720       | 46                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 100                         | NR               | 595       | 1000                        | NR               | 725       | 39                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 78                          | NR               | 600       | 989                         | NR               | 730       | 33                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 76                          | NR               | 605       | 960                         | NR               | 735       | 28                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 83                          | NR               | 610       | 918                         | NR               | 740       | 24                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 105                         | NR               | 615       | 864                         | NR               | 745       | 20                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-4

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.13


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 142                                  | NR                             | 620               | 803                                  | NR                             | 750               | 17                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 189                                  | NR                             | 625               | 734                                  | NR                             | 755               | 15                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 240                                  | NR                             | 630               | 670                                  | NR                             | 760               | 13                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 290                                  | NR                             | 635               | 600                                  | NR                             | 765               | 11                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 335                                  | NR                             | 640               | 535                                  | NR                             | 770               | 9                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 375                                  | NR                             | 645               | 473                                  | NR                             | 775               | 8                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 408                                  | NR                             | 650               | 415                                  | NR                             | 780               | 7                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 434                                  | NR                             | 655               | 362                                  | NR                             | 785               | 6                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 461                                  | NR                             | 660               | 313                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 8                                    | NR                             | 535               | 486                                  | NR                             | 665               | 271                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 16                                   | NR                             | 540               | 514                                  | NR                             | 670               | 231                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 33                                   | NR                             | 545               | 549                                  | NR                             | 675               | 198                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 69                                   | NR                             | 550               | 591                                  | NR                             | 680               | 169                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 131                                  | NR                             | 555               | 640                                  | NR                             | 685               | 144                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 227                                  | NR                             | 560               | 695                                  | NR                             | 690               | 123                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 369                                  | NR                             | 565               | 757                                  | NR                             | 695               | 104                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 517                                  | NR                             | 570               | 822                                  | NR                             | 700               | 88                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 498                                  | NR                             | 575               | 882                                  | NR                             | 705               | 75                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 315                                  | NR                             | 580               | 935                                  | NR                             | 710               | 63                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 204                                  | NR                             | 585               | 972                                  | NR                             | 715               | 54                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 145                                  | NR                             | 590               | 996                                  | NR                             | 720               | 46                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 100                                  | NR                             | 595               | 1000                                 | NR                             | 725               | 39                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 78                                   | NR                             | 600               | 989                                  | NR                             | 730               | 33                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 76                                   | NR                             | 605               | 960                                  | NR                             | 735               | 28                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 83                                   | NR                             | 610               | 918                                  | NR                             | 740               | 24                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 105                                  | NR                             | 615               | 864                                  | NR                             | 745               | 20                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-4





TM-30-18

### Summary

$R_f = 73.8$   
 $R_g = 94.4$   
 $\text{CIE } R_a = 70.8$   
 $R_g = -43.2$




### Color Vector Graphics








**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 |            |



### Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)