

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064551

Luminaire Tested: **GLAN-SA8C-722-U-RBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1064551  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA8C-722-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 8xLight Square PACKAGE  
70CRI 2200K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (112) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 29424.2 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4


Input Watts (W): 372.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 4.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1064551  
CATALOG NUMBER: GLAN-SA8C-722-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 147.3    | 0.0    | 147.3   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 29276.9  | 0.0    | 29276.9 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 29424.2  | 0.0    | 29424.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 11.5    | 0.0       |
| 10°-20°   | 64.6    | 0.2       |
| 20°-30°   | 697.3   | 2.4       |
| 30°-40°   | 2062.1  | 7.0       |
| 40°-50°   | 6145.5  | 20.9      |
| 50°-60°   | 9744.6  | 33.1      |
| 60°-70°   | 8134.4  | 27.6      |
| 70°-80°   | 2508.3  | 8.5       |
| 80°-90°   | 55.8    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 29424.2 | 100.0     |
| 0°-180°   | 29424.2 | 100.0     |



REPORT NUMBER: P1064551


CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 746.4   | 2.5       |                         |      |          |
| FM   | (30°-60°)   | 17899.6 | 60.8      |                         |      |          |
| FH   | (60°-80°)   | 10587.8 | 36.0      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 43.1    | 0.1       |                         |      | G1/100   |
| BL   | (0°-30°)    | 27.1    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 52.7    | 0.2       | B0/220                  |      |          |
| BH   | (60°-80°)   | 55.0    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 12.7    | 0.0       |                         |      | G1/100   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° | 25°   |
|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 129.0  | 129.0  | 129.0  | 129.0  | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 |
| 2.5°   | 117.8  | 117.8  | 117.8  | 117.8  | 115.6 | 115.6 | 113.4 | 113.4 | 111.2 | 111.2 | 109.0 |
| 5°     | 124.5  | 124.5  | 122.3  | 120.1  | 120.1 | 117.8 | 115.6 | 113.4 | 113.4 | 111.2 | 109.0 |
| 7.5°   | 135.6  | 133.4  | 131.2  | 129.0  | 124.5 | 122.3 | 117.8 | 115.6 | 113.4 | 109.0 | 106.7 |
| 10°    | 149.0  | 144.5  | 140.1  | 135.6  | 131.2 | 126.7 | 122.3 | 120.1 | 115.6 | 113.4 | 109.0 |
| 12.5°  | 166.8  | 160.1  | 151.2  | 144.5  | 140.1 | 133.4 | 129.0 | 124.5 | 117.8 | 113.4 | 106.7 |
| 15°    | 182.3  | 173.4  | 162.3  | 153.4  | 146.8 | 137.9 | 131.2 | 124.5 | 120.1 | 113.4 | 106.7 |
| 17.5°  | 204.6  | 189.0  | 171.2  | 160.1  | 151.2 | 140.1 | 129.0 | 122.3 | 115.6 | 106.7 | 100.1 |
| 20°    | 242.4  | 211.2  | 177.9  | 164.5  | 151.2 | 137.9 | 124.5 | 115.6 | 109.0 | 100.1 | 93.4  |
| 22.5°  | 302.4  | 249.0  | 195.7  | 175.7  | 157.9 | 137.9 | 120.1 | 111.2 | 102.3 | 93.4  | 84.5  |
| 25°    | 418.0  | 322.4  | 226.8  | 200.1  | 173.4 | 146.8 | 120.1 | 109.0 | 100.1 | 88.9  | 80.0  |
| 27.5°  | 555.9  | 413.6  | 269.1  | 231.3  | 195.7 | 157.9 | 120.1 | 106.7 | 95.6  | 82.3  | 68.9  |
| 30°    | 696.0  | 507.0  | 315.7  | 266.8  | 217.9 | 169.0 | 120.1 | 104.5 | 91.2  | 75.6  | 60.0  |
| 32.5°  | 829.4  | 593.7  | 355.8  | 298.0  | 240.1 | 180.1 | 122.3 | 104.5 | 86.7  | 68.9  | 51.1  |
| 35°    | 965.0  | 664.8  | 362.4  | 302.4  | 242.4 | 180.1 | 120.1 | 100.1 | 82.3  | 62.3  | 44.5  |
| 37.5°  | 1138.5 | 744.9  | 349.1  | 289.1  | 231.3 | 171.2 | 113.4 | 95.6  | 77.8  | 57.8  | 40.0  |
| 40°    | 1400.8 | 878.3  | 355.8  | 293.5  | 231.3 | 169.0 | 106.7 | 88.9  | 73.4  | 55.6  | 37.8  |
| 42.5°  | 1885.6 | 1136.2 | 384.7  | 313.5  | 242.4 | 169.0 | 97.8  | 82.3  | 68.9  | 53.4  | 37.8  |
| 45°    | 3259.7 | 1887.8 | 515.9  | 409.1  | 302.4 | 195.7 | 88.9  | 75.6  | 64.5  | 51.1  | 40.0  |
| 47.5°  | 5392.1 | 3159.7 | 927.2  | 716.0  | 507.0 | 295.7 | 86.7  | 75.6  | 64.5  | 51.1  | 40.0  |
| 50°    | 6881.9 | 4024.6 | 1167.4 | 898.3  | 629.3 | 360.2 | 91.2  | 77.8  | 66.7  | 53.4  | 42.2  |
| 52.5°  | 6870.8 | 4086.9 | 1300.8 | 998.4  | 698.2 | 395.8 | 95.6  | 82.3  | 71.2  | 57.8  | 44.5  |
| 55°    | 6108.1 | 3717.8 | 1325.2 | 1018.4 | 713.8 | 406.9 | 102.3 | 88.9  | 75.6  | 62.3  | 48.9  |
| 57.5°  | 5105.3 | 3157.5 | 1209.6 | 936.1  | 664.8 | 391.3 | 117.8 | 102.3 | 88.9  | 73.4  | 60.0  |
| 60°    | 4038.0 | 2490.4 | 942.8  | 744.9  | 549.2 | 351.3 | 155.6 | 135.6 | 117.8 | 97.8  | 77.8  |
| 62.5°  | 2788.3 | 1805.5 | 822.7  | 660.4  | 500.3 | 338.0 | 177.9 | 157.9 | 140.1 | 120.1 | 100.1 |
| 65°    | 1972.3 | 1358.6 | 742.7  | 604.8  | 469.2 | 331.3 | 193.4 | 171.2 | 151.2 | 129.0 | 106.7 |
| 67.5°  | 1474.2 | 1080.7 | 684.9  | 567.0  | 449.2 | 331.3 | 213.5 | 186.8 | 162.3 | 135.6 | 109.0 |
| 70°    | 1129.6 | 887.2  | 642.6  | 547.0  | 453.6 | 358.0 | 262.4 | 224.6 | 189.0 | 151.2 | 115.6 |
| 72.5°  | 920.6  | 758.2  | 593.7  | 524.8  | 455.8 | 386.9 | 318.0 | 269.1 | 220.1 | 169.0 | 120.1 |
| 75°    | 762.7  | 649.3  | 535.9  | 478.1  | 422.5 | 364.7 | 306.9 | 262.4 | 220.1 | 175.7 | 131.2 |
| 77.5°  | 507.0  | 462.5  | 415.8  | 382.5  | 349.1 | 313.5 | 280.2 | 242.4 | 206.8 | 169.0 | 131.2 |
| 80°    | 177.9  | 171.2  | 164.5  | 177.9  | 191.2 | 204.6 | 217.9 | 191.2 | 166.8 | 140.1 | 115.6 |
| 82.5°  | 26.7   | 24.5   | 22.2   | 24.5   | 26.7  | 28.9  | 31.1  | 33.4  | 35.6  | 37.8  | 40.0  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   | 52.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 |
| 2.5°   | 109.0 | 109.0 | 106.7 | 106.7 | 106.7 | 104.5 | 104.5 | 102.3 | 102.3 | 102.3 | 100.1 |
| 5°     | 106.7 | 106.7 | 104.5 | 102.3 | 100.1 | 100.1 | 97.8  | 95.6  | 95.6  | 93.4  | 93.4  |
| 7.5°   | 104.5 | 102.3 | 100.1 | 97.8  | 95.6  | 93.4  | 91.2  | 88.9  | 88.9  | 86.7  | 86.7  |
| 10°    | 106.7 | 102.3 | 100.1 | 95.6  | 93.4  | 91.2  | 86.7  | 84.5  | 82.3  | 82.3  | 80.0  |
| 12.5°  | 102.3 | 100.1 | 95.6  | 91.2  | 88.9  | 84.5  | 82.3  | 77.8  | 75.6  | 75.6  | 73.4  |
| 15°    | 102.3 | 97.8  | 91.2  | 86.7  | 82.3  | 80.0  | 75.6  | 71.2  | 68.9  | 66.7  | 64.5  |
| 17.5°  | 95.6  | 91.2  | 84.5  | 80.0  | 75.6  | 71.2  | 66.7  | 62.3  | 60.0  | 57.8  | 55.6  |
| 20°    | 86.7  | 82.3  | 75.6  | 68.9  | 64.5  | 60.0  | 55.6  | 51.1  | 48.9  | 46.7  | 42.2  |
| 22.5°  | 77.8  | 73.4  | 66.7  | 60.0  | 55.6  | 51.1  | 44.5  | 40.0  | 37.8  | 33.4  | 31.1  |
| 25°    | 73.4  | 66.7  | 60.0  | 53.4  | 46.7  | 42.2  | 35.6  | 28.9  | 24.5  | 20.0  | 13.3  |
| 27.5°  | 62.3  | 55.6  | 48.9  | 42.2  | 35.6  | 28.9  | 22.2  | 15.6  | 11.1  | 8.9   | 4.4   |
| 30°    | 53.4  | 46.7  | 40.0  | 33.4  | 24.5  | 17.8  | 11.1  | 2.2   | 2.2   | 2.2   | 0.0   |
| 32.5°  | 44.5  | 37.8  | 28.9  | 22.2  | 17.8  | 11.1  | 6.7   | 0.0   | 0.0   | 0.0   | 0.0   |
| 35°    | 35.6  | 28.9  | 20.0  | 13.3  | 11.1  | 6.7   | 4.4   | 0.0   | 0.0   | 0.0   | 0.0   |
| 37.5°  | 31.1  | 24.5  | 15.6  | 6.7   | 4.4   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   |
| 40°    | 28.9  | 20.0  | 11.1  | 2.2   | 2.2   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 42.5°  | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 45°    | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 47.5°  | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 50°    | 31.1  | 22.2  | 11.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 52.5°  | 35.6  | 26.7  | 17.8  | 8.9   | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55°    | 44.5  | 40.0  | 33.4  | 28.9  | 22.2  | 15.6  | 6.7   | 0.0   | 0.0   | 0.0   | 0.0   |
| 57.5°  | 57.8  | 57.8  | 55.6  | 53.4  | 40.0  | 26.7  | 13.3  | 0.0   | 0.0   | 0.0   | 0.0   |
| 60°    | 77.8  | 77.8  | 77.8  | 77.8  | 57.8  | 40.0  | 20.0  | 0.0   | 0.0   | 0.0   | 0.0   |
| 62.5°  | 95.6  | 91.2  | 84.5  | 80.0  | 60.0  | 40.0  | 20.0  | 0.0   | 0.0   | 0.0   | 0.0   |
| 65°    | 95.6  | 86.7  | 75.6  | 64.5  | 48.9  | 33.4  | 15.6  | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5°  | 88.9  | 71.2  | 51.1  | 33.4  | 24.5  | 17.8  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°    | 88.9  | 62.3  | 35.6  | 8.9   | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5°  | 88.9  | 60.0  | 28.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°    | 97.8  | 66.7  | 33.4  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 77.5°  | 97.8  | 66.7  | 33.4  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°    | 86.7  | 57.8  | 28.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5°  | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° | 80°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 |
| 2.5°   | 100.1 | 100.1 | 100.1 | 97.8  | 97.8  | 97.8  | 97.8  | 95.6  | 95.6  | 95.6  | 95.6  |
| 5°     | 91.2  | 91.2  | 88.9  | 88.9  | 86.7  | 86.7  | 84.5  | 84.5  | 82.3  | 82.3  | 82.3  |
| 7.5°   | 84.5  | 82.3  | 82.3  | 80.0  | 77.8  | 77.8  | 75.6  | 75.6  | 73.4  | 71.2  | 71.2  |
| 10°    | 77.8  | 75.6  | 75.6  | 73.4  | 71.2  | 68.9  | 68.9  | 66.7  | 64.5  | 62.3  | 60.0  |
| 12.5°  | 71.2  | 68.9  | 66.7  | 64.5  | 62.3  | 60.0  | 60.0  | 57.8  | 55.6  | 53.4  | 53.4  |
| 15°    | 62.3  | 60.0  | 57.8  | 55.6  | 53.4  | 51.1  | 51.1  | 48.9  | 46.7  | 44.5  | 42.2  |
| 17.5°  | 53.4  | 51.1  | 51.1  | 48.9  | 46.7  | 44.5  | 42.2  | 37.8  | 35.6  | 33.4  | 28.9  |
| 20°    | 40.0  | 37.8  | 35.6  | 33.4  | 31.1  | 26.7  | 24.5  | 20.0  | 15.6  | 13.3  | 11.1  |
| 22.5°  | 26.7  | 22.2  | 20.0  | 15.6  | 11.1  | 8.9   | 6.7   | 2.2   | 0.0   | 0.0   | 0.0   |
| 25°    | 8.9   | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  | 107.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|--------|
| 0°     | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0 | 129.0  | 129.0 | 129.0  |
| 2.5°   | 93.4  | 93.4  | 93.4  | 91.2  | 91.2  | 91.2  | 91.2  | 91.2  | 91.2   | 91.2  | 91.2   |
| 5°     | 80.0  | 80.0  | 80.0  | 77.8  | 77.8  | 75.6  | 75.6  | 75.6  | 73.4   | 73.4  | 73.4   |
| 7.5°   | 68.9  | 66.7  | 66.7  | 64.5  | 64.5  | 62.3  | 62.3  | 62.3  | 60.0   | 60.0  | 60.0   |
| 10°    | 57.8  | 55.6  | 55.6  | 53.4  | 53.4  | 51.1  | 51.1  | 48.9  | 48.9   | 46.7  | 46.7   |
| 12.5°  | 51.1  | 48.9  | 46.7  | 44.5  | 44.5  | 42.2  | 40.0  | 40.0  | 37.8   | 35.6  | 35.6   |
| 15°    | 40.0  | 37.8  | 35.6  | 33.4  | 31.1  | 28.9  | 26.7  | 26.7  | 24.5   | 22.2  | 20.0   |
| 17.5°  | 26.7  | 22.2  | 20.0  | 17.8  | 17.8  | 15.6  | 13.3  | 11.1  | 8.9    | 6.7   | 6.7    |
| 20°    | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° | 135°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 |
| 2.5°   | 91.2  | 88.9   | 88.9  | 88.9   | 91.2  | 91.2   | 91.2  | 91.2   | 91.2  | 91.2   | 91.2  |
| 5°     | 73.4  | 71.2   | 71.2  | 71.2   | 71.2  | 71.2   | 71.2  | 71.2   | 71.2  | 71.2   | 71.2  |
| 7.5°   | 60.0  | 57.8   | 57.8  | 57.8   | 57.8  | 55.6   | 55.6  | 55.6   | 55.6  | 55.6   | 55.6  |
| 10°    | 46.7  | 44.5   | 44.5  | 44.5   | 44.5  | 42.2   | 42.2  | 42.2   | 42.2  | 42.2   | 42.2  |
| 12.5°  | 33.4  | 33.4   | 31.1  | 31.1   | 31.1  | 28.9   | 28.9  | 28.9   | 28.9  | 26.7   | 26.7  |
| 15°    | 20.0  | 17.8   | 15.6  | 15.6   | 15.6  | 13.3   | 13.3  | 13.3   | 13.3  | 11.1   | 11.1  |
| 17.5°  | 4.4   | 4.4    | 2.2   | 2.2    | 2.2   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  | 162.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  |
| 2.5°   | 93.4   | 93.4  | 95.6   | 95.6  | 97.8   | 102.3 | 104.5  | 106.7 | 111.2  | 115.6 | 117.8  |
| 5°     | 73.4   | 75.6  | 75.6   | 77.8  | 80.0   | 82.3  | 84.5   | 86.7  | 91.2   | 95.6  | 100.1  |
| 7.5°   | 57.8   | 57.8  | 60.0   | 60.0  | 62.3   | 66.7  | 68.9   | 71.2  | 75.6   | 82.3  | 86.7   |
| 10°    | 44.5   | 44.5  | 46.7   | 46.7  | 48.9   | 53.4  | 55.6   | 57.8  | 62.3   | 68.9  | 73.4   |
| 12.5°  | 28.9   | 31.1  | 31.1   | 33.4  | 35.6   | 40.0  | 42.2   | 44.5  | 48.9   | 53.4  | 57.8   |
| 15°    | 13.3   | 15.6  | 15.6   | 17.8  | 20.0   | 24.5  | 26.7   | 28.9  | 33.4   | 40.0  | 44.5   |
| 17.5°  | 2.2    | 2.2   | 4.4    | 4.4   | 6.7    | 8.9   | 11.1   | 13.3  | 20.0   | 24.5  | 31.1   |
| 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    | 8.9   | 13.3   |
| 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 2.2   | 2.2    |
| 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 |
| 2.5°   | 122.3 | 126.7  | 131.2 | 135.6  | 140.1 | 144.5  | 146.8 | 151.2  | 153.4 | 155.6  | 155.6 |
| 5°     | 104.5 | 109.0  | 115.6 | 120.1  | 124.5 | 129.0  | 133.4 | 135.6  | 137.9 | 140.1  | 142.3 |
| 7.5°   | 91.2  | 95.6   | 102.3 | 106.7  | 111.2 | 115.6  | 120.1 | 124.5  | 126.7 | 129.0  | 131.2 |
| 10°    | 77.8  | 84.5   | 88.9  | 95.6   | 100.1 | 104.5  | 109.0 | 113.4  | 117.8 | 120.1  | 124.5 |
| 12.5°  | 62.3  | 68.9   | 75.6  | 80.0   | 86.7  | 93.4   | 97.8  | 102.3  | 106.7 | 111.2  | 113.4 |
| 15°    | 48.9  | 55.6   | 62.3  | 66.7   | 73.4  | 80.0   | 86.7  | 91.2   | 95.6  | 100.1  | 104.5 |
| 17.5°  | 35.6  | 42.2   | 48.9  | 53.4   | 60.0  | 66.7   | 71.2  | 77.8   | 82.3  | 86.7   | 93.4  |
| 20°    | 17.8  | 24.5   | 31.1  | 37.8   | 44.5  | 51.1   | 55.6  | 62.3   | 66.7  | 71.2   | 75.6  |
| 22.5°  | 2.2   | 8.9    | 15.6  | 20.0   | 26.7  | 33.4   | 37.8  | 44.5   | 48.9  | 53.4   | 57.8  |
| 25°    | 0.0   | 2.2    | 6.7   | 8.9    | 11.1  | 15.6   | 20.0  | 24.5   | 28.9  | 33.4   | 40.0  |
| 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 4.4   | 8.9    | 13.3  | 17.8   | 22.2  |
| 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    | 6.7   |
| 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 2.2   |
| 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 2.2   | 4.4    | 8.9   |
| 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    | 6.7   | 11.1   | 13.3  | 15.6   | 20.0  |
| 87.5°  | 0.0   | 2.2    | 4.4   | 6.7    | 8.9   | 13.3   | 17.8  | 22.2   | 24.5  | 26.7   | 28.9  |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  |
| 2.5°   | 157.9  | 157.9 | 157.9  | 157.9 | 155.6  | 155.6 | 155.6  | 153.4 | 153.4  | 151.2 | 151.2  |
| 5°     | 144.5  | 146.8 | 146.8  | 146.8 | 146.8  | 146.8 | 146.8  | 146.8 | 144.5  | 144.5 | 144.5  |
| 7.5°   | 133.4  | 135.6 | 137.9  | 137.9 | 140.1  | 140.1 | 140.1  | 137.9 | 137.9  | 135.6 | 135.6  |
| 10°    | 126.7  | 129.0 | 129.0  | 131.2 | 131.2  | 131.2 | 131.2  | 131.2 | 131.2  | 131.2 | 131.2  |
| 12.5°  | 117.8  | 120.1 | 122.3  | 122.3 | 124.5  | 124.5 | 124.5  | 124.5 | 122.3  | 122.3 | 122.3  |
| 15°    | 106.7  | 111.2 | 113.4  | 115.6 | 115.6  | 117.8 | 117.8  | 117.8 | 117.8  | 117.8 | 117.8  |
| 17.5°  | 97.8   | 102.3 | 104.5  | 106.7 | 106.7  | 109.0 | 109.0  | 111.2 | 111.2  | 111.2 | 111.2  |
| 20°    | 80.0   | 84.5  | 86.7   | 91.2  | 93.4   | 95.6  | 97.8   | 100.1 | 100.1  | 102.3 | 100.1  |
| 22.5°  | 62.3   | 66.7  | 68.9   | 73.4  | 75.6   | 77.8  | 80.0   | 82.3  | 84.5   | 86.7  | 86.7   |
| 25°    | 44.5   | 48.9  | 51.1   | 55.6  | 57.8   | 60.0  | 62.3   | 64.5  | 64.5   | 66.7  | 68.9   |
| 27.5°  | 24.5   | 28.9  | 33.4   | 35.6  | 40.0   | 42.2  | 44.5   | 46.7  | 48.9   | 51.1  | 53.4   |
| 30°    | 11.1   | 13.3  | 15.6   | 20.0  | 22.2   | 24.5  | 26.7   | 31.1  | 33.4   | 35.6  | 37.8   |
| 32.5°  | 0.0    | 0.0   | 2.2    | 6.7   | 8.9    | 11.1  | 13.3   | 15.6  | 15.6   | 17.8  | 22.2   |
| 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 4.4   | 6.7    | 8.9   | 13.3   |
| 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    |
| 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    |
| 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    |
| 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    |
| 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    |
| 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    |
| 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    |
| 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 80°    | 4.4    | 4.4   | 4.4    | 6.7   | 6.7    | 6.7   | 6.7    | 6.7   | 6.7    | 6.7   | 6.7    |
| 82.5°  | 11.1   | 13.3  | 15.6   | 15.6  | 17.8   | 17.8  | 17.8   | 17.8  | 15.6   | 15.6  | 15.6   |
| 85°    | 22.2   | 24.5  | 26.7   | 26.7  | 28.9   | 28.9  | 28.9   | 28.9  | 28.9   | 28.9  | 28.9   |
| 87.5°  | 31.1   | 33.4  | 35.6   | 35.6  | 37.8   | 37.8  | 37.8   | 37.8  | 37.8   | 37.8  | 37.8   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 |
| 2.5°   | 149.0 | 149.0  | 146.8 | 146.8  | 146.8 | 146.8  | 146.8 | 149.0  | 151.2 | 151.2  | 153.4 |
| 5°     | 142.3 | 142.3  | 140.1 | 140.1  | 140.1 | 142.3  | 142.3 | 144.5  | 146.8 | 149.0  | 151.2 |
| 7.5°   | 135.6 | 133.4  | 133.4 | 135.6  | 135.6 | 137.9  | 137.9 | 140.1  | 142.3 | 144.5  | 146.8 |
| 10°    | 131.2 | 129.0  | 129.0 | 129.0  | 131.2 | 131.2  | 133.4 | 135.6  | 137.9 | 140.1  | 142.3 |
| 12.5°  | 122.3 | 122.3  | 122.3 | 122.3  | 124.5 | 124.5  | 126.7 | 129.0  | 133.4 | 135.6  | 137.9 |
| 15°    | 117.8 | 115.6  | 115.6 | 115.6  | 115.6 | 117.8  | 117.8 | 122.3  | 126.7 | 129.0  | 133.4 |
| 17.5°  | 109.0 | 109.0  | 106.7 | 106.7  | 109.0 | 109.0  | 111.2 | 115.6  | 120.1 | 122.3  | 126.7 |
| 20°    | 100.1 | 97.8   | 95.6  | 95.6   | 97.8  | 97.8   | 100.1 | 104.5  | 109.0 | 111.2  | 115.6 |
| 22.5°  | 86.7  | 84.5   | 84.5  | 84.5   | 84.5  | 86.7   | 86.7  | 91.2   | 97.8  | 102.3  | 106.7 |
| 25°    | 68.9  | 71.2   | 71.2  | 73.4   | 73.4  | 75.6   | 77.8  | 82.3   | 88.9  | 93.4   | 97.8  |
| 27.5°  | 53.4  | 55.6   | 55.6  | 60.0   | 62.3  | 64.5   | 66.7  | 73.4   | 80.0  | 84.5   | 91.2  |
| 30°    | 40.0  | 42.2   | 44.5  | 46.7   | 51.1  | 55.6   | 60.0  | 66.7   | 73.4  | 77.8   | 84.5  |
| 32.5°  | 24.5  | 28.9   | 31.1  | 35.6   | 40.0  | 44.5   | 48.9  | 55.6   | 64.5  | 71.2   | 77.8  |
| 35°    | 17.8  | 20.0   | 24.5  | 26.7   | 31.1  | 35.6   | 40.0  | 48.9   | 55.6  | 64.5   | 71.2  |
| 37.5°  | 8.9   | 13.3   | 17.8  | 22.2   | 26.7  | 31.1   | 35.6  | 44.5   | 53.4  | 60.0   | 68.9  |
| 40°    | 6.7   | 11.1   | 13.3  | 17.8   | 24.5  | 28.9   | 33.4  | 42.2   | 51.1  | 60.0   | 68.9  |
| 42.5°  | 4.4   | 6.7    | 8.9   | 15.6   | 20.0  | 26.7   | 33.4  | 42.2   | 51.1  | 60.0   | 68.9  |
| 45°    | 4.4   | 4.4    | 6.7   | 13.3   | 20.0  | 28.9   | 35.6  | 44.5   | 51.1  | 60.0   | 66.7  |
| 47.5°  | 4.4   | 6.7    | 8.9   | 17.8   | 22.2  | 28.9   | 35.6  | 42.2   | 51.1  | 57.8   | 64.5  |
| 50°    | 6.7   | 8.9    | 11.1  | 20.0   | 24.5  | 31.1   | 35.6  | 44.5   | 51.1  | 60.0   | 66.7  |
| 52.5°  | 4.4   | 6.7    | 8.9   | 17.8   | 24.5  | 33.4   | 40.0  | 48.9   | 57.8  | 64.5   | 73.4  |
| 55°    | 2.2   | 2.2    | 2.2   | 13.3   | 26.7  | 37.8   | 51.1  | 57.8   | 66.7  | 73.4   | 80.0  |
| 57.5°  | 0.0   | 0.0    | 0.0   | 8.9    | 26.7  | 42.2   | 57.8  | 66.7   | 75.6  | 82.3   | 91.2  |
| 60°    | 0.0   | 0.0    | 0.0   | 8.9    | 26.7  | 42.2   | 57.8  | 68.9   | 80.0  | 91.2   | 102.3 |
| 62.5°  | 0.0   | 0.0    | 0.0   | 8.9    | 22.2  | 35.6   | 48.9  | 66.7   | 86.7  | 104.5  | 122.3 |
| 65°    | 0.0   | 0.0    | 0.0   | 6.7    | 17.8  | 28.9   | 40.0  | 66.7   | 93.4  | 117.8  | 144.5 |
| 67.5°  | 0.0   | 0.0    | 0.0   | 6.7    | 17.8  | 26.7   | 37.8  | 66.7   | 93.4  | 122.3  | 149.0 |
| 70°    | 0.0   | 0.0    | 0.0   | 6.7    | 17.8  | 28.9   | 40.0  | 66.7   | 93.4  | 120.1  | 146.8 |
| 72.5°  | 0.0   | 0.0    | 0.0   | 6.7    | 20.0  | 31.1   | 44.5  | 66.7   | 88.9  | 111.2  | 133.4 |
| 75°    | 0.0   | 0.0    | 0.0   | 8.9    | 20.0  | 33.4   | 46.7  | 66.7   | 86.7  | 104.5  | 124.5 |
| 77.5°  | 0.0   | 0.0    | 0.0   | 6.7    | 20.0  | 31.1   | 44.5  | 64.5   | 84.5  | 102.3  | 122.3 |
| 80°    | 6.7   | 4.4    | 4.4   | 11.1   | 20.0  | 28.9   | 37.8  | 57.8   | 80.0  | 100.1  | 120.1 |
| 82.5°  | 13.3  | 13.3   | 11.1  | 15.6   | 20.0  | 26.7   | 33.4  | 51.1   | 71.2  | 88.9   | 106.7 |
| 85°    | 26.7  | 26.7   | 24.5  | 26.7   | 26.7  | 28.9   | 31.1  | 40.0   | 48.9  | 57.8   | 66.7  |
| 87.5°  | 35.6  | 35.6   | 33.4  | 33.4   | 33.4  | 31.1   | 31.1  | 31.1   | 31.1  | 28.9   | 28.9  |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   | 272.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|
| 0°     | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0 | 129.0  | 129.0  | 129.0  |
| 2.5°   | 155.6  | 157.9 | 157.9  | 160.1 | 162.3  | 164.5 | 164.5  | 166.8 | 166.8  | 166.8  | 166.8  |
| 5°     | 153.4  | 157.9 | 160.1  | 162.3 | 164.5  | 166.8 | 169.0  | 171.2 | 173.4  | 173.4  | 173.4  |
| 7.5°   | 151.2  | 153.4 | 157.9  | 160.1 | 164.5  | 166.8 | 171.2  | 173.4 | 175.7  | 177.9  | 180.1  |
| 10°    | 146.8  | 151.2 | 155.6  | 160.1 | 164.5  | 169.0 | 173.4  | 177.9 | 182.3  | 184.6  | 189.0  |
| 12.5°  | 142.3  | 149.0 | 153.4  | 157.9 | 164.5  | 171.2 | 175.7  | 182.3 | 186.8  | 191.2  | 197.9  |
| 15°    | 140.1  | 144.5 | 151.2  | 155.6 | 164.5  | 173.4 | 180.1  | 189.0 | 197.9  | 204.6  | 215.7  |
| 17.5°  | 133.4  | 142.3 | 149.0  | 155.6 | 164.5  | 175.7 | 184.6  | 193.4 | 206.8  | 220.1  | 237.9  |
| 20°    | 124.5  | 131.2 | 140.1  | 146.8 | 160.1  | 171.2 | 184.6  | 195.7 | 215.7  | 235.7  | 273.5  |
| 22.5°  | 115.6  | 124.5 | 131.2  | 140.1 | 155.6  | 169.0 | 184.6  | 197.9 | 231.3  | 262.4  | 349.1  |
| 25°    | 106.7  | 117.8 | 126.7  | 135.6 | 153.4  | 171.2 | 189.0  | 206.8 | 262.4  | 318.0  | 473.6  |
| 27.5°  | 102.3  | 111.2 | 122.3  | 131.2 | 153.4  | 177.9 | 200.1  | 222.4 | 311.3  | 398.0  | 658.2  |
| 30°    | 95.6   | 106.7 | 115.6  | 126.7 | 155.6  | 184.6 | 213.5  | 242.4 | 378.0  | 513.6  | 891.6  |
| 32.5°  | 88.9   | 100.1 | 111.2  | 122.3 | 160.1  | 197.9 | 233.5  | 271.3 | 449.2  | 624.8  | 1114.0 |
| 35°    | 82.3   | 95.6  | 106.7  | 117.8 | 166.8  | 217.9 | 266.8  | 315.7 | 513.6  | 709.3  | 1265.2 |
| 37.5°  | 80.0   | 93.4  | 104.5  | 115.6 | 169.0  | 220.1 | 273.5  | 324.6 | 520.3  | 716.0  | 1378.6 |
| 40°    | 82.3   | 93.4  | 106.7  | 117.8 | 162.3  | 206.8 | 249.0  | 293.5 | 498.1  | 700.4  | 1492.0 |
| 42.5°  | 82.3   | 95.6  | 109.0  | 122.3 | 157.9  | 193.4 | 229.0  | 264.6 | 491.4  | 718.2  | 1714.4 |
| 45°    | 80.0   | 93.4  | 106.7  | 120.1 | 153.4  | 184.6 | 217.9  | 249.0 | 531.4  | 811.6  | 2159.1 |
| 47.5°  | 77.8   | 91.2  | 104.5  | 117.8 | 151.2  | 184.6 | 217.9  | 251.3 | 687.1  | 1120.7 | 3290.9 |
| 50°    | 77.8   | 91.2  | 102.3  | 113.4 | 153.4  | 195.7 | 235.7  | 275.7 | 1000.6 | 1723.3 | 5040.8 |
| 52.5°  | 82.3   | 93.4  | 102.3  | 111.2 | 157.9  | 206.8 | 253.5  | 300.2 | 1271.9 | 2241.3 | 6346.0 |
| 55°    | 88.9   | 95.6  | 104.5  | 111.2 | 169.0  | 224.6 | 282.4  | 338.0 | 1354.1 | 2370.3 | 6490.6 |
| 57.5°  | 97.8   | 104.5 | 111.2  | 117.8 | 189.0  | 260.2 | 329.1  | 400.2 | 1360.8 | 2319.2 | 5856.9 |
| 60°    | 109.0  | 117.8 | 124.5  | 131.2 | 206.8  | 284.6 | 360.2  | 435.8 | 1231.9 | 2025.7 | 5007.5 |
| 62.5°  | 133.4  | 144.5 | 153.4  | 164.5 | 237.9  | 309.1 | 382.5  | 453.6 | 1022.8 | 1592.1 | 3913.5 |
| 65°    | 153.4  | 162.3 | 171.2  | 180.1 | 251.3  | 324.6 | 395.8  | 466.9 | 867.2  | 1267.4 | 2957.3 |
| 67.5°  | 157.9  | 166.8 | 173.4  | 182.3 | 255.7  | 329.1 | 400.2  | 473.6 | 742.7  | 1009.5 | 2183.5 |
| 70°    | 160.1  | 171.2 | 184.6  | 195.7 | 271.3  | 346.9 | 420.3  | 495.9 | 658.2  | 820.5  | 1545.4 |
| 72.5°  | 153.4  | 175.7 | 195.7  | 215.7 | 286.8  | 355.8 | 426.9  | 495.9 | 611.5  | 727.1  | 1149.6 |
| 75°    | 153.4  | 184.6 | 213.5  | 242.4 | 295.7  | 346.9 | 400.2  | 451.4 | 540.3  | 629.3  | 836.1  |
| 77.5°  | 162.3  | 202.3 | 242.4  | 282.4 | 313.5  | 342.4 | 373.6  | 402.5 | 460.3  | 518.1  | 629.3  |
| 80°    | 162.3  | 204.6 | 244.6  | 286.8 | 300.2  | 315.7 | 329.1  | 342.4 | 349.1  | 355.8  | 353.5  |
| 82.5°  | 140.1  | 173.4 | 206.8  | 240.1 | 224.6  | 209.0 | 193.4  | 177.9 | 166.8  | 153.4  | 160.1  |
| 85°    | 71.2   | 77.8  | 82.3   | 86.7  | 80.0   | 73.4  | 66.7   | 60.0  | 55.6   | 48.9   | 46.7   |
| 87.5°  | 28.9   | 28.9  | 26.7   | 26.7  | 26.7   | 26.7  | 24.5   | 24.5  | 24.5   | 24.5   | 22.2   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275°    | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  | 300°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   |
| 2.5°   | 166.8   | 164.5   | 164.5   | 162.3   | 160.1   | 157.9   | 155.6   | 153.4   | 151.2   | 149.0   | 146.8   |
| 5°     | 173.4   | 173.4   | 173.4   | 171.2   | 171.2   | 169.0   | 169.0   | 166.8   | 164.5   | 162.3   | 160.1   |
| 7.5°   | 180.1   | 182.3   | 182.3   | 184.6   | 184.6   | 184.6   | 184.6   | 182.3   | 182.3   | 182.3   | 180.1   |
| 10°    | 191.2   | 193.4   | 195.7   | 197.9   | 200.1   | 202.3   | 202.3   | 204.6   | 204.6   | 204.6   | 206.8   |
| 12.5°  | 204.6   | 211.2   | 215.7   | 222.4   | 226.8   | 233.5   | 237.9   | 244.6   | 249.0   | 253.5   | 255.7   |
| 15°    | 224.6   | 235.7   | 249.0   | 260.2   | 271.3   | 286.8   | 304.6   | 320.2   | 335.8   | 360.2   | 386.9   |
| 17.5°  | 253.5   | 289.1   | 324.6   | 358.0   | 393.6   | 471.4   | 549.2   | 624.8   | 702.6   | 816.0   | 927.2   |
| 20°    | 309.1   | 415.8   | 520.3   | 627.0   | 731.6   | 1005.0  | 1276.3  | 1549.8  | 1821.1  | 2112.4  | 2405.9  |
| 22.5°  | 433.6   | 696.0   | 958.4   | 1220.7  | 1483.1  | 2054.6  | 2623.8  | 3195.3  | 3764.5  | 4433.8  | 5103.1  |
| 25°    | 629.3   | 1111.8  | 1594.3  | 2074.6  | 2557.1  | 3451.0  | 4347.1  | 5240.9  | 6134.8  | 7004.2  | 7873.6  |
| 27.5°  | 916.1   | 1654.3  | 2392.6  | 3128.6  | 3866.8  | 5078.6  | 6292.7  | 7504.5  | 8716.4  | 9699.2  | 10682.0 |
| 30°    | 1269.7  | 2270.3  | 3270.9  | 4271.5  | 5272.1  | 6650.7  | 8029.3  | 9405.7  | 10784.3 | 11858.3 | 12934.5 |
| 32.5°  | 1603.2  | 2828.4  | 4053.6  | 5276.5  | 6501.7  | 8071.5  | 9643.6  | 11213.4 | 12783.3 | 13957.3 | 15133.6 |
| 35°    | 1821.1  | 3302.0  | 4785.1  | 6266.0  | 7746.9  | 9445.7  | 11144.5 | 12841.1 | 14539.9 | 15880.7 | 17221.5 |
| 37.5°  | 2039.0  | 3748.9  | 5456.6  | 7166.5  | 8874.2  | 10739.8 | 12605.4 | 14470.9 | 16336.5 | 17993.1 | 19651.8 |
| 40°    | 2283.6  | 4289.3  | 6292.7  | 8298.3  | 10301.8 | 12512.0 | 14720.0 | 16930.2 | 19138.2 | 21475.2 | 23812.1 |
| 42.5°  | 2708.3  | 5185.3  | 7664.6  | 10141.7 | 12618.7 | 15542.7 | 18466.7 | 21388.4 | 24312.4 | 27647.8 | 30983.1 |
| 45°    | 3506.6  | 6997.5  | 10490.8 | 13981.8 | 17472.7 | 21346.2 | 25221.9 | 29095.3 | 32968.7 | 37407.0 | 41845.2 |
| 47.5°  | 5461.1  | 10264.0 | 15064.6 | 19867.5 | 24668.2 | 28850.7 | 33031.0 | 37213.5 | 41393.8 | 45814.3 | 50234.7 |
| 50°    | 8356.1  | 13946.2 | 19536.2 | 25124.0 | 30714.1 | 34498.6 | 38280.8 | 42065.3 | 45847.6 | 50052.4 | 54257.1 |
| 52.5°  | 10450.7 | 16274.2 | 22100.0 | 27923.5 | 33747.0 | 37162.4 | 40580.0 | 43995.4 | 47410.8 | 51339.8 | 55268.8 |
| 55°    | 10608.6 | 16398.8 | 22191.1 | 27981.3 | 33771.5 | 37202.4 | 40633.4 | 44064.3 | 47495.3 | 51660.0 | 55827.0 |
| 57.5°  | 9392.3  | 15135.8 | 20877.0 | 26620.5 | 32361.7 | 36268.5 | 40173.1 | 44079.9 | 47984.5 | 52487.2 | 56989.9 |
| 60°    | 7989.3  | 13734.9 | 19478.4 | 25224.1 | 30967.5 | 35468.0 | 39970.7 | 44471.2 | 48971.7 | 53189.8 | 57405.7 |
| 62.5°  | 6232.6  | 12142.9 | 18055.3 | 23965.5 | 29875.8 | 34445.2 | 39014.6 | 43581.8 | 48151.2 | 51315.4 | 54481.7 |
| 65°    | 4645.0  | 10384.0 | 16123.0 | 21859.8 | 27598.8 | 31258.8 | 34918.8 | 38576.6 | 42236.5 | 44195.5 | 46156.7 |
| 67.5°  | 3357.6  | 8307.2  | 13254.6 | 18204.3 | 23151.7 | 25771.1 | 28390.4 | 31007.6 | 33626.9 | 35125.6 | 36626.5 |
| 70°    | 2270.3  | 5699.0  | 9125.5  | 12554.2 | 15980.7 | 18133.1 | 20287.8 | 22440.2 | 24592.6 | 26616.0 | 28637.2 |
| 72.5°  | 1572.1  | 3497.7  | 5425.5  | 7351.1  | 9276.7  | 11442.4 | 13606.0 | 15771.7 | 17935.2 | 20076.5 | 22217.8 |
| 75°    | 1042.9  | 1918.9  | 2797.2  | 3673.3  | 4549.4  | 6152.6  | 7758.0  | 9361.2  | 10964.4 | 12240.7 | 13517.0 |
| 77.5°  | 740.4   | 1002.8  | 1267.4  | 1529.8  | 1792.2  | 2092.4  | 2394.8  | 2695.0  | 2995.1  | 3451.0  | 3906.8  |
| 80°    | 351.3   | 384.7   | 418.0   | 449.2   | 482.5   | 591.5   | 700.4   | 809.4   | 918.3   | 1034.0  | 1149.6  |
| 82.5°  | 166.8   | 180.1   | 193.4   | 204.6   | 217.9   | 229.0   | 240.1   | 251.3   | 262.4   | 251.3   | 237.9   |
| 85°    | 44.5    | 44.5    | 46.7    | 46.7    | 46.7    | 46.7    | 46.7    | 46.7    | 46.7    | 44.5    | 42.2    |
| 87.5°  | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    | 17.8    | 17.8    | 15.6    | 15.6    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  | 325°    | 327.5° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0°     | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0  |
| 2.5°   | 144.5   | 142.3   | 140.1   | 137.9   | 135.6   | 131.2   | 129.0   | 129.0   | 129.0   | 126.7   | 126.7  |
| 5°     | 157.9   | 155.6   | 153.4   | 151.2   | 151.2   | 146.8   | 146.8   | 146.8   | 144.5   | 142.3   | 142.3  |
| 7.5°   | 180.1   | 177.9   | 175.7   | 173.4   | 173.4   | 171.2   | 169.0   | 169.0   | 169.0   | 166.8   | 164.5  |
| 10°    | 206.8   | 206.8   | 206.8   | 206.8   | 206.8   | 204.6   | 204.6   | 204.6   | 202.3   | 202.3   | 200.1  |
| 12.5°  | 260.2   | 262.4   | 266.8   | 271.3   | 277.9   | 277.9   | 277.9   | 275.7   | 275.7   | 273.5   | 266.8  |
| 15°    | 411.4   | 435.8   | 453.6   | 471.4   | 487.0   | 518.1   | 511.4   | 507.0   | 500.3   | 475.8   |        |
| 17.5°  | 1040.6  | 1151.8  | 1211.8  | 1269.7  | 1329.7  | 1467.6  | 1440.9  | 1416.4  | 1389.7  | 1271.9  |        |
| 20°    | 2697.2  | 2988.5  | 3181.9  | 3375.4  | 3571.0  | 3804.5  | 3728.9  | 3653.3  | 3577.7  | 3257.5  |        |
| 22.5°  | 5770.1  | 6439.4  | 6730.7  | 7022.0  | 7311.1  | 7442.3  | 7199.9  | 6959.7  | 6717.4  | 6123.7  |        |
| 25°    | 8740.8  | 9610.2  | 10101.6 | 10593.0 | 11082.2 | 10979.9 | 10662.0 | 10346.2 | 10028.3 | 9281.1  |        |
| 27.5°  | 11664.8 | 12647.6 | 13081.2 | 13512.6 | 13946.2 | 14001.8 | 13608.2 | 13216.8 | 12825.5 | 11965.0 |        |
| 30°    | 14008.4 | 15082.4 | 15551.6 | 16018.5 | 16487.7 | 16394.3 | 15987.4 | 15582.7 | 15178.0 | 14253.0 |        |
| 32.5°  | 16307.6 | 17481.6 | 17995.3 | 18508.9 | 19020.3 | 18969.2 | 18468.9 | 17970.8 | 17472.7 | 16365.4 |        |
| 35°    | 18560.1 | 19900.9 | 20608.0 | 21315.1 | 22022.2 | 21846.5 | 21252.8 | 20661.3 | 20069.9 | 18778.0 |        |
| 37.5°  | 21308.4 | 22964.9 | 23756.5 | 24548.1 | 25339.7 | 25446.4 | 24792.7 | 24141.2 | 23487.5 | 21899.9 |        |
| 40°    | 26149.1 | 28486.0 | 29700.1 | 30916.4 | 32130.5 | 32286.1 | 31463.4 | 30640.7 | 29818.0 | 27772.3 |        |
| 42.5°  | 34318.4 | 37653.8 | 39399.3 | 41142.6 | 42888.1 | 43550.7 | 42685.7 | 41820.7 | 40955.8 | 38191.9 |        |
| 45°    | 46283.4 | 50721.7 | 52849.6 | 54975.3 | 57103.3 | 56974.3 | 55726.9 | 54481.7 | 53236.5 | 49807.8 |        |
| 47.5°  | 54652.9 | 59073.4 | 60967.8 | 62862.3 | 64756.8 | 64507.7 | 62984.6 | 61463.7 | 59940.5 | 56238.3 |        |
| 50°    | 58459.7 | 62664.4 | 64565.6 | 66464.5 | 68365.6 | 67618.5 | 65857.4 | 64098.6 | 62339.8 | 58570.8 |        |
| 52.5°  | 59195.7 | 63124.7 | 65392.7 | 67663.0 | 69931.0 | 69206.1 | 67127.1 | 65050.3 | 62971.3 | 59126.7 |        |
| 55°    | 59991.7 | 64156.4 | 66786.9 | 69419.6 | 72050.1 | 71574.2 | 69223.9 | 66875.8 | 64525.5 | 60400.8 |        |
| 57.5°  | 61490.4 | 65993.1 | 68616.9 | 71238.5 | 73862.3 | 73097.4 | 70740.4 | 68385.6 | 66030.9 | 61801.7 |        |
| 60°    | 61623.8 | 65839.7 | 68094.3 | 70351.3 | 72606.0 | 71354.1 | 69099.4 | 66846.9 | 64594.5 | 60912.2 |        |
| 62.5°  | 57645.8 | 60810.0 | 62375.3 | 63940.7 | 65506.1 | 64243.1 | 61890.6 | 59540.3 | 57187.8 | 54257.1 |        |
| 65°    | 48115.6 | 50074.6 | 51322.0 | 52569.4 | 53816.9 | 52960.8 | 50808.4 | 48656.0 | 46503.6 | 44364.5 |        |
| 67.5°  | 38125.2 | 39623.9 | 41267.1 | 42910.3 | 44553.5 | 44215.5 | 42490.0 | 40766.8 | 39043.5 | 36633.2 |        |
| 70°    | 30660.7 | 32681.9 | 34529.7 | 36377.5 | 38225.2 | 37629.3 | 35897.2 | 34167.2 | 32435.1 | 29811.3 |        |
| 72.5°  | 24359.1 | 26500.4 | 28043.6 | 29584.5 | 31127.6 | 30133.7 | 28861.8 | 27592.2 | 26320.3 | 23956.7 |        |
| 75°    | 14791.1 | 16067.5 | 16098.6 | 16127.5 | 16158.6 | 15369.3 | 14315.3 | 13263.5 | 12209.6 | 11264.6 |        |
| 77.5°  | 4362.6  | 4818.5  | 5194.2  | 5567.8  | 5943.6  | 6010.3  | 5621.2  | 5234.3  | 4847.4  | 4335.9  |        |
| 80°    | 1263.0  | 1378.6  | 1476.4  | 1572.1  | 1669.9  | 1520.9  | 1429.8  | 1338.6  | 1247.4  | 1118.5  |        |
| 82.5°  | 226.8   | 213.5   | 211.2   | 209.0   | 209.0   | 180.1   | 162.3   | 144.5   | 126.7   | 120.1   |        |
| 85°    | 40.0    | 37.8    | 35.6    | 33.4    | 31.1    | 24.5    | 22.2    | 17.8    | 13.3    | 11.1    |        |
| 87.5°  | 13.3    | 11.1    | 8.9     | 6.7     | 6.7     | 2.2     | 2.2     | 0.0     | 0.0     | 0.0     |        |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |        |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064551

CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    | 352.5°  | 355°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   | 129.0   |
| 2.5°   | 126.7   | 124.5   | 124.5   | 124.5   | 124.5   | 122.3   | 122.3   | 122.3   | 122.3   | 120.1   | 120.1   |
| 5°     | 140.1   | 140.1   | 137.9   | 137.9   | 135.6   | 135.6   | 133.4   | 133.4   | 131.2   | 131.2   | 129.0   |
| 7.5°   | 164.5   | 162.3   | 160.1   | 157.9   | 155.6   | 151.2   | 149.0   | 146.8   | 146.8   | 144.5   | 142.3   |
| 10°    | 197.9   | 193.4   | 191.2   | 186.8   | 184.6   | 180.1   | 175.7   | 171.2   | 166.8   | 162.3   | 157.9   |
| 12.5°  | 260.2   | 251.3   | 244.6   | 235.7   | 226.8   | 220.1   | 211.2   | 204.6   | 195.7   | 189.0   | 180.1   |
| 15°    | 451.4   | 429.1   | 404.7   | 375.8   | 344.7   | 315.7   | 284.6   | 266.8   | 246.8   | 229.0   | 209.0   |
| 17.5°  | 1154.0  | 1038.4  | 920.6   | 824.9   | 729.3   | 635.9   | 540.3   | 471.4   | 402.5   | 331.3   | 262.4   |
| 20°    | 2937.3  | 2617.1  | 2296.9  | 1981.2  | 1663.2  | 1347.5  | 1029.5  | 869.4   | 709.3   | 549.2   | 389.1   |
| 22.5°  | 5527.8  | 4934.1  | 4338.2  | 3762.3  | 3184.1  | 2608.2  | 2032.3  | 1669.9  | 1309.7  | 947.2   | 584.8   |
| 25°    | 8531.8  | 7784.7  | 7037.6  | 6090.3  | 5140.9  | 4193.6  | 3246.4  | 2657.2  | 2067.9  | 1478.7  | 889.4   |
| 27.5°  | 11102.2 | 10241.7 | 9381.2  | 8229.4  | 7077.6  | 5925.8  | 4774.0  | 3895.7  | 3019.6  | 2141.3  | 1263.0  |
| 30°    | 13328.0 | 12403.0 | 11478.0 | 10137.2 | 8796.4  | 7455.6  | 6114.8  | 5016.4  | 3917.9  | 2819.5  | 1721.0  |
| 32.5°  | 15258.1 | 14150.7 | 13043.4 | 11660.4 | 10277.3 | 8894.2  | 7511.2  | 6163.7  | 4816.2  | 3466.5  | 2119.1  |
| 35°    | 17483.9 | 16192.0 | 14897.9 | 13363.6 | 11827.1 | 10292.9 | 8758.6  | 7237.7  | 5714.6  | 4193.6  | 2670.5  |
| 37.5°  | 20312.2 | 18726.8 | 17139.2 | 15429.3 | 13719.4 | 12011.7 | 10301.8 | 8562.9  | 6824.1  | 5085.3  | 3346.5  |
| 40°    | 25726.6 | 23680.9 | 21635.3 | 19462.8 | 17288.2 | 15115.8 | 12943.4 | 10808.7 | 8674.1  | 6537.3  | 4402.7  |
| 42.5°  | 35428.0 | 32664.1 | 29900.2 | 27009.6 | 24116.7 | 21226.1 | 18333.3 | 15322.6 | 12309.6 | 9298.9  | 6286.0  |
| 45°    | 46376.8 | 42948.1 | 39517.1 | 36273.0 | 33026.6 | 29782.4 | 26538.2 | 22406.8 | 18275.5 | 14144.1 | 10012.7 |
| 47.5°  | 52533.9 | 48831.6 | 45129.4 | 42058.7 | 38987.9 | 35917.2 | 32846.4 | 28392.7 | 23938.9 | 19485.1 | 15031.3 |
| 50°    | 54799.7 | 51030.7 | 47261.8 | 44435.7 | 41607.3 | 38781.1 | 35952.8 | 31492.3 | 27029.6 | 22569.1 | 18106.5 |
| 52.5°  | 55282.2 | 51437.6 | 47593.1 | 44749.2 | 41905.2 | 39063.5 | 36219.6 | 31788.0 | 27356.5 | 22922.7 | 18491.1 |
| 55°    | 56273.9 | 52149.2 | 48022.3 | 44780.3 | 41538.4 | 38296.4 | 35054.4 | 30551.7 | 26049.0 | 21546.3 | 17043.6 |
| 57.5°  | 57570.2 | 53341.0 | 49111.8 | 45418.5 | 41725.1 | 38034.0 | 34340.7 | 29417.7 | 24494.8 | 19569.6 | 14646.6 |
| 60°    | 57230.0 | 53550.0 | 49867.8 | 45912.1 | 41954.2 | 37998.4 | 34040.5 | 28626.1 | 23209.5 | 17795.2 | 12378.6 |
| 62.5°  | 51324.2 | 48393.6 | 45460.7 | 42207.6 | 38952.3 | 35699.3 | 32446.2 | 26871.7 | 21297.3 | 15722.8 | 10148.3 |
| 65°    | 42223.2 | 40084.1 | 37945.1 | 35327.9 | 32708.6 | 30091.5 | 27474.3 | 22475.8 | 17479.4 | 12480.9 | 7482.3  |
| 67.5°  | 34220.6 | 31810.3 | 29397.7 | 27312.0 | 25224.1 | 23138.4 | 21050.5 | 17117.0 | 13183.5 | 9250.0  | 5316.5  |
| 70°    | 27187.5 | 24565.9 | 21942.1 | 19905.3 | 17866.3 | 15829.5 | 13792.8 | 11177.8 | 8565.2  | 5950.3  | 3335.3  |
| 72.5°  | 21590.8 | 19227.1 | 16863.5 | 14691.1 | 12516.4 | 10344.0 | 8169.4  | 6624.0  | 5078.6  | 3533.2  | 1987.9  |
| 75°    | 10319.5 | 9374.5  | 8429.5  | 7293.3  | 6157.0  | 5020.8  | 3884.6  | 3210.8  | 2539.3  | 1865.6  | 1191.8  |
| 77.5°  | 3824.5  | 3315.3  | 2803.9  | 2341.4  | 1878.9  | 1418.6  | 956.1   | 876.1   | 796.0   | 716.0   | 635.9   |
| 80°    | 989.5   | 862.7   | 733.8   | 642.6   | 549.2   | 458.1   | 366.9   | 331.3   | 298.0   | 262.4   | 226.8   |
| 82.5°  | 113.4   | 104.5   | 97.8    | 93.4    | 86.7    | 82.3    | 75.6    | 68.9    | 62.3    | 53.4    | 46.7    |
| 85°    | 6.7     | 4.4     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5°  | 360°   |
|--------|---------|--------|
| 0°     | 129.0   | 129.0  |
| 2.5°   | 120.1   | 117.8  |
| 5°     | 126.7   | 124.5  |
| 7.5°   | 140.1   | 135.6  |
| 10°    | 153.4   | 149.0  |
| 12.5°  | 173.4   | 166.8  |
| 15°    | 195.7   | 182.3  |
| 17.5°  | 233.5   | 204.6  |
| 20°    | 315.7   | 242.4  |
| 22.5°  | 444.7   | 302.4  |
| 25°    | 653.7   | 418.0  |
| 27.5°  | 909.4   | 555.9  |
| 30°    | 1209.6  | 696.0  |
| 32.5°  | 1474.2  | 829.4  |
| 35°    | 1818.9  | 965.0  |
| 37.5°  | 2243.6  | 1138.5 |
| 40°    | 2901.7  | 1400.8 |
| 42.5°  | 4086.9  | 1885.6 |
| 45°    | 6637.3  | 3259.7 |
| 47.5°  | 10212.8 | 5392.1 |
| 50°    | 12494.2 | 6881.9 |
| 52.5°  | 12681.0 | 6870.8 |
| 55°    | 11575.9 | 6108.1 |
| 57.5°  | 9877.1  | 5105.3 |
| 60°    | 8209.4  | 4038.0 |
| 62.5°  | 6468.3  | 2788.3 |
| 65°    | 4727.3  | 1972.3 |
| 67.5°  | 3395.4  | 1474.2 |
| 70°    | 2232.5  | 1129.6 |
| 72.5°  | 1454.2  | 920.6  |
| 75°    | 978.4   | 762.7  |
| 77.5°  | 571.5   | 507.0  |
| 80°    | 202.3   | 177.9  |
| 82.5°  | 37.8    | 26.7   |
| 85°    | 0.0     | 0.0    |
| 87.5°  | 0.0     | 0.0    |
| 90°    | 0.0     | 0.0    |
| 92.5°  | 0.0     | 0.0    |
| 95°    | 0.0     | 0.0    |
| 97.5°  | 0.0     | 0.0    |
| 100°   | 0.0     | 0.0    |
| 102.5° | 0.0     | 0.0    |
| 105°   | 0.0     | 0.0    |
| 107.5° | 0.0     | 0.0    |
| 110°   | 0.0     | 0.0    |



REPORT NUMBER: P1064551  
 CATALOG NUMBER: GLAN-SA8C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-722-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 2200K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 2160     | CRI (Ra): | 71.9 |      |       |
| CIE u':                   | 0.2927   | R1:       | 68.7 | R9:  | -17.8 |
| CIE v':                   | 0.5388   | R2:       | 82.6 | R10: | 60.5  |
| Duv:                      | 0.0015   | R3:       | 95.5 | R11: | 60.2  |
| CIE x:                    | 0.5130   | R4:       | 66.4 | R12: | 48.2  |
| CIE y:                    | 0.4197   | R5:       | 65.4 | R13: | 70.7  |
| CIE z:                    | 0.0674   | R6:       | 75.9 | R14: | 96.8  |
| Peak Wavelength (nm):     | 609      | R7:       | 77.2 | R15: | 61.8  |
| Dominant Wavelength (nm): | 587      | R8:       | 43.5 |      |       |
| Purity:                   | 79.96089 |           |      |      |       |
| Rf:                       | 70.6     |           |      |      |       |
| Rg:                       | 97.6     |           |      |      |       |



### Test Conditions

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 27                          | NR               | 620       | 966                         | NR               | 750       | 46                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 42                          | NR               | 625       | 930                         | NR               | 755       | 39                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 67                          | NR               | 630       | 888                         | NR               | 760       | 34                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 101                         | NR               | 635       | 835                         | NR               | 765       | 30                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 139                         | NR               | 640       | 778                         | NR               | 770       | 26                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 183                         | NR               | 645       | 717                         | NR               | 775       | 22                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 224                         | NR               | 650       | 656                         | NR               | 780       | 19                          | NR               | 910       | 1                           | NR               |
| 395       | 0                           | NR               | 525       | 262                         | NR               | 655       | 595                         | NR               | 785       | 17                          | NR               | 915       | 1                           | NR               |
| 400       | 1                           | NR               | 530       | 299                         | NR               | 660       | 536                         | NR               | 790       | 15                          | NR               | 920       | 1                           | NR               |
| 405       | 3                           | NR               | 535       | 332                         | NR               | 665       | 480                         | NR               | 795       | 13                          | NR               | 925       | 1                           | NR               |
| 410       | 7                           | NR               | 540       | 365                         | NR               | 670       | 425                         | NR               | 800       | 11                          | NR               | 930       | 1                           | NR               |
| 415       | 17                          | NR               | 545       | 400                         | NR               | 675       | 376                         | NR               | 805       | 10                          | NR               | 935       | 0                           | NR               |
| 420       | 36                          | NR               | 550       | 437                         | NR               | 680       | 332                         | NR               | 810       | 8                           | NR               | 940       | 0                           | NR               |
| 425       | 67                          | NR               | 555       | 479                         | NR               | 685       | 291                         | NR               | 815       | 8                           | NR               | 945       | 0                           | NR               |
| 430       | 105                         | NR               | 560       | 525                         | NR               | 690       | 255                         | NR               | 820       | 7                           | NR               | 950       | 0                           | NR               |
| 435       | 141                         | NR               | 565       | 579                         | NR               | 695       | 221                         | NR               | 825       | 6                           | NR               | 955       | 0                           | NR               |
| 440       | 169                         | NR               | 570       | 639                         | NR               | 700       | 192                         | NR               | 830       | 5                           | NR               | 960       | 0                           | NR               |
| 445       | 173                         | NR               | 575       | 703                         | NR               | 705       | 167                         | NR               | 835       | 4                           | NR               | 965       | 0                           | NR               |
| 450       | 136                         | NR               | 580       | 769                         | NR               | 710       | 144                         | NR               | 840       | 4                           | NR               | 970       | 0                           | NR               |
| 455       | 80                          | NR               | 585       | 832                         | NR               | 715       | 125                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 45                          | NR               | 590       | 890                         | NR               | 720       | 109                         | NR               | 850       | 3                           | NR               | 980       | 0                           | NR               |
| 465       | 32                          | NR               | 595       | 937                         | NR               | 725       | 94                          | NR               | 855       | 3                           | NR               | 985       | 0                           | NR               |
| 470       | 23                          | NR               | 600       | 972                         | NR               | 730       | 81                          | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 18                          | NR               | 605       | 992                         | NR               | 735       | 70                          | NR               | 865       | 2                           | NR               | 995       | 0                           | NR               |
| 480       | 18                          | NR               | 610       | 998                         | NR               | 740       | 61                          | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 20                          | NR               | 615       | 990                         | NR               | 745       | 53                          | NR               | 875       | 2                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-2

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 0.8

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 1.21**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2



TM-30-18

### Summary

$R_f = 70.6$   
 $R_g = 97.6$   
 $CIE\ R_a = 71.9$   
 $R_g = -17.8$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)