

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057600

Luminaire Tested: **GAP-SA1A-735-U-T4BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1057600
Test Lab: INNOVATION CENTER(G1)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAP-SA1A-735-U-T4BC
Description: GALLEON PEDESTRAIAN COMPANION 615mA 1xLight Square PACKAGE 70CRI
3500K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (14) 3500K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3356.2 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G1

Input Watts (W): 29.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1057600

CATALOG NUMBER: GAP-SA1A-735-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P1057600

CATALOG NUMBER: GAP-SA1A-735-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1057600

CATALOG NUMBER: GAP-SA1A-735-U-T4BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14.7	0.0	14.7
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	3341.5	0.0	3341.5
	% Fixture	99.6	0.0	99.6
Total	Lumens	3356.2	0.0	3356.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.1	0.2
10°-20°	53.6	1.6
20°-30°	161.4	4.8
30°-40°	355.5	10.6
40°-50°	546.2	16.3
50°-60°	672.6	20.0
60°-70°	849.2	25.3
70°-80°	653.2	19.5
80°-90°	57.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3356.2	100.0
0°-180°	3356.2	100.0



REPORT NUMBER: P1057600


CATALOG NUMBER: GAP-SA1A-735-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	219.6	6.5			
FM	(30°-60°)	1570.7	46.8			
FH	(60°-80°)	1493.9	44.5			G1/1800
FVH	(80°-90°)	57.2	1.7			G1/100
BL	(0°-30°)	2.5	0.1	B0/110		
BM	(30°-60°)	3.6	0.1	B0/220		
BH	(60°-80°)	8.4	0.3	B0/110		G0/110
BVH	(80°-90°)	0.2	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type IV Short



REPORT NUMBER: P1057600

CATALOG NUMBER: GAP-SA1A-735-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6
2.5°	54.8	54.1	51.6	48.5	46.0	44.1	41.5	37.8	34.0	29.6	26.4
5°	143.5	142.9	132.8	120.2	103.2	91.9	80.6	62.3	47.2	36.5	27.7
7.5°	265.7	263.8	254.3	234.8	198.9	179.4	158.6	111.4	72.4	45.3	29.6
10°	386.5	385.3	373.3	345.0	305.9	286.4	258.7	190.1	113.9	59.2	32.1
12.5°	457.7	460.8	452.0	438.8	405.4	387.2	355.7	276.4	175.0	81.2	35.3
15°	516.2	517.5	509.3	501.1	482.8	467.7	441.3	368.3	248.0	110.8	39.0
17.5°	588.6	586.7	577.9	568.5	548.3	537.0	520.0	453.3	326.1	153.0	44.1
20°	680.5	675.5	665.4	649.0	627.0	613.1	595.5	540.1	404.1	199.6	50.4
22.5°	798.2	791.9	781.2	766.1	727.1	705.7	683.0	614.4	490.4	258.7	58.5
25°	934.2	931.1	919.7	898.3	856.8	828.4	791.9	701.3	576.0	321.7	68.6
27.5°	1094.1	1088.4	1073.3	1048.1	1003.4	966.3	921.0	797.0	657.8	388.4	81.2
30°	1272.9	1260.3	1229.4	1207.4	1155.2	1118.6	1065.8	924.1	742.2	458.3	94.4
32.5°	1439.1	1422.7	1378.0	1347.8	1299.3	1266.6	1218.1	1052.6	837.3	531.3	111.4
35°	1589.5	1571.9	1499.5	1453.6	1429.0	1401.3	1352.2	1199.2	939.9	609.4	130.9
37.5°	1716.7	1699.1	1605.9	1533.5	1518.4	1508.9	1469.3	1323.2	1056.3	697.5	153.6
40°	1787.8	1776.5	1695.9	1614.1	1585.1	1573.8	1544.8	1427.1	1186.0	785.6	180.0
42.5°	1809.9	1802.9	1737.5	1697.2	1644.3	1621.6	1587.0	1506.4	1297.4	884.5	210.3
45°	1797.9	1790.3	1742.5	1751.9	1707.9	1663.8	1616.6	1560.6	1391.2	1000.9	248.0
47.5°	1746.9	1744.4	1711.7	1765.2	1760.1	1709.8	1651.2	1596.5	1471.8	1113.6	295.2
50°	1622.3	1621.0	1636.1	1746.9	1794.7	1747.5	1689.0	1628.6	1536.0	1226.3	355.7
52.5°	1454.2	1463.0	1539.2	1712.9	1804.8	1777.1	1726.8	1665.1	1588.9	1339.0	436.9
55°	1365.4	1373.0	1473.1	1675.8	1802.9	1794.7	1765.2	1700.3	1637.4	1431.5	545.2
57.5°	1432.8	1424.6	1470.5	1670.7	1794.7	1809.9	1792.9	1728.0	1681.4	1513.4	695.0
60°	1560.6	1558.1	1563.7	1706.6	1811.7	1834.4	1822.4	1746.9	1724.9	1575.7	859.9
62.5°	1689.6	1682.7	1688.4	1805.5	1870.9	1886.7	1872.2	1777.8	1758.9	1621.0	1038.7
65°	1753.8	1748.8	1775.2	1904.9	1955.3	1966.0	1947.1	1827.5	1764.5	1644.3	1151.4
67.5°	1745.6	1744.4	1806.1	1974.8	2025.8	2032.1	2016.3	1877.2	1740.6	1643.7	1163.3
69°	1707.2	1704.7	1785.9	1981.7	2048.4	2052.9	2027.0	1852.0	1680.2	1601.5	1078.4
70°	1661.9	1664.4	1756.3	1969.1	2049.1	2042.8	1983.0	1816.2	1634.2	1553.0	970.1
72.5°	1493.2	1508.9	1634.9	1886.7	1962.8	1892.3	1814.3	1698.4	1546.7	1323.9	677.4
75°	1249.0	1271.0	1433.4	1715.4	1687.7	1652.5	1643.0	1554.9	1401.3	879.4	481.6
77.5°	610.6	683.7	1017.3	1317.6	1384.9	1420.8	1407.6	1285.5	1126.2	431.8	314.1
80°	32.1	33.4	53.5	125.9	641.5	815.9	1003.4	981.4	852.4	197.0	165.6
82.5°	17.0	17.0	18.9	22.0	25.8	30.8	81.8	562.2	506.8	101.4	61.7
85°	9.4	9.4	11.3	15.1	19.5	22.7	25.8	34.0	108.9	36.5	10.1
87.5°	4.4	5.7	7.6	10.7	13.8	17.6	20.1	25.2	32.1	30.8	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1057600

CATALOG NUMBER: GAP-SA1A-735-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6
2.5°	24.6	23.3	21.4	20.1	19.5	18.3	17.0	16.4	15.7	15.1	15.7
5°	24.6	22.7	19.5	17.6	16.4	14.5	13.2	12.6	12.0	11.3	11.3
7.5°	24.6	21.4	17.6	15.1	13.2	12.0	10.1	9.4	8.8	8.2	8.2
10°	25.2	20.1	15.7	13.2	11.3	9.4	8.2	6.9	6.3	6.3	6.3
12.5°	25.2	18.9	13.8	11.3	9.4	7.6	5.7	4.4	3.8	3.8	3.8
15°	25.2	17.6	12.6	9.4	7.6	5.7	3.1	1.9	1.3	1.3	0.6
17.5°	25.8	17.0	11.3	8.2	5.7	3.1	0.6	0.0	0.0	0.0	0.0
20°	27.1	16.4	10.1	6.9	3.8	1.3	0.0	0.0	0.0	0.0	0.0
22.5°	28.3	15.7	8.8	5.0	1.9	0.6	0.0	0.0	0.0	0.0	0.0
25°	30.8	15.7	8.2	4.4	1.3	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	33.4	15.7	6.3	2.5	0.6	0.0	0.0	0.0	0.0	0.0	0.0
30°	35.3	15.7	5.7	1.9	0.6	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	37.8	15.7	5.0	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	39.7	15.1	3.8	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	41.5	14.5	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	44.1	13.8	2.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	46.6	12.6	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	49.7	12.0	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	54.1	11.3	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	60.4	11.3	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	71.1	11.3	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	88.8	11.3	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	119.6	11.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	180.0	11.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	278.2	12.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	425.6	15.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	539.5	18.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
69°	487.2	17.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	413.0	13.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	229.8	6.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	119.6	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	51.0	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	15.1	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	5.0	1.3	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	1.9	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.3	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ


Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.36


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5





TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 CIE $R_a = 70.1$
 $R_g = -40.2$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)