

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057599

Luminaire Tested: **GAP-SA1B-735-U-T4BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1057599
Test Lab: INNOVATION CENTER(G1)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAP-SA1B-735-U-T4BC
Description: GALLEON PEDESTRAIAN COMPANION 800mA 1xLight Square PACKAGE 70CRI
3500K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (14) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4205.4 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 38.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1057599

CATALOG NUMBER: GAP-SA1B-735-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P1057599

CATALOG NUMBER: GAP-SA1B-735-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1057599

CATALOG NUMBER: GAP-SA1B-735-U-T4BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	18.4	0.0	18.4
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	4186.9	0.0	4186.9
	% Fixture	99.6	0.0	99.6
Total	Lumens	4205.4	0.0	4205.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.9	0.2
10°-20°	67.2	1.6
20°-30°	202.3	4.8
30°-40°	445.4	10.6
40°-50°	684.4	16.3
50°-60°	842.8	20.0
60°-70°	1064.0	25.3
70°-80°	818.4	19.5
80°-90°	71.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4205.4	100.0
0°-180°	4205.4	100.0



REPORT NUMBER: P1057599


CATALOG NUMBER: GAP-SA1B-735-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	275.2	6.5			
FM	(30°-60°)	1968.1	46.8			
FH	(60°-80°)	1871.9	44.5			G2/5000
FVH	(80°-90°)	71.7	1.7			G1/100
BL	(0°-30°)	3.1	0.1	B0/110		
BM	(30°-60°)	4.5	0.1	B0/220		
BH	(60°-80°)	10.6	0.3	B0/110		G0/110
BVH	(80°-90°)	0.2	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short



REPORT NUMBER: P1057599

CATALOG NUMBER: GAP-SA1B-735-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8
2.5°	68.6	67.8	64.7	60.7	57.6	55.2	52.1	47.3	42.6	37.1	33.1
5°	179.8	179.1	166.4	150.7	129.4	115.2	101.0	78.1	59.2	45.8	34.7
7.5°	332.9	330.5	318.7	294.2	249.3	224.8	198.8	139.6	90.7	56.8	37.1
10°	484.3	482.7	467.8	432.3	383.4	358.9	324.2	238.2	142.8	74.1	40.2
12.5°	573.5	577.4	566.4	549.8	508.0	485.1	445.7	346.3	219.3	101.8	44.2
15°	646.8	648.4	638.1	627.9	605.0	586.1	552.9	461.4	310.8	138.8	48.9
17.5°	737.5	735.2	724.1	712.3	687.0	672.8	651.5	567.9	408.6	191.7	55.2
20°	852.7	846.4	833.8	813.3	785.6	768.3	746.2	676.8	506.4	250.0	63.1
22.5°	1000.2	992.3	978.9	960.0	911.1	884.2	855.8	769.9	614.5	324.2	73.4
25°	1170.6	1166.6	1152.4	1125.6	1073.6	1038.1	992.3	878.7	721.8	403.1	86.0
27.5°	1370.9	1363.8	1344.9	1313.3	1257.3	1210.8	1154.0	998.6	824.3	486.7	101.8
30°	1595.0	1579.2	1540.5	1512.9	1447.4	1401.7	1335.4	1158.0	930.0	574.2	118.3
32.5°	1803.2	1782.7	1726.7	1688.8	1628.1	1587.1	1526.3	1318.9	1049.1	665.7	139.6
35°	1991.7	1969.6	1878.9	1821.3	1790.6	1755.9	1694.3	1502.7	1177.7	763.6	164.1
37.5°	2151.1	2129.0	2012.2	1921.5	1902.6	1890.8	1841.1	1658.1	1323.6	874.0	192.5
40°	2240.2	2226.0	2125.0	2022.5	1986.2	1972.0	1935.7	1788.2	1486.1	984.4	225.6
42.5°	2267.8	2259.1	2177.1	2126.6	2060.3	2031.9	1988.6	1887.6	1625.7	1108.3	263.5
45°	2252.8	2243.3	2183.4	2195.2	2140.0	2084.8	2025.6	1955.4	1743.2	1254.2	310.8
47.5°	2188.9	2185.8	2144.7	2211.8	2205.5	2142.4	2069.0	2000.4	1844.2	1395.4	369.9
50°	2032.7	2031.2	2050.1	2188.9	2248.9	2189.7	2116.3	2040.6	1924.7	1536.6	445.7
52.5°	1822.1	1833.2	1928.6	2146.3	2261.5	2226.8	2163.7	2086.4	1990.9	1677.8	547.4
55°	1710.9	1720.4	1845.8	2099.8	2259.1	2248.9	2211.8	2130.5	2051.7	1793.7	683.1
57.5°	1795.3	1785.1	1842.6	2093.5	2248.9	2267.8	2246.5	2165.3	2106.9	1896.3	870.8
60°	1955.4	1952.3	1959.4	2138.4	2270.2	2298.6	2283.6	2188.9	2161.3	1974.4	1077.5
62.5°	2117.1	2108.5	2115.6	2262.3	2344.3	2364.0	2345.9	2227.6	2203.9	2031.2	1301.5
65°	2197.6	2191.3	2224.4	2386.9	2450.0	2463.4	2439.8	2289.9	2211.0	2060.3	1442.7
67.5°	2187.3	2185.8	2263.1	2474.5	2538.4	2546.2	2526.5	2352.2	2181.0	2059.6	1457.7
69°	2139.2	2136.1	2237.8	2483.1	2566.8	2572.3	2539.9	2320.6	2105.3	2006.7	1351.2
70°	2082.4	2085.6	2200.7	2467.4	2567.5	2559.7	2484.7	2275.7	2047.7	1946.0	1215.5
72.5°	1871.0	1890.8	2048.5	2364.0	2459.5	2371.1	2273.3	2128.2	1938.1	1658.8	848.7
75°	1565.0	1592.6	1796.1	2149.5	2114.8	2070.6	2058.8	1948.3	1755.9	1102.0	603.4
77.5°	765.1	856.6	1274.7	1651.0	1735.4	1780.3	1763.8	1610.7	1411.2	541.1	393.6
80°	40.2	41.8	67.0	157.8	803.8	1022.3	1257.3	1229.7	1068.0	246.9	207.5
82.5°	21.3	21.3	23.7	27.6	32.3	38.7	102.5	704.4	635.0	127.0	77.3
85°	11.8	11.8	14.2	18.9	24.5	28.4	32.3	42.6	136.5	45.8	12.6
87.5°	5.5	7.1	9.5	13.4	17.4	22.1	25.2	31.6	40.2	38.7	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1057599

CATALOG NUMBER: GAP-SA1B-735-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8
2.5°	30.8	29.2	26.8	25.2	24.5	22.9	21.3	20.5	19.7	18.9	19.7
5°	30.8	28.4	24.5	22.1	20.5	18.1	16.6	15.8	15.0	14.2	14.2
7.5°	30.8	26.8	22.1	18.9	16.6	15.0	12.6	11.8	11.0	10.3	10.3
10°	31.6	25.2	19.7	16.6	14.2	11.8	10.3	8.7	7.9	7.9	7.9
12.5°	31.6	23.7	17.4	14.2	11.8	9.5	7.1	5.5	4.7	4.7	4.7
15°	31.6	22.1	15.8	11.8	9.5	7.1	3.9	2.4	1.6	1.6	0.8
17.5°	32.3	21.3	14.2	10.3	7.1	3.9	0.8	0.0	0.0	0.0	0.0
20°	33.9	20.5	12.6	8.7	4.7	1.6	0.0	0.0	0.0	0.0	0.0
22.5°	35.5	19.7	11.0	6.3	2.4	0.8	0.0	0.0	0.0	0.0	0.0
25°	38.7	19.7	10.3	5.5	1.6	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	41.8	19.7	7.9	3.2	0.8	0.0	0.0	0.0	0.0	0.0	0.0
30°	44.2	19.7	7.1	2.4	0.8	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	47.3	19.7	6.3	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	49.7	18.9	4.7	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	52.1	18.1	3.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	55.2	17.4	3.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	58.4	15.8	2.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	62.3	15.0	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	67.8	14.2	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	75.7	14.2	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	89.1	14.2	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	111.2	14.2	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	149.9	14.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	225.6	14.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	348.6	15.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	533.2	18.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	676.0	22.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
69°	610.5	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	517.5	16.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	287.9	8.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	149.9	3.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	63.9	2.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	18.9	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	6.3	1.6	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	2.4	1.6	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.6	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ


Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.36


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5





TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 $CIE R_a = 70.1$
 $R_g = -40.2$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)