

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1057530

Luminaire Tested: **GAP-SA2C-735-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1057530
Test Lab: INNOVATION CENTER(G1)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAP-SA2C-735-U-T2BC
Description: GALLEON PEDESTRAIAN COMPANION 1050mA 2xLight Square PACKAGE 70CRI
3500K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (28) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10152.8 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Luminous Opening: Rectangular (W 1.33' x L: 0.67' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 94.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1057530

CATALOG NUMBER: GAP-SA2C-735-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 14.6 fc
 Type II - Short - N/A

REPORT NUMBER: P1057530

CATALOG NUMBER: GAP-SA2C-735-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1057530

CATALOG NUMBER: GAP-SA2C-735-U-T2BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	45.2	0.0	45.2
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	10107.6	0.0	10107.6
	% Fixture	99.6	0.0	99.6
Total	Lumens	10152.8	0.0	10152.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.5	0.1
10°-20°	112.1	1.1
20°-30°	343.7	3.4
30°-40°	893.0	8.8
40°-50°	2248.3	22.1
50°-60°	3259.3	32.1
60°-70°	2513.8	24.8
70°-80°	693.5	6.8
80°-90°	75.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10152.8	100.0
0°-180°	10152.8	100.0



REPORT NUMBER: P1057530


CATALOG NUMBER: GAP-SA2C-735-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	460.9	4.5			
FM	(30°-60°)	6385.8	62.9			
FH	(60°-80°)	3187.0	31.4			G2/5000
FVH	(80°-90°)	73.9	0.7			G1/100
BL	(0°-30°)	8.4	0.1	B0/110		
BM	(30°-60°)	14.8	0.1	B0/220		
BH	(60°-80°)	20.2	0.2	B0/110		G0/110
BVH	(80°-90°)	1.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short



REPORT NUMBER: P1057530

CATALOG NUMBER: GAP-SA2C-735-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9
2.5°	117.0	117.0	115.1	111.3	101.7	95.9	90.2	84.4	82.5	78.7	74.8
5°	213.0	209.1	207.2	188.0	168.8	145.8	122.8	103.6	101.7	88.3	76.7
7.5°	447.0	447.0	408.7	362.6	310.8	239.8	176.5	136.2	130.5	101.7	78.7
10°	731.0	732.9	708.0	635.0	541.0	422.1	285.9	176.5	172.7	119.0	80.6
12.5°	986.1	984.2	959.3	907.5	803.9	654.2	448.9	255.2	239.8	138.1	80.6
15°	1149.2	1149.2	1145.4	1118.5	1045.6	892.1	665.7	374.1	356.9	166.9	82.5
17.5°	1308.5	1318.1	1304.6	1293.1	1239.4	1124.3	892.1	539.1	504.6	213.0	86.3
20°	1500.3	1509.9	1504.2	1486.9	1419.7	1318.1	1118.5	729.1	694.5	289.7	94.0
22.5°	1722.9	1730.5	1719.0	1713.3	1628.9	1500.3	1327.6	957.4	905.6	387.6	103.6
25°	1997.2	1991.5	1987.6	1955.0	1872.5	1732.5	1525.3	1168.4	1128.1	518.0	117.0
27.5°	2319.5	2311.9	2286.9	2244.7	2123.9	1970.4	1736.3	1392.9	1354.5	675.3	136.2
30°	2755.1	2709.0	2672.6	2578.6	2417.4	2214.0	1972.3	1613.5	1571.3	863.4	157.3
32.5°	3369.0	3355.6	3213.6	2968.0	2735.9	2492.2	2235.1	1847.6	1803.5	1057.1	186.1
35°	4470.3	4407.0	4159.5	3541.7	3106.2	2841.4	2501.8	2081.6	2035.6	1281.6	224.5
37.5°	5707.7	5652.1	5412.3	4667.9	3668.3	3202.1	2799.2	2346.4	2296.5	1527.2	272.4
40°	6949.1	6931.8	6841.6	6246.9	4807.9	3683.7	3192.5	2684.1	2626.5	1774.7	339.6
42.5°	8345.8	8295.9	8238.3	8036.9	6776.4	4648.7	3739.3	3069.7	3019.8	2079.7	435.5
45°	8789.0	8769.8	8838.8	9032.6	8838.8	6670.9	4587.3	3595.4	3545.5	2471.1	573.7
47.5°	8639.3	8620.1	8810.1	9128.5	9571.7	9097.9	5901.5	4349.4	4257.3	2939.2	778.9
50°	7883.4	7891.1	8226.8	8863.8	9498.8	10064.8	8096.4	5352.8	5289.5	3605.0	1055.2
52.5°	7167.8	7181.2	7601.4	8416.8	9115.1	10101.3	10189.5	6812.8	6540.4	4420.4	1396.7
55°	6471.3	6452.1	6770.6	7998.5	9046.1	9602.4	10847.6	8526.1	8347.7	5477.5	1732.5
57.5°	5734.6	5711.6	5878.5	6791.7	8902.2	9671.5	10674.9	10542.5	10329.6	6692.0	2003.0
60°	4399.3	4347.5	4677.5	5375.8	7791.3	9755.9	10333.4	11283.1	11269.7	8318.9	2139.2
62.5°	2108.5	2192.9	2640.0	3397.8	5208.9	9007.7	10465.8	11008.7	11035.6	9754.0	2453.8
65°	1076.3	1095.5	1325.7	1855.3	2757.0	6475.2	10084.0	10628.9	10588.6	9473.9	3269.2
67.5°	725.2	734.8	842.3	1122.4	1600.1	2712.9	7835.4	9945.9	9917.1	8075.3	3754.6
70°	642.7	646.6	673.4	763.6	959.3	1195.3	3587.7	8345.8	8560.7	6168.2	3428.5
72.5°	629.3	629.3	625.5	631.2	619.7	648.5	1258.6	5024.7	5337.5	4309.1	2778.1
75°	615.9	617.8	612.0	592.8	481.6	404.8	460.5	2116.2	2346.4	2835.6	2081.6
77.5°	575.6	579.4	596.7	548.7	437.4	285.9	262.8	671.5	784.7	1811.1	1525.3
80°	216.8	216.8	216.8	199.5	291.6	216.8	189.9	274.4	291.6	1020.7	938.2
82.5°	159.2	157.3	149.6	138.1	117.0	109.4	155.4	207.2	207.2	477.7	356.9
85°	46.0	46.0	51.8	69.1	86.3	95.9	119.0	159.2	165.0	182.3	53.7
87.5°	21.1	21.1	26.9	34.5	46.0	69.1	99.8	136.2	138.1	151.6	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1057530

CATALOG NUMBER: GAP-SA2C-735-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9	72.9
2.5°	72.9	71.0	69.1	67.1	63.3	59.5	53.7	51.8	49.9	49.9	49.9
5°	72.9	69.1	63.3	57.6	53.7	48.0	44.1	42.2	40.3	38.4	38.4
7.5°	71.0	65.2	57.6	51.8	48.0	42.2	36.5	34.5	32.6	32.6	32.6
10°	71.0	63.3	53.7	48.0	42.2	34.5	28.8	26.9	24.9	23.0	23.0
12.5°	67.1	59.5	49.9	42.2	34.5	26.9	21.1	17.3	15.3	15.3	15.3
15°	65.2	57.6	46.0	36.5	26.9	19.2	13.4	9.6	7.7	9.6	9.6
17.5°	63.3	51.8	42.2	28.8	19.2	11.5	5.8	1.9	1.9	1.9	1.9
20°	63.3	49.9	36.5	23.0	13.4	5.8	1.9	0.0	0.0	0.0	0.0
22.5°	65.2	49.9	32.6	19.2	7.7	3.8	0.0	0.0	0.0	0.0	0.0
25°	67.1	48.0	28.8	13.4	5.8	1.9	0.0	0.0	0.0	0.0	0.0
27.5°	69.1	46.0	24.9	9.6	3.8	0.0	0.0	0.0	0.0	0.0	0.0
30°	72.9	44.1	21.1	7.7	1.9	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	78.7	42.2	17.3	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	84.4	38.4	11.5	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	92.1	38.4	7.7	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	103.6	38.4	7.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	122.8	40.3	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	159.2	51.8	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	226.4	78.7	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	320.4	113.2	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	401.0	119.0	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	416.3	84.4	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	358.8	69.1	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	308.9	46.0	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	372.2	38.4	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	592.8	36.5	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	922.8	36.5	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1034.1	36.5	5.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	800.0	28.8	5.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	502.7	23.0	5.8	3.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	274.4	15.3	5.8	3.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0
80°	103.6	11.5	5.8	3.8	3.8	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	36.5	9.6	7.7	5.8	3.8	1.9	0.0	0.0	0.0	0.0	0.0
85°	13.4	7.7	7.7	5.8	5.8	1.9	0.0	0.0	0.0	0.0	0.0
87.5°	7.7	7.7	7.7	7.7	5.8	1.9	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ


Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5


Scotopic Flux vs. Wavelength


Scotopic Lumens: NR
S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.36


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5





TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 $CIE R_a = 70.1$
 $R_g = -40.2$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)