

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1062710

Luminaire Tested: **GLAN-SA7B-722-U-T3BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1062710
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA7B-722-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 7xLight Square PACKAGE
70CRI 2200K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (98) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23945.2 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 249.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1062710

CATALOG NUMBER: GLAN-SA7B-722-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 26.9 fc
Type III - Short - N/A

REPORT NUMBER: P1062710

CATALOG NUMBER: GLAN-SA7B-722-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1062710

CATALOG NUMBER: GLAN-SA7B-722-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	87.4	0.0	87.4
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	23857.8	0.0	23857.8
	% Fixture	99.6	0.0	99.6
Total	Lumens	23945.2	0.0	23945.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.9	0.1
10°-20°	275.2	1.1
20°-30°	992.1	4.1
30°-40°	2269.9	9.5
40°-50°	3828.4	16.0
50°-60°	6317.7	26.4
60°-70°	7060.9	29.5
70°-80°	2915.3	12.2
80°-90°	262.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23945.2	100.0
0°-180°	23945.2	100.0



REPORT NUMBER: P1062710


CATALOG NUMBER: GLAN-SA7B-722-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1267.5	5.3			
FM	(30°-60°)	12395.0	51.8			
FH	(60°-80°)	9936.1	41.5			G4/12000
FVH	(80°-90°)	259.2	1.1			G3/500
BL	(0°-30°)	22.8	0.1	B0/110		
BM	(30°-60°)	21.0	0.1	B0/220		
BH	(60°-80°)	40.1	0.2	B0/110		G0/110
BVH	(80°-90°)	3.6	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type III Short





REPORT NUMBER: P1062710

CATALOG NUMBER: GLAN-SA7B-722-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6
2.5°	187.9	194.1	187.9	187.9	187.9	181.6	181.6	175.4	175.4	169.1	162.8
5°	275.6	275.6	256.8	244.2	231.7	225.5	219.2	206.7	194.1	181.6	169.1
7.5°	613.7	613.7	557.4	482.2	382.0	325.7	313.1	256.8	219.2	194.1	169.1
10°	1465.5	1465.5	1340.2	1133.5	876.8	651.3	582.4	369.5	263.0	206.7	175.4
12.5°	2436.2	2467.5	2310.9	2047.9	1665.9	1271.3	1133.5	676.4	350.7	225.5	175.4
15°	3306.7	3231.5	3187.7	2937.2	2574.0	2104.3	1928.9	1139.8	507.3	256.8	175.4
17.5°	3895.4	3895.4	3832.7	3663.7	3331.7	2918.4	2774.4	1841.2	820.4	294.3	181.6
20°	4584.3	4584.3	4471.5	4352.5	4058.2	3707.5	3569.7	2617.8	1271.3	375.8	181.6
22.5°	5417.2	5429.7	5304.5	5091.5	4809.7	4421.4	4302.4	3338.0	1841.2	501.0	187.9
25°	6431.7	6444.3	6262.7	6062.3	5630.1	5210.5	5028.9	4164.7	2536.4	701.4	187.9
27.5°	7552.8	7640.4	7371.1	7026.7	6569.5	6043.5	5905.7	4909.9	3225.3	989.5	200.4
30°	8949.3	8949.3	8592.4	8110.1	7615.4	6964.1	6788.7	5692.8	3958.0	1371.5	212.9
32.5°	10151.8	10057.8	9600.7	9093.4	8567.3	7959.8	7772.0	6513.2	4709.5	1847.5	238.0
35°	11072.4	10991.0	10427.3	9882.5	9425.3	8867.9	8642.5	7402.5	5504.9	2386.1	275.6
37.5°	11861.5	11830.2	11066.1	10383.5	10082.9	9594.4	9394.0	8241.7	6287.7	2968.5	319.4
40°	12725.7	12625.5	11811.4	10965.9	10515.0	10120.5	9938.8	8918.0	7039.2	3651.1	382.0
42.5°	13464.7	13345.7	12613.0	11786.3	11016.0	10483.7	10308.3	9487.9	7772.0	4333.8	463.4
45°	14285.1	14222.5	13483.5	12857.2	11830.2	10978.4	10746.7	9945.1	8442.1	5147.9	569.9
47.5°	15518.9	15406.1	14717.2	14203.7	13013.8	11730.0	11398.0	10414.8	9087.1	5949.5	732.7
50°	16953.0	16877.9	16470.8	16063.7	14880.1	13013.8	12619.3	11091.2	9807.3	6901.4	945.7
52.5°	18124.1	18111.6	18161.7	18168.0	17272.4	15174.4	14585.7	12180.9	10634.0	7840.8	1246.3
55°	18099.1	18155.4	18706.6	19339.1	19408.0	18124.1	17554.2	14015.8	11711.2	8999.4	1665.9
57.5°	17422.7	17378.9	17961.3	18913.2	19583.3	19721.1	19627.2	16865.3	13333.2	10396.0	2310.9
58°	17203.5	17165.9	17717.1	18687.8	19458.1	19827.6	19733.6	17510.4	13696.4	10596.4	2486.3
60°	16408.2	16414.4	16740.1	17623.1	18393.4	19270.2	19357.9	19351.6	15506.3	11936.6	3369.3
62.5°	15356.0	15305.9	15606.5	16326.7	17003.1	17591.8	17742.1	19476.9	18155.4	13640.1	5054.0
65°	13903.1	13827.9	14147.3	14961.5	15688.0	16070.0	16076.2	17798.5	19401.7	15468.8	7458.8
67.5°	11203.9	11141.3	11780.1	12825.9	13946.9	14447.9	14673.4	15443.7	18349.6	16708.8	8836.6
70°	6863.9	6995.4	7884.7	9525.5	11441.9	12362.5	12700.7	12938.6	15625.3	16520.9	7389.9
72.5°	3168.9	3012.3	3770.1	4916.2	7101.9	9149.7	9500.5	10433.6	12387.5	14341.5	5511.1
75°	1478.0	1421.6	1597.0	2148.1	3219.0	4941.2	5580.0	8329.3	9500.5	9976.4	3976.8
77.5°	757.8	764.0	908.1	977.0	1327.7	2285.9	2624.1	5479.8	6964.1	5567.5	2667.9
80°	331.9	344.4	350.7	382.0	538.6	883.0	995.8	2542.6	4759.6	2837.0	1459.2
82.5°	212.9	219.2	219.2	219.2	256.8	350.7	400.8	1020.8	2373.5	1409.1	450.9
85°	112.7	112.7	125.3	156.6	181.6	212.9	225.5	325.7	782.8	419.6	106.5
87.5°	62.6	68.9	75.2	93.9	119.0	144.0	156.6	225.5	300.6	288.1	25.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1062710

CATALOG NUMBER: GLAN-SA7B-722-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6
2.5°	162.8	156.6	150.3	144.0	137.8	131.5	131.5	131.5	131.5	131.5	131.5
5°	156.6	150.3	144.0	131.5	119.0	112.7	106.5	100.2	100.2	100.2	100.2
7.5°	156.6	150.3	131.5	119.0	106.5	93.9	81.4	81.4	81.4	81.4	81.4
10°	156.6	144.0	125.3	106.5	87.7	75.2	68.9	62.6	62.6	62.6	62.6
12.5°	156.6	137.8	119.0	93.9	75.2	62.6	56.4	50.1	50.1	50.1	50.1
15°	156.6	137.8	112.7	87.7	68.9	50.1	43.8	37.6	37.6	37.6	37.6
17.5°	150.3	131.5	106.5	75.2	56.4	37.6	31.3	25.1	25.1	31.3	31.3
20°	144.0	125.3	93.9	62.6	43.8	31.3	18.8	18.8	18.8	18.8	18.8
22.5°	144.0	125.3	87.7	56.4	37.6	18.8	12.5	12.5	12.5	12.5	18.8
25°	144.0	119.0	75.2	43.8	25.1	12.5	6.3	6.3	6.3	6.3	6.3
27.5°	144.0	119.0	68.9	37.6	18.8	12.5	6.3	0.0	0.0	0.0	0.0
30°	137.8	112.7	62.6	31.3	12.5	6.3	0.0	0.0	0.0	0.0	0.0
32.5°	137.8	106.5	50.1	25.1	12.5	6.3	0.0	0.0	0.0	0.0	0.0
35°	144.0	100.2	43.8	18.8	6.3	0.0	0.0	0.0	0.0	0.0	6.3
37.5°	150.3	93.9	37.6	12.5	6.3	0.0	0.0	0.0	0.0	0.0	0.0
40°	156.6	87.7	37.6	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	169.1	87.7	31.3	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	181.6	87.7	25.1	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	206.7	93.9	25.1	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	225.5	100.2	18.8	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	250.5	93.9	18.8	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	281.8	93.9	18.8	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	306.9	87.7	18.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	319.4	81.4	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	382.0	75.2	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	595.0	62.6	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1208.7	56.4	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2254.6	50.1	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2523.9	56.4	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1590.7	43.8	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	839.2	43.8	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	419.6	43.8	6.3	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	194.1	31.3	6.3	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	81.4	18.8	12.5	6.3	6.3	0.0	0.0	0.0	0.0	0.0	0.0
85°	37.6	18.8	12.5	12.5	6.3	6.3	0.0	0.0	0.0	0.0	0.0
87.5°	18.8	18.8	18.8	12.5	12.5	6.3	6.3	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-722-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160	CRI (Ra):	71.9		
CIE u':	0.2927	R1:	68.7	R9:	-17.8
CIE v':	0.5388	R2:	82.6	R10:	60.5
Duv:	0.0015	R3:	95.5	R11:	60.2
CIE x:	0.5130	R4:	66.4	R12:	48.2
CIE y:	0.4197	R5:	65.4	R13:	70.7
CIE z:	0.0674	R6:	75.9	R14:	96.8
Peak Wavelength (nm):	609	R7:	77.2	R15:	61.8
Dominant Wavelength (nm):	587	R8:	43.5		
Purity:	79.96089				
Rf:	70.6				
Rg:	97.6				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 0.8

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 1.21

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

TM-30-18

Summary

$R_f = 70.6$
 $R_g = 97.6$
 $CIE\ R_a = 71.9$
 $R_g = -17.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)