

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063338

Luminaire Tested: **GLAN-SA2B-727-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1063338
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA2B-727-U-T2BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 2xLight Square PACKAGE
70CRI 2700K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (28) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8301.4 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 72.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1063338

CATALOG NUMBER: GLAN-SA2B-727-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 11 fc
 Type II - Short - N/A

REPORT NUMBER: P1063338

CATALOG NUMBER: GLAN-SA2B-727-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1063338

CATALOG NUMBER: GLAN-SA2B-727-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	35.4	0.0	35.4
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	8266.0	0.0	8266.0
	% Fixture	99.6	0.0	99.6
Total	Lumens	8301.4	0.0	8301.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.5	0.1
10°-20°	68.3	0.8
20°-30°	245.0	3.0
30°-40°	652.3	7.9
40°-50°	1713.5	20.6
50°-60°	2654.5	32.0
60°-70°	2225.7	26.8
70°-80°	655.0	7.9
80°-90°	80.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8301.4	100.0
0°-180°	8301.4	100.0



REPORT NUMBER: P1063338


CATALOG NUMBER: GLAN-SA2B-727-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	311.8	3.8			
FM	(30°-60°)	5006.7	60.3			
FH	(60°-80°)	2868.2	34.6			G2/5000
FVH	(80°-90°)	79.3	1.0			G1/100
BL	(0°-30°)	8.0	0.1	B0/110		
BM	(30°-60°)	13.5	0.2	B0/220		
BH	(60°-80°)	12.5	0.2	B0/110		G0/110
BVH	(80°-90°)	1.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short



REPORT NUMBER: P1063338

CATALOG NUMBER: GLAN-SA2B-727-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8
2.5°	61.7	62.2	61.1	58.8	57.1	57.1	56.5	54.8	54.8	53.1	52.0
5°	86.2	85.1	82.8	78.2	74.2	70.2	66.2	62.2	61.7	56.5	53.1
7.5°	141.0	142.2	134.8	120.5	108.5	93.1	78.8	70.2	69.1	60.5	53.7
10°	309.5	300.9	283.8	228.4	187.9	141.6	105.1	81.7	80.5	65.1	54.8
12.5°	564.2	557.3	525.9	468.8	364.3	253.5	153.6	101.1	97.6	69.1	55.4
15°	813.2	802.3	785.2	727.5	605.3	454.6	251.3	138.2	129.1	74.8	54.8
17.5°	971.9	973.6	958.2	933.7	854.9	672.7	434.0	206.1	188.4	85.1	53.7
20°	1110.7	1106.7	1115.3	1102.1	1046.7	914.3	631.6	326.6	296.4	101.6	54.2
22.5°	1270.6	1280.3	1286.6	1283.7	1222.6	1109.5	856.0	488.8	450.6	131.9	56.0
25°	1484.7	1483.6	1484.2	1476.7	1417.3	1291.7	1081.0	690.4	651.6	181.0	60.0
27.5°	1709.2	1716.0	1718.9	1692.0	1614.4	1491.0	1289.4	910.8	865.1	259.8	65.1
30°	2015.8	2010.1	1997.0	1942.1	1847.9	1694.9	1495.0	1142.1	1094.1	370.0	73.1
32.5°	2429.2	2423.0	2356.7	2235.7	2094.6	1907.3	1701.7	1373.9	1315.7	507.7	83.9
35°	3110.5	3120.2	2957.5	2644.0	2391.0	2162.6	1930.7	1604.6	1553.3	677.3	98.8
37.5°	4153.8	4100.7	3879.7	3325.8	2781.0	2481.2	2149.4	1837.6	1793.1	886.3	118.2
40°	5167.4	5114.9	5050.9	4526.1	3458.8	2832.4	2455.5	2111.2	2053.5	1122.1	146.8
42.5°	6233.0	6203.9	6201.0	5805.3	4695.7	3384.6	2823.8	2431.5	2382.4	1380.8	193.6
45°	6987.9	6958.8	7019.9	7089.0	6380.3	4567.8	3465.1	2847.8	2776.4	1694.9	268.4
47.5°	7089.6	7090.7	7254.0	7470.5	7632.1	6398.0	4319.4	3399.5	3312.7	2144.3	394.0
50°	6751.5	6764.7	7024.5	7411.7	7846.8	7933.6	5825.8	4200.1	4071.6	2677.1	572.2
52.5°	6107.9	6122.8	6484.8	7121.6	7649.2	8302.5	7599.5	5247.4	5099.5	3341.8	823.5
55°	5528.3	5537.5	5952.6	6757.2	7411.1	8102.1	8652.5	6645.9	6451.7	4159.5	1071.3
57.5°	4954.4	4933.3	5203.4	6124.5	7370.5	7855.9	8807.9	8239.7	8025.5	5053.2	1264.3
60°	4186.9	4151.5	4368.5	4954.4	6837.2	8017.5	8517.2	9121.4	9072.8	6297.5	1413.3
61°	3745.5	3730.7	3948.8	4451.3	6388.3	7976.4	8447.5	9158.5	9163.6	6886.3	1480.2
62.5°	2674.8	2717.1	3050.5	3703.8	5350.7	7709.7	8456.7	9043.7	9094.5	7668.6	1653.2
65°	1188.9	1256.9	1516.1	2047.8	3111.7	6413.5	8375.6	8791.9	8766.8	7883.3	2249.4
67.5°	705.2	715.5	844.6	1160.4	1648.0	3449.7	7391.1	8459.0	8425.3	6862.9	2798.7
70°	555.6	560.8	601.9	728.1	956.5	1321.4	4218.3	7318.6	7465.3	5564.9	2739.9
72.5°	527.1	525.9	531.6	553.9	602.5	655.6	1633.2	4864.8	5163.4	4007.6	2297.3
75°	520.2	517.9	512.2	503.7	436.3	386.0	506.0	2151.7	2324.7	2738.2	1729.7
77.5°	504.8	505.4	506.5	483.1	374.0	273.0	245.0	690.4	849.2	1737.7	1229.5
80°	341.5	346.6	355.2	346.1	336.3	197.6	173.0	245.6	249.0	975.4	812.0
82.5°	173.0	173.0	169.0	150.8	130.2	128.5	137.6	178.2	180.5	493.4	382.0
85°	104.5	110.2	112.5	102.2	93.7	86.2	105.1	141.6	146.8	191.3	89.1
87.5°	23.4	24.0	26.3	34.8	50.8	69.1	97.6	129.6	131.9	122.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1063338

CATALOG NUMBER: GLAN-SA2B-727-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8
2.5°	51.4	50.3	49.7	48.0	46.3	44.5	43.4	42.8	43.4	44.0	44.0
5°	50.8	49.1	46.3	43.4	41.1	38.8	36.5	36.0	36.0	36.5	36.5
7.5°	50.8	48.0	44.0	40.5	37.1	33.7	32.0	30.8	31.4	31.4	31.4
10°	50.8	47.4	42.3	37.1	33.1	29.1	26.3	25.1	25.1	25.1	25.1
12.5°	50.3	46.8	40.5	34.3	28.6	24.0	20.6	18.8	19.4	19.4	19.4
15°	49.1	45.1	38.3	29.1	22.8	18.3	14.8	13.1	13.7	14.8	15.4
17.5°	47.4	43.4	34.3	24.6	18.3	13.7	10.3	9.1	9.7	11.4	11.4
20°	46.8	41.7	30.3	20.0	13.7	9.7	6.9	5.7	6.3	8.6	9.1
22.5°	46.8	40.5	27.4	16.6	10.3	6.3	4.0	2.3	2.3	4.0	4.0
25°	47.4	40.0	25.1	13.7	7.4	4.6	2.3	1.1	2.3	6.3	7.4
27.5°	48.5	39.4	24.0	11.4	5.7	4.0	1.7	4.0	6.9	6.9	6.9
30°	49.7	38.3	22.3	9.7	5.1	2.9	2.9	5.7	5.7	6.9	7.4
32.5°	51.4	37.7	21.1	8.6	4.0	2.3	4.0	3.4	3.4	4.0	4.6
35°	54.8	38.3	20.0	8.6	4.0	2.9	3.4	1.7	1.1	1.1	1.1
37.5°	59.4	38.8	18.3	7.4	3.4	3.4	1.7	0.0	0.0	0.0	0.0
40°	66.8	40.5	17.1	6.9	2.9	2.9	0.6	0.0	0.0	0.0	0.0
42.5°	79.4	44.0	16.6	6.3	2.9	2.3	0.0	0.0	0.0	0.0	0.0
45°	104.5	52.0	15.4	5.7	2.9	1.1	0.0	0.0	0.0	0.0	0.0
47.5°	150.2	70.8	14.8	4.6	1.7	0.0	0.0	0.0	0.0	0.0	0.0
50°	219.3	95.9	14.3	4.0	0.6	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	279.8	101.1	9.7	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	286.7	69.7	7.4	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	228.4	45.1	6.3	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	173.0	34.3	5.7	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
61°	166.2	30.8	5.7	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	183.3	26.8	5.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	298.1	22.3	4.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	517.9	19.4	4.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	654.4	18.3	3.4	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	570.5	16.6	3.4	1.1	0.6	0.0	0.0	0.0	0.0	0.0	0.0
75°	343.2	14.3	3.4	2.3	1.1	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	179.9	10.8	3.4	2.9	1.7	0.6	0.0	0.0	0.0	0.0	0.0
80°	87.4	9.7	4.0	2.9	2.3	1.1	0.0	0.0	0.0	0.0	0.0
82.5°	34.3	8.0	4.6	4.0	2.9	1.7	0.6	0.0	0.0	0.0	0.0
85°	15.4	6.9	5.1	4.6	4.0	2.3	0.6	0.0	0.0	0.0	0.0
87.5°	8.0	6.3	5.7	5.1	4.0	2.9	1.1	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-727-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672	CRI (Ra):	71.1		
CIE u':	0.2638	R1:	68.3	R9:	-27.8
CIE v':	0.5276	R2:	79.8	R10:	54.4
Duv:	-0.0002	R3:	91.2	R11:	65.8
CIE x:	0.4619	R4:	69.4	R12:	45.6
CIE y:	0.4106	R5:	66.5	R13:	69.8
CIE z:	0.1275	R6:	72.6	R14:	94.5
Peak Wavelength (nm):	601	R7:	77.0	R15:	60.1
Dominant Wavelength (nm):	584	R8:	44.1		
Purity:	61.88407				
Rf:	67.9				
Rg:	98.6				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength

Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.02

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.71

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

TM-30-18

Summary

$R_f = 67.9$
 $R_g = 98.6$
 $CIE R_a = 71.1$
 $R_g = -27.8$

Spectral Power Distribution Comparison



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)