

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064499

Luminaire Tested: **GLAN-SA4C-740-U-RBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1064499  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA4C-740-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 4xLight Square PACKAGE  
70CRI 4000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (56) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20504 lumens  
Efficiency: N/A  
Efficacy: 107.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3

Input Watts (W): 190.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3 fc

Type III - Short - N/A

REPORT NUMBER: P1064499  
CATALOG NUMBER: GLAN-SA4C-740-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 102.7    | 0.0    | 102.7   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 20401.4  | 0.0    | 20401.4 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 20504.0  | 0.0    | 20504.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 8.0     | 0.0       |
| 10°-20°   | 45.0    | 0.2       |
| 20°-30°   | 485.9   | 2.4       |
| 30°-40°   | 1436.9  | 7.0       |
| 40°-50°   | 4282.5  | 20.9      |
| 50°-60°   | 6790.4  | 33.1      |
| 60°-70°   | 5668.4  | 27.6      |
| 70°-80°   | 1747.9  | 8.5       |
| 80°-90°   | 38.9    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20504.0 | 100.0     |
| 0°-180°   | 20504.0 | 100.0     |



REPORT NUMBER: P1064499


CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 520.1   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 12473.2 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 7378.0  | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 30.0    | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 18.9    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 36.7    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 38.3    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 8.8     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 89.9   | 89.9   | 89.9  | 89.9  | 89.9  | 89.9  | 89.9  | 89.9  | 89.9  | 89.9  |
| 2.5°   | 82.1   | 82.1   | 82.1  | 82.1  | 80.6  | 80.6  | 79.0  | 79.0  | 77.5  | 77.5  |
| 5°     | 86.8   | 86.8   | 85.2  | 83.7  | 83.7  | 82.1  | 80.6  | 79.0  | 79.0  | 77.5  |
| 7.5°   | 94.5   | 93.0   | 91.4  | 89.9  | 86.8  | 85.2  | 82.1  | 80.6  | 79.0  | 75.9  |
| 10°    | 103.8  | 100.7  | 97.6  | 94.5  | 91.4  | 88.3  | 85.2  | 83.7  | 80.6  | 79.0  |
| 12.5°  | 116.2  | 111.6  | 105.4 | 100.7 | 97.6  | 93.0  | 89.9  | 86.8  | 82.1  | 79.0  |
| 15°    | 127.1  | 120.9  | 113.1 | 106.9 | 102.3 | 96.1  | 91.4  | 86.8  | 83.7  | 79.0  |
| 17.5°  | 142.6  | 131.7  | 119.3 | 111.6 | 105.4 | 97.6  | 89.9  | 85.2  | 80.6  | 74.4  |
| 20°    | 168.9  | 147.2  | 124.0 | 114.7 | 105.4 | 96.1  | 86.8  | 80.6  | 75.9  | 69.7  |
| 22.5°  | 210.7  | 173.5  | 136.4 | 122.4 | 110.0 | 96.1  | 83.7  | 77.5  | 71.3  | 65.1  |
| 25°    | 291.3  | 224.7  | 158.0 | 139.5 | 120.9 | 102.3 | 83.7  | 75.9  | 69.7  | 62.0  |
| 27.5°  | 387.4  | 288.2  | 187.5 | 161.1 | 136.4 | 110.0 | 83.7  | 74.4  | 66.6  | 57.3  |
| 30°    | 485.0  | 353.3  | 220.0 | 185.9 | 151.8 | 117.8 | 83.7  | 72.8  | 63.5  | 52.7  |
| 32.5°  | 578.0  | 413.7  | 247.9 | 207.6 | 167.3 | 125.5 | 85.2  | 72.8  | 60.4  | 48.0  |
| 35°    | 672.5  | 463.3  | 252.6 | 210.7 | 168.9 | 125.5 | 83.7  | 69.7  | 57.3  | 43.4  |
| 37.5°  | 793.3  | 519.1  | 243.3 | 201.4 | 161.1 | 119.3 | 79.0  | 66.6  | 54.2  | 40.3  |
| 40°    | 976.2  | 612.0  | 247.9 | 204.5 | 161.1 | 117.8 | 74.4  | 62.0  | 51.1  | 38.7  |
| 42.5°  | 1314.0 | 791.8  | 268.1 | 218.5 | 168.9 | 117.8 | 68.2  | 57.3  | 48.0  | 37.2  |
| 45°    | 2271.5 | 1315.5 | 359.5 | 285.1 | 210.7 | 136.4 | 62.0  | 52.7  | 44.9  | 35.6  |
| 47.5°  | 3757.5 | 2201.8 | 646.1 | 498.9 | 353.3 | 206.1 | 60.4  | 52.7  | 44.9  | 35.6  |
| 50°    | 4795.6 | 2804.5 | 813.5 | 626.0 | 438.5 | 251.0 | 63.5  | 54.2  | 46.5  | 37.2  |
| 52.5°  | 4787.9 | 2847.9 | 906.4 | 695.7 | 486.5 | 275.8 | 66.6  | 57.3  | 49.6  | 40.3  |
| 55°    | 4256.4 | 2590.7 | 923.5 | 709.7 | 497.4 | 283.6 | 71.3  | 62.0  | 52.7  | 43.4  |
| 57.5°  | 3557.6 | 2200.2 | 842.9 | 652.3 | 463.3 | 272.7 | 82.1  | 71.3  | 62.0  | 51.1  |
| 60°    | 2813.8 | 1735.4 | 657.0 | 519.1 | 382.7 | 244.8 | 108.5 | 94.5  | 82.1  | 68.2  |
| 62.5°  | 1943.0 | 1258.2 | 573.3 | 460.2 | 348.6 | 235.5 | 124.0 | 110.0 | 97.6  | 83.7  |
| 65°    | 1374.4 | 946.7  | 517.5 | 421.5 | 326.9 | 230.9 | 134.8 | 119.3 | 105.4 | 89.9  |
| 67.5°  | 1027.3 | 753.0  | 477.2 | 395.1 | 313.0 | 230.9 | 148.7 | 130.2 | 113.1 | 94.5  |
| 70°    | 787.1  | 618.2  | 447.8 | 381.2 | 316.1 | 249.5 | 182.8 | 156.5 | 131.7 | 105.4 |
| 72.5°  | 641.5  | 528.4  | 413.7 | 365.7 | 317.6 | 269.6 | 221.6 | 187.5 | 153.4 | 117.8 |
| 75°    | 531.5  | 452.4  | 373.4 | 333.1 | 294.4 | 254.1 | 213.8 | 182.8 | 153.4 | 122.4 |
| 77.5°  | 353.3  | 322.3  | 289.8 | 266.5 | 243.3 | 218.5 | 195.2 | 168.9 | 144.1 | 117.8 |
| 80°    | 124.0  | 119.3  | 114.7 | 124.0 | 133.3 | 142.6 | 151.8 | 133.3 | 116.2 | 97.6  |
| 82.5°  | 18.6   | 17.0   | 15.5  | 17.0  | 18.6  | 20.1  | 21.7  | 23.2  | 24.8  | 26.3  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 |
| 0.0 | 2.5°   | 75.9  | 75.9 | 74.4  | 74.4 | 74.4  | 72.8 | 72.8  | 71.3 | 71.3  | 71.3 |
| 0.0 | 5°     | 74.4  | 74.4 | 72.8  | 71.3 | 69.7  | 69.7 | 68.2  | 66.6 | 66.6  | 65.1 |
| 0.0 | 7.5°   | 72.8  | 71.3 | 69.7  | 68.2 | 66.6  | 65.1 | 63.5  | 62.0 | 62.0  | 60.4 |
| 0.0 | 10°    | 74.4  | 71.3 | 69.7  | 66.6 | 65.1  | 63.5 | 60.4  | 58.9 | 57.3  | 57.3 |
| 0.0 | 12.5°  | 71.3  | 69.7 | 66.6  | 63.5 | 62.0  | 58.9 | 57.3  | 54.2 | 52.7  | 52.7 |
| 0.0 | 15°    | 71.3  | 68.2 | 63.5  | 60.4 | 57.3  | 55.8 | 52.7  | 49.6 | 48.0  | 46.5 |
| 0.0 | 17.5°  | 66.6  | 63.5 | 58.9  | 55.8 | 52.7  | 49.6 | 46.5  | 43.4 | 41.8  | 40.3 |
| 0.0 | 20°    | 60.4  | 57.3 | 52.7  | 48.0 | 44.9  | 41.8 | 38.7  | 35.6 | 34.1  | 32.5 |
| 0.0 | 22.5°  | 54.2  | 51.1 | 46.5  | 41.8 | 38.7  | 35.6 | 31.0  | 27.9 | 26.3  | 23.2 |
| 0.0 | 25°    | 51.1  | 46.5 | 41.8  | 37.2 | 32.5  | 29.4 | 24.8  | 20.1 | 17.0  | 13.9 |
| 0.0 | 27.5°  | 43.4  | 38.7 | 34.1  | 29.4 | 24.8  | 20.1 | 15.5  | 10.8 | 7.7   | 6.2  |
| 0.0 | 30°    | 37.2  | 32.5 | 27.9  | 23.2 | 17.0  | 12.4 | 7.7   | 1.5  | 1.5   | 1.5  |
| 0.0 | 32.5°  | 31.0  | 26.3 | 20.1  | 15.5 | 12.4  | 7.7  | 4.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 24.8  | 20.1 | 13.9  | 9.3  | 7.7   | 4.6  | 3.1   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 21.7  | 17.0 | 10.8  | 4.6  | 3.1   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 20.1  | 13.9 | 7.7   | 1.5  | 1.5   | 1.5  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 20.1  | 13.9 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 20.1  | 13.9 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 20.1  | 13.9 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 21.7  | 15.5 | 7.7   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 24.8  | 18.6 | 12.4  | 6.2  | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 31.0  | 27.9 | 23.2  | 20.1 | 15.5  | 10.8 | 4.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 40.3  | 40.3 | 38.7  | 37.2 | 27.9  | 18.6 | 9.3   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 54.2  | 54.2 | 54.2  | 54.2 | 40.3  | 27.9 | 13.9  | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 66.6  | 63.5 | 58.9  | 55.8 | 41.8  | 27.9 | 13.9  | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 66.6  | 60.4 | 52.7  | 44.9 | 34.1  | 23.2 | 10.8  | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 62.0  | 49.6 | 35.6  | 23.2 | 17.0  | 12.4 | 6.2   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 62.0  | 43.4 | 24.8  | 6.2  | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 62.0  | 41.8 | 20.1  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 68.2  | 46.5 | 23.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 68.2  | 46.5 | 23.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 60.4  | 40.3 | 20.1  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 20.1  | 13.9 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  |
| 0.0   | 2.5°   | 69.7 | 69.7  | 69.7 | 68.2  | 68.2 | 68.2  | 68.2 | 66.6  | 66.6 | 66.6  |
| 0.0   | 5°     | 63.5 | 63.5  | 62.0 | 62.0  | 60.4 | 60.4  | 58.9 | 58.9  | 57.3 | 57.3  |
| 0.0   | 7.5°   | 58.9 | 57.3  | 57.3 | 55.8  | 54.2 | 54.2  | 52.7 | 52.7  | 51.1 | 49.6  |
| 0.0   | 10°    | 54.2 | 52.7  | 52.7 | 51.1  | 49.6 | 48.0  | 48.0 | 46.5  | 44.9 | 43.4  |
| 0.0   | 12.5°  | 49.6 | 48.0  | 46.5 | 44.9  | 43.4 | 41.8  | 41.8 | 40.3  | 38.7 | 37.2  |
| 0.0   | 15°    | 43.4 | 41.8  | 40.3 | 38.7  | 37.2 | 35.6  | 35.6 | 34.1  | 32.5 | 31.0  |
| 0.0   | 17.5°  | 37.2 | 35.6  | 35.6 | 34.1  | 32.5 | 31.0  | 29.4 | 26.3  | 24.8 | 23.2  |
| 0.0   | 20°    | 27.9 | 26.3  | 24.8 | 23.2  | 21.7 | 18.6  | 17.0 | 13.9  | 10.8 | 9.3   |
| 0.0   | 22.5°  | 18.6 | 15.5  | 13.9 | 10.8  | 7.7  | 6.2   | 4.6  | 1.5   | 0.0  | 0.0   |
| 0.0   | 25°    | 6.2  | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9  | 89.9 | 89.9   | 89.9 |
| 0.0 | 2.5°   | 65.1  | 65.1 | 65.1  | 63.5 | 63.5  | 63.5 | 63.5  | 63.5 | 63.5   | 63.5 |
| 0.0 | 5°     | 55.8  | 55.8 | 55.8  | 54.2 | 54.2  | 52.7 | 52.7  | 52.7 | 51.1   | 51.1 |
| 0.0 | 7.5°   | 48.0  | 46.5 | 46.5  | 44.9 | 44.9  | 43.4 | 43.4  | 43.4 | 41.8   | 41.8 |
| 0.0 | 10°    | 40.3  | 38.7 | 38.7  | 37.2 | 37.2  | 35.6 | 35.6  | 34.1 | 34.1   | 32.5 |
| 0.0 | 12.5°  | 35.6  | 34.1 | 32.5  | 31.0 | 31.0  | 29.4 | 27.9  | 27.9 | 26.3   | 24.8 |
| 0.0 | 15°    | 27.9  | 26.3 | 24.8  | 23.2 | 21.7  | 20.1 | 18.6  | 18.6 | 17.0   | 15.5 |
| 0.0 | 17.5°  | 18.6  | 15.5 | 13.9  | 12.4 | 12.4  | 10.8 | 9.3   | 7.7  | 6.2    | 4.6  |
| 0.0 | 20°    | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   |
| 0.0    | 2.5°   | 63.5 | 62.0   | 62.0 | 62.0   | 63.5 | 63.5   | 63.5 | 63.5   | 63.5 | 63.5   |
| 0.0    | 5°     | 51.1 | 49.6   | 49.6 | 49.6   | 49.6 | 49.6   | 49.6 | 49.6   | 49.6 | 49.6   |
| 0.0    | 7.5°   | 41.8 | 40.3   | 40.3 | 40.3   | 40.3 | 38.7   | 38.7 | 38.7   | 38.7 | 38.7   |
| 0.0    | 10°    | 32.5 | 31.0   | 31.0 | 31.0   | 31.0 | 29.4   | 29.4 | 29.4   | 29.4 | 29.4   |
| 0.0    | 12.5°  | 23.2 | 23.2   | 21.7 | 21.7   | 21.7 | 20.1   | 20.1 | 20.1   | 20.1 | 18.6   |
| 0.0    | 15°    | 13.9 | 12.4   | 10.8 | 10.8   | 10.8 | 9.3    | 9.3  | 9.3    | 9.3  | 7.7    |
| 0.0    | 17.5°  | 3.1  | 3.1    | 1.5  | 1.5    | 1.5  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 |
| 0.0  | 2.5°   | 65.1   | 65.1 | 66.6   | 66.6 | 68.2   | 71.3 | 72.8   | 74.4 | 77.5   | 80.6 |
| 0.0  | 5°     | 51.1   | 52.7 | 52.7   | 54.2 | 55.8   | 57.3 | 58.9   | 60.4 | 63.5   | 66.6 |
| 0.0  | 7.5°   | 40.3   | 40.3 | 41.8   | 41.8 | 43.4   | 46.5 | 48.0   | 49.6 | 52.7   | 57.3 |
| 0.0  | 10°    | 31.0   | 31.0 | 32.5   | 32.5 | 34.1   | 37.2 | 38.7   | 40.3 | 43.4   | 48.0 |
| 0.0  | 12.5°  | 20.1   | 21.7 | 21.7   | 23.2 | 24.8   | 27.9 | 29.4   | 31.0 | 34.1   | 37.2 |
| 0.0  | 15°    | 9.3    | 10.8 | 10.8   | 12.4 | 13.9   | 17.0 | 18.6   | 20.1 | 23.2   | 27.9 |
| 0.0  | 17.5°  | 1.5    | 1.5  | 3.1    | 3.1  | 4.6    | 6.2  | 7.7    | 9.3  | 13.9   | 17.0 |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 6.2  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 1.5  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 89.9 | 89.9   | 89.9 | 89.9   | 89.9 | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   |
| 0.0    | 2.5°   | 85.2 | 88.3   | 91.4 | 94.5   | 97.6 | 100.7  | 102.3 | 105.4  | 106.9 | 108.5  |
| 0.0    | 5°     | 72.8 | 75.9   | 80.6 | 83.7   | 86.8 | 89.9   | 93.0  | 94.5   | 96.1  | 97.6   |
| 0.0    | 7.5°   | 63.5 | 66.6   | 71.3 | 74.4   | 77.5 | 80.6   | 83.7  | 86.8   | 88.3  | 89.9   |
| 0.0    | 10°    | 54.2 | 58.9   | 62.0 | 66.6   | 69.7 | 72.8   | 75.9  | 79.0   | 82.1  | 83.7   |
| 0.0    | 12.5°  | 43.4 | 48.0   | 52.7 | 55.8   | 60.4 | 65.1   | 68.2  | 71.3   | 74.4  | 77.5   |
| 0.0    | 15°    | 34.1 | 38.7   | 43.4 | 46.5   | 51.1 | 55.8   | 60.4  | 63.5   | 66.6  | 69.7   |
| 0.0    | 17.5°  | 24.8 | 29.4   | 34.1 | 37.2   | 41.8 | 46.5   | 49.6  | 54.2   | 57.3  | 60.4   |
| 0.0    | 20°    | 12.4 | 17.0   | 21.7 | 26.3   | 31.0 | 35.6   | 38.7  | 43.4   | 46.5  | 49.6   |
| 0.0    | 22.5°  | 1.5  | 6.2    | 10.8 | 13.9   | 18.6 | 23.2   | 26.3  | 31.0   | 34.1  | 37.2   |
| 0.0    | 25°    | 0.0  | 1.5    | 4.6  | 6.2    | 7.7  | 10.8   | 13.9  | 17.0   | 20.1  | 23.2   |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.5    | 3.1   | 6.2    | 9.3   | 12.4   |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 3.1    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 1.5    | 1.5   | 3.1    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 4.6   | 7.7    | 9.3   | 10.8   |
|        | 87.5°  | 0.0  | 1.5    | 3.1  | 4.6    | 6.2  | 9.3    | 12.4  | 15.5   | 17.0  | 18.6   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 89.9  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 108.5 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 99.2  | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 91.4  | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 86.8  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 79.0  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.8  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65.1  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.7  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.3  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.9  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.5  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4.6   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 1.5   |        |      |        |      |        |      |        |      |        |      |        |
| 6.2   |        |      |        |      |        |      |        |      |        |      |        |
| 13.9  |        |      |        |      |        |      |        |      |        |      |        |
| 20.1  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  |
| 0.0  | 2.5°   | 110.0  | 110.0 | 110.0  | 110.0 | 108.5  | 108.5 | 108.5  | 106.9 | 106.9  | 105.4 |
| 0.0  | 5°     | 100.7  | 102.3 | 102.3  | 102.3 | 102.3  | 102.3 | 102.3  | 102.3 | 100.7  | 100.7 |
| 0.0  | 7.5°   | 93.0   | 94.5  | 96.1   | 96.1  | 97.6   | 97.6  | 97.6   | 96.1  | 96.1   | 94.5  |
| 0.0  | 10°    | 88.3   | 89.9  | 89.9   | 91.4  | 91.4   | 91.4  | 91.4   | 91.4  | 91.4   | 91.4  |
| 0.0  | 12.5°  | 82.1   | 83.7  | 85.2   | 85.2  | 86.8   | 86.8  | 86.8   | 86.8  | 85.2   | 85.2  |
| 0.0  | 15°    | 74.4   | 77.5  | 79.0   | 80.6  | 80.6   | 82.1  | 82.1   | 82.1  | 82.1   | 82.1  |
| 0.0  | 17.5°  | 68.2   | 71.3  | 72.8   | 74.4  | 74.4   | 75.9  | 75.9   | 77.5  | 77.5   | 77.5  |
| 0.0  | 20°    | 55.8   | 58.9  | 60.4   | 63.5  | 65.1   | 66.6  | 68.2   | 69.7  | 69.7   | 71.3  |
| 0.0  | 22.5°  | 43.4   | 46.5  | 48.0   | 51.1  | 52.7   | 54.2  | 55.8   | 57.3  | 58.9   | 60.4  |
| 0.0  | 25°    | 31.0   | 34.1  | 35.6   | 38.7  | 40.3   | 41.8  | 43.4   | 44.9  | 44.9   | 46.5  |
| 0.0  | 27.5°  | 17.0   | 20.1  | 23.2   | 24.8  | 27.9   | 29.4  | 31.0   | 32.5  | 34.1   | 35.6  |
| 0.0  | 30°    | 7.7    | 9.3   | 10.8   | 13.9  | 15.5   | 17.0  | 18.6   | 21.7  | 23.2   | 24.8  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 1.5    | 4.6   | 6.2    | 7.7   | 9.3    | 10.8  | 10.8   | 12.4  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    | 3.1   | 4.6    | 6.2   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 3.1    | 3.1   | 3.1    | 4.6   | 4.6    | 4.6   | 4.6    | 4.6   | 4.6    | 4.6   |
|      | 82.5°  | 7.7    | 9.3   | 10.8   | 10.8  | 12.4   | 12.4  | 12.4   | 12.4  | 10.8   | 10.8  |
|      | 85°    | 15.5   | 17.0  | 18.6   | 18.6  | 20.1   | 20.1  | 20.1   | 20.1  | 20.1   | 20.1  |
|      | 87.5°  | 21.7   | 23.2  | 24.8   | 24.8  | 26.3   | 26.3  | 26.3   | 26.3  | 26.3   | 26.3  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 89.9   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105.4  | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100.7  | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94.5   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 91.4   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85.2   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 82.1   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 77.5   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 69.7   | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 60.4   | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 48.0   | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.2   | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 26.3   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 15.5   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 9.3    | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.1    | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.1    | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 4.6    |        |      |        |      |        |      |        |      |        |      |
| 10.8   |        |      |        |      |        |      |        |      |        |      |
| 20.1   |        |      |        |      |        |      |        |      |        |      |
| 26.3   |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   |
| 0.0    | 2.5°   | 103.8 | 103.8  | 102.3 | 102.3  | 102.3 | 102.3  | 102.3 | 103.8  | 105.4 | 105.4  |
| 0.0    | 5°     | 99.2  | 99.2   | 97.6  | 97.6   | 97.6  | 99.2   | 99.2  | 100.7  | 102.3 | 103.8  |
| 0.0    | 7.5°   | 94.5  | 93.0   | 93.0  | 94.5   | 94.5  | 96.1   | 96.1  | 97.6   | 99.2  | 100.7  |
| 0.0    | 10°    | 91.4  | 89.9   | 89.9  | 89.9   | 91.4  | 91.4   | 93.0  | 94.5   | 96.1  | 97.6   |
| 0.0    | 12.5°  | 85.2  | 85.2   | 85.2  | 85.2   | 86.8  | 86.8   | 88.3  | 89.9   | 93.0  | 94.5   |
| 0.0    | 15°    | 82.1  | 80.6   | 80.6  | 80.6   | 80.6  | 82.1   | 82.1  | 85.2   | 88.3  | 89.9   |
| 0.0    | 17.5°  | 75.9  | 75.9   | 74.4  | 74.4   | 75.9  | 75.9   | 77.5  | 80.6   | 83.7  | 85.2   |
| 0.0    | 20°    | 69.7  | 68.2   | 66.6  | 66.6   | 68.2  | 68.2   | 69.7  | 72.8   | 75.9  | 77.5   |
| 0.0    | 22.5°  | 60.4  | 58.9   | 58.9  | 58.9   | 58.9  | 60.4   | 60.4  | 63.5   | 68.2  | 71.3   |
| 0.0    | 25°    | 48.0  | 49.6   | 49.6  | 51.1   | 51.1  | 52.7   | 54.2  | 57.3   | 62.0  | 65.1   |
| 0.0    | 27.5°  | 37.2  | 38.7   | 38.7  | 41.8   | 43.4  | 44.9   | 46.5  | 51.1   | 55.8  | 58.9   |
| 0.0    | 30°    | 27.9  | 29.4   | 31.0  | 32.5   | 35.6  | 38.7   | 41.8  | 46.5   | 51.1  | 54.2   |
| 0.0    | 32.5°  | 17.0  | 20.1   | 21.7  | 24.8   | 27.9  | 31.0   | 34.1  | 38.7   | 44.9  | 49.6   |
| 0.0    | 35°    | 12.4  | 13.9   | 17.0  | 18.6   | 21.7  | 24.8   | 27.9  | 34.1   | 38.7  | 44.9   |
| 0.0    | 37.5°  | 6.2   | 9.3    | 12.4  | 15.5   | 18.6  | 21.7   | 24.8  | 31.0   | 37.2  | 41.8   |
| 0.0    | 40°    | 4.6   | 7.7    | 9.3   | 12.4   | 17.0  | 20.1   | 23.2  | 29.4   | 35.6  | 41.8   |
| 0.0    | 42.5°  | 3.1   | 4.6    | 6.2   | 10.8   | 13.9  | 18.6   | 23.2  | 29.4   | 35.6  | 41.8   |
| 0.0    | 45°    | 3.1   | 3.1    | 4.6   | 9.3    | 13.9  | 20.1   | 24.8  | 31.0   | 35.6  | 41.8   |
| 0.0    | 47.5°  | 3.1   | 4.6    | 6.2   | 12.4   | 15.5  | 20.1   | 24.8  | 29.4   | 35.6  | 40.3   |
| 0.0    | 50°    | 4.6   | 6.2    | 7.7   | 13.9   | 17.0  | 21.7   | 24.8  | 31.0   | 35.6  | 41.8   |
| 0.0    | 52.5°  | 3.1   | 4.6    | 6.2   | 12.4   | 17.0  | 23.2   | 27.9  | 34.1   | 40.3  | 44.9   |
| 0.0    | 55°    | 1.5   | 1.5    | 1.5   | 9.3    | 18.6  | 26.3   | 35.6  | 40.3   | 46.5  | 51.1   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 6.2    | 18.6  | 29.4   | 40.3  | 46.5   | 52.7  | 57.3   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 6.2    | 18.6  | 29.4   | 40.3  | 48.0   | 55.8  | 63.5   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 6.2    | 15.5  | 24.8   | 34.1  | 46.5   | 60.4  | 72.8   |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 4.6    | 12.4  | 20.1   | 27.9  | 46.5   | 65.1  | 82.1   |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 4.6    | 12.4  | 18.6   | 26.3  | 46.5   | 65.1  | 85.2   |
|        | 70°    | 0.0   | 0.0    | 0.0   | 4.6    | 12.4  | 20.1   | 27.9  | 46.5   | 65.1  | 83.7   |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 4.6    | 13.9  | 21.7   | 31.0  | 46.5   | 62.0  | 77.5   |
|        | 75°    | 0.0   | 0.0    | 0.0   | 6.2    | 13.9  | 23.2   | 32.5  | 46.5   | 60.4  | 72.8   |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 4.6    | 13.9  | 21.7   | 31.0  | 44.9   | 58.9  | 71.3   |
|        | 80°    | 4.6   | 3.1    | 3.1   | 7.7    | 13.9  | 20.1   | 26.3  | 40.3   | 55.8  | 69.7   |
|        | 82.5°  | 9.3   | 9.3    | 7.7   | 10.8   | 13.9  | 18.6   | 23.2  | 35.6   | 49.6  | 62.0   |
|        | 85°    | 18.6  | 18.6   | 17.0  | 18.6   | 18.6  | 20.1   | 21.7  | 27.9   | 34.1  | 40.3   |
|        | 87.5°  | 24.8  | 24.8   | 23.2  | 23.2   | 23.2  | 21.7   | 21.7  | 21.7   | 21.7  | 20.1   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 89.9  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 106.9 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105.4 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.3 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 99.2  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 96.1  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 93.0  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 88.3  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.6  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 74.4  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68.2  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 63.5  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 58.9  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 54.2  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 49.6  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.0  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.0  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.0  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.5  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44.9  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.5  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 51.1  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.8  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 63.5  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71.3  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.2  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100.7 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 103.8 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.3 |        |      |        |      |        |      |        |      |        |      |        |
| 93.0  |        |      |        |      |        |      |        |      |        |      |        |
| 86.8  |        |      |        |      |        |      |        |      |        |      |        |
| 85.2  |        |      |        |      |        |      |        |      |        |      |        |
| 83.7  |        |      |        |      |        |      |        |      |        |      |        |
| 74.4  |        |      |        |      |        |      |        |      |        |      |        |
| 46.5  |        |      |        |      |        |      |        |      |        |      |        |
| 20.1  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9  | 89.9   | 89.9   |
| 0.0  | 2.5°   | 108.5  | 110.0 | 110.0  | 111.6 | 113.1  | 114.7 | 114.7  | 116.2 | 116.2  | 116.2  |
| 0.0  | 5°     | 106.9  | 110.0 | 111.6  | 113.1 | 114.7  | 116.2 | 117.8  | 119.3 | 120.9  | 120.9  |
| 0.0  | 7.5°   | 105.4  | 106.9 | 110.0  | 111.6 | 114.7  | 116.2 | 119.3  | 120.9 | 122.4  | 124.0  |
| 0.0  | 10°    | 102.3  | 105.4 | 108.5  | 111.6 | 114.7  | 117.8 | 120.9  | 124.0 | 127.1  | 128.6  |
| 0.0  | 12.5°  | 99.2   | 103.8 | 106.9  | 110.0 | 114.7  | 119.3 | 122.4  | 127.1 | 130.2  | 133.3  |
| 0.0  | 15°    | 97.6   | 100.7 | 105.4  | 108.5 | 114.7  | 120.9 | 125.5  | 131.7 | 137.9  | 142.6  |
| 0.0  | 17.5°  | 93.0   | 99.2  | 103.8  | 108.5 | 114.7  | 122.4 | 128.6  | 134.8 | 144.1  | 153.4  |
| 0.0  | 20°    | 86.8   | 91.4  | 97.6   | 102.3 | 111.6  | 119.3 | 128.6  | 136.4 | 150.3  | 164.2  |
| 0.0  | 22.5°  | 80.6   | 86.8  | 91.4   | 97.6  | 108.5  | 117.8 | 128.6  | 137.9 | 161.1  | 182.8  |
| 0.0  | 25°    | 74.4   | 82.1  | 88.3   | 94.5  | 106.9  | 119.3 | 131.7  | 144.1 | 182.8  | 221.6  |
| 0.0  | 27.5°  | 71.3   | 77.5  | 85.2   | 91.4  | 106.9  | 124.0 | 139.5  | 154.9 | 216.9  | 277.4  |
| 0.0  | 30°    | 66.6   | 74.4  | 80.6   | 88.3  | 108.5  | 128.6 | 148.7  | 168.9 | 263.4  | 357.9  |
| 0.0  | 32.5°  | 62.0   | 69.7  | 77.5   | 85.2  | 111.6  | 137.9 | 162.7  | 189.0 | 313.0  | 435.4  |
| 0.0  | 35°    | 57.3   | 66.6  | 74.4   | 82.1  | 116.2  | 151.8 | 185.9  | 220.0 | 357.9  | 494.3  |
| 0.0  | 37.5°  | 55.8   | 65.1  | 72.8   | 80.6  | 117.8  | 153.4 | 190.6  | 226.2 | 362.6  | 498.9  |
| 0.0  | 40°    | 57.3   | 65.1  | 74.4   | 82.1  | 113.1  | 144.1 | 173.5  | 204.5 | 347.1  | 488.1  |
| 0.0  | 42.5°  | 57.3   | 66.6  | 75.9   | 85.2  | 110.0  | 134.8 | 159.6  | 184.4 | 342.4  | 500.5  |
| 0.0  | 45°    | 55.8   | 65.1  | 74.4   | 83.7  | 106.9  | 128.6 | 151.8  | 173.5 | 370.3  | 565.6  |
| 0.0  | 47.5°  | 54.2   | 63.5  | 72.8   | 82.1  | 105.4  | 128.6 | 151.8  | 175.1 | 478.8  | 780.9  |
| 0.0  | 50°    | 54.2   | 63.5  | 71.3   | 79.0  | 106.9  | 136.4 | 164.2  | 192.1 | 697.3  | 1200.8 |
| 0.0  | 52.5°  | 57.3   | 65.1  | 71.3   | 77.5  | 110.0  | 144.1 | 176.6  | 209.2 | 886.3  | 1561.9 |
| 0.0  | 55°    | 62.0   | 66.6  | 72.8   | 77.5  | 117.8  | 156.5 | 196.8  | 235.5 | 943.6  | 1651.7 |
| 0.0  | 57.5°  | 68.2   | 72.8  | 77.5   | 82.1  | 131.7  | 181.3 | 229.3  | 278.9 | 948.3  | 1616.1 |
| 0.0  | 60°    | 75.9   | 82.1  | 86.8   | 91.4  | 144.1  | 198.3 | 251.0  | 303.7 | 858.4  | 1411.6 |
| 0.0  | 62.5°  | 93.0   | 100.7 | 106.9  | 114.7 | 165.8  | 215.4 | 266.5  | 316.1 | 712.8  | 1109.4 |
| 0.0  | 65°    | 106.9  | 113.1 | 119.3  | 125.5 | 175.1  | 226.2 | 275.8  | 325.4 | 604.3  | 883.2  |
| 0.0  | 67.5°  | 110.0  | 116.2 | 120.9  | 127.1 | 178.2  | 229.3 | 278.9  | 330.0 | 517.5  | 703.5  |
|      | 70°    | 111.6  | 119.3 | 128.6  | 136.4 | 189.0  | 241.7 | 292.9  | 345.5 | 458.6  | 571.8  |
|      | 72.5°  | 106.9  | 122.4 | 136.4  | 150.3 | 199.9  | 247.9 | 297.5  | 345.5 | 426.1  | 506.7  |
|      | 75°    | 106.9  | 128.6 | 148.7  | 168.9 | 206.1  | 241.7 | 278.9  | 314.5 | 376.5  | 438.5  |
|      | 77.5°  | 113.1  | 141.0 | 168.9  | 196.8 | 218.5  | 238.6 | 260.3  | 280.5 | 320.7  | 361.0  |
|      | 80°    | 113.1  | 142.6 | 170.4  | 199.9 | 209.2  | 220.0 | 229.3  | 238.6 | 243.3  | 247.9  |
|      | 82.5°  | 97.6   | 120.9 | 144.1  | 167.3 | 156.5  | 145.7 | 134.8  | 124.0 | 116.2  | 106.9  |
|      | 85°    | 49.6   | 54.2  | 57.3   | 60.4  | 55.8   | 51.1  | 46.5   | 41.8  | 38.7   | 34.1   |
|      | 87.5°  | 20.1   | 20.1  | 18.6   | 18.6  | 18.6   | 18.6  | 17.0   | 17.0  | 17.0   | 17.0   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 89.9   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 116.2  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120.9  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125.5  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 131.7  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.9  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150.3  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165.8  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 190.6  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 243.3  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 330.0  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 458.6  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 621.3  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 776.3  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 881.6  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 960.7  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1039.7 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1194.6 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1504.5 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2293.2 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3512.7 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4422.2 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4522.9 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4081.3 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3489.4 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2727.1 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2060.8 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1521.6 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1076.9 |        |        |      |        |      |        |      |        |      |        |      |
| 801.1  |        |        |      |        |      |        |      |        |      |        |      |
| 582.6  |        |        |      |        |      |        |      |        |      |        |      |
| 438.5  |        |        |      |        |      |        |      |        |      |        |      |
| 246.4  |        |        |      |        |      |        |      |        |      |        |      |
| 111.6  |        |        |      |        |      |        |      |        |      |        |      |
| 32.5   |        |        |      |        |      |        |      |        |      |        |      |
| 15.5   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 89.9   | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    |
| 0.0    | 2.5°   | 116.2  | 114.7   | 114.7   | 113.1   | 111.6   | 110.0   | 108.5   | 106.9   | 105.4   | 103.8   |
| 0.0    | 5°     | 120.9  | 120.9   | 120.9   | 119.3   | 119.3   | 117.8   | 117.8   | 116.2   | 114.7   | 113.1   |
| 0.0    | 7.5°   | 125.5  | 127.1   | 127.1   | 128.6   | 128.6   | 128.6   | 128.6   | 127.1   | 127.1   | 127.1   |
| 0.0    | 10°    | 133.3  | 134.8   | 136.4   | 137.9   | 139.5   | 141.0   | 141.0   | 142.6   | 142.6   | 142.6   |
| 0.0    | 12.5°  | 142.6  | 147.2   | 150.3   | 154.9   | 158.0   | 162.7   | 165.8   | 170.4   | 173.5   | 176.6   |
| 0.0    | 15°    | 156.5  | 164.2   | 173.5   | 181.3   | 189.0   | 199.9   | 212.3   | 223.1   | 234.0   | 251.0   |
| 0.0    | 17.5°  | 176.6  | 201.4   | 226.2   | 249.5   | 274.3   | 328.5   | 382.7   | 435.4   | 489.6   | 568.7   |
| 0.0    | 20°    | 215.4  | 289.8   | 362.6   | 437.0   | 509.8   | 700.4   | 889.4   | 1080.0  | 1269.0  | 1472.0  |
| 0.0    | 22.5°  | 302.1  | 485.0   | 667.8   | 850.7   | 1033.5  | 1431.7  | 1828.4  | 2226.6  | 2623.3  | 3089.6  |
| 0.0    | 25°    | 438.5  | 774.7   | 1111.0  | 1445.7  | 1781.9  | 2404.8  | 3029.2  | 3652.1  | 4275.0  | 4880.8  |
| 0.0    | 27.5°  | 638.4  | 1152.8  | 1667.2  | 2180.1  | 2694.5  | 3539.0  | 4385.0  | 5229.5  | 6073.9  | 6758.8  |
| 0.0    | 30°    | 884.7  | 1582.0  | 2279.3  | 2976.5  | 3673.8  | 4634.5  | 5595.1  | 6554.3  | 7514.9  | 8263.3  |
| 0.0    | 32.5°  | 1117.2 | 1970.9  | 2824.7  | 3676.9  | 4530.7  | 5624.6  | 6720.1  | 7814.0  | 8907.9  | 9726.0  |
| 0.0    | 35°    | 1269.0 | 2301.0  | 3334.5  | 4366.4  | 5398.4  | 6582.2  | 7766.0  | 8948.2  | 10132.0 | 11066.3 |
| 0.0    | 37.5°  | 1420.9 | 2612.4  | 3802.4  | 4993.9  | 6183.9  | 7483.9  | 8784.0  | 10084.0 | 11384.0 | 12538.3 |
| 0.0    | 40°    | 1591.3 | 2988.9  | 4385.0  | 5782.6  | 7178.7  | 8718.9  | 10257.5 | 11797.7 | 13336.3 | 14964.8 |
| 0.0    | 42.5°  | 1887.3 | 3613.4  | 5341.0  | 7067.1  | 8793.3  | 10830.8 | 12868.4 | 14904.4 | 16941.9 | 19266.1 |
| 0.0    | 45°    | 2443.5 | 4876.2  | 7310.4  | 9743.1  | 12175.7 | 14874.9 | 17575.7 | 20274.8 | 22974.0 | 26066.8 |
| 0.0    | 47.5°  | 3805.5 | 7152.4  | 10497.7 | 13844.5 | 17189.8 | 20104.4 | 23017.4 | 25932.0 | 28845.0 | 31925.3 |
| 0.0    | 50°    | 5822.9 | 9718.3  | 13613.7 | 17507.5 | 21402.9 | 24040.1 | 26675.7 | 29312.9 | 31948.6 | 34878.6 |
| 0.0    | 52.5°  | 7282.5 | 11340.6 | 15400.2 | 19458.3 | 23516.3 | 25896.3 | 28277.9 | 30657.8 | 33037.8 | 35775.8 |
| 0.0    | 55°    | 7392.5 | 11427.4 | 15463.7 | 19498.6 | 23533.4 | 25924.2 | 28315.0 | 30705.9 | 33096.7 | 35998.9 |
| 0.0    | 57.5°  | 6545.0 | 10547.3 | 14548.0 | 18550.3 | 22551.0 | 25273.4 | 27994.3 | 30716.7 | 33437.6 | 36575.3 |
| 0.0    | 60°    | 5567.3 | 9571.1  | 13573.4 | 17577.2 | 21579.5 | 24715.6 | 27853.3 | 30989.4 | 34125.6 | 37064.9 |
| 0.0    | 62.5°  | 4343.2 | 8461.7  | 12581.7 | 16700.2 | 20818.7 | 24002.9 | 27187.0 | 30369.6 | 33553.8 | 35758.7 |
| 0.0    | 65°    | 3236.8 | 7236.0  | 11235.2 | 15232.9 | 19232.0 | 21782.5 | 24332.9 | 26881.8 | 29432.2 | 30797.3 |
| 0.0    | 67.5°  | 2339.7 | 5788.8  | 9236.4  | 12685.5 | 16133.1 | 17958.4 | 19783.7 | 21607.4 | 23432.7 | 24477.0 |
|        | 70°    | 1582.0 | 3971.3  | 6359.0  | 8748.3  | 11136.1 | 12635.9 | 14137.4 | 15637.3 | 17137.2 | 18547.2 |
|        | 72.5°  | 1095.5 | 2437.3  | 3780.7  | 5122.6  | 6464.4  | 7973.6  | 9481.2  | 10990.4 | 12498.0 | 13990.2 |
|        | 75°    | 726.7  | 1337.2  | 1949.2  | 2559.7  | 3170.2  | 4287.4  | 5406.1  | 6523.3  | 7640.4  | 8529.8  |
|        | 77.5°  | 516.0  | 698.8   | 883.2   | 1066.0  | 1248.9  | 1458.1  | 1668.8  | 1878.0  | 2087.1  | 2404.8  |
|        | 80°    | 244.8  | 268.1   | 291.3   | 313.0   | 336.2   | 412.2   | 488.1   | 564.0   | 639.9   | 720.5   |
|        | 82.5°  | 116.2  | 125.5   | 134.8   | 142.6   | 151.8   | 159.6   | 167.3   | 175.1   | 182.8   | 175.1   |
|        | 85°    | 31.0   | 31.0    | 32.5    | 32.5    | 32.5    | 32.5    | 32.5    | 32.5    | 32.5    | 31.0    |
|        | 87.5°  | 13.9   | 13.9    | 13.9    | 13.9    | 13.9    | 13.9    | 13.9    | 12.4    | 12.4    | 10.8    |
|        | 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 89.9    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.3   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 111.6   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125.5   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 144.1   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 178.2   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 269.6   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 646.1   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1676.5  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3556.0  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5486.7  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7443.7  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9013.3  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10545.7 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12000.7 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13694.2 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16593.3 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21590.3 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29159.5 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35005.7 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37808.7 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38513.7 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38902.6 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39713.0 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40002.7 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37965.2 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32163.9 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25522.9 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19955.6 |        |      |        |      |        |      |        |      |        |      |        |
| 15482.3 |        |      |        |      |        |      |        |      |        |      |        |
| 9419.2  |        |      |        |      |        |      |        |      |        |      |        |
| 2722.4  |        |      |        |      |        |      |        |      |        |      |        |
| 801.1   |        |      |        |      |        |      |        |      |        |      |        |
| 165.8   |        |      |        |      |        |      |        |      |        |      |        |
| 29.4    |        |      |        |      |        |      |        |      |        |      |        |
| 10.8    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    |
| 0.0  | 2.5°   | 100.7   | 99.2    | 97.6    | 96.1    | 94.5    | 91.4    | 91.4    | 89.9    | 89.9    |
| 0.0  | 5°     | 110.0   | 108.5   | 106.9   | 105.4   | 105.4   | 103.8   | 102.3   | 102.3   | 100.7   |
| 0.0  | 7.5°   | 125.5   | 124.0   | 122.4   | 120.9   | 120.9   | 119.3   | 119.3   | 117.8   | 117.8   |
| 0.0  | 10°    | 144.1   | 144.1   | 144.1   | 144.1   | 144.1   | 142.6   | 142.6   | 142.6   | 141.0   |
| 0.0  | 12.5°  | 181.3   | 182.8   | 185.9   | 189.0   | 193.7   | 193.7   | 193.7   | 192.1   | 192.1   |
| 0.0  | 15°    | 286.7   | 303.7   | 316.1   | 328.5   | 339.3   | 364.1   | 361.0   | 356.4   | 353.3   |
| 0.0  | 17.5°  | 725.2   | 802.6   | 844.5   | 884.7   | 926.6   | 1041.2  | 1022.7  | 1004.1  | 987.0   |
| 0.0  | 20°    | 1879.5  | 2082.5  | 2217.3  | 2352.1  | 2488.5  | 2703.8  | 2651.1  | 2598.5  | 2545.8  |
| 0.0  | 22.5°  | 4020.9  | 4487.3  | 4690.3  | 4893.2  | 5094.7  | 5355.0  | 5186.1  | 5017.2  | 4849.8  |
| 0.0  | 25°    | 6091.0  | 6696.8  | 7039.3  | 7381.7  | 7722.6  | 7871.3  | 7651.3  | 7429.7  | 7209.7  |
| 0.0  | 27.5°  | 8128.5  | 8813.4  | 9115.5  | 9416.1  | 9718.3  | 10029.7 | 9757.0  | 9482.8  | 9210.1  |
| 0.0  | 30°    | 9761.7  | 10510.1 | 10837.0 | 11162.4 | 11489.3 | 11706.3 | 11424.3 | 11140.7 | 10858.7 |
| 0.0  | 32.5°  | 11363.8 | 12181.9 | 12539.9 | 12897.8 | 13254.2 | 13565.6 | 13218.5 | 12869.9 | 12522.8 |
| 0.0  | 35°    | 12933.4 | 13867.8 | 14360.5 | 14853.2 | 15346.0 | 15635.7 | 15223.6 | 14809.9 | 14397.7 |
| 0.0  | 37.5°  | 14848.6 | 16002.9 | 16554.6 | 17106.2 | 17657.8 | 18186.2 | 17732.2 | 17276.6 | 16822.6 |
| 0.0  | 40°    | 18221.8 | 19850.3 | 20696.3 | 21543.9 | 22389.9 | 23071.6 | 22498.3 | 21925.0 | 21351.7 |
| 0.0  | 42.5°  | 23914.5 | 26238.8 | 27455.1 | 28669.9 | 29886.2 | 30950.7 | 30348.0 | 29745.2 | 29142.5 |
| 0.0  | 45°    | 32252.3 | 35345.0 | 36827.8 | 38309.1 | 39792.0 | 40569.8 | 39702.1 | 38832.9 | 37965.2 |
| 0.0  | 47.5°  | 38084.5 | 41164.8 | 42485.0 | 43805.1 | 45125.3 | 46013.1 | 44951.7 | 43890.3 | 42830.5 |
| 0.0  | 50°    | 40737.2 | 43667.2 | 44992.0 | 46315.3 | 47640.1 | 48345.1 | 47119.4 | 45892.3 | 44666.6 |
| 0.0  | 52.5°  | 41250.0 | 43988.0 | 45568.4 | 47150.4 | 48730.9 | 49673.0 | 48225.8 | 46777.0 | 45329.8 |
| 0.0  | 55°    | 41804.7 | 44706.9 | 46539.9 | 48374.5 | 50207.5 | 51512.2 | 49875.9 | 48238.2 | 46601.9 |
| 0.0  | 57.5°  | 42849.1 | 45986.8 | 47815.1 | 49642.0 | 51470.4 | 52578.2 | 50937.3 | 49294.9 | 47654.0 |
| 0.0  | 60°    | 42942.1 | 45879.9 | 47451.0 | 49023.7 | 50594.9 | 51292.2 | 49722.5 | 48151.4 | 46581.8 |
| 0.0  | 62.5°  | 40170.1 | 42375.0 | 43465.8 | 44556.6 | 45647.4 | 46405.1 | 44767.3 | 43128.0 | 41490.2 |
| 0.0  | 65°    | 33529.0 | 34894.1 | 35763.4 | 36632.6 | 37501.9 | 38405.2 | 36905.3 | 35405.4 | 33905.5 |
| 0.0  | 67.5°  | 26567.2 | 27611.6 | 28756.6 | 29901.7 | 31046.8 | 32012.1 | 30811.2 | 29608.9 | 28408.0 |
|      | 70°    | 21365.7 | 22774.1 | 24061.7 | 25349.4 | 26637.0 | 27427.2 | 26221.7 | 25014.7 | 23809.2 |
|      | 72.5°  | 16974.5 | 18466.6 | 19541.9 | 20615.7 | 21691.1 | 21884.7 | 20998.4 | 20112.1 | 19227.4 |
|      | 75°    | 10307.1 | 11196.5 | 11218.2 | 11238.3 | 11260.0 | 11444.4 | 10709.9 | 9975.5  | 9242.6  |
|      | 77.5°  | 3040.1  | 3357.7  | 3619.6  | 3879.9  | 4141.7  | 4457.8  | 4188.2  | 3917.1  | 3647.5  |
|      | 80°    | 880.1   | 960.7   | 1028.8  | 1095.5  | 1163.7  | 1123.4  | 1059.8  | 996.3   | 932.8   |
|      | 82.5°  | 158.0   | 148.7   | 147.2   | 145.7   | 145.7   | 137.9   | 125.5   | 113.1   | 100.7   |
|      | 85°    | 27.9    | 26.3    | 24.8    | 23.2    | 21.7    | 20.1    | 17.0    | 15.5    | 12.4    |
|      | 87.5°  | 9.3     | 7.7     | 6.2     | 4.6     | 4.6     | 1.5     | 1.5     | 1.5     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    | 89.9    |
| 0.0  | 0.0    | 2.5°   | 88.3    | 86.8    | 86.8    | 86.8    | 86.8    | 85.2    | 85.2    | 85.2    | 85.2    |
| 0.0  | 0.0    | 5°     | 97.6    | 97.6    | 96.1    | 96.1    | 94.5    | 94.5    | 93.0    | 93.0    | 91.4    |
| 0.0  | 0.0    | 7.5°   | 114.7   | 113.1   | 111.6   | 110.0   | 108.5   | 105.4   | 103.8   | 102.3   | 102.3   |
| 0.0  | 0.0    | 10°    | 137.9   | 134.8   | 133.3   | 130.2   | 128.6   | 125.5   | 122.4   | 119.3   | 116.2   |
| 0.0  | 0.0    | 12.5°  | 181.3   | 175.1   | 170.4   | 164.2   | 158.0   | 153.4   | 147.2   | 142.6   | 136.4   |
| 0.0  | 0.0    | 15°    | 314.5   | 299.0   | 282.0   | 261.9   | 240.2   | 220.0   | 198.3   | 185.9   | 172.0   |
| 0.0  | 0.0    | 17.5°  | 804.2   | 723.6   | 641.5   | 574.9   | 508.2   | 443.1   | 376.5   | 328.5   | 280.5   |
| 0.0  | 0.0    | 20°    | 2046.9  | 1823.7  | 1600.6  | 1380.6  | 1159.0  | 939.0   | 717.4   | 605.8   | 494.3   |
| 0.0  | 0.0    | 22.5°  | 3852.0  | 3438.3  | 3023.0  | 2621.7  | 2218.8  | 1817.5  | 1416.2  | 1163.7  | 912.6   |
| 0.0  | 0.0    | 25°    | 5945.3  | 5424.7  | 4904.1  | 4244.0  | 3582.4  | 2922.3  | 2262.2  | 1851.6  | 1441.0  |
| 0.0  | 0.0    | 27.5°  | 7736.5  | 7136.9  | 6537.2  | 5734.6  | 4932.0  | 4129.3  | 3326.7  | 2714.7  | 2104.2  |
| 0.0  | 0.0    | 30°    | 9287.5  | 8643.0  | 7998.4  | 7064.0  | 6129.7  | 5195.4  | 4261.0  | 3495.6  | 2730.2  |
| 0.0  | 0.0    | 32.5°  | 10632.5 | 9860.8  | 9089.2  | 8125.4  | 7161.7  | 6197.9  | 5234.1  | 4295.1  | 3356.2  |
| 0.0  | 0.0    | 35°    | 12183.5 | 11283.3 | 10381.5 | 9312.3  | 8241.6  | 7172.5  | 6103.4  | 5043.5  | 3982.1  |
| 0.0  | 0.0    | 37.5°  | 14154.4 | 13049.7 | 11943.3 | 10751.8 | 9560.2  | 8370.2  | 7178.7  | 5967.0  | 4755.3  |
| 0.0  | 0.0    | 40°    | 17927.4 | 16501.9 | 15076.4 | 13562.5 | 12047.1 | 10533.3 | 9019.5  | 7532.0  | 6044.5  |
| 0.0  | 0.0    | 42.5°  | 24687.7 | 22761.7 | 20835.7 | 18821.4 | 16805.6 | 14791.3 | 12775.4 | 10677.4 | 8577.9  |
| 0.0  | 0.0    | 45°    | 32317.3 | 29928.0 | 27537.2 | 25276.5 | 23014.3 | 20753.6 | 18492.9 | 15614.0 | 12735.1 |
| 0.0  | 0.0    | 47.5°  | 36607.8 | 34027.9 | 31448.1 | 29308.3 | 27168.4 | 25028.6 | 22888.8 | 19785.2 | 16681.6 |
| 0.0  | 0.0    | 50°    | 38186.7 | 35560.4 | 32934.0 | 30964.6 | 28993.7 | 27024.3 | 25053.4 | 21945.2 | 18835.4 |
| 0.0  | 0.0    | 52.5°  | 38523.0 | 35843.9 | 33164.9 | 31183.1 | 29201.3 | 27221.1 | 25239.3 | 22151.2 | 19063.2 |
| 0.0  | 0.0    | 55°    | 39214.0 | 36339.8 | 33463.9 | 31204.8 | 28945.7 | 26686.6 | 24427.4 | 21289.7 | 18152.1 |
| 0.0  | 0.0    | 57.5°  | 40117.4 | 37170.3 | 34223.2 | 31649.5 | 29075.8 | 26503.7 | 23930.0 | 20499.5 | 17069.0 |
| 0.0  | 0.0    | 60°    | 39880.3 | 37315.9 | 34750.0 | 31993.5 | 29235.4 | 26478.9 | 23720.9 | 19947.9 | 16173.4 |
| 0.0  | 0.0    | 62.5°  | 35764.9 | 33722.7 | 31679.0 | 29412.1 | 27143.6 | 24876.8 | 22609.9 | 18725.4 | 14840.8 |
| 0.0  | 0.0    | 65°    | 29422.9 | 27932.3 | 26441.7 | 24618.0 | 22792.7 | 20969.0 | 19145.3 | 15662.1 | 12180.4 |
| 0.0  | 0.0    | 67.5°  | 23846.4 | 22166.7 | 20485.6 | 19032.2 | 17577.2 | 16123.8 | 14668.8 | 11927.8 | 9186.8  |
|      |        | 70°    | 18945.4 | 17118.6 | 15290.2 | 13870.9 | 12450.0 | 11030.7 | 9611.4  | 7789.2  | 5968.6  |
|      |        | 72.5°  | 15045.4 | 13398.3 | 11751.2 | 10237.4 | 8722.0  | 7208.1  | 5692.8  | 4615.9  | 3539.0  |
|      |        | 75°    | 7191.1  | 6532.6  | 5874.0  | 5082.3  | 4290.5  | 3498.7  | 2706.9  | 2237.4  | 1769.5  |
|      |        | 77.5°  | 2665.1  | 2310.3  | 1953.9  | 1631.6  | 1309.3  | 988.6   | 666.3   | 610.5   | 554.7   |
|      |        | 80°    | 689.5   | 601.2   | 511.3   | 447.8   | 382.7   | 319.2   | 255.7   | 230.9   | 207.6   |
|      |        | 82.5°  | 79.0    | 72.8    | 68.2    | 65.1    | 60.4    | 57.3    | 52.7    | 48.0    | 43.4    |
|      |        | 85°    | 4.6     | 3.1     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 89.9   | 89.9   |
| 0.0    | 0.0  | 2.5°   | 83.7   | 82.1   |
| 0.0    | 0.0  | 5°     | 88.3   | 86.8   |
| 0.0    | 0.0  | 7.5°   | 97.6   | 94.5   |
| 0.0    | 0.0  | 10°    | 106.9  | 103.8  |
| 0.0    | 0.0  | 12.5°  | 120.9  | 116.2  |
| 0.0    | 0.0  | 15°    | 136.4  | 127.1  |
| 0.0    | 0.0  | 17.5°  | 162.7  | 142.6  |
| 0.0    | 0.0  | 20°    | 220.0  | 168.9  |
| 0.0    | 0.0  | 22.5°  | 309.9  | 210.7  |
| 0.0    | 0.0  | 25°    | 455.5  | 291.3  |
| 0.0    | 0.0  | 27.5°  | 633.7  | 387.4  |
| 0.0    | 0.0  | 30°    | 842.9  | 485.0  |
| 0.0    | 0.0  | 32.5°  | 1027.3 | 578.0  |
| 0.0    | 0.0  | 35°    | 1267.5 | 672.5  |
| 0.0    | 0.0  | 37.5°  | 1563.4 | 793.3  |
| 0.0    | 0.0  | 40°    | 2022.1 | 976.2  |
| 0.0    | 0.0  | 42.5°  | 2847.9 | 1314.0 |
| 0.0    | 0.0  | 45°    | 4625.2 | 2271.5 |
| 0.0    | 0.0  | 47.5°  | 7116.7 | 3757.5 |
| 0.0    | 0.0  | 50°    | 8706.5 | 4795.6 |
| 0.0    | 0.0  | 52.5°  | 8836.6 | 4787.9 |
| 0.0    | 0.0  | 55°    | 8066.6 | 4256.4 |
| 0.0    | 0.0  | 57.5°  | 6882.8 | 3557.6 |
| 0.0    | 0.0  | 60°    | 5720.6 | 2813.8 |
| 0.0    | 0.0  | 62.5°  | 4507.4 | 1943.0 |
| 0.0    | 0.0  | 65°    | 3294.2 | 1374.4 |
| 0.0    | 0.0  | 67.5°  | 2366.0 | 1027.3 |
|        |      | 70°    | 1555.7 | 787.1  |
|        |      | 72.5°  | 1013.4 | 641.5  |
|        |      | 75°    | 681.8  | 531.5  |
|        |      | 77.5°  | 398.2  | 353.3  |
|        |      | 80°    | 141.0  | 124.0  |
|        |      | 82.5°  | 26.3   | 18.6   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1064499

CATALOG NUMBER: GLAN-SA4C-740-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ


Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-740-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 3949     | CRI (Ra): | 70.7 |      |       |
| CIE u':                   | 0.2248   | R1:       | 68.0 | R9:  | -36.7 |
| CIE v':                   | 0.5053   | R2:       | 76.0 | R10: | 45.1  |
| Duv:                      | 0.0022   | R3:       | 84.3 | R11: | 70.7  |
| CIE x:                    | 0.3844   | R4:       | 72.0 | R12: | 47.1  |
| CIE y:                    | 0.3840   | R5:       | 68.6 | R13: | 68.5  |
| CIE z:                    | 0.2316   | R6:       | 68.3 | R14: | 91.1  |
| Peak Wavelength (nm):     | 440      | R7:       | 77.9 | R15: | 58.7  |
| Dominant Wavelength (nm): | 578      | R8:       | 50.3 |      |       |
| Purity:                   | 30.60026 |           |      |      |       |
| Rf:                       | 71.8     |           |      |      |       |
| Rg:                       | 96.5     |           |      |      |       |



### Test Conditions


Stabilization Time: 34M  
 Operation Time: 1H 34M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-1


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-1

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 0                             | NR                             | 490               | 139                           | NR                             | 620               | 607                           | NR                             | 750               | 15                            | NR                             | 880               | 0                             | NR                             |
| 365               | 0                             | NR                             | 495               | 198                           | NR                             | 625               | 554                           | NR                             | 755               | 13                            | NR                             | 885               | 0                             | NR                             |
| 370               | 0                             | NR                             | 500               | 267                           | NR                             | 630               | 504                           | NR                             | 760               | 11                            | NR                             | 890               | 0                             | NR                             |
| 375               | 0                             | NR                             | 505               | 343                           | NR                             | 635               | 452                           | NR                             | 765               | 10                            | NR                             | 895               | 0                             | NR                             |
| 380               | 0                             | NR                             | 510               | 410                           | NR                             | 640               | 403                           | NR                             | 770               | 8                             | NR                             | 900               | 0                             | NR                             |
| 385               | 2                             | NR                             | 515               | 470                           | NR                             | 645               | 357                           | NR                             | 775               | 7                             | NR                             | 905               | 0                             | NR                             |
| 390               | 4                             | NR                             | 520               | 516                           | NR                             | 650               | 314                           | NR                             | 780               | 6                             | NR                             | 910               | 0                             | NR                             |
| 395               | 7                             | NR                             | 525               | 550                           | NR                             | 655               | 275                           | NR                             | 785               | 5                             | NR                             | 915               | 0                             | NR                             |
| 400               | 10                            | NR                             | 530               | 578                           | NR                             | 660               | 240                           | NR                             | 790               | 5                             | NR                             | 920               | 0                             | NR                             |
| 405               | 17                            | NR                             | 535               | 601                           | NR                             | 665               | 208                           | NR                             | 795               | 4                             | NR                             | 925               | 0                             | NR                             |
| 410               | 35                            | NR                             | 540               | 620                           | NR                             | 670               | 179                           | NR                             | 800               | 4                             | NR                             | 930               | 0                             | NR                             |
| 415               | 70                            | NR                             | 545               | 641                           | NR                             | 675               | 155                           | NR                             | 805               | 3                             | NR                             | 935               | 0                             | NR                             |
| 420               | 147                           | NR                             | 550               | 664                           | NR                             | 680               | 133                           | NR                             | 810               | 3                             | NR                             | 940               | 0                             | NR                             |
| 425               | 285                           | NR                             | 555               | 689                           | NR                             | 685               | 114                           | NR                             | 815               | 2                             | NR                             | 945               | 0                             | NR                             |
| 430               | 487                           | NR                             | 560               | 715                           | NR                             | 690               | 98                            | NR                             | 820               | 2                             | NR                             | 950               | 0                             | NR                             |
| 435               | 787                           | NR                             | 565               | 743                           | NR                             | 695               | 84                            | NR                             | 825               | 2                             | NR                             | 955               | 0                             | NR                             |
| 440               | 1000                          | NR                             | 570               | 771                           | NR                             | 700               | 72                            | NR                             | 830               | 2                             | NR                             | 960               | 0                             | NR                             |
| 445               | 783                           | NR                             | 575               | 794                           | NR                             | 705               | 61                            | NR                             | 835               | 1                             | NR                             | 965               | 0                             | NR                             |
| 450               | 417                           | NR                             | 580               | 811                           | NR                             | 710               | 52                            | NR                             | 840               | 1                             | NR                             | 970               | 0                             | NR                             |
| 455               | 261                           | NR                             | 585               | 817                           | NR                             | 715               | 45                            | NR                             | 845               | 1                             | NR                             | 975               | 0                             | NR                             |
| 460               | 167                           | NR                             | 590               | 815                           | NR                             | 720               | 39                            | NR                             | 850               | 1                             | NR                             | 980               | 0                             | NR                             |
| 465               | 104                           | NR                             | 595               | 801                           | NR                             | 725               | 33                            | NR                             | 855               | 1                             | NR                             | 985               | 0                             | NR                             |
| 470               | 79                            | NR                             | 600               | 777                           | NR                             | 730               | 28                            | NR                             | 860               | 1                             | NR                             | 990               | 0                             | NR                             |
| 475               | 73                            | NR                             | 605               | 744                           | NR                             | 735               | 24                            | NR                             | 865               | 1                             | NR                             | 995               | 0                             | NR                             |
| 480               | 76                            | NR                             | 610               | 704                           | NR                             | 740               | 21                            | NR                             | 870               | 1                             | NR                             | 1000              | 0                             | NR                             |
| 485               | 98                            | NR                             | 615               | 657                           | NR                             | 745               | 18                            | NR                             | 875               | 1                             | NR                             |                   |                               |                                |

REPORT NUMBER: SP1-2407-184-1

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR


S/P: 1.47

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 139                         | NR               | 620       | 607                         | NR               | 750       | 15                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 198                         | NR               | 625       | 554                         | NR               | 755       | 13                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 267                         | NR               | 630       | 504                         | NR               | 760       | 11                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 343                         | NR               | 635       | 452                         | NR               | 765       | 10                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 410                         | NR               | 640       | 403                         | NR               | 770       | 8                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 470                         | NR               | 645       | 357                         | NR               | 775       | 7                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 516                         | NR               | 650       | 314                         | NR               | 780       | 6                           | NR               | 910       | 0                           | NR               |
| 395       | 7                           | NR               | 525       | 550                         | NR               | 655       | 275                         | NR               | 785       | 5                           | NR               | 915       | 0                           | NR               |
| 400       | 10                          | NR               | 530       | 578                         | NR               | 660       | 240                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 17                          | NR               | 535       | 601                         | NR               | 665       | 208                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 35                          | NR               | 540       | 620                         | NR               | 670       | 179                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 70                          | NR               | 545       | 641                         | NR               | 675       | 155                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 147                         | NR               | 550       | 664                         | NR               | 680       | 133                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 285                         | NR               | 555       | 689                         | NR               | 685       | 114                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 487                         | NR               | 560       | 715                         | NR               | 690       | 98                          | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 787                         | NR               | 565       | 743                         | NR               | 695       | 84                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 1000                        | NR               | 570       | 771                         | NR               | 700       | 72                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 783                         | NR               | 575       | 794                         | NR               | 705       | 61                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 417                         | NR               | 580       | 811                         | NR               | 710       | 52                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 261                         | NR               | 585       | 817                         | NR               | 715       | 45                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 167                         | NR               | 590       | 815                         | NR               | 720       | 39                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 104                         | NR               | 595       | 801                         | NR               | 725       | 33                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 79                          | NR               | 600       | 777                         | NR               | 730       | 28                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 73                          | NR               | 605       | 744                         | NR               | 735       | 24                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 704                         | NR               | 740       | 21                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 98                          | NR               | 615       | 657                         | NR               | 745       | 18                          | NR               | 875       | 1                           | NR               |           |                             |                  |



REPORT NUMBER: SP1-2407-184-1

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.78


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 139                                  | NR                             | 620               | 607                                  | NR                             | 750               | 15                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 198                                  | NR                             | 625               | 554                                  | NR                             | 755               | 13                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 267                                  | NR                             | 630               | 504                                  | NR                             | 760               | 11                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 343                                  | NR                             | 635               | 452                                  | NR                             | 765               | 10                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 410                                  | NR                             | 640               | 403                                  | NR                             | 770               | 8                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 2                                    | NR                             | 515               | 470                                  | NR                             | 645               | 357                                  | NR                             | 775               | 7                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 4                                    | NR                             | 520               | 516                                  | NR                             | 650               | 314                                  | NR                             | 780               | 6                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 7                                    | NR                             | 525               | 550                                  | NR                             | 655               | 275                                  | NR                             | 785               | 5                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 10                                   | NR                             | 530               | 578                                  | NR                             | 660               | 240                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 17                                   | NR                             | 535               | 601                                  | NR                             | 665               | 208                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 35                                   | NR                             | 540               | 620                                  | NR                             | 670               | 179                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 70                                   | NR                             | 545               | 641                                  | NR                             | 675               | 155                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 147                                  | NR                             | 550               | 664                                  | NR                             | 680               | 133                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 285                                  | NR                             | 555               | 689                                  | NR                             | 685               | 114                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 487                                  | NR                             | 560               | 715                                  | NR                             | 690               | 98                                   | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 787                                  | NR                             | 565               | 743                                  | NR                             | 695               | 84                                   | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 1000                                 | NR                             | 570               | 771                                  | NR                             | 700               | 72                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 783                                  | NR                             | 575               | 794                                  | NR                             | 705               | 61                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 417                                  | NR                             | 580               | 811                                  | NR                             | 710               | 52                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 261                                  | NR                             | 585               | 817                                  | NR                             | 715               | 45                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 167                                  | NR                             | 590               | 815                                  | NR                             | 720               | 39                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 104                                  | NR                             | 595               | 801                                  | NR                             | 725               | 33                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 79                                   | NR                             | 600               | 777                                  | NR                             | 730               | 28                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 73                                   | NR                             | 605               | 744                                  | NR                             | 735               | 24                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 76                                   | NR                             | 610               | 704                                  | NR                             | 740               | 21                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 98                                   | NR                             | 615               | 657                                  | NR                             | 745               | 18                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-1





TM-30-18

### Summary

$R_f = 71.8$   
 $R_g = 96.5$   
 $CIE R_a = 70.7$   
 $R_g = -36.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 56 | CES51 = 86 | CES76 = 48 |
| CES02 = 61 | CES27 = 79 | CES52 = 88 | CES77 = 71 |
| CES03 = 30 | CES28 = 80 | CES53 = 73 | CES78 = 52 |
| CES04 = 70 | CES29 = 49 | CES54 = 79 | CES79 = 79 |
| CES05 = 47 | CES30 = 53 | CES55 = 77 | CES80 = 77 |
| CES06 = 50 | CES31 = 55 | CES56 = 67 | CES81 = 75 |
| CES07 = 40 | CES32 = 53 | CES57 = 64 | CES82 = 90 |
| CES08 = 39 | CES33 = 59 | CES58 = 67 | CES83 = 84 |
| CES09 = 29 | CES34 = 67 | CES59 = 87 | CES84 = 89 |
| CES10 = 74 | CES35 = 82 | CES60 = 91 | CES85 = 86 |
| CES11 = 57 | CES36 = 86 | CES61 = 87 | CES86 = 71 |
| CES12 = 63 | CES37 = 76 | CES62 = 76 | CES87 = 78 |
| CES13 = 42 | CES38 = 62 | CES63 = 73 | CES88 = 76 |
| CES14 = 74 | CES39 = 91 | CES64 = 71 | CES89 = 72 |
| CES15 = 71 | CES40 = 84 | CES65 = 64 | CES90 = 72 |
| CES16 = 46 | CES41 = 81 | CES66 = 67 | CES91 = 97 |
| CES17 = 49 | CES42 = 76 | CES67 = 65 | CES92 = 66 |
| CES18 = 56 | CES43 = 71 | CES68 = 72 | CES93 = 81 |
| CES19 = 72 | CES44 = 98 | CES69 = 82 | CES94 = 55 |
| CES20 = 65 | CES45 = 80 | CES70 = 61 | CES95 = 73 |
| CES21 = 86 | CES46 = 76 | CES71 = 59 | CES96 = 78 |
| CES22 = 78 | CES47 = 71 | CES72 = 86 | CES97 = 83 |
| CES23 = 92 | CES48 = 61 | CES73 = 52 | CES98 = 72 |
| CES24 = 91 | CES49 = 76 | CES74 = 93 | CES99 = 60 |
| CES25 = 72 | CES50 = 84 | CES75 = 56 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)