

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064007

Luminaire Tested: **GLAN-SA7C-730-U-T4BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1064007  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA7C-730-U-T4BC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 7xLight Square PACKAGE  
70CRI 3000K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL  
Light Source: (98) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 38066.5 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B0 - U0 - G5

Input Watts (W): 330  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1064007

CATALOG NUMBER: GLAN-SA7C-730-U-T4BC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 39.1 fc  
Type IV - Short - N/A

REPORT NUMBER: P1064007

CATALOG NUMBER: GLAN-SA7C-730-U-T4BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064007

CATALOG NUMBER: GLAN-SA7C-730-U-T4BC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 135.3    | 0.0    | 135.3   |
|                    | % Fixture | 0.4      | 0.0    | 0.4     |
| <b>Street Side</b> | Lumens    | 37931.2  | 0.0    | 37931.2 |
|                    | % Fixture | 99.6     | 0.0    | 99.6    |
| <b>Total</b>       | Lumens    | 38066.5  | 0.0    | 38066.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 31.8    | 0.1       |
| 10°-20°   | 406.9   | 1.1       |
| 20°-30°   | 1448.9  | 3.8       |
| 30°-40°   | 3492.0  | 9.2       |
| 40°-50°   | 5844.1  | 15.4      |
| 50°-60°   | 7506.1  | 19.7      |
| 60°-70°   | 9499.0  | 25.0      |
| 70°-80°   | 8468.8  | 22.2      |
| 80°-90°   | 1368.9  | 3.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 38066.5 | 100.0     |
| 0°-180°   | 38066.5 | 100.0     |



REPORT NUMBER: P1064007


CATALOG NUMBER: GLAN-SA7C-730-U-T4BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|---------|-----------|-------------------------|------|--------|
|      |             |         |           | B                       | U    | G      |
| FL   | (0°-30°)    | 1854.9  | 4.9       |                         |      |        |
| FM   | (30°-60°)   | 16810.9 | 44.2      |                         |      |        |
| FH   | (60°-80°)   | 17902.7 | 47.0      |                         |      | G5     |
| FVH  | (80°-90°)   | 1362.7  | 3.6       |                         |      | G5     |
| BL   | (0°-30°)    | 32.7    | 0.1       | B0/110                  |      |        |
| BM   | (30°-60°)   | 31.3    | 0.1       | B0/220                  |      |        |
| BH   | (60°-80°)   | 65.0    | 0.2       | B0/110                  |      | G0/110 |
| BVH  | (80°-90°)   | 6.2     | 0.0       |                         |      | G0/10  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B0-U0-G5**

Type IV Short







LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ


Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 3000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 2985     | CRI (Ra): | 70.8 |      |       |
| CIE u':                   | 0.2504   | R1:       | 66.3 | R9:  | -43.2 |
| CIE v':                   | 0.5243   | R2:       | 80.6 | R10: | 57.6  |
| Duv:                      | 0.0019   | R3:       | 94.5 | R11: | 64.8  |
| CIE x:                    | 0.4408   | R4:       | 68.2 | R12: | 53.5  |
| CIE y:                    | 0.4101   | R5:       | 66.5 | R13: | 68.7  |
| CIE z:                    | 0.1491   | R6:       | 74.7 | R14: | 97.0  |
| Peak Wavelength (nm):     | 595      | R7:       | 76.2 | R15: | 56.4  |
| Dominant Wavelength (nm): | 582      | R8:       | 39.6 |      |       |
| Purity:                   | 55.41818 |           |      |      |       |
| Rf:                       | 73.8     |           |      |      |       |
| Rg:                       | 94.4     |           |      |      |       |



### Test Conditions


Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle








REPORT NUMBER: SP1-2407-184-4





TM-30-18

### Summary

$R_f = 73.8$   
 $R_g = 94.4$   
 $CIE R_a = 70.8$   
 $R_g = -43.2$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)