

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1062670

Luminaire Tested: **GLAN-SA6B-740-U-T3BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1062670
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA6B-740-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 6xLight Square PACKAGE
70CRI 4000K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (84) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 27974.9 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 213.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1062670

CATALOG NUMBER: GLAN-SA6B-740-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 31.4 fc
 Type III - Short - N/A

REPORT NUMBER: P1062670

CATALOG NUMBER: GLAN-SA6B-740-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1062670

CATALOG NUMBER: GLAN-SA6B-740-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	102.1	0.0	102.1
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	27872.8	0.0	27872.8
	% Fixture	99.6	0.0	99.6
Total	Lumens	27974.9	0.0	27974.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.8	0.1
10°-20°	321.6	1.1
20°-30°	1159.0	4.1
30°-40°	2651.8	9.5
40°-50°	4472.6	16.0
50°-60°	7380.9	26.4
60°-70°	8249.2	29.5
70°-80°	3405.9	12.2
80°-90°	307.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	27974.9	100.0
0°-180°	27974.9	100.0



REPORT NUMBER: P1062670


CATALOG NUMBER: GLAN-SA6B-740-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1480.8	5.3			
FM	(30°-60°)	14480.9	51.8			
FH	(60°-80°)	11608.3	41.5			G4/12000
FVH	(80°-90°)	302.8	1.1			G3/500
BL	(0°-30°)	26.6	0.1	B0/110		
BM	(30°-60°)	24.5	0.1	B0/220		
BH	(60°-80°)	46.8	0.2	B0/110		G0/110
BVH	(80°-90°)	4.2	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type III Short



REPORT NUMBER: P1062670

CATALOG NUMBER: GLAN-SA6B-740-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9
2.5°	219.5	226.8	219.5	219.5	219.5	212.2	212.2	204.9	204.9	197.5	190.2
5°	321.9	321.9	300.0	285.3	270.7	263.4	256.1	241.4	226.8	212.2	197.5
7.5°	717.0	717.0	651.2	563.4	446.3	380.5	365.8	300.0	256.1	226.8	197.5
10°	1712.1	1712.1	1565.8	1324.3	1024.3	760.9	680.4	431.7	307.3	241.4	204.9
12.5°	2846.2	2882.7	2699.8	2392.5	1946.2	1485.3	1324.3	790.2	409.7	263.4	204.9
15°	3863.2	3775.4	3724.1	3431.5	3007.1	2458.4	2253.5	1331.6	592.6	300.0	204.9
17.5°	4550.9	4550.9	4477.8	4280.2	3892.4	3409.5	3241.3	2151.1	958.5	343.9	212.2
20°	5355.7	5355.7	5224.0	5085.0	4741.2	4331.4	4170.5	3058.3	1485.3	439.0	212.2
22.5°	6328.9	6343.5	6197.2	5948.4	5619.1	5165.5	5026.5	3899.7	2151.1	585.3	219.5
25°	7514.1	7528.8	7316.6	7082.5	6577.6	6087.4	5875.2	4865.5	2963.2	819.5	219.5
27.5°	8823.8	8926.2	8611.6	8209.2	7675.1	7060.5	6899.5	5736.2	3768.0	1156.0	234.1
30°	10455.4	10455.4	10038.4	9475.0	8897.0	8136.1	7931.2	6650.8	4624.1	1602.3	248.8
32.5°	11860.2	11750.5	11216.3	10623.7	10009.1	9299.4	9079.9	7609.3	5502.1	2158.4	278.0
35°	12935.7	12840.6	12182.1	11545.6	11011.5	10360.3	10096.9	8648.2	6431.3	2787.6	321.9
37.5°	13857.6	13821.0	12928.4	12130.9	11779.7	11209.0	10974.9	9628.6	7345.9	3468.1	373.1
40°	14867.3	14750.3	13799.1	12811.4	12284.6	11823.6	11611.4	10418.8	8223.9	4265.6	446.3
42.5°	15730.7	15591.7	14735.6	13769.8	12869.9	12248.0	12043.1	11084.6	9079.9	5063.1	541.4
45°	16689.2	16616.0	15752.6	15021.0	13821.0	12826.0	12555.3	11618.8	9862.8	6014.2	665.8
47.5°	18130.5	17998.8	17194.0	16594.0	15203.9	13704.0	13316.2	12167.5	10616.4	6950.8	856.0
50°	19806.0	19718.2	19242.6	18767.1	17384.2	15203.9	14742.9	12957.7	11457.8	8062.9	1104.8
52.5°	21174.2	21159.6	21218.1	21225.4	20179.2	17728.1	17040.3	14230.8	12423.6	9160.4	1456.0
55°	21145.0	21210.8	21854.7	22593.6	22674.1	21174.2	20508.4	16374.5	13682.0	10513.9	1946.2
57.5°	20354.8	20303.6	20984.0	22096.1	22879.0	23040.0	22930.2	19703.6	15577.0	12145.5	2699.8
58°	20098.7	20054.8	20698.6	21832.7	22732.7	23164.3	23054.6	20457.2	16001.4	12379.7	2904.7
60°	19169.5	19176.8	19557.3	20588.9	21488.8	22513.2	22615.6	22608.3	18115.9	13945.4	3936.3
62.5°	17940.3	17881.8	18233.0	19074.4	19864.6	20552.3	20727.9	22754.6	21210.8	15935.5	5904.5
65°	16242.8	16155.0	16528.2	17479.3	18328.1	18774.4	18781.7	20793.8	22666.8	18072.0	8714.1
67.5°	13089.4	13016.2	13762.5	14984.4	16294.1	16879.4	17142.8	18042.7	21437.6	19520.7	10323.7
70°	8019.0	8172.6	9211.6	11128.5	13367.4	14443.0	14838.1	15116.1	18254.9	19301.2	8633.6
72.5°	3702.2	3519.3	4404.6	5743.5	8297.0	10689.5	11099.3	12189.4	14472.2	16755.0	6438.6
75°	1726.7	1660.9	1865.7	2509.6	3760.7	5772.8	6519.1	9731.1	11099.3	11655.3	4646.0
77.5°	885.3	892.6	1060.9	1141.4	1551.1	2670.6	3065.7	6402.0	8136.1	6504.5	3116.9
80°	387.8	402.4	409.7	446.3	629.2	1031.6	1163.3	2970.5	5560.6	3314.4	1704.8
82.5°	248.8	256.1	256.1	256.1	300.0	409.7	468.3	1192.6	2773.0	1646.2	526.8
85°	131.7	131.7	146.3	182.9	212.2	248.8	263.4	380.5	914.6	490.2	124.4
87.5°	73.2	80.5	87.8	109.7	139.0	168.3	182.9	263.4	351.2	336.6	29.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1062670

CATALOG NUMBER: GLAN-SA6B-740-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9	182.9
2.5°	190.2	182.9	175.6	168.3	161.0	153.6	153.6	153.6	153.6	153.6	153.6
5°	182.9	175.6	168.3	153.6	139.0	131.7	124.4	117.1	117.1	117.1	117.1
7.5°	182.9	175.6	153.6	139.0	124.4	109.7	95.1	95.1	95.1	95.1	95.1
10°	182.9	168.3	146.3	124.4	102.4	87.8	80.5	73.2	73.2	73.2	73.2
12.5°	182.9	161.0	139.0	109.7	87.8	73.2	65.8	58.5	58.5	58.5	58.5
15°	182.9	161.0	131.7	102.4	80.5	58.5	51.2	43.9	43.9	43.9	43.9
17.5°	175.6	153.6	124.4	87.8	65.8	43.9	36.6	29.3	29.3	36.6	36.6
20°	168.3	146.3	109.7	73.2	51.2	36.6	21.9	21.9	21.9	21.9	21.9
22.5°	168.3	146.3	102.4	65.8	43.9	21.9	14.6	14.6	14.6	14.6	21.9
25°	168.3	139.0	87.8	51.2	29.3	14.6	7.3	7.3	7.3	7.3	7.3
27.5°	168.3	139.0	80.5	43.9	21.9	14.6	7.3	0.0	0.0	0.0	0.0
30°	161.0	131.7	73.2	36.6	14.6	7.3	0.0	0.0	0.0	0.0	0.0
32.5°	161.0	124.4	58.5	29.3	14.6	7.3	0.0	0.0	0.0	0.0	0.0
35°	168.3	117.1	51.2	21.9	7.3	0.0	0.0	0.0	0.0	0.0	7.3
37.5°	175.6	109.7	43.9	14.6	7.3	0.0	0.0	0.0	0.0	0.0	0.0
40°	182.9	102.4	43.9	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	197.5	102.4	36.6	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	212.2	102.4	29.3	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	241.4	109.7	29.3	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	263.4	117.1	21.9	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	292.7	109.7	21.9	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	329.2	109.7	21.9	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	358.5	102.4	21.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	373.1	95.1	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	446.3	87.8	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	695.1	73.2	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1412.1	65.8	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2634.0	58.5	14.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2948.6	65.8	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1858.4	51.2	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	980.4	51.2	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	490.2	51.2	7.3	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	226.8	36.6	7.3	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	95.1	21.9	14.6	7.3	7.3	0.0	0.0	0.0	0.0	0.0	0.0
85°	43.9	21.9	14.6	14.6	7.3	7.3	0.0	0.0	0.0	0.0	0.0
87.5°	21.9	21.9	21.9	14.6	14.6	7.3	7.3	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-740-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949	CRI (Ra):	70.7		
CIE u':	0.2248	R1:	68.0	R9:	-36.7
CIE v':	0.5053	R2:	76.0	R10:	45.1
Duv:	0.0022	R3:	84.3	R11:	70.7
CIE x:	0.3844	R4:	72.0	R12:	47.1
CIE y:	0.3840	R5:	68.6	R13:	68.5
CIE z:	0.2316	R6:	68.3	R14:	91.1
Peak Wavelength (nm):	440	R7:	77.9	R15:	58.7
Dominant Wavelength (nm):	578	R8:	50.3		
Purity:	30.60026				
Rf:	71.8				
Rg:	96.5				



Test Conditions

Stabilization Time: 34M
 Operation Time: 1H 34M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.47

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength

Melanopic Lumens: NR
M/P: 2.78

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

TM-30-18

Summary

$R_f = 71.8$
 $R_g = 96.5$
 $CIE R_a = 70.7$
 $R_g = -36.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)