

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063411

Luminaire Tested: **GLAN-SA2C-735-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1063411
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA2C-735-U-T2BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 2xLight Square PACKAGE
70CRI 3500K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (28) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11144.9 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 96.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1063411

CATALOG NUMBER: GLAN-SA2C-735-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 14.7 fc
 Type II - Short - N/A

REPORT NUMBER: P1063411

CATALOG NUMBER: GLAN-SA2C-735-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1063411

CATALOG NUMBER: GLAN-SA2C-735-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	47.6	0.0	47.6
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	11097.3	0.0	11097.3
	% Fixture	99.6	0.0	99.6
Total	Lumens	11144.9	0.0	11144.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.7	0.1
10°-20°	91.6	0.8
20°-30°	328.9	3.0
30°-40°	875.7	7.9
40°-50°	2300.4	20.6
50°-60°	3563.7	32.0
60°-70°	2988.1	26.8
70°-80°	879.3	7.9
80°-90°	108.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11144.9	100.0
0°-180°	11144.9	100.0



REPORT NUMBER: P1063411


CATALOG NUMBER: GLAN-SA2C-735-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	418.5	3.8			
FM	(30°-60°)	6721.6	60.3			
FH	(60°-80°)	3850.7	34.6			G2/5000
FVH	(80°-90°)	106.5	1.0			G2/225
BL	(0°-30°)	10.7	0.1	B0/110		
BM	(30°-60°)	18.1	0.2	B0/220		
BH	(60°-80°)	16.8	0.2	B0/110		G0/110
BVH	(80°-90°)	2.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short



REPORT NUMBER: P1063411

CATALOG NUMBER: GLAN-SA2C-735-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2
2.5°	82.8	83.6	82.0	79.0	76.7	76.7	75.9	73.6	73.6	71.3	69.8
5°	115.8	114.2	111.2	105.0	99.7	94.3	88.9	83.6	82.8	75.9	71.3
7.5°	189.4	190.9	180.9	161.8	145.7	125.0	105.8	94.3	92.8	81.3	72.1
10°	415.5	404.0	381.0	306.7	252.2	190.1	141.1	109.6	108.1	87.4	73.6
12.5°	757.4	748.2	706.1	629.4	489.1	340.4	206.2	135.7	131.1	92.8	74.4
15°	1091.7	1077.1	1054.1	976.7	812.6	610.2	337.3	185.5	173.3	100.4	73.6
17.5°	1304.8	1307.1	1286.4	1253.5	1147.7	903.1	582.7	276.8	253.0	114.2	72.1
20°	1491.1	1485.8	1497.3	1479.6	1405.3	1227.4	847.9	438.5	397.9	136.5	72.8
22.5°	1705.8	1718.8	1727.3	1723.4	1641.4	1489.6	1149.2	656.2	604.9	177.1	75.1
25°	1993.3	1991.7	1992.5	1982.5	1902.8	1734.2	1451.3	926.9	874.7	243.0	80.5
27.5°	2294.6	2303.8	2307.6	2271.6	2167.3	2001.7	1731.1	1222.8	1161.5	348.8	87.4
30°	2706.3	2698.6	2681.0	2607.4	2480.9	2275.4	2007.1	1533.3	1468.9	496.8	98.1
32.5°	3261.3	3252.9	3163.9	3001.4	2812.1	2560.6	2284.6	1844.5	1766.4	681.5	112.7
35°	4175.9	4189.0	3970.5	3549.6	3209.9	2903.3	2592.0	2154.3	2085.3	909.2	132.6
37.5°	5576.6	5505.3	5208.6	4464.9	3733.6	3331.1	2885.7	2467.1	2407.3	1189.8	158.7
40°	6937.4	6866.8	6781.0	6076.4	4643.6	3802.6	3296.6	2834.3	2756.9	1506.5	197.0
42.5°	8367.9	8328.8	8325.0	7793.7	6304.1	4543.9	3791.1	3264.4	3198.4	1853.7	259.9
45°	9381.4	9342.3	9424.4	9517.1	8565.7	6132.4	4652.0	3823.3	3727.4	2275.4	360.3
47.5°	9517.9	9519.4	9738.7	10029.3	10246.2	8589.5	5798.9	4563.8	4447.3	2878.8	529.0
50°	9064.1	9081.7	9430.5	9950.3	10534.5	10651.0	7821.3	5638.7	5466.2	3594.0	768.2
52.5°	8200.0	8220.0	8706.0	9560.8	10269.2	11146.3	10202.5	7044.7	6846.1	4486.4	1105.5
55°	7421.9	7434.2	7991.5	9071.7	9949.5	10877.2	11616.2	8922.2	8661.6	5584.2	1438.2
57.5°	6651.4	6623.1	6985.7	8222.3	9895.1	10546.7	11824.7	11061.9	10774.4	6784.0	1697.4
60°	5621.0	5573.5	5864.8	6651.4	9179.0	10763.7	11434.5	12245.6	12180.5	8454.6	1897.4
61°	5028.4	5008.5	5301.4	5976.0	8576.5	10708.5	11341.0	12295.5	12302.4	9245.0	1987.1
62.5°	3591.0	3647.7	4095.4	4972.5	7183.5	10350.5	11353.3	12141.4	12209.6	10295.3	2219.4
65°	1596.2	1687.4	2035.4	2749.2	4177.5	8610.2	11244.4	11803.3	11769.5	10583.5	3019.8
67.5°	946.8	960.6	1133.9	1557.8	2212.5	4631.3	9922.7	11356.3	11311.1	9213.5	3757.3
70°	745.9	752.8	808.0	977.5	1284.1	1774.0	5663.2	9825.3	10022.4	7471.0	3678.4
72.5°	707.6	706.1	713.7	743.6	808.8	880.1	2192.6	6531.1	6932.0	5380.3	3084.2
75°	698.4	695.3	687.7	676.2	585.7	518.3	679.2	2888.7	3121.0	3676.1	2322.2
77.5°	677.7	678.5	680.0	648.6	502.2	366.5	328.9	926.9	1140.0	2332.9	1650.6
80°	458.5	465.4	476.9	464.6	451.6	265.3	232.3	329.7	334.3	1309.4	1090.2
82.5°	232.3	232.3	226.9	202.4	174.8	172.5	184.8	239.2	242.3	662.4	512.9
85°	140.3	148.0	151.0	137.2	125.7	115.8	141.1	190.1	197.0	256.8	119.6
87.5°	31.4	32.2	35.3	46.8	68.2	92.8	131.1	174.0	177.1	164.8	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1063411

CATALOG NUMBER: GLAN-SA2C-735-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2
2.5°	69.0	67.5	66.7	64.4	62.1	59.8	58.3	57.5	58.3	59.0	59.0
5°	68.2	65.9	62.1	58.3	55.2	52.1	49.1	48.3	48.3	49.1	49.1
7.5°	68.2	64.4	59.0	54.4	49.8	45.2	42.9	41.4	42.2	42.2	42.2
10°	68.2	63.6	56.7	49.8	44.5	39.1	35.3	33.7	33.7	33.7	33.7
12.5°	67.5	62.9	54.4	46.0	38.3	32.2	27.6	25.3	26.1	26.1	26.1
15°	65.9	60.6	51.4	39.1	30.7	24.5	19.9	17.6	18.4	19.9	20.7
17.5°	63.6	58.3	46.0	33.0	24.5	18.4	13.8	12.3	13.0	15.3	15.3
20°	62.9	56.0	40.6	26.8	18.4	13.0	9.2	7.7	8.4	11.5	12.3
22.5°	62.9	54.4	36.8	22.2	13.8	8.4	5.4	3.1	3.1	5.4	5.4
25°	63.6	53.7	33.7	18.4	10.0	6.1	3.1	1.5	3.1	8.4	10.0
27.5°	65.2	52.9	32.2	15.3	7.7	5.4	2.3	5.4	9.2	9.2	9.2
30°	66.7	51.4	29.9	13.0	6.9	3.8	3.8	7.7	7.7	9.2	10.0
32.5°	69.0	50.6	28.4	11.5	5.4	3.1	5.4	4.6	4.6	5.4	6.1
35°	73.6	51.4	26.8	11.5	5.4	3.8	4.6	2.3	1.5	1.5	1.5
37.5°	79.7	52.1	24.5	10.0	4.6	4.6	2.3	0.0	0.0	0.0	0.0
40°	89.7	54.4	23.0	9.2	3.8	3.8	0.8	0.0	0.0	0.0	0.0
42.5°	106.6	59.0	22.2	8.4	3.8	3.1	0.0	0.0	0.0	0.0	0.0
45°	140.3	69.8	20.7	7.7	3.8	1.5	0.0	0.0	0.0	0.0	0.0
47.5°	201.6	95.1	19.9	6.1	2.3	0.0	0.0	0.0	0.0	0.0	0.0
50°	294.4	128.8	19.2	5.4	0.8	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	375.7	135.7	13.0	4.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	384.9	93.5	10.0	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	306.7	60.6	8.4	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	232.3	46.0	7.7	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
61°	223.1	41.4	7.7	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	246.1	36.0	6.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	400.2	29.9	6.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	695.3	26.1	5.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	878.6	24.5	4.6	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	765.9	22.2	4.6	1.5	0.8	0.0	0.0	0.0	0.0	0.0	0.0
75°	460.8	19.2	4.6	3.1	1.5	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	241.5	14.6	4.6	3.8	2.3	0.8	0.0	0.0	0.0	0.0	0.0
80°	117.3	13.0	5.4	3.8	3.1	1.5	0.0	0.0	0.0	0.0	0.0
82.5°	46.0	10.7	6.1	5.4	3.8	2.3	0.8	0.0	0.0	0.0	0.0
85°	20.7	9.2	6.9	6.1	5.4	3.1	0.8	0.0	0.0	0.0	0.0
87.5°	10.7	8.4	7.7	6.9	5.4	3.8	1.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.36

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5


TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 CIE $R_a = 70.1$
 $R_g = -40.2$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)