

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065123

Luminaire Tested: **GLAN-SA7C-740-U-LBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065123  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA7C-740-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 7xLight Square PACKAGE  
70CRI 4000K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (98) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 35255.2 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G5

Input Watts (W): 330  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1065123

CATALOG NUMBER: GLAN-SA7C-740-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd


--- 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 61.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065123  
CATALOG NUMBER: GLAN-SA7C-740-U-LBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1065123

CATALOG NUMBER: GLAN-SA7C-740-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 240.7    | 0.0    | 240.7   |
|                    | % Fixture | 0.7      | 0.0    | 0.7     |
| <b>Street Side</b> | Lumens    | 35014.5  | 0.0    | 35014.5 |
|                    | % Fixture | 99.3     | 0.0    | 99.3    |
| <b>Total</b>       | Lumens    | 35255.2  | 0.0    | 35255.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 13.8    | 0.0       |
| 10°-20°   | 77.3    | 0.2       |
| 20°-30°   | 835.2   | 2.4       |
| 30°-40°   | 2470.0  | 7.0       |
| 40°-50°   | 7361.9  | 20.9      |
| 50°-60°   | 11681.5 | 33.1      |
| 60°-70°   | 9743.7  | 27.6      |
| 70°-80°   | 3005.1  | 8.5       |
| 80°-90°   | 66.7    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 35255.2 | 100.0     |
| 0°-180°   | 35255.2 | 100.0     |



REPORT NUMBER: P1065123


CATALOG NUMBER: GLAN-SA7C-740-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|---------|-----------|-------------------------|------|--------|
|      |             |         |           | B                       | U    | G      |
| FL   | (0°-30°)    | 902.7   | 2.6       |                         |      |        |
| FM   | (30°-60°)   | 21381.6 | 60.6      |                         |      |        |
| FH   | (60°-80°)   | 12666.7 | 35.9      |                         |      | G5     |
| FVH  | (80°-90°)   | 63.5    | 0.2       |                         |      | G1/100 |
| BL   | (0°-30°)    | 23.6    | 0.1       | B0/110                  |      |        |
| BM   | (30°-60°)   | 131.8   | 0.4       | B0/220                  |      |        |
| BH   | (60°-80°)   | 82.2    | 0.2       | B0/110                  |      | G0/110 |
| BVH  | (80°-90°)   | 3.2     | 0.0       |                         |      | G0/10  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B0-U0-G5**

Type III Short



REPORT NUMBER: P1065123

CATALOG NUMBER: GLAN-SA7C-740-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°      | 15°     | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°     |
|-------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 154.5  | 154.5   | 154.5   | 154.5   | 154.5   | 154.5   | 154.5   | 154.5   | 154.5   | 154.5   |
| 2.5°  | 199.7  | 199.7   | 191.8   | 181.1   | 170.4   | 159.8   | 157.1   | 151.8   | 149.1   | 146.5   |
| 5°    | 207.7  | 207.7   | 205.1   | 197.1   | 186.4   | 178.4   | 178.4   | 170.4   | 165.1   | 159.8   |
| 7.5°  | 213.1  | 215.7   | 221.0   | 218.4   | 213.1   | 205.1   | 205.1   | 199.7   | 191.8   | 178.4   |
| 10°   | 221.0  | 229.0   | 239.7   | 245.0   | 247.7   | 247.7   | 245.0   | 242.4   | 229.0   | 210.4   |
| 12.5° | 229.0  | 245.0   | 271.6   | 298.3   | 314.3   | 335.6   | 332.9   | 327.6   | 293.0   | 253.0   |
| 15°   | 245.0  | 269.0   | 324.9   | 402.1   | 522.0   | 596.6   | 625.9   | 599.2   | 484.7   | 340.9   |
| 17.5° | 263.7  | 303.6   | 471.4   | 841.6   | 1379.6  | 1635.2  | 1789.7  | 1664.5  | 1102.6  | 647.2   |
| 20°   | 282.3  | 370.2   | 876.2   | 2181.2  | 3579.4  | 4415.6  | 4647.3  | 4285.1  | 2751.1  | 1233.1  |
| 22.5° | 314.3  | 519.3   | 1776.4  | 4508.9  | 7712.7  | 8967.1  | 9204.1  | 8045.6  | 5196.0  | 2434.2  |
| 25°   | 380.8  | 753.7   | 3062.7  | 7347.9  | 11510.5 | 13627.8 | 13529.2 | 12011.2 | 8429.1  | 3888.3  |
| 27.5° | 476.7  | 1097.3  | 4631.4  | 10439.9 | 15148.5 | 17015.4 | 17239.1 | 15361.5 | 11236.2 | 5718.0  |
| 30°   | 615.2  | 1520.7  | 6314.5  | 12916.7 | 18064.7 | 20083.4 | 20120.7 | 18179.2 | 13747.6 | 7323.9  |
| 32.5° | 748.4  | 1920.2  | 7787.3  | 15310.9 | 20938.3 | 23151.5 | 23316.6 | 20927.7 | 15622.5 | 8996.4  |
| 35°   | 849.6  | 2181.2  | 9278.7  | 17414.9 | 23835.9 | 26885.3 | 26874.7 | 24038.3 | 17843.7 | 10490.5 |
| 37.5° | 857.6  | 2442.2  | 10629.0 | 19566.8 | 27505.9 | 30920.1 | 31258.4 | 28131.7 | 20528.2 | 12338.8 |
| 40°   | 838.9  | 2735.1  | 12338.8 | 22922.4 | 34118.7 | 39357.3 | 39655.5 | 35714.0 | 25913.3 | 15502.7 |
| 42.5° | 860.2  | 3243.8  | 15113.8 | 29119.8 | 45099.2 | 52622.8 | 53198.1 | 49054.1 | 35812.5 | 21958.4 |
| 45°   | 972.1  | 4199.9  | 20927.7 | 39487.8 | 60751.0 | 69923.2 | 69731.4 | 63763.1 | 47331.0 | 31785.7 |
| 47.5° | 1342.3 | 6540.9  | 29545.9 | 49578.7 | 70754.1 | 78922.3 | 79087.4 | 71792.8 | 54053.0 | 39341.3 |
| 50°   | 2064.0 | 10008.4 | 36787.2 | 54913.2 | 75055.2 | 83250.0 | 83095.5 | 74666.4 | 56607.0 | 43061.8 |
| 52.5° | 2684.5 | 12517.2 | 40419.9 | 56785.5 | 75606.5 | 85388.6 | 85377.9 | 75422.8 | 57003.8 | 43381.4 |
| 55°   | 2839.0 | 12706.3 | 40449.2 | 56886.7 | 76842.3 | 88187.6 | 88539.2 | 77284.4 | 57517.8 | 41985.9 |
| 57.5° | 2777.8 | 11249.5 | 38760.7 | 57472.6 | 79042.1 | 90352.8 | 90371.5 | 79087.4 | 58822.8 | 41131.0 |
| 58°   | 2724.5 | 11020.5 | 38419.8 | 57805.5 | 79420.3 | 90443.4 | 90398.1 | 79169.9 | 59885.5 | 41099.0 |
| 60°   | 2426.2 | 9569.0  | 37090.8 | 58655.0 | 78858.3 | 88584.5 | 88161.0 | 77366.9 | 59728.3 | 40771.4 |
| 62.5° | 1906.9 | 7465.0  | 35783.2 | 57672.3 | 72834.1 | 79585.4 | 79761.2 | 68495.7 | 54449.8 | 38861.9 |
| 65°   | 1518.0 | 5563.5  | 33056.0 | 50588.1 | 59976.0 | 65355.7 | 66010.9 | 55698.9 | 45448.1 | 32906.9 |
| 67.5° | 1209.1 | 4021.5  | 27729.6 | 40276.1 | 47458.8 | 54545.7 | 55022.4 | 46763.7 | 35210.6 | 25212.8 |
| 70°   | 982.7  | 2719.2  | 19140.7 | 29455.4 | 39144.2 | 47112.6 | 47141.9 | 38848.6 | 26280.8 | 16520.0 |
| 72.5° | 870.9  | 1882.9  | 11111.0 | 21481.6 | 31740.4 | 38390.5 | 37615.5 | 31524.7 | 20198.0 | 9784.7  |
| 75°   | 753.7  | 1249.1  | 5449.0  | 13132.4 | 19244.5 | 19375.0 | 19670.6 | 14623.8 | 10096.3 | 4652.7  |
| 77.5° | 620.5  | 886.9   | 2146.6  | 3587.4  | 5771.2  | 7387.8  | 7662.1  | 5805.8  | 3358.3  | 1145.2  |
| 80°   | 426.1  | 420.8   | 577.9   | 1099.9  | 1651.2  | 2069.3  | 1930.8  | 1494.1  | 878.9   | 439.4   |
| 82.5° | 183.8  | 199.7   | 261.0   | 314.3   | 255.7   | 247.7   | 237.0   | 151.8   | 117.2   | 90.5    |
| 85°   | 58.6   | 53.3    | 55.9    | 55.9    | 45.3    | 34.6    | 34.6    | 16.0    | 0.0     | 0.0     |
| 87.5° | 29.3   | 24.0    | 24.0    | 21.3    | 13.3    | 5.3     | 2.7     | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065123

CATALOG NUMBER: GLAN-SA7C-740-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°     |       | 90°    | 95°    | 105°  | 115°  | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  |
|---------|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 154.5   | 0°    | 154.5  | 154.5  | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 |
| 143.8   | 2.5°  | 141.2  | 141.2  | 135.8 | 130.5 | 127.8 | 122.5 | 119.8 | 117.2 | 114.5 | 111.9 |
| 154.5   | 5°    | 149.1  | 146.5  | 138.5 | 130.5 | 122.5 | 114.5 | 109.2 | 103.9 | 98.5  | 95.9  |
| 170.4   | 7.5°  | 162.5  | 157.1  | 141.2 | 127.8 | 117.2 | 106.5 | 101.2 | 93.2  | 87.9  | 79.9  |
| 189.1   | 10°   | 178.4  | 167.8  | 146.5 | 130.5 | 114.5 | 101.2 | 93.2  | 85.2  | 77.2  | 66.6  |
| 215.7   | 12.5° | 199.7  | 181.1  | 154.5 | 127.8 | 109.2 | 93.2  | 85.2  | 74.6  | 66.6  | 58.6  |
| 250.3   | 15°   | 218.4  | 194.4  | 157.1 | 127.8 | 103.9 | 85.2  | 74.6  | 63.9  | 55.9  | 45.3  |
| 314.3   | 17.5° | 245.0  | 205.1  | 154.5 | 119.8 | 95.9  | 74.6  | 63.9  | 55.9  | 42.6  | 26.6  |
| 466.1   | 20°   | 290.3  | 213.1  | 149.1 | 111.9 | 82.6  | 61.3  | 47.9  | 37.3  | 18.6  | 5.3   |
| 700.4   | 22.5° | 362.2  | 234.4  | 143.8 | 101.2 | 71.9  | 47.9  | 32.0  | 13.3  | 0.0   | 0.0   |
| 1065.3  | 25°   | 500.7  | 271.6  | 143.8 | 95.9  | 63.9  | 34.6  | 10.7  | 0.0   | 0.0   | 0.0   |
| 1512.7  | 27.5° | 665.8  | 322.3  | 143.8 | 82.6  | 50.6  | 18.6  | 0.0   | 0.0   | 0.0   | 0.0   |
| 2061.3  | 30°   | 833.6  | 378.2  | 143.8 | 71.9  | 39.9  | 2.7   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2538.1  | 32.5° | 993.4  | 426.1  | 146.5 | 61.3  | 26.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 3198.5  | 35°   | 1155.8 | 434.1  | 143.8 | 53.3  | 16.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 4008.2  | 37.5° | 1363.6 | 418.1  | 135.8 | 47.9  | 8.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 5273.2  | 40°   | 1677.8 | 426.1  | 127.8 | 45.3  | 2.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 7529.0  | 42.5° | 2258.4 | 460.7  | 117.2 | 45.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 11992.5 | 45°   | 3904.3 | 617.9  | 106.5 | 47.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 18003.5 | 47.5° | 6458.3 | 1110.6 | 103.9 | 47.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 21686.7 | 50°   | 8242.7 | 1398.2 | 109.2 | 50.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 22147.4 | 52.5° | 8229.4 | 1558.0 | 114.5 | 53.3  | 10.7  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 20413.7 | 55°   | 7315.9 | 1587.3 | 122.5 | 58.6  | 34.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 17542.7 | 57.5° | 6114.8 | 1448.8 | 141.2 | 71.9  | 63.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 17092.6 | 58°   | 5901.7 | 1384.9 | 146.5 | 74.6  | 69.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 14826.2 | 60°   | 4836.4 | 1129.2 | 186.4 | 93.2  | 93.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 12155.0 | 62.5° | 3339.7 | 985.4  | 213.1 | 119.8 | 95.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 8961.8  | 65°   | 2362.3 | 889.5  | 231.7 | 127.8 | 77.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 6367.8  | 67.5° | 1765.7 | 820.3  | 255.7 | 130.5 | 39.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 3994.8  | 70°   | 1352.9 | 769.7  | 314.3 | 138.5 | 10.7  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2380.9  | 72.5° | 1102.6 | 711.1  | 380.8 | 143.8 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 1427.5  | 75°   | 913.5  | 641.8  | 367.5 | 157.1 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 761.7   | 77.5° | 607.2  | 498.0  | 335.6 | 157.1 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 271.6   | 80°   | 213.1  | 197.1  | 261.0 | 138.5 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55.9    | 82.5° | 32.0   | 26.6   | 37.3  | 47.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0     | 85°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0     | 87.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0     | 90°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P1065123

CATALOG NUMBER: GLAN-SA7C-740-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180°  |       | 185°  | 195°  | 205°  | 215°  | 225°  | 235°  | 245°  | 255°  | 265°  | 270°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 154.5 | 0°    | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 |
| 109.2 | 2.5°  | 109.2 | 109.2 | 106.5 | 109.2 | 109.2 | 114.5 | 127.8 | 146.5 | 167.8 | 175.8 |
| 93.2  | 5°    | 90.5  | 87.9  | 85.2  | 85.2  | 85.2  | 93.2  | 103.9 | 125.2 | 149.1 | 159.8 |
| 77.2  | 7.5°  | 74.6  | 71.9  | 69.2  | 66.6  | 66.6  | 71.9  | 85.2  | 109.2 | 133.2 | 143.8 |
| 63.9  | 10°   | 61.3  | 55.9  | 53.3  | 50.6  | 50.6  | 55.9  | 69.2  | 93.2  | 119.8 | 130.5 |
| 53.3  | 12.5° | 50.6  | 42.6  | 37.3  | 34.6  | 32.0  | 39.9  | 53.3  | 74.6  | 103.9 | 117.2 |
| 39.9  | 15°   | 34.6  | 26.6  | 18.6  | 16.0  | 13.3  | 21.3  | 34.6  | 58.6  | 87.9  | 103.9 |
| 21.3  | 17.5° | 18.6  | 8.0   | 2.7   | 0.0   | 0.0   | 5.3   | 16.0  | 42.6  | 71.9  | 85.2  |
| 0.0   | 20°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 21.3  | 53.3  | 66.6  |
| 0.0   | 22.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 2.7   | 32.0  | 45.3  |
| 0.0   | 25°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 13.3  | 24.0  |
| 0.0   | 27.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 5.3   |
| 0.0   | 30°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 58°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 8.0   |
| 0.0   | 87.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 10.7  | 21.3  |
| 0.0   | 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065123

CATALOG NUMBER: GLAN-SA7C-740-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275°  |       | 285°  | 295°  | 305°  | 315°  | 316°  | 325°  | 335°  | 345°  | 355°  | 360°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 154.5 | 0°    | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5 | 154.5  |
| 183.8 | 2.5°  | 189.1 | 186.4 | 181.1 | 175.8 | 175.8 | 175.8 | 183.8 | 191.8 | 199.7 | 199.7  |
| 165.1 | 5°    | 175.8 | 175.8 | 173.1 | 167.8 | 167.8 | 170.4 | 181.1 | 194.4 | 205.1 | 207.7  |
| 151.8 | 7.5°  | 162.5 | 167.8 | 162.5 | 159.8 | 162.5 | 165.1 | 175.8 | 191.8 | 207.7 | 213.1  |
| 141.2 | 10°   | 154.5 | 157.1 | 157.1 | 154.5 | 154.5 | 159.8 | 170.4 | 191.8 | 213.1 | 221.0  |
| 127.8 | 12.5° | 143.8 | 149.1 | 146.5 | 146.5 | 146.5 | 151.8 | 165.1 | 189.1 | 218.4 | 229.0  |
| 114.5 | 15°   | 133.2 | 141.2 | 141.2 | 138.5 | 138.5 | 141.2 | 159.8 | 186.4 | 226.4 | 245.0  |
| 98.5  | 17.5° | 122.5 | 130.5 | 133.2 | 127.8 | 127.8 | 133.2 | 151.8 | 186.4 | 231.7 | 263.7  |
| 79.9  | 20°   | 101.2 | 114.5 | 122.5 | 114.5 | 114.5 | 119.8 | 138.5 | 175.8 | 234.4 | 282.3  |
| 58.6  | 22.5° | 79.9  | 93.2  | 103.9 | 101.2 | 101.2 | 103.9 | 127.8 | 167.8 | 237.0 | 314.3  |
| 34.6  | 25°   | 58.6  | 71.9  | 79.9  | 85.2  | 85.2  | 93.2  | 117.2 | 162.5 | 247.7 | 380.8  |
| 16.0  | 27.5° | 34.6  | 50.6  | 61.3  | 66.6  | 69.2  | 79.9  | 109.2 | 157.1 | 266.3 | 476.7  |
| 0.0   | 30°   | 16.0  | 29.3  | 42.6  | 53.3  | 53.3  | 71.9  | 101.2 | 151.8 | 290.3 | 615.2  |
| 0.0   | 32.5° | 0.0   | 13.3  | 21.3  | 37.3  | 39.9  | 58.6  | 93.2  | 146.5 | 324.9 | 748.4  |
| 0.0   | 35°   | 0.0   | 0.0   | 10.7  | 29.3  | 29.3  | 47.9  | 85.2  | 141.2 | 378.2 | 849.6  |
| 0.0   | 37.5° | 0.0   | 0.0   | 0.0   | 21.3  | 24.0  | 42.6  | 82.6  | 138.5 | 388.8 | 857.6  |
| 0.0   | 40°   | 0.0   | 0.0   | 0.0   | 16.0  | 18.6  | 39.9  | 82.6  | 141.2 | 351.5 | 838.9  |
| 0.0   | 42.5° | 0.0   | 0.0   | 0.0   | 10.7  | 13.3  | 39.9  | 82.6  | 146.5 | 316.9 | 860.2  |
| 0.0   | 45°   | 0.0   | 0.0   | 0.0   | 8.0   | 10.7  | 42.6  | 79.9  | 143.8 | 298.3 | 972.1  |
| 0.0   | 47.5° | 0.0   | 0.0   | 0.0   | 10.7  | 16.0  | 42.6  | 77.2  | 141.2 | 300.9 | 1342.3 |
| 0.0   | 50°   | 0.0   | 0.0   | 0.0   | 13.3  | 18.6  | 42.6  | 79.9  | 135.8 | 330.2 | 2064.0 |
| 0.0   | 52.5° | 0.0   | 0.0   | 0.0   | 10.7  | 16.0  | 47.9  | 87.9  | 133.2 | 359.5 | 2684.5 |
| 0.0   | 55°   | 0.0   | 0.0   | 0.0   | 2.7   | 8.0   | 61.3  | 95.9  | 133.2 | 404.8 | 2839.0 |
| 0.0   | 57.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 69.2  | 109.2 | 141.2 | 479.4 | 2777.8 |
| 0.0   | 58°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 69.2  | 111.9 | 141.2 | 484.7 | 2724.5 |
| 0.0   | 60°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 69.2  | 122.5 | 157.1 | 522.0 | 2426.2 |
| 0.0   | 62.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 58.6  | 146.5 | 197.1 | 543.3 | 1906.9 |
| 0.0   | 65°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 47.9  | 173.1 | 215.7 | 559.3 | 1518.0 |
| 0.0   | 67.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 45.3  | 178.4 | 218.4 | 567.3 | 1209.1 |
| 0.0   | 70°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 47.9  | 175.8 | 234.4 | 593.9 | 982.7  |
| 0.0   | 72.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 53.3  | 159.8 | 258.3 | 593.9 | 870.9  |
| 0.0   | 75°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 55.9  | 149.1 | 290.3 | 540.6 | 753.7  |
| 0.0   | 77.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 53.3  | 146.5 | 338.2 | 482.0 | 620.5  |
| 0.0   | 80°   | 5.3   | 8.0   | 8.0   | 5.3   | 5.3   | 45.3  | 143.8 | 343.6 | 410.1 | 426.1  |
| 2.7   | 82.5° | 16.0  | 21.3  | 18.6  | 13.3  | 13.3  | 39.9  | 127.8 | 287.6 | 213.1 | 183.8  |
| 16.0  | 85°   | 29.3  | 34.6  | 34.6  | 29.3  | 29.3  | 37.3  | 79.9  | 103.9 | 71.9  | 58.6   |
| 29.3  | 87.5° | 39.9  | 45.3  | 45.3  | 39.9  | 39.9  | 37.3  | 34.6  | 32.0  | 29.3  | 29.3   |
| 0.0   | 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ


Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-740-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 3949     | CRI (Ra): | 70.7 |      |       |
| CIE u':                   | 0.2248   | R1:       | 68.0 | R9:  | -36.7 |
| CIE v':                   | 0.5053   | R2:       | 76.0 | R10: | 45.1  |
| Duv:                      | 0.0022   | R3:       | 84.3 | R11: | 70.7  |
| CIE x:                    | 0.3844   | R4:       | 72.0 | R12: | 47.1  |
| CIE y:                    | 0.3840   | R5:       | 68.6 | R13: | 68.5  |
| CIE z:                    | 0.2316   | R6:       | 68.3 | R14: | 91.1  |
| Peak Wavelength (nm):     | 440      | R7:       | 77.9 | R15: | 58.7  |
| Dominant Wavelength (nm): | 578      | R8:       | 50.3 |      |       |
| Purity:                   | 30.60026 |           |      |      |       |
| Rf:                       | 71.8     |           |      |      |       |
| Rg:                       | 96.5     |           |      |      |       |



### Test Conditions

Stabilization Time: 34M  
 Operation Time: 1H 34M  
 Sphere Temperature (°C): 25.2


REPORT NUMBER: SP1-2407-184-1

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |



REPORT NUMBER: SP1-2407-184-1

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 0                             | NR                             | 490               | 139                           | NR                             | 620               | 607                           | NR                             | 750               | 15                            | NR                             | 880               | 0                             | NR                             |
| 365               | 0                             | NR                             | 495               | 198                           | NR                             | 625               | 554                           | NR                             | 755               | 13                            | NR                             | 885               | 0                             | NR                             |
| 370               | 0                             | NR                             | 500               | 267                           | NR                             | 630               | 504                           | NR                             | 760               | 11                            | NR                             | 890               | 0                             | NR                             |
| 375               | 0                             | NR                             | 505               | 343                           | NR                             | 635               | 452                           | NR                             | 765               | 10                            | NR                             | 895               | 0                             | NR                             |
| 380               | 0                             | NR                             | 510               | 410                           | NR                             | 640               | 403                           | NR                             | 770               | 8                             | NR                             | 900               | 0                             | NR                             |
| 385               | 2                             | NR                             | 515               | 470                           | NR                             | 645               | 357                           | NR                             | 775               | 7                             | NR                             | 905               | 0                             | NR                             |
| 390               | 4                             | NR                             | 520               | 516                           | NR                             | 650               | 314                           | NR                             | 780               | 6                             | NR                             | 910               | 0                             | NR                             |
| 395               | 7                             | NR                             | 525               | 550                           | NR                             | 655               | 275                           | NR                             | 785               | 5                             | NR                             | 915               | 0                             | NR                             |
| 400               | 10                            | NR                             | 530               | 578                           | NR                             | 660               | 240                           | NR                             | 790               | 5                             | NR                             | 920               | 0                             | NR                             |
| 405               | 17                            | NR                             | 535               | 601                           | NR                             | 665               | 208                           | NR                             | 795               | 4                             | NR                             | 925               | 0                             | NR                             |
| 410               | 35                            | NR                             | 540               | 620                           | NR                             | 670               | 179                           | NR                             | 800               | 4                             | NR                             | 930               | 0                             | NR                             |
| 415               | 70                            | NR                             | 545               | 641                           | NR                             | 675               | 155                           | NR                             | 805               | 3                             | NR                             | 935               | 0                             | NR                             |
| 420               | 147                           | NR                             | 550               | 664                           | NR                             | 680               | 133                           | NR                             | 810               | 3                             | NR                             | 940               | 0                             | NR                             |
| 425               | 285                           | NR                             | 555               | 689                           | NR                             | 685               | 114                           | NR                             | 815               | 2                             | NR                             | 945               | 0                             | NR                             |
| 430               | 487                           | NR                             | 560               | 715                           | NR                             | 690               | 98                            | NR                             | 820               | 2                             | NR                             | 950               | 0                             | NR                             |
| 435               | 787                           | NR                             | 565               | 743                           | NR                             | 695               | 84                            | NR                             | 825               | 2                             | NR                             | 955               | 0                             | NR                             |
| 440               | 1000                          | NR                             | 570               | 771                           | NR                             | 700               | 72                            | NR                             | 830               | 2                             | NR                             | 960               | 0                             | NR                             |
| 445               | 783                           | NR                             | 575               | 794                           | NR                             | 705               | 61                            | NR                             | 835               | 1                             | NR                             | 965               | 0                             | NR                             |
| 450               | 417                           | NR                             | 580               | 811                           | NR                             | 710               | 52                            | NR                             | 840               | 1                             | NR                             | 970               | 0                             | NR                             |
| 455               | 261                           | NR                             | 585               | 817                           | NR                             | 715               | 45                            | NR                             | 845               | 1                             | NR                             | 975               | 0                             | NR                             |
| 460               | 167                           | NR                             | 590               | 815                           | NR                             | 720               | 39                            | NR                             | 850               | 1                             | NR                             | 980               | 0                             | NR                             |
| 465               | 104                           | NR                             | 595               | 801                           | NR                             | 725               | 33                            | NR                             | 855               | 1                             | NR                             | 985               | 0                             | NR                             |
| 470               | 79                            | NR                             | 600               | 777                           | NR                             | 730               | 28                            | NR                             | 860               | 1                             | NR                             | 990               | 0                             | NR                             |
| 475               | 73                            | NR                             | 605               | 744                           | NR                             | 735               | 24                            | NR                             | 865               | 1                             | NR                             | 995               | 0                             | NR                             |
| 480               | 76                            | NR                             | 610               | 704                           | NR                             | 740               | 21                            | NR                             | 870               | 1                             | NR                             | 1000              | 0                             | NR                             |
| 485               | 98                            | NR                             | 615               | 657                           | NR                             | 745               | 18                            | NR                             | 875               | 1                             | NR                             |                   |                               |                                |

REPORT NUMBER: SP1-2407-184-1

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.47

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 139                      | NR            | 620    | 607                      | NR            | 750    | 15                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 198                      | NR            | 625    | 554                      | NR            | 755    | 13                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 267                      | NR            | 630    | 504                      | NR            | 760    | 11                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 343                      | NR            | 635    | 452                      | NR            | 765    | 10                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 410                      | NR            | 640    | 403                      | NR            | 770    | 8                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 470                      | NR            | 645    | 357                      | NR            | 775    | 7                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 516                      | NR            | 650    | 314                      | NR            | 780    | 6                        | NR            | 910    | 0                        | NR            |
| 395    | 7                        | NR            | 525    | 550                      | NR            | 655    | 275                      | NR            | 785    | 5                        | NR            | 915    | 0                        | NR            |
| 400    | 10                       | NR            | 530    | 578                      | NR            | 660    | 240                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 17                       | NR            | 535    | 601                      | NR            | 665    | 208                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 35                       | NR            | 540    | 620                      | NR            | 670    | 179                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 70                       | NR            | 545    | 641                      | NR            | 675    | 155                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 147                      | NR            | 550    | 664                      | NR            | 680    | 133                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 285                      | NR            | 555    | 689                      | NR            | 685    | 114                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 487                      | NR            | 560    | 715                      | NR            | 690    | 98                       | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 787                      | NR            | 565    | 743                      | NR            | 695    | 84                       | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 1000                     | NR            | 570    | 771                      | NR            | 700    | 72                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 783                      | NR            | 575    | 794                      | NR            | 705    | 61                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 417                      | NR            | 580    | 811                      | NR            | 710    | 52                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 261                      | NR            | 585    | 817                      | NR            | 715    | 45                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 167                      | NR            | 590    | 815                      | NR            | 720    | 39                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 104                      | NR            | 595    | 801                      | NR            | 725    | 33                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 79                       | NR            | 600    | 777                      | NR            | 730    | 28                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 73                       | NR            | 605    | 744                      | NR            | 735    | 24                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 76                       | NR            | 610    | 704                      | NR            | 740    | 21                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 98                       | NR            | 615    | 657                      | NR            | 745    | 18                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-1

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 2.78**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 139                                  | NR                             | 620               | 607                                  | NR                             | 750               | 15                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 198                                  | NR                             | 625               | 554                                  | NR                             | 755               | 13                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 267                                  | NR                             | 630               | 504                                  | NR                             | 760               | 11                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 343                                  | NR                             | 635               | 452                                  | NR                             | 765               | 10                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 410                                  | NR                             | 640               | 403                                  | NR                             | 770               | 8                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 2                                    | NR                             | 515               | 470                                  | NR                             | 645               | 357                                  | NR                             | 775               | 7                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 4                                    | NR                             | 520               | 516                                  | NR                             | 650               | 314                                  | NR                             | 780               | 6                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 7                                    | NR                             | 525               | 550                                  | NR                             | 655               | 275                                  | NR                             | 785               | 5                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 10                                   | NR                             | 530               | 578                                  | NR                             | 660               | 240                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 17                                   | NR                             | 535               | 601                                  | NR                             | 665               | 208                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 35                                   | NR                             | 540               | 620                                  | NR                             | 670               | 179                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 70                                   | NR                             | 545               | 641                                  | NR                             | 675               | 155                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 147                                  | NR                             | 550               | 664                                  | NR                             | 680               | 133                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 285                                  | NR                             | 555               | 689                                  | NR                             | 685               | 114                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 487                                  | NR                             | 560               | 715                                  | NR                             | 690               | 98                                   | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 787                                  | NR                             | 565               | 743                                  | NR                             | 695               | 84                                   | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 1000                                 | NR                             | 570               | 771                                  | NR                             | 700               | 72                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 783                                  | NR                             | 575               | 794                                  | NR                             | 705               | 61                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 417                                  | NR                             | 580               | 811                                  | NR                             | 710               | 52                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 261                                  | NR                             | 585               | 817                                  | NR                             | 715               | 45                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 167                                  | NR                             | 590               | 815                                  | NR                             | 720               | 39                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 104                                  | NR                             | 595               | 801                                  | NR                             | 725               | 33                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 79                                   | NR                             | 600               | 777                                  | NR                             | 730               | 28                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 73                                   | NR                             | 605               | 744                                  | NR                             | 735               | 24                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 76                                   | NR                             | 610               | 704                                  | NR                             | 740               | 21                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 98                                   | NR                             | 615               | 657                                  | NR                             | 745               | 18                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-1





TM-30-18

### Summary

$R_f = 71.8$   
 $R_g = 96.5$   
 $CIE R_a = 70.7$   
 $R_g = -36.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 56 | CES51 = 86 | CES76 = 48 |
| CES02 = 61 | CES27 = 79 | CES52 = 88 | CES77 = 71 |
| CES03 = 30 | CES28 = 80 | CES53 = 73 | CES78 = 52 |
| CES04 = 70 | CES29 = 49 | CES54 = 79 | CES79 = 79 |
| CES05 = 47 | CES30 = 53 | CES55 = 77 | CES80 = 77 |
| CES06 = 50 | CES31 = 55 | CES56 = 67 | CES81 = 75 |
| CES07 = 40 | CES32 = 53 | CES57 = 64 | CES82 = 90 |
| CES08 = 39 | CES33 = 59 | CES58 = 67 | CES83 = 84 |
| CES09 = 29 | CES34 = 67 | CES59 = 87 | CES84 = 89 |
| CES10 = 74 | CES35 = 82 | CES60 = 91 | CES85 = 86 |
| CES11 = 57 | CES36 = 86 | CES61 = 87 | CES86 = 71 |
| CES12 = 63 | CES37 = 76 | CES62 = 76 | CES87 = 78 |
| CES13 = 42 | CES38 = 62 | CES63 = 73 | CES88 = 76 |
| CES14 = 74 | CES39 = 91 | CES64 = 71 | CES89 = 72 |
| CES15 = 71 | CES40 = 84 | CES65 = 64 | CES90 = 72 |
| CES16 = 46 | CES41 = 81 | CES66 = 67 | CES91 = 97 |
| CES17 = 49 | CES42 = 76 | CES67 = 65 | CES92 = 66 |
| CES18 = 56 | CES43 = 71 | CES68 = 72 | CES93 = 81 |
| CES19 = 72 | CES44 = 98 | CES69 = 82 | CES94 = 55 |
| CES20 = 65 | CES45 = 80 | CES70 = 61 | CES95 = 73 |
| CES21 = 86 | CES46 = 76 | CES71 = 59 | CES96 = 78 |
| CES22 = 78 | CES47 = 71 | CES72 = 86 | CES97 = 83 |
| CES23 = 92 | CES48 = 61 | CES73 = 52 | CES98 = 72 |
| CES24 = 91 | CES49 = 76 | CES74 = 93 | CES99 = 60 |
| CES25 = 72 | CES50 = 84 | CES75 = 56 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)