

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065333

Luminaire Tested: **GLAN-SA6A-760-U-LBC**

Issue Date: 08/07/2025



Test Information

Test Method: LM-79-08
Report Number: P1065333
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA6A-760-U-LBC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 6xLight Square PACKAGE
70CRI 5700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL
Light Source: (84) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19530.3 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G3

Input Watts (W): 162.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1065333
 CATALOG NUMBER: GLAN-SA6A-760-U-LBC

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 34 fc
 Type III - Short - N/A

REPORT NUMBER: P1065333
CATALOG NUMBER: GLAN-SA6A-760-U-LBC

Luminous Intensity Polar Plot



REPORT NUMBER: P1065333

CATALOG NUMBER: GLAN-SA6A-760-U-LBC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	133.4	0.0	133.4
	% Fixture	0.7	0.0	0.7
Street Side	Lumens	19396.9	0.0	19396.9
	% Fixture	99.3	0.0	99.3
Total	Lumens	19530.3	0.0	19530.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.6	0.0
10°-20°	42.8	0.2
20°-30°	462.7	2.4
30°-40°	1368.3	7.0
40°-50°	4078.2	20.9
50°-60°	6471.2	33.1
60°-70°	5397.7	27.6
70°-80°	1664.7	8.5
80°-90°	37.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19530.3	100.0
0°-180°	19530.3	100.0



REPORT NUMBER: P1065333


CATALOG NUMBER: GLAN-SA6A-760-U-LBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	500.1	2.6			
FM	(30°-60°)	11844.7	60.6			
FH	(60°-80°)	7016.9	35.9			G3/7500
FVH	(80°-90°)	35.2	0.2			G1/100
BL	(0°-30°)	13.0	0.1	B0/110		
BM	(30°-60°)	73.0	0.4	B0/220		
BH	(60°-80°)	45.5	0.2	B0/110		G0/110
BVH	(80°-90°)	1.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G3

Type III Short





REPORT NUMBER: P1065333

CATALOG NUMBER: GLAN-SA6A-760-U-LBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6
2.5°	110.7	110.7	106.2	100.3	94.4	88.5	87.0	84.1	82.6	81.1	79.7
5°	115.1	115.1	113.6	109.2	103.3	98.8	98.8	94.4	91.5	88.5	85.6
7.5°	118.0	119.5	122.5	121.0	118.0	113.6	113.6	110.7	106.2	98.8	94.4
10°	122.5	126.9	132.8	135.7	137.2	137.2	135.7	134.3	126.9	116.6	104.7
12.5°	126.9	135.7	150.5	165.2	174.1	185.9	184.4	181.5	162.3	140.2	119.5
15°	135.7	149.0	180.0	222.8	289.2	330.5	346.7	332.0	268.5	188.8	138.7
17.5°	146.1	168.2	261.1	466.2	764.2	905.9	991.4	922.1	610.8	358.5	174.1
20°	156.4	205.1	485.4	1208.3	1982.9	2446.1	2574.5	2373.8	1524.0	683.1	258.2
22.5°	174.1	287.7	984.1	2497.8	4272.6	4967.5	5098.8	4457.0	2878.4	1348.5	388.0
25°	211.0	417.5	1696.6	4070.5	6376.5	7549.4	7494.8	6653.8	4669.5	2154.0	590.1
27.5°	264.1	607.8	2565.6	5783.4	8391.8	9426.0	9549.9	8509.8	6224.5	3167.6	838.0
30°	340.8	842.4	3498.0	7155.4	10007.3	11125.6	11146.2	10070.7	7615.7	4057.2	1141.9
32.5°	414.6	1063.7	4313.9	8481.8	11599.2	12825.2	12916.7	11593.3	8654.4	4983.7	1406.0
35°	470.6	1208.3	5140.1	9647.3	13204.4	14893.6	14887.7	13316.5	9884.8	5811.4	1771.9
37.5°	475.1	1352.9	5888.1	10839.4	15237.4	17128.8	17316.1	15584.1	11372.0	6835.3	2220.4
40°	464.7	1515.2	6835.3	12698.3	18900.7	21802.7	21967.9	19784.4	14355.1	8588.0	2921.2
42.5°	476.5	1797.0	8372.6	16131.4	24983.5	29151.4	29470.1	27174.4	19839.0	12164.2	4170.8
45°	538.5	2326.6	11593.3	21875.0	33654.1	38735.2	38629.0	35322.8	26219.9	17608.3	6643.5
47.5°	743.6	3623.5	16367.5	27465.1	39195.5	43720.4	43811.9	39770.9	29943.6	21793.8	9973.3
50°	1143.4	5544.4	20379.0	30420.2	41578.2	46117.9	46032.3	41362.8	31358.5	23854.9	12013.8
52.5°	1487.1	6934.1	22391.3	31457.4	41883.6	47302.6	47296.7	41781.8	31578.3	24031.9	12269.0
55°	1572.7	7038.9	22407.6	31513.4	42568.2	48853.2	49047.9	42813.1	31863.1	23258.8	11308.5
57.5°	1538.8	6231.9	21472.2	31838.0	43786.8	50052.6	50063.0	43811.9	32586.0	22785.3	9718.1
58°	1509.3	6105.0	21283.4	32022.4	43996.3	50102.8	50077.7	43857.6	33174.7	22767.6	9468.8
60°	1344.0	5300.9	20547.2	32493.0	43685.0	49073.0	48838.4	42858.8	33087.6	22586.1	8213.3
62.5°	1056.3	4135.4	19822.8	31948.6	40347.8	44087.8	44185.2	37944.5	30163.5	21528.3	6733.5
65°	840.9	3082.0	18312.0	28024.2	33224.8	36205.0	36568.0	30855.4	25176.8	18229.4	4964.5
67.5°	669.8	2227.8	15361.3	22311.7	26290.7	30216.6	30480.7	25905.6	19505.6	13967.1	3527.6
70°	544.4	1506.3	10603.3	16317.3	21684.7	26098.9	26115.1	21520.9	14558.7	9151.6	2213.0
72.5°	482.4	1043.1	6155.1	11900.1	17583.2	21267.1	20837.8	17463.7	11189.0	5420.4	1319.0
75°	417.5	691.9	3018.6	7274.9	10660.9	10733.1	10896.9	8101.1	5593.0	2577.4	790.8
77.5°	343.8	491.3	1189.1	1987.3	3197.1	4092.6	4244.6	3216.3	1860.4	634.4	421.9
80°	236.1	233.1	320.2	609.3	914.7	1146.3	1069.6	827.7	486.9	243.4	150.5
82.5°	101.8	110.7	144.6	174.1	141.6	137.2	131.3	84.1	64.9	50.2	31.0
85°	32.5	29.5	31.0	31.0	25.1	19.2	19.2	8.9	0.0	0.0	0.0
87.5°	16.2	13.3	13.3	11.8	7.4	3.0	1.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065333

CATALOG NUMBER: GLAN-SA6A-760-U-LBC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6
2.5°	78.2	78.2	75.2	72.3	70.8	67.9	66.4	64.9	63.4	62.0	60.5
5°	82.6	81.1	76.7	72.3	67.9	63.4	60.5	57.5	54.6	53.1	51.6
7.5°	90.0	87.0	78.2	70.8	64.9	59.0	56.1	51.6	48.7	44.3	42.8
10°	98.8	92.9	81.1	72.3	63.4	56.1	51.6	47.2	42.8	36.9	35.4
12.5°	110.7	100.3	85.6	70.8	60.5	51.6	47.2	41.3	36.9	32.5	29.5
15°	121.0	107.7	87.0	70.8	57.5	47.2	41.3	35.4	31.0	25.1	22.1
17.5°	135.7	113.6	85.6	66.4	53.1	41.3	35.4	31.0	23.6	14.8	11.8
20°	160.8	118.0	82.6	62.0	45.7	33.9	26.6	20.7	10.3	3.0	0.0
22.5°	200.6	129.8	79.7	56.1	39.8	26.6	17.7	7.4	0.0	0.0	0.0
25°	277.4	150.5	79.7	53.1	35.4	19.2	5.9	0.0	0.0	0.0	0.0
27.5°	368.8	178.5	79.7	45.7	28.0	10.3	0.0	0.0	0.0	0.0	0.0
30°	461.8	209.5	79.7	39.8	22.1	1.5	0.0	0.0	0.0	0.0	0.0
32.5°	550.3	236.1	81.1	33.9	14.8	0.0	0.0	0.0	0.0	0.0	0.0
35°	640.3	240.5	79.7	29.5	8.9	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	755.4	231.6	75.2	26.6	4.4	0.0	0.0	0.0	0.0	0.0	0.0
40°	929.5	236.1	70.8	25.1	1.5	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	1251.1	255.2	64.9	25.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	2162.9	342.3	59.0	26.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	3577.7	615.2	57.5	26.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	4566.2	774.6	60.5	28.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	4558.8	863.1	63.4	29.5	5.9	0.0	0.0	0.0	0.0	0.0	0.0
55°	4052.8	879.3	67.9	32.5	19.2	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	3387.4	802.6	78.2	39.8	35.4	0.0	0.0	0.0	0.0	0.0	0.0
58°	3269.4	767.2	81.1	41.3	38.4	0.0	0.0	0.0	0.0	0.0	0.0
60°	2679.2	625.5	103.3	51.6	51.6	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	1850.1	545.9	118.0	66.4	53.1	0.0	0.0	0.0	0.0	0.0	0.0
65°	1308.6	492.8	128.4	70.8	42.8	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	978.2	454.4	141.6	72.3	22.1	0.0	0.0	0.0	0.0	0.0	0.0
70°	749.5	426.4	174.1	76.7	5.9	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	610.8	393.9	211.0	79.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	506.0	355.6	203.6	87.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	336.4	275.9	185.9	87.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	118.0	109.2	144.6	76.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	17.7	14.8	20.7	26.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065333

CATALOG NUMBER: GLAN-SA6A-760-U-LBC

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6
2.5°	60.5	60.5	59.0	60.5	60.5	63.4	70.8	81.1	92.9	97.4	101.8
5°	50.2	48.7	47.2	47.2	47.2	51.6	57.5	69.3	82.6	88.5	91.5
7.5°	41.3	39.8	38.4	36.9	36.9	39.8	47.2	60.5	73.8	79.7	84.1
10°	33.9	31.0	29.5	28.0	28.0	31.0	38.4	51.6	66.4	72.3	78.2
12.5°	28.0	23.6	20.7	19.2	17.7	22.1	29.5	41.3	57.5	64.9	70.8
15°	19.2	14.8	10.3	8.9	7.4	11.8	19.2	32.5	48.7	57.5	63.4
17.5°	10.3	4.4	1.5	0.0	0.0	3.0	8.9	23.6	39.8	47.2	54.6
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	11.8	29.5	36.9	44.3
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.5	17.7	25.1	32.5
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.4	13.3	19.2
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	3.0	8.9
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.9	11.8	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065333

CATALOG NUMBER: GLAN-SA6A-760-U-LBC

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	316°	325°	335°	345°	355°	360°
0°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6
2.5°	104.7	103.3	100.3	97.4	97.4	97.4	101.8	106.2	110.7	110.7
5°	97.4	97.4	95.9	92.9	92.9	94.4	100.3	107.7	113.6	115.1
7.5°	90.0	92.9	90.0	88.5	90.0	91.5	97.4	106.2	115.1	118.0
10°	85.6	87.0	87.0	85.6	85.6	88.5	94.4	106.2	118.0	122.5
12.5°	79.7	82.6	81.1	81.1	81.1	84.1	91.5	104.7	121.0	126.9
15°	73.8	78.2	78.2	76.7	76.7	78.2	88.5	103.3	125.4	135.7
17.5°	67.9	72.3	73.8	70.8	70.8	73.8	84.1	103.3	128.4	146.1
20°	56.1	63.4	67.9	63.4	63.4	66.4	76.7	97.4	129.8	156.4
22.5°	44.3	51.6	57.5	56.1	56.1	57.5	70.8	92.9	131.3	174.1
25°	32.5	39.8	44.3	47.2	47.2	51.6	64.9	90.0	137.2	211.0
27.5°	19.2	28.0	33.9	36.9	38.4	44.3	60.5	87.0	147.5	264.1
30°	8.9	16.2	23.6	29.5	29.5	39.8	56.1	84.1	160.8	340.8
32.5°	0.0	7.4	11.8	20.7	22.1	32.5	51.6	81.1	180.0	414.6
35°	0.0	0.0	5.9	16.2	16.2	26.6	47.2	78.2	209.5	470.6
37.5°	0.0	0.0	0.0	11.8	13.3	23.6	45.7	76.7	215.4	475.1
40°	0.0	0.0	0.0	8.9	10.3	22.1	45.7	78.2	194.7	464.7
42.5°	0.0	0.0	0.0	5.9	7.4	22.1	45.7	81.1	175.6	476.5
45°	0.0	0.0	0.0	4.4	5.9	23.6	44.3	79.7	165.2	538.5
47.5°	0.0	0.0	0.0	5.9	8.9	23.6	42.8	78.2	166.7	743.6
50°	0.0	0.0	0.0	7.4	10.3	23.6	44.3	75.2	182.9	1143.4
52.5°	0.0	0.0	0.0	5.9	8.9	26.6	48.7	73.8	199.2	1487.1
55°	0.0	0.0	0.0	1.5	4.4	33.9	53.1	73.8	224.3	1572.7
57.5°	0.0	0.0	0.0	0.0	0.0	38.4	60.5	78.2	265.6	1538.8
58°	0.0	0.0	0.0	0.0	0.0	38.4	62.0	78.2	268.5	1509.3
60°	0.0	0.0	0.0	0.0	0.0	38.4	67.9	87.0	289.2	1344.0
62.5°	0.0	0.0	0.0	0.0	0.0	32.5	81.1	109.2	301.0	1056.3
65°	0.0	0.0	0.0	0.0	0.0	26.6	95.9	119.5	309.8	840.9
67.5°	0.0	0.0	0.0	0.0	0.0	25.1	98.8	121.0	314.2	669.8
70°	0.0	0.0	0.0	0.0	0.0	26.6	97.4	129.8	329.0	544.4
72.5°	0.0	0.0	0.0	0.0	0.0	29.5	88.5	143.1	329.0	482.4
75°	0.0	0.0	0.0	0.0	0.0	31.0	82.6	160.8	299.5	417.5
77.5°	0.0	0.0	0.0	0.0	0.0	29.5	81.1	187.4	267.0	343.8
80°	3.0	4.4	4.4	3.0	3.0	25.1	79.7	190.3	227.2	236.1
82.5°	8.9	11.8	10.3	7.4	7.4	22.1	70.8	159.3	118.0	101.8
85°	16.2	19.2	19.2	16.2	16.2	20.7	44.3	57.5	39.8	32.5
87.5°	22.1	25.1	25.1	22.1	22.1	20.7	19.2	17.7	16.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength

Melanopic Lumens: NR
M/P: 3.71


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7





TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE R_a = 69.9$
 $R_g = -35.4$







Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin


Measure Comparisons


(END OF REPORT)