

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065342

Luminaire Tested: **GLAN-SA8B-760-U-LBC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1065342
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA8B-760-U-LBC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 8xLight Square PACKAGE
70CRI 5700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL
Light Source: (112) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 32742.8 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 282.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1065342
 CATALOG NUMBER: GLAN-SA8B-760-U-LBC

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 57 fc
 Type III - Short - N/A

REPORT NUMBER: P1065342
CATALOG NUMBER: GLAN-SA8B-760-U-LBC

Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P1065342

CATALOG NUMBER: GLAN-SA8B-760-U-LBC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	223.6	0.0	223.6
	% Fixture	0.7	0.0	0.7
Street Side	Lumens	32519.2	0.0	32519.2
	% Fixture	99.3	0.0	99.3
Total	Lumens	32742.8	0.0	32742.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.8	0.0
10°-20°	71.8	0.2
20°-30°	775.7	2.4
30°-40°	2294.0	7.0
40°-50°	6837.2	20.9
50°-60°	10849.0	33.1
60°-70°	9049.4	27.6
70°-80°	2791.0	8.5
80°-90°	62.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	32742.8	100.0
0°-180°	32742.8	100.0



REPORT NUMBER: P1065342


CATALOG NUMBER: GLAN-SA8B-760-U-LBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	838.4	2.6			
FM	(30°-60°)	19857.8	60.6			
FH	(60°-80°)	11764.0	35.9			G4/12000
FVH	(80°-90°)	59.0	0.2			G1/100
BL	(0°-30°)	21.9	0.1	B0/110		
BM	(30°-60°)	122.4	0.4	B0/220		
BH	(60°-80°)	76.3	0.2	B0/110		G0/110
BVH	(80°-90°)	3.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type III Short





REPORT NUMBER: P1065342

CATALOG NUMBER: GLAN-SA8B-760-U-LBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5
2.5°	185.5	185.5	178.1	168.2	158.3	148.4	145.9	141.0	138.5	136.0	133.6
5°	192.9	192.9	190.5	183.0	173.1	165.7	165.7	158.3	153.4	148.4	143.5
7.5°	197.9	200.3	205.3	202.8	197.9	190.5	190.5	185.5	178.1	165.7	158.3
10°	205.3	212.7	222.6	227.6	230.0	230.0	227.6	225.1	212.7	195.4	175.6
12.5°	212.7	227.6	252.3	277.0	291.9	311.7	309.2	304.2	272.1	235.0	200.3
15°	227.6	249.8	301.8	373.5	484.8	554.1	581.3	556.5	450.2	316.6	232.5
17.5°	244.9	282.0	437.8	781.6	1281.2	1518.7	1662.2	1545.9	1024.0	601.0	291.9
20°	262.2	343.8	813.8	2025.7	3324.3	4101.0	4316.1	3979.8	2555.1	1145.2	432.9
22.5°	291.9	482.3	1649.8	4187.5	7163.1	8328.1	8548.2	7472.3	4825.7	2260.7	650.5
25°	353.7	700.0	2844.5	6824.2	10690.2	12656.6	12565.1	11155.2	7828.4	3611.2	989.4
27.5°	442.7	1019.1	4301.3	9695.9	14068.9	15802.8	16010.6	14266.8	10435.4	5310.5	1404.9
30°	571.4	1412.3	5864.5	11996.2	16777.3	18652.2	18686.8	16883.7	12767.9	6802.0	1914.4
32.5°	695.0	1783.3	7232.3	14219.8	19446.2	21501.6	21655.0	19436.3	14509.2	8355.3	2357.2
35°	789.0	2025.7	8617.5	16173.8	22137.3	24969.4	24959.5	22325.3	16572.0	9742.9	2970.6
37.5°	796.4	2268.1	9871.5	18172.3	25545.7	28716.6	29030.7	26126.9	19065.3	11459.4	3722.5
40°	779.1	2540.2	11459.4	21288.9	31687.2	36552.5	36829.5	33168.8	24066.6	14397.9	4897.4
42.5°	798.9	3012.6	14036.8	27044.6	41885.2	48872.7	49406.9	45558.3	33260.3	20393.5	6992.4
45°	902.8	3900.6	19436.3	36673.7	56421.6	64940.1	64762.0	59219.1	43957.9	29520.5	11137.9
47.5°	1246.6	6074.8	27440.3	46045.5	65711.8	73297.9	73451.2	66676.5	50200.9	36537.6	16720.4
50°	1916.9	9295.2	34165.6	50999.8	69706.4	77317.2	77173.7	69345.3	52572.9	39993.0	20141.2
52.5°	2493.2	11625.2	37539.4	52738.6	70218.4	79303.4	79293.5	70047.8	52941.5	40289.8	20569.1
55°	2636.7	11800.8	37566.6	52832.6	71366.1	81903.0	82229.5	71776.7	53418.8	38993.8	18958.9
57.5°	2579.8	10447.8	35998.4	53376.8	73409.2	83913.9	83931.2	73451.2	54630.8	38199.8	16292.5
58°	2530.3	10235.1	35681.8	53686.0	73760.4	83998.0	83955.9	73527.9	55617.7	38170.1	15874.5
60°	2253.3	8887.1	34447.6	54475.0	73238.5	82271.5	81878.2	71853.4	55471.8	37865.9	13769.6
62.5°	1771.0	6933.0	33233.1	53562.3	67643.6	73913.8	74077.0	63614.4	50569.4	36092.4	11288.8
65°	1409.9	5167.0	30700.3	46983.0	55701.8	60698.2	61306.6	51729.5	42209.2	30561.8	8323.1
67.5°	1122.9	3734.9	25753.4	37405.8	44076.7	50658.5	51101.2	43431.1	32701.3	23416.0	5914.0
70°	912.7	2525.4	17776.6	27356.2	36354.6	43755.1	43782.3	36080.0	24407.9	15342.7	3710.2
72.5°	808.8	1748.7	10319.2	19950.8	29478.4	35654.6	34934.8	29278.1	18758.6	9087.4	2211.3
75°	700.0	1160.0	5060.7	12196.5	17873.1	17994.3	18268.8	13581.6	9376.8	4321.1	1325.8
77.5°	576.3	823.7	1993.6	3331.7	5359.9	6861.3	7116.1	5392.1	3119.0	1063.6	707.4
80°	395.8	390.8	536.7	1021.5	1533.5	1921.9	1793.2	1387.6	816.2	408.1	252.3
82.5°	170.7	185.5	242.4	291.9	237.5	230.0	220.1	141.0	108.8	84.1	51.9
85°	54.4	49.5	51.9	51.9	42.0	32.2	32.2	14.8	0.0	0.0	0.0
87.5°	27.2	22.3	22.3	19.8	12.4	4.9	2.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1065342

CATALOG NUMBER: GLAN-SA8B-760-U-LBC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5
2.5°	131.1	131.1	126.1	121.2	118.7	113.8	111.3	108.8	106.4	103.9	101.4
5°	138.5	136.0	128.6	121.2	113.8	106.4	101.4	96.5	91.5	89.0	86.6
7.5°	150.9	145.9	131.1	118.7	108.8	98.9	94.0	86.6	81.6	74.2	71.7
10°	165.7	155.8	136.0	121.2	106.4	94.0	86.6	79.2	71.7	61.8	59.4
12.5°	185.5	168.2	143.5	118.7	101.4	86.6	79.2	69.3	61.8	54.4	49.5
15°	202.8	180.6	145.9	118.7	96.5	79.2	69.3	59.4	51.9	42.0	37.1
17.5°	227.6	190.5	143.5	111.3	89.0	69.3	59.4	51.9	39.6	24.7	19.8
20°	269.6	197.9	138.5	103.9	76.7	56.9	44.5	34.6	17.3	4.9	0.0
22.5°	336.4	217.7	133.6	94.0	66.8	44.5	29.7	12.4	0.0	0.0	0.0
25°	465.0	252.3	133.6	89.0	59.4	32.2	9.9	0.0	0.0	0.0	0.0
27.5°	618.4	299.3	133.6	76.7	47.0	17.3	0.0	0.0	0.0	0.0	0.0
30°	774.2	351.2	133.6	66.8	37.1	2.5	0.0	0.0	0.0	0.0	0.0
32.5°	922.6	395.8	136.0	56.9	24.7	0.0	0.0	0.0	0.0	0.0	0.0
35°	1073.5	403.2	133.6	49.5	14.8	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	1266.4	388.3	126.1	44.5	7.4	0.0	0.0	0.0	0.0	0.0	0.0
40°	1558.3	395.8	118.7	42.0	2.5	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	2097.5	427.9	108.8	42.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	3626.1	573.8	98.9	44.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	5998.1	1031.4	96.5	44.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	7655.3	1298.6	101.4	47.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	7642.9	1447.0	106.4	49.5	9.9	0.0	0.0	0.0	0.0	0.0	0.0
55°	6794.5	1474.2	113.8	54.4	32.2	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	5679.0	1345.6	131.1	66.8	59.4	0.0	0.0	0.0	0.0	0.0	0.0
58°	5481.1	1286.2	136.0	69.3	64.3	0.0	0.0	0.0	0.0	0.0	0.0
60°	4491.8	1048.7	173.1	86.6	86.6	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	3101.7	915.2	197.9	111.3	89.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	2193.9	826.1	215.2	118.7	71.7	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	1639.9	761.8	237.5	121.2	37.1	0.0	0.0	0.0	0.0	0.0	0.0
70°	1256.5	714.8	291.9	128.6	9.9	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1024.0	660.4	353.7	133.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	848.4	596.1	341.3	145.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	563.9	462.5	311.7	145.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	197.9	183.0	242.4	128.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	29.7	24.7	34.6	44.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1065342

CATALOG NUMBER: GLAN-SA8B-760-U-LBC

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5
2.5°	101.4	101.4	98.9	101.4	101.4	106.4	118.7	136.0	155.8	163.2	170.7
5°	84.1	81.6	79.2	79.2	79.2	86.6	96.5	116.3	138.5	148.4	153.4
7.5°	69.3	66.8	64.3	61.8	61.8	66.8	79.2	101.4	123.7	133.6	141.0
10°	56.9	51.9	49.5	47.0	47.0	51.9	64.3	86.6	111.3	121.2	131.1
12.5°	47.0	39.6	34.6	32.2	29.7	37.1	49.5	69.3	96.5	108.8	118.7
15°	32.2	24.7	17.3	14.8	12.4	19.8	32.2	54.4	81.6	96.5	106.4
17.5°	17.3	7.4	2.5	0.0	0.0	4.9	14.8	39.6	66.8	79.2	91.5
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	19.8	49.5	61.8	74.2
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.5	29.7	42.0	54.4
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	12.4	22.3	32.2
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.9	14.8
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.4	14.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.9	19.8	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065342

CATALOG NUMBER: GLAN-SA8B-760-U-LBC

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	316°	325°	335°	345°	355°	360°
0°	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5	143.5
2.5°	175.6	173.1	168.2	163.2	163.2	163.2	170.7	178.1	185.5	185.5
5°	163.2	163.2	160.8	155.8	155.8	158.3	168.2	180.6	190.5	192.9
7.5°	150.9	155.8	150.9	148.4	150.9	153.4	163.2	178.1	192.9	197.9
10°	143.5	145.9	145.9	143.5	143.5	148.4	158.3	178.1	197.9	205.3
12.5°	133.6	138.5	136.0	136.0	136.0	141.0	153.4	175.6	202.8	212.7
15°	123.7	131.1	131.1	128.6	128.6	131.1	148.4	173.1	210.2	227.6
17.5°	113.8	121.2	123.7	118.7	118.7	123.7	141.0	173.1	215.2	244.9
20°	94.0	106.4	113.8	106.4	106.4	111.3	128.6	163.2	217.7	262.2
22.5°	74.2	86.6	96.5	94.0	94.0	96.5	118.7	155.8	220.1	291.9
25°	54.4	66.8	74.2	79.2	79.2	86.6	108.8	150.9	230.0	353.7
27.5°	32.2	47.0	56.9	61.8	64.3	74.2	101.4	145.9	247.3	442.7
30°	14.8	27.2	39.6	49.5	49.5	66.8	94.0	141.0	269.6	571.4
32.5°	0.0	12.4	19.8	34.6	37.1	54.4	86.6	136.0	301.8	695.0
35°	0.0	0.0	9.9	27.2	27.2	44.5	79.2	131.1	351.2	789.0
37.5°	0.0	0.0	0.0	19.8	22.3	39.6	76.7	128.6	361.1	796.4
40°	0.0	0.0	0.0	14.8	17.3	37.1	76.7	131.1	326.5	779.1
42.5°	0.0	0.0	0.0	9.9	12.4	37.1	76.7	136.0	294.3	798.9
45°	0.0	0.0	0.0	7.4	9.9	39.6	74.2	133.6	277.0	902.8
47.5°	0.0	0.0	0.0	9.9	14.8	39.6	71.7	131.1	279.5	1246.6
50°	0.0	0.0	0.0	12.4	17.3	39.6	74.2	126.1	306.7	1916.9
52.5°	0.0	0.0	0.0	9.9	14.8	44.5	81.6	123.7	333.9	2493.2
55°	0.0	0.0	0.0	2.5	7.4	56.9	89.0	123.7	376.0	2636.7
57.5°	0.0	0.0	0.0	0.0	0.0	64.3	101.4	131.1	445.2	2579.8
58°	0.0	0.0	0.0	0.0	0.0	64.3	103.9	131.1	450.2	2530.3
60°	0.0	0.0	0.0	0.0	0.0	64.3	113.8	145.9	484.8	2253.3
62.5°	0.0	0.0	0.0	0.0	0.0	54.4	136.0	183.0	504.6	1771.0
65°	0.0	0.0	0.0	0.0	0.0	44.5	160.8	200.3	519.4	1409.9
67.5°	0.0	0.0	0.0	0.0	0.0	42.0	165.7	202.8	526.8	1122.9
70°	0.0	0.0	0.0	0.0	0.0	44.5	163.2	217.7	551.6	912.7
72.5°	0.0	0.0	0.0	0.0	0.0	49.5	148.4	239.9	551.6	808.8
75°	0.0	0.0	0.0	0.0	0.0	51.9	138.5	269.6	502.1	700.0
77.5°	0.0	0.0	0.0	0.0	0.0	49.5	136.0	314.1	447.7	576.3
80°	4.9	7.4	7.4	4.9	4.9	42.0	133.6	319.1	380.9	395.8
82.5°	14.8	19.8	17.3	12.4	12.4	37.1	118.7	267.1	197.9	170.7
85°	27.2	32.2	32.2	27.2	27.2	34.6	74.2	96.5	66.8	54.4
87.5°	37.1	42.0	42.0	37.1	37.1	34.6	32.2	29.7	27.2	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7





TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $\text{CIE } R_a = 69.9$
 $R_g = -35.4$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)