

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065283

Luminaire Tested: **GLAN-SA2C-750-U-LBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065283  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA2C-750-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 2xLight Square PACKAGE  
70CRI 5000K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (28) 5000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10403.2 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 96.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1065283

CATALOG NUMBER: GLAN-SA2C-750-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 18.1 fc

Type III - Short - N/A

REPORT NUMBER: P1065283  
CATALOG NUMBER: GLAN-SA2C-750-U-LBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1065283

CATALOG NUMBER: GLAN-SA2C-750-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 71.0     | 0.0    | 71.0    |
|                    | % Fixture | 0.7      | 0.0    | 0.7     |
| <b>Street Side</b> | Lumens    | 10332.2  | 0.0    | 10332.2 |
|                    | % Fixture | 99.3     | 0.0    | 99.3    |
| <b>Total</b>       | Lumens    | 10403.2  | 0.0    | 10403.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 4.1     | 0.0       |
| 10°-20°   | 22.8    | 0.2       |
| 20°-30°   | 246.5   | 2.4       |
| 30°-40°   | 728.8   | 7.0       |
| 40°-50°   | 2172.4  | 20.9      |
| 50°-60°   | 3447.0  | 33.1      |
| 60°-70°   | 2875.2  | 27.6      |
| 70°-80°   | 886.8   | 8.5       |
| 80°-90°   | 19.7    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 10403.2 | 100.0     |
| 0°-180°   | 10403.2 | 100.0     |



REPORT NUMBER: P1065283


CATALOG NUMBER: GLAN-SA2C-750-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 266.4  | 2.6       |                         |      |         |
| FM   | (30°-60°)   | 6309.3 | 60.6      |                         |      |         |
| FH   | (60°-80°)   | 3737.7 | 35.9      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 18.7   | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 6.9    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 38.9   | 0.4       | B0/220                  |      |         |
| BH   | (60°-80°)   | 24.3   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 1.0    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1065283

CATALOG NUMBER: GLAN-SA2C-750-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°     | 15°     | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°     |
|-------|-------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 45.6  | 45.6   | 45.6    | 45.6    | 45.6    | 45.6    | 45.6    | 45.6    | 45.6    | 45.6    |
| 2.5°  | 58.9  | 58.9   | 56.6    | 53.4    | 50.3    | 47.2    | 46.4    | 44.8    | 44.0    | 43.2    |
| 5°    | 61.3  | 61.3   | 60.5    | 58.2    | 55.0    | 52.7    | 52.7    | 50.3    | 48.7    | 47.2    |
| 7.5°  | 62.9  | 63.7   | 65.2    | 64.4    | 62.9    | 60.5    | 60.5    | 58.9    | 56.6    | 52.7    |
| 10°   | 65.2  | 67.6   | 70.7    | 72.3    | 73.1    | 73.1    | 72.3    | 71.5    | 67.6    | 62.1    |
| 12.5° | 67.6  | 72.3   | 80.2    | 88.0    | 92.7    | 99.0    | 98.2    | 96.7    | 86.4    | 74.7    |
| 15°   | 72.3  | 79.4   | 95.9    | 118.7   | 154.0   | 176.0   | 184.7   | 176.8   | 143.0   | 100.6   |
| 17.5° | 77.8  | 89.6   | 139.1   | 248.3   | 407.1   | 482.5   | 528.1   | 491.2   | 325.4   | 191.0   |
| 20°   | 83.3  | 109.2  | 258.6   | 643.6   | 1056.2  | 1303.0  | 1371.4  | 1264.5  | 811.8   | 363.9   |
| 22.5° | 92.7  | 153.2  | 524.2   | 1330.5  | 2275.9  | 2646.0  | 2716.0  | 2374.1  | 1533.2  | 718.3   |
| 25°   | 112.4 | 222.4  | 903.8   | 2168.2  | 3396.5  | 4021.3  | 3992.2  | 3544.3  | 2487.3  | 1147.4  |
| 27.5° | 140.7 | 323.8  | 1366.6  | 3080.6  | 4470.1  | 5021.0  | 5087.0  | 4532.9  | 3315.6  | 1687.3  |
| 30°   | 181.5 | 448.7  | 1863.3  | 3811.5  | 5330.6  | 5926.3  | 5937.3  | 5364.4  | 4056.7  | 2161.2  |
| 32.5° | 220.8 | 566.6  | 2297.9  | 4518.0  | 6178.5  | 6831.6  | 6880.3  | 6175.4  | 4609.9  | 2654.7  |
| 35°   | 250.7 | 643.6  | 2738.0  | 5138.8  | 7033.6  | 7933.4  | 7930.3  | 7093.3  | 5265.4  | 3095.6  |
| 37.5° | 253.1 | 720.6  | 3136.4  | 5773.8  | 8116.5  | 9124.0  | 9223.8  | 8301.2  | 6057.5  | 3641.0  |
| 40°   | 247.6 | 807.1  | 3641.0  | 6764.0  | 10067.8 | 11613.7 | 11701.7 | 10538.6 | 7646.6  | 4574.6  |
| 42.5° | 253.8 | 957.2  | 4459.8  | 8592.8  | 13308.0 | 15528.1 | 15697.8 | 14475.0 | 10567.7 | 6479.5  |
| 45°   | 286.8 | 1239.3 | 6175.4  | 11652.2 | 17926.6 | 20633.1 | 20576.6 | 18815.4 | 13966.6 | 9379.4  |
| 47.5° | 396.1 | 1930.1 | 8718.5  | 14629.8 | 20878.3 | 23288.6 | 23337.3 | 21184.8 | 15950.1 | 11608.9 |
| 50°   | 609.1 | 2953.3 | 10855.3 | 16203.9 | 22147.5 | 24565.7 | 24520.1 | 22032.8 | 16703.8 | 12706.8 |
| 52.5° | 792.2 | 3693.6 | 11927.2 | 16756.4 | 22310.2 | 25196.7 | 25193.6 | 22256.0 | 16820.9 | 12801.1 |
| 55°   | 837.7 | 3749.4 | 11935.9 | 16786.3 | 22674.8 | 26022.7 | 26126.4 | 22805.3 | 16972.5 | 12389.3 |
| 57.5° | 819.7 | 3319.5 | 11437.6 | 16959.2 | 23324.0 | 26661.6 | 26667.1 | 23337.3 | 17357.6 | 12137.0 |
| 58°   | 803.9 | 3251.9 | 11337.0 | 17057.4 | 23435.6 | 26688.3 | 26674.9 | 23361.7 | 17671.2 | 12127.6 |
| 60°   | 715.9 | 2823.6 | 10944.9 | 17308.1 | 23269.7 | 26139.8 | 26014.8 | 22829.7 | 17624.8 | 12031.0 |
| 62.5° | 562.7 | 2202.8 | 10559.0 | 17018.1 | 21492.1 | 23484.3 | 23536.2 | 20211.9 | 16067.2 | 11467.5 |
| 65°   | 447.9 | 1641.7 | 9754.3  | 14927.7 | 17697.9 | 19285.4 | 19478.7 | 16435.8 | 13410.9 | 9710.3  |
| 67.5° | 356.8 | 1186.7 | 8182.5  | 11884.8 | 14004.3 | 16095.5 | 16236.2 | 13799.2 | 10390.0 | 7439.9  |
| 70°   | 290.0 | 802.4  | 5648.1  | 8691.8  | 11550.8 | 13902.1 | 13910.8 | 11463.6 | 7755.0  | 4874.8  |
| 72.5° | 257.0 | 555.6  | 3278.7  | 6338.9  | 9366.1  | 11328.4 | 11099.7 | 9302.4  | 5960.1  | 2887.3  |
| 75°   | 222.4 | 368.6  | 1607.9  | 3875.1  | 5678.7  | 5717.2  | 5804.5  | 4315.2  | 2979.3  | 1372.9  |
| 77.5° | 183.1 | 261.7  | 633.4   | 1058.6  | 1703.0  | 2180.0  | 2261.0  | 1713.2  | 991.0   | 337.9   |
| 80°   | 125.7 | 124.2  | 170.5   | 324.6   | 487.2   | 610.6   | 569.8   | 440.9   | 259.3   | 129.7   |
| 82.5° | 54.2  | 58.9   | 77.0    | 92.7    | 75.4    | 73.1    | 69.9    | 44.8    | 34.6    | 26.7    |
| 85°   | 17.3  | 15.7   | 16.5    | 16.5    | 13.4    | 10.2    | 10.2    | 4.7     | 0.0     | 0.0     |
| 87.5° | 8.6   | 7.1    | 7.1     | 6.3     | 3.9     | 1.6     | 0.8     | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065283

CATALOG NUMBER: GLAN-SA2C-750-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°    |       | 90°    | 95°   | 105°  | 115° | 125° | 135° | 145° | 155° | 165° | 175° |
|--------|-------|--------|-------|-------|------|------|------|------|------|------|------|
| 45.6   | 0°    | 45.6   | 45.6  | 45.6  | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 |
| 42.4   | 2.5°  | 41.7   | 41.7  | 40.1  | 38.5 | 37.7 | 36.2 | 35.4 | 34.6 | 33.8 | 33.0 |
| 45.6   | 5°    | 44.0   | 43.2  | 40.9  | 38.5 | 36.2 | 33.8 | 32.2 | 30.6 | 29.1 | 28.3 |
| 50.3   | 7.5°  | 47.9   | 46.4  | 41.7  | 37.7 | 34.6 | 31.4 | 29.9 | 27.5 | 25.9 | 23.6 |
| 55.8   | 10°   | 52.7   | 49.5  | 43.2  | 38.5 | 33.8 | 29.9 | 27.5 | 25.1 | 22.8 | 19.6 |
| 63.7   | 12.5° | 58.9   | 53.4  | 45.6  | 37.7 | 32.2 | 27.5 | 25.1 | 22.0 | 19.6 | 17.3 |
| 73.9   | 15°   | 64.4   | 57.4  | 46.4  | 37.7 | 30.6 | 25.1 | 22.0 | 18.9 | 16.5 | 13.4 |
| 92.7   | 17.5° | 72.3   | 60.5  | 45.6  | 35.4 | 28.3 | 22.0 | 18.9 | 16.5 | 12.6 | 7.9  |
| 137.5  | 20°   | 85.7   | 62.9  | 44.0  | 33.0 | 24.4 | 18.1 | 14.1 | 11.0 | 5.5  | 1.6  |
| 206.7  | 22.5° | 106.9  | 69.2  | 42.4  | 29.9 | 21.2 | 14.1 | 9.4  | 3.9  | 0.0  | 0.0  |
| 314.3  | 25°   | 147.7  | 80.2  | 42.4  | 28.3 | 18.9 | 10.2 | 3.1  | 0.0  | 0.0  | 0.0  |
| 446.4  | 27.5° | 196.5  | 95.1  | 42.4  | 24.4 | 14.9 | 5.5  | 0.0  | 0.0  | 0.0  | 0.0  |
| 608.3  | 30°   | 246.0  | 111.6 | 42.4  | 21.2 | 11.8 | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  |
| 748.9  | 32.5° | 293.1  | 125.7 | 43.2  | 18.1 | 7.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 943.8  | 35°   | 341.1  | 128.1 | 42.4  | 15.7 | 4.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1182.7 | 37.5° | 402.4  | 123.4 | 40.1  | 14.1 | 2.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1556.0 | 40°   | 495.1  | 125.7 | 37.7  | 13.4 | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2221.7 | 42.5° | 666.4  | 136.0 | 34.6  | 13.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3538.8 | 45°   | 1152.1 | 182.3 | 31.4  | 14.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 5312.5 | 47.5° | 1905.7 | 327.7 | 30.6  | 14.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 6399.4 | 50°   | 2432.3 | 412.6 | 32.2  | 14.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 6535.3 | 52.5° | 2428.4 | 459.7 | 33.8  | 15.7 | 3.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 6023.7 | 55°   | 2158.8 | 468.4 | 36.2  | 17.3 | 10.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 5176.6 | 57.5° | 1804.4 | 427.5 | 41.7  | 21.2 | 18.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 5043.7 | 58°   | 1741.5 | 408.7 | 43.2  | 22.0 | 20.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 4375.0 | 60°   | 1427.1 | 333.2 | 55.0  | 27.5 | 27.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3586.7 | 62.5° | 985.5  | 290.8 | 62.9  | 35.4 | 28.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2644.5 | 65°   | 697.1  | 262.5 | 68.4  | 37.7 | 22.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1879.0 | 67.5° | 521.0  | 242.0 | 75.4  | 38.5 | 11.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1178.8 | 70°   | 399.2  | 227.1 | 92.7  | 40.9 | 3.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 702.6  | 72.5° | 325.4  | 209.8 | 112.4 | 42.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 421.2  | 75°   | 269.6  | 189.4 | 108.5 | 46.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 224.8  | 77.5° | 179.2  | 147.0 | 99.0  | 46.4 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 80.2   | 80°   | 62.9   | 58.2  | 77.0  | 40.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 16.5   | 82.5° | 9.4    | 7.9   | 11.0  | 14.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 85°   | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 87.5° | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 90°   | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

REPORT NUMBER: P1065283

CATALOG NUMBER: GLAN-SA2C-750-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180° |       | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° |
|------|-------|------|------|------|------|------|------|------|------|------|------|
| 45.6 | 0°    | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 |
| 32.2 | 2.5°  | 32.2 | 32.2 | 31.4 | 32.2 | 32.2 | 33.8 | 37.7 | 43.2 | 49.5 | 51.9 |
| 27.5 | 5°    | 26.7 | 25.9 | 25.1 | 25.1 | 25.1 | 27.5 | 30.6 | 36.9 | 44.0 | 47.2 |
| 22.8 | 7.5°  | 22.0 | 21.2 | 20.4 | 19.6 | 19.6 | 21.2 | 25.1 | 32.2 | 39.3 | 42.4 |
| 18.9 | 10°   | 18.1 | 16.5 | 15.7 | 14.9 | 14.9 | 16.5 | 20.4 | 27.5 | 35.4 | 38.5 |
| 15.7 | 12.5° | 14.9 | 12.6 | 11.0 | 10.2 | 9.4  | 11.8 | 15.7 | 22.0 | 30.6 | 34.6 |
| 11.8 | 15°   | 10.2 | 7.9  | 5.5  | 4.7  | 3.9  | 6.3  | 10.2 | 17.3 | 25.9 | 30.6 |
| 6.3  | 17.5° | 5.5  | 2.4  | 0.8  | 0.0  | 0.0  | 1.6  | 4.7  | 12.6 | 21.2 | 25.1 |
| 0.0  | 20°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 6.3  | 15.7 | 19.6 |
| 0.0  | 22.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.8  | 9.4  | 13.4 |
| 0.0  | 25°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 3.9  | 7.1  |
| 0.0  | 27.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.6  |
| 0.0  | 30°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 32.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 35°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 80°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 82.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 85°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 2.4  |
| 0.0  | 87.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 3.1  | 6.3  |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P1065283

CATALOG NUMBER: GLAN-SA2C-750-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275° |       | 285° | 295° | 305° | 315° | 316° | 325° | 335° | 345°  | 355°  | 360°  |
|------|-------|------|------|------|------|------|------|------|-------|-------|-------|
| 45.6 | 0°    | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6 | 45.6  | 45.6  | 45.6  |
| 54.2 | 2.5°  | 55.8 | 55.0 | 53.4 | 51.9 | 51.9 | 51.9 | 54.2 | 56.6  | 58.9  | 58.9  |
| 48.7 | 5°    | 51.9 | 51.9 | 51.1 | 49.5 | 49.5 | 50.3 | 53.4 | 57.4  | 60.5  | 61.3  |
| 44.8 | 7.5°  | 47.9 | 49.5 | 47.9 | 47.2 | 47.9 | 48.7 | 51.9 | 56.6  | 61.3  | 62.9  |
| 41.7 | 10°   | 45.6 | 46.4 | 46.4 | 45.6 | 45.6 | 47.2 | 50.3 | 56.6  | 62.9  | 65.2  |
| 37.7 | 12.5° | 42.4 | 44.0 | 43.2 | 43.2 | 43.2 | 44.8 | 48.7 | 55.8  | 64.4  | 67.6  |
| 33.8 | 15°   | 39.3 | 41.7 | 41.7 | 40.9 | 40.9 | 41.7 | 47.2 | 55.0  | 66.8  | 72.3  |
| 29.1 | 17.5° | 36.2 | 38.5 | 39.3 | 37.7 | 37.7 | 39.3 | 44.8 | 55.0  | 68.4  | 77.8  |
| 23.6 | 20°   | 29.9 | 33.8 | 36.2 | 33.8 | 33.8 | 35.4 | 40.9 | 51.9  | 69.2  | 83.3  |
| 17.3 | 22.5° | 23.6 | 27.5 | 30.6 | 29.9 | 29.9 | 30.6 | 37.7 | 49.5  | 69.9  | 92.7  |
| 10.2 | 25°   | 17.3 | 21.2 | 23.6 | 25.1 | 25.1 | 27.5 | 34.6 | 47.9  | 73.1  | 112.4 |
| 4.7  | 27.5° | 10.2 | 14.9 | 18.1 | 19.6 | 20.4 | 23.6 | 32.2 | 46.4  | 78.6  | 140.7 |
| 0.0  | 30°   | 4.7  | 8.6  | 12.6 | 15.7 | 15.7 | 21.2 | 29.9 | 44.8  | 85.7  | 181.5 |
| 0.0  | 32.5° | 0.0  | 3.9  | 6.3  | 11.0 | 11.8 | 17.3 | 27.5 | 43.2  | 95.9  | 220.8 |
| 0.0  | 35°   | 0.0  | 0.0  | 3.1  | 8.6  | 8.6  | 14.1 | 25.1 | 41.7  | 111.6 | 250.7 |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 6.3  | 7.1  | 12.6 | 24.4 | 40.9  | 114.7 | 253.1 |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 4.7  | 5.5  | 11.8 | 24.4 | 41.7  | 103.7 | 247.6 |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 3.1  | 3.9  | 11.8 | 24.4 | 43.2  | 93.5  | 253.8 |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 2.4  | 3.1  | 12.6 | 23.6 | 42.4  | 88.0  | 286.8 |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 3.1  | 4.7  | 12.6 | 22.8 | 41.7  | 88.8  | 396.1 |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 3.9  | 5.5  | 12.6 | 23.6 | 40.1  | 97.4  | 609.1 |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 3.1  | 4.7  | 14.1 | 25.9 | 39.3  | 106.1 | 792.2 |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.8  | 2.4  | 18.1 | 28.3 | 39.3  | 119.5 | 837.7 |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 20.4 | 32.2 | 41.7  | 141.5 | 819.7 |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 20.4 | 33.0 | 41.7  | 143.0 | 803.9 |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 20.4 | 36.2 | 46.4  | 154.0 | 715.9 |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 17.3 | 43.2 | 58.2  | 160.3 | 562.7 |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 14.1 | 51.1 | 63.7  | 165.0 | 447.9 |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 13.4 | 52.7 | 64.4  | 167.4 | 356.8 |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 14.1 | 51.9 | 69.2  | 175.3 | 290.0 |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 15.7 | 47.2 | 76.2  | 175.3 | 257.0 |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 16.5 | 44.0 | 85.7  | 159.5 | 222.4 |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 15.7 | 43.2 | 99.8  | 142.2 | 183.1 |
| 0.0  | 80°   | 1.6  | 2.4  | 2.4  | 1.6  | 1.6  | 13.4 | 42.4 | 101.4 | 121.0 | 125.7 |
| 0.8  | 82.5° | 4.7  | 6.3  | 5.5  | 3.9  | 3.9  | 11.8 | 37.7 | 84.9  | 62.9  | 54.2  |
| 4.7  | 85°   | 8.6  | 10.2 | 10.2 | 8.6  | 8.6  | 11.0 | 23.6 | 30.6  | 21.2  | 17.3  |
| 8.6  | 87.5° | 11.8 | 13.4 | 13.4 | 11.8 | 11.8 | 11.0 | 10.2 | 9.4   | 8.6   | 8.6   |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   | 0.0   |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ


Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-750-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 4896     | CRI (Ra): | 70.2 |      |       |
| CIE u':                   | 0.2101   | R1:       | 68.1 | R9:  | -35.1 |
| CIE v':                   | 0.4901   | R2:       | 73.9 | R10: | 39.3  |
| Duv:                      | 0.0035   | R3:       | 79.4 | R11: | 71.1  |
| CIE x:                    | 0.3489   | R4:       | 72.1 | R12: | 43.8  |
| CIE y:                    | 0.3618   | R5:       | 69.2 | R13: | 68.1  |
| CIE z:                    | 0.2893   | R6:       | 65.7 | R14: | 88.4  |
| Peak Wavelength (nm):     | 443      | R7:       | 78.1 | R15: | 59.7  |
| Dominant Wavelength (nm): | 570      | R8:       | 55.3 |      |       |
| Purity:                   | 13.25435 |           |      |      |       |
| Rf:                       | 70.7     |           |      |      |       |
| Rg:                       | 96.8     |           |      |      |       |



### Test Conditions


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-6


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-6

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2407-184-6

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 118                         | NR               | 620       | 401                         | NR               | 750       | 12                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 168                         | NR               | 625       | 365                         | NR               | 755       | 10                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 331                         | NR               | 760       | 9                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 299                         | NR               | 635       | 298                         | NR               | 765       | 8                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 362                         | NR               | 640       | 266                         | NR               | 770       | 6                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 418                         | NR               | 645       | 236                         | NR               | 775       | 6                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 461                         | NR               | 650       | 209                         | NR               | 780       | 5                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 491                         | NR               | 655       | 184                         | NR               | 785       | 4                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 514                         | NR               | 660       | 160                         | NR               | 790       | 4                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 530                         | NR               | 665       | 140                         | NR               | 795       | 3                           | NR               | 925       | 0                           | NR               |
| 410       | 27                          | NR               | 540       | 539                         | NR               | 670       | 122                         | NR               | 800       | 3                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 549                         | NR               | 675       | 106                         | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 115                         | NR               | 550       | 557                         | NR               | 680       | 92                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 226                         | NR               | 555       | 565                         | NR               | 685       | 79                          | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 395                         | NR               | 560       | 572                         | NR               | 690       | 68                          | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 648                         | NR               | 565       | 580                         | NR               | 695       | 59                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 937                         | NR               | 570       | 586                         | NR               | 700       | 51                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 953                         | NR               | 575       | 588                         | NR               | 705       | 44                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 591                         | NR               | 580       | 588                         | NR               | 710       | 38                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 334                         | NR               | 585       | 580                         | NR               | 715       | 32                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 221                         | NR               | 590       | 568                         | NR               | 720       | 28                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 140                         | NR               | 595       | 550                         | NR               | 725       | 24                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 93                          | NR               | 600       | 527                         | NR               | 730       | 21                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 79                          | NR               | 605       | 499                         | NR               | 735       | 18                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 469                         | NR               | 740       | 15                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 87                          | NR               | 615       | 435                         | NR               | 745       | 13                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-6

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.7

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 118                      | NR            | 620    | 401                      | NR            | 750    | 12                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 168                      | NR            | 625    | 365                      | NR            | 755    | 10                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 230                      | NR            | 630    | 331                      | NR            | 760    | 9                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 299                      | NR            | 635    | 298                      | NR            | 765    | 8                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 362                      | NR            | 640    | 266                      | NR            | 770    | 6                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 418                      | NR            | 645    | 236                      | NR            | 775    | 6                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 461                      | NR            | 650    | 209                      | NR            | 780    | 5                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 491                      | NR            | 655    | 184                      | NR            | 785    | 4                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 514                      | NR            | 660    | 160                      | NR            | 790    | 4                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 530                      | NR            | 665    | 140                      | NR            | 795    | 3                        | NR            | 925    | 0                        | NR            |
| 410    | 27                       | NR            | 540    | 539                      | NR            | 670    | 122                      | NR            | 800    | 3                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 549                      | NR            | 675    | 106                      | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 115                      | NR            | 550    | 557                      | NR            | 680    | 92                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 226                      | NR            | 555    | 565                      | NR            | 685    | 79                       | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 395                      | NR            | 560    | 572                      | NR            | 690    | 68                       | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 648                      | NR            | 565    | 580                      | NR            | 695    | 59                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 937                      | NR            | 570    | 586                      | NR            | 700    | 51                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 953                      | NR            | 575    | 588                      | NR            | 705    | 44                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 591                      | NR            | 580    | 588                      | NR            | 710    | 38                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 334                      | NR            | 585    | 580                      | NR            | 715    | 32                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 221                      | NR            | 590    | 568                      | NR            | 720    | 28                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 140                      | NR            | 595    | 550                      | NR            | 725    | 24                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 93                       | NR            | 600    | 527                      | NR            | 730    | 21                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 79                       | NR            | 605    | 499                      | NR            | 735    | 18                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 76                       | NR            | 610    | 469                      | NR            | 740    | 15                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 87                       | NR            | 615    | 435                      | NR            | 745    | 13                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-6

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.37


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 118                                  | NR                             | 620               | 401                                  | NR                             | 750               | 12                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 168                                  | NR                             | 625               | 365                                  | NR                             | 755               | 10                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 331                                  | NR                             | 760               | 9                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 299                                  | NR                             | 635               | 298                                  | NR                             | 765               | 8                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 362                                  | NR                             | 640               | 266                                  | NR                             | 770               | 6                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 2                                    | NR                             | 515               | 418                                  | NR                             | 645               | 236                                  | NR                             | 775               | 6                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 4                                    | NR                             | 520               | 461                                  | NR                             | 650               | 209                                  | NR                             | 780               | 5                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 6                                    | NR                             | 525               | 491                                  | NR                             | 655               | 184                                  | NR                             | 785               | 4                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 9                                    | NR                             | 530               | 514                                  | NR                             | 660               | 160                                  | NR                             | 790               | 4                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 14                                   | NR                             | 535               | 530                                  | NR                             | 665               | 140                                  | NR                             | 795               | 3                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 27                                   | NR                             | 540               | 539                                  | NR                             | 670               | 122                                  | NR                             | 800               | 3                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 55                                   | NR                             | 545               | 549                                  | NR                             | 675               | 106                                  | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 115                                  | NR                             | 550               | 557                                  | NR                             | 680               | 92                                   | NR                             | 810               | 2                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 226                                  | NR                             | 555               | 565                                  | NR                             | 685               | 79                                   | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 395                                  | NR                             | 560               | 572                                  | NR                             | 690               | 68                                   | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 648                                  | NR                             | 565               | 580                                  | NR                             | 695               | 59                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 937                                  | NR                             | 570               | 586                                  | NR                             | 700               | 51                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 953                                  | NR                             | 575               | 588                                  | NR                             | 705               | 44                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 591                                  | NR                             | 580               | 588                                  | NR                             | 710               | 38                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 334                                  | NR                             | 585               | 580                                  | NR                             | 715               | 32                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 221                                  | NR                             | 590               | 568                                  | NR                             | 720               | 28                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 140                                  | NR                             | 595               | 550                                  | NR                             | 725               | 24                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 93                                   | NR                             | 600               | 527                                  | NR                             | 730               | 21                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 79                                   | NR                             | 605               | 499                                  | NR                             | 735               | 18                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 76                                   | NR                             | 610               | 469                                  | NR                             | 740               | 15                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 87                                   | NR                             | 615               | 435                                  | NR                             | 745               | 13                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-6





TM-30-18

### Summary

$R_f = 70.7$   
 $R_g = 96.8$   
 $CIE R_a = 70.2$   
 $R_g = -35.1$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 53 | CES51 = 87 | CES76 = 42 |
| CES02 = 59 | CES27 = 78 | CES52 = 88 | CES77 = 64 |
| CES03 = 30 | CES28 = 76 | CES53 = 74 | CES78 = 45 |
| CES04 = 69 | CES29 = 48 | CES54 = 80 | CES79 = 74 |
| CES05 = 46 | CES30 = 56 | CES55 = 79 | CES80 = 71 |
| CES06 = 50 | CES31 = 54 | CES56 = 68 | CES81 = 72 |
| CES07 = 39 | CES32 = 50 | CES57 = 65 | CES82 = 88 |
| CES08 = 38 | CES33 = 60 | CES58 = 67 | CES83 = 82 |
| CES09 = 29 | CES34 = 62 | CES59 = 87 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 91 | CES85 = 84 |
| CES11 = 56 | CES36 = 90 | CES61 = 87 | CES86 = 74 |
| CES12 = 61 | CES37 = 72 | CES62 = 79 | CES87 = 75 |
| CES13 = 41 | CES38 = 66 | CES63 = 72 | CES88 = 76 |
| CES14 = 74 | CES39 = 91 | CES64 = 70 | CES89 = 74 |
| CES15 = 70 | CES40 = 83 | CES65 = 63 | CES90 = 73 |
| CES16 = 46 | CES41 = 83 | CES66 = 64 | CES91 = 92 |
| CES17 = 49 | CES42 = 70 | CES67 = 62 | CES92 = 67 |
| CES18 = 55 | CES43 = 68 | CES68 = 69 | CES93 = 81 |
| CES19 = 71 | CES44 = 98 | CES69 = 80 | CES94 = 56 |
| CES20 = 64 | CES45 = 78 | CES70 = 56 | CES95 = 71 |
| CES21 = 85 | CES46 = 77 | CES71 = 53 | CES96 = 77 |
| CES22 = 77 | CES47 = 73 | CES72 = 84 | CES97 = 82 |
| CES23 = 91 | CES48 = 65 | CES73 = 46 | CES98 = 71 |
| CES24 = 90 | CES49 = 76 | CES74 = 94 | CES99 = 59 |
| CES25 = 71 | CES50 = 85 | CES75 = 49 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)