

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065318

Luminaire Tested: **GLAN-SA2B-760-U-LBC**

Issue Date: 08/07/2025



Test Information

Test Method: LM-79-08
Report Number: P1065318
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA2B-760-U-LBC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 2xLight Square PACKAGE
70CRI 5700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL
Light Source: (28) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8390.2 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 72.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1065318
 CATALOG NUMBER: GLAN-SA2B-760-U-LBC

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 14.6 fc
 Type III - Short - N/A

REPORT NUMBER: P1065318
CATALOG NUMBER: GLAN-SA2B-760-U-LBC

Luminous Intensity Polar Plot



REPORT NUMBER: P1065318

CATALOG NUMBER: GLAN-SA2B-760-U-LBC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	57.3	0.0	57.3
	% Fixture	0.7	0.0	0.7
Street Side	Lumens	8332.9	0.0	8332.9
	% Fixture	99.3	0.0	99.3
Total	Lumens	8390.2	0.0	8390.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3.3	0.0
10°-20°	18.4	0.2
20°-30°	198.8	2.4
30°-40°	587.8	7.0
40°-50°	1752.0	20.9
50°-60°	2780.0	33.1
60°-70°	2318.9	27.6
70°-80°	715.2	8.5
80°-90°	15.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8390.2	100.0
0°-180°	8390.2	100.0



REPORT NUMBER: P1065318


CATALOG NUMBER: GLAN-SA2B-760-U-LBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	214.8	2.6			
FM	(30°-60°)	5088.5	60.6			
FH	(60°-80°)	3014.5	35.9			G2/5000
FVH	(80°-90°)	15.1	0.2			G1/100
BL	(0°-30°)	5.6	0.1	B0/110		
BM	(30°-60°)	31.4	0.4	B0/220		
BH	(60°-80°)	19.6	0.2	B0/110		G0/110
BVH	(80°-90°)	0.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short



REPORT NUMBER: P1065318

CATALOG NUMBER: GLAN-SA2B-760-U-LBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
2.5°	47.5	47.5	45.6	43.1	40.6	38.0	37.4	36.1	35.5	34.9	34.2
5°	49.4	49.4	48.8	46.9	44.4	42.5	42.5	40.6	39.3	38.0	36.8
7.5°	50.7	51.3	52.6	52.0	50.7	48.8	48.8	47.5	45.6	42.5	40.6
10°	52.6	54.5	57.0	58.3	58.9	58.9	58.3	57.7	54.5	50.1	45.0
12.5°	54.5	58.3	64.6	71.0	74.8	79.9	79.2	78.0	69.7	60.2	51.3
15°	58.3	64.0	77.3	95.7	124.2	142.0	148.9	142.6	115.4	81.1	59.6
17.5°	62.7	72.3	112.2	200.3	328.3	389.2	425.9	396.1	262.4	154.0	74.8
20°	67.2	88.1	208.5	519.1	851.8	1050.9	1106.0	1019.8	654.7	293.5	110.9
22.5°	74.8	123.6	422.8	1073.0	1835.5	2134.0	2190.4	1914.7	1236.6	579.3	166.7
25°	90.6	179.4	728.9	1748.7	2739.3	3243.2	3219.8	2858.5	2006.0	925.4	253.5
27.5°	113.5	261.1	1102.2	2484.5	3605.1	4049.4	4102.7	3655.8	2674.0	1360.8	360.0
30°	146.4	361.9	1502.8	3074.0	4299.1	4779.6	4788.4	4326.4	3271.7	1743.0	490.6
32.5°	178.1	457.0	1853.3	3643.8	4983.0	5509.7	5549.0	4980.5	3717.9	2141.0	604.0
35°	202.2	519.1	2208.2	4144.5	5672.6	6398.3	6395.8	5720.8	4246.5	2496.6	761.2
37.5°	204.1	581.2	2529.5	4656.6	6546.0	7358.5	7439.0	6694.9	4885.4	2936.4	953.9
40°	199.7	650.9	2936.4	5455.2	8119.7	9366.4	9437.4	8499.4	6167.0	3689.4	1254.9
42.5°	204.7	772.0	3596.9	6930.1	10732.9	12523.5	12660.4	11674.2	8522.8	5225.8	1791.8
45°	231.3	999.5	4980.5	9397.5	14457.8	16640.7	16595.1	15174.7	11264.1	7564.5	2854.0
47.5°	319.4	1556.6	7031.5	11799.0	16838.4	18782.3	18821.6	17085.6	12863.8	9362.6	4284.6
50°	491.2	2381.9	8754.8	13068.5	17862.0	19812.3	19775.5	17769.5	13471.6	10248.1	5161.1
52.5°	638.9	2978.9	9619.3	13514.1	17993.2	20321.2	20318.7	17949.5	13566.1	10324.1	5270.8
55°	675.6	3023.9	9626.3	13538.2	18287.3	20987.4	21071.0	18392.5	13688.4	9992.0	4858.2
57.5°	661.1	2677.2	9224.5	13677.6	18810.9	21502.6	21507.1	18821.6	13999.0	9788.6	4174.9
58°	648.4	2622.7	9143.3	13756.9	18900.9	21524.2	21513.4	18841.3	14251.9	9781.0	4067.8
60°	577.4	2277.3	8827.1	13959.0	18767.1	21081.8	20981.0	18412.2	14214.5	9703.0	3528.4
62.5°	453.8	1776.6	8515.9	13725.2	17333.4	18940.2	18982.0	16301.0	12958.3	9248.6	2892.7
65°	361.3	1324.0	7866.9	12039.2	14273.4	15553.7	15709.6	13255.5	10816.0	7831.4	2132.8
67.5°	287.7	957.1	6599.2	9585.1	11294.5	12981.1	13094.5	11129.1	8379.6	6000.3	1515.4
70°	233.9	647.1	4555.2	7009.9	9315.7	11212.1	11219.1	9245.4	6254.4	3931.5	950.7
72.5°	207.3	448.1	2644.3	5112.3	7553.8	9136.4	8951.9	7502.4	4806.8	2328.6	566.6
75°	179.4	297.3	1296.8	3125.3	4579.9	4611.0	4681.3	3480.3	2402.8	1107.3	339.7
77.5°	147.7	211.1	510.9	853.7	1373.5	1758.2	1823.5	1381.7	799.2	272.5	181.3
80°	101.4	100.1	137.5	261.8	393.0	492.5	459.5	355.6	209.2	104.6	64.6
82.5°	43.7	47.5	62.1	74.8	60.8	58.9	56.4	36.1	27.9	21.5	13.3
85°	13.9	12.7	13.3	13.3	10.8	8.2	8.2	3.8	0.0	0.0	0.0
87.5°	7.0	5.7	5.7	5.1	3.2	1.3	0.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065318

CATALOG NUMBER: GLAN-SA2B-760-U-LBC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
2.5°	33.6	33.6	32.3	31.1	30.4	29.2	28.5	27.9	27.3	26.6	26.0
5°	35.5	34.9	33.0	31.1	29.2	27.3	26.0	24.7	23.5	22.8	22.2
7.5°	38.7	37.4	33.6	30.4	27.9	25.4	24.1	22.2	20.9	19.0	18.4
10°	42.5	39.9	34.9	31.1	27.3	24.1	22.2	20.3	18.4	15.8	15.2
12.5°	47.5	43.1	36.8	30.4	26.0	22.2	20.3	17.7	15.8	13.9	12.7
15°	52.0	46.3	37.4	30.4	24.7	20.3	17.7	15.2	13.3	10.8	9.5
17.5°	58.3	48.8	36.8	28.5	22.8	17.7	15.2	13.3	10.1	6.3	5.1
20°	69.1	50.7	35.5	26.6	19.6	14.6	11.4	8.9	4.4	1.3	0.0
22.5°	86.2	55.8	34.2	24.1	17.1	11.4	7.6	3.2	0.0	0.0	0.0
25°	119.2	64.6	34.2	22.8	15.2	8.2	2.5	0.0	0.0	0.0	0.0
27.5°	158.5	76.7	34.2	19.6	12.0	4.4	0.0	0.0	0.0	0.0	0.0
30°	198.4	90.0	34.2	17.1	9.5	0.6	0.0	0.0	0.0	0.0	0.0
32.5°	236.4	101.4	34.9	14.6	6.3	0.0	0.0	0.0	0.0	0.0	0.0
35°	275.1	103.3	34.2	12.7	3.8	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	324.5	99.5	32.3	11.4	1.9	0.0	0.0	0.0	0.0	0.0	0.0
40°	399.3	101.4	30.4	10.8	0.6	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	537.5	109.6	27.9	10.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	929.2	147.0	25.4	11.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	1537.0	264.3	24.7	11.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	1961.6	332.8	26.0	12.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	1958.5	370.8	27.3	12.7	2.5	0.0	0.0	0.0	0.0	0.0	0.0
55°	1741.1	377.8	29.2	13.9	8.2	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	1455.2	344.8	33.6	17.1	15.2	0.0	0.0	0.0	0.0	0.0	0.0
58°	1404.5	329.6	34.9	17.7	16.5	0.0	0.0	0.0	0.0	0.0	0.0
60°	1151.0	268.7	44.4	22.2	22.2	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	794.8	234.5	50.7	28.5	22.8	0.0	0.0	0.0	0.0	0.0	0.0
65°	562.2	211.7	55.1	30.4	18.4	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	420.2	195.2	60.8	31.1	9.5	0.0	0.0	0.0	0.0	0.0	0.0
70°	322.0	183.2	74.8	33.0	2.5	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	262.4	169.2	90.6	34.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	217.4	152.7	87.5	37.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	144.5	118.5	79.9	37.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	50.7	46.9	62.1	33.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	7.6	6.3	8.9	11.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1065318

CATALOG NUMBER: GLAN-SA2B-760-U-LBC

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
2.5°	26.0	26.0	25.4	26.0	26.0	27.3	30.4	34.9	39.9	41.8	43.7
5°	21.5	20.9	20.3	20.3	20.3	22.2	24.7	29.8	35.5	38.0	39.3
7.5°	17.7	17.1	16.5	15.8	15.8	17.1	20.3	26.0	31.7	34.2	36.1
10°	14.6	13.3	12.7	12.0	12.0	13.3	16.5	22.2	28.5	31.1	33.6
12.5°	12.0	10.1	8.9	8.2	7.6	9.5	12.7	17.7	24.7	27.9	30.4
15°	8.2	6.3	4.4	3.8	3.2	5.1	8.2	13.9	20.9	24.7	27.3
17.5°	4.4	1.9	0.6	0.0	0.0	1.3	3.8	10.1	17.1	20.3	23.5
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.1	12.7	15.8	19.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6	7.6	10.8	13.9
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	3.2	5.7	8.2
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.3	3.8
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.9	3.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.5	5.1	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065318

CATALOG NUMBER: GLAN-SA2B-760-U-LBC

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	316°	325°	335°	345°	355°	360°
0°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
2.5°	45.0	44.4	43.1	41.8	41.8	41.8	43.7	45.6	47.5	47.5
5°	41.8	41.8	41.2	39.9	39.9	40.6	43.1	46.3	48.8	49.4
7.5°	38.7	39.9	38.7	38.0	38.7	39.3	41.8	45.6	49.4	50.7
10°	36.8	37.4	37.4	36.8	36.8	38.0	40.6	45.6	50.7	52.6
12.5°	34.2	35.5	34.9	34.9	34.9	36.1	39.3	45.0	52.0	54.5
15°	31.7	33.6	33.6	33.0	33.0	33.6	38.0	44.4	53.9	58.3
17.5°	29.2	31.1	31.7	30.4	30.4	31.7	36.1	44.4	55.1	62.7
20°	24.1	27.3	29.2	27.3	27.3	28.5	33.0	41.8	55.8	67.2
22.5°	19.0	22.2	24.7	24.1	24.1	24.7	30.4	39.9	56.4	74.8
25°	13.9	17.1	19.0	20.3	20.3	22.2	27.9	38.7	58.9	90.6
27.5°	8.2	12.0	14.6	15.8	16.5	19.0	26.0	37.4	63.4	113.5
30°	3.8	7.0	10.1	12.7	12.7	17.1	24.1	36.1	69.1	146.4
32.5°	0.0	3.2	5.1	8.9	9.5	13.9	22.2	34.9	77.3	178.1
35°	0.0	0.0	2.5	7.0	7.0	11.4	20.3	33.6	90.0	202.2
37.5°	0.0	0.0	0.0	5.1	5.7	10.1	19.6	33.0	92.5	204.1
40°	0.0	0.0	0.0	3.8	4.4	9.5	19.6	33.6	83.7	199.7
42.5°	0.0	0.0	0.0	2.5	3.2	9.5	19.6	34.9	75.4	204.7
45°	0.0	0.0	0.0	1.9	2.5	10.1	19.0	34.2	71.0	231.3
47.5°	0.0	0.0	0.0	2.5	3.8	10.1	18.4	33.6	71.6	319.4
50°	0.0	0.0	0.0	3.2	4.4	10.1	19.0	32.3	78.6	491.2
52.5°	0.0	0.0	0.0	2.5	3.8	11.4	20.9	31.7	85.6	638.9
55°	0.0	0.0	0.0	0.6	1.9	14.6	22.8	31.7	96.3	675.6
57.5°	0.0	0.0	0.0	0.0	0.0	16.5	26.0	33.6	114.1	661.1
58°	0.0	0.0	0.0	0.0	0.0	16.5	26.6	33.6	115.4	648.4
60°	0.0	0.0	0.0	0.0	0.0	16.5	29.2	37.4	124.2	577.4
62.5°	0.0	0.0	0.0	0.0	0.0	13.9	34.9	46.9	129.3	453.8
65°	0.0	0.0	0.0	0.0	0.0	11.4	41.2	51.3	133.1	361.3
67.5°	0.0	0.0	0.0	0.0	0.0	10.8	42.5	52.0	135.0	287.7
70°	0.0	0.0	0.0	0.0	0.0	11.4	41.8	55.8	141.3	233.9
72.5°	0.0	0.0	0.0	0.0	0.0	12.7	38.0	61.5	141.3	207.3
75°	0.0	0.0	0.0	0.0	0.0	13.3	35.5	69.1	128.7	179.4
77.5°	0.0	0.0	0.0	0.0	0.0	12.7	34.9	80.5	114.7	147.7
80°	1.3	1.9	1.9	1.3	1.3	10.8	34.2	81.8	97.6	101.4
82.5°	3.8	5.1	4.4	3.2	3.2	9.5	30.4	68.5	50.7	43.7
85°	7.0	8.2	8.2	7.0	7.0	8.9	19.0	24.7	17.1	13.9
87.5°	9.5	10.8	10.8	9.5	9.5	8.9	8.2	7.6	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7





TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE R_a = 69.9$
 $R_g = -35.4$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)