

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064715

Luminaire Tested: **GLAN-SA4C-760-U-RBC**

Issue Date: 08/07/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1064715  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA4C-760-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 4xLight Square PACKAGE  
70CRI 5700K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (56) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 20600.4 lumens  
Efficiency: N/A  
Efficacy: 108.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3

Input Watts (W): 190.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1064715  
CATALOG NUMBER: GLAN-SA4C-760-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 103.2    | 0.0    | 103.2   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 20497.2  | 0.0    | 20497.2 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 20600.4  | 0.0    | 20600.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 8.1     | 0.0       |
| 10°-20°   | 45.3    | 0.2       |
| 20°-30°   | 488.2   | 2.4       |
| 30°-40°   | 1443.7  | 7.0       |
| 40°-50°   | 4302.6  | 20.9      |
| 50°-60°   | 6822.4  | 33.1      |
| 60°-70°   | 5695.0  | 27.6      |
| 70°-80°   | 1756.1  | 8.5       |
| 80°-90°   | 39.1    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20600.4 | 100.0     |
| 0°-180°   | 20600.4 | 100.0     |



REPORT NUMBER: P1064715


CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 522.6   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 12531.8 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 7412.7  | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 30.2    | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 18.9    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 36.9    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 38.5    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 8.9     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° | 25°  |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|------|
| 0°     | 90.3   | 90.3   | 90.3  | 90.3  | 90.3  | 90.3  | 90.3  | 90.3  | 90.3  | 90.3  | 90.3 |
| 2.5°   | 82.5   | 82.5   | 82.5  | 82.5  | 81.0  | 81.0  | 79.4  | 79.4  | 77.8  | 77.8  | 76.3 |
| 5°     | 87.2   | 87.2   | 85.6  | 84.1  | 84.1  | 82.5  | 81.0  | 79.4  | 79.4  | 77.8  | 76.3 |
| 7.5°   | 95.0   | 93.4   | 91.8  | 90.3  | 87.2  | 85.6  | 82.5  | 81.0  | 79.4  | 76.3  | 74.7 |
| 10°    | 104.3  | 101.2  | 98.1  | 95.0  | 91.8  | 88.7  | 85.6  | 84.1  | 81.0  | 79.4  | 76.3 |
| 12.5°  | 116.8  | 112.1  | 105.9 | 101.2 | 98.1  | 93.4  | 90.3  | 87.2  | 82.5  | 79.4  | 74.7 |
| 15°    | 127.7  | 121.4  | 113.6 | 107.4 | 102.7 | 96.5  | 91.8  | 87.2  | 84.1  | 79.4  | 74.7 |
| 17.5°  | 143.2  | 132.3  | 119.9 | 112.1 | 105.9 | 98.1  | 90.3  | 85.6  | 81.0  | 74.7  | 70.1 |
| 20°    | 169.7  | 147.9  | 124.5 | 115.2 | 105.9 | 96.5  | 87.2  | 81.0  | 76.3  | 70.1  | 65.4 |
| 22.5°  | 211.7  | 174.4  | 137.0 | 123.0 | 110.5 | 96.5  | 84.1  | 77.8  | 71.6  | 65.4  | 59.2 |
| 25°    | 292.7  | 225.7  | 158.8 | 140.1 | 121.4 | 102.7 | 84.1  | 76.3  | 70.1  | 62.3  | 56.0 |
| 27.5°  | 389.2  | 289.6  | 188.4 | 161.9 | 137.0 | 110.5 | 84.1  | 74.7  | 66.9  | 57.6  | 48.3 |
| 30°    | 487.3  | 354.9  | 221.1 | 186.8 | 152.6 | 118.3 | 84.1  | 73.2  | 63.8  | 52.9  | 42.0 |
| 32.5°  | 580.7  | 415.7  | 249.1 | 208.6 | 168.1 | 126.1 | 85.6  | 73.2  | 60.7  | 48.3  | 35.8 |
| 35°    | 675.6  | 465.5  | 253.8 | 211.7 | 169.7 | 126.1 | 84.1  | 70.1  | 57.6  | 43.6  | 31.1 |
| 37.5°  | 797.1  | 521.5  | 244.4 | 202.4 | 161.9 | 119.9 | 79.4  | 66.9  | 54.5  | 40.5  | 28.0 |
| 40°    | 980.8  | 614.9  | 249.1 | 205.5 | 161.9 | 118.3 | 74.7  | 62.3  | 51.4  | 38.9  | 26.5 |
| 42.5°  | 1320.1 | 795.5  | 269.3 | 219.5 | 169.7 | 118.3 | 68.5  | 57.6  | 48.3  | 37.4  | 26.5 |
| 45°    | 2282.2 | 1321.7 | 361.2 | 286.4 | 211.7 | 137.0 | 62.3  | 52.9  | 45.1  | 35.8  | 28.0 |
| 47.5°  | 3775.1 | 2212.1 | 649.2 | 501.3 | 354.9 | 207.0 | 60.7  | 52.9  | 45.1  | 35.8  | 28.0 |
| 50°    | 4818.2 | 2817.7 | 817.3 | 628.9 | 440.6 | 252.2 | 63.8  | 54.5  | 46.7  | 37.4  | 29.6 |
| 52.5°  | 4810.4 | 2861.3 | 910.7 | 699.0 | 488.8 | 277.1 | 66.9  | 57.6  | 49.8  | 40.5  | 31.1 |
| 55°    | 4276.4 | 2602.9 | 927.8 | 713.0 | 499.7 | 284.9 | 71.6  | 62.3  | 52.9  | 43.6  | 34.2 |
| 57.5°  | 3574.3 | 2210.6 | 846.9 | 655.4 | 465.5 | 274.0 | 82.5  | 71.6  | 62.3  | 51.4  | 42.0 |
| 60°    | 2827.1 | 1743.6 | 660.1 | 521.5 | 384.5 | 246.0 | 109.0 | 95.0  | 82.5  | 68.5  | 54.5 |
| 62.5°  | 1952.2 | 1264.1 | 576.0 | 462.4 | 350.3 | 236.6 | 124.5 | 110.5 | 98.1  | 84.1  | 70.1 |
| 65°    | 1380.8 | 951.2  | 520.0 | 423.4 | 328.5 | 232.0 | 135.4 | 119.9 | 105.9 | 90.3  | 74.7 |
| 67.5°  | 1032.1 | 756.6  | 479.5 | 397.0 | 314.5 | 232.0 | 149.4 | 130.8 | 113.6 | 95.0  | 76.3 |
| 70°    | 790.8  | 621.1  | 449.9 | 383.0 | 317.6 | 250.6 | 183.7 | 157.2 | 132.3 | 105.9 | 81.0 |
| 72.5°  | 644.5  | 530.9  | 415.7 | 367.4 | 319.1 | 270.9 | 222.6 | 188.4 | 154.1 | 118.3 | 84.1 |
| 75°    | 534.0  | 454.6  | 375.2 | 334.7 | 295.8 | 255.3 | 214.8 | 183.7 | 154.1 | 123.0 | 91.8 |
| 77.5°  | 354.9  | 323.8  | 291.1 | 267.8 | 244.4 | 219.5 | 196.2 | 169.7 | 144.8 | 118.3 | 91.8 |
| 80°    | 124.5  | 119.9  | 115.2 | 124.5 | 133.9 | 143.2 | 152.6 | 133.9 | 116.8 | 98.1  | 81.0 |
| 82.5°  | 18.7   | 17.1   | 15.6  | 17.1  | 18.7  | 20.2  | 21.8  | 23.4  | 24.9  | 26.5  | 28.0 |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  | 52.5° |
|--------|-------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0°     | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  |
| 2.5°   | 76.3  | 76.3 | 74.7  | 74.7 | 74.7  | 73.2 | 73.2  | 71.6 | 71.6  | 71.6 | 70.1  |
| 5°     | 74.7  | 74.7 | 73.2  | 71.6 | 70.1  | 70.1 | 68.5  | 66.9 | 66.9  | 65.4 | 65.4  |
| 7.5°   | 73.2  | 71.6 | 70.1  | 68.5 | 66.9  | 65.4 | 63.8  | 62.3 | 62.3  | 60.7 | 60.7  |
| 10°    | 74.7  | 71.6 | 70.1  | 66.9 | 65.4  | 63.8 | 60.7  | 59.2 | 57.6  | 57.6 | 56.0  |
| 12.5°  | 71.6  | 70.1 | 66.9  | 63.8 | 62.3  | 59.2 | 57.6  | 54.5 | 52.9  | 52.9 | 51.4  |
| 15°    | 71.6  | 68.5 | 63.8  | 60.7 | 57.6  | 56.0 | 52.9  | 49.8 | 48.3  | 46.7 | 45.1  |
| 17.5°  | 66.9  | 63.8 | 59.2  | 56.0 | 52.9  | 49.8 | 46.7  | 43.6 | 42.0  | 40.5 | 38.9  |
| 20°    | 60.7  | 57.6 | 52.9  | 48.3 | 45.1  | 42.0 | 38.9  | 35.8 | 34.2  | 32.7 | 29.6  |
| 22.5°  | 54.5  | 51.4 | 46.7  | 42.0 | 38.9  | 35.8 | 31.1  | 28.0 | 26.5  | 23.4 | 21.8  |
| 25°    | 51.4  | 46.7 | 42.0  | 37.4 | 32.7  | 29.6 | 24.9  | 20.2 | 17.1  | 14.0 | 9.3   |
| 27.5°  | 43.6  | 38.9 | 34.2  | 29.6 | 24.9  | 20.2 | 15.6  | 10.9 | 7.8   | 6.2  | 3.1   |
| 30°    | 37.4  | 32.7 | 28.0  | 23.4 | 17.1  | 12.5 | 7.8   | 1.6  | 1.6   | 1.6  | 0.0   |
| 32.5°  | 31.1  | 26.5 | 20.2  | 15.6 | 12.5  | 7.8  | 4.7   | 0.0  | 0.0   | 0.0  | 0.0   |
| 35°    | 24.9  | 20.2 | 14.0  | 9.3  | 7.8   | 4.7  | 3.1   | 0.0  | 0.0   | 0.0  | 0.0   |
| 37.5°  | 21.8  | 17.1 | 10.9  | 4.7  | 3.1   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   |
| 40°    | 20.2  | 14.0 | 7.8   | 1.6  | 1.6   | 1.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 42.5°  | 20.2  | 14.0 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 45°    | 20.2  | 14.0 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 47.5°  | 20.2  | 14.0 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 50°    | 21.8  | 15.6 | 7.8   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 52.5°  | 24.9  | 18.7 | 12.5  | 6.2  | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   |
| 55°    | 31.1  | 28.0 | 23.4  | 20.2 | 15.6  | 10.9 | 4.7   | 0.0  | 0.0   | 0.0  | 0.0   |
| 57.5°  | 40.5  | 40.5 | 38.9  | 37.4 | 28.0  | 18.7 | 9.3   | 0.0  | 0.0   | 0.0  | 0.0   |
| 60°    | 54.5  | 54.5 | 54.5  | 54.5 | 40.5  | 28.0 | 14.0  | 0.0  | 0.0   | 0.0  | 0.0   |
| 62.5°  | 66.9  | 63.8 | 59.2  | 56.0 | 42.0  | 28.0 | 14.0  | 0.0  | 0.0   | 0.0  | 0.0   |
| 65°    | 66.9  | 60.7 | 52.9  | 45.1 | 34.2  | 23.4 | 10.9  | 0.0  | 0.0   | 0.0  | 0.0   |
| 67.5°  | 62.3  | 49.8 | 35.8  | 23.4 | 17.1  | 12.5 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   |
| 70°    | 62.3  | 43.6 | 24.9  | 6.2  | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   |
| 72.5°  | 62.3  | 42.0 | 20.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 75°    | 68.5  | 46.7 | 23.4  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 77.5°  | 68.5  | 46.7 | 23.4  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 80°    | 60.7  | 40.5 | 20.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 82.5°  | 20.2  | 14.0 | 6.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° | 80°  |
|--------|------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0°     | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 |
| 2.5°   | 70.1 | 70.1  | 70.1 | 68.5  | 68.5 | 68.5  | 68.5 | 66.9  | 66.9 | 66.9  | 66.9 |
| 5°     | 63.8 | 63.8  | 62.3 | 62.3  | 60.7 | 60.7  | 59.2 | 59.2  | 57.6 | 57.6  | 57.6 |
| 7.5°   | 59.2 | 57.6  | 57.6 | 56.0  | 54.5 | 54.5  | 52.9 | 52.9  | 51.4 | 49.8  | 49.8 |
| 10°    | 54.5 | 52.9  | 52.9 | 51.4  | 49.8 | 48.3  | 48.3 | 46.7  | 45.1 | 43.6  | 42.0 |
| 12.5°  | 49.8 | 48.3  | 46.7 | 45.1  | 43.6 | 42.0  | 42.0 | 40.5  | 38.9 | 37.4  | 37.4 |
| 15°    | 43.6 | 42.0  | 40.5 | 38.9  | 37.4 | 35.8  | 35.8 | 34.2  | 32.7 | 31.1  | 29.6 |
| 17.5°  | 37.4 | 35.8  | 35.8 | 34.2  | 32.7 | 31.1  | 29.6 | 26.5  | 24.9 | 23.4  | 20.2 |
| 20°    | 28.0 | 26.5  | 24.9 | 23.4  | 21.8 | 18.7  | 17.1 | 14.0  | 10.9 | 9.3   | 7.8  |
| 22.5°  | 18.7 | 15.6  | 14.0 | 10.9  | 7.8  | 6.2   | 4.7  | 1.6   | 0.0  | 0.0   | 0.0  |
| 25°    | 6.2  | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|------|-------|------|-------|------|-------|------|--------|------|--------|
| 0°     | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3  | 90.3 | 90.3   | 90.3 | 90.3   |
| 2.5°   | 65.4  | 65.4 | 65.4  | 63.8 | 63.8  | 63.8 | 63.8  | 63.8 | 63.8   | 63.8 | 63.8   |
| 5°     | 56.0  | 56.0 | 56.0  | 54.5 | 54.5  | 52.9 | 52.9  | 52.9 | 51.4   | 51.4 | 51.4   |
| 7.5°   | 48.3  | 46.7 | 46.7  | 45.1 | 45.1  | 43.6 | 43.6  | 43.6 | 42.0   | 42.0 | 42.0   |
| 10°    | 40.5  | 38.9 | 38.9  | 37.4 | 37.4  | 35.8 | 35.8  | 34.2 | 34.2   | 32.7 | 32.7   |
| 12.5°  | 35.8  | 34.2 | 32.7  | 31.1 | 31.1  | 29.6 | 28.0  | 28.0 | 26.5   | 24.9 | 24.9   |
| 15°    | 28.0  | 26.5 | 24.9  | 23.4 | 21.8  | 20.2 | 18.7  | 18.7 | 17.1   | 15.6 | 14.0   |
| 17.5°  | 18.7  | 15.6 | 14.0  | 12.5 | 12.5  | 10.9 | 9.3   | 7.8  | 6.2    | 4.7  | 4.7    |
| 20°    | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0°     | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 |
| 2.5°   | 63.8 | 62.3   | 62.3 | 62.3   | 63.8 | 63.8   | 63.8 | 63.8   | 63.8 | 63.8   | 63.8 |
| 5°     | 51.4 | 49.8   | 49.8 | 49.8   | 49.8 | 49.8   | 49.8 | 49.8   | 49.8 | 49.8   | 49.8 |
| 7.5°   | 42.0 | 40.5   | 40.5 | 40.5   | 40.5 | 38.9   | 38.9 | 38.9   | 38.9 | 38.9   | 38.9 |
| 10°    | 32.7 | 31.1   | 31.1 | 31.1   | 31.1 | 29.6   | 29.6 | 29.6   | 29.6 | 29.6   | 29.6 |
| 12.5°  | 23.4 | 23.4   | 21.8 | 21.8   | 21.8 | 20.2   | 20.2 | 20.2   | 20.2 | 18.7   | 18.7 |
| 15°    | 14.0 | 12.5   | 10.9 | 10.9   | 10.9 | 9.3    | 9.3  | 9.3    | 9.3  | 7.8    | 7.8  |
| 17.5°  | 3.1  | 3.1    | 1.6  | 1.6    | 1.6  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0°     | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   |
| 2.5°   | 65.4   | 65.4 | 66.9   | 66.9 | 68.5   | 71.6 | 73.2   | 74.7 | 77.8   | 81.0 | 82.5   |
| 5°     | 51.4   | 52.9 | 52.9   | 54.5 | 56.0   | 57.6 | 59.2   | 60.7 | 63.8   | 66.9 | 70.1   |
| 7.5°   | 40.5   | 40.5 | 42.0   | 42.0 | 43.6   | 46.7 | 48.3   | 49.8 | 52.9   | 57.6 | 60.7   |
| 10°    | 31.1   | 31.1 | 32.7   | 32.7 | 34.2   | 37.4 | 38.9   | 40.5 | 43.6   | 48.3 | 51.4   |
| 12.5°  | 20.2   | 21.8 | 21.8   | 23.4 | 24.9   | 28.0 | 29.6   | 31.1 | 34.2   | 37.4 | 40.5   |
| 15°    | 9.3    | 10.9 | 10.9   | 12.5 | 14.0   | 17.1 | 18.7   | 20.2 | 23.4   | 28.0 | 31.1   |
| 17.5°  | 1.6    | 1.6  | 3.1    | 3.1  | 4.7    | 6.2  | 7.8    | 9.3  | 14.0   | 17.1 | 21.8   |
| 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 6.2  | 9.3    |
| 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 1.6  | 1.6    |
| 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|--------|------|--------|------|--------|------|--------|-------|--------|-------|--------|-------|
| 0°     | 90.3 | 90.3   | 90.3 | 90.3   | 90.3 | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  |
| 2.5°   | 85.6 | 88.7   | 91.8 | 95.0   | 98.1 | 101.2  | 102.7 | 105.9  | 107.4 | 109.0  | 109.0 |
| 5°     | 73.2 | 76.3   | 81.0 | 84.1   | 87.2 | 90.3   | 93.4  | 95.0   | 96.5  | 98.1   | 99.6  |
| 7.5°   | 63.8 | 66.9   | 71.6 | 74.7   | 77.8 | 81.0   | 84.1  | 87.2   | 88.7  | 90.3   | 91.8  |
| 10°    | 54.5 | 59.2   | 62.3 | 66.9   | 70.1 | 73.2   | 76.3  | 79.4   | 82.5  | 84.1   | 87.2  |
| 12.5°  | 43.6 | 48.3   | 52.9 | 56.0   | 60.7 | 65.4   | 68.5  | 71.6   | 74.7  | 77.8   | 79.4  |
| 15°    | 34.2 | 38.9   | 43.6 | 46.7   | 51.4 | 56.0   | 60.7  | 63.8   | 66.9  | 70.1   | 73.2  |
| 17.5°  | 24.9 | 29.6   | 34.2 | 37.4   | 42.0 | 46.7   | 49.8  | 54.5   | 57.6  | 60.7   | 65.4  |
| 20°    | 12.5 | 17.1   | 21.8 | 26.5   | 31.1 | 35.8   | 38.9  | 43.6   | 46.7  | 49.8   | 52.9  |
| 22.5°  | 1.6  | 6.2    | 10.9 | 14.0   | 18.7 | 23.4   | 26.5  | 31.1   | 34.2  | 37.4   | 40.5  |
| 25°    | 0.0  | 1.6    | 4.7  | 6.2    | 7.8  | 10.9   | 14.0  | 17.1   | 20.2  | 23.4   | 28.0  |
| 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.6    | 3.1   | 6.2    | 9.3   | 12.5   | 15.6  |
| 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 3.1    | 4.7   |
| 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    | 1.6   |
| 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 1.6    | 1.6   | 3.1    | 6.2   |
| 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 4.7   | 7.8    | 9.3   | 10.9   | 14.0  |
| 87.5°  | 0.0  | 1.6    | 3.1  | 4.7    | 6.2  | 9.3    | 12.5  | 15.6   | 17.1  | 18.7   | 20.2  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   |
| 2.5°   | 110.5  | 110.5 | 110.5  | 110.5 | 109.0  | 109.0 | 109.0  | 107.4 | 107.4  | 105.9 | 105.9  |
| 5°     | 101.2  | 102.7 | 102.7  | 102.7 | 102.7  | 102.7 | 102.7  | 102.7 | 101.2  | 101.2 | 101.2  |
| 7.5°   | 93.4   | 95.0  | 96.5   | 96.5  | 98.1   | 98.1  | 98.1   | 96.5  | 96.5   | 95.0  | 95.0   |
| 10°    | 88.7   | 90.3  | 90.3   | 91.8  | 91.8   | 91.8  | 91.8   | 91.8  | 91.8   | 91.8  | 91.8   |
| 12.5°  | 82.5   | 84.1  | 85.6   | 85.6  | 87.2   | 87.2  | 87.2   | 87.2  | 85.6   | 85.6  | 85.6   |
| 15°    | 74.7   | 77.8  | 79.4   | 81.0  | 81.0   | 82.5  | 82.5   | 82.5  | 82.5   | 82.5  | 82.5   |
| 17.5°  | 68.5   | 71.6  | 73.2   | 74.7  | 74.7   | 76.3  | 76.3   | 77.8  | 77.8   | 77.8  | 77.8   |
| 20°    | 56.0   | 59.2  | 60.7   | 63.8  | 65.4   | 66.9  | 68.5   | 70.1  | 70.1   | 71.6  | 70.1   |
| 22.5°  | 43.6   | 46.7  | 48.3   | 51.4  | 52.9   | 54.5  | 56.0   | 57.6  | 59.2   | 60.7  | 60.7   |
| 25°    | 31.1   | 34.2  | 35.8   | 38.9  | 40.5   | 42.0  | 43.6   | 45.1  | 45.1   | 46.7  | 48.3   |
| 27.5°  | 17.1   | 20.2  | 23.4   | 24.9  | 28.0   | 29.6  | 31.1   | 32.7  | 34.2   | 35.8  | 37.4   |
| 30°    | 7.8    | 9.3   | 10.9   | 14.0  | 15.6   | 17.1  | 18.7   | 21.8  | 23.4   | 24.9  | 26.5   |
| 32.5°  | 0.0    | 0.0   | 1.6    | 4.7   | 6.2    | 7.8   | 9.3    | 10.9  | 10.9   | 12.5  | 15.6   |
| 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    | 3.1   | 4.7    | 6.2   | 9.3    |
| 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.1    |
| 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.1    |
| 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    |
| 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    |
| 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    |
| 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    |
| 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    |
| 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 80°    | 3.1    | 3.1   | 3.1    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    |
| 82.5°  | 7.8    | 9.3   | 10.9   | 10.9  | 12.5   | 12.5  | 12.5   | 12.5  | 10.9   | 10.9  | 10.9   |
| 85°    | 15.6   | 17.1  | 18.7   | 18.7  | 20.2   | 20.2  | 20.2   | 20.2  | 20.2   | 20.2  | 20.2   |
| 87.5°  | 21.8   | 23.4  | 24.9   | 24.9  | 26.5   | 26.5  | 26.5   | 26.5  | 26.5   | 26.5  | 26.5   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  |
| 2.5°   | 104.3 | 104.3  | 102.7 | 102.7  | 102.7 | 102.7  | 102.7 | 104.3  | 105.9 | 105.9  | 107.4 |
| 5°     | 99.6  | 99.6   | 98.1  | 98.1   | 98.1  | 99.6   | 99.6  | 101.2  | 102.7 | 104.3  | 105.9 |
| 7.5°   | 95.0  | 93.4   | 93.4  | 95.0   | 95.0  | 96.5   | 96.5  | 98.1   | 99.6  | 101.2  | 102.7 |
| 10°    | 91.8  | 90.3   | 90.3  | 90.3   | 91.8  | 91.8   | 93.4  | 95.0   | 96.5  | 98.1   | 99.6  |
| 12.5°  | 85.6  | 85.6   | 85.6  | 85.6   | 87.2  | 87.2   | 88.7  | 90.3   | 93.4  | 95.0   | 96.5  |
| 15°    | 82.5  | 81.0   | 81.0  | 81.0   | 81.0  | 82.5   | 82.5  | 85.6   | 88.7  | 90.3   | 93.4  |
| 17.5°  | 76.3  | 76.3   | 74.7  | 74.7   | 76.3  | 76.3   | 77.8  | 81.0   | 84.1  | 85.6   | 88.7  |
| 20°    | 70.1  | 68.5   | 66.9  | 66.9   | 68.5  | 68.5   | 70.1  | 73.2   | 76.3  | 77.8   | 81.0  |
| 22.5°  | 60.7  | 59.2   | 59.2  | 59.2   | 59.2  | 60.7   | 60.7  | 63.8   | 68.5  | 71.6   | 74.7  |
| 25°    | 48.3  | 49.8   | 49.8  | 51.4   | 51.4  | 52.9   | 54.5  | 57.6   | 62.3  | 65.4   | 68.5  |
| 27.5°  | 37.4  | 38.9   | 38.9  | 42.0   | 43.6  | 45.1   | 46.7  | 51.4   | 56.0  | 59.2   | 63.8  |
| 30°    | 28.0  | 29.6   | 31.1  | 32.7   | 35.8  | 38.9   | 42.0  | 46.7   | 51.4  | 54.5   | 59.2  |
| 32.5°  | 17.1  | 20.2   | 21.8  | 24.9   | 28.0  | 31.1   | 34.2  | 38.9   | 45.1  | 49.8   | 54.5  |
| 35°    | 12.5  | 14.0   | 17.1  | 18.7   | 21.8  | 24.9   | 28.0  | 34.2   | 38.9  | 45.1   | 49.8  |
| 37.5°  | 6.2   | 9.3    | 12.5  | 15.6   | 18.7  | 21.8   | 24.9  | 31.1   | 37.4  | 42.0   | 48.3  |
| 40°    | 4.7   | 7.8    | 9.3   | 12.5   | 17.1  | 20.2   | 23.4  | 29.6   | 35.8  | 42.0   | 48.3  |
| 42.5°  | 3.1   | 4.7    | 6.2   | 10.9   | 14.0  | 18.7   | 23.4  | 29.6   | 35.8  | 42.0   | 48.3  |
| 45°    | 3.1   | 3.1    | 4.7   | 9.3    | 14.0  | 20.2   | 24.9  | 31.1   | 35.8  | 42.0   | 46.7  |
| 47.5°  | 3.1   | 4.7    | 6.2   | 12.5   | 15.6  | 20.2   | 24.9  | 29.6   | 35.8  | 40.5   | 45.1  |
| 50°    | 4.7   | 6.2    | 7.8   | 14.0   | 17.1  | 21.8   | 24.9  | 31.1   | 35.8  | 42.0   | 46.7  |
| 52.5°  | 3.1   | 4.7    | 6.2   | 12.5   | 17.1  | 23.4   | 28.0  | 34.2   | 40.5  | 45.1   | 51.4  |
| 55°    | 1.6   | 1.6    | 1.6   | 9.3    | 18.7  | 26.5   | 35.8  | 40.5   | 46.7  | 51.4   | 56.0  |
| 57.5°  | 0.0   | 0.0    | 0.0   | 6.2    | 18.7  | 29.6   | 40.5  | 46.7   | 52.9  | 57.6   | 63.8  |
| 60°    | 0.0   | 0.0    | 0.0   | 6.2    | 18.7  | 29.6   | 40.5  | 48.3   | 56.0  | 63.8   | 71.6  |
| 62.5°  | 0.0   | 0.0    | 0.0   | 6.2    | 15.6  | 24.9   | 34.2  | 46.7   | 60.7  | 73.2   | 85.6  |
| 65°    | 0.0   | 0.0    | 0.0   | 4.7    | 12.5  | 20.2   | 28.0  | 46.7   | 65.4  | 82.5   | 101.2 |
| 67.5°  | 0.0   | 0.0    | 0.0   | 4.7    | 12.5  | 18.7   | 26.5  | 46.7   | 65.4  | 85.6   | 104.3 |
| 70°    | 0.0   | 0.0    | 0.0   | 4.7    | 12.5  | 20.2   | 28.0  | 46.7   | 65.4  | 84.1   | 102.7 |
| 72.5°  | 0.0   | 0.0    | 0.0   | 4.7    | 14.0  | 21.8   | 31.1  | 46.7   | 62.3  | 77.8   | 93.4  |
| 75°    | 0.0   | 0.0    | 0.0   | 6.2    | 14.0  | 23.4   | 32.7  | 46.7   | 60.7  | 73.2   | 87.2  |
| 77.5°  | 0.0   | 0.0    | 0.0   | 4.7    | 14.0  | 21.8   | 31.1  | 45.1   | 59.2  | 71.6   | 85.6  |
| 80°    | 4.7   | 3.1    | 3.1   | 7.8    | 14.0  | 20.2   | 26.5  | 40.5   | 56.0  | 70.1   | 84.1  |
| 82.5°  | 9.3   | 9.3    | 7.8   | 10.9   | 14.0  | 18.7   | 23.4  | 35.8   | 49.8  | 62.3   | 74.7  |
| 85°    | 18.7  | 18.7   | 17.1  | 18.7   | 18.7  | 20.2   | 21.8  | 28.0   | 34.2  | 40.5   | 46.7  |
| 87.5°  | 24.9  | 24.9   | 23.4  | 23.4   | 23.4  | 21.8   | 21.8  | 21.8   | 21.8  | 20.2   | 20.2  |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   | 272.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|
| 0°     | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3  | 90.3   | 90.3   | 90.3   |
| 2.5°   | 109.0  | 110.5 | 110.5  | 112.1 | 113.6  | 115.2 | 115.2  | 116.8 | 116.8  | 116.8  | 116.8  |
| 5°     | 107.4  | 110.5 | 112.1  | 113.6 | 115.2  | 116.8 | 118.3  | 119.9 | 121.4  | 121.4  | 121.4  |
| 7.5°   | 105.9  | 107.4 | 110.5  | 112.1 | 115.2  | 116.8 | 119.9  | 121.4 | 123.0  | 124.5  | 126.1  |
| 10°    | 102.7  | 105.9 | 109.0  | 112.1 | 115.2  | 118.3 | 121.4  | 124.5 | 127.7  | 129.2  | 132.3  |
| 12.5°  | 99.6   | 104.3 | 107.4  | 110.5 | 115.2  | 119.9 | 123.0  | 127.7 | 130.8  | 133.9  | 138.6  |
| 15°    | 98.1   | 101.2 | 105.9  | 109.0 | 115.2  | 121.4 | 126.1  | 132.3 | 138.6  | 143.2  | 151.0  |
| 17.5°  | 93.4   | 99.6  | 104.3  | 109.0 | 115.2  | 123.0 | 129.2  | 135.4 | 144.8  | 154.1  | 166.6  |
| 20°    | 87.2   | 91.8  | 98.1   | 102.7 | 112.1  | 119.9 | 129.2  | 137.0 | 151.0  | 165.0  | 191.5  |
| 22.5°  | 81.0   | 87.2  | 91.8   | 98.1  | 109.0  | 118.3 | 129.2  | 138.6 | 161.9  | 183.7  | 244.4  |
| 25°    | 74.7   | 82.5  | 88.7   | 95.0  | 107.4  | 119.9 | 132.3  | 144.8 | 183.7  | 222.6  | 331.6  |
| 27.5°  | 71.6   | 77.8  | 85.6   | 91.8  | 107.4  | 124.5 | 140.1  | 155.7 | 217.9  | 278.7  | 460.8  |
| 30°    | 66.9   | 74.7  | 81.0   | 88.7  | 109.0  | 129.2 | 149.4  | 169.7 | 264.6  | 359.6  | 624.3  |
| 32.5°  | 62.3   | 70.1  | 77.8   | 85.6  | 112.1  | 138.6 | 163.5  | 189.9 | 314.5  | 437.4  | 779.9  |
| 35°    | 57.6   | 66.9  | 74.7   | 82.5  | 116.8  | 152.6 | 186.8  | 221.1 | 359.6  | 496.6  | 885.8  |
| 37.5°  | 56.0   | 65.4  | 73.2   | 81.0  | 118.3  | 154.1 | 191.5  | 227.3 | 364.3  | 501.3  | 965.2  |
| 40°    | 57.6   | 65.4  | 74.7   | 82.5  | 113.6  | 144.8 | 174.4  | 205.5 | 348.7  | 490.4  | 1044.6 |
| 42.5°  | 57.6   | 66.9  | 76.3   | 85.6  | 110.5  | 135.4 | 160.3  | 185.3 | 344.0  | 502.8  | 1200.3 |
| 45°    | 56.0   | 65.4  | 74.7   | 84.1  | 107.4  | 129.2 | 152.6  | 174.4 | 372.1  | 568.2  | 1511.6 |
| 47.5°  | 54.5   | 63.8  | 73.2   | 82.5  | 105.9  | 129.2 | 152.6  | 175.9 | 481.0  | 784.6  | 2304.0 |
| 50°    | 54.5   | 63.8  | 71.6   | 79.4  | 107.4  | 137.0 | 165.0  | 193.0 | 700.5  | 1206.5 | 3529.2 |
| 52.5°  | 57.6   | 65.4  | 71.6   | 77.8  | 110.5  | 144.8 | 177.5  | 210.2 | 890.5  | 1569.2 | 4443.0 |
| 55°    | 62.3   | 66.9  | 73.2   | 77.8  | 118.3  | 157.2 | 197.7  | 236.6 | 948.1  | 1659.5 | 4544.2 |
| 57.5°  | 68.5   | 73.2  | 77.8   | 82.5  | 132.3  | 182.1 | 230.4  | 280.2 | 952.7  | 1623.7 | 4100.5 |
| 60°    | 76.3   | 82.5  | 87.2   | 91.8  | 144.8  | 199.3 | 252.2  | 305.1 | 862.4  | 1418.2 | 3505.8 |
| 62.5°  | 93.4   | 101.2 | 107.4  | 115.2 | 166.6  | 216.4 | 267.8  | 317.6 | 716.1  | 1114.6 | 2739.9 |
| 65°    | 107.4  | 113.6 | 119.9  | 126.1 | 175.9  | 227.3 | 277.1  | 326.9 | 607.1  | 887.3  | 2070.5 |
| 67.5°  | 110.5  | 116.8 | 121.4  | 127.7 | 179.0  | 230.4 | 280.2  | 331.6 | 520.0  | 706.8  | 1528.7 |
| 70°    | 112.1  | 119.9 | 129.2  | 137.0 | 189.9  | 242.9 | 294.2  | 347.2 | 460.8  | 574.4  | 1081.9 |
| 72.5°  | 107.4  | 123.0 | 137.0  | 151.0 | 200.8  | 249.1 | 298.9  | 347.2 | 428.1  | 509.1  | 804.8  |
| 75°    | 107.4  | 129.2 | 149.4  | 169.7 | 207.0  | 242.9 | 280.2  | 316.0 | 378.3  | 440.6  | 585.3  |
| 77.5°  | 113.6  | 141.7 | 169.7  | 197.7 | 219.5  | 239.7 | 261.5  | 281.8 | 322.2  | 362.7  | 440.6  |
| 80°    | 113.6  | 143.2 | 171.2  | 200.8 | 210.2  | 221.1 | 230.4  | 239.7 | 244.4  | 249.1  | 247.5  |
| 82.5°  | 98.1   | 121.4 | 144.8  | 168.1 | 157.2  | 146.3 | 135.4  | 124.5 | 116.8  | 107.4  | 112.1  |
| 85°    | 49.8   | 54.5  | 57.6   | 60.7  | 56.0   | 51.4  | 46.7   | 42.0  | 38.9   | 34.2   | 32.7   |
| 87.5°  | 20.2   | 20.2  | 18.7   | 18.7  | 18.7   | 18.7  | 17.1   | 17.1  | 17.1   | 17.1   | 15.6   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  | 300°    |
|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 90.3   | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    |
| 2.5°   | 116.8  | 115.2   | 115.2   | 113.6   | 112.1   | 110.5   | 109.0   | 107.4   | 105.9   | 104.3   | 102.7   |
| 5°     | 121.4  | 121.4   | 121.4   | 119.9   | 119.9   | 118.3   | 118.3   | 116.8   | 115.2   | 113.6   | 112.1   |
| 7.5°   | 126.1  | 127.7   | 127.7   | 129.2   | 129.2   | 129.2   | 129.2   | 127.7   | 127.7   | 127.7   | 126.1   |
| 10°    | 133.9  | 135.4   | 137.0   | 138.6   | 140.1   | 141.7   | 141.7   | 143.2   | 143.2   | 143.2   | 144.8   |
| 12.5°  | 143.2  | 147.9   | 151.0   | 155.7   | 158.8   | 163.5   | 166.6   | 171.2   | 174.4   | 177.5   | 179.0   |
| 15°    | 157.2  | 165.0   | 174.4   | 182.1   | 189.9   | 200.8   | 213.3   | 224.2   | 235.1   | 252.2   | 270.9   |
| 17.5°  | 177.5  | 202.4   | 227.3   | 250.6   | 275.5   | 330.0   | 384.5   | 437.4   | 491.9   | 571.3   | 649.2   |
| 20°    | 216.4  | 291.1   | 364.3   | 439.0   | 512.2   | 703.7   | 893.6   | 1085.1  | 1275.0  | 1478.9  | 1684.4  |
| 22.5°  | 303.6  | 487.3   | 671.0   | 854.7   | 1038.4  | 1438.4  | 1837.0  | 2237.1  | 2635.6  | 3104.2  | 3572.8  |
| 25°    | 440.6  | 778.4   | 1116.2  | 1452.5  | 1790.3  | 2416.1  | 3043.5  | 3669.3  | 4295.1  | 4903.8  | 5512.5  |
| 27.5°  | 641.4  | 1158.2  | 1675.1  | 2190.4  | 2707.2  | 3555.6  | 4405.6  | 5254.0  | 6102.5  | 6790.6  | 7478.6  |
| 30°    | 888.9  | 1589.4  | 2290.0  | 2990.5  | 3691.1  | 4656.3  | 5621.4  | 6585.1  | 7550.3  | 8302.2  | 9055.6  |
| 32.5°  | 1122.4 | 1980.2  | 2838.0  | 3694.2  | 4551.9  | 5651.0  | 6751.6  | 7850.7  | 8949.8  | 9771.7  | 10595.3 |
| 35°    | 1275.0 | 2311.8  | 3350.1  | 4386.9  | 5423.7  | 6613.1  | 7802.5  | 8990.3  | 10179.6 | 11118.3 | 12057.1 |
| 37.5°  | 1427.5 | 2624.7  | 3820.3  | 5017.4  | 6213.0  | 7519.1  | 8825.2  | 10131.4 | 11437.5 | 12597.3 | 13758.6 |
| 40°    | 1598.8 | 3003.0  | 4405.6  | 5809.8  | 7212.4  | 8759.9  | 10305.7 | 11853.1 | 13399.0 | 15035.1 | 16671.3 |
| 42.5°  | 1896.1 | 3630.4  | 5366.1  | 7100.4  | 8834.6  | 10881.7 | 12928.8 | 14974.4 | 17021.6 | 19356.7 | 21691.8 |
| 45°    | 2455.0 | 4899.1  | 7344.8  | 9788.9  | 12233.0 | 14944.8 | 17658.3 | 20370.1 | 23082.0 | 26189.3 | 29296.6 |
| 47.5°  | 3823.4 | 7186.0  | 10547.0 | 13909.6 | 17270.6 | 20198.9 | 23125.6 | 26053.8 | 28980.5 | 32075.4 | 35170.2 |
| 50°    | 5850.3 | 9764.0  | 13677.6 | 17589.8 | 21503.4 | 24153.0 | 26801.1 | 29450.7 | 32098.7 | 35042.5 | 37986.4 |
| 52.5°  | 7316.7 | 11393.9 | 15472.6 | 19549.7 | 23626.9 | 26018.0 | 28410.8 | 30801.9 | 33193.1 | 35943.9 | 38694.7 |
| 55°    | 7427.3 | 11481.1 | 15536.4 | 19590.2 | 23644.0 | 26046.1 | 28448.1 | 30850.2 | 33252.3 | 36168.1 | 39085.4 |
| 57.5°  | 6575.7 | 10596.8 | 14616.4 | 18637.5 | 22657.0 | 25392.2 | 28125.9 | 30861.1 | 33594.8 | 36747.2 | 39899.6 |
| 60°    | 5593.4 | 9616.1  | 13637.2 | 17659.8 | 21680.9 | 24831.8 | 27984.2 | 31135.1 | 34286.0 | 37239.1 | 40190.7 |
| 62.5°  | 4363.6 | 8501.4  | 12640.8 | 16778.7 | 20916.6 | 24115.7 | 27314.8 | 30512.4 | 33711.5 | 35926.8 | 38143.6 |
| 65°    | 3252.1 | 7270.0  | 11288.0 | 15304.5 | 19322.4 | 21884.9 | 24447.3 | 27008.1 | 29570.5 | 30942.0 | 32315.1 |
| 67.5°  | 2350.7 | 5816.0  | 9279.8  | 12745.1 | 16208.9 | 18042.8 | 19876.6 | 21708.9 | 23542.8 | 24592.0 | 25642.9 |
| 70°    | 1589.4 | 3990.0  | 6388.9  | 8789.4  | 11188.4 | 12695.3 | 14203.8 | 15710.8 | 17217.7 | 18634.3 | 20049.4 |
| 72.5°  | 1100.6 | 2448.8  | 3798.5  | 5146.6  | 6494.8  | 8011.1  | 9525.8  | 11042.1 | 12556.8 | 14055.9 | 15555.1 |
| 75°    | 730.1  | 1343.5  | 1958.4  | 2571.8  | 3185.1  | 4307.5  | 5431.5  | 6553.9  | 7676.4  | 8569.9  | 9463.5  |
| 77.5°  | 518.4  | 702.1   | 887.3   | 1071.0  | 1254.7  | 1464.9  | 1676.6  | 1886.8  | 2096.9  | 2416.1  | 2735.2  |
| 80°    | 246.0  | 269.3   | 292.7   | 314.5   | 337.8   | 414.1   | 490.4   | 566.7   | 642.9   | 723.9   | 804.8   |
| 82.5°  | 116.8  | 126.1   | 135.4   | 143.2   | 152.6   | 160.3   | 168.1   | 175.9   | 183.7   | 175.9   | 166.6   |
| 85°    | 31.1   | 31.1    | 32.7    | 32.7    | 32.7    | 32.7    | 32.7    | 32.7    | 32.7    | 31.1    | 29.6    |
| 87.5°  | 14.0   | 14.0    | 14.0    | 14.0    | 14.0    | 14.0    | 14.0    | 12.5    | 12.5    | 10.9    | 10.9    |
| 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  | 325°    | 327.5°  |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    |
| 2.5°   | 101.2   | 99.6    | 98.1    | 96.5    | 95.0    | 91.8    | 91.8    | 90.3    | 90.3    | 88.7    | 88.7    |
| 5°     | 110.5   | 109.0   | 107.4   | 105.9   | 105.9   | 104.3   | 102.7   | 102.7   | 101.2   | 99.6    | 99.6    |
| 7.5°   | 126.1   | 124.5   | 123.0   | 121.4   | 121.4   | 119.9   | 119.9   | 118.3   | 118.3   | 116.8   | 115.2   |
| 10°    | 144.8   | 144.8   | 144.8   | 144.8   | 144.8   | 143.2   | 143.2   | 143.2   | 141.7   | 141.7   | 140.1   |
| 12.5°  | 182.1   | 183.7   | 186.8   | 189.9   | 194.6   | 194.6   | 194.6   | 193.0   | 193.0   | 191.5   | 186.8   |
| 15°    | 288.0   | 305.1   | 317.6   | 330.0   | 340.9   | 365.8   | 362.7   | 358.1   | 354.9   | 350.3   | 333.1   |
| 17.5°  | 728.6   | 806.4   | 848.4   | 888.9   | 930.9   | 1046.1  | 1027.5  | 1008.8  | 991.7   | 973.0   | 890.5   |
| 20°    | 1888.3  | 2092.3  | 2227.7  | 2363.2  | 2500.1  | 2716.5  | 2663.6  | 2610.7  | 2557.7  | 2504.8  | 2280.6  |
| 22.5°  | 4039.8  | 4508.4  | 4712.3  | 4916.2  | 5118.6  | 5380.1  | 5210.5  | 5040.8  | 4872.6  | 4703.0  | 4287.3  |
| 25°    | 6119.6  | 6728.3  | 7072.3  | 7416.4  | 7758.9  | 7908.3  | 7687.3  | 7464.6  | 7243.6  | 7021.0  | 6497.9  |
| 27.5°  | 8166.7  | 8854.8  | 9158.4  | 9460.4  | 9764.0  | 10076.9 | 9802.9  | 9527.3  | 9253.3  | 8979.4  | 8376.9  |
| 30°    | 9807.6  | 10559.5 | 10887.9 | 11214.9 | 11543.3 | 11761.3 | 11477.9 | 11193.1 | 10909.7 | 10626.4 | 9978.8  |
| 32.5°  | 11417.2 | 12239.2 | 12598.8 | 12958.4 | 13316.5 | 13629.4 | 13280.7 | 12930.4 | 12581.7 | 12233.0 | 11457.7 |
| 35°    | 12994.2 | 13933.0 | 14428.0 | 14923.0 | 15418.1 | 15709.2 | 15295.1 | 14879.5 | 14465.4 | 14051.3 | 13146.8 |
| 37.5°  | 14918.4 | 16078.2 | 16632.4 | 17186.6 | 17740.8 | 18271.6 | 17815.5 | 17357.8 | 16901.7 | 16444.0 | 15332.5 |
| 40°    | 18307.4 | 19943.6 | 20793.6 | 21645.1 | 22495.1 | 23180.1 | 22604.1 | 22028.1 | 21452.1 | 20876.1 | 19443.9 |
| 42.5°  | 24026.9 | 26362.1 | 27584.1 | 28804.6 | 30026.7 | 31096.2 | 30490.6 | 29885.0 | 29279.4 | 28673.9 | 26738.8 |
| 45°    | 32403.8 | 35511.1 | 37000.9 | 38489.2 | 39979.0 | 40760.5 | 39888.7 | 39015.4 | 38143.6 | 37271.8 | 34871.3 |
| 47.5°  | 38263.5 | 41358.3 | 42684.6 | 44011.0 | 45337.4 | 46229.4 | 45163.0 | 44096.6 | 43031.8 | 41965.4 | 39373.4 |
| 50°    | 40928.6 | 43872.4 | 45203.5 | 46532.9 | 47864.0 | 48572.3 | 47340.9 | 46107.9 | 44876.6 | 43645.2 | 41006.5 |
| 52.5°  | 41443.9 | 44194.7 | 45782.6 | 47372.0 | 48959.9 | 49906.4 | 48452.4 | 46996.9 | 45542.8 | 44087.3 | 41395.7 |
| 55°    | 42001.2 | 44917.0 | 46758.7 | 48601.9 | 50443.5 | 51754.3 | 50110.4 | 48464.9 | 46820.9 | 45175.5 | 42287.7 |
| 57.5°  | 43050.5 | 46202.9 | 48039.9 | 49875.3 | 51712.3 | 52825.3 | 51176.7 | 49526.6 | 47878.0 | 46229.4 | 43268.4 |
| 60°    | 43143.9 | 46095.5 | 47674.0 | 49254.1 | 50832.7 | 51533.2 | 49956.2 | 48377.7 | 46800.7 | 45223.7 | 42645.7 |
| 62.5°  | 40358.9 | 42574.1 | 43670.1 | 44766.0 | 45862.0 | 46623.2 | 44977.7 | 43330.7 | 41685.2 | 40038.2 | 37986.4 |
| 65°    | 33686.6 | 35058.1 | 35931.4 | 36804.8 | 37678.1 | 38585.7 | 37078.8 | 35571.8 | 34064.9 | 32558.0 | 31060.4 |
| 67.5°  | 26692.1 | 27741.4 | 28891.8 | 30042.2 | 31192.7 | 32162.5 | 30956.1 | 29748.0 | 28541.5 | 27335.0 | 25647.5 |
| 70°    | 21466.1 | 22881.2 | 24174.8 | 25468.5 | 26762.2 | 27556.1 | 26345.0 | 25132.2 | 23921.1 | 22708.4 | 20871.4 |
| 72.5°  | 17054.2 | 18553.4 | 19633.8 | 20712.6 | 21793.0 | 21987.6 | 21097.1 | 20206.7 | 19317.8 | 18427.3 | 16772.5 |
| 75°    | 10355.5 | 11249.1 | 11270.9 | 11291.1 | 11312.9 | 11498.2 | 10760.3 | 10022.4 | 9286.0  | 8548.1  | 7886.5  |
| 77.5°  | 3054.4  | 3373.5  | 3636.6  | 3898.1  | 4161.2  | 4478.8  | 4207.9  | 3935.5  | 3664.6  | 3393.7  | 3035.7  |
| 80°    | 884.2   | 965.2   | 1033.7  | 1100.6  | 1169.1  | 1128.6  | 1064.8  | 1001.0  | 937.2   | 873.3   | 783.0   |
| 82.5°  | 158.8   | 149.4   | 147.9   | 146.3   | 146.3   | 138.6   | 126.1   | 113.6   | 101.2   | 88.7    | 84.1    |
| 85°    | 28.0    | 26.5    | 24.9    | 23.4    | 21.8    | 20.2    | 17.1    | 15.6    | 12.5    | 9.3     | 7.8     |
| 87.5°  | 9.3     | 7.8     | 6.2     | 4.7     | 4.7     | 1.6     | 1.6     | 1.6     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064715

CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    | 352.5°  | 355°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    | 90.3    |
| 2.5°   | 88.7    | 87.2    | 87.2    | 87.2    | 87.2    | 85.6    | 85.6    | 85.6    | 85.6    | 84.1    | 84.1    |
| 5°     | 98.1    | 98.1    | 96.5    | 96.5    | 95.0    | 95.0    | 93.4    | 93.4    | 91.8    | 91.8    | 90.3    |
| 7.5°   | 115.2   | 113.6   | 112.1   | 110.5   | 109.0   | 105.9   | 104.3   | 102.7   | 102.7   | 101.2   | 99.6    |
| 10°    | 138.6   | 135.4   | 133.9   | 130.8   | 129.2   | 126.1   | 123.0   | 119.9   | 116.8   | 113.6   | 110.5   |
| 12.5°  | 182.1   | 175.9   | 171.2   | 165.0   | 158.8   | 154.1   | 147.9   | 143.2   | 137.0   | 132.3   | 126.1   |
| 15°    | 316.0   | 300.5   | 283.3   | 263.1   | 241.3   | 221.1   | 199.3   | 186.8   | 172.8   | 160.3   | 146.3   |
| 17.5°  | 808.0   | 727.0   | 644.5   | 577.6   | 510.6   | 445.2   | 378.3   | 330.0   | 281.8   | 232.0   | 183.7   |
| 20°    | 2056.5  | 1832.3  | 1608.1  | 1387.1  | 1164.5  | 943.4   | 720.8   | 608.7   | 496.6   | 384.5   | 272.4   |
| 22.5°  | 3870.1  | 3454.4  | 3037.2  | 2634.0  | 2229.3  | 1826.1  | 1422.9  | 1169.1  | 916.9   | 663.2   | 409.4   |
| 25°    | 5973.3  | 5450.2  | 4927.1  | 4264.0  | 3599.2  | 2936.0  | 2272.9  | 1860.3  | 1447.8  | 1035.2  | 622.7   |
| 27.5°  | 7772.9  | 7170.4  | 6567.9  | 5761.5  | 4955.1  | 4148.8  | 3342.4  | 2727.4  | 2114.1  | 1499.2  | 884.2   |
| 30°    | 9331.2  | 8683.6  | 8036.0  | 7097.2  | 6158.5  | 5219.8  | 4281.1  | 3512.0  | 2743.0  | 1974.0  | 1204.9  |
| 32.5°  | 10682.4 | 9907.2  | 9131.9  | 8163.6  | 7195.3  | 6227.0  | 5258.7  | 4315.3  | 3371.9  | 2427.0  | 1483.6  |
| 35°    | 12240.8 | 11336.3 | 10430.3 | 9356.1  | 8280.4  | 7206.2  | 6132.1  | 5067.2  | 4000.9  | 2936.0  | 1869.7  |
| 37.5°  | 14221.0 | 13111.0 | 11999.5 | 10802.3 | 9605.2  | 8409.6  | 7212.4  | 5995.1  | 4777.7  | 3560.3  | 2342.9  |
| 40°    | 18011.6 | 16579.4 | 15147.2 | 13626.3 | 12103.8 | 10582.8 | 9061.9  | 7567.4  | 6072.9  | 4576.9  | 3082.4  |
| 42.5°  | 24803.8 | 22868.7 | 20933.7 | 18909.9 | 16884.6 | 14860.8 | 12835.4 | 10727.6 | 8618.2  | 6510.3  | 4400.9  |
| 45°    | 32469.2 | 30068.7 | 27666.6 | 25395.3 | 23122.5 | 20851.2 | 18579.9 | 15687.4 | 12795.0 | 9902.5  | 7010.1  |
| 47.5°  | 36779.9 | 34187.9 | 31595.9 | 29446.0 | 27296.1 | 25146.3 | 22996.4 | 19878.2 | 16760.0 | 13641.8 | 10523.7 |
| 50°    | 38366.2 | 35727.5 | 33088.8 | 31110.2 | 29130.0 | 27151.4 | 25171.2 | 22048.3 | 18923.9 | 15801.1 | 12676.7 |
| 52.5°  | 38704.0 | 36012.4 | 33320.8 | 31329.7 | 29338.6 | 27349.1 | 25358.0 | 22255.4 | 19152.7 | 16048.6 | 12946.0 |
| 55°    | 39398.3 | 36510.6 | 33621.2 | 31351.5 | 29081.7 | 26812.0 | 24542.2 | 21389.8 | 18237.4 | 15084.9 | 11932.5 |
| 57.5°  | 40305.9 | 37345.0 | 34384.0 | 31798.3 | 29212.5 | 26628.3 | 24042.5 | 20595.9 | 17149.2 | 13701.0 | 10254.3 |
| 60°    | 40067.7 | 37491.3 | 34913.3 | 32143.9 | 29372.8 | 26603.4 | 23832.4 | 20041.7 | 16249.4 | 12458.7 | 8666.5  |
| 62.5°  | 35933.0 | 33881.2 | 31827.8 | 29550.3 | 27271.2 | 24993.7 | 22716.2 | 18813.4 | 14910.6 | 11007.8 | 7105.0  |
| 65°    | 29561.2 | 28063.6 | 26566.0 | 24733.7 | 22899.9 | 21067.6 | 19235.3 | 15735.7 | 12237.6 | 8738.1  | 5238.5  |
| 67.5°  | 23958.4 | 22270.9 | 20581.8 | 19121.6 | 17659.8 | 16199.6 | 14737.8 | 11983.9 | 9230.0  | 6476.1  | 3722.2  |
| 70°    | 19034.4 | 17199.0 | 15362.1 | 13936.1 | 12508.5 | 11082.5 | 9656.5  | 7825.8  | 5996.6  | 4165.9  | 2335.1  |
| 72.5°  | 15116.1 | 13461.3 | 11806.4 | 10285.5 | 8763.0  | 7242.0  | 5719.5  | 4637.6  | 3555.6  | 2473.7  | 1391.7  |
| 75°    | 7224.9  | 6563.3  | 5901.7  | 5106.2  | 4310.7  | 3515.2  | 2719.6  | 2248.0  | 1777.8  | 1306.1  | 834.4   |
| 77.5°  | 2677.6  | 2321.1  | 1963.1  | 1639.3  | 1315.5  | 993.2   | 669.4   | 613.4   | 557.3   | 501.3   | 445.2   |
| 80°    | 692.8   | 604.0   | 513.7   | 449.9   | 384.5   | 320.7   | 256.9   | 232.0   | 208.6   | 183.7   | 158.8   |
| 82.5°  | 79.4    | 73.2    | 68.5    | 65.4    | 60.7    | 57.6    | 52.9    | 48.3    | 43.6    | 37.4    | 32.7    |
| 85°    | 4.7     | 3.1     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P1064715  
 CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 90.3   | 90.3   |
| 2.5°   | 84.1   | 82.5   |
| 5°     | 88.7   | 87.2   |
| 7.5°   | 98.1   | 95.0   |
| 10°    | 107.4  | 104.3  |
| 12.5°  | 121.4  | 116.8  |
| 15°    | 137.0  | 127.7  |
| 17.5°  | 163.5  | 143.2  |
| 20°    | 221.1  | 169.7  |
| 22.5°  | 311.4  | 211.7  |
| 25°    | 457.7  | 292.7  |
| 27.5°  | 636.7  | 389.2  |
| 30°    | 846.9  | 487.3  |
| 32.5°  | 1032.1 | 580.7  |
| 35°    | 1273.4 | 675.6  |
| 37.5°  | 1570.8 | 797.1  |
| 40°    | 2031.6 | 980.8  |
| 42.5°  | 2861.3 | 1320.1 |
| 45°    | 4646.9 | 2282.2 |
| 47.5°  | 7150.2 | 3775.1 |
| 50°    | 8747.4 | 4818.2 |
| 52.5°  | 8878.2 | 4810.4 |
| 55°    | 8104.5 | 4276.4 |
| 57.5°  | 6915.1 | 3574.3 |
| 60°    | 5747.5 | 2827.1 |
| 62.5°  | 4528.6 | 1952.2 |
| 65°    | 3309.7 | 1380.8 |
| 67.5°  | 2377.2 | 1032.1 |
| 70°    | 1563.0 | 790.8  |
| 72.5°  | 1018.1 | 644.5  |
| 75°    | 685.0  | 534.0  |
| 77.5°  | 400.1  | 354.9  |
| 80°    | 141.7  | 124.5  |
| 82.5°  | 26.5   | 18.7   |
| 85°    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |

REPORT NUMBER: P1064715  
CATALOG NUMBER: GLAN-SA4C-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-757-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 5700K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 5571     | CRI (Ra): | 69.9 |      |       |
| CIE u':                   | 0.2033   | R1:       | 68.8 | R9:  | -35.4 |
| CIE v':                   | 0.4806   | R2:       | 72.5 | R10: | 36.7  |
| Duv:                      | 0.0041   | R3:       | 76.8 | R11: | 73.9  |
| CIE x:                    | 0.3308   | R4:       | 72.0 | R12: | 47.8  |
| CIE y:                    | 0.3476   | R5:       | 70.9 | R13: | 68.0  |
| CIE z:                    | 0.3216   | R6:       | 65.6 | R14: | 87.0  |
| Peak Wavelength (nm):     | 442      | R7:       | 75.5 | R15: | 59.8  |
| Dominant Wavelength (nm): | 544      | R8:       | 56.8 |      |       |
| Purity:                   | 3.635698 |           |      |      |       |
| Rf:                       | 70.4     |           |      |      |       |
| Rg:                       | 97.1     |           |      |      |       |



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 120                      | NR            | 620    | 298                      | NR            | 750    | 9                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 167                      | NR            | 625    | 270                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 222                      | NR            | 630    | 245                      | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 279                      | NR            | 635    | 219                      | NR            | 765    | 6                        | NR            | 895    | 0                        | NR            |
| 380    | 1                        | NR            | 510    | 329                      | NR            | 640    | 196                      | NR            | 770    | 5                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 371                      | NR            | 645    | 173                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 403                      | NR            | 650    | 153                      | NR            | 780    | 4                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 424                      | NR            | 655    | 135                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 439                      | NR            | 660    | 117                      | NR            | 790    | 3                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 449                      | NR            | 665    | 103                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 28                       | NR            | 540    | 454                      | NR            | 670    | 89                       | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 459                      | NR            | 675    | 77                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 118                      | NR            | 550    | 463                      | NR            | 680    | 67                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 237                      | NR            | 555    | 466                      | NR            | 685    | 58                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 420                      | NR            | 560    | 467                      | NR            | 690    | 50                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 677                      | NR            | 565    | 469                      | NR            | 695    | 43                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 962                      | NR            | 570    | 469                      | NR            | 700    | 37                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 894                      | NR            | 575    | 466                      | NR            | 705    | 32                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 472                      | NR            | 580    | 461                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 275                      | NR            | 585    | 450                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 180                      | NR            | 590    | 437                      | NR            | 720    | 21                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 420                      | NR            | 725    | 18                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 76                       | NR            | 600    | 400                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 68                       | NR            | 605    | 376                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 69                       | NR            | 610    | 352                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 325                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-7

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR


S/P: 1.84

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 120                      | NR            | 620    | 298                      | NR            | 750    | 9                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 167                      | NR            | 625    | 270                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 222                      | NR            | 630    | 245                      | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 279                      | NR            | 635    | 219                      | NR            | 765    | 6                        | NR            | 895    | 0                        | NR            |
| 380    | 1                        | NR            | 510    | 329                      | NR            | 640    | 196                      | NR            | 770    | 5                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 371                      | NR            | 645    | 173                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 403                      | NR            | 650    | 153                      | NR            | 780    | 4                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 424                      | NR            | 655    | 135                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 439                      | NR            | 660    | 117                      | NR            | 790    | 3                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 449                      | NR            | 665    | 103                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 28                       | NR            | 540    | 454                      | NR            | 670    | 89                       | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 459                      | NR            | 675    | 77                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 118                      | NR            | 550    | 463                      | NR            | 680    | 67                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 237                      | NR            | 555    | 466                      | NR            | 685    | 58                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 420                      | NR            | 560    | 467                      | NR            | 690    | 50                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 677                      | NR            | 565    | 469                      | NR            | 695    | 43                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 962                      | NR            | 570    | 469                      | NR            | 700    | 37                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 894                      | NR            | 575    | 466                      | NR            | 705    | 32                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 472                      | NR            | 580    | 461                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 275                      | NR            | 585    | 450                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 180                      | NR            | 590    | 437                      | NR            | 720    | 21                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 420                      | NR            | 725    | 18                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 76                       | NR            | 600    | 400                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 68                       | NR            | 605    | 376                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 69                       | NR            | 610    | 352                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 325                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |



REPORT NUMBER: SP1-2407-184-7

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 120                         | NR               | 620       | 298                         | NR               | 750       | 9                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 167                         | NR               | 625       | 270                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 222                         | NR               | 630       | 245                         | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 279                         | NR               | 635       | 219                         | NR               | 765       | 6                           | NR               | 895       | 0                           | NR               |
| 380       | 1                           | NR               | 510       | 329                         | NR               | 640       | 196                         | NR               | 770       | 5                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 371                         | NR               | 645       | 173                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 403                         | NR               | 650       | 153                         | NR               | 780       | 4                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 424                         | NR               | 655       | 135                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 439                         | NR               | 660       | 117                         | NR               | 790       | 3                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 449                         | NR               | 665       | 103                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 28                          | NR               | 540       | 454                         | NR               | 670       | 89                          | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 459                         | NR               | 675       | 77                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 118                         | NR               | 550       | 463                         | NR               | 680       | 67                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 237                         | NR               | 555       | 466                         | NR               | 685       | 58                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 420                         | NR               | 560       | 467                         | NR               | 690       | 50                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 677                         | NR               | 565       | 469                         | NR               | 695       | 43                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 962                         | NR               | 570       | 469                         | NR               | 700       | 37                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 894                         | NR               | 575       | 466                         | NR               | 705       | 32                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 472                         | NR               | 580       | 461                         | NR               | 710       | 28                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 275                         | NR               | 585       | 450                         | NR               | 715       | 24                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 180                         | NR               | 590       | 437                         | NR               | 720       | 21                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 107                         | NR               | 595       | 420                         | NR               | 725       | 18                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 76                          | NR               | 600       | 400                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 68                          | NR               | 605       | 376                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 69                          | NR               | 610       | 352                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 325                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-7





TM-30-18

### Summary

$R_f = 70.4$   
 $R_g = 97.1$   
 $CIE R_a = 69.9$   
 $R_g = -35.4$







### Color Vector Graphics




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 52 | CES51 = 87 | CES76 = 40 |
| CES02 = 59 | CES27 = 77 | CES52 = 88 | CES77 = 62 |
| CES03 = 30 | CES28 = 76 | CES53 = 74 | CES78 = 43 |
| CES04 = 68 | CES29 = 46 | CES54 = 79 | CES79 = 72 |
| CES05 = 45 | CES30 = 54 | CES55 = 78 | CES80 = 68 |
| CES06 = 49 | CES31 = 52 | CES56 = 67 | CES81 = 70 |
| CES07 = 38 | CES32 = 49 | CES57 = 64 | CES82 = 87 |
| CES08 = 37 | CES33 = 59 | CES58 = 66 | CES83 = 81 |
| CES09 = 29 | CES34 = 61 | CES59 = 87 | CES84 = 87 |
| CES10 = 72 | CES35 = 78 | CES60 = 91 | CES85 = 83 |
| CES11 = 55 | CES36 = 88 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 71 | CES62 = 77 | CES87 = 74 |
| CES13 = 41 | CES38 = 64 | CES63 = 74 | CES88 = 76 |
| CES14 = 74 | CES39 = 90 | CES64 = 71 | CES89 = 75 |
| CES15 = 70 | CES40 = 81 | CES65 = 63 | CES90 = 73 |
| CES16 = 46 | CES41 = 82 | CES66 = 66 | CES91 = 93 |
| CES17 = 48 | CES42 = 69 | CES67 = 63 | CES92 = 69 |
| CES18 = 55 | CES43 = 67 | CES68 = 71 | CES93 = 82 |
| CES19 = 70 | CES44 = 98 | CES69 = 81 | CES94 = 58 |
| CES20 = 63 | CES45 = 77 | CES70 = 57 | CES95 = 72 |
| CES21 = 85 | CES46 = 76 | CES71 = 54 | CES96 = 78 |
| CES22 = 77 | CES47 = 73 | CES72 = 84 | CES97 = 82 |
| CES23 = 91 | CES48 = 65 | CES73 = 45 | CES98 = 70 |
| CES24 = 90 | CES49 = 77 | CES74 = 92 | CES99 = 59 |
| CES25 = 71 | CES50 = 85 | CES75 = 49 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)