

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064165

Luminaire Tested: **GLAN-SA2A-830-U-T4BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1064165  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA2A-830-U-T4BC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 2xLight Square PACKAGE  
80CRI 3000K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL  
Light Source: (28) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6666.4 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B0 - U0 - G3

Input Watts (W): 55.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1064165

CATALOG NUMBER: GLAN-SA2A-830-U-T4BC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P1064165

CATALOG NUMBER: GLAN-SA2A-830-U-T4BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064165

CATALOG NUMBER: GLAN-SA2A-830-U-T4BC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 23.7     | 0.0    | 23.7   |
|                    | % Fixture | 0.4      | 0.0    | 0.4    |
| <b>Street Side</b> | Lumens    | 6642.7   | 0.0    | 6642.7 |
|                    | % Fixture | 99.6     | 0.0    | 99.6   |
| <b>Total</b>       | Lumens    | 6666.4   | 0.0    | 6666.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 5.6    | 0.1       |
| 10°-20°   | 71.2   | 1.1       |
| 20°-30°   | 253.7  | 3.8       |
| 30°-40°   | 611.5  | 9.2       |
| 40°-50°   | 1023.5 | 15.4      |
| 50°-60°   | 1314.5 | 19.7      |
| 60°-70°   | 1663.5 | 25.0      |
| 70°-80°   | 1483.1 | 22.2      |
| 80°-90°   | 239.7  | 3.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6666.4 | 100.0     |
| 0°-180°   | 6666.4 | 100.0     |



REPORT NUMBER: P1064165


CATALOG NUMBER: GLAN-SA2A-830-U-T4BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 324.8  | 4.9       |                         |      |         |
| FM   | (30°-60°)   | 2944.0 | 44.2      |                         |      |         |
| FH   | (60°-80°)   | 3135.2 | 47.0      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 238.6  | 3.6       |                         |      | G3/500  |
| BL   | (0°-30°)    | 5.7    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 5.5    | 0.1       | B0/220                  |      |         |
| BH   | (60°-80°)   | 11.4   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 1.1    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type IV Short



REPORT NUMBER: P1064165

CATALOG NUMBER: GLAN-SA2A-830-U-T4BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 39°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   |
| 2.5°  | 42.0   | 42.0   | 42.0   | 40.6   | 40.6   | 40.2   | 39.7   | 39.7   | 38.8   | 38.4   | 37.5   |
| 5°    | 63.6   | 62.3   | 59.1   | 57.3   | 53.7   | 51.4   | 49.2   | 46.0   | 42.9   | 40.6   | 37.9   |
| 7.5°  | 144.0  | 147.1  | 136.7  | 117.3  | 97.5   | 88.9   | 74.5   | 60.0   | 49.6   | 42.9   | 38.4   |
| 10°   | 366.9  | 365.1  | 329.9  | 291.1  | 224.7  | 198.1  | 155.2  | 97.9   | 64.1   | 46.9   | 38.8   |
| 12.5° | 624.1  | 622.3  | 580.8  | 528.0  | 440.4  | 384.9  | 303.7  | 182.8  | 92.1   | 53.3   | 38.8   |
| 15°   | 840.3  | 833.1  | 820.0  | 767.6  | 665.2  | 618.7  | 511.3  | 323.1  | 148.9  | 64.1   | 39.7   |
| 17.5° | 983.3  | 977.0  | 964.8  | 945.9  | 880.9  | 825.8  | 739.6  | 507.7  | 241.0  | 83.0   | 41.5   |
| 20°   | 1114.7 | 1110.1 | 1100.2 | 1096.6 | 1054.6 | 1025.3 | 954.0  | 719.8  | 375.5  | 112.8  | 44.2   |
| 22.5° | 1295.2 | 1285.7 | 1289.8 | 1268.1 | 1227.0 | 1191.8 | 1148.1 | 941.8  | 539.7  | 162.5  | 49.2   |
| 25°   | 1516.3 | 1511.8 | 1500.5 | 1485.2 | 1428.3 | 1397.6 | 1330.4 | 1151.2 | 723.4  | 227.4  | 54.6   |
| 27.5° | 1783.5 | 1778.5 | 1775.8 | 1740.6 | 1675.1 | 1641.8 | 1547.9 | 1348.9 | 930.1  | 318.6  | 61.8   |
| 30°   | 2091.2 | 2093.5 | 2075.9 | 2030.8 | 1954.5 | 1907.6 | 1811.0 | 1556.0 | 1141.7 | 425.6  | 69.5   |
| 32.5° | 2409.8 | 2405.3 | 2378.2 | 2325.0 | 2256.8 | 2213.1 | 2090.3 | 1783.0 | 1363.8 | 566.8  | 78.5   |
| 35°   | 2753.3 | 2744.7 | 2673.4 | 2612.5 | 2554.2 | 2499.2 | 2387.3 | 2046.6 | 1585.8 | 725.2  | 90.7   |
| 37.5° | 3099.8 | 3059.7 | 2916.6 | 2839.5 | 2799.3 | 2754.2 | 2649.9 | 2327.7 | 1806.5 | 902.1  | 105.6  |
| 40°   | 3361.6 | 3330.4 | 3160.8 | 3018.6 | 2986.6 | 2948.2 | 2870.6 | 2570.5 | 2041.1 | 1092.1 | 123.7  |
| 42.5° | 3506.4 | 3489.3 | 3336.8 | 3196.4 | 3121.0 | 3087.2 | 3020.9 | 2782.6 | 2273.1 | 1301.9 | 149.8  |
| 45°   | 3568.3 | 3541.6 | 3439.7 | 3374.2 | 3254.2 | 3198.2 | 3119.2 | 2942.8 | 2515.4 | 1540.2 | 186.4  |
| 47.5° | 3549.3 | 3534.0 | 3460.9 | 3484.8 | 3397.7 | 3310.6 | 3194.6 | 3065.5 | 2722.6 | 1813.7 | 236.5  |
| 50°   | 3430.2 | 3417.1 | 3394.5 | 3524.0 | 3513.2 | 3410.3 | 3292.1 | 3162.6 | 2891.8 | 2095.7 | 314.1  |
| 52.5° | 3203.6 | 3198.2 | 3256.0 | 3493.4 | 3578.6 | 3498.3 | 3386.0 | 3248.3 | 3049.7 | 2390.4 | 425.1  |
| 55°   | 2911.7 | 2933.8 | 3098.9 | 3445.5 | 3612.0 | 3563.3 | 3469.0 | 3328.6 | 3176.6 | 2654.0 | 588.9  |
| 57.5° | 2791.6 | 2797.5 | 3003.7 | 3411.7 | 3626.9 | 3620.6 | 3549.8 | 3405.4 | 3293.0 | 2864.7 | 838.9  |
| 60°   | 2932.0 | 2922.9 | 3031.7 | 3437.4 | 3656.7 | 3672.1 | 3621.5 | 3476.7 | 3394.1 | 3045.7 | 1172.0 |
| 62.5° | 3185.6 | 3180.6 | 3215.4 | 3547.1 | 3743.8 | 3775.0 | 3721.3 | 3528.1 | 3483.4 | 3164.8 | 1552.0 |
| 65°   | 3412.1 | 3401.7 | 3466.3 | 3741.6 | 3896.8 | 3918.9 | 3872.0 | 3616.1 | 3522.7 | 3251.5 | 1908.9 |
| 67.5° | 3510.1 | 3507.8 | 3611.6 | 3926.6 | 4057.5 | 4081.4 | 4040.3 | 3737.5 | 3513.7 | 3279.0 | 2066.4 |
| 70°   | 3465.4 | 3456.8 | 3622.9 | 4005.1 | 4148.2 | 4175.2 | 4135.5 | 3782.6 | 3415.7 | 3191.9 | 1833.1 |
| 71°   | 3416.2 | 3393.2 | 3589.0 | 3999.7 | 4160.8 | 4183.8 | 4114.3 | 3741.6 | 3317.4 | 3068.2 | 1621.4 |
| 72.5° | 3263.7 | 3267.7 | 3496.1 | 3943.3 | 4130.6 | 4123.8 | 3994.3 | 3594.4 | 3198.7 | 2787.6 | 1302.4 |
| 75°   | 2888.2 | 2912.1 | 3195.1 | 3706.4 | 3860.7 | 3774.5 | 3576.4 | 3313.3 | 2960.4 | 1998.7 | 904.4  |
| 77.5° | 2360.2 | 2395.8 | 2706.8 | 3250.6 | 3206.8 | 3198.2 | 3190.1 | 2919.3 | 2528.1 | 1073.6 | 629.1  |
| 80°   | 1126.8 | 1204.0 | 1632.7 | 2320.5 | 2520.8 | 2617.9 | 2556.9 | 2352.5 | 1954.9 | 511.3  | 375.9  |
| 82.5° | 73.6   | 72.7   | 102.9  | 195.0  | 821.8  | 1062.3 | 1687.8 | 1681.5 | 1362.9 | 249.1  | 153.4  |
| 85°   | 34.7   | 35.7   | 39.3   | 44.7   | 51.9   | 56.9   | 78.5   | 460.3  | 652.1  | 118.7  | 33.4   |
| 87.5° | 20.3   | 20.8   | 24.4   | 31.1   | 40.6   | 45.1   | 53.7   | 69.0   | 84.8   | 65.4   | 7.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1064165

CATALOG NUMBER: GLAN-SA2A-830-U-T4BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°   | 95°  | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|------|------|------|------|------|------|------|------|------|------|
| 0°    | 36.6  | 36.6 | 36.6 | 36.6 | 36.6 | 36.6 | 36.6 | 36.6 | 36.6 | 36.6 | 36.6 |
| 2.5°  | 37.0  | 36.6 | 35.2 | 33.8 | 32.5 | 31.6 | 31.1 | 31.6 | 31.6 | 32.0 | 32.0 |
| 5°    | 37.0  | 35.7 | 33.4 | 30.7 | 28.9 | 27.1 | 26.2 | 25.7 | 26.2 | 26.2 | 26.2 |
| 7.5°  | 36.6  | 34.3 | 31.1 | 28.0 | 25.7 | 23.5 | 22.6 | 22.1 | 22.1 | 22.6 | 22.6 |
| 10°   | 35.7  | 33.4 | 29.3 | 25.7 | 23.0 | 20.3 | 19.0 | 17.6 | 17.6 | 17.6 | 18.1 |
| 12.5° | 35.2  | 32.0 | 27.1 | 23.5 | 19.9 | 16.7 | 14.0 | 12.6 | 13.1 | 13.1 | 13.1 |
| 15°   | 34.3  | 30.7 | 25.7 | 21.2 | 16.7 | 12.6 | 10.4 | 9.0  | 9.5  | 9.9  | 9.5  |
| 17.5° | 34.3  | 30.2 | 23.9 | 18.5 | 13.1 | 9.5  | 7.7  | 6.8  | 6.8  | 7.2  | 7.2  |
| 20°   | 34.3  | 29.3 | 22.6 | 15.8 | 9.9  | 7.2  | 5.4  | 5.0  | 5.0  | 5.9  | 6.3  |
| 22.5° | 35.2  | 29.3 | 20.8 | 13.1 | 8.1  | 5.4  | 4.1  | 3.6  | 4.1  | 5.0  | 5.4  |
| 25°   | 36.6  | 28.9 | 19.0 | 11.7 | 6.8  | 4.1  | 3.2  | 2.3  | 2.7  | 3.6  | 4.1  |
| 27.5° | 37.9  | 28.4 | 17.1 | 10.4 | 5.4  | 3.2  | 2.3  | 1.8  | 1.4  | 1.8  | 1.8  |
| 30°   | 39.3  | 28.4 | 15.3 | 8.6  | 4.5  | 2.3  | 1.4  | 0.9  | 0.5  | 0.0  | 0.0  |
| 32.5° | 40.2  | 27.5 | 14.0 | 6.8  | 3.6  | 1.8  | 0.9  | 0.5  | 0.0  | 0.0  | 0.0  |
| 35°   | 41.1  | 26.6 | 12.2 | 5.4  | 2.7  | 1.4  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  |
| 37.5° | 42.0  | 25.3 | 10.4 | 4.5  | 2.3  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 40°   | 42.9  | 23.5 | 8.6  | 4.1  | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 42.5° | 43.8  | 22.1 | 7.2  | 3.2  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 45°   | 46.0  | 21.2 | 5.9  | 2.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 47.5° | 50.1  | 20.3 | 5.4  | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 50°   | 56.0  | 19.4 | 5.0  | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 52.5° | 64.1  | 19.0 | 4.5  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 55°   | 78.5  | 18.5 | 4.1  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 57.5° | 103.3 | 18.1 | 4.1  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 60°   | 158.4 | 17.1 | 4.1  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 62.5° | 283.0 | 16.7 | 3.6  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 65°   | 493.2 | 17.1 | 3.6  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 67.5° | 707.2 | 18.1 | 3.2  | 1.4  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 70°   | 605.2 | 15.8 | 3.2  | 1.8  | 0.9  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 71°   | 493.2 | 14.0 | 3.2  | 1.8  | 0.9  | 0.5  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.5° | 317.2 | 10.8 | 2.7  | 1.8  | 0.9  | 0.9  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  |
| 75°   | 134.0 | 9.0  | 2.7  | 1.8  | 1.4  | 0.9  | 0.9  | 0.5  | 0.0  | 0.0  | 0.0  |
| 77.5° | 57.3  | 6.8  | 2.7  | 2.3  | 1.8  | 1.4  | 1.4  | 0.9  | 0.5  | 0.0  | 0.0  |
| 80°   | 21.7  | 5.4  | 3.2  | 2.7  | 2.3  | 2.3  | 1.8  | 0.9  | 0.5  | 0.0  | 0.0  |
| 82.5° | 9.9   | 4.5  | 3.2  | 2.7  | 2.7  | 2.3  | 1.8  | 1.4  | 0.9  | 0.0  | 0.0  |
| 85°   | 6.3   | 4.1  | 3.2  | 2.7  | 2.7  | 2.3  | 2.3  | 1.4  | 0.9  | 0.0  | 0.0  |
| 87.5° | 5.0   | 4.1  | 3.2  | 3.2  | 2.7  | 2.7  | 1.8  | 1.4  | 0.5  | 0.0  | 0.0  |
| 90°   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-9

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-830-U-5WQ

Data in this report applies to families of products including GSS-SB1A-830-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-830-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI  
 3000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3055  
 CIE  $u'$ : 0.2475  
 CIE  $v'$ : 0.5247  
 Duv: 0.0032  
 CIE x: 0.4377  
 CIE y: 0.4124  
 CIE z: 0.1499  
 Peak Wavelength (nm): 604  
 Dominant Wavelength (nm): 581  
 Purity: 55.16339  
 R<sub>f</sub>: 81.5  
 R<sub>g</sub>: 99.2

CRI (Ra): 80.9  
 R1: 79.5  
 R2: 85.6  
 R3: 92.1  
 R4: 82.4  
 R5: 78.9  
 R6: 81.7  
 R7: 85.1  
 R8: 61.9  
 R9: 6.8  
 R10: 67.1  
 R11: 82.5  
 R12: 63.4  
 R13: 80.2  
 R14: 95.1  
 R15: 71.7



### Test Conditions

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-9

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2407-184-9

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 170                      | NR            | 620    | 938                      | NR            | 750    | 35                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 234                      | NR            | 625    | 894                      | NR            | 755    | 30                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 302                      | NR            | 630    | 847                      | NR            | 760    | 26                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 371                      | NR            | 635    | 788                      | NR            | 765    | 22                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 431                      | NR            | 640    | 728                      | NR            | 770    | 19                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 482                      | NR            | 645    | 665                      | NR            | 775    | 16                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 523                      | NR            | 650    | 603                      | NR            | 780    | 14                       | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 553                      | NR            | 655    | 542                      | NR            | 785    | 12                       | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 580                      | NR            | 660    | 484                      | NR            | 790    | 11                       | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 603                      | NR            | 665    | 430                      | NR            | 795    | 9                        | NR            | 925    | 0                        | NR            |
| 410    | 18                       | NR            | 540    | 622                      | NR            | 670    | 377                      | NR            | 800    | 8                        | NR            | 930    | 0                        | NR            |
| 415    | 36                       | NR            | 545    | 644                      | NR            | 675    | 330                      | NR            | 805    | 7                        | NR            | 935    | 0                        | NR            |
| 420    | 71                       | NR            | 550    | 668                      | NR            | 680    | 289                      | NR            | 810    | 6                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 693                      | NR            | 685    | 250                      | NR            | 815    | 5                        | NR            | 945    | 0                        | NR            |
| 430    | 215                      | NR            | 560    | 720                      | NR            | 690    | 218                      | NR            | 820    | 4                        | NR            | 950    | 0                        | NR            |
| 435    | 341                      | NR            | 565    | 754                      | NR            | 695    | 188                      | NR            | 825    | 4                        | NR            | 955    | 0                        | NR            |
| 440    | 514                      | NR            | 570    | 792                      | NR            | 700    | 161                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 576                      | NR            | 575    | 832                      | NR            | 705    | 139                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 358                      | NR            | 580    | 875                      | NR            | 710    | 119                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 222                      | NR            | 585    | 913                      | NR            | 715    | 102                      | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 170                      | NR            | 590    | 950                      | NR            | 720    | 88                       | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 115                      | NR            | 595    | 977                      | NR            | 725    | 76                       | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 88                       | NR            | 600    | 994                      | NR            | 730    | 65                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 87                       | NR            | 605    | 997                      | NR            | 735    | 56                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 96                       | NR            | 610    | 990                      | NR            | 740    | 47                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 122                      | NR            | 615    | 971                      | NR            | 745    | 41                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-9

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.28

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 170                      | NR            | 620    | 938                      | NR            | 750    | 35                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 234                      | NR            | 625    | 894                      | NR            | 755    | 30                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 302                      | NR            | 630    | 847                      | NR            | 760    | 26                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 371                      | NR            | 635    | 788                      | NR            | 765    | 22                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 431                      | NR            | 640    | 728                      | NR            | 770    | 19                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 482                      | NR            | 645    | 665                      | NR            | 775    | 16                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 523                      | NR            | 650    | 603                      | NR            | 780    | 14                       | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 553                      | NR            | 655    | 542                      | NR            | 785    | 12                       | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 580                      | NR            | 660    | 484                      | NR            | 790    | 11                       | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 603                      | NR            | 665    | 430                      | NR            | 795    | 9                        | NR            | 925    | 0                        | NR            |
| 410    | 18                       | NR            | 540    | 622                      | NR            | 670    | 377                      | NR            | 800    | 8                        | NR            | 930    | 0                        | NR            |
| 415    | 36                       | NR            | 545    | 644                      | NR            | 675    | 330                      | NR            | 805    | 7                        | NR            | 935    | 0                        | NR            |
| 420    | 71                       | NR            | 550    | 668                      | NR            | 680    | 289                      | NR            | 810    | 6                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 693                      | NR            | 685    | 250                      | NR            | 815    | 5                        | NR            | 945    | 0                        | NR            |
| 430    | 215                      | NR            | 560    | 720                      | NR            | 690    | 218                      | NR            | 820    | 4                        | NR            | 950    | 0                        | NR            |
| 435    | 341                      | NR            | 565    | 754                      | NR            | 695    | 188                      | NR            | 825    | 4                        | NR            | 955    | 0                        | NR            |
| 440    | 514                      | NR            | 570    | 792                      | NR            | 700    | 161                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 576                      | NR            | 575    | 832                      | NR            | 705    | 139                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 358                      | NR            | 580    | 875                      | NR            | 710    | 119                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 222                      | NR            | 585    | 913                      | NR            | 715    | 102                      | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 170                      | NR            | 590    | 950                      | NR            | 720    | 88                       | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 115                      | NR            | 595    | 977                      | NR            | 725    | 76                       | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 88                       | NR            | 600    | 994                      | NR            | 730    | 65                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 87                       | NR            | 605    | 997                      | NR            | 735    | 56                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 96                       | NR            | 610    | 990                      | NR            | 740    | 47                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 122                      | NR            | 615    | 971                      | NR            | 745    | 41                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-9

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.33

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 170                                    | NR                             | 620               | 938                                    | NR                             | 750               | 35                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 234                                    | NR                             | 625               | 894                                    | NR                             | 755               | 30                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 302                                    | NR                             | 630               | 847                                    | NR                             | 760               | 26                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 371                                    | NR                             | 635               | 788                                    | NR                             | 765               | 22                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 431                                    | NR                             | 640               | 728                                    | NR                             | 770               | 19                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 482                                    | NR                             | 645               | 665                                    | NR                             | 775               | 16                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 523                                    | NR                             | 650               | 603                                    | NR                             | 780               | 14                                     | NR                             | 910               | 0                                      | NR                             |
| 395               | 2                                      | NR                             | 525               | 553                                    | NR                             | 655               | 542                                    | NR                             | 785               | 12                                     | NR                             | 915               | 0                                      | NR                             |
| 400               | 4                                      | NR                             | 530               | 580                                    | NR                             | 660               | 484                                    | NR                             | 790               | 11                                     | NR                             | 920               | 0                                      | NR                             |
| 405               | 8                                      | NR                             | 535               | 603                                    | NR                             | 665               | 430                                    | NR                             | 795               | 9                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 18                                     | NR                             | 540               | 622                                    | NR                             | 670               | 377                                    | NR                             | 800               | 8                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 36                                     | NR                             | 545               | 644                                    | NR                             | 675               | 330                                    | NR                             | 805               | 7                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 71                                     | NR                             | 550               | 668                                    | NR                             | 680               | 289                                    | NR                             | 810               | 6                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 131                                    | NR                             | 555               | 693                                    | NR                             | 685               | 250                                    | NR                             | 815               | 5                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 215                                    | NR                             | 560               | 720                                    | NR                             | 690               | 218                                    | NR                             | 820               | 4                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 341                                    | NR                             | 565               | 754                                    | NR                             | 695               | 188                                    | NR                             | 825               | 4                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 514                                    | NR                             | 570               | 792                                    | NR                             | 700               | 161                                    | NR                             | 830               | 3                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 576                                    | NR                             | 575               | 832                                    | NR                             | 705               | 139                                    | NR                             | 835               | 3                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 358                                    | NR                             | 580               | 875                                    | NR                             | 710               | 119                                    | NR                             | 840               | 3                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 222                                    | NR                             | 585               | 913                                    | NR                             | 715               | 102                                    | NR                             | 845               | 2                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 170                                    | NR                             | 590               | 950                                    | NR                             | 720               | 88                                     | NR                             | 850               | 2                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 115                                    | NR                             | 595               | 977                                    | NR                             | 725               | 76                                     | NR                             | 855               | 2                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 88                                     | NR                             | 600               | 994                                    | NR                             | 730               | 65                                     | NR                             | 860               | 1                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 87                                     | NR                             | 605               | 997                                    | NR                             | 735               | 56                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 96                                     | NR                             | 610               | 990                                    | NR                             | 740               | 47                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 122                                    | NR                             | 615               | 971                                    | NR                             | 745               | 41                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-9

TM-30-18

### Summary

$R_f = 81.5$   
 $R_g = 99.2$   
 $CIE R_a = 80.9$   
 $R_g = 6.8$



### Color Vector Graphics




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 74 | CES51 = 89 | CES76 = 70 |
| CES02 = 63 | CES27 = 88 | CES52 = 91 | CES77 = 86 |
| CES03 = 31 | CES28 = 89 | CES53 = 81 | CES78 = 72 |
| CES04 = 70 | CES29 = 67 | CES54 = 87 | CES79 = 90 |
| CES05 = 50 | CES30 = 68 | CES55 = 85 | CES80 = 88 |
| CES06 = 51 | CES31 = 71 | CES56 = 78 | CES81 = 78 |
| CES07 = 42 | CES32 = 70 | CES57 = 76 | CES82 = 95 |
| CES08 = 41 | CES33 = 71 | CES58 = 78 | CES83 = 90 |
| CES09 = 29 | CES34 = 82 | CES59 = 92 | CES84 = 93 |
| CES10 = 76 | CES35 = 90 | CES60 = 95 | CES85 = 86 |
| CES11 = 59 | CES36 = 93 | CES61 = 93 | CES86 = 72 |
| CES12 = 65 | CES37 = 87 | CES62 = 83 | CES87 = 85 |
| CES13 = 43 | CES38 = 75 | CES63 = 77 | CES88 = 83 |
| CES14 = 74 | CES39 = 94 | CES64 = 83 | CES89 = 75 |
| CES15 = 71 | CES40 = 89 | CES65 = 77 | CES90 = 81 |
| CES16 = 47 | CES41 = 85 | CES66 = 80 | CES91 = 96 |
| CES17 = 50 | CES42 = 86 | CES67 = 79 | CES92 = 73 |
| CES18 = 56 | CES43 = 81 | CES68 = 84 | CES93 = 84 |
| CES19 = 72 | CES44 = 99 | CES69 = 90 | CES94 = 64 |
| CES20 = 66 | CES45 = 87 | CES70 = 77 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 76 | CES96 = 84 |
| CES22 = 79 | CES47 = 77 | CES72 = 92 | CES97 = 87 |
| CES23 = 92 | CES48 = 71 | CES73 = 71 | CES98 = 81 |
| CES24 = 91 | CES49 = 81 | CES74 = 93 | CES99 = 74 |
| CES25 = 72 | CES50 = 89 | CES75 = 74 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)