

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064721

Luminaire Tested: **GLAN-SA6A-760-U-RBC**

Issue Date: 08/07/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1064721  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA6A-760-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 6xLight Square PACKAGE  
70CRI 5700K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (84) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 19530.5 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3

Input Watts (W): 162.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2.9 fc  
 Type III - Short - N/A

REPORT NUMBER: P1064721  
CATALOG NUMBER: GLAN-SA6A-760-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 97.8     | 0.0    | 97.8    |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 19432.7  | 0.0    | 19432.7 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 19530.5  | 0.0    | 19530.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 7.7     | 0.0       |
| 10°-20°   | 42.9    | 0.2       |
| 20°-30°   | 462.8   | 2.4       |
| 30°-40°   | 1368.7  | 7.0       |
| 40°-50°   | 4079.2  | 20.9      |
| 50°-60°   | 6468.0  | 33.1      |
| 60°-70°   | 5399.3  | 27.6      |
| 70°-80°   | 1664.9  | 8.5       |
| 80°-90°   | 37.0    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 19530.5 | 100.0     |
| 0°-180°   | 19530.5 | 100.0     |



REPORT NUMBER: P1064721


CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 495.4   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 11881.0 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 7027.7  | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 28.6    | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 18.0    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 35.0    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 36.5    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 8.4     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° | 25°  |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|------|
| 0°     | 85.6   | 85.6   | 85.6  | 85.6  | 85.6  | 85.6  | 85.6  | 85.6  | 85.6  | 85.6  | 85.6 |
| 2.5°   | 78.2   | 78.2   | 78.2  | 78.2  | 76.7  | 76.7  | 75.3  | 75.3  | 73.8  | 73.8  | 72.3 |
| 5°     | 82.7   | 82.7   | 81.2  | 79.7  | 79.7  | 78.2  | 76.7  | 75.3  | 75.3  | 73.8  | 72.3 |
| 7.5°   | 90.0   | 88.6   | 87.1  | 85.6  | 82.7  | 81.2  | 78.2  | 76.7  | 75.3  | 72.3  | 70.8 |
| 10°    | 98.9   | 95.9   | 93.0  | 90.0  | 87.1  | 84.1  | 81.2  | 79.7  | 76.7  | 75.3  | 72.3 |
| 12.5°  | 110.7  | 106.3  | 100.4 | 95.9  | 93.0  | 88.6  | 85.6  | 82.7  | 78.2  | 75.3  | 70.8 |
| 15°    | 121.0  | 115.1  | 107.7 | 101.8 | 97.4  | 91.5  | 87.1  | 82.7  | 79.7  | 75.3  | 70.8 |
| 17.5°  | 135.8  | 125.5  | 113.6 | 106.3 | 100.4 | 93.0  | 85.6  | 81.2  | 76.7  | 70.8  | 66.4 |
| 20°    | 160.9  | 140.2  | 118.1 | 109.2 | 100.4 | 91.5  | 82.7  | 76.7  | 72.3  | 66.4  | 62.0 |
| 22.5°  | 200.7  | 165.3  | 129.9 | 116.6 | 104.8 | 91.5  | 79.7  | 73.8  | 67.9  | 62.0  | 56.1 |
| 25°    | 277.5  | 214.0  | 150.5 | 132.8 | 115.1 | 97.4  | 79.7  | 72.3  | 66.4  | 59.0  | 53.1 |
| 27.5°  | 369.0  | 274.5  | 178.6 | 153.5 | 129.9 | 104.8 | 79.7  | 70.8  | 63.5  | 54.6  | 45.8 |
| 30°    | 462.0  | 336.5  | 209.6 | 177.1 | 144.6 | 112.2 | 79.7  | 69.4  | 60.5  | 50.2  | 39.8 |
| 32.5°  | 550.5  | 394.1  | 236.1 | 197.8 | 159.4 | 119.5 | 81.2  | 69.4  | 57.6  | 45.8  | 33.9 |
| 35°    | 640.5  | 441.3  | 240.6 | 200.7 | 160.9 | 119.5 | 79.7  | 66.4  | 54.6  | 41.3  | 29.5 |
| 37.5°  | 755.7  | 494.4  | 231.7 | 191.9 | 153.5 | 113.6 | 75.3  | 63.5  | 51.7  | 38.4  | 26.6 |
| 40°    | 929.8  | 583.0  | 236.1 | 194.8 | 153.5 | 112.2 | 70.8  | 59.0  | 48.7  | 36.9  | 25.1 |
| 42.5°  | 1251.6 | 754.2  | 255.3 | 208.1 | 160.9 | 112.2 | 64.9  | 54.6  | 45.8  | 35.4  | 25.1 |
| 45°    | 2163.7 | 1253.0 | 342.4 | 271.6 | 200.7 | 129.9 | 59.0  | 50.2  | 42.8  | 33.9  | 26.6 |
| 47.5°  | 3579.1 | 2097.3 | 615.5 | 475.2 | 336.5 | 196.3 | 57.6  | 50.2  | 42.8  | 33.9  | 26.6 |
| 50°    | 4567.9 | 2671.4 | 774.8 | 596.3 | 417.7 | 239.1 | 60.5  | 51.7  | 44.3  | 35.4  | 28.0 |
| 52.5°  | 4560.5 | 2712.7 | 863.4 | 662.7 | 463.4 | 262.7 | 63.5  | 54.6  | 47.2  | 38.4  | 29.5 |
| 55°    | 4054.3 | 2467.7 | 879.6 | 676.0 | 473.8 | 270.1 | 67.9  | 59.0  | 50.2  | 41.3  | 32.5 |
| 57.5°  | 3388.7 | 2095.8 | 802.9 | 621.4 | 441.3 | 259.8 | 78.2  | 67.9  | 59.0  | 48.7  | 39.8 |
| 60°    | 2680.2 | 1653.0 | 625.8 | 494.4 | 364.5 | 233.2 | 103.3 | 90.0  | 78.2  | 64.9  | 51.7 |
| 62.5°  | 1850.8 | 1198.4 | 546.1 | 438.3 | 332.1 | 224.3 | 118.1 | 104.8 | 93.0  | 79.7  | 66.4 |
| 65°    | 1309.1 | 901.8  | 493.0 | 401.4 | 311.4 | 219.9 | 128.4 | 113.6 | 100.4 | 85.6  | 70.8 |
| 67.5°  | 978.5  | 717.3  | 454.6 | 376.4 | 298.1 | 219.9 | 141.7 | 124.0 | 107.7 | 90.0  | 72.3 |
| 70°    | 749.8  | 588.9  | 426.5 | 363.1 | 301.1 | 237.6 | 174.2 | 149.1 | 125.5 | 100.4 | 76.7 |
| 72.5°  | 611.0  | 503.3  | 394.1 | 348.3 | 302.6 | 256.8 | 211.1 | 178.6 | 146.1 | 112.2 | 79.7 |
| 75°    | 506.2  | 431.0  | 355.7 | 317.3 | 280.4 | 242.0 | 203.7 | 174.2 | 146.1 | 116.6 | 87.1 |
| 77.5°  | 336.5  | 307.0  | 276.0 | 253.9 | 231.7 | 208.1 | 186.0 | 160.9 | 137.3 | 112.2 | 87.1 |
| 80°    | 118.1  | 113.6  | 109.2 | 118.1 | 126.9 | 135.8 | 144.6 | 126.9 | 110.7 | 93.0  | 76.7 |
| 82.5°  | 17.7   | 16.2   | 14.8  | 16.2  | 17.7  | 19.2  | 20.7  | 22.1  | 23.6  | 25.1  | 26.6 |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  | 52.5° |
|--------|-------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0°     | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  |
| 2.5°   | 72.3  | 72.3 | 70.8  | 70.8 | 70.8  | 69.4 | 69.4  | 67.9 | 67.9  | 67.9 | 66.4  |
| 5°     | 70.8  | 70.8 | 69.4  | 67.9 | 66.4  | 66.4 | 64.9  | 63.5 | 63.5  | 62.0 | 62.0  |
| 7.5°   | 69.4  | 67.9 | 66.4  | 64.9 | 63.5  | 62.0 | 60.5  | 59.0 | 59.0  | 57.6 | 57.6  |
| 10°    | 70.8  | 67.9 | 66.4  | 63.5 | 62.0  | 60.5 | 57.6  | 56.1 | 54.6  | 54.6 | 53.1  |
| 12.5°  | 67.9  | 66.4 | 63.5  | 60.5 | 59.0  | 56.1 | 54.6  | 51.7 | 50.2  | 50.2 | 48.7  |
| 15°    | 67.9  | 64.9 | 60.5  | 57.6 | 54.6  | 53.1 | 50.2  | 47.2 | 45.8  | 44.3 | 42.8  |
| 17.5°  | 63.5  | 60.5 | 56.1  | 53.1 | 50.2  | 47.2 | 44.3  | 41.3 | 39.8  | 38.4 | 36.9  |
| 20°    | 57.6  | 54.6 | 50.2  | 45.8 | 42.8  | 39.8 | 36.9  | 33.9 | 32.5  | 31.0 | 28.0  |
| 22.5°  | 51.7  | 48.7 | 44.3  | 39.8 | 36.9  | 33.9 | 29.5  | 26.6 | 25.1  | 22.1 | 20.7  |
| 25°    | 48.7  | 44.3 | 39.8  | 35.4 | 31.0  | 28.0 | 23.6  | 19.2 | 16.2  | 13.3 | 8.9   |
| 27.5°  | 41.3  | 36.9 | 32.5  | 28.0 | 23.6  | 19.2 | 14.8  | 10.3 | 7.4   | 5.9  | 3.0   |
| 30°    | 35.4  | 31.0 | 26.6  | 22.1 | 16.2  | 11.8 | 7.4   | 1.5  | 1.5   | 1.5  | 0.0   |
| 32.5°  | 29.5  | 25.1 | 19.2  | 14.8 | 11.8  | 7.4  | 4.4   | 0.0  | 0.0   | 0.0  | 0.0   |
| 35°    | 23.6  | 19.2 | 13.3  | 8.9  | 7.4   | 4.4  | 3.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 37.5°  | 20.7  | 16.2 | 10.3  | 4.4  | 3.0   | 3.0  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   |
| 40°    | 19.2  | 13.3 | 7.4   | 1.5  | 1.5   | 1.5  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 42.5°  | 19.2  | 13.3 | 5.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 45°    | 19.2  | 13.3 | 5.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 47.5°  | 19.2  | 13.3 | 5.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 50°    | 20.7  | 14.8 | 7.4   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 52.5°  | 23.6  | 17.7 | 11.8  | 5.9  | 4.4   | 3.0  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   |
| 55°    | 29.5  | 26.6 | 22.1  | 19.2 | 14.8  | 10.3 | 4.4   | 0.0  | 0.0   | 0.0  | 0.0   |
| 57.5°  | 38.4  | 38.4 | 36.9  | 35.4 | 26.6  | 17.7 | 8.9   | 0.0  | 0.0   | 0.0  | 0.0   |
| 60°    | 51.7  | 51.7 | 51.7  | 51.7 | 38.4  | 26.6 | 13.3  | 0.0  | 0.0   | 0.0  | 0.0   |
| 62.5°  | 63.5  | 60.5 | 56.1  | 53.1 | 39.8  | 26.6 | 13.3  | 0.0  | 0.0   | 0.0  | 0.0   |
| 65°    | 63.5  | 57.6 | 50.2  | 42.8 | 32.5  | 22.1 | 10.3  | 0.0  | 0.0   | 0.0  | 0.0   |
| 67.5°  | 59.0  | 47.2 | 33.9  | 22.1 | 16.2  | 11.8 | 5.9   | 0.0  | 0.0   | 0.0  | 0.0   |
| 70°    | 59.0  | 41.3 | 23.6  | 5.9  | 4.4   | 3.0  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   |
| 72.5°  | 59.0  | 39.8 | 19.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 75°    | 64.9  | 44.3 | 22.1  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 77.5°  | 64.9  | 44.3 | 22.1  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 80°    | 57.6  | 38.4 | 19.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 82.5°  | 19.2  | 13.3 | 5.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° | 80°  |
|--------|------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0°     | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 |
| 2.5°   | 66.4 | 66.4  | 66.4 | 64.9  | 64.9 | 64.9  | 64.9 | 63.5  | 63.5 | 63.5  | 63.5 |
| 5°     | 60.5 | 60.5  | 59.0 | 59.0  | 57.6 | 57.6  | 56.1 | 56.1  | 54.6 | 54.6  | 54.6 |
| 7.5°   | 56.1 | 54.6  | 54.6 | 53.1  | 51.7 | 51.7  | 50.2 | 50.2  | 48.7 | 47.2  | 47.2 |
| 10°    | 51.7 | 50.2  | 50.2 | 48.7  | 47.2 | 45.8  | 45.8 | 44.3  | 42.8 | 41.3  | 39.8 |
| 12.5°  | 47.2 | 45.8  | 44.3 | 42.8  | 41.3 | 39.8  | 39.8 | 38.4  | 36.9 | 35.4  | 35.4 |
| 15°    | 41.3 | 39.8  | 38.4 | 36.9  | 35.4 | 33.9  | 33.9 | 32.5  | 31.0 | 29.5  | 28.0 |
| 17.5°  | 35.4 | 33.9  | 33.9 | 32.5  | 31.0 | 29.5  | 28.0 | 25.1  | 23.6 | 22.1  | 19.2 |
| 20°    | 26.6 | 25.1  | 23.6 | 22.1  | 20.7 | 17.7  | 16.2 | 13.3  | 10.3 | 8.9   | 7.4  |
| 22.5°  | 17.7 | 14.8  | 13.3 | 10.3  | 7.4  | 5.9   | 4.4  | 1.5   | 0.0  | 0.0   | 0.0  |
| 25°    | 5.9  | 4.4   | 3.0  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|------|-------|------|-------|------|-------|------|--------|------|--------|
| 0°     | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6  | 85.6 | 85.6   | 85.6 | 85.6   |
| 2.5°   | 62.0  | 62.0 | 62.0  | 60.5 | 60.5  | 60.5 | 60.5  | 60.5 | 60.5   | 60.5 | 60.5   |
| 5°     | 53.1  | 53.1 | 53.1  | 51.7 | 51.7  | 50.2 | 50.2  | 50.2 | 48.7   | 48.7 | 48.7   |
| 7.5°   | 45.8  | 44.3 | 44.3  | 42.8 | 42.8  | 41.3 | 41.3  | 41.3 | 39.8   | 39.8 | 39.8   |
| 10°    | 38.4  | 36.9 | 36.9  | 35.4 | 35.4  | 33.9 | 33.9  | 32.5 | 32.5   | 31.0 | 31.0   |
| 12.5°  | 33.9  | 32.5 | 31.0  | 29.5 | 29.5  | 28.0 | 26.6  | 26.6 | 25.1   | 23.6 | 23.6   |
| 15°    | 26.6  | 25.1 | 23.6  | 22.1 | 20.7  | 19.2 | 17.7  | 17.7 | 16.2   | 14.8 | 13.3   |
| 17.5°  | 17.7  | 14.8 | 13.3  | 11.8 | 11.8  | 10.3 | 8.9   | 7.4  | 5.9    | 4.4  | 4.4    |
| 20°    | 4.4   | 3.0  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0°     | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 |
| 2.5°   | 60.5 | 59.0   | 59.0 | 59.0   | 60.5 | 60.5   | 60.5 | 60.5   | 60.5 | 60.5   | 60.5 |
| 5°     | 48.7 | 47.2   | 47.2 | 47.2   | 47.2 | 47.2   | 47.2 | 47.2   | 47.2 | 47.2   | 47.2 |
| 7.5°   | 39.8 | 38.4   | 38.4 | 38.4   | 38.4 | 36.9   | 36.9 | 36.9   | 36.9 | 36.9   | 36.9 |
| 10°    | 31.0 | 29.5   | 29.5 | 29.5   | 29.5 | 28.0   | 28.0 | 28.0   | 28.0 | 28.0   | 28.0 |
| 12.5°  | 22.1 | 22.1   | 20.7 | 20.7   | 20.7 | 19.2   | 19.2 | 19.2   | 19.2 | 17.7   | 17.7 |
| 15°    | 13.3 | 11.8   | 10.3 | 10.3   | 10.3 | 8.9    | 8.9  | 8.9    | 8.9  | 7.4    | 7.4  |
| 17.5°  | 3.0  | 3.0    | 1.5  | 1.5    | 1.5  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0°     | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   |
| 2.5°   | 62.0   | 62.0 | 63.5   | 63.5 | 64.9   | 67.9 | 69.4   | 70.8 | 73.8   | 76.7 | 78.2   |
| 5°     | 48.7   | 50.2 | 50.2   | 51.7 | 53.1   | 54.6 | 56.1   | 57.6 | 60.5   | 63.5 | 66.4   |
| 7.5°   | 38.4   | 38.4 | 39.8   | 39.8 | 41.3   | 44.3 | 45.8   | 47.2 | 50.2   | 54.6 | 57.6   |
| 10°    | 29.5   | 29.5 | 31.0   | 31.0 | 32.5   | 35.4 | 36.9   | 38.4 | 41.3   | 45.8 | 48.7   |
| 12.5°  | 19.2   | 20.7 | 20.7   | 22.1 | 23.6   | 26.6 | 28.0   | 29.5 | 32.5   | 35.4 | 38.4   |
| 15°    | 8.9    | 10.3 | 10.3   | 11.8 | 13.3   | 16.2 | 17.7   | 19.2 | 22.1   | 26.6 | 29.5   |
| 17.5°  | 1.5    | 1.5  | 3.0    | 3.0  | 4.4    | 5.9  | 7.4    | 8.9  | 13.3   | 16.2 | 20.7   |
| 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.0    | 5.9  | 8.9    |
| 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 1.5  | 1.5    |
| 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185°  | 187.5° | 190°  |
|--------|------|--------|------|--------|------|--------|------|--------|-------|--------|-------|
| 0°     | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6  | 85.6   | 85.6  |
| 2.5°   | 81.2 | 84.1   | 87.1 | 90.0   | 93.0 | 95.9   | 97.4 | 100.4  | 101.8 | 103.3  | 103.3 |
| 5°     | 69.4 | 72.3   | 76.7 | 79.7   | 82.7 | 85.6   | 88.6 | 90.0   | 91.5  | 93.0   | 94.5  |
| 7.5°   | 60.5 | 63.5   | 67.9 | 70.8   | 73.8 | 76.7   | 79.7 | 82.7   | 84.1  | 85.6   | 87.1  |
| 10°    | 51.7 | 56.1   | 59.0 | 63.5   | 66.4 | 69.4   | 72.3 | 75.3   | 78.2  | 79.7   | 82.7  |
| 12.5°  | 41.3 | 45.8   | 50.2 | 53.1   | 57.6 | 62.0   | 64.9 | 67.9   | 70.8  | 73.8   | 75.3  |
| 15°    | 32.5 | 36.9   | 41.3 | 44.3   | 48.7 | 53.1   | 57.6 | 60.5   | 63.5  | 66.4   | 69.4  |
| 17.5°  | 23.6 | 28.0   | 32.5 | 35.4   | 39.8 | 44.3   | 47.2 | 51.7   | 54.6  | 57.6   | 62.0  |
| 20°    | 11.8 | 16.2   | 20.7 | 25.1   | 29.5 | 33.9   | 36.9 | 41.3   | 44.3  | 47.2   | 50.2  |
| 22.5°  | 1.5  | 5.9    | 10.3 | 13.3   | 17.7 | 22.1   | 25.1 | 29.5   | 32.5  | 35.4   | 38.4  |
| 25°    | 0.0  | 1.5    | 4.4  | 5.9    | 7.4  | 10.3   | 13.3 | 16.2   | 19.2  | 22.1   | 26.6  |
| 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.5    | 3.0  | 5.9    | 8.9   | 11.8   | 14.8  |
| 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 3.0    | 4.4   |
| 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 1.5    | 1.5   |
| 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.5    | 1.5   | 3.0    | 5.9   |
| 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.0    | 4.4  | 7.4    | 8.9   | 10.3   | 13.3  |
| 87.5°  | 0.0  | 1.5    | 3.0  | 4.4    | 5.9  | 8.9    | 11.8 | 14.8   | 16.2  | 17.7   | 19.2  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   |
| 2.5°   | 104.8  | 104.8 | 104.8  | 104.8 | 103.3  | 103.3 | 103.3  | 101.8 | 101.8  | 100.4 | 100.4  |
| 5°     | 95.9   | 97.4  | 97.4   | 97.4  | 97.4   | 97.4  | 97.4   | 97.4  | 95.9   | 95.9  | 95.9   |
| 7.5°   | 88.6   | 90.0  | 91.5   | 91.5  | 93.0   | 93.0  | 93.0   | 91.5  | 91.5   | 90.0  | 90.0   |
| 10°    | 84.1   | 85.6  | 85.6   | 87.1  | 87.1   | 87.1  | 87.1   | 87.1  | 87.1   | 87.1  | 87.1   |
| 12.5°  | 78.2   | 79.7  | 81.2   | 81.2  | 82.7   | 82.7  | 82.7   | 82.7  | 81.2   | 81.2  | 81.2   |
| 15°    | 70.8   | 73.8  | 75.3   | 76.7  | 76.7   | 78.2  | 78.2   | 78.2  | 78.2   | 78.2  | 78.2   |
| 17.5°  | 64.9   | 67.9  | 69.4   | 70.8  | 70.8   | 72.3  | 72.3   | 73.8  | 73.8   | 73.8  | 73.8   |
| 20°    | 53.1   | 56.1  | 57.6   | 60.5  | 62.0   | 63.5  | 64.9   | 66.4  | 66.4   | 67.9  | 66.4   |
| 22.5°  | 41.3   | 44.3  | 45.8   | 48.7  | 50.2   | 51.7  | 53.1   | 54.6  | 56.1   | 57.6  | 57.6   |
| 25°    | 29.5   | 32.5  | 33.9   | 36.9  | 38.4   | 39.8  | 41.3   | 42.8  | 42.8   | 44.3  | 45.8   |
| 27.5°  | 16.2   | 19.2  | 22.1   | 23.6  | 26.6   | 28.0  | 29.5   | 31.0  | 32.5   | 33.9  | 35.4   |
| 30°    | 7.4    | 8.9   | 10.3   | 13.3  | 14.8   | 16.2  | 17.7   | 20.7  | 22.1   | 23.6  | 25.1   |
| 32.5°  | 0.0    | 0.0   | 1.5    | 4.4   | 5.9    | 7.4   | 8.9    | 10.3  | 10.3   | 11.8  | 14.8   |
| 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    | 3.0   | 4.4    | 5.9   | 8.9    |
| 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.0    |
| 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.0    |
| 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
| 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
| 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
| 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
| 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
| 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 80°    | 3.0    | 3.0   | 3.0    | 4.4   | 4.4    | 4.4   | 4.4    | 4.4   | 4.4    | 4.4   | 4.4    |
| 82.5°  | 7.4    | 8.9   | 10.3   | 10.3  | 11.8   | 11.8  | 11.8   | 11.8  | 10.3   | 10.3  | 10.3   |
| 85°    | 14.8   | 16.2  | 17.7   | 17.7  | 19.2   | 19.2  | 19.2   | 19.2  | 19.2   | 19.2  | 19.2   |
| 87.5°  | 20.7   | 22.1  | 23.6   | 23.6  | 25.1   | 25.1  | 25.1   | 25.1  | 25.1   | 25.1  | 25.1   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240°  | 242.5° | 245°  |
|--------|------|--------|------|--------|------|--------|------|--------|-------|--------|-------|
| 0°     | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6 | 85.6   | 85.6  | 85.6   | 85.6  |
| 2.5°   | 98.9 | 98.9   | 97.4 | 97.4   | 97.4 | 97.4   | 97.4 | 98.9   | 100.4 | 100.4  | 101.8 |
| 5°     | 94.5 | 94.5   | 93.0 | 93.0   | 93.0 | 94.5   | 94.5 | 95.9   | 97.4  | 98.9   | 100.4 |
| 7.5°   | 90.0 | 88.6   | 88.6 | 90.0   | 90.0 | 91.5   | 91.5 | 93.0   | 94.5  | 95.9   | 97.4  |
| 10°    | 87.1 | 85.6   | 85.6 | 85.6   | 87.1 | 87.1   | 88.6 | 90.0   | 91.5  | 93.0   | 94.5  |
| 12.5°  | 81.2 | 81.2   | 81.2 | 81.2   | 82.7 | 82.7   | 84.1 | 85.6   | 88.6  | 90.0   | 91.5  |
| 15°    | 78.2 | 76.7   | 76.7 | 76.7   | 76.7 | 78.2   | 78.2 | 81.2   | 84.1  | 85.6   | 88.6  |
| 17.5°  | 72.3 | 72.3   | 70.8 | 70.8   | 72.3 | 72.3   | 73.8 | 76.7   | 79.7  | 81.2   | 84.1  |
| 20°    | 66.4 | 64.9   | 63.5 | 63.5   | 64.9 | 64.9   | 66.4 | 69.4   | 72.3  | 73.8   | 76.7  |
| 22.5°  | 57.6 | 56.1   | 56.1 | 56.1   | 56.1 | 57.6   | 57.6 | 60.5   | 64.9  | 67.9   | 70.8  |
| 25°    | 45.8 | 47.2   | 47.2 | 48.7   | 48.7 | 50.2   | 51.7 | 54.6   | 59.0  | 62.0   | 64.9  |
| 27.5°  | 35.4 | 36.9   | 36.9 | 39.8   | 41.3 | 42.8   | 44.3 | 48.7   | 53.1  | 56.1   | 60.5  |
| 30°    | 26.6 | 28.0   | 29.5 | 31.0   | 33.9 | 36.9   | 39.8 | 44.3   | 48.7  | 51.7   | 56.1  |
| 32.5°  | 16.2 | 19.2   | 20.7 | 23.6   | 26.6 | 29.5   | 32.5 | 36.9   | 42.8  | 47.2   | 51.7  |
| 35°    | 11.8 | 13.3   | 16.2 | 17.7   | 20.7 | 23.6   | 26.6 | 32.5   | 36.9  | 42.8   | 47.2  |
| 37.5°  | 5.9  | 8.9    | 11.8 | 14.8   | 17.7 | 20.7   | 23.6 | 29.5   | 35.4  | 39.8   | 45.8  |
| 40°    | 4.4  | 7.4    | 8.9  | 11.8   | 16.2 | 19.2   | 22.1 | 28.0   | 33.9  | 39.8   | 45.8  |
| 42.5°  | 3.0  | 4.4    | 5.9  | 10.3   | 13.3 | 17.7   | 22.1 | 28.0   | 33.9  | 39.8   | 45.8  |
| 45°    | 3.0  | 3.0    | 4.4  | 8.9    | 13.3 | 19.2   | 23.6 | 29.5   | 33.9  | 39.8   | 44.3  |
| 47.5°  | 3.0  | 4.4    | 5.9  | 11.8   | 14.8 | 19.2   | 23.6 | 28.0   | 33.9  | 38.4   | 42.8  |
| 50°    | 4.4  | 5.9    | 7.4  | 13.3   | 16.2 | 20.7   | 23.6 | 29.5   | 33.9  | 39.8   | 44.3  |
| 52.5°  | 3.0  | 4.4    | 5.9  | 11.8   | 16.2 | 22.1   | 26.6 | 32.5   | 38.4  | 42.8   | 48.7  |
| 55°    | 1.5  | 1.5    | 1.5  | 8.9    | 17.7 | 25.1   | 33.9 | 38.4   | 44.3  | 48.7   | 53.1  |
| 57.5°  | 0.0  | 0.0    | 0.0  | 5.9    | 17.7 | 28.0   | 38.4 | 44.3   | 50.2  | 54.6   | 60.5  |
| 60°    | 0.0  | 0.0    | 0.0  | 5.9    | 17.7 | 28.0   | 38.4 | 45.8   | 53.1  | 60.5   | 67.9  |
| 62.5°  | 0.0  | 0.0    | 0.0  | 5.9    | 14.8 | 23.6   | 32.5 | 44.3   | 57.6  | 69.4   | 81.2  |
| 65°    | 0.0  | 0.0    | 0.0  | 4.4    | 11.8 | 19.2   | 26.6 | 44.3   | 62.0  | 78.2   | 95.9  |
| 67.5°  | 0.0  | 0.0    | 0.0  | 4.4    | 11.8 | 17.7   | 25.1 | 44.3   | 62.0  | 81.2   | 98.9  |
| 70°    | 0.0  | 0.0    | 0.0  | 4.4    | 11.8 | 19.2   | 26.6 | 44.3   | 62.0  | 79.7   | 97.4  |
| 72.5°  | 0.0  | 0.0    | 0.0  | 4.4    | 13.3 | 20.7   | 29.5 | 44.3   | 59.0  | 73.8   | 88.6  |
| 75°    | 0.0  | 0.0    | 0.0  | 5.9    | 13.3 | 22.1   | 31.0 | 44.3   | 57.6  | 69.4   | 82.7  |
| 77.5°  | 0.0  | 0.0    | 0.0  | 4.4    | 13.3 | 20.7   | 29.5 | 42.8   | 56.1  | 67.9   | 81.2  |
| 80°    | 4.4  | 3.0    | 3.0  | 7.4    | 13.3 | 19.2   | 25.1 | 38.4   | 53.1  | 66.4   | 79.7  |
| 82.5°  | 8.9  | 8.9    | 7.4  | 10.3   | 13.3 | 17.7   | 22.1 | 33.9   | 47.2  | 59.0   | 70.8  |
| 85°    | 17.7 | 17.7   | 16.2 | 17.7   | 17.7 | 19.2   | 20.7 | 26.6   | 32.5  | 38.4   | 44.3  |
| 87.5°  | 23.6 | 23.6   | 22.1 | 22.1   | 22.1 | 20.7   | 20.7 | 20.7   | 20.7  | 19.2   | 19.2  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   | 272.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|
| 0°     | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   | 85.6  | 85.6   | 85.6   | 85.6   |
| 2.5°   | 103.3  | 104.8 | 104.8  | 106.3 | 107.7  | 109.2 | 109.2  | 110.7 | 110.7  | 110.7  | 110.7  |
| 5°     | 101.8  | 104.8 | 106.3  | 107.7 | 109.2  | 110.7 | 112.2  | 113.6 | 115.1  | 115.1  | 115.1  |
| 7.5°   | 100.4  | 101.8 | 104.8  | 106.3 | 109.2  | 110.7 | 113.6  | 115.1 | 116.6  | 118.1  | 119.5  |
| 10°    | 97.4   | 100.4 | 103.3  | 106.3 | 109.2  | 112.2 | 115.1  | 118.1 | 121.0  | 122.5  | 125.5  |
| 12.5°  | 94.5   | 98.9  | 101.8  | 104.8 | 109.2  | 113.6 | 116.6  | 121.0 | 124.0  | 126.9  | 131.4  |
| 15°    | 93.0   | 95.9  | 100.4  | 103.3 | 109.2  | 115.1 | 119.5  | 125.5 | 131.4  | 135.8  | 143.2  |
| 17.5°  | 88.6   | 94.5  | 98.9   | 103.3 | 109.2  | 116.6 | 122.5  | 128.4 | 137.3  | 146.1  | 157.9  |
| 20°    | 82.7   | 87.1  | 93.0   | 97.4  | 106.3  | 113.6 | 122.5  | 129.9 | 143.2  | 156.4  | 181.5  |
| 22.5°  | 76.7   | 82.7  | 87.1   | 93.0  | 103.3  | 112.2 | 122.5  | 131.4 | 153.5  | 174.2  | 231.7  |
| 25°    | 70.8   | 78.2  | 84.1   | 90.0  | 101.8  | 113.6 | 125.5  | 137.3 | 174.2  | 211.1  | 314.4  |
| 27.5°  | 67.9   | 73.8  | 81.2   | 87.1  | 101.8  | 118.1 | 132.8  | 147.6 | 206.6  | 264.2  | 436.9  |
| 30°    | 63.5   | 70.8  | 76.7   | 84.1  | 103.3  | 122.5 | 141.7  | 160.9 | 250.9  | 340.9  | 591.8  |
| 32.5°  | 59.0   | 66.4  | 73.8   | 81.2  | 106.3  | 131.4 | 155.0  | 180.1 | 298.1  | 414.7  | 739.4  |
| 35°    | 54.6   | 63.5  | 70.8   | 78.2  | 110.7  | 144.6 | 177.1  | 209.6 | 340.9  | 470.8  | 839.8  |
| 37.5°  | 53.1   | 62.0  | 69.4   | 76.7  | 112.2  | 146.1 | 181.5  | 215.5 | 345.4  | 475.2  | 915.1  |
| 40°    | 54.6   | 62.0  | 70.8   | 78.2  | 107.7  | 137.3 | 165.3  | 194.8 | 330.6  | 464.9  | 990.3  |
| 42.5°  | 54.6   | 63.5  | 72.3   | 81.2  | 104.8  | 128.4 | 152.0  | 175.6 | 326.2  | 476.7  | 1137.9 |
| 45°    | 53.1   | 62.0  | 70.8   | 79.7  | 101.8  | 122.5 | 144.6  | 165.3 | 352.7  | 538.7  | 1433.1 |
| 47.5°  | 51.7   | 60.5  | 69.4   | 78.2  | 100.4  | 122.5 | 144.6  | 166.8 | 456.1  | 743.9  | 2184.3 |
| 50°    | 51.7   | 60.5  | 67.9   | 75.3  | 101.8  | 129.9 | 156.4  | 183.0 | 664.2  | 1143.8 | 3345.9 |
| 52.5°  | 54.6   | 62.0  | 67.9   | 73.8  | 104.8  | 137.3 | 168.3  | 199.2 | 844.2  | 1487.7 | 4212.2 |
| 55°    | 59.0   | 63.5  | 69.4   | 73.8  | 112.2  | 149.1 | 187.4  | 224.3 | 898.8  | 1573.3 | 4308.2 |
| 57.5°  | 64.9   | 69.4  | 73.8   | 78.2  | 125.5  | 172.7 | 218.4  | 265.7 | 903.3  | 1539.4 | 3887.5 |
| 60°    | 72.3   | 78.2  | 82.7   | 87.1  | 137.3  | 188.9 | 239.1  | 289.3 | 817.7  | 1344.5 | 3323.7 |
| 62.5°  | 88.6   | 95.9  | 101.8  | 109.2 | 157.9  | 205.2 | 253.9  | 301.1 | 678.9  | 1056.7 | 2597.6 |
| 65°    | 101.8  | 107.7 | 113.6  | 119.5 | 166.8  | 215.5 | 262.7  | 309.9 | 575.6  | 841.3  | 1963.0 |
| 67.5°  | 104.8  | 110.7 | 115.1  | 121.0 | 169.7  | 218.4 | 265.7  | 314.4 | 493.0  | 670.1  | 1449.3 |
| 70°    | 106.3  | 113.6 | 122.5  | 129.9 | 180.1  | 230.2 | 278.9  | 329.1 | 436.9  | 544.6  | 1025.8 |
| 72.5°  | 101.8  | 116.6 | 129.9  | 143.2 | 190.4  | 236.1 | 283.4  | 329.1 | 405.9  | 482.6  | 763.0  |
| 75°    | 101.8  | 122.5 | 141.7  | 160.9 | 196.3  | 230.2 | 265.7  | 299.6 | 358.6  | 417.7  | 554.9  |
| 77.5°  | 107.7  | 134.3 | 160.9  | 187.4 | 208.1  | 227.3 | 248.0  | 267.1 | 305.5  | 343.9  | 417.7  |
| 80°    | 107.7  | 135.8 | 162.3  | 190.4 | 199.2  | 209.6 | 218.4  | 227.3 | 231.7  | 236.1  | 234.7  |
| 82.5°  | 93.0   | 115.1 | 137.3  | 159.4 | 149.1  | 138.7 | 128.4  | 118.1 | 110.7  | 101.8  | 106.3  |
| 85°    | 47.2   | 51.7  | 54.6   | 57.6  | 53.1   | 48.7  | 44.3   | 39.8  | 36.9   | 32.5   | 31.0   |
| 87.5°  | 19.2   | 19.2  | 17.7   | 17.7  | 17.7   | 17.7  | 16.2   | 16.2  | 16.2   | 16.2   | 14.8   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  | 300°    |
|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 85.6   | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    |
| 2.5°   | 110.7  | 109.2   | 109.2   | 107.7   | 106.3   | 104.8   | 103.3   | 101.8   | 100.4   | 98.9    | 97.4    |
| 5°     | 115.1  | 115.1   | 115.1   | 113.6   | 113.6   | 112.2   | 112.2   | 110.7   | 109.2   | 107.7   | 106.3   |
| 7.5°   | 119.5  | 121.0   | 121.0   | 122.5   | 122.5   | 122.5   | 122.5   | 121.0   | 121.0   | 121.0   | 119.5   |
| 10°    | 126.9  | 128.4   | 129.9   | 131.4   | 132.8   | 134.3   | 134.3   | 135.8   | 135.8   | 135.8   | 137.3   |
| 12.5°  | 135.8  | 140.2   | 143.2   | 147.6   | 150.5   | 155.0   | 157.9   | 162.3   | 165.3   | 168.3   | 169.7   |
| 15°    | 149.1  | 156.4   | 165.3   | 172.7   | 180.1   | 190.4   | 202.2   | 212.5   | 222.9   | 239.1   | 256.8   |
| 17.5°  | 168.3  | 191.9   | 215.5   | 237.6   | 261.2   | 312.9   | 364.5   | 414.7   | 466.4   | 541.7   | 615.5   |
| 20°    | 205.2  | 276.0   | 345.4   | 416.2   | 485.6   | 667.1   | 847.2   | 1028.7  | 1208.8  | 1402.1  | 1596.9  |
| 22.5°  | 287.8  | 462.0   | 636.1   | 810.3   | 984.4   | 1363.7  | 1741.6  | 2120.9  | 2498.7  | 2943.0  | 3387.2  |
| 25°    | 417.7  | 738.0   | 1058.2  | 1377.0  | 1697.3  | 2290.6  | 2885.4  | 3478.7  | 4072.0  | 4649.1  | 5226.2  |
| 27.5°  | 608.1  | 1098.1  | 1588.1  | 2076.6  | 2566.6  | 3371.0  | 4176.8  | 4981.2  | 5785.5  | 6437.9  | 7090.2  |
| 30°    | 842.7  | 1506.9  | 2171.1  | 2835.2  | 3499.4  | 4414.4  | 5329.5  | 6243.1  | 7158.1  | 7871.0  | 8585.3  |
| 32.5°  | 1064.1 | 1877.4  | 2690.6  | 3502.3  | 4315.5  | 5357.5  | 6401.0  | 7443.0  | 8485.0  | 9264.3  | 10045.0 |
| 35°    | 1208.8 | 2191.7  | 3176.1  | 4159.1  | 5142.1  | 6269.6  | 7397.2  | 8523.3  | 9650.9  | 10540.9 | 11430.9 |
| 37.5°  | 1353.4 | 2488.4  | 3621.9  | 4756.8  | 5890.3  | 7128.6  | 8366.9  | 9605.2  | 10843.5 | 11943.0 | 13044.0 |
| 40°    | 1515.8 | 2847.0  | 4176.8  | 5508.1  | 6837.9  | 8304.9  | 9770.5  | 11237.5 | 12703.1 | 14254.3 | 15805.5 |
| 42.5°  | 1797.7 | 3441.8  | 5087.4  | 6731.6  | 8375.8  | 10316.6 | 12257.4 | 14196.7 | 16137.5 | 18351.4 | 20565.3 |
| 45°    | 2327.5 | 4644.7  | 6963.3  | 9280.5  | 11597.7 | 14168.7 | 16741.2 | 19312.2 | 21883.2 | 24829.1 | 27775.0 |
| 47.5°  | 3624.8 | 6812.8  | 9999.3  | 13187.2 | 16373.7 | 19149.9 | 21924.6 | 24700.7 | 27475.4 | 30409.5 | 33343.6 |
| 50°    | 5546.4 | 9256.9  | 12967.3 | 16676.2 | 20386.7 | 22898.7 | 25409.2 | 27921.2 | 30431.7 | 33222.6 | 36013.5 |
| 52.5°  | 6936.8 | 10802.1 | 14669.0 | 18534.4 | 22399.8 | 24666.8 | 26935.3 | 29202.2 | 31469.2 | 34077.2 | 36685.1 |
| 55°    | 7041.5 | 10884.8 | 14729.5 | 18572.8 | 22416.0 | 24693.4 | 26970.7 | 29248.0 | 31525.3 | 34289.7 | 37055.5 |
| 57.5°  | 6234.2 | 10046.5 | 13857.3 | 17669.5 | 21480.3 | 24073.5 | 26665.2 | 29258.3 | 31850.0 | 34838.7 | 37827.4 |
| 60°    | 5302.9 | 9116.7  | 12928.9 | 16742.7 | 20554.9 | 23542.2 | 26530.9 | 29518.1 | 32505.3 | 35305.1 | 38103.4 |
| 62.5°  | 4137.0 | 8059.9  | 11984.3 | 15907.3 | 19830.3 | 22863.2 | 25896.2 | 28927.7 | 31960.7 | 34060.9 | 36162.6 |
| 65°    | 3083.2 | 6892.5  | 10701.8 | 14509.6 | 18318.9 | 20748.3 | 23177.6 | 25605.5 | 28034.8 | 29335.1 | 30636.8 |
| 67.5°  | 2228.6 | 5514.0  | 8797.9  | 12083.2 | 15367.1 | 17105.7 | 18844.3 | 20581.5 | 22320.1 | 23314.9 | 24311.1 |
| 70°    | 1506.9 | 3782.7  | 6057.1  | 8333.0  | 10607.3 | 12036.0 | 13466.2 | 14894.8 | 16323.5 | 17666.6 | 19008.2 |
| 72.5°  | 1043.5 | 2321.6  | 3601.2  | 4879.3  | 6157.5  | 7595.0  | 9031.1  | 10468.6 | 11904.6 | 13325.9 | 14747.2 |
| 75°    | 692.2  | 1273.7  | 1856.7  | 2438.2  | 3019.7  | 4083.8  | 5149.4  | 6213.6  | 7277.7  | 8124.9  | 8972.0  |
| 77.5°  | 491.5  | 665.6   | 841.3   | 1015.4  | 1189.6  | 1388.8  | 1589.5  | 1788.8  | 1988.0  | 2290.6  | 2593.2  |
| 80°    | 233.2  | 255.3   | 277.5   | 298.1   | 320.3   | 392.6   | 464.9   | 537.2   | 609.5   | 686.3   | 763.0   |
| 82.5°  | 110.7  | 119.5   | 128.4   | 135.8   | 144.6   | 152.0   | 159.4   | 166.8   | 174.2   | 166.8   | 157.9   |
| 85°    | 29.5   | 29.5    | 31.0    | 31.0    | 31.0    | 31.0    | 31.0    | 31.0    | 31.0    | 29.5    | 28.0    |
| 87.5°  | 13.3   | 13.3    | 13.3    | 13.3    | 13.3    | 13.3    | 13.3    | 11.8    | 11.8    | 10.3    | 10.3    |
| 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  | 325°    | 327.5°  |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    |
| 2.5°   | 95.9    | 94.5    | 93.0    | 91.5    | 90.0    | 87.1    | 87.1    | 85.6    | 85.6    | 84.1    | 84.1    |
| 5°     | 104.8   | 103.3   | 101.8   | 100.4   | 100.4   | 98.9    | 97.4    | 97.4    | 95.9    | 94.5    | 94.5    |
| 7.5°   | 119.5   | 118.1   | 116.6   | 115.1   | 115.1   | 113.6   | 113.6   | 112.2   | 112.2   | 110.7   | 109.2   |
| 10°    | 137.3   | 137.3   | 137.3   | 137.3   | 137.3   | 135.8   | 135.8   | 135.8   | 134.3   | 134.3   | 132.8   |
| 12.5°  | 172.7   | 174.2   | 177.1   | 180.1   | 184.5   | 184.5   | 184.5   | 183.0   | 183.0   | 181.5   | 177.1   |
| 15°    | 273.0   | 289.3   | 301.1   | 312.9   | 323.2   | 346.8   | 343.9   | 339.5   | 336.5   | 332.1   | 315.8   |
| 17.5°  | 690.7   | 764.5   | 804.4   | 842.7   | 882.6   | 991.8   | 974.1   | 956.4   | 940.2   | 922.4   | 844.2   |
| 20°    | 1790.3  | 1983.6  | 2112.0  | 2240.4  | 2370.3  | 2575.5  | 2525.3  | 2475.1  | 2424.9  | 2374.7  | 2162.2  |
| 22.5°  | 3830.0  | 4274.2  | 4467.6  | 4660.9  | 4852.8  | 5100.7  | 4939.9  | 4779.0  | 4619.6  | 4458.7  | 4064.6  |
| 25°    | 5801.8  | 6378.9  | 6705.0  | 7031.2  | 7355.9  | 7497.6  | 7288.0  | 7077.0  | 6867.4  | 6656.3  | 6160.4  |
| 27.5°  | 7742.6  | 8394.9  | 8682.7  | 8969.1  | 9256.9  | 9553.5  | 9293.8  | 9032.5  | 8772.8  | 8513.0  | 7941.8  |
| 30°    | 9298.2  | 10011.1 | 10322.5 | 10632.4 | 10943.8 | 11150.5 | 10881.8 | 10611.8 | 10343.1 | 10074.5 | 9460.5  |
| 32.5°  | 10824.3 | 11603.6 | 11944.5 | 12285.4 | 12624.9 | 12921.5 | 12590.9 | 12258.9 | 11928.3 | 11597.7 | 10862.7 |
| 35°    | 12319.4 | 13209.3 | 13678.7 | 14148.0 | 14617.4 | 14893.4 | 14500.8 | 14106.7 | 13714.1 | 13321.5 | 12464.0 |
| 37.5°  | 14143.6 | 15243.1 | 15768.6 | 16294.0 | 16819.4 | 17322.7 | 16890.3 | 16456.3 | 16023.9 | 15590.0 | 14536.2 |
| 40°    | 17356.6 | 18907.8 | 19713.7 | 20521.0 | 21326.8 | 21976.2 | 21430.1 | 20884.0 | 20338.0 | 19791.9 | 18434.0 |
| 42.5°  | 22779.1 | 24993.0 | 26151.6 | 27308.7 | 28467.2 | 29481.2 | 28907.1 | 28332.9 | 27758.8 | 27184.7 | 25350.1 |
| 45°    | 30721.0 | 33666.9 | 35079.3 | 36490.3 | 37902.7 | 38643.6 | 37817.1 | 36989.1 | 36162.6 | 35336.1 | 33060.3 |
| 47.5°  | 36276.3 | 39210.4 | 40467.8 | 41725.3 | 42982.8 | 43828.5 | 42817.5 | 41806.5 | 40797.0 | 39786.0 | 37328.6 |
| 50°    | 38803.0 | 41593.9 | 42855.8 | 44116.3 | 45378.2 | 46049.7 | 44882.3 | 43713.3 | 42545.9 | 41378.5 | 38876.8 |
| 52.5°  | 39291.5 | 41899.5 | 43404.9 | 44911.8 | 46417.2 | 47314.5 | 45936.1 | 44556.1 | 43177.6 | 41797.6 | 39245.8 |
| 55°    | 39819.9 | 42584.3 | 44330.3 | 46077.7 | 47823.7 | 49066.4 | 47507.9 | 45947.9 | 44389.3 | 42829.3 | 40091.5 |
| 57.5°  | 40814.7 | 43803.4 | 45544.9 | 47285.0 | 49026.6 | 50081.9 | 48518.9 | 46954.4 | 45391.4 | 43828.5 | 41021.3 |
| 60°    | 40903.2 | 43701.5 | 45198.1 | 46696.1 | 48192.7 | 48856.9 | 47361.8 | 45865.2 | 44370.1 | 42875.0 | 40430.9 |
| 62.5°  | 38262.8 | 40363.0 | 41402.1 | 42441.1 | 43480.1 | 44201.9 | 42641.8 | 41080.3 | 39520.3 | 37958.8 | 36013.5 |
| 65°    | 31937.1 | 33237.4 | 34065.4 | 34893.3 | 35721.3 | 36581.8 | 35153.1 | 33724.4 | 32295.7 | 30867.1 | 29447.2 |
| 67.5°  | 25305.9 | 26300.6 | 27391.3 | 28482.0 | 29572.7 | 30492.2 | 29348.4 | 28203.1 | 27059.2 | 25915.4 | 24315.5 |
| 70°    | 20351.2 | 21692.8 | 22919.3 | 24145.8 | 25372.3 | 26125.0 | 24976.7 | 23827.0 | 22678.7 | 21529.0 | 19787.5 |
| 72.5°  | 16168.5 | 17589.8 | 18614.1 | 19636.9 | 20661.2 | 20845.7 | 20001.5 | 19157.2 | 18314.5 | 17470.3 | 15901.4 |
| 75°    | 9817.7  | 10664.9 | 10685.5 | 10704.7 | 10725.4 | 10901.0 | 10201.5 | 9501.9  | 8803.8  | 8104.2  | 7476.9  |
| 77.5°  | 2895.7  | 3198.3  | 3447.7  | 3695.7  | 3945.1  | 4246.2  | 3989.4  | 3731.1  | 3474.3  | 3217.5  | 2878.0  |
| 80°    | 838.3   | 915.1   | 980.0   | 1043.5  | 1108.4  | 1070.0  | 1009.5  | 949.0   | 888.5   | 828.0   | 742.4   |
| 82.5°  | 150.5   | 141.7   | 140.2   | 138.7   | 138.7   | 131.4   | 119.5   | 107.7   | 95.9    | 84.1    | 79.7    |
| 85°    | 26.6    | 25.1    | 23.6    | 22.1    | 20.7    | 19.2    | 16.2    | 14.8    | 11.8    | 8.9     | 7.4     |
| 87.5°  | 8.9     | 7.4     | 5.9     | 4.4     | 4.4     | 1.5     | 1.5     | 1.5     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    | 352.5°  | 355°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    | 85.6    |
| 2.5°   | 84.1    | 82.7    | 82.7    | 82.7    | 82.7    | 81.2    | 81.2    | 81.2    | 81.2    | 79.7    | 79.7    |
| 5°     | 93.0    | 93.0    | 91.5    | 91.5    | 90.0    | 90.0    | 88.6    | 88.6    | 87.1    | 87.1    | 85.6    |
| 7.5°   | 109.2   | 107.7   | 106.3   | 104.8   | 103.3   | 100.4   | 98.9    | 97.4    | 97.4    | 95.9    | 94.5    |
| 10°    | 131.4   | 128.4   | 126.9   | 124.0   | 122.5   | 119.5   | 116.6   | 113.6   | 110.7   | 107.7   | 104.8   |
| 12.5°  | 172.7   | 166.8   | 162.3   | 156.4   | 150.5   | 146.1   | 140.2   | 135.8   | 129.9   | 125.5   | 119.5   |
| 15°    | 299.6   | 284.8   | 268.6   | 249.4   | 228.8   | 209.6   | 188.9   | 177.1   | 163.8   | 152.0   | 138.7   |
| 17.5°  | 766.0   | 689.2   | 611.0   | 547.6   | 484.1   | 422.1   | 358.6   | 312.9   | 267.1   | 219.9   | 174.2   |
| 20°    | 1949.7  | 1737.1  | 1524.6  | 1315.0  | 1104.0  | 894.4   | 683.3   | 577.1   | 470.8   | 364.5   | 258.3   |
| 22.5°  | 3669.1  | 3275.0  | 2879.5  | 2497.2  | 2113.5  | 1731.2  | 1349.0  | 1108.4  | 869.3   | 628.7   | 388.2   |
| 25°    | 5663.0  | 5167.1  | 4671.2  | 4042.5  | 3412.3  | 2783.6  | 2154.8  | 1763.7  | 1372.6  | 981.5   | 590.4   |
| 27.5°  | 7369.2  | 6798.0  | 6226.8  | 5462.3  | 4697.8  | 3933.3  | 3168.8  | 2585.8  | 2004.3  | 1421.3  | 838.3   |
| 30°    | 8846.6  | 8232.6  | 7618.6  | 6728.6  | 5838.7  | 4948.7  | 4058.7  | 3329.6  | 2600.5  | 1871.4  | 1142.4  |
| 32.5°  | 10127.7 | 9392.7  | 8657.7  | 7739.6  | 6821.6  | 5903.6  | 4985.6  | 4091.2  | 3196.8  | 2300.9  | 1406.5  |
| 35°    | 11605.0 | 10747.5 | 9888.6  | 8870.2  | 7850.3  | 6832.0  | 5813.6  | 4804.1  | 3793.1  | 2783.6  | 1772.6  |
| 37.5°  | 13482.4 | 12430.1 | 11376.3 | 10241.3 | 9106.3  | 7972.8  | 6837.9  | 5683.7  | 4529.6  | 3375.4  | 2221.2  |
| 40°    | 17076.2 | 15718.4 | 14360.6 | 12918.6 | 11475.2 | 10033.2 | 8591.2  | 7174.4  | 5757.5  | 4339.2  | 2922.3  |
| 42.5°  | 23515.6 | 21681.0 | 19846.5 | 17927.8 | 16007.7 | 14089.0 | 12168.8 | 10170.5 | 8170.6  | 6172.2  | 4172.4  |
| 45°    | 30782.9 | 28507.1 | 26229.8 | 24076.4 | 21921.6 | 19768.3 | 17614.9 | 14872.7 | 12130.5 | 9388.2  | 6646.0  |
| 47.5°  | 34869.7 | 32412.3 | 29955.0 | 27916.7 | 25878.5 | 23840.3 | 21802.1 | 18845.8 | 15889.6 | 12933.4 | 9977.1  |
| 50°    | 36373.7 | 33872.0 | 31370.4 | 29494.5 | 27617.1 | 25741.3 | 23863.9 | 20903.2 | 17941.1 | 14980.4 | 12018.3 |
| 52.5°  | 36693.9 | 34142.1 | 31590.3 | 29702.6 | 27814.9 | 25928.7 | 24041.0 | 21099.5 | 18158.1 | 15215.1 | 12273.6 |
| 55°    | 37352.2 | 34614.4 | 31875.1 | 29723.2 | 27571.4 | 25419.5 | 23267.6 | 20278.9 | 17290.2 | 14301.5 | 11312.8 |
| 57.5°  | 38212.6 | 35405.5 | 32598.3 | 30146.8 | 27695.3 | 25245.3 | 22793.9 | 19526.2 | 16258.6 | 12989.4 | 9721.8  |
| 60°    | 37986.8 | 35544.2 | 33100.1 | 30474.5 | 27847.4 | 25221.7 | 22594.6 | 19000.8 | 15405.5 | 11811.7 | 8216.4  |
| 62.5°  | 34066.8 | 32121.6 | 30174.9 | 28015.6 | 25854.9 | 23695.6 | 21536.4 | 17836.3 | 14136.2 | 10436.1 | 6736.0  |
| 65°    | 28026.0 | 26606.1 | 25186.3 | 23449.2 | 21710.6 | 19973.4 | 18236.3 | 14918.4 | 11602.1 | 8284.3  | 4966.4  |
| 67.5°  | 22714.2 | 21114.3 | 19512.9 | 18128.5 | 16742.7 | 15358.3 | 13972.4 | 11361.5 | 8750.6  | 6139.8  | 3528.9  |
| 70°    | 18045.9 | 16305.8 | 14564.2 | 13212.3 | 11858.9 | 10507.0 | 9155.0  | 7419.4  | 5685.2  | 3949.5  | 2213.9  |
| 72.5°  | 14331.0 | 12762.1 | 11193.3 | 9751.3  | 8307.9  | 6865.9  | 5422.5  | 4396.7  | 3371.0  | 2345.2  | 1319.5  |
| 75°    | 6849.7  | 6222.4  | 5595.2  | 4841.0  | 4086.8  | 3332.6  | 2578.4  | 2131.2  | 1685.5  | 1238.3  | 791.1   |
| 77.5°  | 2538.6  | 2200.6  | 1861.1  | 1554.1  | 1247.1  | 941.6   | 634.6   | 581.5   | 528.4   | 475.2   | 422.1   |
| 80°    | 656.8   | 572.7   | 487.0   | 426.5   | 364.5   | 304.0   | 243.5   | 219.9   | 197.8   | 174.2   | 150.5   |
| 82.5°  | 75.3    | 69.4    | 64.9    | 62.0    | 57.6    | 54.6    | 50.2    | 45.8    | 41.3    | 35.4    | 31.0    |
| 85°    | 4.4     | 3.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064721

CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064721  
 CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 85.6   | 85.6   |
| 2.5°   | 79.7   | 78.2   |
| 5°     | 84.1   | 82.7   |
| 7.5°   | 93.0   | 90.0   |
| 10°    | 101.8  | 98.9   |
| 12.5°  | 115.1  | 110.7  |
| 15°    | 129.9  | 121.0  |
| 17.5°  | 155.0  | 135.8  |
| 20°    | 209.6  | 160.9  |
| 22.5°  | 295.2  | 200.7  |
| 25°    | 433.9  | 277.5  |
| 27.5°  | 603.6  | 369.0  |
| 30°    | 802.9  | 462.0  |
| 32.5°  | 978.5  | 550.5  |
| 35°    | 1207.3 | 640.5  |
| 37.5°  | 1489.2 | 755.7  |
| 40°    | 1926.1 | 929.8  |
| 42.5°  | 2712.7 | 1251.6 |
| 45°    | 4405.6 | 2163.7 |
| 47.5°  | 6778.8 | 3579.1 |
| 50°    | 8293.1 | 4567.9 |
| 52.5°  | 8417.1 | 4560.5 |
| 55°    | 7683.6 | 4054.3 |
| 57.5°  | 6556.0 | 3388.7 |
| 60°    | 5449.0 | 2680.2 |
| 62.5°  | 4293.4 | 1850.8 |
| 65°    | 3137.8 | 1309.1 |
| 67.5°  | 2253.7 | 978.5  |
| 70°    | 1481.8 | 749.8  |
| 72.5°  | 965.2  | 611.0  |
| 75°    | 649.4  | 506.2  |
| 77.5°  | 379.3  | 336.5  |
| 80°    | 134.3  | 118.1  |
| 82.5°  | 25.1   | 17.7   |
| 85°    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1064721  
CATALOG NUMBER: GLAN-SA6A-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-757-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 5700K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 5571     | CRI (Ra): | 69.9 |      |       |
| CIE u':                   | 0.2033   | R1:       | 68.8 | R9:  | -35.4 |
| CIE v':                   | 0.4806   | R2:       | 72.5 | R10: | 36.7  |
| Duv:                      | 0.0041   | R3:       | 76.8 | R11: | 73.9  |
| CIE x:                    | 0.3308   | R4:       | 72.0 | R12: | 47.8  |
| CIE y:                    | 0.3476   | R5:       | 70.9 | R13: | 68.0  |
| CIE z:                    | 0.3216   | R6:       | 65.6 | R14: | 87.0  |
| Peak Wavelength (nm):     | 442      | R7:       | 75.5 | R15: | 59.8  |
| Dominant Wavelength (nm): | 544      | R8:       | 56.8 |      |       |
| Purity:                   | 3.635698 |           |      |      |       |
| Rf:                       | 70.4     |           |      |      |       |
| Rg:                       | 97.1     |           |      |      |       |



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 0                             | NR                             | 490               | 120                           | NR                             | 620               | 298                           | NR                             | 750               | 9                             | NR                             | 880               | 0                             | NR                             |
| 365               | 0                             | NR                             | 495               | 167                           | NR                             | 625               | 270                           | NR                             | 755               | 7                             | NR                             | 885               | 0                             | NR                             |
| 370               | 0                             | NR                             | 500               | 222                           | NR                             | 630               | 245                           | NR                             | 760               | 6                             | NR                             | 890               | 0                             | NR                             |
| 375               | 0                             | NR                             | 505               | 279                           | NR                             | 635               | 219                           | NR                             | 765               | 6                             | NR                             | 895               | 0                             | NR                             |
| 380               | 1                             | NR                             | 510               | 329                           | NR                             | 640               | 196                           | NR                             | 770               | 5                             | NR                             | 900               | 0                             | NR                             |
| 385               | 2                             | NR                             | 515               | 371                           | NR                             | 645               | 173                           | NR                             | 775               | 4                             | NR                             | 905               | 0                             | NR                             |
| 390               | 4                             | NR                             | 520               | 403                           | NR                             | 650               | 153                           | NR                             | 780               | 4                             | NR                             | 910               | 0                             | NR                             |
| 395               | 6                             | NR                             | 525               | 424                           | NR                             | 655               | 135                           | NR                             | 785               | 3                             | NR                             | 915               | 0                             | NR                             |
| 400               | 9                             | NR                             | 530               | 439                           | NR                             | 660               | 117                           | NR                             | 790               | 3                             | NR                             | 920               | 0                             | NR                             |
| 405               | 14                            | NR                             | 535               | 449                           | NR                             | 665               | 103                           | NR                             | 795               | 2                             | NR                             | 925               | 0                             | NR                             |
| 410               | 28                            | NR                             | 540               | 454                           | NR                             | 670               | 89                            | NR                             | 800               | 2                             | NR                             | 930               | 0                             | NR                             |
| 415               | 55                            | NR                             | 545               | 459                           | NR                             | 675               | 77                            | NR                             | 805               | 2                             | NR                             | 935               | 0                             | NR                             |
| 420               | 118                           | NR                             | 550               | 463                           | NR                             | 680               | 67                            | NR                             | 810               | 2                             | NR                             | 940               | 0                             | NR                             |
| 425               | 237                           | NR                             | 555               | 466                           | NR                             | 685               | 58                            | NR                             | 815               | 1                             | NR                             | 945               | 0                             | NR                             |
| 430               | 420                           | NR                             | 560               | 467                           | NR                             | 690               | 50                            | NR                             | 820               | 1                             | NR                             | 950               | 0                             | NR                             |
| 435               | 677                           | NR                             | 565               | 469                           | NR                             | 695               | 43                            | NR                             | 825               | 1                             | NR                             | 955               | 0                             | NR                             |
| 440               | 962                           | NR                             | 570               | 469                           | NR                             | 700               | 37                            | NR                             | 830               | 1                             | NR                             | 960               | 0                             | NR                             |
| 445               | 894                           | NR                             | 575               | 466                           | NR                             | 705               | 32                            | NR                             | 835               | 1                             | NR                             | 965               | 0                             | NR                             |
| 450               | 472                           | NR                             | 580               | 461                           | NR                             | 710               | 28                            | NR                             | 840               | 1                             | NR                             | 970               | 0                             | NR                             |
| 455               | 275                           | NR                             | 585               | 450                           | NR                             | 715               | 24                            | NR                             | 845               | 1                             | NR                             | 975               | 0                             | NR                             |
| 460               | 180                           | NR                             | 590               | 437                           | NR                             | 720               | 21                            | NR                             | 850               | 1                             | NR                             | 980               | 0                             | NR                             |
| 465               | 107                           | NR                             | 595               | 420                           | NR                             | 725               | 18                            | NR                             | 855               | 0                             | NR                             | 985               | 0                             | NR                             |
| 470               | 76                            | NR                             | 600               | 400                           | NR                             | 730               | 15                            | NR                             | 860               | 0                             | NR                             | 990               | 0                             | NR                             |
| 475               | 68                            | NR                             | 605               | 376                           | NR                             | 735               | 13                            | NR                             | 865               | 0                             | NR                             | 995               | 0                             | NR                             |
| 480               | 69                            | NR                             | 610               | 352                           | NR                             | 740               | 11                            | NR                             | 870               | 0                             | NR                             | 1000              | 0                             | NR                             |
| 485               | 86                            | NR                             | 615               | 325                           | NR                             | 745               | 10                            | NR                             | 875               | 0                             | NR                             |                   |                               |                                |

REPORT NUMBER: SP1-2407-184-7

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 120                      | NR            | 620    | 298                      | NR            | 750    | 9                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 167                      | NR            | 625    | 270                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 222                      | NR            | 630    | 245                      | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 279                      | NR            | 635    | 219                      | NR            | 765    | 6                        | NR            | 895    | 0                        | NR            |
| 380    | 1                        | NR            | 510    | 329                      | NR            | 640    | 196                      | NR            | 770    | 5                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 371                      | NR            | 645    | 173                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 403                      | NR            | 650    | 153                      | NR            | 780    | 4                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 424                      | NR            | 655    | 135                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 439                      | NR            | 660    | 117                      | NR            | 790    | 3                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 449                      | NR            | 665    | 103                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 28                       | NR            | 540    | 454                      | NR            | 670    | 89                       | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 459                      | NR            | 675    | 77                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 118                      | NR            | 550    | 463                      | NR            | 680    | 67                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 237                      | NR            | 555    | 466                      | NR            | 685    | 58                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 420                      | NR            | 560    | 467                      | NR            | 690    | 50                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 677                      | NR            | 565    | 469                      | NR            | 695    | 43                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 962                      | NR            | 570    | 469                      | NR            | 700    | 37                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 894                      | NR            | 575    | 466                      | NR            | 705    | 32                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 472                      | NR            | 580    | 461                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 275                      | NR            | 585    | 450                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 180                      | NR            | 590    | 437                      | NR            | 720    | 21                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 420                      | NR            | 725    | 18                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 76                       | NR            | 600    | 400                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 68                       | NR            | 605    | 376                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 69                       | NR            | 610    | 352                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 325                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-7

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 120                         | NR               | 620       | 298                         | NR               | 750       | 9                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 167                         | NR               | 625       | 270                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 222                         | NR               | 630       | 245                         | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 279                         | NR               | 635       | 219                         | NR               | 765       | 6                           | NR               | 895       | 0                           | NR               |
| 380       | 1                           | NR               | 510       | 329                         | NR               | 640       | 196                         | NR               | 770       | 5                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 371                         | NR               | 645       | 173                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 403                         | NR               | 650       | 153                         | NR               | 780       | 4                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 424                         | NR               | 655       | 135                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 439                         | NR               | 660       | 117                         | NR               | 790       | 3                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 449                         | NR               | 665       | 103                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 28                          | NR               | 540       | 454                         | NR               | 670       | 89                          | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 459                         | NR               | 675       | 77                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 118                         | NR               | 550       | 463                         | NR               | 680       | 67                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 237                         | NR               | 555       | 466                         | NR               | 685       | 58                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 420                         | NR               | 560       | 467                         | NR               | 690       | 50                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 677                         | NR               | 565       | 469                         | NR               | 695       | 43                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 962                         | NR               | 570       | 469                         | NR               | 700       | 37                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 894                         | NR               | 575       | 466                         | NR               | 705       | 32                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 472                         | NR               | 580       | 461                         | NR               | 710       | 28                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 275                         | NR               | 585       | 450                         | NR               | 715       | 24                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 180                         | NR               | 590       | 437                         | NR               | 720       | 21                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 107                         | NR               | 595       | 420                         | NR               | 725       | 18                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 76                          | NR               | 600       | 400                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 68                          | NR               | 605       | 376                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 69                          | NR               | 610       | 352                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 325                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-7





TM-30-18

### Summary

$R_f = 70.4$   
 $R_g = 97.1$   
 $CIE R_a = 69.9$   
 $R_g = -35.4$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 52 | CES51 = 87 | CES76 = 40 |
| CES02 = 59 | CES27 = 77 | CES52 = 88 | CES77 = 62 |
| CES03 = 30 | CES28 = 76 | CES53 = 74 | CES78 = 43 |
| CES04 = 68 | CES29 = 46 | CES54 = 79 | CES79 = 72 |
| CES05 = 45 | CES30 = 54 | CES55 = 78 | CES80 = 68 |
| CES06 = 49 | CES31 = 52 | CES56 = 67 | CES81 = 70 |
| CES07 = 38 | CES32 = 49 | CES57 = 64 | CES82 = 87 |
| CES08 = 37 | CES33 = 59 | CES58 = 66 | CES83 = 81 |
| CES09 = 29 | CES34 = 61 | CES59 = 87 | CES84 = 87 |
| CES10 = 72 | CES35 = 78 | CES60 = 91 | CES85 = 83 |
| CES11 = 55 | CES36 = 88 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 71 | CES62 = 77 | CES87 = 74 |
| CES13 = 41 | CES38 = 64 | CES63 = 74 | CES88 = 76 |
| CES14 = 74 | CES39 = 90 | CES64 = 71 | CES89 = 75 |
| CES15 = 70 | CES40 = 81 | CES65 = 63 | CES90 = 73 |
| CES16 = 46 | CES41 = 82 | CES66 = 66 | CES91 = 93 |
| CES17 = 48 | CES42 = 69 | CES67 = 63 | CES92 = 69 |
| CES18 = 55 | CES43 = 67 | CES68 = 71 | CES93 = 82 |
| CES19 = 70 | CES44 = 98 | CES69 = 81 | CES94 = 58 |
| CES20 = 63 | CES45 = 77 | CES70 = 57 | CES95 = 72 |
| CES21 = 85 | CES46 = 76 | CES71 = 54 | CES96 = 78 |
| CES22 = 77 | CES47 = 73 | CES72 = 84 | CES97 = 82 |
| CES23 = 91 | CES48 = 65 | CES73 = 45 | CES98 = 70 |
| CES24 = 90 | CES49 = 77 | CES74 = 92 | CES99 = 59 |
| CES25 = 71 | CES50 = 85 | CES75 = 49 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)