

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064890

Luminaire Tested: **GLAN-SA3B-850-U-RBC**

Issue Date: 08/07/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1064890  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA3B-850-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 3xLight Square PACKAGE  
80CRI 5000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (42) 5000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11686.7 lumens  
Efficiency: N/A  
Efficacy: 110.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 106.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1.7 fc

Type III - Short - N/A

REPORT NUMBER: P1064890  
CATALOG NUMBER: GLAN-SA3B-850-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 58.5     | 0.0    | 58.5    |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 11628.2  | 0.0    | 11628.2 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 11686.7  | 0.0    | 11686.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 4.6     | 0.0       |
| 10°-20°   | 25.7    | 0.2       |
| 20°-30°   | 277.0   | 2.4       |
| 30°-40°   | 819.0   | 7.0       |
| 40°-50°   | 2440.9  | 20.9      |
| 50°-60°   | 3870.4  | 33.1      |
| 60°-70°   | 3230.8  | 27.6      |
| 70°-80°   | 996.3   | 8.5       |
| 80°-90°   | 22.2    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 11686.7 | 100.0     |
| 0°-180°   | 11686.7 | 100.0     |



REPORT NUMBER: P1064890


CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 296.5  | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 7109.4 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 4205.3 | 36.0      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 17.1   | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 10.7   | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 20.9   | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 21.8   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 5.0    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°  | 22.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|------|-------|
| 0°     | 51.2   | 51.2   | 51.2  | 51.2  | 51.2  | 51.2  | 51.2  | 51.2  | 51.2 | 51.2  |
| 2.5°   | 46.8   | 46.8   | 46.8  | 46.8  | 45.9  | 45.9  | 45.0  | 45.0  | 44.2 | 44.2  |
| 5°     | 49.5   | 49.5   | 48.6  | 47.7  | 47.7  | 46.8  | 45.9  | 45.0  | 45.0 | 44.2  |
| 7.5°   | 53.9   | 53.0   | 52.1  | 51.2  | 49.5  | 48.6  | 46.8  | 45.9  | 45.0 | 43.3  |
| 10°    | 59.2   | 57.4   | 55.6  | 53.9  | 52.1  | 50.3  | 48.6  | 47.7  | 45.9 | 45.0  |
| 12.5°  | 66.2   | 63.6   | 60.1  | 57.4  | 55.6  | 53.0  | 51.2  | 49.5  | 46.8 | 45.0  |
| 15°    | 72.4   | 68.9   | 64.5  | 60.9  | 58.3  | 54.8  | 52.1  | 49.5  | 47.7 | 45.0  |
| 17.5°  | 81.3   | 75.1   | 68.0  | 63.6  | 60.1  | 55.6  | 51.2  | 48.6  | 45.9 | 42.4  |
| 20°    | 96.3   | 83.9   | 70.7  | 65.4  | 60.1  | 54.8  | 49.5  | 45.9  | 43.3 | 39.7  |
| 22.5°  | 120.1  | 98.9   | 77.7  | 69.8  | 62.7  | 54.8  | 47.7  | 44.2  | 40.6 | 37.1  |
| 25°    | 166.0  | 128.1  | 90.1  | 79.5  | 68.9  | 58.3  | 47.7  | 43.3  | 39.7 | 35.3  |
| 27.5°  | 220.8  | 164.3  | 106.9 | 91.8  | 77.7  | 62.7  | 47.7  | 42.4  | 38.0 | 32.7  |
| 30°    | 276.4  | 201.4  | 125.4 | 106.0 | 86.5  | 67.1  | 47.7  | 41.5  | 36.2 | 30.0  |
| 32.5°  | 329.4  | 235.8  | 141.3 | 118.3 | 95.4  | 71.5  | 48.6  | 41.5  | 34.4 | 27.4  |
| 35°    | 383.3  | 264.1  | 144.0 | 120.1 | 96.3  | 71.5  | 47.7  | 39.7  | 32.7 | 24.7  |
| 37.5°  | 452.2  | 295.9  | 138.7 | 114.8 | 91.8  | 68.0  | 45.0  | 38.0  | 30.9 | 23.0  |
| 40°    | 556.4  | 348.8  | 141.3 | 116.6 | 91.8  | 67.1  | 42.4  | 35.3  | 29.1 | 22.1  |
| 42.5°  | 748.9  | 451.3  | 152.8 | 124.5 | 96.3  | 67.1  | 38.9  | 32.7  | 27.4 | 21.2  |
| 45°    | 1294.7 | 749.8  | 204.9 | 162.5 | 120.1 | 77.7  | 35.3  | 30.0  | 25.6 | 20.3  |
| 47.5°  | 2141.7 | 1255.0 | 368.3 | 284.4 | 201.4 | 117.5 | 34.4  | 30.0  | 25.6 | 20.3  |
| 50°    | 2733.4 | 1598.5 | 463.7 | 356.8 | 249.9 | 143.1 | 36.2  | 30.9  | 26.5 | 21.2  |
| 52.5°  | 2729.0 | 1623.2 | 516.6 | 396.5 | 277.3 | 157.2 | 38.0  | 32.7  | 28.3 | 23.0  |
| 55°    | 2426.0 | 1476.6 | 526.4 | 404.5 | 283.5 | 161.6 | 40.6  | 35.3  | 30.0 | 24.7  |
| 57.5°  | 2027.7 | 1254.1 | 480.4 | 371.8 | 264.1 | 155.4 | 46.8  | 40.6  | 35.3 | 29.1  |
| 60°    | 1603.8 | 989.1  | 374.5 | 295.9 | 218.1 | 139.5 | 61.8  | 53.9  | 46.8 | 38.9  |
| 62.5°  | 1107.5 | 717.1  | 326.8 | 262.3 | 198.7 | 134.2 | 70.7  | 62.7  | 55.6 | 47.7  |
| 65°    | 783.4  | 539.6  | 295.0 | 240.2 | 186.3 | 131.6 | 76.8  | 68.0  | 60.1 | 51.2  |
| 67.5°  | 585.5  | 429.2  | 272.0 | 225.2 | 178.4 | 131.6 | 84.8  | 74.2  | 64.5 | 53.9  |
| 70°    | 448.6  | 352.4  | 255.2 | 217.3 | 180.2 | 142.2 | 104.2 | 89.2  | 75.1 | 60.1  |
| 72.5°  | 365.6  | 301.2  | 235.8 | 208.4 | 181.0 | 153.7 | 126.3 | 106.9 | 87.4 | 67.1  |
| 75°    | 302.9  | 257.9  | 212.8 | 189.9 | 167.8 | 144.8 | 121.9 | 104.2 | 87.4 | 69.8  |
| 77.5°  | 201.4  | 183.7  | 165.2 | 151.9 | 138.7 | 124.5 | 111.3 | 96.3  | 82.1 | 67.1  |
| 80°    | 70.7   | 68.0   | 65.4  | 70.7  | 76.0  | 81.3  | 86.5  | 76.0  | 66.2 | 55.6  |
| 82.5°  | 10.6   | 9.7    | 8.8   | 9.7   | 10.6  | 11.5  | 12.4  | 13.2  | 14.1 | 15.0  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 |
| 0.0 | 2.5°   | 43.3  | 43.3 | 42.4  | 42.4 | 42.4  | 41.5 | 41.5  | 40.6 | 40.6  | 40.6 |
| 0.0 | 5°     | 42.4  | 42.4 | 41.5  | 40.6 | 39.7  | 39.7 | 38.9  | 38.0 | 38.0  | 37.1 |
| 0.0 | 7.5°   | 41.5  | 40.6 | 39.7  | 38.9 | 38.0  | 37.1 | 36.2  | 35.3 | 35.3  | 34.4 |
| 0.0 | 10°    | 42.4  | 40.6 | 39.7  | 38.0 | 37.1  | 36.2 | 34.4  | 33.6 | 32.7  | 32.7 |
| 0.0 | 12.5°  | 40.6  | 39.7 | 38.0  | 36.2 | 35.3  | 33.6 | 32.7  | 30.9 | 30.0  | 30.0 |
| 0.0 | 15°    | 40.6  | 38.9 | 36.2  | 34.4 | 32.7  | 31.8 | 30.0  | 28.3 | 27.4  | 26.5 |
| 0.0 | 17.5°  | 38.0  | 36.2 | 33.6  | 31.8 | 30.0  | 28.3 | 26.5  | 24.7 | 23.8  | 23.0 |
| 0.0 | 20°    | 34.4  | 32.7 | 30.0  | 27.4 | 25.6  | 23.8 | 22.1  | 20.3 | 19.4  | 18.5 |
| 0.0 | 22.5°  | 30.9  | 29.1 | 26.5  | 23.8 | 22.1  | 20.3 | 17.7  | 15.9 | 15.0  | 13.2 |
| 0.0 | 25°    | 29.1  | 26.5 | 23.8  | 21.2 | 18.5  | 16.8 | 14.1  | 11.5 | 9.7   | 7.9  |
| 0.0 | 27.5°  | 24.7  | 22.1 | 19.4  | 16.8 | 14.1  | 11.5 | 8.8   | 6.2  | 4.4   | 3.5  |
| 0.0 | 30°    | 21.2  | 18.5 | 15.9  | 13.2 | 9.7   | 7.1  | 4.4   | 0.9  | 0.9   | 0.9  |
| 0.0 | 32.5°  | 17.7  | 15.0 | 11.5  | 8.8  | 7.1   | 4.4  | 2.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 14.1  | 11.5 | 7.9   | 5.3  | 4.4   | 2.6  | 1.8   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 12.4  | 9.7  | 6.2   | 2.6  | 1.8   | 1.8  | 0.9   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 11.5  | 7.9  | 4.4   | 0.9  | 0.9   | 0.9  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 11.5  | 7.9  | 3.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 11.5  | 7.9  | 3.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 11.5  | 7.9  | 3.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 12.4  | 8.8  | 4.4   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 14.1  | 10.6 | 7.1   | 3.5  | 2.6   | 1.8  | 0.9   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 17.7  | 15.9 | 13.2  | 11.5 | 8.8   | 6.2  | 2.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 23.0  | 23.0 | 22.1  | 21.2 | 15.9  | 10.6 | 5.3   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 30.9  | 30.9 | 30.9  | 30.9 | 23.0  | 15.9 | 7.9   | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 38.0  | 36.2 | 33.6  | 31.8 | 23.8  | 15.9 | 7.9   | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 38.0  | 34.4 | 30.0  | 25.6 | 19.4  | 13.2 | 6.2   | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 35.3  | 28.3 | 20.3  | 13.2 | 9.7   | 7.1  | 3.5   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 35.3  | 24.7 | 14.1  | 3.5  | 2.6   | 1.8  | 0.9   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 35.3  | 23.8 | 11.5  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 38.9  | 26.5 | 13.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 38.9  | 26.5 | 13.2  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 34.4  | 23.0 | 11.5  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 11.5  | 7.9  | 3.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  |
| 0.0   | 2.5°   | 39.7 | 39.7  | 39.7 | 38.9  | 38.9 | 38.9  | 38.9 | 38.0  | 38.0 | 38.0  |
| 0.0   | 5°     | 36.2 | 36.2  | 35.3 | 35.3  | 34.4 | 34.4  | 33.6 | 33.6  | 32.7 | 32.7  |
| 0.0   | 7.5°   | 33.6 | 32.7  | 32.7 | 31.8  | 30.9 | 30.9  | 30.0 | 30.0  | 29.1 | 28.3  |
| 0.0   | 10°    | 30.9 | 30.0  | 30.0 | 29.1  | 28.3 | 27.4  | 27.4 | 26.5  | 25.6 | 24.7  |
| 0.0   | 12.5°  | 28.3 | 27.4  | 26.5 | 25.6  | 24.7 | 23.8  | 23.8 | 23.0  | 22.1 | 21.2  |
| 0.0   | 15°    | 24.7 | 23.8  | 23.0 | 22.1  | 21.2 | 20.3  | 20.3 | 19.4  | 18.5 | 17.7  |
| 0.0   | 17.5°  | 21.2 | 20.3  | 20.3 | 19.4  | 18.5 | 17.7  | 16.8 | 15.0  | 14.1 | 13.2  |
| 0.0   | 20°    | 15.9 | 15.0  | 14.1 | 13.2  | 12.4 | 10.6  | 9.7  | 7.9   | 6.2  | 5.3   |
| 0.0   | 22.5°  | 10.6 | 8.8   | 7.9  | 6.2   | 4.4  | 3.5   | 2.6  | 0.9   | 0.0  | 0.0   |
| 0.0   | 25°    | 3.5  | 2.6   | 1.8  | 0.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2  | 51.2 | 51.2   | 51.2 |
| 0.0 | 2.5°   | 37.1  | 37.1 | 37.1  | 36.2 | 36.2  | 36.2 | 36.2  | 36.2 | 36.2   | 36.2 |
| 0.0 | 5°     | 31.8  | 31.8 | 31.8  | 30.9 | 30.9  | 30.0 | 30.0  | 30.0 | 29.1   | 29.1 |
| 0.0 | 7.5°   | 27.4  | 26.5 | 26.5  | 25.6 | 25.6  | 24.7 | 24.7  | 24.7 | 23.8   | 23.8 |
| 0.0 | 10°    | 23.0  | 22.1 | 22.1  | 21.2 | 21.2  | 20.3 | 20.3  | 19.4 | 19.4   | 18.5 |
| 0.0 | 12.5°  | 20.3  | 19.4 | 18.5  | 17.7 | 17.7  | 16.8 | 15.9  | 15.9 | 15.0   | 14.1 |
| 0.0 | 15°    | 15.9  | 15.0 | 14.1  | 13.2 | 12.4  | 11.5 | 10.6  | 10.6 | 9.7    | 8.8  |
| 0.0 | 17.5°  | 10.6  | 8.8  | 7.9   | 7.1  | 7.1   | 6.2  | 5.3   | 4.4  | 3.5    | 2.6  |
| 0.0 | 20°    | 2.6   | 1.8  | 0.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   |
| 0.0    | 2.5°   | 36.2 | 35.3   | 35.3 | 35.3   | 36.2 | 36.2   | 36.2 | 36.2   | 36.2 | 36.2   |
| 0.0    | 5°     | 29.1 | 28.3   | 28.3 | 28.3   | 28.3 | 28.3   | 28.3 | 28.3   | 28.3 | 28.3   |
| 0.0    | 7.5°   | 23.8 | 23.0   | 23.0 | 23.0   | 23.0 | 22.1   | 22.1 | 22.1   | 22.1 | 22.1   |
| 0.0    | 10°    | 18.5 | 17.7   | 17.7 | 17.7   | 17.7 | 16.8   | 16.8 | 16.8   | 16.8 | 16.8   |
| 0.0    | 12.5°  | 13.2 | 13.2   | 12.4 | 12.4   | 12.4 | 11.5   | 11.5 | 11.5   | 11.5 | 10.6   |
| 0.0    | 15°    | 7.9  | 7.1    | 6.2  | 6.2    | 6.2  | 5.3    | 5.3  | 5.3    | 5.3  | 4.4    |
| 0.0    | 17.5°  | 1.8  | 1.8    | 0.9  | 0.9    | 0.9  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 |
| 0.0  | 2.5°   | 37.1   | 37.1 | 38.0   | 38.0 | 38.9   | 40.6 | 41.5   | 42.4 | 44.2   | 45.9 |
| 0.0  | 5°     | 29.1   | 30.0 | 30.0   | 30.9 | 31.8   | 32.7 | 33.6   | 34.4 | 36.2   | 38.0 |
| 0.0  | 7.5°   | 23.0   | 23.0 | 23.8   | 23.8 | 24.7   | 26.5 | 27.4   | 28.3 | 30.0   | 32.7 |
| 0.0  | 10°    | 17.7   | 17.7 | 18.5   | 18.5 | 19.4   | 21.2 | 22.1   | 23.0 | 24.7   | 27.4 |
| 0.0  | 12.5°  | 11.5   | 12.4 | 12.4   | 13.2 | 14.1   | 15.9 | 16.8   | 17.7 | 19.4   | 21.2 |
| 0.0  | 15°    | 5.3    | 6.2  | 6.2    | 7.1  | 7.9    | 9.7  | 10.6   | 11.5 | 13.2   | 15.9 |
| 0.0  | 17.5°  | 0.9    | 0.9  | 1.8    | 1.8  | 2.6    | 3.5  | 4.4    | 5.3  | 7.9    | 9.7  |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.8    | 3.5  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.9  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   |
| 0.0    | 2.5°   | 48.6 | 50.3   | 52.1 | 53.9   | 55.6 | 57.4   | 58.3 | 60.1   | 60.9 | 61.8   |
| 0.0    | 5°     | 41.5 | 43.3   | 45.9 | 47.7   | 49.5 | 51.2   | 53.0 | 53.9   | 54.8 | 55.6   |
| 0.0    | 7.5°   | 36.2 | 38.0   | 40.6 | 42.4   | 44.2 | 45.9   | 47.7 | 49.5   | 50.3 | 51.2   |
| 0.0    | 10°    | 30.9 | 33.6   | 35.3 | 38.0   | 39.7 | 41.5   | 43.3 | 45.0   | 46.8 | 47.7   |
| 0.0    | 12.5°  | 24.7 | 27.4   | 30.0 | 31.8   | 34.4 | 37.1   | 38.9 | 40.6   | 42.4 | 44.2   |
| 0.0    | 15°    | 19.4 | 22.1   | 24.7 | 26.5   | 29.1 | 31.8   | 34.4 | 36.2   | 38.0 | 39.7   |
| 0.0    | 17.5°  | 14.1 | 16.8   | 19.4 | 21.2   | 23.8 | 26.5   | 28.3 | 30.9   | 32.7 | 34.4   |
| 0.0    | 20°    | 7.1  | 9.7    | 12.4 | 15.0   | 17.7 | 20.3   | 22.1 | 24.7   | 26.5 | 28.3   |
| 0.0    | 22.5°  | 0.9  | 3.5    | 6.2  | 7.9    | 10.6 | 13.2   | 15.0 | 17.7   | 19.4 | 21.2   |
| 0.0    | 25°    | 0.0  | 0.9    | 2.6  | 3.5    | 4.4  | 6.2    | 7.9  | 9.7    | 11.5 | 13.2   |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.9    | 1.8  | 3.5    | 5.3  | 7.1    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.8    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.9    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.9    | 0.9  | 1.8    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.8    | 2.6  | 4.4    | 5.3  | 6.2    |
|        | 87.5°  | 0.0  | 0.9    | 1.8  | 2.6    | 3.5  | 5.3    | 7.1  | 8.8    | 9.7  | 10.6   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 51.2 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 61.8 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 56.5 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.1 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 49.5 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45.0 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 41.5 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.1 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30.0 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23.0 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.9 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8.8  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2.6  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.9  |        |      |        |      |        |      |        |      |        |      |        |
| 3.5  |        |      |        |      |        |      |        |      |        |      |        |
| 7.9  |        |      |        |      |        |      |        |      |        |      |        |
| 11.5 |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 |
| 0.0  | 2.5°   | 62.7   | 62.7 | 62.7   | 62.7 | 61.8   | 61.8 | 61.8   | 60.9 | 60.9   | 60.1 |
| 0.0  | 5°     | 57.4   | 58.3 | 58.3   | 58.3 | 58.3   | 58.3 | 58.3   | 58.3 | 57.4   | 57.4 |
| 0.0  | 7.5°   | 53.0   | 53.9 | 54.8   | 54.8 | 55.6   | 55.6 | 55.6   | 54.8 | 54.8   | 53.9 |
| 0.0  | 10°    | 50.3   | 51.2 | 51.2   | 52.1 | 52.1   | 52.1 | 52.1   | 52.1 | 52.1   | 52.1 |
| 0.0  | 12.5°  | 46.8   | 47.7 | 48.6   | 48.6 | 49.5   | 49.5 | 49.5   | 49.5 | 48.6   | 48.6 |
| 0.0  | 15°    | 42.4   | 44.2 | 45.0   | 45.9 | 45.9   | 46.8 | 46.8   | 46.8 | 46.8   | 46.8 |
| 0.0  | 17.5°  | 38.9   | 40.6 | 41.5   | 42.4 | 42.4   | 43.3 | 43.3   | 44.2 | 44.2   | 44.2 |
| 0.0  | 20°    | 31.8   | 33.6 | 34.4   | 36.2 | 37.1   | 38.0 | 38.9   | 39.7 | 39.7   | 40.6 |
| 0.0  | 22.5°  | 24.7   | 26.5 | 27.4   | 29.1 | 30.0   | 30.9 | 31.8   | 32.7 | 33.6   | 34.4 |
| 0.0  | 25°    | 17.7   | 19.4 | 20.3   | 22.1 | 23.0   | 23.8 | 24.7   | 25.6 | 25.6   | 26.5 |
| 0.0  | 27.5°  | 9.7    | 11.5 | 13.2   | 14.1 | 15.9   | 16.8 | 17.7   | 18.5 | 19.4   | 20.3 |
| 0.0  | 30°    | 4.4    | 5.3  | 6.2    | 7.9  | 8.8    | 9.7  | 10.6   | 12.4 | 13.2   | 14.1 |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.9    | 2.6  | 3.5    | 4.4  | 5.3    | 6.2  | 6.2    | 7.1  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.9    | 1.8  | 2.6    | 3.5  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 1.8    | 1.8  | 1.8    | 2.6  | 2.6    | 2.6  | 2.6    | 2.6  | 2.6    | 2.6  |
|      | 82.5°  | 4.4    | 5.3  | 6.2    | 6.2  | 7.1    | 7.1  | 7.1    | 7.1  | 6.2    | 6.2  |
|      | 85°    | 8.8    | 9.7  | 10.6   | 10.6 | 11.5   | 11.5 | 11.5   | 11.5 | 11.5   | 11.5 |
|      | 87.5°  | 12.4   | 13.2 | 14.1   | 14.1 | 15.0   | 15.0 | 15.0   | 15.0 | 15.0   | 15.0 |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 51.2   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 60.1   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.4   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 53.9   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 52.1   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 48.6   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 46.8   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 44.2   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 39.7   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 34.4   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27.4   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 21.2   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 15.0   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 8.8    | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.3    | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.9    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.9    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.9    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.9    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.9    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 2.6    |        |        |      |        |      |        |      |        |      |        |      |
| 6.2    |        |        |      |        |      |        |      |        |      |        |      |
| 11.5   |        |        |      |        |      |        |      |        |      |        |      |
| 15.0   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   | 51.2 | 51.2   |
| 0.0    | 2.5°   | 59.2 | 59.2   | 58.3 | 58.3   | 58.3 | 58.3   | 58.3 | 59.2   | 60.1 | 60.1   |
| 0.0    | 5°     | 56.5 | 56.5   | 55.6 | 55.6   | 55.6 | 56.5   | 56.5 | 57.4   | 58.3 | 59.2   |
| 0.0    | 7.5°   | 53.9 | 53.0   | 53.0 | 53.9   | 53.9 | 54.8   | 54.8 | 55.6   | 56.5 | 57.4   |
| 0.0    | 10°    | 52.1 | 51.2   | 51.2 | 51.2   | 52.1 | 52.1   | 53.0 | 53.9   | 54.8 | 55.6   |
| 0.0    | 12.5°  | 48.6 | 48.6   | 48.6 | 48.6   | 49.5 | 49.5   | 50.3 | 51.2   | 53.0 | 53.9   |
| 0.0    | 15°    | 46.8 | 45.9   | 45.9 | 45.9   | 45.9 | 46.8   | 46.8 | 48.6   | 50.3 | 51.2   |
| 0.0    | 17.5°  | 43.3 | 43.3   | 42.4 | 42.4   | 43.3 | 43.3   | 44.2 | 45.9   | 47.7 | 48.6   |
| 0.0    | 20°    | 39.7 | 38.9   | 38.0 | 38.0   | 38.9 | 38.9   | 39.7 | 41.5   | 43.3 | 44.2   |
| 0.0    | 22.5°  | 34.4 | 33.6   | 33.6 | 33.6   | 33.6 | 34.4   | 34.4 | 36.2   | 38.9 | 40.6   |
| 0.0    | 25°    | 27.4 | 28.3   | 28.3 | 29.1   | 29.1 | 30.0   | 30.9 | 32.7   | 35.3 | 37.1   |
| 0.0    | 27.5°  | 21.2 | 22.1   | 22.1 | 23.8   | 24.7 | 25.6   | 26.5 | 29.1   | 31.8 | 33.6   |
| 0.0    | 30°    | 15.9 | 16.8   | 17.7 | 18.5   | 20.3 | 22.1   | 23.8 | 26.5   | 29.1 | 30.9   |
| 0.0    | 32.5°  | 9.7  | 11.5   | 12.4 | 14.1   | 15.9 | 17.7   | 19.4 | 22.1   | 25.6 | 28.3   |
| 0.0    | 35°    | 7.1  | 7.9    | 9.7  | 10.6   | 12.4 | 14.1   | 15.9 | 19.4   | 22.1 | 25.6   |
| 0.0    | 37.5°  | 3.5  | 5.3    | 7.1  | 8.8    | 10.6 | 12.4   | 14.1 | 17.7   | 21.2 | 23.8   |
| 0.0    | 40°    | 2.6  | 4.4    | 5.3  | 7.1    | 9.7  | 11.5   | 13.2 | 16.8   | 20.3 | 23.8   |
| 0.0    | 42.5°  | 1.8  | 2.6    | 3.5  | 6.2    | 7.9  | 10.6   | 13.2 | 16.8   | 20.3 | 23.8   |
| 0.0    | 45°    | 1.8  | 1.8    | 2.6  | 5.3    | 7.9  | 11.5   | 14.1 | 17.7   | 20.3 | 23.8   |
| 0.0    | 47.5°  | 1.8  | 2.6    | 3.5  | 7.1    | 8.8  | 11.5   | 14.1 | 16.8   | 20.3 | 23.0   |
| 0.0    | 50°    | 2.6  | 3.5    | 4.4  | 7.9    | 9.7  | 12.4   | 14.1 | 17.7   | 20.3 | 23.8   |
| 0.0    | 52.5°  | 1.8  | 2.6    | 3.5  | 7.1    | 9.7  | 13.2   | 15.9 | 19.4   | 23.0 | 25.6   |
| 0.0    | 55°    | 0.9  | 0.9    | 0.9  | 5.3    | 10.6 | 15.0   | 20.3 | 23.0   | 26.5 | 29.1   |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 3.5    | 10.6 | 16.8   | 23.0 | 26.5   | 30.0 | 32.7   |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 3.5    | 10.6 | 16.8   | 23.0 | 27.4   | 31.8 | 36.2   |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 3.5    | 8.8  | 14.1   | 19.4 | 26.5   | 34.4 | 41.5   |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 2.6    | 7.1  | 11.5   | 15.9 | 26.5   | 37.1 | 46.8   |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 2.6    | 7.1  | 10.6   | 15.0 | 26.5   | 37.1 | 48.6   |
|        | 70°    | 0.0  | 0.0    | 0.0  | 2.6    | 7.1  | 11.5   | 15.9 | 26.5   | 37.1 | 47.7   |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 2.6    | 7.9  | 12.4   | 17.7 | 26.5   | 35.3 | 44.2   |
|        | 75°    | 0.0  | 0.0    | 0.0  | 3.5    | 7.9  | 13.2   | 18.5 | 26.5   | 34.4 | 41.5   |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 2.6    | 7.9  | 12.4   | 17.7 | 25.6   | 33.6 | 40.6   |
|        | 80°    | 2.6  | 1.8    | 1.8  | 4.4    | 7.9  | 11.5   | 15.0 | 23.0   | 31.8 | 39.7   |
|        | 82.5°  | 5.3  | 5.3    | 4.4  | 6.2    | 7.9  | 10.6   | 13.2 | 20.3   | 28.3 | 35.3   |
|        | 85°    | 10.6 | 10.6   | 9.7  | 10.6   | 10.6 | 11.5   | 12.4 | 15.9   | 19.4 | 23.0   |
|        | 87.5°  | 14.1 | 14.1   | 13.2 | 13.2   | 13.2 | 12.4   | 12.4 | 12.4   | 12.4 | 11.5   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 51.2 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60.9 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60.1 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 58.3 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 56.5 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 54.8 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.0 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50.3 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45.9 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.4 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38.9 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 36.2 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 33.6 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30.9 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28.3 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.4 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.4 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.4 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.5 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25.6 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.5 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29.1 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31.8 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 36.2 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.6 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.6 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.4 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.2 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 58.3 |        |      |        |      |        |      |        |      |        |      |        |
| 53.0 |        |      |        |      |        |      |        |      |        |      |        |
| 49.5 |        |      |        |      |        |      |        |      |        |      |        |
| 48.6 |        |      |        |      |        |      |        |      |        |      |        |
| 47.7 |        |      |        |      |        |      |        |      |        |      |        |
| 42.4 |        |      |        |      |        |      |        |      |        |      |        |
| 26.5 |        |      |        |      |        |      |        |      |        |      |        |
| 11.5 |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250° | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°  |
|------|--------|--------|------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 51.2   | 51.2 | 51.2   | 51.2  | 51.2   | 51.2  | 51.2   | 51.2  | 51.2   | 51.2  |
| 0.0  | 2.5°   | 61.8   | 62.7 | 62.7   | 63.6  | 64.5   | 65.4  | 65.4   | 66.2  | 66.2   | 66.2  |
| 0.0  | 5°     | 60.9   | 62.7 | 63.6   | 64.5  | 65.4   | 66.2  | 67.1   | 68.0  | 68.9   | 68.9  |
| 0.0  | 7.5°   | 60.1   | 60.9 | 62.7   | 63.6  | 65.4   | 66.2  | 68.0   | 68.9  | 69.8   | 70.7  |
| 0.0  | 10°    | 58.3   | 60.1 | 61.8   | 63.6  | 65.4   | 67.1  | 68.9   | 70.7  | 72.4   | 73.3  |
| 0.0  | 12.5°  | 56.5   | 59.2 | 60.9   | 62.7  | 65.4   | 68.0  | 69.8   | 72.4  | 74.2   | 76.0  |
| 0.0  | 15°    | 55.6   | 57.4 | 60.1   | 61.8  | 65.4   | 68.9  | 71.5   | 75.1  | 78.6   | 81.3  |
| 0.0  | 17.5°  | 53.0   | 56.5 | 59.2   | 61.8  | 65.4   | 69.8  | 73.3   | 76.8  | 82.1   | 87.4  |
| 0.0  | 20°    | 49.5   | 52.1 | 55.6   | 58.3  | 63.6   | 68.0  | 73.3   | 77.7  | 85.7   | 93.6  |
| 0.0  | 22.5°  | 45.9   | 49.5 | 52.1   | 55.6  | 61.8   | 67.1  | 73.3   | 78.6  | 91.8   | 104.2 |
| 0.0  | 25°    | 42.4   | 46.8 | 50.3   | 53.9  | 60.9   | 68.0  | 75.1   | 82.1  | 104.2  | 126.3 |
| 0.0  | 27.5°  | 40.6   | 44.2 | 48.6   | 52.1  | 60.9   | 70.7  | 79.5   | 88.3  | 123.6  | 158.1 |
| 0.0  | 30°    | 38.0   | 42.4 | 45.9   | 50.3  | 61.8   | 73.3  | 84.8   | 96.3  | 150.1  | 204.0 |
| 0.0  | 32.5°  | 35.3   | 39.7 | 44.2   | 48.6  | 63.6   | 78.6  | 92.7   | 107.7 | 178.4  | 248.2 |
| 0.0  | 35°    | 32.7   | 38.0 | 42.4   | 46.8  | 66.2   | 86.5  | 106.0  | 125.4 | 204.0  | 281.7 |
| 0.0  | 37.5°  | 31.8   | 37.1 | 41.5   | 45.9  | 67.1   | 87.4  | 108.6  | 128.9 | 206.7  | 284.4 |
| 0.0  | 40°    | 32.7   | 37.1 | 42.4   | 46.8  | 64.5   | 82.1  | 98.9   | 116.6 | 197.8  | 278.2 |
| 0.0  | 42.5°  | 32.7   | 38.0 | 43.3   | 48.6  | 62.7   | 76.8  | 91.0   | 105.1 | 195.2  | 285.3 |
| 0.0  | 45°    | 31.8   | 37.1 | 42.4   | 47.7  | 60.9   | 73.3  | 86.5   | 98.9  | 211.1  | 322.4 |
| 0.0  | 47.5°  | 30.9   | 36.2 | 41.5   | 46.8  | 60.1   | 73.3  | 86.5   | 99.8  | 272.9  | 445.1 |
| 0.0  | 50°    | 30.9   | 36.2 | 40.6   | 45.0  | 60.9   | 77.7  | 93.6   | 109.5 | 397.4  | 684.4 |
| 0.0  | 52.5°  | 32.7   | 37.1 | 40.6   | 44.2  | 62.7   | 82.1  | 100.7  | 119.2 | 505.2  | 890.2 |
| 0.0  | 55°    | 35.3   | 38.0 | 41.5   | 44.2  | 67.1   | 89.2  | 112.2  | 134.2 | 537.8  | 941.4 |
| 0.0  | 57.5°  | 38.9   | 41.5 | 44.2   | 46.8  | 75.1   | 103.3 | 130.7  | 159.0 | 540.5  | 921.1 |
| 0.0  | 60°    | 43.3   | 46.8 | 49.5   | 52.1  | 82.1   | 113.0 | 143.1  | 173.1 | 489.3  | 804.6 |
| 0.0  | 62.5°  | 53.0   | 57.4 | 60.9   | 65.4  | 94.5   | 122.8 | 151.9  | 180.2 | 406.3  | 632.3 |
| 0.0  | 65°    | 60.9   | 64.5 | 68.0   | 71.5  | 99.8   | 128.9 | 157.2  | 185.5 | 344.4  | 503.4 |
| 0.0  | 67.5°  | 62.7   | 66.2 | 68.9   | 72.4  | 101.6  | 130.7 | 159.0  | 188.1 | 295.0  | 401.0 |
|      | 70°    | 63.6   | 68.0 | 73.3   | 77.7  | 107.7  | 137.8 | 166.9  | 196.9 | 261.4  | 325.9 |
|      | 72.5°  | 60.9   | 69.8 | 77.7   | 85.7  | 113.9  | 141.3 | 169.6  | 196.9 | 242.9  | 288.8 |
|      | 75°    | 60.9   | 73.3 | 84.8   | 96.3  | 117.5  | 137.8 | 159.0  | 179.3 | 214.6  | 249.9 |
|      | 77.5°  | 64.5   | 80.4 | 96.3   | 112.2 | 124.5  | 136.0 | 148.4  | 159.9 | 182.8  | 205.8 |
|      | 80°    | 64.5   | 81.3 | 97.1   | 113.9 | 119.2  | 125.4 | 130.7  | 136.0 | 138.7  | 141.3 |
|      | 82.5°  | 55.6   | 68.9 | 82.1   | 95.4  | 89.2   | 83.0  | 76.8   | 70.7  | 66.2   | 60.9  |
|      | 85°    | 28.3   | 30.9 | 32.7   | 34.4  | 31.8   | 29.1  | 26.5   | 23.8  | 22.1   | 19.4  |
|      | 87.5°  | 11.5   | 11.5 | 10.6   | 10.6  | 10.6   | 10.6  | 9.7    | 9.7   | 9.7    | 9.7   |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 51.2   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 66.2   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 68.9   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 71.5   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 75.1   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 78.6   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85.7   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94.5   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 108.6  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 138.7  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 188.1  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 261.4  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 354.1  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 442.5  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 502.5  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 547.6  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 592.6  | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 680.9  | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 857.5  | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1307.1 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2002.1 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2520.5 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2577.9 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2326.2 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1988.9 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1554.4 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1174.6 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 867.3  | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 613.8  |        |        |      |        |      |        |      |        |      |        |      |
| 456.6  |        |        |      |        |      |        |      |        |      |        |      |
| 332.1  |        |        |      |        |      |        |      |        |      |        |      |
| 249.9  |        |        |      |        |      |        |      |        |      |        |      |
| 140.4  |        |        |      |        |      |        |      |        |      |        |      |
| 63.6   |        |        |      |        |      |        |      |        |      |        |      |
| 18.5   |        |        |      |        |      |        |      |        |      |        |      |
| 8.8    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5° | 280°   | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 51.2   | 51.2   | 51.2   | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    |
| 0.0    | 2.5°   | 66.2   | 65.4   | 65.4   | 64.5    | 63.6    | 62.7    | 61.8    | 60.9    | 60.1    | 59.2    |
| 0.0    | 5°     | 68.9   | 68.9   | 68.9   | 68.0    | 68.0    | 67.1    | 67.1    | 66.2    | 65.4    | 64.5    |
| 0.0    | 7.5°   | 71.5   | 72.4   | 72.4   | 73.3    | 73.3    | 73.3    | 73.3    | 72.4    | 72.4    | 72.4    |
| 0.0    | 10°    | 76.0   | 76.8   | 77.7   | 78.6    | 79.5    | 80.4    | 80.4    | 81.3    | 81.3    | 81.3    |
| 0.0    | 12.5°  | 81.3   | 83.9   | 85.7   | 88.3    | 90.1    | 92.7    | 94.5    | 97.1    | 98.9    | 100.7   |
| 0.0    | 15°    | 89.2   | 93.6   | 98.9   | 103.3   | 107.7   | 113.9   | 121.0   | 127.2   | 133.4   | 143.1   |
| 0.0    | 17.5°  | 100.7  | 114.8  | 128.9  | 142.2   | 156.3   | 187.2   | 218.1   | 248.2   | 279.1   | 324.1   |
| 0.0    | 20°    | 122.8  | 165.2  | 206.7  | 249.1   | 290.6   | 399.2   | 506.9   | 615.6   | 723.3   | 839.0   |
| 0.0    | 22.5°  | 172.2  | 276.4  | 380.6  | 484.9   | 589.1   | 816.0   | 1042.1  | 1269.1  | 1495.2  | 1761.0  |
| 0.0    | 25°    | 249.9  | 441.6  | 633.2  | 824.0   | 1015.6  | 1370.7  | 1726.6  | 2081.6  | 2436.6  | 2781.9  |
| 0.0    | 27.5°  | 363.9  | 657.1  | 950.3  | 1242.6  | 1535.8  | 2017.1  | 2499.3  | 2980.7  | 3462.0  | 3852.3  |
| 0.0    | 30°    | 504.3  | 901.7  | 1299.1 | 1696.5  | 2094.0  | 2641.5  | 3189.1  | 3735.8  | 4283.3  | 4709.9  |
| 0.0    | 32.5°  | 636.8  | 1123.4 | 1610.0 | 2095.7  | 2582.4  | 3205.9  | 3830.3  | 4453.8  | 5077.3  | 5543.6  |
| 0.0    | 35°    | 723.3  | 1311.5 | 1900.6 | 2488.7  | 3076.9  | 3751.7  | 4426.4  | 5100.2  | 5775.0  | 6307.5  |
| 0.0    | 37.5°  | 809.9  | 1489.0 | 2167.3 | 2846.4  | 3524.7  | 4265.6  | 5006.6  | 5747.6  | 6488.6  | 7146.5  |
| 0.0    | 40°    | 907.0  | 1703.6 | 2499.3 | 3295.9  | 4091.7  | 4969.5  | 5846.5  | 6724.4  | 7601.3  | 8529.5  |
| 0.0    | 42.5°  | 1075.7 | 2059.5 | 3044.2 | 4028.1  | 5011.9  | 6173.3  | 7334.6  | 8495.1  | 9656.4  | 10981.2 |
| 0.0    | 45°    | 1392.7 | 2779.3 | 4166.7 | 5553.3  | 6939.8  | 8478.3  | 10017.7 | 11556.1 | 13094.6 | 14857.4 |
| 0.0    | 47.5°  | 2169.0 | 4076.7 | 5983.4 | 7891.0  | 9797.7  | 11459.0 | 13119.3 | 14780.5 | 16440.9 | 18196.6 |
| 0.0    | 50°    | 3318.9 | 5539.2 | 7759.4 | 9978.8  | 12199.0 | 13702.2 | 15204.4 | 16707.6 | 18209.8 | 19879.9 |
| 0.0    | 52.5°  | 4150.8 | 6463.8 | 8777.7 | 11090.7 | 13403.7 | 14760.2 | 16117.6 | 17474.1 | 18830.7 | 20391.2 |
| 0.0    | 55°    | 4213.5 | 6513.3 | 8813.9 | 11113.6 | 13413.4 | 14776.1 | 16138.8 | 17501.5 | 18864.2 | 20518.4 |
| 0.0    | 57.5°  | 3730.5 | 6011.7 | 8292.0 | 10573.2 | 12853.5 | 14405.2 | 15956.0 | 17507.7 | 19058.5 | 20846.9 |
| 0.0    | 60°    | 3173.2 | 5455.3 | 7736.5 | 10018.5 | 12299.7 | 14087.2 | 15875.6 | 17663.1 | 19450.7 | 21126.0 |
| 0.0    | 62.5°  | 2475.5 | 4822.9 | 7171.2 | 9518.7  | 11866.1 | 13681.0 | 15495.9 | 17309.9 | 19124.8 | 20381.5 |
| 0.0    | 65°    | 1844.9 | 4124.3 | 6403.8 | 8682.3  | 10961.7 | 12415.4 | 13869.1 | 15321.9 | 16775.6 | 17553.6 |
| 0.0    | 67.5°  | 1333.6 | 3299.5 | 5264.5 | 7230.4  | 9195.4  | 10235.8 | 11276.2 | 12315.6 | 13356.0 | 13951.2 |
|        | 70°    | 901.7  | 2263.5 | 3624.5 | 4986.3  | 6347.3  | 7202.1  | 8057.9  | 8912.8  | 9767.7  | 10571.4 |
|        | 72.5°  | 624.4  | 1389.2 | 2154.9 | 2919.7  | 3684.5  | 4544.7  | 5404.0  | 6264.2  | 7123.5  | 7974.0  |
|        | 75°    | 414.2  | 762.2  | 1111.0 | 1459.0  | 1806.9  | 2443.7  | 3081.3  | 3718.1  | 4354.8  | 4861.8  |
|        | 77.5°  | 294.1  | 398.3  | 503.4  | 607.6   | 711.8   | 831.1   | 951.2   | 1070.4  | 1189.6  | 1370.7  |
|        | 80°    | 139.5  | 152.8  | 166.0  | 178.4   | 191.6   | 234.9   | 278.2   | 321.5   | 364.7   | 410.7   |
|        | 82.5°  | 66.2   | 71.5   | 76.8   | 81.3    | 86.5    | 91.0    | 95.4    | 99.8    | 104.2   | 99.8    |
|        | 85°    | 17.7   | 17.7   | 18.5   | 18.5    | 18.5    | 18.5    | 18.5    | 18.5    | 18.5    | 17.7    |
|        | 87.5°  | 7.9    | 7.9    | 7.9    | 7.9     | 7.9     | 7.9     | 7.9     | 7.1     | 7.1     | 6.2     |
|        | 90°    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 51.2    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 58.3    | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 63.6    | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71.5    | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.1    | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.6   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 153.7   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 368.3   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 955.6   | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2026.8  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3127.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4242.7  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5137.3  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6010.8  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6840.1  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7805.3  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9457.7  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12305.9 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16620.1 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19952.3 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21549.9 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21951.8 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22173.4 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22635.3 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22800.5 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21639.1 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18332.6 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 14547.4 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 11374.2 |        |      |        |      |        |      |        |      |        |      |        |
| 8824.5  |        |      |        |      |        |      |        |      |        |      |        |
| 5368.7  |        |      |        |      |        |      |        |      |        |      |        |
| 1551.7  |        |      |        |      |        |      |        |      |        |      |        |
| 456.6   |        |      |        |      |        |      |        |      |        |      |        |
| 94.5    |        |      |        |      |        |      |        |      |        |      |        |
| 16.8    |        |      |        |      |        |      |        |      |        |      |        |
| 6.2     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    |
| 0.0  | 2.5°   | 57.4    | 56.5    | 55.6    | 54.8    | 53.9    | 52.1    | 52.1    | 51.2    | 51.2    |
| 0.0  | 5°     | 62.7    | 61.8    | 60.9    | 60.1    | 60.1    | 59.2    | 58.3    | 58.3    | 57.4    |
| 0.0  | 7.5°   | 71.5    | 70.7    | 69.8    | 68.9    | 68.9    | 68.0    | 68.0    | 67.1    | 67.1    |
| 0.0  | 10°    | 82.1    | 82.1    | 82.1    | 82.1    | 82.1    | 81.3    | 81.3    | 81.3    | 80.4    |
| 0.0  | 12.5°  | 103.3   | 104.2   | 106.0   | 107.7   | 110.4   | 110.4   | 110.4   | 109.5   | 109.5   |
| 0.0  | 15°    | 163.4   | 173.1   | 180.2   | 187.2   | 193.4   | 207.5   | 205.8   | 203.1   | 201.4   |
| 0.0  | 17.5°  | 413.3   | 457.5   | 481.3   | 504.3   | 528.1   | 593.5   | 582.9   | 572.3   | 562.6   |
| 0.0  | 20°    | 1071.3  | 1187.0  | 1263.8  | 1340.6  | 1418.4  | 1541.1  | 1511.1  | 1481.1  | 1451.0  |
| 0.0  | 22.5°  | 2291.8  | 2557.6  | 2673.3  | 2789.0  | 2903.8  | 3052.2  | 2955.9  | 2859.7  | 2764.3  |
| 0.0  | 25°    | 3471.7  | 3817.0  | 4012.2  | 4207.4  | 4401.7  | 4486.4  | 4361.0  | 4234.7  | 4109.3  |
| 0.0  | 27.5°  | 4633.0  | 5023.4  | 5195.6  | 5366.9  | 5539.2  | 5716.7  | 5561.2  | 5404.9  | 5249.5  |
| 0.0  | 30°    | 5563.9  | 5990.5  | 6176.8  | 6362.3  | 6548.6  | 6672.3  | 6511.5  | 6349.9  | 6189.2  |
| 0.0  | 32.5°  | 6477.1  | 6943.4  | 7147.4  | 7351.4  | 7554.5  | 7732.0  | 7534.2  | 7335.5  | 7137.7  |
| 0.0  | 35°    | 7371.7  | 7904.3  | 8185.1  | 8465.9  | 8746.8  | 8911.9  | 8677.0  | 8441.2  | 8206.3  |
| 0.0  | 37.5°  | 8463.3  | 9121.2  | 9435.7  | 9750.1  | 10064.5 | 10365.6 | 10106.9 | 9847.2  | 9588.4  |
| 0.0  | 40°    | 10385.9 | 11314.1 | 11796.3 | 12279.4 | 12761.6 | 13150.2 | 12823.4 | 12496.7 | 12169.9 |
| 0.0  | 42.5°  | 13630.6 | 14955.4 | 15648.7 | 16341.1 | 17034.3 | 17641.1 | 17297.5 | 16954.0 | 16610.4 |
| 0.0  | 45°    | 18382.9 | 20145.7 | 20990.9 | 21835.2 | 22680.4 | 23123.7 | 22629.1 | 22133.7 | 21639.1 |
| 0.0  | 47.5°  | 21707.1 | 23462.8 | 24215.3 | 24967.7 | 25720.2 | 26226.2 | 25621.3 | 25016.3 | 24412.2 |
| 0.0  | 50°    | 23219.1 | 24889.1 | 25644.2 | 26398.5 | 27153.5 | 27555.4 | 26856.8 | 26157.3 | 25458.8 |
| 0.0  | 52.5°  | 23511.4 | 25071.9 | 25972.8 | 26874.5 | 27775.3 | 28312.3 | 27487.4 | 26661.6 | 25836.8 |
| 0.0  | 55°    | 23827.6 | 25481.7 | 26526.5 | 27572.2 | 28616.9 | 29360.6 | 28427.9 | 27494.4 | 26561.8 |
| 0.0  | 57.5°  | 24422.8 | 26211.2 | 27253.3 | 28294.6 | 29336.7 | 29968.2 | 29032.9 | 28096.8 | 27161.5 |
| 0.0  | 60°    | 24475.8 | 26150.3 | 27045.8 | 27942.2 | 28837.7 | 29235.2 | 28340.5 | 27445.0 | 26550.4 |
| 0.0  | 62.5°  | 22895.8 | 24152.6 | 24774.3 | 25396.1 | 26017.8 | 26449.7 | 25516.2 | 24581.8 | 23648.3 |
| 0.0  | 65°    | 19110.6 | 19888.7 | 20384.1 | 20879.6 | 21375.1 | 21889.9 | 21035.0 | 20180.1 | 19325.2 |
| 0.0  | 67.5°  | 15142.6 | 15737.9 | 16390.5 | 17043.2 | 17695.8 | 18246.0 | 17561.6 | 16876.2 | 16191.8 |
|      | 70°    | 12177.9 | 12980.6 | 13714.5 | 14448.5 | 15182.4 | 15632.8 | 14945.7 | 14257.7 | 13570.6 |
|      | 72.5°  | 9675.0  | 10525.5 | 11138.4 | 11750.4 | 12363.3 | 12473.7 | 11968.5 | 11463.4 | 10959.1 |
|      | 75°    | 5874.8  | 6381.7  | 6394.1  | 6405.5  | 6417.9  | 6523.0  | 6104.4  | 5685.8  | 5268.0  |
|      | 77.5°  | 1732.8  | 1913.8  | 2063.1  | 2211.4  | 2360.7  | 2540.8  | 2387.2  | 2232.6  | 2079.0  |
|      | 80°    | 501.6   | 547.6   | 586.4   | 624.4   | 663.3   | 640.3   | 604.1   | 567.9   | 531.7   |
|      | 82.5°  | 90.1    | 84.8    | 83.9    | 83.0    | 83.0    | 78.6    | 71.5    | 64.5    | 57.4    |
|      | 85°    | 15.9    | 15.0    | 14.1    | 13.2    | 12.4    | 11.5    | 9.7     | 8.8     | 7.1     |
|      | 87.5°  | 5.3     | 4.4     | 3.5     | 2.6     | 2.6     | 0.9     | 0.9     | 0.9     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    | 51.2    |
| 0.0  | 0.0    | 2.5°   | 50.3    | 49.5    | 49.5    | 49.5    | 49.5    | 48.6    | 48.6    | 48.6    | 48.6    |
| 0.0  | 0.0    | 5°     | 55.6    | 55.6    | 54.8    | 54.8    | 53.9    | 53.9    | 53.0    | 53.0    | 52.1    |
| 0.0  | 0.0    | 7.5°   | 65.4    | 64.5    | 63.6    | 62.7    | 61.8    | 60.1    | 59.2    | 58.3    | 58.3    |
| 0.0  | 0.0    | 10°    | 78.6    | 76.8    | 76.0    | 74.2    | 73.3    | 71.5    | 69.8    | 68.0    | 66.2    |
| 0.0  | 0.0    | 12.5°  | 103.3   | 99.8    | 97.1    | 93.6    | 90.1    | 87.4    | 83.9    | 81.3    | 77.7    |
| 0.0  | 0.0    | 15°    | 179.3   | 170.4   | 160.7   | 149.3   | 136.9   | 125.4   | 113.0   | 106.0   | 98.0    |
| 0.0  | 0.0    | 17.5°  | 458.4   | 412.4   | 365.6   | 327.7   | 289.7   | 252.6   | 214.6   | 187.2   | 159.9   |
| 0.0  | 0.0    | 20°    | 1166.7  | 1039.5  | 912.3   | 786.9   | 660.6   | 535.2   | 408.9   | 345.3   | 281.7   |
| 0.0  | 0.0    | 22.5°  | 2195.5  | 1959.7  | 1723.0  | 1494.3  | 1264.7  | 1035.9  | 807.2   | 663.3   | 520.2   |
| 0.0  | 0.0    | 25°    | 3388.7  | 3091.9  | 2795.2  | 2419.0  | 2041.9  | 1665.6  | 1289.4  | 1055.4  | 821.3   |
| 0.0  | 0.0    | 27.5°  | 4409.6  | 4067.8  | 3726.0  | 3268.6  | 2811.1  | 2353.6  | 1896.1  | 1547.3  | 1199.3  |
| 0.0  | 0.0    | 30°    | 5293.6  | 4926.3  | 4558.9  | 4026.3  | 3493.8  | 2961.2  | 2428.7  | 1992.4  | 1556.1  |
| 0.0  | 0.0    | 32.5°  | 6060.2  | 5620.4  | 5180.6  | 4631.3  | 4082.0  | 3532.6  | 2983.3  | 2448.1  | 1912.9  |
| 0.0  | 0.0    | 35°    | 6944.3  | 6431.2  | 5917.2  | 5307.8  | 4697.5  | 4088.1  | 3478.8  | 2874.7  | 2269.7  |
| 0.0  | 0.0    | 37.5°  | 8067.6  | 7437.9  | 6807.4  | 6128.2  | 5449.1  | 4770.8  | 4091.7  | 3401.0  | 2710.4  |
| 0.0  | 0.0    | 40°    | 10218.1 | 9405.6  | 8593.1  | 7730.3  | 6866.5  | 6003.7  | 5140.9  | 4293.0  | 3445.2  |
| 0.0  | 0.0    | 42.5°  | 14071.3 | 12973.6 | 11875.8 | 10727.7 | 9578.7  | 8430.6  | 7281.6  | 6085.8  | 4889.2  |
| 0.0  | 0.0    | 45°    | 18420.0 | 17058.2 | 15695.5 | 14406.9 | 13117.5 | 11829.0 | 10540.5 | 8899.6  | 7258.7  |
| 0.0  | 0.0    | 47.5°  | 20865.5 | 19395.0 | 17924.6 | 16704.9 | 15485.3 | 14265.6 | 13046.0 | 11277.0 | 9508.1  |
| 0.0  | 0.0    | 50°    | 21765.4 | 20268.5 | 18771.5 | 17649.0 | 16525.6 | 15403.1 | 14279.8 | 12508.2 | 10735.7 |
| 0.0  | 0.0    | 52.5°  | 21957.1 | 20430.1 | 18903.1 | 17773.5 | 16644.0 | 15515.3 | 14385.7 | 12625.6 | 10865.5 |
| 0.0  | 0.0    | 55°    | 22350.9 | 20712.7 | 19073.5 | 17785.9 | 16498.3 | 15210.6 | 13923.0 | 12134.6 | 10346.2 |
| 0.0  | 0.0    | 57.5°  | 22865.8 | 21186.1 | 19506.3 | 18039.4 | 16572.4 | 15106.4 | 13639.5 | 11684.2 | 9728.9  |
| 0.0  | 0.0    | 60°    | 22730.7 | 21269.1 | 19806.6 | 18235.4 | 16663.4 | 15092.3 | 13520.3 | 11369.8 | 9218.4  |
| 0.0  | 0.0    | 62.5°  | 20385.0 | 19221.0 | 18056.1 | 16764.1 | 15471.1 | 14179.1 | 12887.0 | 10673.0 | 8458.9  |
| 0.0  | 0.0    | 65°    | 16770.3 | 15920.7 | 15071.1 | 14031.6 | 12991.2 | 11951.8 | 10912.3 | 8927.0  | 6942.5  |
| 0.0  | 0.0    | 67.5°  | 13591.8 | 12634.4 | 11676.2 | 10847.8 | 10018.5 | 9190.1  | 8360.8  | 6798.5  | 5236.2  |
|      |        | 70°    | 10798.4 | 9757.1  | 8715.0  | 7906.0  | 7096.2  | 6287.2  | 5478.2  | 4439.6  | 3401.9  |
|      |        | 72.5°  | 8575.5  | 7636.7  | 6697.9  | 5835.0  | 4971.3  | 4108.4  | 3244.7  | 2630.9  | 2017.1  |
|      |        | 75°    | 4098.7  | 3723.4  | 3348.0  | 2896.8  | 2445.5  | 1994.2  | 1542.9  | 1275.3  | 1008.6  |
|      |        | 77.5°  | 1519.0  | 1316.8  | 1113.7  | 930.0   | 746.3   | 563.5   | 379.8   | 348.0   | 316.2   |
|      |        | 80°    | 393.0   | 342.7   | 291.4   | 255.2   | 218.1   | 181.9   | 145.7   | 131.6   | 118.3   |
|      |        | 82.5°  | 45.0    | 41.5    | 38.9    | 37.1    | 34.4    | 32.7    | 30.0    | 27.4    | 24.7    |
|      |        | 85°    | 2.6     | 1.8     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064890  
CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 51.2   | 51.2   |
| 0.0    | 0.0  | 2.5°   | 47.7   | 46.8   |
| 0.0    | 0.0  | 5°     | 50.3   | 49.5   |
| 0.0    | 0.0  | 7.5°   | 55.6   | 53.9   |
| 0.0    | 0.0  | 10°    | 60.9   | 59.2   |
| 0.0    | 0.0  | 12.5°  | 68.9   | 66.2   |
| 0.0    | 0.0  | 15°    | 77.7   | 72.4   |
| 0.0    | 0.0  | 17.5°  | 92.7   | 81.3   |
| 0.0    | 0.0  | 20°    | 125.4  | 96.3   |
| 0.0    | 0.0  | 22.5°  | 176.6  | 120.1  |
| 0.0    | 0.0  | 25°    | 259.6  | 166.0  |
| 0.0    | 0.0  | 27.5°  | 361.2  | 220.8  |
| 0.0    | 0.0  | 30°    | 480.4  | 276.4  |
| 0.0    | 0.0  | 32.5°  | 585.5  | 329.4  |
| 0.0    | 0.0  | 35°    | 722.4  | 383.3  |
| 0.0    | 0.0  | 37.5°  | 891.1  | 452.2  |
| 0.0    | 0.0  | 40°    | 1152.5 | 556.4  |
| 0.0    | 0.0  | 42.5°  | 1623.2 | 748.9  |
| 0.0    | 0.0  | 45°    | 2636.2 | 1294.7 |
| 0.0    | 0.0  | 47.5°  | 4056.3 | 2141.7 |
| 0.0    | 0.0  | 50°    | 4962.5 | 2733.4 |
| 0.0    | 0.0  | 52.5°  | 5036.6 | 2729.0 |
| 0.0    | 0.0  | 55°    | 4597.7 | 2426.0 |
| 0.0    | 0.0  | 57.5°  | 3923.0 | 2027.7 |
| 0.0    | 0.0  | 60°    | 3260.6 | 1603.8 |
| 0.0    | 0.0  | 62.5°  | 2569.1 | 1107.5 |
| 0.0    | 0.0  | 65°    | 1877.6 | 783.4  |
| 0.0    | 0.0  | 67.5°  | 1348.6 | 585.5  |
|        |      | 70°    | 886.7  | 448.6  |
|        |      | 72.5°  | 577.6  | 365.6  |
|        |      | 75°    | 388.6  | 302.9  |
|        |      | 77.5°  | 227.0  | 201.4  |
|        |      | 80°    | 80.4   | 70.7   |
|        |      | 82.5°  | 15.0   | 10.6   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1064890

CATALOG NUMBER: GLAN-SA3B-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-12

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-850-U-5WQ

Data in this report applies to families of products including GSS-SB1A-850-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-12  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-850-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 4760  
 CIE  $u'$ : 0.2107  
 CIE  $v'$ : 0.4939  
 Duv: 0.0050  
 CIE x: 0.3537  
 CIE y: 0.3685  
 CIE z: 0.2779  
 Peak Wavelength (nm): 443  
 Dominant Wavelength (nm): 571  
 Purity: 16.69598  
 R<sub>f</sub>: 82  
 R<sub>g</sub>: 99.4

CRI (Ra): 81.1  
 R1: 79.8  
 R2: 83.5  
 R3: 87.9  
 R4: 83.1  
 R5: 80.5  
 R6: 79.1  
 R7: 86.1  
 R8: 69.0  
 R9: 8.7  
 R10: 62.4  
 R11: 83.8  
 R12: 63.0  
 R13: 79.9  
 R14: 93.3  
 R15: 72.7



### Test Conditions


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-12


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-12

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-12

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 270                      | NR            | 620    | 517                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 335                      | NR            | 625    | 486                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 397                      | NR            | 630    | 454                      | NR            | 760    | 12                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 451                      | NR            | 635    | 419                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 492                      | NR            | 640    | 384                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 1                        | NR            | 515    | 524                      | NR            | 645    | 347                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 3                        | NR            | 520    | 545                      | NR            | 650    | 313                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 5                        | NR            | 525    | 558                      | NR            | 655    | 280                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 7                        | NR            | 530    | 568                      | NR            | 660    | 248                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 13                       | NR            | 535    | 575                      | NR            | 665    | 219                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 24                       | NR            | 540    | 579                      | NR            | 670    | 192                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 47                       | NR            | 545    | 585                      | NR            | 675    | 167                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 95                       | NR            | 550    | 588                      | NR            | 680    | 146                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 181                      | NR            | 555    | 593                      | NR            | 685    | 126                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 319                      | NR            | 560    | 595                      | NR            | 690    | 109                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 539                      | NR            | 565    | 600                      | NR            | 695    | 94                       | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 868                      | NR            | 570    | 603                      | NR            | 700    | 80                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 977                      | NR            | 575    | 606                      | NR            | 705    | 69                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 601                      | NR            | 580    | 609                      | NR            | 710    | 59                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 397                      | NR            | 585    | 611                      | NR            | 715    | 51                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 302                      | NR            | 590    | 610                      | NR            | 720    | 44                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 201                      | NR            | 595    | 604                      | NR            | 725    | 37                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 157                      | NR            | 600    | 596                      | NR            | 730    | 32                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 157                      | NR            | 605    | 583                      | NR            | 735    | 27                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 171                      | NR            | 610    | 566                      | NR            | 740    | 23                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 210                      | NR            | 615    | 543                      | NR            | 745    | 20                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-12

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.83

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 270                         | NR               | 620       | 517                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 335                         | NR               | 625       | 486                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 397                         | NR               | 630       | 454                         | NR               | 760       | 12                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 451                         | NR               | 635       | 419                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 492                         | NR               | 640       | 384                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 524                         | NR               | 645       | 347                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 3                           | NR               | 520       | 545                         | NR               | 650       | 313                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 5                           | NR               | 525       | 558                         | NR               | 655       | 280                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 7                           | NR               | 530       | 568                         | NR               | 660       | 248                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 13                          | NR               | 535       | 575                         | NR               | 665       | 219                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 24                          | NR               | 540       | 579                         | NR               | 670       | 192                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 47                          | NR               | 545       | 585                         | NR               | 675       | 167                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 95                          | NR               | 550       | 588                         | NR               | 680       | 146                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 181                         | NR               | 555       | 593                         | NR               | 685       | 126                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 319                         | NR               | 560       | 595                         | NR               | 690       | 109                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 539                         | NR               | 565       | 600                         | NR               | 695       | 94                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 868                         | NR               | 570       | 603                         | NR               | 700       | 80                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 977                         | NR               | 575       | 606                         | NR               | 705       | 69                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 601                         | NR               | 580       | 609                         | NR               | 710       | 59                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 397                         | NR               | 585       | 611                         | NR               | 715       | 51                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 302                         | NR               | 590       | 610                         | NR               | 720       | 44                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 201                         | NR               | 595       | 604                         | NR               | 725       | 37                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 596                         | NR               | 730       | 32                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 157                         | NR               | 605       | 583                         | NR               | 735       | 27                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 171                         | NR               | 610       | 566                         | NR               | 740       | 23                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 210                         | NR               | 615       | 543                         | NR               | 745       | 20                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-12

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.74


| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 270                         | NR               | 620       | 517                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 335                         | NR               | 625       | 486                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 397                         | NR               | 630       | 454                         | NR               | 760       | 12                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 451                         | NR               | 635       | 419                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 492                         | NR               | 640       | 384                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 524                         | NR               | 645       | 347                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 3                           | NR               | 520       | 545                         | NR               | 650       | 313                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 5                           | NR               | 525       | 558                         | NR               | 655       | 280                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 7                           | NR               | 530       | 568                         | NR               | 660       | 248                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 13                          | NR               | 535       | 575                         | NR               | 665       | 219                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 24                          | NR               | 540       | 579                         | NR               | 670       | 192                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 47                          | NR               | 545       | 585                         | NR               | 675       | 167                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 95                          | NR               | 550       | 588                         | NR               | 680       | 146                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 181                         | NR               | 555       | 593                         | NR               | 685       | 126                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 319                         | NR               | 560       | 595                         | NR               | 690       | 109                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 539                         | NR               | 565       | 600                         | NR               | 695       | 94                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 868                         | NR               | 570       | 603                         | NR               | 700       | 80                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 977                         | NR               | 575       | 606                         | NR               | 705       | 69                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 601                         | NR               | 580       | 609                         | NR               | 710       | 59                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 397                         | NR               | 585       | 611                         | NR               | 715       | 51                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 302                         | NR               | 590       | 610                         | NR               | 720       | 44                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 201                         | NR               | 595       | 604                         | NR               | 725       | 37                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 596                         | NR               | 730       | 32                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 157                         | NR               | 605       | 583                         | NR               | 735       | 27                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 171                         | NR               | 610       | 566                         | NR               | 740       | 23                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 210                         | NR               | 615       | 543                         | NR               | 745       | 20                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-12





TM-30-18

### Summary

$R_f = 82$   
 $R_g = 99.4$   
 $CIE R_a = 81.1$   
 $R_9 = 8.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 73 | CES51 = 92 | CES76 = 66 |
| CES02 = 60 | CES27 = 90 | CES52 = 93 | CES77 = 80 |
| CES03 = 30 | CES28 = 87 | CES53 = 84 | CES78 = 65 |
| CES04 = 69 | CES29 = 69 | CES54 = 88 | CES79 = 87 |
| CES05 = 47 | CES30 = 73 | CES55 = 88 | CES80 = 83 |
| CES06 = 50 | CES31 = 72 | CES56 = 80 | CES81 = 84 |
| CES07 = 40 | CES32 = 69 | CES57 = 78 | CES82 = 93 |
| CES08 = 39 | CES33 = 75 | CES58 = 80 | CES83 = 90 |
| CES09 = 29 | CES34 = 78 | CES59 = 93 | CES84 = 92 |
| CES10 = 73 | CES35 = 88 | CES60 = 95 | CES85 = 87 |
| CES11 = 56 | CES36 = 98 | CES61 = 93 | CES86 = 80 |
| CES12 = 62 | CES37 = 85 | CES62 = 88 | CES87 = 84 |
| CES13 = 42 | CES38 = 81 | CES63 = 83 | CES88 = 85 |
| CES14 = 74 | CES39 = 93 | CES64 = 83 | CES89 = 80 |
| CES15 = 71 | CES40 = 88 | CES65 = 77 | CES90 = 83 |
| CES16 = 46 | CES41 = 89 | CES66 = 81 | CES91 = 89 |
| CES17 = 48 | CES42 = 82 | CES67 = 80 | CES92 = 73 |
| CES18 = 55 | CES43 = 80 | CES68 = 83 | CES93 = 85 |
| CES19 = 70 | CES44 = 99 | CES69 = 89 | CES94 = 67 |
| CES20 = 64 | CES45 = 87 | CES70 = 75 | CES95 = 78 |
| CES21 = 85 | CES46 = 85 | CES71 = 73 | CES96 = 84 |
| CES22 = 77 | CES47 = 82 | CES72 = 91 | CES97 = 87 |
| CES23 = 91 | CES48 = 78 | CES73 = 67 | CES98 = 81 |
| CES24 = 90 | CES49 = 84 | CES74 = 98 | CES99 = 74 |
| CES25 = 71 | CES50 = 91 | CES75 = 70 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)