

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065531

Luminaire Tested: **GLAN-SA1C-927-U-LBC**

Issue Date: 08/07/2025



Test Information

Test Method: LM-79-08
Report Number: P1065531
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA1C-927-U-LBC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 1xLight Square PACKAGE
90CRI 2700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL
Light Source: (14) 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3243.9 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G1

Input Watts (W): 50.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT


REPORT NUMBER: P1065531

CATALOG NUMBER: GLAN-SA1C-927-U-LBC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 5.6 fc

Type III - Short - N/A

REPORT NUMBER: P1065531
CATALOG NUMBER: GLAN-SA1C-927-U-LBC

Luminous Intensity Polar Plot



REPORT NUMBER: P1065531

CATALOG NUMBER: GLAN-SA1C-927-U-LBC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	22.2	0.0	22.2
	% Fixture	0.7	0.0	0.7
Street Side	Lumens	3221.8	0.0	3221.8
	% Fixture	99.3	0.0	99.3
Total	Lumens	3243.9	0.0	3243.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.3	0.0
10°-20°	7.1	0.2
20°-30°	76.8	2.4
30°-40°	227.3	7.0
40°-50°	677.4	20.9
50°-60°	1074.8	33.1
60°-70°	896.6	27.6
70°-80°	276.5	8.5
80°-90°	6.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3243.9	100.0
0°-180°	3243.9	100.0



REPORT NUMBER: P1065531


CATALOG NUMBER: GLAN-SA1C-927-U-LBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	83.1	2.6			
FM	(30°-60°)	1967.4	60.6			
FH	(60°-80°)	1165.5	35.9			G1/1800
FVH	(80°-90°)	5.8	0.2			G0/10
BL	(0°-30°)	2.2	0.1	B0/110		
BM	(30°-60°)	12.1	0.4	B0/220		
BH	(60°-80°)	7.6	0.2	B0/110		G0/110
BVH	(80°-90°)	0.3	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type III Short



REPORT NUMBER: P1065531

CATALOG NUMBER: GLAN-SA1C-927-U-LBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°
0°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
2.5°	18.4	18.4	17.6	16.7	15.7	14.7	14.5	14.0	13.7	13.5
5°	19.1	19.1	18.9	18.1	17.2	16.4	16.4	15.7	15.2	14.7
7.5°	19.6	19.8	20.3	20.1	19.6	18.9	18.9	18.4	17.6	16.4
10°	20.3	21.1	22.1	22.5	22.8	22.8	22.5	22.3	21.1	19.4
12.5°	21.1	22.5	25.0	27.4	28.9	30.9	30.6	30.1	27.0	23.3
15°	22.5	24.8	29.9	37.0	48.0	54.9	57.6	55.1	44.6	31.4
17.5°	24.3	27.9	43.4	77.4	126.9	150.5	164.7	153.2	101.5	59.5
20°	26.0	34.1	80.6	200.7	329.3	406.3	427.6	394.3	253.1	113.5
22.5°	28.9	47.8	163.4	414.9	709.7	825.1	846.9	740.3	478.1	224.0
25°	35.0	69.3	281.8	676.1	1059.1	1253.9	1244.9	1105.2	775.6	357.8
27.5°	43.9	101.0	426.1	960.6	1393.9	1565.6	1586.2	1413.5	1033.9	526.1
30°	56.6	139.9	581.0	1188.5	1662.2	1847.9	1851.4	1672.7	1265.0	673.9
32.5°	68.9	176.7	716.5	1408.8	1926.6	2130.2	2145.4	1925.6	1437.5	827.8
35°	78.2	200.7	853.8	1602.4	2193.2	2473.8	2472.8	2211.8	1641.8	965.3
37.5°	78.9	224.7	978.0	1800.4	2530.9	2845.0	2876.2	2588.5	1888.9	1135.3
40°	77.2	251.7	1135.3	2109.2	3139.4	3621.4	3648.8	3286.1	2384.3	1426.4
42.5°	79.2	298.5	1390.7	2679.4	4149.7	4842.0	4894.9	4513.6	3295.2	2020.4
45°	89.4	386.4	1925.6	3633.4	5589.9	6433.8	6416.2	5867.0	4355.0	2924.7
47.5°	123.5	601.8	2718.6	4561.9	6510.3	7261.8	7277.0	6605.8	4973.6	3619.9
50°	189.9	920.9	3384.9	5052.7	6906.0	7660.1	7645.8	6870.3	5208.6	3962.2
52.5°	247.0	1151.7	3719.1	5225.0	6956.8	7856.8	7855.9	6939.8	5245.1	3991.6
55°	261.2	1169.1	3721.8	5234.3	7070.5	8114.4	8146.7	7111.1	5292.4	3863.2
57.5°	255.6	1035.1	3566.5	5288.2	7272.9	8313.6	8315.3	7277.0	5412.4	3784.6
58°	250.7	1014.0	3535.1	5318.8	7307.7	8321.9	8317.8	7284.6	5510.2	3781.6
60°	223.2	880.5	3412.8	5397.0	7256.0	8150.9	8111.9	7118.7	5495.8	3751.5
62.5°	175.5	686.9	3292.5	5306.6	6701.7	7322.9	7339.0	6302.5	5010.1	3575.8
65°	139.7	511.9	3041.6	4654.7	5518.6	6013.6	6073.8	5125.0	4181.8	3027.9
67.5°	111.3	370.0	2551.5	3705.9	4366.8	5018.9	5062.8	4302.9	3239.8	2319.9
70°	90.4	250.2	1761.2	2710.3	3601.8	4335.0	4337.7	3574.6	2418.2	1520.1
72.5°	80.1	173.3	1022.4	1976.6	2920.5	3532.4	3461.1	2900.7	1858.5	900.3
75°	69.3	114.9	501.4	1208.3	1770.7	1782.7	1809.9	1345.6	929.0	428.1
77.5°	57.1	81.6	197.5	330.1	531.0	679.8	705.0	534.2	309.0	105.4
80°	39.2	38.7	53.2	101.2	151.9	190.4	177.7	137.5	80.9	40.4
82.5°	16.9	18.4	24.0	28.9	23.5	22.8	21.8	14.0	10.8	8.3
85°	5.4	4.9	5.1	5.1	4.2	3.2	3.2	1.5	0.0	0.0
87.5°	2.7	2.2	2.2	2.0	1.2	0.5	0.2	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065531

CATALOG NUMBER: GLAN-SA1C-927-U-LBC

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
14.2	0°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
13.2	2.5°	13.0	13.0	12.5	12.0	11.8	11.3	11.0	10.8	10.5	10.3
14.2	5°	13.7	13.5	12.7	12.0	11.3	10.5	10.0	9.6	9.1	8.8
15.7	7.5°	14.9	14.5	13.0	11.8	10.8	9.8	9.3	8.6	8.1	7.4
17.4	10°	16.4	15.4	13.5	12.0	10.5	9.3	8.6	7.8	7.1	6.1
19.8	12.5°	18.4	16.7	14.2	11.8	10.0	8.6	7.8	6.9	6.1	5.4
23.0	15°	20.1	17.9	14.5	11.8	9.6	7.8	6.9	5.9	5.1	4.2
28.9	17.5°	22.5	18.9	14.2	11.0	8.8	6.9	5.9	5.1	3.9	2.5
42.9	20°	26.7	19.6	13.7	10.3	7.6	5.6	4.4	3.4	1.7	0.5
64.4	22.5°	33.3	21.6	13.2	9.3	6.6	4.4	2.9	1.2	0.0	0.0
98.0	25°	46.1	25.0	13.2	8.8	5.9	3.2	1.0	0.0	0.0	0.0
139.2	27.5°	61.3	29.7	13.2	7.6	4.7	1.7	0.0	0.0	0.0	0.0
189.7	30°	76.7	34.8	13.2	6.6	3.7	0.2	0.0	0.0	0.0	0.0
233.5	32.5°	91.4	39.2	13.5	5.6	2.5	0.0	0.0	0.0	0.0	0.0
294.3	35°	106.4	39.9	13.2	4.9	1.5	0.0	0.0	0.0	0.0	0.0
368.8	37.5°	125.5	38.5	12.5	4.4	0.7	0.0	0.0	0.0	0.0	0.0
485.2	40°	154.4	39.2	11.8	4.2	0.2	0.0	0.0	0.0	0.0	0.0
692.8	42.5°	207.8	42.4	10.8	4.2	0.0	0.0	0.0	0.0	0.0	0.0
1103.5	45°	359.2	56.9	9.8	4.4	0.0	0.0	0.0	0.0	0.0	0.0
1656.5	47.5°	594.2	102.2	9.6	4.4	0.0	0.0	0.0	0.0	0.0	0.0
1995.5	50°	758.4	128.7	10.0	4.7	0.0	0.0	0.0	0.0	0.0	0.0
2037.8	52.5°	757.2	143.4	10.5	4.9	1.0	0.0	0.0	0.0	0.0	0.0
1878.3	55°	673.2	146.1	11.3	5.4	3.2	0.0	0.0	0.0	0.0	0.0
1614.2	57.5°	562.6	133.3	13.0	6.6	5.9	0.0	0.0	0.0	0.0	0.0
1572.7	58°	543.0	127.4	13.5	6.9	6.4	0.0	0.0	0.0	0.0	0.0
1364.2	60°	445.0	103.9	17.2	8.6	8.6	0.0	0.0	0.0	0.0	0.0
1118.4	62.5°	307.3	90.7	19.6	11.0	8.8	0.0	0.0	0.0	0.0	0.0
824.6	65°	217.4	81.8	21.3	11.8	7.1	0.0	0.0	0.0	0.0	0.0
585.9	67.5°	162.5	75.5	23.5	12.0	3.7	0.0	0.0	0.0	0.0	0.0
367.6	70°	124.5	70.8	28.9	12.7	1.0	0.0	0.0	0.0	0.0	0.0
219.1	72.5°	101.5	65.4	35.0	13.2	0.0	0.0	0.0	0.0	0.0	0.0
131.3	75°	84.1	59.1	33.8	14.5	0.0	0.0	0.0	0.0	0.0	0.0
70.1	77.5°	55.9	45.8	30.9	14.5	0.0	0.0	0.0	0.0	0.0	0.0
25.0	80°	19.6	18.1	24.0	12.7	0.0	0.0	0.0	0.0	0.0	0.0
5.1	82.5°	2.9	2.5	3.4	4.4	0.0	0.0	0.0	0.0	0.0	0.0
0.0	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065531

CATALOG NUMBER: GLAN-SA1C-927-U-LBC

CANDELA DISTRIBUTION (continued):

180°		185°	195°	205°	215°	225°	235°	245°	255°	265°	270°
14.2	0°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
10.0	2.5°	10.0	10.0	9.8	10.0	10.0	10.5	11.8	13.5	15.4	16.2
8.6	5°	8.3	8.1	7.8	7.8	7.8	8.6	9.6	11.5	13.7	14.7
7.1	7.5°	6.9	6.6	6.4	6.1	6.1	6.6	7.8	10.0	12.3	13.2
5.9	10°	5.6	5.1	4.9	4.7	4.7	5.1	6.4	8.6	11.0	12.0
4.9	12.5°	4.7	3.9	3.4	3.2	2.9	3.7	4.9	6.9	9.6	10.8
3.7	15°	3.2	2.5	1.7	1.5	1.2	2.0	3.2	5.4	8.1	9.6
2.0	17.5°	1.7	0.7	0.2	0.0	0.0	0.5	1.5	3.9	6.6	7.8
0.0	20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.0	4.9	6.1
0.0	22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	2.9	4.2
0.0	25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	2.2
0.0	27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5
0.0	30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	58°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.0	2.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1065531

CATALOG NUMBER: GLAN-SA1C-927-U-LBC

CANDELA DISTRIBUTION (continued):

275°		285°	295°	305°	315°	316°	325°	335°	345°	355°	360°
14.2	0°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
16.9	2.5°	17.4	17.2	16.7	16.2	16.2	16.2	16.9	17.6	18.4	18.4
15.2	5°	16.2	16.2	15.9	15.4	15.4	15.7	16.7	17.9	18.9	19.1
14.0	7.5°	14.9	15.4	14.9	14.7	14.9	15.2	16.2	17.6	19.1	19.6
13.0	10°	14.2	14.5	14.5	14.2	14.2	14.7	15.7	17.6	19.6	20.3
11.8	12.5°	13.2	13.7	13.5	13.5	13.5	14.0	15.2	17.4	20.1	21.1
10.5	15°	12.3	13.0	13.0	12.7	12.7	13.0	14.7	17.2	20.8	22.5
9.1	17.5°	11.3	12.0	12.3	11.8	11.8	12.3	14.0	17.2	21.3	24.3
7.4	20°	9.3	10.5	11.3	10.5	10.5	11.0	12.7	16.2	21.6	26.0
5.4	22.5°	7.4	8.6	9.6	9.3	9.3	9.6	11.8	15.4	21.8	28.9
3.2	25°	5.4	6.6	7.4	7.8	7.8	8.6	10.8	14.9	22.8	35.0
1.5	27.5°	3.2	4.7	5.6	6.1	6.4	7.4	10.0	14.5	24.5	43.9
0.0	30°	1.5	2.7	3.9	4.9	4.9	6.6	9.3	14.0	26.7	56.6
0.0	32.5°	0.0	1.2	2.0	3.4	3.7	5.4	8.6	13.5	29.9	68.9
0.0	35°	0.0	0.0	1.0	2.7	2.7	4.4	7.8	13.0	34.8	78.2
0.0	37.5°	0.0	0.0	0.0	2.0	2.2	3.9	7.6	12.7	35.8	78.9
0.0	40°	0.0	0.0	0.0	1.5	1.7	3.7	7.6	13.0	32.3	77.2
0.0	42.5°	0.0	0.0	0.0	1.0	1.2	3.7	7.6	13.5	29.2	79.2
0.0	45°	0.0	0.0	0.0	0.7	1.0	3.9	7.4	13.2	27.4	89.4
0.0	47.5°	0.0	0.0	0.0	1.0	1.5	3.9	7.1	13.0	27.7	123.5
0.0	50°	0.0	0.0	0.0	1.2	1.7	3.9	7.4	12.5	30.4	189.9
0.0	52.5°	0.0	0.0	0.0	1.0	1.5	4.4	8.1	12.3	33.1	247.0
0.0	55°	0.0	0.0	0.0	0.2	0.7	5.6	8.8	12.3	37.2	261.2
0.0	57.5°	0.0	0.0	0.0	0.0	0.0	6.4	10.0	13.0	44.1	255.6
0.0	58°	0.0	0.0	0.0	0.0	0.0	6.4	10.3	13.0	44.6	250.7
0.0	60°	0.0	0.0	0.0	0.0	0.0	6.4	11.3	14.5	48.0	223.2
0.0	62.5°	0.0	0.0	0.0	0.0	0.0	5.4	13.5	18.1	50.0	175.5
0.0	65°	0.0	0.0	0.0	0.0	0.0	4.4	15.9	19.8	51.5	139.7
0.0	67.5°	0.0	0.0	0.0	0.0	0.0	4.2	16.4	20.1	52.2	111.3
0.0	70°	0.0	0.0	0.0	0.0	0.0	4.4	16.2	21.6	54.6	90.4
0.0	72.5°	0.0	0.0	0.0	0.0	0.0	4.9	14.7	23.8	54.6	80.1
0.0	75°	0.0	0.0	0.0	0.0	0.0	5.1	13.7	26.7	49.7	69.3
0.0	77.5°	0.0	0.0	0.0	0.0	0.0	4.9	13.5	31.1	44.4	57.1
0.0	80°	0.5	0.7	0.7	0.5	0.5	4.2	13.2	31.6	37.7	39.2
0.2	82.5°	1.5	2.0	1.7	1.2	1.2	3.7	11.8	26.5	19.6	16.9
1.5	85°	2.7	3.2	3.2	2.7	2.7	3.4	7.4	9.6	6.6	5.4
2.7	87.5°	3.7	4.2	4.2	3.7	3.7	3.4	3.2	2.9	2.7	2.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-13

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-927-U-5WQ

Data in this report applies to families of products including GSS-SB1A-927-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-13
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-927-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K): 2731
 CIE u' : 0.2605
 CIE v' : 0.5298
 Duv: 0.0021
 CIE x: 0.4610
 CIE y: 0.4166
 CIE z: 0.1224
 Peak Wavelength (nm): 622
 Dominant Wavelength (nm): 583
 Purity: 63.43685
 R_f: 92.6
 R_g: 98

CRI (Ra): 91.8
 R1: 91.4
 R2: 95.1
 R3: 97.6
 R4: 92.3
 R5: 91.1
 R6: 94.7
 R7: 92.3
 R8: 80.0
 R9: 54.7
 R10: 87.7
 R11: 92.9
 R12: 84.0
 R13: 92.2
 R14: 97.8
 R15: 86.8



Test Conditions


Stabilization Time: M
 Operation Time: 1H 0M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-13


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-13

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-13

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			






REPORT NUMBER: SP1-2407-184-13

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.38


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13




TM-30-18
Summary
 $R_f = 92.6$
 $R_g = 98$
 $CIE\ R_a = 91.8$
 $R_9 = 54.7$

Color Vector Graphics


Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 94	CES51 = 98	CES76 = 90
CES02 = 64	CES27 = 95	CES52 = 98	CES77 = 90
CES03 = 32	CES28 = 97	CES53 = 96	CES78 = 89
CES04 = 71	CES29 = 95	CES54 = 96	CES79 = 93
CES05 = 51	CES30 = 98	CES55 = 95	CES80 = 94
CES06 = 52	CES31 = 96	CES56 = 94	CES81 = 82
CES07 = 44	CES32 = 91	CES57 = 94	CES82 = 97
CES08 = 43	CES33 = 97	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 96	CES59 = 96	CES84 = 96
CES10 = 77	CES35 = 98	CES60 = 96	CES85 = 85
CES11 = 59	CES36 = 90	CES61 = 94	CES86 = 82
CES12 = 66	CES37 = 95	CES62 = 95	CES87 = 93
CES13 = 44	CES38 = 96	CES63 = 94	CES88 = 95
CES14 = 74	CES39 = 99	CES64 = 92	CES89 = 85
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 98	CES66 = 91	CES91 = 85
CES17 = 50	CES42 = 97	CES67 = 90	CES92 = 82
CES18 = 57	CES43 = 97	CES68 = 91	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 93	CES94 = 79
CES20 = 68	CES45 = 99	CES70 = 90	CES95 = 87
CES21 = 87	CES46 = 96	CES71 = 89	CES96 = 92
CES22 = 79	CES47 = 94	CES72 = 96	CES97 = 96
CES23 = 92	CES48 = 93	CES73 = 87	CES98 = 93
CES24 = 91	CES49 = 96	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 98	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)