

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063698

Luminaire Tested: **GLAN-SA2B-927-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1063698
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA2B-927-U-T2BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 2xLight Square PACKAGE
90CRI 2700K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (28) 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5710 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 72.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1063698

CATALOG NUMBER: GLAN-SA2B-927-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 7.6 fc
 Type II - Short - N/A

REPORT NUMBER: P1063698

CATALOG NUMBER: GLAN-SA2B-927-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1063698

CATALOG NUMBER: GLAN-SA2B-927-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	24.4	0.0	24.4
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	5685.6	0.0	5685.6
	% Fixture	99.6	0.0	99.6
Total	Lumens	5710.0	0.0	5710.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.4	0.1
10°-20°	47.0	0.8
20°-30°	168.5	3.0
30°-40°	448.6	7.9
40°-50°	1178.6	20.6
50°-60°	1825.8	32.0
60°-70°	1530.9	26.8
70°-80°	450.5	7.9
80°-90°	55.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5710.0	100.0
0°-180°	5710.0	100.0



REPORT NUMBER: P1063698


CATALOG NUMBER: GLAN-SA2B-927-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	214.4	3.8			
FM	(30°-60°)	3443.8	60.3			
FH	(60°-80°)	1972.9	34.6			G2/5000
FVH	(80°-90°)	54.5	1.0			G1/100
BL	(0°-30°)	5.5	0.1	B0/110		
BM	(30°-60°)	9.3	0.2	B0/220		
BH	(60°-80°)	8.6	0.2	B0/110		G0/110
BVH	(80°-90°)	1.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short



REPORT NUMBER: P1063698

CATALOG NUMBER: GLAN-SA2B-927-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0
2.5°	42.4	42.8	42.0	40.5	39.3	39.3	38.9	37.7	37.7	36.5	35.7
5°	59.3	58.5	57.0	53.8	51.1	48.3	45.6	42.8	42.4	38.9	36.5
7.5°	97.0	97.8	92.7	82.9	74.6	64.0	54.2	48.3	47.5	41.6	36.9
10°	212.9	207.0	195.2	157.1	129.2	97.4	72.3	56.2	55.4	44.8	37.7
12.5°	388.1	383.4	361.8	322.5	250.6	174.4	105.7	69.5	67.2	47.5	38.1
15°	559.3	551.9	540.1	500.4	416.4	312.7	172.8	95.1	88.8	51.5	37.7
17.5°	668.5	669.7	659.1	642.2	588.0	462.7	298.5	141.8	129.6	58.5	36.9
20°	764.0	761.2	767.1	758.1	720.0	628.8	434.4	224.7	203.9	69.9	37.3
22.5°	873.9	880.6	884.9	883.0	841.0	763.2	588.8	336.2	309.9	90.7	38.5
25°	1021.2	1020.5	1020.8	1015.7	974.9	888.5	743.5	474.9	448.2	124.5	41.2
27.5°	1175.6	1180.3	1182.3	1163.8	1110.4	1025.6	886.9	626.5	595.1	178.7	44.8
30°	1386.5	1382.6	1373.6	1335.9	1271.1	1165.8	1028.3	785.6	752.6	254.5	50.3
32.5°	1670.9	1666.6	1621.0	1537.8	1440.7	1311.9	1170.5	945.0	905.0	349.2	57.7
35°	2139.5	2146.2	2034.2	1818.6	1644.6	1487.5	1328.0	1103.7	1068.4	465.8	68.0
37.5°	2857.1	2820.6	2668.6	2287.6	1912.9	1706.7	1478.4	1264.0	1233.3	609.6	81.3
40°	3554.3	3518.2	3474.2	3113.2	2379.1	1948.2	1689.0	1452.1	1412.5	771.8	100.9
42.5°	4287.3	4267.2	4265.3	3993.1	3229.9	2328.0	1942.3	1672.5	1638.7	949.8	133.2
45°	4806.5	4786.5	4828.5	4876.0	4388.6	3141.9	2383.4	1958.8	1909.7	1165.8	184.6
47.5°	4876.4	4877.2	4989.6	5138.4	5249.6	4400.8	2971.0	2338.3	2278.5	1474.9	271.0
50°	4643.9	4652.9	4831.7	5098.0	5397.3	5457.0	4007.2	2888.9	2800.6	1841.4	393.6
52.5°	4201.2	4211.4	4460.5	4898.4	5261.4	5710.7	5227.2	3609.3	3507.6	2298.6	566.4
55°	3802.6	3808.8	4094.4	4647.8	5097.6	5572.8	5951.5	4571.2	4437.7	2861.0	736.9
57.5°	3407.8	3393.3	3579.1	4212.6	5069.7	5403.5	6058.3	5667.5	5520.2	3475.8	869.6
60°	2879.9	2855.5	3004.8	3407.8	4702.8	5514.7	5858.4	6274.0	6240.6	4331.6	972.1
61°	2576.3	2566.1	2716.1	3061.8	4394.1	5486.4	5810.5	6299.5	6303.0	4736.6	1018.1
62.5°	1839.8	1868.9	2098.3	2547.6	3680.4	5303.0	5816.8	6220.5	6255.5	5274.7	1137.1
65°	817.8	864.5	1042.8	1408.5	2140.3	4411.4	5761.0	6047.3	6030.0	5422.4	1547.2
67.5°	485.1	492.2	580.9	798.1	1133.6	2372.8	5083.8	5818.3	5795.2	4720.5	1925.0
70°	382.2	385.7	414.0	500.8	657.9	908.9	2901.5	5033.9	5134.9	3827.7	1884.6
72.5°	362.5	361.8	365.7	381.0	414.4	450.9	1123.4	3346.1	3551.6	2756.6	1580.2
75°	357.8	356.3	352.3	346.4	300.1	265.5	348.0	1480.0	1599.0	1883.4	1189.7
77.5°	347.2	347.6	348.4	332.3	257.3	187.8	168.5	474.9	584.1	1195.2	845.7
80°	234.9	238.4	244.3	238.0	231.4	135.9	119.0	168.9	171.3	670.9	558.5
82.5°	119.0	119.0	116.3	103.7	89.6	88.4	94.7	122.5	124.1	339.4	262.8
85°	71.9	75.8	77.4	70.3	64.4	59.3	72.3	97.4	100.9	131.6	61.3
87.5°	16.1	16.5	18.1	24.0	35.0	47.5	67.2	89.2	90.7	84.4	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1063698

CATALOG NUMBER: GLAN-SA2B-927-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0
2.5°	35.4	34.6	34.2	33.0	31.8	30.6	29.9	29.5	29.9	30.2	30.2
5°	35.0	33.8	31.8	29.9	28.3	26.7	25.1	24.7	24.7	25.1	25.1
7.5°	35.0	33.0	30.2	27.9	25.5	23.2	22.0	21.2	21.6	21.6	21.6
10°	35.0	32.6	29.1	25.5	22.8	20.0	18.1	17.3	17.3	17.3	17.3
12.5°	34.6	32.2	27.9	23.6	19.6	16.5	14.1	13.0	13.4	13.4	13.4
15°	33.8	31.0	26.3	20.0	15.7	12.6	10.2	9.0	9.4	10.2	10.6
17.5°	32.6	29.9	23.6	16.9	12.6	9.4	7.1	6.3	6.7	7.9	7.9
20°	32.2	28.7	20.8	13.7	9.4	6.7	4.7	3.9	4.3	5.9	6.3
22.5°	32.2	27.9	18.9	11.4	7.1	4.3	2.7	1.6	1.6	2.7	2.7
25°	32.6	27.5	17.3	9.4	5.1	3.1	1.6	0.8	1.6	4.3	5.1
27.5°	33.4	27.1	16.5	7.9	3.9	2.7	1.2	2.7	4.7	4.7	4.7
30°	34.2	26.3	15.3	6.7	3.5	2.0	2.0	3.9	3.9	4.7	5.1
32.5°	35.4	25.9	14.5	5.9	2.7	1.6	2.7	2.4	2.4	2.7	3.1
35°	37.7	26.3	13.7	5.9	2.7	2.0	2.4	1.2	0.8	0.8	0.8
37.5°	40.8	26.7	12.6	5.1	2.4	2.4	1.2	0.0	0.0	0.0	0.0
40°	46.0	27.9	11.8	4.7	2.0	2.0	0.4	0.0	0.0	0.0	0.0
42.5°	54.6	30.2	11.4	4.3	2.0	1.6	0.0	0.0	0.0	0.0	0.0
45°	71.9	35.7	10.6	3.9	2.0	0.8	0.0	0.0	0.0	0.0	0.0
47.5°	103.3	48.7	10.2	3.1	1.2	0.0	0.0	0.0	0.0	0.0	0.0
50°	150.8	66.0	9.8	2.7	0.4	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	192.5	69.5	6.7	2.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	197.2	47.9	5.1	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	157.1	31.0	4.3	1.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	119.0	23.6	3.9	0.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
61°	114.3	21.2	3.9	0.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	126.1	18.5	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	205.0	15.3	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	356.3	13.4	2.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	450.1	12.6	2.4	0.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	392.4	11.4	2.4	0.8	0.4	0.0	0.0	0.0	0.0	0.0	0.0
75°	236.1	9.8	2.4	1.6	0.8	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	123.7	7.5	2.4	2.0	1.2	0.4	0.0	0.0	0.0	0.0	0.0
80°	60.1	6.7	2.7	2.0	1.6	0.8	0.0	0.0	0.0	0.0	0.0
82.5°	23.6	5.5	3.1	2.7	2.0	1.2	0.4	0.0	0.0	0.0	0.0
85°	10.6	4.7	3.5	3.1	2.7	1.6	0.4	0.0	0.0	0.0	0.0
87.5°	5.5	4.3	3.9	3.5	2.7	2.0	0.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-13

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-927-U-5WQ

Data in this report applies to families of products including GSS-SB1A-927-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-13
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-927-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K): 2731
 CIE u' : 0.2605
 CIE v' : 0.5298
 Duv: 0.0021
 CIE x: 0.4610
 CIE y: 0.4166
 CIE z: 0.1224
 Peak Wavelength (nm): 622
 Dominant Wavelength (nm): 583
 Purity: 63.43685
 R_f: 92.6
 R_g: 98

CRI (Ra): 91.8
 R1: 91.4
 R2: 95.1
 R3: 97.6
 R4: 92.3
 R5: 91.1
 R6: 94.7
 R7: 92.3
 R8: 80.0
 R9: 54.7
 R10: 87.7
 R11: 92.9
 R12: 84.0
 R13: 92.2
 R14: 97.8
 R15: 86.8



Test Conditions

Stabilization Time: M
 Operation Time: 1H 0M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-13

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-13

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.38

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13

TM-30-18

Summary

$R_f = 92.6$
 $R_g = 98$
 $CIE R_a = 91.8$
 $R_9 = 54.7$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 98	CES76 = 90
CES02 = 64	CES27 = 95	CES52 = 98	CES77 = 90
CES03 = 32	CES28 = 97	CES53 = 96	CES78 = 89
CES04 = 71	CES29 = 95	CES54 = 96	CES79 = 93
CES05 = 51	CES30 = 98	CES55 = 95	CES80 = 94
CES06 = 52	CES31 = 96	CES56 = 94	CES81 = 82
CES07 = 44	CES32 = 91	CES57 = 94	CES82 = 97
CES08 = 43	CES33 = 97	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 96	CES59 = 96	CES84 = 96
CES10 = 77	CES35 = 98	CES60 = 96	CES85 = 85
CES11 = 59	CES36 = 90	CES61 = 94	CES86 = 82
CES12 = 66	CES37 = 95	CES62 = 95	CES87 = 93
CES13 = 44	CES38 = 96	CES63 = 94	CES88 = 95
CES14 = 74	CES39 = 99	CES64 = 92	CES89 = 85
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 98	CES66 = 91	CES91 = 85
CES17 = 50	CES42 = 97	CES67 = 90	CES92 = 82
CES18 = 57	CES43 = 97	CES68 = 91	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 93	CES94 = 79
CES20 = 68	CES45 = 99	CES70 = 90	CES95 = 87
CES21 = 87	CES46 = 96	CES71 = 89	CES96 = 92
CES22 = 79	CES47 = 94	CES72 = 96	CES97 = 96
CES23 = 92	CES48 = 93	CES73 = 87	CES98 = 93
CES24 = 91	CES49 = 96	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 98	CES75 = 90	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)