

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063658

Luminaire Tested: **GLAN-SA1B-850-U-T2BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1063658  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA1B-850-U-T2BC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 1xLight Square PACKAGE  
80CRI 5000K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL  
Light Source: (14) 5000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4145.7 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B0 - U0 - G1

Input Watts (W): 38.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1063658

CATALOG NUMBER: GLAN-SA1B-850-U-T2BC

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 5.5 fc  
 Type II - Short - N/A

REPORT NUMBER: P1063658

CATALOG NUMBER: GLAN-SA1B-850-U-T2BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1063658

CATALOG NUMBER: GLAN-SA1B-850-U-T2BC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 17.7     | 0.0    | 17.7   |
|                    | % Fixture | 0.4      | 0.0    | 0.4    |
| <b>Street Side</b> | Lumens    | 4128.0   | 0.0    | 4128.0 |
|                    | % Fixture | 99.6     | 0.0    | 99.6   |
| <b>Total</b>       | Lumens    | 4145.7   | 0.0    | 4145.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 3.2    | 0.1       |
| 10°-20°   | 34.1   | 0.8       |
| 20°-30°   | 122.3  | 3.0       |
| 30°-40°   | 325.7  | 7.9       |
| 40°-50°   | 855.7  | 20.6      |
| 50°-60°   | 1325.6 | 32.0      |
| 60°-70°   | 1111.5 | 26.8      |
| 70°-80°   | 327.1  | 7.9       |
| 80°-90°   | 40.4   | 1.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4145.7 | 100.0     |
| 0°-180°   | 4145.7 | 100.0     |



REPORT NUMBER: P1063658


CATALOG NUMBER: GLAN-SA1B-850-U-T2BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 155.7  | 3.8       |                         |      |         |
| FM   | (30°-60°)   | 2500.3 | 60.3      |                         |      |         |
| FH   | (60°-80°)   | 1432.4 | 34.6      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 39.6   | 1.0       |                         |      | G1/100  |
| BL   | (0°-30°)    | 4.0    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 6.7    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 6.2    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.8    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G1**

Type II Short





REPORT NUMBER: P1063658

CATALOG NUMBER: GLAN-SA1B-850-U-T2BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 64°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   |
| 2.5°  | 30.8   | 31.1   | 30.5   | 29.4   | 28.5   | 28.5   | 28.2   | 27.4   | 27.4   | 26.5   | 26.0   |
| 5°    | 43.1   | 42.5   | 41.4   | 39.1   | 37.1   | 35.1   | 33.1   | 31.1   | 30.8   | 28.2   | 26.5   |
| 7.5°  | 70.4   | 71.0   | 67.3   | 60.2   | 54.2   | 46.5   | 39.4   | 35.1   | 34.5   | 30.2   | 26.8   |
| 10°   | 154.6  | 150.3  | 141.7  | 114.1  | 93.8   | 70.7   | 52.5   | 40.8   | 40.2   | 32.5   | 27.4   |
| 12.5° | 281.8  | 278.3  | 262.6  | 234.1  | 181.9  | 126.6  | 76.7   | 50.5   | 48.8   | 34.5   | 27.7   |
| 15°   | 406.1  | 400.7  | 392.1  | 363.3  | 302.3  | 227.0  | 125.5  | 69.0   | 64.5   | 37.4   | 27.4   |
| 17.5° | 485.4  | 486.2  | 478.5  | 466.3  | 426.9  | 335.9  | 216.7  | 102.9  | 94.1   | 42.5   | 26.8   |
| 20°   | 554.7  | 552.7  | 557.0  | 550.4  | 522.7  | 456.6  | 315.4  | 163.1  | 148.0  | 50.8   | 27.1   |
| 22.5° | 634.5  | 639.4  | 642.5  | 641.1  | 610.6  | 554.1  | 427.5  | 244.1  | 225.0  | 65.9   | 27.9   |
| 25°   | 741.5  | 740.9  | 741.2  | 737.5  | 707.8  | 645.1  | 539.8  | 344.8  | 325.4  | 90.4   | 29.9   |
| 27.5° | 853.5  | 857.0  | 858.4  | 845.0  | 806.2  | 744.6  | 643.9  | 454.9  | 432.0  | 129.8  | 32.5   |
| 30°   | 1006.7 | 1003.8 | 997.3  | 969.9  | 922.8  | 846.4  | 746.6  | 570.4  | 546.4  | 184.8  | 36.5   |
| 32.5° | 1213.1 | 1210.0 | 1176.9 | 1116.5 | 1046.0 | 952.5  | 849.8  | 686.1  | 657.1  | 253.5  | 41.9   |
| 35°   | 1553.4 | 1558.2 | 1476.9 | 1320.4 | 1194.0 | 1080.0 | 964.2  | 801.4  | 775.7  | 338.2  | 49.3   |
| 37.5° | 2074.4 | 2047.9 | 1937.5 | 1660.9 | 1388.8 | 1239.1 | 1073.4 | 917.7  | 895.5  | 442.6  | 59.0   |
| 40°   | 2580.6 | 2554.3 | 2522.4 | 2260.3 | 1727.3 | 1414.5 | 1226.3 | 1054.3 | 1025.5 | 560.4  | 73.3   |
| 42.5° | 3112.7 | 3098.2 | 3096.8 | 2899.1 | 2345.0 | 1690.3 | 1410.2 | 1214.3 | 1189.8 | 689.6  | 96.7   |
| 45°   | 3489.7 | 3475.2 | 3505.7 | 3540.2 | 3186.3 | 2281.1 | 1730.5 | 1422.2 | 1386.5 | 846.4  | 134.0  |
| 47.5° | 3540.5 | 3541.1 | 3622.6 | 3730.7 | 3811.4 | 3195.1 | 2157.1 | 1697.7 | 1654.3 | 1070.8 | 196.8  |
| 50°   | 3371.7 | 3378.2 | 3508.0 | 3701.3 | 3918.6 | 3962.0 | 2909.4 | 2097.5 | 2033.3 | 1336.9 | 285.7  |
| 52.5° | 3050.3 | 3057.7 | 3238.5 | 3556.5 | 3820.0 | 4146.2 | 3795.2 | 2620.5 | 2546.6 | 1668.9 | 411.2  |
| 55°   | 2760.8 | 2765.4 | 2972.7 | 3374.5 | 3701.0 | 4046.1 | 4321.0 | 3318.9 | 3221.9 | 2077.2 | 535.0  |
| 57.5° | 2474.2 | 2463.7 | 2598.5 | 3058.5 | 3680.8 | 3923.2 | 4398.6 | 4114.8 | 4007.9 | 2523.5 | 631.4  |
| 60°   | 2090.9 | 2073.2 | 2181.6 | 2474.2 | 3414.4 | 4003.9 | 4253.4 | 4555.2 | 4530.9 | 3144.9 | 705.8  |
| 61°   | 1870.5 | 1863.1 | 1972.0 | 2223.0 | 3190.3 | 3983.4 | 4218.6 | 4573.7 | 4576.3 | 3439.0 | 739.2  |
| 62.5° | 1335.8 | 1356.9 | 1523.4 | 1849.7 | 2672.1 | 3850.2 | 4223.2 | 4516.4 | 4541.8 | 3829.7 | 825.6  |
| 65°   | 593.7  | 627.7  | 757.1  | 1022.6 | 1553.9 | 3202.8 | 4182.7 | 4390.6 | 4378.1 | 3936.9 | 1123.3 |
| 67.5° | 352.2  | 357.3  | 421.8  | 579.5  | 823.0  | 1722.8 | 3691.1 | 4224.3 | 4207.5 | 3427.3 | 1397.7 |
| 70°   | 277.5  | 280.0  | 300.6  | 363.6  | 477.7  | 659.9  | 2106.6 | 3654.8 | 3728.1 | 2779.1 | 1368.3 |
| 72.5° | 263.2  | 262.6  | 265.5  | 276.6  | 300.9  | 327.4  | 815.6  | 2429.4 | 2578.6 | 2001.4 | 1147.3 |
| 75°   | 259.8  | 258.7  | 255.8  | 251.5  | 217.9  | 192.8  | 252.7  | 1074.6 | 1161.0 | 1367.4 | 863.8  |
| 77.5° | 252.1  | 252.4  | 253.0  | 241.3  | 186.8  | 136.3  | 122.3  | 344.8  | 424.1  | 867.8  | 614.0  |
| 80°   | 170.5  | 173.1  | 177.4  | 172.8  | 168.0  | 98.7   | 86.4   | 122.6  | 124.3  | 487.1  | 405.5  |
| 82.5° | 86.4   | 86.4   | 84.4   | 75.3   | 65.0   | 64.2   | 68.7   | 89.0   | 90.1   | 246.4  | 190.8  |
| 85°   | 52.2   | 55.0   | 56.2   | 51.0   | 46.8   | 43.1   | 52.5   | 70.7   | 73.3   | 95.5   | 44.5   |
| 87.5° | 11.7   | 12.0   | 13.1   | 17.4   | 25.4   | 34.5   | 48.8   | 64.7   | 65.9   | 61.3   | 5.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1063658

CATALOG NUMBER: GLAN-SA1B-850-U-T2BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°   | 95°  | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|------|------|------|------|------|------|------|------|------|------|
| 0°    | 25.4  | 25.4 | 25.4 | 25.4 | 25.4 | 25.4 | 25.4 | 25.4 | 25.4 | 25.4 | 25.4 |
| 2.5°  | 25.7  | 25.1 | 24.8 | 24.0 | 23.1 | 22.2 | 21.7 | 21.4 | 21.7 | 22.0 | 22.0 |
| 5°    | 25.4  | 24.5 | 23.1 | 21.7 | 20.5 | 19.4 | 18.3 | 18.0 | 18.0 | 18.3 | 18.3 |
| 7.5°  | 25.4  | 24.0 | 22.0 | 20.2 | 18.5 | 16.8 | 16.0 | 15.4 | 15.7 | 15.7 | 15.7 |
| 10°   | 25.4  | 23.7 | 21.1 | 18.5 | 16.5 | 14.5 | 13.1 | 12.5 | 12.5 | 12.5 | 12.5 |
| 12.5° | 25.1  | 23.4 | 20.2 | 17.1 | 14.3 | 12.0 | 10.3 | 9.4  | 9.7  | 9.7  | 9.7  |
| 15°   | 24.5  | 22.5 | 19.1 | 14.5 | 11.4 | 9.1  | 7.4  | 6.6  | 6.8  | 7.4  | 7.7  |
| 17.5° | 23.7  | 21.7 | 17.1 | 12.3 | 9.1  | 6.8  | 5.1  | 4.6  | 4.8  | 5.7  | 5.7  |
| 20°   | 23.4  | 20.8 | 15.1 | 10.0 | 6.8  | 4.8  | 3.4  | 2.9  | 3.1  | 4.3  | 4.6  |
| 22.5° | 23.4  | 20.2 | 13.7 | 8.3  | 5.1  | 3.1  | 2.0  | 1.1  | 1.1  | 2.0  | 2.0  |
| 25°   | 23.7  | 20.0 | 12.5 | 6.8  | 3.7  | 2.3  | 1.1  | 0.6  | 1.1  | 3.1  | 3.7  |
| 27.5° | 24.2  | 19.7 | 12.0 | 5.7  | 2.9  | 2.0  | 0.9  | 2.0  | 3.4  | 3.4  | 3.4  |
| 30°   | 24.8  | 19.1 | 11.1 | 4.8  | 2.6  | 1.4  | 1.4  | 2.9  | 2.9  | 3.4  | 3.7  |
| 32.5° | 25.7  | 18.8 | 10.6 | 4.3  | 2.0  | 1.1  | 2.0  | 1.7  | 1.7  | 2.0  | 2.3  |
| 35°   | 27.4  | 19.1 | 10.0 | 4.3  | 2.0  | 1.4  | 1.7  | 0.9  | 0.6  | 0.6  | 0.6  |
| 37.5° | 29.7  | 19.4 | 9.1  | 3.7  | 1.7  | 1.7  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  |
| 40°   | 33.4  | 20.2 | 8.6  | 3.4  | 1.4  | 1.4  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  |
| 42.5° | 39.6  | 22.0 | 8.3  | 3.1  | 1.4  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 45°   | 52.2  | 26.0 | 7.7  | 2.9  | 1.4  | 0.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 47.5° | 75.0  | 35.4 | 7.4  | 2.3  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 50°   | 109.5 | 47.9 | 7.1  | 2.0  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 52.5° | 139.7 | 50.5 | 4.8  | 1.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 55°   | 143.2 | 34.8 | 3.7  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 57.5° | 114.1 | 22.5 | 3.1  | 0.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 60°   | 86.4  | 17.1 | 2.9  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 61°   | 83.0  | 15.4 | 2.9  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 62.5° | 91.5  | 13.4 | 2.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 65°   | 148.9 | 11.1 | 2.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 67.5° | 258.7 | 9.7  | 2.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 70°   | 326.8 | 9.1  | 1.7  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.5° | 284.9 | 8.3  | 1.7  | 0.6  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 75°   | 171.4 | 7.1  | 1.7  | 1.1  | 0.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 77.5° | 89.8  | 5.4  | 1.7  | 1.4  | 0.9  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 80°   | 43.6  | 4.8  | 2.0  | 1.4  | 1.1  | 0.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 82.5° | 17.1  | 4.0  | 2.3  | 2.0  | 1.4  | 0.9  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  |
| 85°   | 7.7   | 3.4  | 2.6  | 2.3  | 2.0  | 1.1  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  |
| 87.5° | 4.0   | 3.1  | 2.9  | 2.6  | 2.0  | 1.4  | 0.6  | 0.0  | 0.0  | 0.0  | 0.0  |
| 90°   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-12

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-850-U-5WQ

Data in this report applies to families of products including GSS-SB1A-850-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-12  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-850-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 4760  
 CIE  $u'$ : 0.2107  
 CIE  $v'$ : 0.4939  
 Duv: 0.0050  
 CIE x: 0.3537  
 CIE y: 0.3685  
 CIE z: 0.2779  
 Peak Wavelength (nm): 443  
 Dominant Wavelength (nm): 571  
 Purity: 16.69598  
 R<sub>f</sub>: 82  
 R<sub>g</sub>: 99.4

CRI (Ra): 81.1  
 R1: 79.8  
 R2: 83.5  
 R3: 87.9  
 R4: 83.1  
 R5: 80.5  
 R6: 79.1  
 R7: 86.1  
 R8: 69.0  
 R9: 8.7  
 R10: 62.4  
 R11: 83.8  
 R12: 63.0  
 R13: 79.9  
 R14: 93.3  
 R15: 72.7



### Test Conditions

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-12

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-12

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-12

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 270                                  | NR                             | 620               | 517                                  | NR                             | 750               | 17                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 335                                  | NR                             | 625               | 486                                  | NR                             | 755               | 15                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 397                                  | NR                             | 630               | 454                                  | NR                             | 760               | 12                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 451                                  | NR                             | 635               | 419                                  | NR                             | 765               | 11                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 492                                  | NR                             | 640               | 384                                  | NR                             | 770               | 9                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 1                                    | NR                             | 515               | 524                                  | NR                             | 645               | 347                                  | NR                             | 775               | 8                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 3                                    | NR                             | 520               | 545                                  | NR                             | 650               | 313                                  | NR                             | 780               | 7                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 5                                    | NR                             | 525               | 558                                  | NR                             | 655               | 280                                  | NR                             | 785               | 6                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 7                                    | NR                             | 530               | 568                                  | NR                             | 660               | 248                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 13                                   | NR                             | 535               | 575                                  | NR                             | 665               | 219                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 24                                   | NR                             | 540               | 579                                  | NR                             | 670               | 192                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 47                                   | NR                             | 545               | 585                                  | NR                             | 675               | 167                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 95                                   | NR                             | 550               | 588                                  | NR                             | 680               | 146                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 181                                  | NR                             | 555               | 593                                  | NR                             | 685               | 126                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 319                                  | NR                             | 560               | 595                                  | NR                             | 690               | 109                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 539                                  | NR                             | 565               | 600                                  | NR                             | 695               | 94                                   | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 868                                  | NR                             | 570               | 603                                  | NR                             | 700               | 80                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 977                                  | NR                             | 575               | 606                                  | NR                             | 705               | 69                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 601                                  | NR                             | 580               | 609                                  | NR                             | 710               | 59                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 397                                  | NR                             | 585               | 611                                  | NR                             | 715               | 51                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 302                                  | NR                             | 590               | 610                                  | NR                             | 720               | 44                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 201                                  | NR                             | 595               | 604                                  | NR                             | 725               | 37                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 157                                  | NR                             | 600               | 596                                  | NR                             | 730               | 32                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 157                                  | NR                             | 605               | 583                                  | NR                             | 735               | 27                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 171                                  | NR                             | 610               | 566                                  | NR                             | 740               | 23                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 210                                  | NR                             | 615               | 543                                  | NR                             | 745               | 20                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-12

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.83

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 270                         | NR               | 620       | 517                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 335                         | NR               | 625       | 486                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 397                         | NR               | 630       | 454                         | NR               | 760       | 12                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 451                         | NR               | 635       | 419                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 492                         | NR               | 640       | 384                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 524                         | NR               | 645       | 347                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 3                           | NR               | 520       | 545                         | NR               | 650       | 313                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 5                           | NR               | 525       | 558                         | NR               | 655       | 280                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 7                           | NR               | 530       | 568                         | NR               | 660       | 248                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 13                          | NR               | 535       | 575                         | NR               | 665       | 219                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 24                          | NR               | 540       | 579                         | NR               | 670       | 192                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 47                          | NR               | 545       | 585                         | NR               | 675       | 167                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 95                          | NR               | 550       | 588                         | NR               | 680       | 146                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 181                         | NR               | 555       | 593                         | NR               | 685       | 126                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 319                         | NR               | 560       | 595                         | NR               | 690       | 109                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 539                         | NR               | 565       | 600                         | NR               | 695       | 94                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 868                         | NR               | 570       | 603                         | NR               | 700       | 80                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 977                         | NR               | 575       | 606                         | NR               | 705       | 69                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 601                         | NR               | 580       | 609                         | NR               | 710       | 59                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 397                         | NR               | 585       | 611                         | NR               | 715       | 51                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 302                         | NR               | 590       | 610                         | NR               | 720       | 44                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 201                         | NR               | 595       | 604                         | NR               | 725       | 37                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 596                         | NR               | 730       | 32                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 157                         | NR               | 605       | 583                         | NR               | 735       | 27                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 171                         | NR               | 610       | 566                         | NR               | 740       | 23                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 210                         | NR               | 615       | 543                         | NR               | 745       | 20                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-12

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.74

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 270                         | NR               | 620       | 517                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 335                         | NR               | 625       | 486                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 397                         | NR               | 630       | 454                         | NR               | 760       | 12                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 451                         | NR               | 635       | 419                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 492                         | NR               | 640       | 384                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 524                         | NR               | 645       | 347                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 3                           | NR               | 520       | 545                         | NR               | 650       | 313                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 5                           | NR               | 525       | 558                         | NR               | 655       | 280                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 7                           | NR               | 530       | 568                         | NR               | 660       | 248                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 13                          | NR               | 535       | 575                         | NR               | 665       | 219                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 24                          | NR               | 540       | 579                         | NR               | 670       | 192                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 47                          | NR               | 545       | 585                         | NR               | 675       | 167                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 95                          | NR               | 550       | 588                         | NR               | 680       | 146                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 181                         | NR               | 555       | 593                         | NR               | 685       | 126                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 319                         | NR               | 560       | 595                         | NR               | 690       | 109                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 539                         | NR               | 565       | 600                         | NR               | 695       | 94                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 868                         | NR               | 570       | 603                         | NR               | 700       | 80                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 977                         | NR               | 575       | 606                         | NR               | 705       | 69                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 601                         | NR               | 580       | 609                         | NR               | 710       | 59                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 397                         | NR               | 585       | 611                         | NR               | 715       | 51                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 302                         | NR               | 590       | 610                         | NR               | 720       | 44                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 201                         | NR               | 595       | 604                         | NR               | 725       | 37                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 596                         | NR               | 730       | 32                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 157                         | NR               | 605       | 583                         | NR               | 735       | 27                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 171                         | NR               | 610       | 566                         | NR               | 740       | 23                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 210                         | NR               | 615       | 543                         | NR               | 745       | 20                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-12


TM-30-18

### Summary

$R_f = 82$   
 $R_g = 99.4$   
 $CIE R_a = 81.1$   
 $R_9 = 8.7$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 73 | CES51 = 92 | CES76 = 66 |
| CES02 = 60 | CES27 = 90 | CES52 = 93 | CES77 = 80 |
| CES03 = 30 | CES28 = 87 | CES53 = 84 | CES78 = 65 |
| CES04 = 69 | CES29 = 69 | CES54 = 88 | CES79 = 87 |
| CES05 = 47 | CES30 = 73 | CES55 = 88 | CES80 = 83 |
| CES06 = 50 | CES31 = 72 | CES56 = 80 | CES81 = 84 |
| CES07 = 40 | CES32 = 69 | CES57 = 78 | CES82 = 93 |
| CES08 = 39 | CES33 = 75 | CES58 = 80 | CES83 = 90 |
| CES09 = 29 | CES34 = 78 | CES59 = 93 | CES84 = 92 |
| CES10 = 73 | CES35 = 88 | CES60 = 95 | CES85 = 87 |
| CES11 = 56 | CES36 = 98 | CES61 = 93 | CES86 = 80 |
| CES12 = 62 | CES37 = 85 | CES62 = 88 | CES87 = 84 |
| CES13 = 42 | CES38 = 81 | CES63 = 83 | CES88 = 85 |
| CES14 = 74 | CES39 = 93 | CES64 = 83 | CES89 = 80 |
| CES15 = 71 | CES40 = 88 | CES65 = 77 | CES90 = 83 |
| CES16 = 46 | CES41 = 89 | CES66 = 81 | CES91 = 89 |
| CES17 = 48 | CES42 = 82 | CES67 = 80 | CES92 = 73 |
| CES18 = 55 | CES43 = 80 | CES68 = 83 | CES93 = 85 |
| CES19 = 70 | CES44 = 99 | CES69 = 89 | CES94 = 67 |
| CES20 = 64 | CES45 = 87 | CES70 = 75 | CES95 = 78 |
| CES21 = 85 | CES46 = 85 | CES71 = 73 | CES96 = 84 |
| CES22 = 77 | CES47 = 82 | CES72 = 91 | CES97 = 87 |
| CES23 = 91 | CES48 = 78 | CES73 = 67 | CES98 = 81 |
| CES24 = 90 | CES49 = 84 | CES74 = 98 | CES99 = 74 |
| CES25 = 71 | CES50 = 91 | CES75 = 70 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)