

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065537

Luminaire Tested: **GLAN-SA3A-927-U-LBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065537  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA3A-927-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 3xLight Square PACKAGE  
90CRI 2700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (42) 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6256.2 lumens  
Efficiency: N/A  
Efficacy: 76.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 81.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1065537

CATALOG NUMBER: GLAN-SA3A-927-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 10.9 fc

Type III - Short - N/A

REPORT NUMBER: P1065537  
CATALOG NUMBER: GLAN-SA3A-927-U-LBC

## Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P1065537

CATALOG NUMBER: GLAN-SA3A-927-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 42.7     | 0.0    | 42.7   |
|                    | % Fixture | 0.7      | 0.0    | 0.7    |
| <b>Street Side</b> | Lumens    | 6213.5   | 0.0    | 6213.5 |
|                    | % Fixture | 99.3     | 0.0    | 99.3   |
| <b>Total</b>       | Lumens    | 6256.2   | 0.0    | 6256.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 2.4    | 0.0       |
| 10°-20°   | 13.7   | 0.2       |
| 20°-30°   | 148.2  | 2.4       |
| 30°-40°   | 438.3  | 7.0       |
| 40°-50°   | 1306.4 | 20.9      |
| 50°-60°   | 2072.9 | 33.1      |
| 60°-70°   | 1729.1 | 27.6      |
| 70°-80°   | 533.3  | 8.5       |
| 80°-90°   | 11.8   | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6256.2 | 100.0     |
| 0°-180°   | 6256.2 | 100.0     |



REPORT NUMBER: P1065537


CATALOG NUMBER: GLAN-SA3A-927-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 160.2  | 2.6       |                         |      |         |
| FM   | (30°-60°)   | 3794.2 | 60.6      |                         |      |         |
| FH   | (60°-80°)   | 2247.8 | 35.9      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 11.3   | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 4.2    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 23.4   | 0.4       | B0/220                  |      |         |
| BH   | (60°-80°)   | 14.6   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.6    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1065537

CATALOG NUMBER: GLAN-SA3A-927-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°     | 15°    | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°    |
|-------|-------|--------|--------|---------|---------|---------|---------|---------|---------|--------|
| 0°    | 27.4  | 27.4   | 27.4   | 27.4    | 27.4    | 27.4    | 27.4    | 27.4    | 27.4    | 27.4   |
| 2.5°  | 35.4  | 35.4   | 34.0   | 32.1    | 30.2    | 28.4    | 27.9    | 26.9    | 26.5    | 26.0   |
| 5°    | 36.9  | 36.9   | 36.4   | 35.0    | 33.1    | 31.7    | 31.7    | 30.2    | 29.3    | 28.4   |
| 7.5°  | 37.8  | 38.3   | 39.2   | 38.8    | 37.8    | 36.4    | 36.4    | 35.4    | 34.0    | 31.7   |
| 10°   | 39.2  | 40.6   | 42.5   | 43.5    | 44.0    | 44.0    | 43.5    | 43.0    | 40.6    | 37.3   |
| 12.5° | 40.6  | 43.5   | 48.2   | 52.9    | 55.8    | 59.5    | 59.1    | 58.1    | 52.0    | 44.9   |
| 15°   | 43.5  | 47.7   | 57.7   | 71.4    | 92.6    | 105.9   | 111.1   | 106.3   | 86.0    | 60.5   |
| 17.5° | 46.8  | 53.9   | 83.7   | 149.3   | 244.8   | 290.2   | 317.6   | 295.4   | 195.7   | 114.8  |
| 20°   | 50.1  | 65.7   | 155.5  | 387.1   | 635.2   | 783.6   | 824.7   | 760.4   | 488.2   | 218.8  |
| 22.5° | 55.8  | 92.2   | 315.2  | 800.1   | 1368.7  | 1591.2  | 1633.3  | 1427.7  | 922.0   | 432.0  |
| 25°   | 67.6  | 133.7  | 543.5  | 1303.9  | 2042.6  | 2418.3  | 2400.8  | 2131.4  | 1495.8  | 690.0  |
| 27.5° | 84.6  | 194.7  | 821.9  | 1852.6  | 2688.2  | 3019.5  | 3059.2  | 2726.0  | 1993.9  | 1014.7 |
| 30°   | 109.2 | 269.9  | 1120.5 | 2292.1  | 3205.7  | 3563.9  | 3570.5  | 3226.0  | 2439.6  | 1299.7 |
| 32.5° | 132.8 | 340.7  | 1381.9 | 2717.0  | 3715.6  | 4108.3  | 4137.6  | 3713.7  | 2772.3  | 1596.4 |
| 35°   | 150.8 | 387.1  | 1646.5 | 3090.3  | 4229.8  | 4770.9  | 4769.0  | 4265.7  | 3166.4  | 1861.6 |
| 37.5° | 152.2 | 433.4  | 1886.2 | 3472.2  | 4881.0  | 5486.9  | 5546.9  | 4992.1  | 3642.8  | 2189.6 |
| 40°   | 148.9 | 485.4  | 2189.6 | 4067.7  | 6054.5  | 6984.1  | 7037.0  | 6337.6  | 4598.4  | 2751.0 |
| 42.5° | 152.7 | 575.6  | 2682.0 | 5167.4  | 8003.0  | 9338.1  | 9440.2  | 8704.9  | 6355.1  | 3896.6 |
| 45°   | 172.5 | 745.3  | 3713.7 | 7007.3  | 10780.5 | 12408.2 | 12374.1 | 11315.0 | 8399.1  | 5640.5 |
| 47.5° | 238.2 | 1160.7 | 5243.0 | 8798.0  | 12555.6 | 14005.1 | 14034.4 | 12739.9 | 9591.9  | 6981.3 |
| 50°   | 366.3 | 1776.0 | 6528.0 | 9744.6  | 13318.9 | 14773.1 | 14745.6 | 13249.9 | 10045.1 | 7641.5 |
| 52.5° | 476.4 | 2221.2 | 7172.7 | 10076.8 | 13416.7 | 15152.6 | 15150.7 | 13384.1 | 10115.6 | 7698.2 |
| 55°   | 503.8 | 2254.8 | 7177.9 | 10094.8 | 13636.0 | 15649.3 | 15711.6 | 13714.4 | 10206.8 | 7450.6 |
| 57.5° | 492.9 | 1996.3 | 6878.2 | 10198.7 | 14026.3 | 16033.5 | 16036.8 | 14034.4 | 10438.4 | 7298.9 |
| 58°   | 483.5 | 1955.6 | 6817.8 | 10257.8 | 14093.5 | 16049.6 | 16041.5 | 14049.0 | 10626.9 | 7293.2 |
| 60°   | 430.5 | 1698.1 | 6581.9 | 10408.6 | 13993.7 | 15719.7 | 15644.5 | 13729.1 | 10599.0 | 7235.1 |
| 62.5° | 338.4 | 1324.7 | 6349.9 | 10234.2 | 12924.7 | 14122.8 | 14153.9 | 12154.8 | 9662.3  | 6896.2 |
| 65°   | 269.4 | 987.3  | 5865.9 | 8977.1  | 10643.0 | 11597.6 | 11713.9 | 9884.0  | 8064.9  | 5839.5 |
| 67.5° | 214.6 | 713.6  | 4920.7 | 7147.2  | 8421.8  | 9679.4  | 9764.0  | 8298.4  | 6248.3  | 4474.1 |
| 70°   | 174.4 | 482.5  | 3396.6 | 5227.0  | 6946.3  | 8360.3  | 8365.5  | 6893.8  | 4663.6  | 2931.5 |
| 72.5° | 154.5 | 334.1  | 1971.7 | 3812.0  | 5632.5  | 6812.6  | 6675.0  | 5594.2  | 3584.2  | 1736.3 |
| 75°   | 133.7 | 221.7  | 966.9  | 2330.4  | 3415.0  | 3438.2  | 3490.6  | 2595.1  | 1791.6  | 825.6  |
| 77.5° | 110.1 | 157.4  | 380.9  | 636.6   | 1024.1  | 1311.0  | 1359.7  | 1030.3  | 596.0   | 203.2  |
| 80°   | 75.6  | 74.7   | 102.6  | 195.2   | 293.0   | 367.2   | 342.6   | 265.1   | 156.0   | 78.0   |
| 82.5° | 32.6  | 35.4   | 46.3   | 55.8    | 45.4    | 44.0    | 42.1    | 26.9    | 20.8    | 16.1   |
| 85°   | 10.4  | 9.5    | 9.9    | 9.9     | 8.0     | 6.1     | 6.1     | 2.8     | 0.0     | 0.0    |
| 87.5° | 5.2   | 4.3    | 4.3    | 3.8     | 2.4     | 0.9     | 0.5     | 0.0     | 0.0     | 0.0    |
| 90°   | 0.0   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |

REPORT NUMBER: P1065537

CATALOG NUMBER: GLAN-SA3A-927-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°    |       | 90°    | 95°   | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° |
|--------|-------|--------|-------|------|------|------|------|------|------|------|------|
| 27.4   | 0°    | 27.4   | 27.4  | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 |
| 25.5   | 2.5°  | 25.0   | 25.0  | 24.1 | 23.2 | 22.7 | 21.7 | 21.3 | 20.8 | 20.3 | 19.8 |
| 27.4   | 5°    | 26.5   | 26.0  | 24.6 | 23.2 | 21.7 | 20.3 | 19.4 | 18.4 | 17.5 | 17.0 |
| 30.2   | 7.5°  | 28.8   | 27.9  | 25.0 | 22.7 | 20.8 | 18.9 | 18.0 | 16.5 | 15.6 | 14.2 |
| 33.6   | 10°   | 31.7   | 29.8  | 26.0 | 23.2 | 20.3 | 18.0 | 16.5 | 15.1 | 13.7 | 11.8 |
| 38.3   | 12.5° | 35.4   | 32.1  | 27.4 | 22.7 | 19.4 | 16.5 | 15.1 | 13.2 | 11.8 | 10.4 |
| 44.4   | 15°   | 38.8   | 34.5  | 27.9 | 22.7 | 18.4 | 15.1 | 13.2 | 11.3 | 9.9  | 8.0  |
| 55.8   | 17.5° | 43.5   | 36.4  | 27.4 | 21.3 | 17.0 | 13.2 | 11.3 | 9.9  | 7.6  | 4.7  |
| 82.7   | 20°   | 51.5   | 37.8  | 26.5 | 19.8 | 14.7 | 10.9 | 8.5  | 6.6  | 3.3  | 0.9  |
| 124.3  | 22.5° | 64.3   | 41.6  | 25.5 | 18.0 | 12.8 | 8.5  | 5.7  | 2.4  | 0.0  | 0.0  |
| 189.0  | 25°   | 88.8   | 48.2  | 25.5 | 17.0 | 11.3 | 6.1  | 1.9  | 0.0  | 0.0  | 0.0  |
| 268.4  | 27.5° | 118.2  | 57.2  | 25.5 | 14.7 | 9.0  | 3.3  | 0.0  | 0.0  | 0.0  | 0.0  |
| 365.8  | 30°   | 147.9  | 67.1  | 25.5 | 12.8 | 7.1  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  |
| 450.4  | 32.5° | 176.3  | 75.6  | 26.0 | 10.9 | 4.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 567.6  | 35°   | 205.1  | 77.0  | 25.5 | 9.5  | 2.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 711.3  | 37.5° | 242.0  | 74.2  | 24.1 | 8.5  | 1.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 935.8  | 40°   | 297.7  | 75.6  | 22.7 | 8.0  | 0.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1336.0 | 42.5° | 400.8  | 81.8  | 20.8 | 8.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2128.1 | 45°   | 692.8  | 109.6 | 18.9 | 8.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3194.8 | 47.5° | 1146.1 | 197.1 | 18.4 | 8.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3848.4 | 50°   | 1462.7 | 248.1 | 19.4 | 9.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3930.2 | 52.5° | 1460.3 | 276.5 | 20.3 | 9.5  | 1.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3622.5 | 55°   | 1298.2 | 281.7 | 21.7 | 10.4 | 6.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3113.0 | 57.5° | 1085.1 | 257.1 | 25.0 | 12.8 | 11.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3033.2 | 58°   | 1047.3 | 245.8 | 26.0 | 13.2 | 12.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2631.0 | 60°   | 858.2  | 200.4 | 33.1 | 16.5 | 16.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2157.0 | 62.5° | 592.6  | 174.9 | 37.8 | 21.3 | 17.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1590.3 | 65°   | 419.2  | 157.8 | 41.1 | 22.7 | 13.7 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1130.0 | 67.5° | 313.3  | 145.6 | 45.4 | 23.2 | 7.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 708.9  | 70°   | 240.1  | 136.6 | 55.8 | 24.6 | 1.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 422.5  | 72.5° | 195.7  | 126.2 | 67.6 | 25.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 253.3  | 75°   | 162.1  | 113.9 | 65.2 | 27.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135.2  | 77.5° | 107.8  | 88.4  | 59.5 | 27.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 48.2   | 80°   | 37.8   | 35.0  | 46.3 | 24.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 9.9    | 82.5° | 5.7    | 4.7   | 6.6  | 8.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 85°   | 0.0    | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 87.5° | 0.0    | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 90°   | 0.0    | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

REPORT NUMBER: P1065537

CATALOG NUMBER: GLAN-SA3A-927-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180° |       | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° |
|------|-------|------|------|------|------|------|------|------|------|------|------|
| 27.4 | 0°    | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 |
| 19.4 | 2.5°  | 19.4 | 19.4 | 18.9 | 19.4 | 19.4 | 20.3 | 22.7 | 26.0 | 29.8 | 31.2 |
| 16.5 | 5°    | 16.1 | 15.6 | 15.1 | 15.1 | 15.1 | 16.5 | 18.4 | 22.2 | 26.5 | 28.4 |
| 13.7 | 7.5°  | 13.2 | 12.8 | 12.3 | 11.8 | 11.8 | 12.8 | 15.1 | 19.4 | 23.6 | 25.5 |
| 11.3 | 10°   | 10.9 | 9.9  | 9.5  | 9.0  | 9.0  | 9.9  | 12.3 | 16.5 | 21.3 | 23.2 |
| 9.5  | 12.5° | 9.0  | 7.6  | 6.6  | 6.1  | 5.7  | 7.1  | 9.5  | 13.2 | 18.4 | 20.8 |
| 7.1  | 15°   | 6.1  | 4.7  | 3.3  | 2.8  | 2.4  | 3.8  | 6.1  | 10.4 | 15.6 | 18.4 |
| 3.8  | 17.5° | 3.3  | 1.4  | 0.5  | 0.0  | 0.0  | 0.9  | 2.8  | 7.6  | 12.8 | 15.1 |
| 0.0  | 20°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 3.8  | 9.5  | 11.8 |
| 0.0  | 22.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.5  | 5.7  | 8.0  |
| 0.0  | 25°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 2.4  | 4.3  |
| 0.0  | 27.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.9  |
| 0.0  | 30°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 32.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 35°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 80°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 82.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 85°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.4  |
| 0.0  | 87.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.9  | 3.8  |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P1065537

CATALOG NUMBER: GLAN-SA3A-927-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275° |       | 285° | 295° | 305° | 315° | 316° | 325° | 335° | 345° | 355°  | 360°  |
|------|-------|------|------|------|------|------|------|------|------|-------|-------|
| 27.4 | 0°    | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4 | 27.4  | 27.4  |
| 32.6 | 2.5°  | 33.6 | 33.1 | 32.1 | 31.2 | 31.2 | 31.2 | 32.6 | 34.0 | 35.4  | 35.4  |
| 29.3 | 5°    | 31.2 | 31.2 | 30.7 | 29.8 | 29.8 | 30.2 | 32.1 | 34.5 | 36.4  | 36.9  |
| 26.9 | 7.5°  | 28.8 | 29.8 | 28.8 | 28.4 | 28.8 | 29.3 | 31.2 | 34.0 | 36.9  | 37.8  |
| 25.0 | 10°   | 27.4 | 27.9 | 27.9 | 27.4 | 27.4 | 28.4 | 30.2 | 34.0 | 37.8  | 39.2  |
| 22.7 | 12.5° | 25.5 | 26.5 | 26.0 | 26.0 | 26.0 | 26.9 | 29.3 | 33.6 | 38.8  | 40.6  |
| 20.3 | 15°   | 23.6 | 25.0 | 25.0 | 24.6 | 24.6 | 25.0 | 28.4 | 33.1 | 40.2  | 43.5  |
| 17.5 | 17.5° | 21.7 | 23.2 | 23.6 | 22.7 | 22.7 | 23.6 | 26.9 | 33.1 | 41.1  | 46.8  |
| 14.2 | 20°   | 18.0 | 20.3 | 21.7 | 20.3 | 20.3 | 21.3 | 24.6 | 31.2 | 41.6  | 50.1  |
| 10.4 | 22.5° | 14.2 | 16.5 | 18.4 | 18.0 | 18.0 | 18.4 | 22.7 | 29.8 | 42.1  | 55.8  |
| 6.1  | 25°   | 10.4 | 12.8 | 14.2 | 15.1 | 15.1 | 16.5 | 20.8 | 28.8 | 44.0  | 67.6  |
| 2.8  | 27.5° | 6.1  | 9.0  | 10.9 | 11.8 | 12.3 | 14.2 | 19.4 | 27.9 | 47.3  | 84.6  |
| 0.0  | 30°   | 2.8  | 5.2  | 7.6  | 9.5  | 9.5  | 12.8 | 18.0 | 26.9 | 51.5  | 109.2 |
| 0.0  | 32.5° | 0.0  | 2.4  | 3.8  | 6.6  | 7.1  | 10.4 | 16.5 | 26.0 | 57.7  | 132.8 |
| 0.0  | 35°   | 0.0  | 0.0  | 1.9  | 5.2  | 5.2  | 8.5  | 15.1 | 25.0 | 67.1  | 150.8 |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 3.8  | 4.3  | 7.6  | 14.7 | 24.6 | 69.0  | 152.2 |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 2.8  | 3.3  | 7.1  | 14.7 | 25.0 | 62.4  | 148.9 |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 1.9  | 2.4  | 7.1  | 14.7 | 26.0 | 56.2  | 152.7 |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 1.4  | 1.9  | 7.6  | 14.2 | 25.5 | 52.9  | 172.5 |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 1.9  | 2.8  | 7.6  | 13.7 | 25.0 | 53.4  | 238.2 |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 2.4  | 3.3  | 7.6  | 14.2 | 24.1 | 58.6  | 366.3 |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 1.9  | 2.8  | 8.5  | 15.6 | 23.6 | 63.8  | 476.4 |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.5  | 1.4  | 10.9 | 17.0 | 23.6 | 71.8  | 503.8 |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 12.3 | 19.4 | 25.0 | 85.1  | 492.9 |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 12.3 | 19.8 | 25.0 | 86.0  | 483.5 |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 12.3 | 21.7 | 27.9 | 92.6  | 430.5 |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 10.4 | 26.0 | 35.0 | 96.4  | 338.4 |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 8.5  | 30.7 | 38.3 | 99.2  | 269.4 |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 8.0  | 31.7 | 38.8 | 100.7 | 214.6 |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 8.5  | 31.2 | 41.6 | 105.4 | 174.4 |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 9.5  | 28.4 | 45.8 | 105.4 | 154.5 |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 9.9  | 26.5 | 51.5 | 95.9  | 133.7 |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 9.5  | 26.0 | 60.0 | 85.5  | 110.1 |
| 0.0  | 80°   | 0.9  | 1.4  | 1.4  | 0.9  | 0.9  | 8.0  | 25.5 | 61.0 | 72.8  | 75.6  |
| 0.5  | 82.5° | 2.8  | 3.8  | 3.3  | 2.4  | 2.4  | 7.1  | 22.7 | 51.0 | 37.8  | 32.6  |
| 2.8  | 85°   | 5.2  | 6.1  | 6.1  | 5.2  | 5.2  | 6.6  | 14.2 | 18.4 | 12.8  | 10.4  |
| 5.2  | 87.5° | 7.1  | 8.0  | 8.0  | 7.1  | 7.1  | 6.6  | 6.1  | 5.7  | 5.2   | 5.2   |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |

(END OF RI



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-13

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-927-U-5WQ

Data in this report applies to families of products including GSS-SB1A-927-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-13  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-927-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 2700K CCT 26 LEDS

### Spectral Parameters

CCT (K): 2731  
 CIE  $u'$ : 0.2605  
 CIE  $v'$ : 0.5298  
 Duv: 0.0021  
 CIE x: 0.4610  
 CIE y: 0.4166  
 CIE z: 0.1224  
 Peak Wavelength (nm): 622  
 Dominant Wavelength (nm): 583  
 Purity: 63.43685  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 98

CRI (Ra): 91.8  
 R1: 91.4  
 R2: 95.1  
 R3: 97.6  
 R4: 92.3  
 R5: 91.1  
 R6: 94.7  
 R7: 92.3  
 R8: 80.0  
 R9: 54.7  
 R10: 87.7  
 R11: 92.9  
 R12: 84.0  
 R13: 92.2  
 R14: 97.8  
 R15: 86.8



### Test Conditions


Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-13


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-13

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-13

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 253                                    | NR                             | 620               | 997                                    | NR                             | 750               | 78                                     | NR                             | 880               | 2                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 285                                    | NR                             | 625               | 996                                    | NR                             | 755               | 67                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 314                                    | NR                             | 630               | 989                                    | NR                             | 760               | 58                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 343                                    | NR                             | 635               | 969                                    | NR                             | 765               | 50                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 372                                    | NR                             | 640               | 939                                    | NR                             | 770               | 42                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 401                                    | NR                             | 645               | 901                                    | NR                             | 775               | 36                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 431                                    | NR                             | 650               | 858                                    | NR                             | 780               | 31                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 459                                    | NR                             | 655               | 806                                    | NR                             | 785               | 26                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 0                                      | NR                             | 530               | 488                                    | NR                             | 660               | 752                                    | NR                             | 790               | 23                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 516                                    | NR                             | 665               | 696                                    | NR                             | 795               | 19                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 5                                      | NR                             | 540               | 540                                    | NR                             | 670               | 636                                    | NR                             | 800               | 17                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 566                                    | NR                             | 675               | 579                                    | NR                             | 805               | 14                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 19                                     | NR                             | 550               | 589                                    | NR                             | 680               | 524                                    | NR                             | 810               | 12                                     | NR                             | 940               | 0                                      | NR                             |
| 425               | 34                                     | NR                             | 555               | 612                                    | NR                             | 685               | 470                                    | NR                             | 815               | 11                                     | NR                             | 945               | 0                                      | NR                             |
| 430               | 61                                     | NR                             | 560               | 634                                    | NR                             | 690               | 421                                    | NR                             | 820               | 9                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 113                                    | NR                             | 565               | 660                                    | NR                             | 695               | 371                                    | NR                             | 825               | 8                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 198                                    | NR                             | 570               | 688                                    | NR                             | 700               | 327                                    | NR                             | 830               | 7                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 288                                    | NR                             | 575               | 719                                    | NR                             | 705               | 288                                    | NR                             | 835               | 6                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 286                                    | NR                             | 580               | 754                                    | NR                             | 710               | 251                                    | NR                             | 840               | 5                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 228                                    | NR                             | 585               | 791                                    | NR                             | 715               | 220                                    | NR                             | 845               | 4                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 207                                    | NR                             | 590               | 831                                    | NR                             | 720               | 192                                    | NR                             | 850               | 4                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 186                                    | NR                             | 595               | 870                                    | NR                             | 725               | 166                                    | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 168                                    | NR                             | 600               | 907                                    | NR                             | 730               | 144                                    | NR                             | 860               | 3                                      | NR                             | 990               | 1                                      | NR                             |
| 475               | 177                                    | NR                             | 605               | 940                                    | NR                             | 735               | 124                                    | NR                             | 865               | 2                                      | NR                             | 995               | 1                                      | NR                             |
| 480               | 198                                    | NR                             | 610               | 967                                    | NR                             | 740               | 106                                    | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 223                                    | NR                             | 615               | 988                                    | NR                             | 745               | 91                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-13

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.27

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 253                                  | NR                             | 620               | 997                                  | NR                             | 750               | 78                                   | NR                             | 880               | 2                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 285                                  | NR                             | 625               | 996                                  | NR                             | 755               | 67                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 314                                  | NR                             | 630               | 989                                  | NR                             | 760               | 58                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 343                                  | NR                             | 635               | 969                                  | NR                             | 765               | 50                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 372                                  | NR                             | 640               | 939                                  | NR                             | 770               | 42                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 401                                  | NR                             | 645               | 901                                  | NR                             | 775               | 36                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 431                                  | NR                             | 650               | 858                                  | NR                             | 780               | 31                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 459                                  | NR                             | 655               | 806                                  | NR                             | 785               | 26                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 0                                    | NR                             | 530               | 488                                  | NR                             | 660               | 752                                  | NR                             | 790               | 23                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 516                                  | NR                             | 665               | 696                                  | NR                             | 795               | 19                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 5                                    | NR                             | 540               | 540                                  | NR                             | 670               | 636                                  | NR                             | 800               | 17                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 566                                  | NR                             | 675               | 579                                  | NR                             | 805               | 14                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 19                                   | NR                             | 550               | 589                                  | NR                             | 680               | 524                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 34                                   | NR                             | 555               | 612                                  | NR                             | 685               | 470                                  | NR                             | 815               | 11                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 61                                   | NR                             | 560               | 634                                  | NR                             | 690               | 421                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 113                                  | NR                             | 565               | 660                                  | NR                             | 695               | 371                                  | NR                             | 825               | 8                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 198                                  | NR                             | 570               | 688                                  | NR                             | 700               | 327                                  | NR                             | 830               | 7                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 288                                  | NR                             | 575               | 719                                  | NR                             | 705               | 288                                  | NR                             | 835               | 6                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 286                                  | NR                             | 580               | 754                                  | NR                             | 710               | 251                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 228                                  | NR                             | 585               | 791                                  | NR                             | 715               | 220                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 207                                  | NR                             | 590               | 831                                  | NR                             | 720               | 192                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 186                                  | NR                             | 595               | 870                                  | NR                             | 725               | 166                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 168                                  | NR                             | 600               | 907                                  | NR                             | 730               | 144                                  | NR                             | 860               | 3                                    | NR                             | 990               | 1                                    | NR                             |
| 475               | 177                                  | NR                             | 605               | 940                                  | NR                             | 735               | 124                                  | NR                             | 865               | 2                                    | NR                             | 995               | 1                                    | NR                             |
| 480               | 198                                  | NR                             | 610               | 967                                  | NR                             | 740               | 106                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 223                                  | NR                             | 615               | 988                                  | NR                             | 745               | 91                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-13

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.38


| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 253                      | NR            | 620    | 997                      | NR            | 750    | 78                       | NR            | 880    | 2                        | NR            |
| 365    | 0                        | NR            | 495    | 285                      | NR            | 625    | 996                      | NR            | 755    | 67                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 314                      | NR            | 630    | 989                      | NR            | 760    | 58                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 343                      | NR            | 635    | 969                      | NR            | 765    | 50                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 372                      | NR            | 640    | 939                      | NR            | 770    | 42                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 401                      | NR            | 645    | 901                      | NR            | 775    | 36                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 431                      | NR            | 650    | 858                      | NR            | 780    | 31                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 459                      | NR            | 655    | 806                      | NR            | 785    | 26                       | NR            | 915    | 1                        | NR            |
| 400    | 0                        | NR            | 530    | 488                      | NR            | 660    | 752                      | NR            | 790    | 23                       | NR            | 920    | 1                        | NR            |
| 405    | 2                        | NR            | 535    | 516                      | NR            | 665    | 696                      | NR            | 795    | 19                       | NR            | 925    | 1                        | NR            |
| 410    | 5                        | NR            | 540    | 540                      | NR            | 670    | 636                      | NR            | 800    | 17                       | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 566                      | NR            | 675    | 579                      | NR            | 805    | 14                       | NR            | 935    | 0                        | NR            |
| 420    | 19                       | NR            | 550    | 589                      | NR            | 680    | 524                      | NR            | 810    | 12                       | NR            | 940    | 0                        | NR            |
| 425    | 34                       | NR            | 555    | 612                      | NR            | 685    | 470                      | NR            | 815    | 11                       | NR            | 945    | 0                        | NR            |
| 430    | 61                       | NR            | 560    | 634                      | NR            | 690    | 421                      | NR            | 820    | 9                        | NR            | 950    | 0                        | NR            |
| 435    | 113                      | NR            | 565    | 660                      | NR            | 695    | 371                      | NR            | 825    | 8                        | NR            | 955    | 0                        | NR            |
| 440    | 198                      | NR            | 570    | 688                      | NR            | 700    | 327                      | NR            | 830    | 7                        | NR            | 960    | 0                        | NR            |
| 445    | 288                      | NR            | 575    | 719                      | NR            | 705    | 288                      | NR            | 835    | 6                        | NR            | 965    | 0                        | NR            |
| 450    | 286                      | NR            | 580    | 754                      | NR            | 710    | 251                      | NR            | 840    | 5                        | NR            | 970    | 0                        | NR            |
| 455    | 228                      | NR            | 585    | 791                      | NR            | 715    | 220                      | NR            | 845    | 4                        | NR            | 975    | 0                        | NR            |
| 460    | 207                      | NR            | 590    | 831                      | NR            | 720    | 192                      | NR            | 850    | 4                        | NR            | 980    | 0                        | NR            |
| 465    | 186                      | NR            | 595    | 870                      | NR            | 725    | 166                      | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 168                      | NR            | 600    | 907                      | NR            | 730    | 144                      | NR            | 860    | 3                        | NR            | 990    | 1                        | NR            |
| 475    | 177                      | NR            | 605    | 940                      | NR            | 735    | 124                      | NR            | 865    | 2                        | NR            | 995    | 1                        | NR            |
| 480    | 198                      | NR            | 610    | 967                      | NR            | 740    | 106                      | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 223                      | NR            | 615    | 988                      | NR            | 745    | 91                       | NR            | 875    | 2                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-13





TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 98$   
 $CIE\ R_a = 91.8$   
 $R_9 = 54.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 98 | CES76 = 90 |
| CES02 = 64 | CES27 = 95 | CES52 = 98 | CES77 = 90 |
| CES03 = 32 | CES28 = 97 | CES53 = 96 | CES78 = 89 |
| CES04 = 71 | CES29 = 95 | CES54 = 96 | CES79 = 93 |
| CES05 = 51 | CES30 = 98 | CES55 = 95 | CES80 = 94 |
| CES06 = 52 | CES31 = 96 | CES56 = 94 | CES81 = 82 |
| CES07 = 44 | CES32 = 91 | CES57 = 94 | CES82 = 97 |
| CES08 = 43 | CES33 = 97 | CES58 = 94 | CES83 = 96 |
| CES09 = 29 | CES34 = 96 | CES59 = 96 | CES84 = 96 |
| CES10 = 77 | CES35 = 98 | CES60 = 96 | CES85 = 85 |
| CES11 = 59 | CES36 = 90 | CES61 = 94 | CES86 = 82 |
| CES12 = 66 | CES37 = 95 | CES62 = 95 | CES87 = 93 |
| CES13 = 44 | CES38 = 96 | CES63 = 94 | CES88 = 95 |
| CES14 = 74 | CES39 = 99 | CES64 = 92 | CES89 = 85 |
| CES15 = 72 | CES40 = 98 | CES65 = 89 | CES90 = 96 |
| CES16 = 48 | CES41 = 98 | CES66 = 91 | CES91 = 85 |
| CES17 = 50 | CES42 = 97 | CES67 = 90 | CES92 = 82 |
| CES18 = 57 | CES43 = 97 | CES68 = 91 | CES93 = 89 |
| CES19 = 72 | CES44 = 99 | CES69 = 93 | CES94 = 79 |
| CES20 = 68 | CES45 = 99 | CES70 = 90 | CES95 = 87 |
| CES21 = 87 | CES46 = 96 | CES71 = 89 | CES96 = 92 |
| CES22 = 79 | CES47 = 94 | CES72 = 96 | CES97 = 96 |
| CES23 = 92 | CES48 = 93 | CES73 = 87 | CES98 = 93 |
| CES24 = 91 | CES49 = 96 | CES74 = 92 | CES99 = 90 |
| CES25 = 72 | CES50 = 98 | CES75 = 90 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)