

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064969

Luminaire Tested: **GLAN-SA5A-930-U-RBC**

Issue Date: 08/07/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1064969  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA5A-930-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 5xLight Square PACKAGE  
90CRI 3000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (70) 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11210.4 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 136.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1.7 fc

Type III - Short - N/A

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 56.1     | 0.0    | 56.1    |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 11154.2  | 0.0    | 11154.2 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 11210.4  | 0.0    | 11210.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 4.4     | 0.0       |
| 10°-20°   | 24.6    | 0.2       |
| 20°-30°   | 265.7   | 2.4       |
| 30°-40°   | 785.6   | 7.0       |
| 40°-50°   | 2341.4  | 20.9      |
| 50°-60°   | 3712.6  | 33.1      |
| 60°-70°   | 3099.1  | 27.6      |
| 70°-80°   | 955.7   | 8.5       |
| 80°-90°   | 21.2    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 11210.4 | 100.0     |
| 0°-180°   | 11210.4 | 100.0     |



REPORT NUMBER: P1064969


CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 284.4  | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 6819.6 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 4033.8 | 36.0      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 16.4   | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 10.3   | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 20.1   | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 20.9   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 4.8    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°  | 22.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|------|-------|
| 0°     | 49.1   | 49.1   | 49.1  | 49.1  | 49.1  | 49.1  | 49.1  | 49.1  | 49.1 | 49.1  |
| 2.5°   | 44.9   | 44.9   | 44.9  | 44.9  | 44.1  | 44.1  | 43.2  | 43.2  | 42.4 | 42.4  |
| 5°     | 47.4   | 47.4   | 46.6  | 45.7  | 45.7  | 44.9  | 44.1  | 43.2  | 43.2 | 42.4  |
| 7.5°   | 51.7   | 50.8   | 50.0  | 49.1  | 47.4  | 46.6  | 44.9  | 44.1  | 43.2 | 41.5  |
| 10°    | 56.8   | 55.1   | 53.4  | 51.7  | 50.0  | 48.3  | 46.6  | 45.7  | 44.1 | 43.2  |
| 12.5°  | 63.5   | 61.0   | 57.6  | 55.1  | 53.4  | 50.8  | 49.1  | 47.4  | 44.9 | 43.2  |
| 15°    | 69.5   | 66.1   | 61.8  | 58.5  | 55.9  | 52.5  | 50.0  | 47.4  | 45.7 | 43.2  |
| 17.5°  | 77.9   | 72.0   | 65.2  | 61.0  | 57.6  | 53.4  | 49.1  | 46.6  | 44.1 | 40.7  |
| 20°    | 92.3   | 80.5   | 67.8  | 62.7  | 57.6  | 52.5  | 47.4  | 44.1  | 41.5 | 38.1  |
| 22.5°  | 115.2  | 94.9   | 74.5  | 66.9  | 60.1  | 52.5  | 45.7  | 42.4  | 39.0 | 35.6  |
| 25°    | 159.3  | 122.8  | 86.4  | 76.2  | 66.1  | 55.9  | 45.7  | 41.5  | 38.1 | 33.9  |
| 27.5°  | 211.8  | 157.6  | 102.5 | 88.1  | 74.5  | 60.1  | 45.7  | 40.7  | 36.4 | 31.3  |
| 30°    | 265.2  | 193.2  | 120.3 | 101.7 | 83.0  | 64.4  | 45.7  | 39.8  | 34.7 | 28.8  |
| 32.5°  | 316.0  | 226.2  | 135.5 | 113.5 | 91.5  | 68.6  | 46.6  | 39.8  | 33.0 | 26.3  |
| 35°    | 367.7  | 253.3  | 138.1 | 115.2 | 92.3  | 68.6  | 45.7  | 38.1  | 31.3 | 23.7  |
| 37.5°  | 433.7  | 283.8  | 133.0 | 110.1 | 88.1  | 65.2  | 43.2  | 36.4  | 29.7 | 22.0  |
| 40°    | 533.7  | 334.6  | 135.5 | 111.8 | 88.1  | 64.4  | 40.7  | 33.9  | 28.0 | 21.2  |
| 42.5°  | 718.4  | 432.9  | 146.6 | 119.4 | 92.3  | 64.4  | 37.3  | 31.3  | 26.3 | 20.3  |
| 45°    | 1241.9 | 719.2  | 196.5 | 155.9 | 115.2 | 74.5  | 33.9  | 28.8  | 24.6 | 19.5  |
| 47.5°  | 2054.4 | 1203.8 | 353.3 | 272.8 | 193.2 | 112.7 | 33.0  | 28.8  | 24.6 | 19.5  |
| 50°    | 2622.0 | 1533.4 | 444.8 | 342.3 | 239.7 | 137.2 | 34.7  | 29.7  | 25.4 | 20.3  |
| 52.5°  | 2617.7 | 1557.1 | 495.6 | 380.4 | 266.0 | 150.8 | 36.4  | 31.3  | 27.1 | 22.0  |
| 55°    | 2327.1 | 1416.4 | 504.9 | 388.0 | 271.9 | 155.0 | 39.0  | 33.9  | 28.8 | 23.7  |
| 57.5°  | 1945.1 | 1203.0 | 460.9 | 356.7 | 253.3 | 149.1 | 44.9  | 39.0  | 33.9 | 28.0  |
| 60°    | 1538.4 | 948.8  | 359.2 | 283.8 | 209.2 | 133.9 | 59.3  | 51.7  | 44.9 | 37.3  |
| 62.5°  | 1062.3 | 687.9  | 313.4 | 251.6 | 190.6 | 128.8 | 67.8  | 60.1  | 53.4 | 45.7  |
| 65°    | 751.4  | 517.6  | 283.0 | 230.4 | 178.8 | 126.2 | 73.7  | 65.2  | 57.6 | 49.1  |
| 67.5°  | 561.7  | 411.7  | 260.9 | 216.0 | 171.1 | 126.2 | 81.3  | 71.2  | 61.8 | 51.7  |
| 70°    | 430.4  | 338.0  | 244.8 | 208.4 | 172.8 | 136.4 | 100.0 | 85.6  | 72.0 | 57.6  |
| 72.5°  | 350.7  | 288.9  | 226.2 | 199.9 | 173.7 | 147.4 | 121.1 | 102.5 | 83.9 | 64.4  |
| 75°    | 290.6  | 247.4  | 204.2 | 182.1 | 161.0 | 138.9 | 116.9 | 100.0 | 83.9 | 66.9  |
| 77.5°  | 193.2  | 176.2  | 158.4 | 145.7 | 133.0 | 119.4 | 106.7 | 92.3  | 78.8 | 64.4  |
| 80°    | 67.8   | 65.2   | 62.7  | 67.8  | 72.9  | 77.9  | 83.0  | 72.9  | 63.5 | 53.4  |
| 82.5°  | 10.2   | 9.3    | 8.5   | 9.3   | 10.2  | 11.0  | 11.9  | 12.7  | 13.6 | 14.4  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 |
| 0.0 | 2.5°   | 41.5  | 41.5 | 40.7  | 40.7 | 40.7  | 39.8 | 39.8  | 39.0 | 39.0  | 39.0 |
| 0.0 | 5°     | 40.7  | 40.7 | 39.8  | 39.0 | 38.1  | 38.1 | 37.3  | 36.4 | 36.4  | 35.6 |
| 0.0 | 7.5°   | 39.8  | 39.0 | 38.1  | 37.3 | 36.4  | 35.6 | 34.7  | 33.9 | 33.9  | 33.0 |
| 0.0 | 10°    | 40.7  | 39.0 | 38.1  | 36.4 | 35.6  | 34.7 | 33.0  | 32.2 | 31.3  | 31.3 |
| 0.0 | 12.5°  | 39.0  | 38.1 | 36.4  | 34.7 | 33.9  | 32.2 | 31.3  | 29.7 | 28.8  | 28.8 |
| 0.0 | 15°    | 39.0  | 37.3 | 34.7  | 33.0 | 31.3  | 30.5 | 28.8  | 27.1 | 26.3  | 25.4 |
| 0.0 | 17.5°  | 36.4  | 34.7 | 32.2  | 30.5 | 28.8  | 27.1 | 25.4  | 23.7 | 22.9  | 22.0 |
| 0.0 | 20°    | 33.0  | 31.3 | 28.8  | 26.3 | 24.6  | 22.9 | 21.2  | 19.5 | 18.6  | 17.8 |
| 0.0 | 22.5°  | 29.7  | 28.0 | 25.4  | 22.9 | 21.2  | 19.5 | 16.9  | 15.2 | 14.4  | 12.7 |
| 0.0 | 25°    | 28.0  | 25.4 | 22.9  | 20.3 | 17.8  | 16.1 | 13.6  | 11.0 | 9.3   | 7.6  |
| 0.0 | 27.5°  | 23.7  | 21.2 | 18.6  | 16.1 | 13.6  | 11.0 | 8.5   | 5.9  | 4.2   | 3.4  |
| 0.0 | 30°    | 20.3  | 17.8 | 15.2  | 12.7 | 9.3   | 6.8  | 4.2   | 0.8  | 0.8   | 0.8  |
| 0.0 | 32.5°  | 16.9  | 14.4 | 11.0  | 8.5  | 6.8   | 4.2  | 2.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 13.6  | 11.0 | 7.6   | 5.1  | 4.2   | 2.5  | 1.7   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 11.9  | 9.3  | 5.9   | 2.5  | 1.7   | 1.7  | 0.8   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 11.0  | 7.6  | 4.2   | 0.8  | 0.8   | 0.8  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 11.0  | 7.6  | 3.4   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 11.0  | 7.6  | 3.4   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 11.0  | 7.6  | 3.4   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 11.9  | 8.5  | 4.2   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 13.6  | 10.2 | 6.8   | 3.4  | 2.5   | 1.7  | 0.8   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 16.9  | 15.2 | 12.7  | 11.0 | 8.5   | 5.9  | 2.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 22.0  | 22.0 | 21.2  | 20.3 | 15.2  | 10.2 | 5.1   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 29.7  | 29.7 | 29.7  | 29.7 | 22.0  | 15.2 | 7.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 36.4  | 34.7 | 32.2  | 30.5 | 22.9  | 15.2 | 7.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 36.4  | 33.0 | 28.8  | 24.6 | 18.6  | 12.7 | 5.9   | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 33.9  | 27.1 | 19.5  | 12.7 | 9.3   | 6.8  | 3.4   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 33.9  | 23.7 | 13.6  | 3.4  | 2.5   | 1.7  | 0.8   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 33.9  | 22.9 | 11.0  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 37.3  | 25.4 | 12.7  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 37.3  | 25.4 | 12.7  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 33.0  | 22.0 | 11.0  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 11.0  | 7.6  | 3.4   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  |
| 0.0   | 2.5°   | 38.1 | 38.1  | 38.1 | 37.3  | 37.3 | 37.3  | 37.3 | 36.4  | 36.4 | 36.4  |
| 0.0   | 5°     | 34.7 | 34.7  | 33.9 | 33.9  | 33.0 | 33.0  | 32.2 | 32.2  | 31.3 | 31.3  |
| 0.0   | 7.5°   | 32.2 | 31.3  | 31.3 | 30.5  | 29.7 | 29.7  | 28.8 | 28.8  | 28.0 | 27.1  |
| 0.0   | 10°    | 29.7 | 28.8  | 28.8 | 28.0  | 27.1 | 26.3  | 26.3 | 25.4  | 24.6 | 23.7  |
| 0.0   | 12.5°  | 27.1 | 26.3  | 25.4 | 24.6  | 23.7 | 22.9  | 22.9 | 22.0  | 21.2 | 20.3  |
| 0.0   | 15°    | 23.7 | 22.9  | 22.0 | 21.2  | 20.3 | 19.5  | 19.5 | 18.6  | 17.8 | 16.9  |
| 0.0   | 17.5°  | 20.3 | 19.5  | 19.5 | 18.6  | 17.8 | 16.9  | 16.1 | 14.4  | 13.6 | 12.7  |
| 0.0   | 20°    | 15.2 | 14.4  | 13.6 | 12.7  | 11.9 | 10.2  | 9.3  | 7.6   | 5.9  | 5.1   |
| 0.0   | 22.5°  | 10.2 | 8.5   | 7.6  | 5.9   | 4.2  | 3.4   | 2.5  | 0.8   | 0.0  | 0.0   |
| 0.0   | 25°    | 3.4  | 2.5   | 1.7  | 0.8   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1  | 49.1 | 49.1   | 49.1 |
| 0.0 | 2.5°   | 35.6  | 35.6 | 35.6  | 34.7 | 34.7  | 34.7 | 34.7  | 34.7 | 34.7   | 34.7 |
| 0.0 | 5°     | 30.5  | 30.5 | 30.5  | 29.7 | 29.7  | 28.8 | 28.8  | 28.8 | 28.0   | 28.0 |
| 0.0 | 7.5°   | 26.3  | 25.4 | 25.4  | 24.6 | 24.6  | 23.7 | 23.7  | 23.7 | 22.9   | 22.9 |
| 0.0 | 10°    | 22.0  | 21.2 | 21.2  | 20.3 | 20.3  | 19.5 | 19.5  | 18.6 | 18.6   | 17.8 |
| 0.0 | 12.5°  | 19.5  | 18.6 | 17.8  | 16.9 | 16.9  | 16.1 | 15.2  | 15.2 | 14.4   | 13.6 |
| 0.0 | 15°    | 15.2  | 14.4 | 13.6  | 12.7 | 11.9  | 11.0 | 10.2  | 10.2 | 9.3    | 8.5  |
| 0.0 | 17.5°  | 10.2  | 8.5  | 7.6   | 6.8  | 6.8   | 5.9  | 5.1   | 4.2  | 3.4    | 2.5  |
| 0.0 | 20°    | 2.5   | 1.7  | 0.8   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   |
| 0.0    | 2.5°   | 34.7 | 33.9   | 33.9 | 33.9   | 34.7 | 34.7   | 34.7 | 34.7   | 34.7 | 34.7   |
| 0.0    | 5°     | 28.0 | 27.1   | 27.1 | 27.1   | 27.1 | 27.1   | 27.1 | 27.1   | 27.1 | 27.1   |
| 0.0    | 7.5°   | 22.9 | 22.0   | 22.0 | 22.0   | 22.0 | 21.2   | 21.2 | 21.2   | 21.2 | 21.2   |
| 0.0    | 10°    | 17.8 | 16.9   | 16.9 | 16.9   | 16.9 | 16.1   | 16.1 | 16.1   | 16.1 | 16.1   |
| 0.0    | 12.5°  | 12.7 | 12.7   | 11.9 | 11.9   | 11.9 | 11.0   | 11.0 | 11.0   | 11.0 | 10.2   |
| 0.0    | 15°    | 7.6  | 6.8    | 5.9  | 5.9    | 5.9  | 5.1    | 5.1  | 5.1    | 5.1  | 4.2    |
| 0.0    | 17.5°  | 1.7  | 1.7    | 0.8  | 0.8    | 0.8  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]





REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 |
| 0.0  | 2.5°   | 35.6   | 35.6 | 36.4   | 36.4 | 37.3   | 39.0 | 39.8   | 40.7 | 42.4   | 44.1 |
| 0.0  | 5°     | 28.0   | 28.8 | 28.8   | 29.7 | 30.5   | 31.3 | 32.2   | 33.0 | 34.7   | 36.4 |
| 0.0  | 7.5°   | 22.0   | 22.0 | 22.9   | 22.9 | 23.7   | 25.4 | 26.3   | 27.1 | 28.8   | 31.3 |
| 0.0  | 10°    | 16.9   | 16.9 | 17.8   | 17.8 | 18.6   | 20.3 | 21.2   | 22.0 | 23.7   | 26.3 |
| 0.0  | 12.5°  | 11.0   | 11.9 | 11.9   | 12.7 | 13.6   | 15.2 | 16.1   | 16.9 | 18.6   | 20.3 |
| 0.0  | 15°    | 5.1    | 5.9  | 5.9    | 6.8  | 7.6    | 9.3  | 10.2   | 11.0 | 12.7   | 15.2 |
| 0.0  | 17.5°  | 0.8    | 0.8  | 1.7    | 1.7  | 2.5    | 3.4  | 4.2    | 5.1  | 7.6    | 9.3  |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.7    | 3.4  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.8  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   |
| 0.0    | 2.5°   | 46.6 | 48.3   | 50.0 | 51.7   | 53.4 | 55.1   | 55.9 | 57.6   | 58.5 | 59.3   |
| 0.0    | 5°     | 39.8 | 41.5   | 44.1 | 45.7   | 47.4 | 49.1   | 50.8 | 51.7   | 52.5 | 53.4   |
| 0.0    | 7.5°   | 34.7 | 36.4   | 39.0 | 40.7   | 42.4 | 44.1   | 45.7 | 47.4   | 48.3 | 49.1   |
| 0.0    | 10°    | 29.7 | 32.2   | 33.9 | 36.4   | 38.1 | 39.8   | 41.5 | 43.2   | 44.9 | 45.7   |
| 0.0    | 12.5°  | 23.7 | 26.3   | 28.8 | 30.5   | 33.0 | 35.6   | 37.3 | 39.0   | 40.7 | 42.4   |
| 0.0    | 15°    | 18.6 | 21.2   | 23.7 | 25.4   | 28.0 | 30.5   | 33.0 | 34.7   | 36.4 | 38.1   |
| 0.0    | 17.5°  | 13.6 | 16.1   | 18.6 | 20.3   | 22.9 | 25.4   | 27.1 | 29.7   | 31.3 | 33.0   |
| 0.0    | 20°    | 6.8  | 9.3    | 11.9 | 14.4   | 16.9 | 19.5   | 21.2 | 23.7   | 25.4 | 27.1   |
| 0.0    | 22.5°  | 0.8  | 3.4    | 5.9  | 7.6    | 10.2 | 12.7   | 14.4 | 16.9   | 18.6 | 20.3   |
| 0.0    | 25°    | 0.0  | 0.8    | 2.5  | 3.4    | 4.2  | 5.9    | 7.6  | 9.3    | 11.0 | 12.7   |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.8    | 1.7  | 3.4    | 5.1  | 6.8    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.7    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.8    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.8    | 0.8  | 1.7    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.7    | 2.5  | 4.2    | 5.1  | 5.9    |
|        | 87.5°  | 0.0  | 0.8    | 1.7  | 2.5    | 3.4  | 5.1    | 6.8  | 8.5    | 9.3  | 10.2   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 49.1 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.3 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 54.2 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50.0 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.4 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 43.2 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39.8 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35.6 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28.8 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.0 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.2 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8.5  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2.5  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.8  |        |      |        |      |        |      |        |      |        |      |        |
| 3.4  |        |      |        |      |        |      |        |      |        |      |        |
| 7.6  |        |      |        |      |        |      |        |      |        |      |        |
| 11.0 |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 |
| 0.0  | 2.5°   | 60.1   | 60.1 | 60.1   | 60.1 | 59.3   | 59.3 | 59.3   | 58.5 | 58.5   | 57.6 |
| 0.0  | 5°     | 55.1   | 55.9 | 55.9   | 55.9 | 55.9   | 55.9 | 55.9   | 55.9 | 55.1   | 55.1 |
| 0.0  | 7.5°   | 50.8   | 51.7 | 52.5   | 52.5 | 53.4   | 53.4 | 53.4   | 52.5 | 52.5   | 51.7 |
| 0.0  | 10°    | 48.3   | 49.1 | 49.1   | 50.0 | 50.0   | 50.0 | 50.0   | 50.0 | 50.0   | 50.0 |
| 0.0  | 12.5°  | 44.9   | 45.7 | 46.6   | 46.6 | 47.4   | 47.4 | 47.4   | 47.4 | 46.6   | 46.6 |
| 0.0  | 15°    | 40.7   | 42.4 | 43.2   | 44.1 | 44.1   | 44.9 | 44.9   | 44.9 | 44.9   | 44.9 |
| 0.0  | 17.5°  | 37.3   | 39.0 | 39.8   | 40.7 | 40.7   | 41.5 | 41.5   | 42.4 | 42.4   | 42.4 |
| 0.0  | 20°    | 30.5   | 32.2 | 33.0   | 34.7 | 35.6   | 36.4 | 37.3   | 38.1 | 38.1   | 39.0 |
| 0.0  | 22.5°  | 23.7   | 25.4 | 26.3   | 28.0 | 28.8   | 29.7 | 30.5   | 31.3 | 32.2   | 33.0 |
| 0.0  | 25°    | 16.9   | 18.6 | 19.5   | 21.2 | 22.0   | 22.9 | 23.7   | 24.6 | 24.6   | 25.4 |
| 0.0  | 27.5°  | 9.3    | 11.0 | 12.7   | 13.6 | 15.2   | 16.1 | 16.9   | 17.8 | 18.6   | 19.5 |
| 0.0  | 30°    | 4.2    | 5.1  | 5.9    | 7.6  | 8.5    | 9.3  | 10.2   | 11.9 | 12.7   | 13.6 |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.8    | 2.5  | 3.4    | 4.2  | 5.1    | 5.9  | 5.9    | 6.8  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.8    | 1.7  | 2.5    | 3.4  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 1.7    | 1.7  | 1.7    | 2.5  | 2.5    | 2.5  | 2.5    | 2.5  | 2.5    | 2.5  |
|      | 82.5°  | 4.2    | 5.1  | 5.9    | 5.9  | 6.8    | 6.8  | 6.8    | 6.8  | 5.9    | 5.9  |
|      | 85°    | 8.5    | 9.3  | 10.2   | 10.2 | 11.0   | 11.0 | 11.0   | 11.0 | 11.0   | 11.0 |
|      | 87.5°  | 11.9   | 12.7 | 13.6   | 13.6 | 14.4   | 14.4 | 14.4   | 14.4 | 14.4   | 14.4 |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 49.1   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.6   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 55.1   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 51.7   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 50.0   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 46.6   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 44.9   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.4   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 38.1   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 33.0   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 26.3   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 20.3   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 14.4   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 8.5    | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.1    | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.8    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.8    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.8    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.8    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.8    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 2.5    |        |        |      |        |      |        |      |        |      |        |      |
| 5.9    |        |        |      |        |      |        |      |        |      |        |      |
| 11.0   |        |        |      |        |      |        |      |        |      |        |      |
| 14.4   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   |
| 0.0    | 2.5°   | 56.8 | 56.8   | 55.9 | 55.9   | 55.9 | 55.9   | 55.9 | 56.8   | 57.6 | 57.6   |
| 0.0    | 5°     | 54.2 | 54.2   | 53.4 | 53.4   | 53.4 | 54.2   | 54.2 | 55.1   | 55.9 | 56.8   |
| 0.0    | 7.5°   | 51.7 | 50.8   | 50.8 | 51.7   | 51.7 | 52.5   | 52.5 | 53.4   | 54.2 | 55.1   |
| 0.0    | 10°    | 50.0 | 49.1   | 49.1 | 49.1   | 50.0 | 50.0   | 50.8 | 51.7   | 52.5 | 53.4   |
| 0.0    | 12.5°  | 46.6 | 46.6   | 46.6 | 46.6   | 47.4 | 47.4   | 48.3 | 49.1   | 50.8 | 51.7   |
| 0.0    | 15°    | 44.9 | 44.1   | 44.1 | 44.1   | 44.1 | 44.9   | 44.9 | 46.6   | 48.3 | 49.1   |
| 0.0    | 17.5°  | 41.5 | 41.5   | 40.7 | 40.7   | 41.5 | 41.5   | 42.4 | 44.1   | 45.7 | 46.6   |
| 0.0    | 20°    | 38.1 | 37.3   | 36.4 | 36.4   | 37.3 | 37.3   | 38.1 | 39.8   | 41.5 | 42.4   |
| 0.0    | 22.5°  | 33.0 | 32.2   | 32.2 | 32.2   | 32.2 | 33.0   | 33.0 | 34.7   | 37.3 | 39.0   |
| 0.0    | 25°    | 26.3 | 27.1   | 27.1 | 28.0   | 28.0 | 28.8   | 29.7 | 31.3   | 33.9 | 35.6   |
| 0.0    | 27.5°  | 20.3 | 21.2   | 21.2 | 22.9   | 23.7 | 24.6   | 25.4 | 28.0   | 30.5 | 32.2   |
| 0.0    | 30°    | 15.2 | 16.1   | 16.9 | 17.8   | 19.5 | 21.2   | 22.9 | 25.4   | 28.0 | 29.7   |
| 0.0    | 32.5°  | 9.3  | 11.0   | 11.9 | 13.6   | 15.2 | 16.9   | 18.6 | 21.2   | 24.6 | 27.1   |
| 0.0    | 35°    | 6.8  | 7.6    | 9.3  | 10.2   | 11.9 | 13.6   | 15.2 | 18.6   | 21.2 | 24.6   |
| 0.0    | 37.5°  | 3.4  | 5.1    | 6.8  | 8.5    | 10.2 | 11.9   | 13.6 | 16.9   | 20.3 | 22.9   |
| 0.0    | 40°    | 2.5  | 4.2    | 5.1  | 6.8    | 9.3  | 11.0   | 12.7 | 16.1   | 19.5 | 22.9   |
| 0.0    | 42.5°  | 1.7  | 2.5    | 3.4  | 5.9    | 7.6  | 10.2   | 12.7 | 16.1   | 19.5 | 22.9   |
| 0.0    | 45°    | 1.7  | 1.7    | 2.5  | 5.1    | 7.6  | 11.0   | 13.6 | 16.9   | 19.5 | 22.9   |
| 0.0    | 47.5°  | 1.7  | 2.5    | 3.4  | 6.8    | 8.5  | 11.0   | 13.6 | 16.1   | 19.5 | 22.0   |
| 0.0    | 50°    | 2.5  | 3.4    | 4.2  | 7.6    | 9.3  | 11.9   | 13.6 | 16.9   | 19.5 | 22.9   |
| 0.0    | 52.5°  | 1.7  | 2.5    | 3.4  | 6.8    | 9.3  | 12.7   | 15.2 | 18.6   | 22.0 | 24.6   |
| 0.0    | 55°    | 0.8  | 0.8    | 0.8  | 5.1    | 10.2 | 14.4   | 19.5 | 22.0   | 25.4 | 28.0   |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 3.4    | 10.2 | 16.1   | 22.0 | 25.4   | 28.8 | 31.3   |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 3.4    | 10.2 | 16.1   | 22.0 | 26.3   | 30.5 | 34.7   |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 3.4    | 8.5  | 13.6   | 18.6 | 25.4   | 33.0 | 39.8   |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 2.5    | 6.8  | 11.0   | 15.2 | 25.4   | 35.6 | 44.9   |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 2.5    | 6.8  | 10.2   | 14.4 | 25.4   | 35.6 | 46.6   |
|        | 70°    | 0.0  | 0.0    | 0.0  | 2.5    | 6.8  | 11.0   | 15.2 | 25.4   | 35.6 | 45.7   |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 2.5    | 7.6  | 11.9   | 16.9 | 25.4   | 33.9 | 42.4   |
|        | 75°    | 0.0  | 0.0    | 0.0  | 3.4    | 7.6  | 12.7   | 17.8 | 25.4   | 33.0 | 39.8   |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 2.5    | 7.6  | 11.9   | 16.9 | 24.6   | 32.2 | 39.0   |
|        | 80°    | 2.5  | 1.7    | 1.7  | 4.2    | 7.6  | 11.0   | 14.4 | 22.0   | 30.5 | 38.1   |
|        | 82.5°  | 5.1  | 5.1    | 4.2  | 5.9    | 7.6  | 10.2   | 12.7 | 19.5   | 27.1 | 33.9   |
|        | 85°    | 10.2 | 10.2   | 9.3  | 10.2   | 10.2 | 11.0   | 11.9 | 15.2   | 18.6 | 22.0   |
|        | 87.5°  | 13.6 | 13.6   | 12.7 | 12.7   | 12.7 | 11.9   | 11.9 | 11.9   | 11.9 | 11.0   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 49.1 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 58.5 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.6 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.9 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 54.2 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50.8 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.3 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44.1 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.7 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.3 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34.7 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.2 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29.7 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.1 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.3 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.3 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.3 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25.4 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 24.6 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25.4 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28.0 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30.5 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34.7 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39.0 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.6 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.1 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 56.8 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.9 |        |      |        |      |        |      |        |      |        |      |        |
| 50.8 |        |      |        |      |        |      |        |      |        |      |        |
| 47.4 |        |      |        |      |        |      |        |      |        |      |        |
| 46.6 |        |      |        |      |        |      |        |      |        |      |        |
| 45.7 |        |      |        |      |        |      |        |      |        |      |        |
| 40.7 |        |      |        |      |        |      |        |      |        |      |        |
| 25.4 |        |      |        |      |        |      |        |      |        |      |        |
| 11.0 |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250° | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°  |
|------|--------|--------|------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 49.1   | 49.1 | 49.1   | 49.1  | 49.1   | 49.1  | 49.1   | 49.1  | 49.1   | 49.1  |
| 0.0  | 2.5°   | 59.3   | 60.1 | 60.1   | 61.0  | 61.8   | 62.7  | 62.7   | 63.5  | 63.5   | 63.5  |
| 0.0  | 5°     | 58.5   | 60.1 | 61.0   | 61.8  | 62.7   | 63.5  | 64.4   | 65.2  | 66.1   | 66.1  |
| 0.0  | 7.5°   | 57.6   | 58.5 | 60.1   | 61.0  | 62.7   | 63.5  | 65.2   | 66.1  | 66.9   | 67.8  |
| 0.0  | 10°    | 55.9   | 57.6 | 59.3   | 61.0  | 62.7   | 64.4  | 66.1   | 67.8  | 69.5   | 70.3  |
| 0.0  | 12.5°  | 54.2   | 56.8 | 58.5   | 60.1  | 62.7   | 65.2  | 66.9   | 69.5  | 71.2   | 72.9  |
| 0.0  | 15°    | 53.4   | 55.1 | 57.6   | 59.3  | 62.7   | 66.1  | 68.6   | 72.0  | 75.4   | 77.9  |
| 0.0  | 17.5°  | 50.8   | 54.2 | 56.8   | 59.3  | 62.7   | 66.9  | 70.3   | 73.7  | 78.8   | 83.9  |
| 0.0  | 20°    | 47.4   | 50.0 | 53.4   | 55.9  | 61.0   | 65.2  | 70.3   | 74.5  | 82.2   | 89.8  |
| 0.0  | 22.5°  | 44.1   | 47.4 | 50.0   | 53.4  | 59.3   | 64.4  | 70.3   | 75.4  | 88.1   | 100.0 |
| 0.0  | 25°    | 40.7   | 44.9 | 48.3   | 51.7  | 58.5   | 65.2  | 72.0   | 78.8  | 100.0  | 121.1 |
| 0.0  | 27.5°  | 39.0   | 42.4 | 46.6   | 50.0  | 58.5   | 67.8  | 76.2   | 84.7  | 118.6  | 151.6 |
| 0.0  | 30°    | 36.4   | 40.7 | 44.1   | 48.3  | 59.3   | 70.3  | 81.3   | 92.3  | 144.0  | 195.7 |
| 0.0  | 32.5°  | 33.9   | 38.1 | 42.4   | 46.6  | 61.0   | 75.4  | 89.0   | 103.4 | 171.1  | 238.1 |
| 0.0  | 35°    | 31.3   | 36.4 | 40.7   | 44.9  | 63.5   | 83.0  | 101.7  | 120.3 | 195.7  | 270.2 |
| 0.0  | 37.5°  | 30.5   | 35.6 | 39.8   | 44.1  | 64.4   | 83.9  | 104.2  | 123.7 | 198.2  | 272.8 |
| 0.0  | 40°    | 31.3   | 35.6 | 40.7   | 44.9  | 61.8   | 78.8  | 94.9   | 111.8 | 189.8  | 266.9 |
| 0.0  | 42.5°  | 31.3   | 36.4 | 41.5   | 46.6  | 60.1   | 73.7  | 87.3   | 100.8 | 187.2  | 273.6 |
| 0.0  | 45°    | 30.5   | 35.6 | 40.7   | 45.7  | 58.5   | 70.3  | 83.0   | 94.9  | 202.5  | 309.2 |
| 0.0  | 47.5°  | 29.7   | 34.7 | 39.8   | 44.9  | 57.6   | 70.3  | 83.0   | 95.7  | 261.8  | 427.0 |
| 0.0  | 50°    | 29.7   | 34.7 | 39.0   | 43.2  | 58.5   | 74.5  | 89.8   | 105.0 | 381.2  | 656.5 |
| 0.0  | 52.5°  | 31.3   | 35.6 | 39.0   | 42.4  | 60.1   | 78.8  | 96.6   | 114.4 | 484.6  | 853.9 |
| 0.0  | 55°    | 33.9   | 36.4 | 39.8   | 42.4  | 64.4   | 85.6  | 107.6  | 128.8 | 515.9  | 903.1 |
| 0.0  | 57.5°  | 37.3   | 39.8 | 42.4   | 44.9  | 72.0   | 99.1  | 125.4  | 152.5 | 518.5  | 883.6 |
| 0.0  | 60°    | 41.5   | 44.9 | 47.4   | 50.0  | 78.8   | 108.4 | 137.2  | 166.0 | 469.3  | 771.8 |
| 0.0  | 62.5°  | 50.8   | 55.1 | 58.5   | 62.7  | 90.6   | 117.8 | 145.7  | 172.8 | 389.7  | 606.6 |
| 0.0  | 65°    | 58.5   | 61.8 | 65.2   | 68.6  | 95.7   | 123.7 | 150.8  | 177.9 | 330.4  | 482.9 |
| 0.0  | 67.5°  | 60.1   | 63.5 | 66.1   | 69.5  | 97.4   | 125.4 | 152.5  | 180.4 | 283.0  | 384.6 |
|      | 70°    | 61.0   | 65.2 | 70.3   | 74.5  | 103.4  | 132.2 | 160.1  | 188.9 | 250.8  | 312.6 |
|      | 72.5°  | 58.5   | 66.9 | 74.5   | 82.2  | 109.3  | 135.5 | 162.7  | 188.9 | 233.0  | 277.0 |
|      | 75°    | 58.5   | 70.3 | 81.3   | 92.3  | 112.7  | 132.2 | 152.5  | 172.0 | 205.9  | 239.7 |
|      | 77.5°  | 61.8   | 77.1 | 92.3   | 107.6 | 119.4  | 130.5 | 142.3  | 153.3 | 175.4  | 197.4 |
|      | 80°    | 61.8   | 77.9 | 93.2   | 109.3 | 114.4  | 120.3 | 125.4  | 130.5 | 133.0  | 135.5 |
|      | 82.5°  | 53.4   | 66.1 | 78.8   | 91.5  | 85.6   | 79.6  | 73.7   | 67.8  | 63.5   | 58.5  |
|      | 85°    | 27.1   | 29.7 | 31.3   | 33.0  | 30.5   | 28.0  | 25.4   | 22.9  | 21.2   | 18.6  |
|      | 87.5°  | 11.0   | 11.0 | 10.2   | 10.2  | 10.2   | 10.2  | 9.3    | 9.3   | 9.3    | 9.3   |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 49.1   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 63.5   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 66.1   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 68.6   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 72.0   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 75.4   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 82.2   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 90.6   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104.2  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 133.0  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180.4  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 250.8  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 339.7  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 424.4  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 482.0  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 525.2  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 568.4  | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 653.2  | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 822.6  | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1253.8 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1920.5 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2417.8 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2472.9 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2231.4 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1907.8 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1491.0 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1126.7 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 831.9  | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 588.8  |        |        |      |        |      |        |      |        |      |        |      |
| 438.0  |        |        |      |        |      |        |      |        |      |        |      |
| 318.5  |        |        |      |        |      |        |      |        |      |        |      |
| 239.7  |        |        |      |        |      |        |      |        |      |        |      |
| 134.7  |        |        |      |        |      |        |      |        |      |        |      |
| 61.0   |        |        |      |        |      |        |      |        |      |        |      |
| 17.8   |        |        |      |        |      |        |      |        |      |        |      |
| 8.5    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5° | 280°   | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 49.1   | 49.1   | 49.1   | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    |
| 0.0    | 2.5°   | 63.5   | 62.7   | 62.7   | 61.8    | 61.0    | 60.1    | 59.3    | 58.5    | 57.6    | 56.8    |
| 0.0    | 5°     | 66.1   | 66.1   | 66.1   | 65.2    | 65.2    | 64.4    | 64.4    | 63.5    | 62.7    | 61.8    |
| 0.0    | 7.5°   | 68.6   | 69.5   | 69.5   | 70.3    | 70.3    | 70.3    | 70.3    | 69.5    | 69.5    | 69.5    |
| 0.0    | 10°    | 72.9   | 73.7   | 74.5   | 75.4    | 76.2    | 77.1    | 77.1    | 77.9    | 77.9    | 77.9    |
| 0.0    | 12.5°  | 77.9   | 80.5   | 82.2   | 84.7    | 86.4    | 89.0    | 90.6    | 93.2    | 94.9    | 96.6    |
| 0.0    | 15°    | 85.6   | 89.8   | 94.9   | 99.1    | 103.4   | 109.3   | 116.1   | 122.0   | 127.9   | 137.2   |
| 0.0    | 17.5°  | 96.6   | 110.1  | 123.7  | 136.4   | 149.9   | 179.6   | 209.2   | 238.1   | 267.7   | 310.9   |
| 0.0    | 20°    | 117.8  | 158.4  | 198.2  | 238.9   | 278.7   | 382.9   | 486.3   | 590.5   | 693.8   | 804.8   |
| 0.0    | 22.5°  | 165.2  | 265.2  | 365.1  | 465.1   | 565.1   | 782.8   | 999.6   | 1217.4  | 1434.2  | 1689.2  |
| 0.0    | 25°    | 239.7  | 423.6  | 607.4  | 790.4   | 974.2   | 1314.8  | 1656.2  | 1996.8  | 2337.3  | 2668.5  |
| 0.0    | 27.5°  | 349.0  | 630.3  | 911.5  | 1192.0  | 1473.2  | 1934.9  | 2397.5  | 2859.2  | 3320.9  | 3695.3  |
| 0.0    | 30°    | 483.7  | 864.9  | 1246.2 | 1627.4  | 2008.6  | 2533.8  | 3059.1  | 3583.5  | 4108.7  | 4517.9  |
| 0.0    | 32.5°  | 610.8  | 1077.6 | 1544.4 | 2010.3  | 2477.1  | 3075.2  | 3674.1  | 4272.2  | 4870.3  | 5317.6  |
| 0.0    | 35°    | 693.8  | 1258.0 | 1823.1 | 2387.3  | 2951.5  | 3598.7  | 4246.0  | 4892.3  | 5539.6  | 6050.4  |
| 0.0    | 37.5°  | 776.8  | 1428.3 | 2078.9 | 2730.4  | 3381.0  | 4091.8  | 4802.5  | 5513.3  | 6224.1  | 6855.2  |
| 0.0    | 40°    | 870.0  | 1634.2 | 2397.5 | 3161.6  | 3924.9  | 4767.0  | 5608.2  | 6450.3  | 7291.5  | 8181.8  |
| 0.0    | 42.5°  | 1031.8 | 1975.6 | 2920.2 | 3863.9  | 4807.6  | 5921.6  | 7035.6  | 8148.8  | 9262.8  | 10533.6 |
| 0.0    | 45°    | 1336.0 | 2666.0 | 3996.9 | 5326.9  | 6657.0  | 8132.7  | 9609.3  | 11085.1 | 12560.8 | 14251.7 |
| 0.0    | 47.5°  | 2080.6 | 3910.5 | 5739.5 | 7569.4  | 9398.4  | 10991.9 | 12584.5 | 14178.0 | 15770.7 | 17454.8 |
| 0.0    | 50°    | 3183.6 | 5313.4 | 7443.1 | 9572.0  | 11701.8 | 13143.7 | 14584.7 | 16026.5 | 17467.5 | 19069.5 |
| 0.0    | 52.5°  | 3981.6 | 6200.3 | 8419.9 | 10638.6 | 12857.3 | 14158.5 | 15460.6 | 16761.9 | 18063.1 | 19560.0 |
| 0.0    | 55°    | 4041.8 | 6247.8 | 8454.6 | 10660.6 | 12866.6 | 14173.8 | 15481.0 | 16788.1 | 18095.3 | 19682.0 |
| 0.0    | 57.5°  | 3578.4 | 5766.6 | 7954.0 | 10142.2 | 12329.5 | 13818.0 | 15305.6 | 16794.1 | 18281.7 | 19997.2 |
| 0.0    | 60°    | 3043.8 | 5232.9 | 7421.1 | 9610.2  | 11798.4 | 13513.0 | 15228.5 | 16943.2 | 18657.8 | 20264.9 |
| 0.0    | 62.5°  | 2374.6 | 4626.3 | 6878.9 | 9130.7  | 11382.4 | 13123.3 | 14864.2 | 16604.3 | 18345.2 | 19550.7 |
| 0.0    | 65°    | 1769.7 | 3956.2 | 6142.7 | 8328.4  | 10514.9 | 11909.3 | 13303.8 | 14697.3 | 16091.8 | 16838.1 |
| 0.0    | 67.5°  | 1279.2 | 3165.0 | 5049.9 | 6935.7  | 8820.6  | 9818.6  | 10816.5 | 11813.6 | 12811.6 | 13382.5 |
|        | 70°    | 864.9  | 2171.3 | 3476.7 | 4783.1  | 6088.5  | 6908.6  | 7729.5  | 8549.5  | 9369.6  | 10140.5 |
|        | 72.5°  | 598.9  | 1332.6 | 2067.1 | 2800.7  | 3534.3  | 4359.5  | 5183.8  | 6008.9  | 6833.2  | 7649.0  |
|        | 75°    | 397.3  | 731.1  | 1065.7 | 1399.5  | 1733.3  | 2344.1  | 2955.7  | 3566.5  | 4177.3  | 4663.6  |
|        | 77.5°  | 282.1  | 382.1  | 482.9  | 582.8   | 682.8   | 797.2   | 912.4   | 1026.8  | 1141.1  | 1314.8  |
|        | 80°    | 133.9  | 146.6  | 159.3  | 171.1   | 183.8   | 225.3   | 266.9   | 308.4   | 349.9   | 393.9   |
|        | 82.5°  | 63.5   | 68.6   | 73.7   | 77.9    | 83.0    | 87.3    | 91.5    | 95.7    | 100.0   | 95.7    |
|        | 85°    | 16.9   | 16.9   | 17.8   | 17.8    | 17.8    | 17.8    | 17.8    | 17.8    | 17.8    | 16.9    |
|        | 87.5°  | 7.6    | 7.6    | 7.6    | 7.6     | 7.6     | 7.6     | 7.6     | 6.8     | 6.8     | 5.9     |
|        | 90°    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 49.1    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.9    | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 61.0    | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68.6    | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 78.8    | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.4    | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.4   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 353.3   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 916.6   | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1944.2  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2999.8  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4069.7  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4927.9  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5765.8  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6561.2  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7487.2  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9072.2  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 11804.3 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15942.7 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19139.0 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20671.5 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21056.9 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21269.6 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21712.6 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21871.1 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20757.1 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17585.3 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13954.4 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10910.5 |        |      |        |      |        |      |        |      |        |      |        |
| 8464.8  |        |      |        |      |        |      |        |      |        |      |        |
| 5149.9  |        |      |        |      |        |      |        |      |        |      |        |
| 1488.5  |        |      |        |      |        |      |        |      |        |      |        |
| 438.0   |        |      |        |      |        |      |        |      |        |      |        |
| 90.6    |        |      |        |      |        |      |        |      |        |      |        |
| 16.1    |        |      |        |      |        |      |        |      |        |      |        |
| 5.9     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    |
| 0.0  | 2.5°   | 55.1    | 54.2    | 53.4    | 52.5    | 51.7    | 50.0    | 50.0    | 49.1    | 49.1    |
| 0.0  | 5°     | 60.1    | 59.3    | 58.5    | 57.6    | 57.6    | 56.8    | 55.9    | 55.9    | 55.1    |
| 0.0  | 7.5°   | 68.6    | 67.8    | 66.9    | 66.1    | 66.1    | 65.2    | 65.2    | 64.4    | 64.4    |
| 0.0  | 10°    | 78.8    | 78.8    | 78.8    | 78.8    | 78.8    | 77.9    | 77.9    | 77.9    | 77.1    |
| 0.0  | 12.5°  | 99.1    | 100.0   | 101.7   | 103.4   | 105.9   | 105.9   | 105.9   | 105.0   | 105.0   |
| 0.0  | 15°    | 156.7   | 166.0   | 172.8   | 179.6   | 185.5   | 199.1   | 197.4   | 194.8   | 193.2   |
| 0.0  | 17.5°  | 396.5   | 438.8   | 461.7   | 483.7   | 506.6   | 569.3   | 559.1   | 549.0   | 539.6   |
| 0.0  | 20°    | 1027.6  | 1138.6  | 1212.3  | 1286.0  | 1360.5  | 1478.3  | 1449.5  | 1420.7  | 1391.9  |
| 0.0  | 22.5°  | 2198.4  | 2453.4  | 2564.3  | 2675.3  | 2785.5  | 2927.8  | 2835.4  | 2743.1  | 2651.6  |
| 0.0  | 25°    | 3330.2  | 3661.4  | 3848.6  | 4035.9  | 4222.2  | 4303.6  | 4183.3  | 4062.1  | 3941.8  |
| 0.0  | 27.5°  | 4444.2  | 4818.6  | 4983.8  | 5148.2  | 5313.4  | 5483.7  | 5334.6  | 5184.6  | 5035.5  |
| 0.0  | 30°    | 5337.1  | 5746.3  | 5925.0  | 6102.9  | 6281.7  | 6400.3  | 6246.1  | 6091.1  | 5936.9  |
| 0.0  | 32.5°  | 6213.1  | 6660.4  | 6856.0  | 7051.7  | 7246.6  | 7416.9  | 7227.1  | 7036.5  | 6846.7  |
| 0.0  | 35°    | 7071.2  | 7582.1  | 7851.5  | 8120.9  | 8390.2  | 8548.7  | 8323.3  | 8097.1  | 7871.8  |
| 0.0  | 37.5°  | 8118.3  | 8749.4  | 9051.0  | 9352.6  | 9654.2  | 9943.1  | 9694.9  | 9445.8  | 9197.6  |
| 0.0  | 40°    | 9962.6  | 10852.9 | 11315.5 | 11778.9 | 12241.4 | 12614.2 | 12300.7 | 11987.3 | 11673.8 |
| 0.0  | 42.5°  | 13075.0 | 14345.8 | 15010.8 | 15675.0 | 16340.0 | 16922.0 | 16592.4 | 16262.9 | 15933.3 |
| 0.0  | 45°    | 17633.6 | 19324.5 | 20135.2 | 20945.1 | 21755.9 | 22181.1 | 21706.7 | 21231.5 | 20757.1 |
| 0.0  | 47.5°  | 20822.3 | 22506.4 | 23228.2 | 23950.0 | 24671.8 | 25157.2 | 24576.9 | 23996.6 | 23417.1 |
| 0.0  | 50°    | 22272.6 | 23874.6 | 24598.9 | 25322.4 | 26046.7 | 26432.2 | 25762.1 | 25091.1 | 24421.0 |
| 0.0  | 52.5°  | 22553.0 | 24050.0 | 24914.1 | 25779.0 | 26643.1 | 27158.2 | 26366.9 | 25574.8 | 24783.6 |
| 0.0  | 55°    | 22856.3 | 24443.0 | 25445.2 | 26448.3 | 27450.4 | 28163.8 | 27269.2 | 26373.7 | 25479.1 |
| 0.0  | 57.5°  | 23427.3 | 25142.8 | 26142.4 | 27141.2 | 28140.9 | 28746.6 | 27849.5 | 26951.5 | 26054.3 |
| 0.0  | 60°    | 23478.1 | 25084.3 | 25943.4 | 26803.2 | 27662.2 | 28043.5 | 27185.3 | 26326.3 | 25468.1 |
| 0.0  | 62.5°  | 21962.6 | 23168.1 | 23764.5 | 24360.9 | 24957.3 | 25371.5 | 24476.1 | 23579.8 | 22684.3 |
| 0.0  | 65°    | 18331.6 | 19078.0 | 19553.2 | 20028.5 | 20503.8 | 20997.6 | 20177.6 | 19357.6 | 18537.5 |
| 0.0  | 67.5°  | 14525.4 | 15096.3 | 15722.4 | 16348.4 | 16974.5 | 17502.3 | 16845.7 | 16188.3 | 15531.8 |
|      | 70°    | 11681.5 | 12451.5 | 13155.5 | 13859.5 | 14563.5 | 14995.5 | 14336.4 | 13676.5 | 13017.4 |
|      | 72.5°  | 9280.6  | 10096.4 | 10684.4 | 11271.4 | 11859.4 | 11965.3 | 11480.7 | 10996.1 | 10512.4 |
|      | 75°    | 5635.3  | 6121.6  | 6133.4  | 6144.4  | 6156.3  | 6257.1  | 5855.6  | 5454.0  | 5053.3  |
|      | 77.5°  | 1662.1  | 1835.8  | 1979.0  | 2121.3  | 2264.5  | 2437.3  | 2289.9  | 2141.6  | 1994.2  |
|      | 80°    | 481.2   | 525.2   | 562.5   | 598.9   | 636.2   | 614.2   | 579.5   | 544.7   | 510.0   |
|      | 82.5°  | 86.4    | 81.3    | 80.5    | 79.6    | 79.6    | 75.4    | 68.6    | 61.8    | 55.1    |
|      | 85°    | 15.2    | 14.4    | 13.6    | 12.7    | 11.9    | 11.0    | 9.3     | 8.5     | 6.8     |
|      | 87.5°  | 5.1     | 4.2     | 3.4     | 2.5     | 2.5     | 0.8     | 0.8     | 0.8     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    | 49.1    |
| 0.0  | 0.0    | 2.5°   | 48.3    | 47.4    | 47.4    | 47.4    | 47.4    | 46.6    | 46.6    | 46.6    | 46.6    |
| 0.0  | 0.0    | 5°     | 53.4    | 53.4    | 52.5    | 52.5    | 51.7    | 51.7    | 50.8    | 50.8    | 50.0    |
| 0.0  | 0.0    | 7.5°   | 62.7    | 61.8    | 61.0    | 60.1    | 59.3    | 57.6    | 56.8    | 55.9    | 55.9    |
| 0.0  | 0.0    | 10°    | 75.4    | 73.7    | 72.9    | 71.2    | 70.3    | 68.6    | 66.9    | 65.2    | 63.5    |
| 0.0  | 0.0    | 12.5°  | 99.1    | 95.7    | 93.2    | 89.8    | 86.4    | 83.9    | 80.5    | 77.9    | 74.5    |
| 0.0  | 0.0    | 15°    | 172.0   | 163.5   | 154.2   | 143.2   | 131.3   | 120.3   | 108.4   | 101.7   | 94.0    |
| 0.0  | 0.0    | 17.5°  | 439.7   | 395.6   | 350.7   | 314.3   | 277.9   | 242.3   | 205.9   | 179.6   | 153.3   |
| 0.0  | 0.0    | 20°    | 1119.1  | 997.1   | 875.1   | 754.8   | 633.7   | 513.4   | 392.2   | 331.2   | 270.2   |
| 0.0  | 0.0    | 22.5°  | 2106.0  | 1879.8  | 1652.8  | 1433.4  | 1213.1  | 993.7   | 774.3   | 636.2   | 499.0   |
| 0.0  | 0.0    | 25°    | 3250.5  | 2965.9  | 2681.3  | 2320.4  | 1958.6  | 1597.7  | 1236.9  | 1012.4  | 787.9   |
| 0.0  | 0.0    | 27.5°  | 4229.9  | 3902.0  | 3574.2  | 3135.3  | 2696.5  | 2257.7  | 1818.8  | 1484.2  | 1150.4  |
| 0.0  | 0.0    | 30°    | 5077.9  | 4725.4  | 4373.0  | 3862.2  | 3351.4  | 2840.5  | 2329.7  | 1911.2  | 1492.7  |
| 0.0  | 0.0    | 32.5°  | 5813.2  | 5391.3  | 4969.4  | 4442.5  | 3915.6  | 3388.6  | 2861.7  | 2348.3  | 1834.9  |
| 0.0  | 0.0    | 35°    | 6661.2  | 6169.0  | 5676.0  | 5091.4  | 4506.0  | 3921.5  | 3337.0  | 2757.5  | 2177.2  |
| 0.0  | 0.0    | 37.5°  | 7738.8  | 7134.8  | 6529.9  | 5878.4  | 5227.0  | 4576.3  | 3924.9  | 3262.4  | 2599.9  |
| 0.0  | 0.0    | 40°    | 9801.6  | 9022.2  | 8242.8  | 7415.2  | 6586.7  | 5759.0  | 4931.3  | 4118.0  | 3304.8  |
| 0.0  | 0.0    | 42.5°  | 13497.8 | 12444.7 | 11391.7 | 10290.4 | 9188.3  | 8087.0  | 6984.8  | 5837.8  | 4689.9  |
| 0.0  | 0.0    | 45°    | 17669.2 | 16362.8 | 15055.7 | 13819.7 | 12582.8 | 11346.8 | 10110.8 | 8536.8  | 6962.8  |
| 0.0  | 0.0    | 47.5°  | 20014.9 | 18604.4 | 17193.9 | 16024.0 | 14854.1 | 13684.1 | 12514.2 | 10817.4 | 9120.5  |
| 0.0  | 0.0    | 50°    | 20878.2 | 19442.3 | 18006.3 | 16929.6 | 15852.0 | 14775.3 | 13697.7 | 11998.3 | 10298.0 |
| 0.0  | 0.0    | 52.5°  | 21062.0 | 19597.3 | 18132.6 | 17049.0 | 15965.5 | 14882.9 | 13799.4 | 12111.0 | 10422.6 |
| 0.0  | 0.0    | 55°    | 21439.9 | 19868.4 | 18296.1 | 17060.9 | 15825.8 | 14590.6 | 13355.4 | 11639.9 | 9924.5  |
| 0.0  | 0.0    | 57.5°  | 21933.8 | 20322.5 | 18711.2 | 17304.0 | 15896.9 | 14490.6 | 13083.5 | 11207.9 | 9332.3  |
| 0.0  | 0.0    | 60°    | 21804.1 | 20402.1 | 18999.2 | 17492.1 | 15984.2 | 14477.1 | 12969.1 | 10906.3 | 8842.6  |
| 0.0  | 0.0    | 62.5°  | 19554.1 | 18437.5 | 17320.1 | 16080.7 | 14840.5 | 13601.1 | 12361.7 | 10237.9 | 8114.1  |
| 0.0  | 0.0    | 65°    | 16086.7 | 15271.7 | 14456.7 | 13459.6 | 12461.7 | 11464.6 | 10467.5 | 8563.1  | 6659.5  |
| 0.0  | 0.0    | 67.5°  | 13037.8 | 12119.4 | 11200.3 | 10405.6 | 9610.2  | 8815.5  | 8020.0  | 6521.4  | 5022.8  |
|      |        | 70°    | 10358.2 | 9359.4  | 8359.8  | 7583.8  | 6806.9  | 6030.9  | 5254.9  | 4258.7  | 3263.3  |
|      |        | 72.5°  | 8225.9  | 7325.4  | 6424.8  | 5597.2  | 4768.7  | 3941.0  | 3112.5  | 2523.7  | 1934.9  |
|      |        | 75°    | 3931.7  | 3571.6  | 3211.6  | 2778.7  | 2345.8  | 1912.9  | 1480.0  | 1223.3  | 967.5   |
|      |        | 77.5°  | 1457.1  | 1263.1  | 1068.3  | 892.1   | 715.8   | 540.5   | 364.3   | 333.8   | 303.3   |
|      |        | 80°    | 377.0   | 328.7   | 279.6   | 244.8   | 209.2   | 174.5   | 139.8   | 126.2   | 113.5   |
|      |        | 82.5°  | 43.2    | 39.8    | 37.3    | 35.6    | 33.0    | 31.3    | 28.8    | 26.3    | 23.7    |
|      |        | 85°    | 2.5     | 1.7     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 49.1   | 49.1   |
| 0.0    | 0.0  | 2.5°   | 45.7   | 44.9   |
| 0.0    | 0.0  | 5°     | 48.3   | 47.4   |
| 0.0    | 0.0  | 7.5°   | 53.4   | 51.7   |
| 0.0    | 0.0  | 10°    | 58.5   | 56.8   |
| 0.0    | 0.0  | 12.5°  | 66.1   | 63.5   |
| 0.0    | 0.0  | 15°    | 74.5   | 69.5   |
| 0.0    | 0.0  | 17.5°  | 89.0   | 77.9   |
| 0.0    | 0.0  | 20°    | 120.3  | 92.3   |
| 0.0    | 0.0  | 22.5°  | 169.4  | 115.2  |
| 0.0    | 0.0  | 25°    | 249.1  | 159.3  |
| 0.0    | 0.0  | 27.5°  | 346.5  | 211.8  |
| 0.0    | 0.0  | 30°    | 460.9  | 265.2  |
| 0.0    | 0.0  | 32.5°  | 561.7  | 316.0  |
| 0.0    | 0.0  | 35°    | 693.0  | 367.7  |
| 0.0    | 0.0  | 37.5°  | 854.8  | 433.7  |
| 0.0    | 0.0  | 40°    | 1105.5 | 533.7  |
| 0.0    | 0.0  | 42.5°  | 1557.1 | 718.4  |
| 0.0    | 0.0  | 45°    | 2528.8 | 1241.9 |
| 0.0    | 0.0  | 47.5°  | 3891.0 | 2054.4 |
| 0.0    | 0.0  | 50°    | 4760.2 | 2622.0 |
| 0.0    | 0.0  | 52.5°  | 4831.3 | 2617.7 |
| 0.0    | 0.0  | 55°    | 4410.3 | 2327.1 |
| 0.0    | 0.0  | 57.5°  | 3763.1 | 1945.1 |
| 0.0    | 0.0  | 60°    | 3127.7 | 1538.4 |
| 0.0    | 0.0  | 62.5°  | 2464.4 | 1062.3 |
| 0.0    | 0.0  | 65°    | 1801.1 | 751.4  |
| 0.0    | 0.0  | 67.5°  | 1293.6 | 561.7  |
|        |      | 70°    | 850.5  | 430.4  |
|        |      | 72.5°  | 554.0  | 350.7  |
|        |      | 75°    | 372.7  | 290.6  |
|        |      | 77.5°  | 217.7  | 193.2  |
|        |      | 80°    | 77.1   | 67.8   |
|        |      | 82.5°  | 14.4   | 10.2   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1064969

CATALOG NUMBER: GLAN-SA5A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-14

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-930-U-5WQ

Data in this report applies to families of products including GSS-SB1A-930-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-14  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-930-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI 3000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 2993  
 CIE  $u'$ : 0.2501  
 CIE  $v'$ : 0.5245  
 Duv: 0.0021  
 CIE x: 0.4406  
 CIE y: 0.4107  
 CIE z: 0.1487  
 Peak Wavelength (nm): 621  
 Dominant Wavelength (nm): 582  
 Purity: 55.53327  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 98.5

CRI (Ra): 92.4  
 R1: 92.2  
 R2: 95.2  
 R3: 97.0  
 R4: 93.1  
 R5: 91.7  
 R6: 94.2  
 R7: 93.3  
 R8: 82.3  
 R9: 58.2  
 R10: 87.7  
 R11: 93.5  
 R12: 81.7  
 R13: 92.9  
 R14: 97.6  
 R15: 88.1



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-14


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-14

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle


REPORT NUMBER: SP1-2407-184-14

**Photopic Flux vs. Wavelength**

**Photopic Lumens: NR**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 310                                  | NR                             | 620               | 998                                  | NR                             | 750               | 77                                   | NR                             | 880               | 2                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 347                                  | NR                             | 625               | 993                                  | NR                             | 755               | 66                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 379                                  | NR                             | 630               | 983                                  | NR                             | 760               | 56                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 412                                  | NR                             | 635               | 960                                  | NR                             | 765               | 48                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 442                                  | NR                             | 640               | 930                                  | NR                             | 770               | 41                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 475                                  | NR                             | 645               | 889                                  | NR                             | 775               | 35                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 506                                  | NR                             | 650               | 846                                  | NR                             | 780               | 30                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 535                                  | NR                             | 655               | 794                                  | NR                             | 785               | 26                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 565                                  | NR                             | 660               | 740                                  | NR                             | 790               | 22                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 592                                  | NR                             | 665               | 684                                  | NR                             | 795               | 19                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 615                                  | NR                             | 670               | 624                                  | NR                             | 800               | 16                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 638                                  | NR                             | 675               | 567                                  | NR                             | 805               | 14                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 20                                   | NR                             | 550               | 658                                  | NR                             | 680               | 513                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 38                                   | NR                             | 555               | 678                                  | NR                             | 685               | 459                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 70                                   | NR                             | 560               | 695                                  | NR                             | 690               | 412                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 136                                  | NR                             | 565               | 716                                  | NR                             | 695               | 363                                  | NR                             | 825               | 8                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 262                                  | NR                             | 570               | 740                                  | NR                             | 700               | 320                                  | NR                             | 830               | 7                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 424                                  | NR                             | 575               | 765                                  | NR                             | 705               | 281                                  | NR                             | 835               | 6                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 406                                  | NR                             | 580               | 796                                  | NR                             | 710               | 245                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 313                                  | NR                             | 585               | 827                                  | NR                             | 715               | 215                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 294                                  | NR                             | 590               | 861                                  | NR                             | 720               | 188                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 250                                  | NR                             | 595               | 894                                  | NR                             | 725               | 162                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 217                                  | NR                             | 600               | 927                                  | NR                             | 730               | 140                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 228                                  | NR                             | 605               | 954                                  | NR                             | 735               | 121                                  | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 249                                  | NR                             | 610               | 976                                  | NR                             | 740               | 104                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 276                                  | NR                             | 615               | 992                                  | NR                             | 745               | 89                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-14

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR


S/P: 1.39

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 310                      | NR            | 620    | 998                      | NR            | 750    | 77                       | NR            | 880    | 2                        | NR            |
| 365    | 0                        | NR            | 495    | 347                      | NR            | 625    | 993                      | NR            | 755    | 66                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 379                      | NR            | 630    | 983                      | NR            | 760    | 56                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 412                      | NR            | 635    | 960                      | NR            | 765    | 48                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 442                      | NR            | 640    | 930                      | NR            | 770    | 41                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 475                      | NR            | 645    | 889                      | NR            | 775    | 35                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 506                      | NR            | 650    | 846                      | NR            | 780    | 30                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 535                      | NR            | 655    | 794                      | NR            | 785    | 26                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 565                      | NR            | 660    | 740                      | NR            | 790    | 22                       | NR            | 920    | 1                        | NR            |
| 405    | 2                        | NR            | 535    | 592                      | NR            | 665    | 684                      | NR            | 795    | 19                       | NR            | 925    | 1                        | NR            |
| 410    | 6                        | NR            | 540    | 615                      | NR            | 670    | 624                      | NR            | 800    | 16                       | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 638                      | NR            | 675    | 567                      | NR            | 805    | 14                       | NR            | 935    | 0                        | NR            |
| 420    | 20                       | NR            | 550    | 658                      | NR            | 680    | 513                      | NR            | 810    | 12                       | NR            | 940    | 0                        | NR            |
| 425    | 38                       | NR            | 555    | 678                      | NR            | 685    | 459                      | NR            | 815    | 10                       | NR            | 945    | 0                        | NR            |
| 430    | 70                       | NR            | 560    | 695                      | NR            | 690    | 412                      | NR            | 820    | 9                        | NR            | 950    | 0                        | NR            |
| 435    | 136                      | NR            | 565    | 716                      | NR            | 695    | 363                      | NR            | 825    | 8                        | NR            | 955    | 0                        | NR            |
| 440    | 262                      | NR            | 570    | 740                      | NR            | 700    | 320                      | NR            | 830    | 7                        | NR            | 960    | 0                        | NR            |
| 445    | 424                      | NR            | 575    | 765                      | NR            | 705    | 281                      | NR            | 835    | 6                        | NR            | 965    | 0                        | NR            |
| 450    | 406                      | NR            | 580    | 796                      | NR            | 710    | 245                      | NR            | 840    | 5                        | NR            | 970    | 0                        | NR            |
| 455    | 313                      | NR            | 585    | 827                      | NR            | 715    | 215                      | NR            | 845    | 4                        | NR            | 975    | 0                        | NR            |
| 460    | 294                      | NR            | 590    | 861                      | NR            | 720    | 188                      | NR            | 850    | 4                        | NR            | 980    | 0                        | NR            |
| 465    | 250                      | NR            | 595    | 894                      | NR            | 725    | 162                      | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 217                      | NR            | 600    | 927                      | NR            | 730    | 140                      | NR            | 860    | 3                        | NR            | 990    | 0                        | NR            |
| 475    | 228                      | NR            | 605    | 954                      | NR            | 735    | 121                      | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 249                      | NR            | 610    | 976                      | NR            | 740    | 104                      | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 276                      | NR            | 615    | 992                      | NR            | 745    | 89                       | NR            | 875    | 2                        | NR            |        |                          |               |



REPORT NUMBER: SP1-2407-184-14

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.69


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 310                                    | NR                             | 620               | 998                                    | NR                             | 750               | 77                                     | NR                             | 880               | 2                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 347                                    | NR                             | 625               | 993                                    | NR                             | 755               | 66                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 379                                    | NR                             | 630               | 983                                    | NR                             | 760               | 56                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 412                                    | NR                             | 635               | 960                                    | NR                             | 765               | 48                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 442                                    | NR                             | 640               | 930                                    | NR                             | 770               | 41                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 475                                    | NR                             | 645               | 889                                    | NR                             | 775               | 35                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 506                                    | NR                             | 650               | 846                                    | NR                             | 780               | 30                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 535                                    | NR                             | 655               | 794                                    | NR                             | 785               | 26                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 1                                      | NR                             | 530               | 565                                    | NR                             | 660               | 740                                    | NR                             | 790               | 22                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 592                                    | NR                             | 665               | 684                                    | NR                             | 795               | 19                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 6                                      | NR                             | 540               | 615                                    | NR                             | 670               | 624                                    | NR                             | 800               | 16                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 638                                    | NR                             | 675               | 567                                    | NR                             | 805               | 14                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 20                                     | NR                             | 550               | 658                                    | NR                             | 680               | 513                                    | NR                             | 810               | 12                                     | NR                             | 940               | 0                                      | NR                             |
| 425               | 38                                     | NR                             | 555               | 678                                    | NR                             | 685               | 459                                    | NR                             | 815               | 10                                     | NR                             | 945               | 0                                      | NR                             |
| 430               | 70                                     | NR                             | 560               | 695                                    | NR                             | 690               | 412                                    | NR                             | 820               | 9                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 136                                    | NR                             | 565               | 716                                    | NR                             | 695               | 363                                    | NR                             | 825               | 8                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 262                                    | NR                             | 570               | 740                                    | NR                             | 700               | 320                                    | NR                             | 830               | 7                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 424                                    | NR                             | 575               | 765                                    | NR                             | 705               | 281                                    | NR                             | 835               | 6                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 406                                    | NR                             | 580               | 796                                    | NR                             | 710               | 245                                    | NR                             | 840               | 5                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 313                                    | NR                             | 585               | 827                                    | NR                             | 715               | 215                                    | NR                             | 845               | 4                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 294                                    | NR                             | 590               | 861                                    | NR                             | 720               | 188                                    | NR                             | 850               | 4                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 250                                    | NR                             | 595               | 894                                    | NR                             | 725               | 162                                    | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 217                                    | NR                             | 600               | 927                                    | NR                             | 730               | 140                                    | NR                             | 860               | 3                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 228                                    | NR                             | 605               | 954                                    | NR                             | 735               | 121                                    | NR                             | 865               | 2                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 249                                    | NR                             | 610               | 976                                    | NR                             | 740               | 104                                    | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 276                                    | NR                             | 615               | 992                                    | NR                             | 745               | 89                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-14





TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 98.5$   
 $CIE R_a = 92.4$   
 $R_9 = 58.2$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 98 | CES76 = 90 |
| CES02 = 63 | CES27 = 94 | CES52 = 98 | CES77 = 91 |
| CES03 = 32 | CES28 = 97 | CES53 = 96 | CES78 = 88 |
| CES04 = 70 | CES29 = 95 | CES54 = 95 | CES79 = 94 |
| CES05 = 51 | CES30 = 97 | CES55 = 94 | CES80 = 94 |
| CES06 = 51 | CES31 = 96 | CES56 = 94 | CES81 = 84 |
| CES07 = 43 | CES32 = 91 | CES57 = 94 | CES82 = 97 |
| CES08 = 42 | CES33 = 98 | CES58 = 94 | CES83 = 97 |
| CES09 = 29 | CES34 = 96 | CES59 = 97 | CES84 = 95 |
| CES10 = 76 | CES35 = 97 | CES60 = 95 | CES85 = 85 |
| CES11 = 59 | CES36 = 87 | CES61 = 94 | CES86 = 84 |
| CES12 = 65 | CES37 = 95 | CES62 = 92 | CES87 = 92 |
| CES13 = 44 | CES38 = 93 | CES63 = 93 | CES88 = 95 |
| CES14 = 74 | CES39 = 99 | CES64 = 92 | CES89 = 86 |
| CES15 = 72 | CES40 = 98 | CES65 = 89 | CES90 = 96 |
| CES16 = 48 | CES41 = 98 | CES66 = 90 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 89 | CES92 = 81 |
| CES18 = 57 | CES43 = 97 | CES68 = 90 | CES93 = 89 |
| CES19 = 72 | CES44 = 99 | CES69 = 92 | CES94 = 80 |
| CES20 = 67 | CES45 = 99 | CES70 = 89 | CES95 = 86 |
| CES21 = 86 | CES46 = 96 | CES71 = 87 | CES96 = 92 |
| CES22 = 79 | CES47 = 95 | CES72 = 95 | CES97 = 96 |
| CES23 = 92 | CES48 = 93 | CES73 = 85 | CES98 = 94 |
| CES24 = 91 | CES49 = 97 | CES74 = 93 | CES99 = 91 |
| CES25 = 72 | CES50 = 98 | CES75 = 88 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)