Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063218

Luminaire Tested: **GLAN-SA8B-940-U-T3BC**

Issue Date: 08/07/2025

Report Generated By 670347003

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1063218
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	08/07/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	GLAN-SA8B-940-U-T3BC
Description:	GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 8xLight Square PACKAGE 90CRI 4000K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source:	(112) 4000K CCT, 90 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	27401.9 lumens
Efficiency:	N/A
Efficacy:	96.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B0 - U0 - G4

Input Watts (W):	282.8
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.97
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1063218
CATALOG NUMBER: GLAN-SA8B-940-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination



Based on 15 foot mounting height. Maximum calculated value = 30.7 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1063218
CATALOG NUMBER: GLAN-SA8B-940-U-T3BC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1063218
CATALOG NUMBER: GLAN-SA8B-940-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	100.0	0.0	100.0
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	27301.9	0.0	27301.9
	% Fixture	99.6	0.0	99.6
Total	Lumens	27401.9	0.0	27401.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.3	0.1
10°-20°	315.0	1.1
20°-30°	1135.3	4.1
30°-40°	2597.5	9.5
40°-50°	4381.0	16.0
50°-60°	7229.7	26.4
60°-70°	8080.2	29.5
70°-80°	3336.2	12.2
80°-90°	300.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	27401.9	100.0
0°-180°	27401.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1063218
CATALOG NUMBER: GLAN-SA8B-940-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1450.4	5.3			
FM	(30°-60°)	14184.3	51.8			
FH	(60°-80°)	11370.5	41.5			G4/12000
FVH	(80°-90°)	296.6	1.1			G3/500
BL	(0°-30°)	26.1	0.1	B0/110		
BM	(30°-60°)	24.0	0.1	B0/220		
BH	(60°-80°)	45.8	0.2	B0/110		G0/110
BVH	(80°-90°)	4.1	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1063218
CATALOG NUMBER: GLAN-SA8B-940-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2
2.5°	215.0	222.2	215.0	215.0	215.0	207.8	207.8	200.7	200.7	193.5	186.3
5°	315.3	315.3	293.8	279.5	265.2	258.0	250.8	236.5	222.2	207.8	193.5
7.5°	702.3	702.3	637.8	551.8	437.2	372.7	358.3	293.8	250.8	222.2	193.5
10°	1677.0	1677.0	1533.7	1297.2	1003.3	745.3	666.5	422.8	301.0	236.5	200.7
12.5°	2787.9	2823.7	2644.5	2343.5	1906.4	1454.8	1297.2	774.0	401.3	258.0	200.7
15°	3784.0	3698.0	3647.9	3361.2	2945.5	2408.0	2207.4	1304.3	580.5	293.8	200.7
17.5°	4457.7	4457.7	4386.0	4192.5	3812.7	3339.7	3174.9	2107.0	938.8	336.8	207.8
20°	5246.0	5246.0	5117.0	4980.9	4644.0	4242.7	4085.0	2995.7	1454.8	430.0	207.8
22.5°	6199.2	6213.6	6070.2	5826.6	5504.0	5059.7	4923.5	3819.9	2107.0	573.3	215.0
25°	7360.2	7374.6	7166.7	6937.4	6442.9	5962.7	5754.9	4765.9	2902.5	802.7	215.0
27.5°	8643.1	8743.4	8435.2	8041.1	7517.9	6915.9	6758.2	5618.7	3690.9	1132.3	229.3
30°	10241.3	10241.3	9832.8	9280.9	8714.7	7969.4	7768.7	6514.6	4529.4	1569.5	243.7
32.5°	11617.3	11509.8	10986.6	10406.1	9804.1	9108.9	8893.9	7453.4	5389.4	2114.2	272.3
35°	12670.8	12577.6	11932.6	11309.1	10785.9	10148.1	9890.1	8471.1	6299.6	2730.5	315.3
37.5°	13573.8	13538.0	12663.6	11882.4	11538.4	10979.4	10750.1	9431.4	7195.4	3397.0	365.5
40°	14562.8	14448.1	13516.5	12548.9	12032.9	11581.4	11373.6	10205.4	8055.4	4178.2	437.2
42.5°	15408.5	15272.3	14433.8	13487.8	12606.3	11997.1	11796.4	10857.6	8893.9	4959.4	530.3
45°	16347.3	16275.6	15430.0	14713.3	13538.0	12563.3	12298.1	11380.8	9660.8	5891.1	652.2
47.5°	17759.2	17630.2	16841.8	16254.1	14892.5	13423.3	13043.4	11918.3	10398.9	6808.4	838.5
50°	19400.3	19314.3	18848.5	18382.7	17028.1	14892.5	14441.0	12692.3	11223.1	7897.7	1082.2
52.5°	20740.5	20726.2	20783.5	20790.7	19765.8	17365.0	16691.3	13939.3	12169.1	8972.7	1426.2
55°	20711.8	20776.3	21407.0	22130.9	22209.7	20740.5	20088.3	16039.1	13401.8	10298.6	1906.4
57.5°	19937.8	19887.7	20554.2	21643.5	22410.4	22568.0	22460.5	19300.0	15258.0	11896.8	2644.5
58°	19687.0	19644.0	20274.7	21385.5	22267.0	22689.9	22582.4	20038.2	15673.6	12126.1	2845.2
60°	18776.8	18784.0	19156.7	20167.2	21048.7	22052.0	22152.4	22145.2	17744.8	13659.8	3855.7
62.5°	17572.8	17515.5	17859.5	18683.7	19457.7	20131.3	20303.3	22288.5	20776.3	15609.1	5783.6
65°	15910.1	15824.1	16189.6	17121.3	17952.7	18389.8	18397.0	20367.8	22202.5	17701.8	8535.6
67.5°	12821.3	12749.6	13480.6	14677.5	15960.3	16533.6	16791.6	17673.2	20998.5	19120.8	10112.3
70°	7854.7	8005.2	9022.9	10900.6	13093.6	14147.1	14534.1	14806.5	17881.0	18905.8	8456.7
72.5°	3626.4	3447.2	4314.4	5625.9	8127.1	10470.6	10871.9	11939.8	14175.8	16411.8	6306.7
75°	1691.3	1626.8	1827.5	2458.2	3683.7	5654.5	6385.6	9531.8	10871.9	11416.6	4550.9
77.5°	867.2	874.3	1039.2	1118.0	1519.3	2615.9	3002.9	6270.9	7969.4	6371.2	3053.0
80°	379.8	394.2	401.3	437.2	616.3	1010.5	1139.5	2909.7	5446.7	3246.5	1669.8
82.5°	243.7	250.8	250.8	250.8	293.8	401.3	458.7	1168.2	2716.2	1612.5	516.0
85°	129.0	129.0	143.3	179.2	207.8	243.7	258.0	372.7	895.8	480.2	121.8
87.5°	71.7	78.8	86.0	107.5	136.2	164.8	179.2	258.0	344.0	329.7	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1063218
CATALOG NUMBER: GLAN-SA8B-940-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2
2.5°	186.3	179.2	172.0	164.8	157.7	150.5	150.5	150.5	150.5	150.5	150.5
5°	179.2	172.0	164.8	150.5	136.2	129.0	121.8	114.7	114.7	114.7	114.7
7.5°	179.2	172.0	150.5	136.2	121.8	107.5	93.2	93.2	93.2	93.2	93.2
10°	179.2	164.8	143.3	121.8	100.3	86.0	78.8	71.7	71.7	71.7	71.7
12.5°	179.2	157.7	136.2	107.5	86.0	71.7	64.5	57.3	57.3	57.3	57.3
15°	179.2	157.7	129.0	100.3	78.8	57.3	50.2	43.0	43.0	43.0	43.0
17.5°	172.0	150.5	121.8	86.0	64.5	43.0	35.8	28.7	28.7	35.8	35.8
20°	164.8	143.3	107.5	71.7	50.2	35.8	21.5	21.5	21.5	21.5	21.5
22.5°	164.8	143.3	100.3	64.5	43.0	21.5	14.3	14.3	14.3	14.3	21.5
25°	164.8	136.2	86.0	50.2	28.7	14.3	7.2	7.2	7.2	7.2	7.2
27.5°	164.8	136.2	78.8	43.0	21.5	14.3	7.2	0.0	0.0	0.0	0.0
30°	157.7	129.0	71.7	35.8	14.3	7.2	0.0	0.0	0.0	0.0	0.0
32.5°	157.7	121.8	57.3	28.7	14.3	7.2	0.0	0.0	0.0	0.0	0.0
35°	164.8	114.7	50.2	21.5	7.2	0.0	0.0	0.0	0.0	0.0	7.2
37.5°	172.0	107.5	43.0	14.3	7.2	0.0	0.0	0.0	0.0	0.0	0.0
40°	179.2	100.3	43.0	14.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	193.5	100.3	35.8	14.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	207.8	100.3	28.7	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	236.5	107.5	28.7	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	258.0	114.7	21.5	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	286.7	107.5	21.5	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	322.5	107.5	21.5	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	351.2	100.3	21.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	*365.5*	*93.2*	*14.3*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*
60°	437.2	86.0	14.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	680.8	71.7	14.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1383.2	64.5	14.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2580.0	57.3	14.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2888.2	64.5	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1820.3	50.2	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	960.3	50.2	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	480.2	50.2	7.2	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	222.2	35.8	7.2	7.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	93.2	21.5	14.3	7.2	7.2	0.0	0.0	0.0	0.0	0.0	0.0
85°	43.0	21.5	14.3	14.3	7.2	7.2	0.0	0.0	0.0	0.0	0.0
87.5°	21.5	21.5	21.5	14.3	14.3	7.2	7.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-16

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-940-U-5WQ

Data in this report applies to families of products including GSS-SB1A-940-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-16
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-940-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3856
CIE u':	0.2261
CIE v':	0.5084
Duv:	0.0032
CIE x:	0.3896
CIE y:	0.3894
CIE z:	0.2211
Peak Wavelength (nm):	614
Dominant Wavelength (nm):	578
Purity:	33.77304
Rf:	91.8
Rg:	98.4

CRI (Ra):	92.1
R1:	91.8
R2:	94.1
R3:	95.3
R4:	92.8
R5:	91.0
R6:	91.6
R7:	95.0
R8:	85.2
R9:	60.7
R10:	85.2
R11:	92.4
R12:	74.5
R13:	92.3
R14:	97.0
R15:	88.5



Test Conditions

Stabilization Time:	23M
Operation Time:	1H 23M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-16

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-16

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3856K
CIE x = 0.3896
CIE y = 0.3894
Duv = 0.0032

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-16

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR **S/P: 1.72**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.52**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

TM-30-18

Summary

R_f = 91.8
R_g = 98.4
CIE R_a = 92.1
R_9 = 60.7

Spectral Power Distribution Comparison



Color Vector Graphics









REPORT NUMBER: SP1-2407-184-16

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 96	CES76 = 87
CES02 = 62	CES27 = 91	CES52 = 98	CES77 = 90
CES03 = 31	CES28 = 96	CES53 = 95	CES78 = 84
CES04 = 69	CES29 = 96	CES54 = 94	CES79 = 96
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 94
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 92	CES57 = 92	CES82 = 97
CES08 = 41	CES33 = 99	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 94
CES10 = 74	CES35 = 96	CES60 = 93	CES85 = 85
CES11 = 57	CES36 = 82	CES61 = 92	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 87	CES87 = 92
CES13 = 43	CES38 = 88	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 89	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 88	CES90 = 96
CES16 = 47	CES41 = 97	CES66 = 87	CES91 = 74
CES17 = 49	CES42 = 96	CES67 = 86	CES92 = 80
CES18 = 56	CES43 = 96	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 82
CES20 = 66	CES45 = 98	CES70 = 86	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 81	CES96 = 92
CES22 = 78	CES47 = 97	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 91	CES73 = 81	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 93	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 83	



REPORT NUMBER: SP1-2407-184-16

TM-30-18

Color Rendition by Hue-Angle Bin







REPORT NUMBER: SP1-2407-184-16

TM-30-18

Measure Comparisons





(END OF REPORT)