

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065667

Luminaire Tested: **GLAN-SA8C-940-U-LBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065667  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA8C-940-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 8xLight Square PACKAGE  
90CRI 4000K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (112) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 29419.8 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4


Input Watts (W): 372.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1065667

CATALOG NUMBER: GLAN-SA8C-940-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 51.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065667  
CATALOG NUMBER: GLAN-SA8C-940-U-LBC

## Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P1065667

CATALOG NUMBER: GLAN-SA8C-940-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 200.9    | 0.0    | 200.9   |
|                    | % Fixture | 0.7      | 0.0    | 0.7     |
| <b>Street Side</b> | Lumens    | 29218.9  | 0.0    | 29218.9 |
|                    | % Fixture | 99.3     | 0.0    | 99.3    |
| <b>Total</b>       | Lumens    | 29419.8  | 0.0    | 29419.8 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 11.5    | 0.0       |
| 10°-20°   | 64.5    | 0.2       |
| 20°-30°   | 697.0   | 2.4       |
| 30°-40°   | 2061.1  | 7.0       |
| 40°-50°   | 6143.3  | 20.9      |
| 50°-60°   | 9748.0  | 33.1      |
| 60°-70°   | 8131.0  | 27.6      |
| 70°-80°   | 2507.7  | 8.5       |
| 80°-90°   | 55.7    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 29419.8 | 100.0     |
| 0°-180°   | 29419.8 | 100.0     |



REPORT NUMBER: P1065667


CATALOG NUMBER: GLAN-SA8C-940-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 753.3   | 2.6       |                         |      |          |
| FM   | (30°-60°)   | 17842.5 | 60.6      |                         |      |          |
| FH   | (60°-80°)   | 10570.1 | 35.9      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 53.0    | 0.2       |                         |      | G1/100   |
| BL   | (0°-30°)    | 19.7    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 109.9   | 0.4       | B0/220                  |      |          |
| BH   | (60°-80°)   | 68.6    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 2.7     | 0.0       |                         |      | G0/10    |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1065667

CATALOG NUMBER: GLAN-SA8C-940-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°      | 15°     | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°     |
|-------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 128.9  | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   |
| 2.5°  | 166.7  | 166.7   | 160.0   | 151.1   | 142.2   | 133.3   | 131.1   | 126.7   | 124.5   | 122.2   |
| 5°    | 173.3  | 173.3   | 171.1   | 164.5   | 155.6   | 148.9   | 148.9   | 142.2   | 137.8   | 133.3   |
| 7.5°  | 177.8  | 180.0   | 184.5   | 182.2   | 177.8   | 171.1   | 171.1   | 166.7   | 160.0   | 148.9   |
| 10°   | 184.5  | 191.1   | 200.0   | 204.5   | 206.7   | 206.7   | 204.5   | 202.2   | 191.1   | 175.6   |
| 12.5° | 191.1  | 204.5   | 226.7   | 248.9   | 262.2   | 280.0   | 277.8   | 273.4   | 244.5   | 211.1   |
| 15°   | 204.5  | 224.5   | 271.1   | 335.6   | 435.6   | 497.8   | 522.3   | 500.0   | 404.5   | 284.5   |
| 17.5° | 220.0  | 253.4   | 393.4   | 702.3   | 1151.2  | 1364.6  | 1493.5  | 1389.0  | 920.1   | 540.0   |
| 20°   | 235.6  | 308.9   | 731.2   | 1820.2  | 2986.9  | 3684.8  | 3878.1  | 3575.9  | 2295.8  | 1029.0  |
| 22.5° | 262.2  | 433.4   | 1482.4  | 3762.6  | 6436.1  | 7482.9  | 7680.7  | 6713.9  | 4335.9  | 2031.3  |
| 25°   | 317.8  | 628.9   | 2555.8  | 6131.7  | 9605.3  | 11372.1 | 11289.9 | 10023.1 | 7034.0  | 3244.7  |
| 27.5° | 397.8  | 915.6   | 3864.8  | 8711.9  | 12641.1 | 14199.0 | 14385.7 | 12818.9 | 9376.4  | 4771.5  |
| 30°   | 513.4  | 1269.0  | 5269.4  | 10778.7 | 15074.7 | 16759.3 | 16790.4 | 15170.2 | 11472.1 | 6111.6  |
| 32.5° | 624.5  | 1602.4  | 6498.3  | 12776.7 | 17472.6 | 19319.5 | 19457.3 | 17463.8 | 13036.7 | 7507.3  |
| 35°   | 709.0  | 1820.2  | 7742.9  | 14532.4 | 19890.6 | 22435.3 | 22426.4 | 20059.5 | 14890.2 | 8754.1  |
| 37.5° | 715.6  | 2038.0  | 8869.7  | 16328.1 | 22953.1 | 25802.3 | 26084.5 | 23475.4 | 17130.4 | 10296.5 |
| 40°   | 700.1  | 2282.4  | 10296.5 | 19128.3 | 28471.4 | 32842.9 | 33091.8 | 29802.6 | 21624.1 | 12936.7 |
| 42.5° | 717.8  | 2706.9  | 12612.2 | 24299.9 | 37634.4 | 43912.8 | 44392.8 | 40934.7 | 29884.9 | 18323.8 |
| 45°   | 811.2  | 3504.8  | 17463.8 | 32951.8 | 50695.6 | 58349.6 | 58189.6 | 53209.1 | 39496.8 | 26524.6 |
| 47.5° | 1120.1 | 5458.3  | 24655.5 | 41372.5 | 59043.0 | 65859.1 | 65996.9 | 59909.7 | 45106.2 | 32829.6 |
| 50°   | 1722.4 | 8351.8  | 30698.3 | 45824.0 | 62632.2 | 69470.6 | 69341.7 | 62307.7 | 47237.5 | 35934.3 |
| 52.5° | 2240.2 | 10445.4 | 33729.6 | 47386.4 | 63092.2 | 71255.2 | 71246.3 | 62938.9 | 47568.6 | 36201.0 |
| 55°   | 2369.1 | 10603.2 | 33754.1 | 47470.8 | 64123.4 | 73590.9 | 73884.3 | 64492.3 | 47997.6 | 35036.4 |
| 57.5° | 2318.0 | 9387.5  | 32345.1 | 47959.8 | 65959.1 | 75397.7 | 75413.3 | 65996.9 | 49086.5 | 34323.0 |
| 58°   | 2273.5 | 9196.4  | 32060.6 | 48237.6 | 66274.7 | 75473.3 | 75435.5 | 66065.8 | 49973.3 | 34296.4 |
| 60°   | 2024.6 | 7985.1  | 30951.6 | 48946.5 | 65805.8 | 73922.1 | 73568.7 | 64561.2 | 49842.2 | 34023.0 |
| 62.5° | 1591.3 | 6229.4  | 29860.4 | 48126.5 | 60778.7 | 66412.5 | 66559.2 | 57158.4 | 45437.3 | 32429.5 |
| 65°   | 1266.8 | 4642.6  | 27584.6 | 42214.8 | 50048.8 | 54538.1 | 55084.8 | 46479.6 | 37925.6 | 27460.2 |
| 67.5° | 1009.0 | 3355.9  | 23139.8 | 33609.6 | 39603.5 | 45517.3 | 45915.2 | 39023.4 | 29382.6 | 21039.6 |
| 70°   | 820.1  | 2269.1  | 15972.5 | 24579.9 | 32665.1 | 39314.6 | 39339.0 | 32418.4 | 21930.8 | 13785.7 |
| 72.5° | 726.7  | 1571.2  | 9271.9  | 17926.0 | 26486.8 | 32036.2 | 31389.4 | 26306.8 | 16854.8 | 8165.2  |
| 75°   | 628.9  | 1042.3  | 4547.1  | 10958.7 | 16059.2 | 16168.1 | 16414.8 | 12203.3 | 8425.2  | 3882.6  |
| 77.5° | 517.8  | 740.1   | 1791.3  | 2993.6  | 4816.0  | 6165.0  | 6393.9  | 4844.9  | 2802.5  | 955.6   |
| 80°   | 355.6  | 351.1   | 482.3   | 917.9   | 1377.9  | 1726.8  | 1611.3  | 1246.8  | 733.4   | 366.7   |
| 82.5° | 153.3  | 166.7   | 217.8   | 262.2   | 213.4   | 206.7   | 197.8   | 126.7   | 97.8    | 75.6    |
| 85°   | 48.9   | 44.4    | 46.7    | 46.7    | 37.8    | 28.9    | 28.9    | 13.3    | 0.0     | 0.0     |
| 87.5° | 24.4   | 20.0    | 20.0    | 17.8    | 11.1    | 4.4     | 2.2     | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065667

CATALOG NUMBER: GLAN-SA8C-940-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°     |       | 90°    | 95°    | 105°  | 115°  | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  |
|---------|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 128.9   | 0°    | 128.9  | 128.9  | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 |
| 120.0   | 2.5°  | 117.8  | 117.8  | 113.3 | 108.9 | 106.7 | 102.2 | 100.0 | 97.8  | 95.6  | 93.3  |
| 128.9   | 5°    | 124.5  | 122.2  | 115.6 | 108.9 | 102.2 | 95.6  | 91.1  | 86.7  | 82.2  | 80.0  |
| 142.2   | 7.5°  | 135.6  | 131.1  | 117.8 | 106.7 | 97.8  | 88.9  | 84.5  | 77.8  | 73.3  | 66.7  |
| 157.8   | 10°   | 148.9  | 140.0  | 122.2 | 108.9 | 95.6  | 84.5  | 77.8  | 71.1  | 64.5  | 55.6  |
| 180.0   | 12.5° | 166.7  | 151.1  | 128.9 | 106.7 | 91.1  | 77.8  | 71.1  | 62.2  | 55.6  | 48.9  |
| 208.9   | 15°   | 182.2  | 162.2  | 131.1 | 106.7 | 86.7  | 71.1  | 62.2  | 53.3  | 46.7  | 37.8  |
| 262.2   | 17.5° | 204.5  | 171.1  | 128.9 | 100.0 | 80.0  | 62.2  | 53.3  | 46.7  | 35.6  | 22.2  |
| 388.9   | 20°   | 242.2  | 177.8  | 124.5 | 93.3  | 68.9  | 51.1  | 40.0  | 31.1  | 15.6  | 4.4   |
| 584.5   | 22.5° | 302.2  | 195.6  | 120.0 | 84.5  | 60.0  | 40.0  | 26.7  | 11.1  | 0.0   | 0.0   |
| 889.0   | 25°   | 417.8  | 226.7  | 120.0 | 80.0  | 53.3  | 28.9  | 8.9   | 0.0   | 0.0   | 0.0   |
| 1262.3  | 27.5° | 555.6  | 268.9  | 120.0 | 68.9  | 42.2  | 15.6  | 0.0   | 0.0   | 0.0   | 0.0   |
| 1720.2  | 30°   | 695.6  | 315.6  | 120.0 | 60.0  | 33.3  | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2118.0  | 32.5° | 829.0  | 355.6  | 122.2 | 51.1  | 22.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2669.1  | 35°   | 964.5  | 362.3  | 120.0 | 44.4  | 13.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 3344.7  | 37.5° | 1137.9 | 348.9  | 113.3 | 40.0  | 6.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 4400.4  | 40°   | 1400.1 | 355.6  | 106.7 | 37.8  | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 6282.8  | 42.5° | 1884.6 | 384.5  | 97.8  | 37.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 10007.5 | 45°   | 3258.1 | 515.6  | 88.9  | 40.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 15023.5 | 47.5° | 5389.4 | 926.7  | 86.7  | 40.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 18097.1 | 50°   | 6878.4 | 1166.8 | 91.1  | 42.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 18481.6 | 52.5° | 6867.3 | 1300.1 | 95.6  | 44.4  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 17034.8 | 55°   | 6105.0 | 1324.6 | 102.2 | 48.9  | 28.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 14639.1 | 57.5° | 5102.7 | 1209.0 | 117.8 | 60.0  | 53.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 14263.5 | 58°   | 4924.9 | 1155.7 | 122.2 | 62.2  | 57.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 12372.2 | 60°   | 4035.9 | 942.3  | 155.6 | 77.8  | 77.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 10143.1 | 62.5° | 2786.9 | 822.3  | 177.8 | 100.0 | 80.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 7478.4  | 65°   | 1971.3 | 742.3  | 193.4 | 106.7 | 64.5  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 5313.8  | 67.5° | 1473.5 | 684.5  | 213.4 | 108.9 | 33.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 3333.6  | 70°   | 1129.0 | 642.3  | 262.2 | 115.6 | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 1986.8  | 72.5° | 920.1  | 593.4  | 317.8 | 120.0 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 1191.2  | 75°   | 762.3  | 535.6  | 306.7 | 131.1 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 635.6   | 77.5° | 506.7  | 415.6  | 280.0 | 131.1 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 226.7   | 80°   | 177.8  | 164.5  | 217.8 | 115.6 | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 46.7    | 82.5° | 26.7   | 22.2   | 31.1  | 40.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0     | 85°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0     | 87.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0     | 90°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P1065667

CATALOG NUMBER: GLAN-SA8C-940-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180°  |       | 185°  | 195°  | 205°  | 215°  | 225°  | 235°  | 245°  | 255°  | 265°  | 270°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 128.9 | 0°    | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 |
| 91.1  | 2.5°  | 91.1  | 91.1  | 88.9  | 91.1  | 91.1  | 95.6  | 106.7 | 122.2 | 140.0 | 146.7 |
| 77.8  | 5°    | 75.6  | 73.3  | 71.1  | 71.1  | 71.1  | 77.8  | 86.7  | 104.5 | 124.5 | 133.3 |
| 64.5  | 7.5°  | 62.2  | 60.0  | 57.8  | 55.6  | 55.6  | 60.0  | 71.1  | 91.1  | 111.1 | 120.0 |
| 53.3  | 10°   | 51.1  | 46.7  | 44.4  | 42.2  | 42.2  | 46.7  | 57.8  | 77.8  | 100.0 | 108.9 |
| 44.4  | 12.5° | 42.2  | 35.6  | 31.1  | 28.9  | 26.7  | 33.3  | 44.4  | 62.2  | 86.7  | 97.8  |
| 33.3  | 15°   | 28.9  | 22.2  | 15.6  | 13.3  | 11.1  | 17.8  | 28.9  | 48.9  | 73.3  | 86.7  |
| 17.8  | 17.5° | 15.6  | 6.7   | 2.2   | 0.0   | 0.0   | 4.4   | 13.3  | 35.6  | 60.0  | 71.1  |
| 0.0   | 20°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 17.8  | 44.4  | 55.6  |
| 0.0   | 22.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 2.2   | 26.7  | 37.8  |
| 0.0   | 25°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 11.1  | 20.0  |
| 0.0   | 27.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 4.4   |
| 0.0   | 30°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 58°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 6.7   |
| 0.0   | 87.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 8.9   | 17.8  |
| 0.0   | 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065667

CATALOG NUMBER: GLAN-SA8C-940-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275°  |       | 285°  | 295°  | 305°  | 315°  | 316°  | 325°  | 335°  | 345°  | 355°  | 360°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 128.9 | 0°    | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9  |
| 153.3 | 2.5°  | 157.8 | 155.6 | 151.1 | 146.7 | 146.7 | 146.7 | 153.3 | 160.0 | 166.7 | 166.7  |
| 137.8 | 5°    | 146.7 | 146.7 | 144.5 | 140.0 | 140.0 | 142.2 | 151.1 | 162.2 | 171.1 | 173.3  |
| 126.7 | 7.5°  | 135.6 | 140.0 | 135.6 | 133.3 | 135.6 | 137.8 | 146.7 | 160.0 | 173.3 | 177.8  |
| 117.8 | 10°   | 128.9 | 131.1 | 131.1 | 128.9 | 128.9 | 133.3 | 142.2 | 160.0 | 177.8 | 184.5  |
| 106.7 | 12.5° | 120.0 | 124.5 | 122.2 | 122.2 | 122.2 | 126.7 | 137.8 | 157.8 | 182.2 | 191.1  |
| 95.6  | 15°   | 111.1 | 117.8 | 117.8 | 115.6 | 115.6 | 117.8 | 133.3 | 155.6 | 188.9 | 204.5  |
| 82.2  | 17.5° | 102.2 | 108.9 | 111.1 | 106.7 | 106.7 | 111.1 | 126.7 | 155.6 | 193.4 | 220.0  |
| 66.7  | 20°   | 84.5  | 95.6  | 102.2 | 95.6  | 95.6  | 100.0 | 115.6 | 146.7 | 195.6 | 235.6  |
| 48.9  | 22.5° | 66.7  | 77.8  | 86.7  | 84.5  | 84.5  | 86.7  | 106.7 | 140.0 | 197.8 | 262.2  |
| 28.9  | 25°   | 48.9  | 60.0  | 66.7  | 71.1  | 71.1  | 77.8  | 97.8  | 135.6 | 206.7 | 317.8  |
| 13.3  | 27.5° | 28.9  | 42.2  | 51.1  | 55.6  | 57.8  | 66.7  | 91.1  | 131.1 | 222.2 | 397.8  |
| 0.0   | 30°   | 13.3  | 24.4  | 35.6  | 44.4  | 44.4  | 60.0  | 84.5  | 126.7 | 242.2 | 513.4  |
| 0.0   | 32.5° | 0.0   | 11.1  | 17.8  | 31.1  | 33.3  | 48.9  | 77.8  | 122.2 | 271.1 | 624.5  |
| 0.0   | 35°   | 0.0   | 0.0   | 8.9   | 24.4  | 24.4  | 40.0  | 71.1  | 117.8 | 315.6 | 709.0  |
| 0.0   | 37.5° | 0.0   | 0.0   | 0.0   | 17.8  | 20.0  | 35.6  | 68.9  | 115.6 | 324.5 | 715.6  |
| 0.0   | 40°   | 0.0   | 0.0   | 0.0   | 13.3  | 15.6  | 33.3  | 68.9  | 117.8 | 293.4 | 700.1  |
| 0.0   | 42.5° | 0.0   | 0.0   | 0.0   | 8.9   | 11.1  | 33.3  | 68.9  | 122.2 | 264.5 | 717.8  |
| 0.0   | 45°   | 0.0   | 0.0   | 0.0   | 6.7   | 8.9   | 35.6  | 66.7  | 120.0 | 248.9 | 811.2  |
| 0.0   | 47.5° | 0.0   | 0.0   | 0.0   | 8.9   | 13.3  | 35.6  | 64.5  | 117.8 | 251.1 | 1120.1 |
| 0.0   | 50°   | 0.0   | 0.0   | 0.0   | 11.1  | 15.6  | 35.6  | 66.7  | 113.3 | 275.6 | 1722.4 |
| 0.0   | 52.5° | 0.0   | 0.0   | 0.0   | 8.9   | 13.3  | 40.0  | 73.3  | 111.1 | 300.0 | 2240.2 |
| 0.0   | 55°   | 0.0   | 0.0   | 0.0   | 2.2   | 6.7   | 51.1  | 80.0  | 111.1 | 337.8 | 2369.1 |
| 0.0   | 57.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 57.8  | 91.1  | 117.8 | 400.0 | 2318.0 |
| 0.0   | 58°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 57.8  | 93.3  | 117.8 | 404.5 | 2273.5 |
| 0.0   | 60°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 57.8  | 102.2 | 131.1 | 435.6 | 2024.6 |
| 0.0   | 62.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 48.9  | 122.2 | 164.5 | 453.4 | 1591.3 |
| 0.0   | 65°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 40.0  | 144.5 | 180.0 | 466.7 | 1266.8 |
| 0.0   | 67.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 37.8  | 148.9 | 182.2 | 473.4 | 1009.0 |
| 0.0   | 70°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 40.0  | 146.7 | 195.6 | 495.6 | 820.1  |
| 0.0   | 72.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 44.4  | 133.3 | 215.6 | 495.6 | 726.7  |
| 0.0   | 75°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 46.7  | 124.5 | 242.2 | 451.2 | 628.9  |
| 0.0   | 77.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 44.4  | 122.2 | 282.2 | 402.3 | 517.8  |
| 0.0   | 80°   | 4.4   | 6.7   | 6.7   | 4.4   | 4.4   | 37.8  | 120.0 | 286.7 | 342.3 | 355.6  |
| 2.2   | 82.5° | 13.3  | 17.8  | 15.6  | 11.1  | 11.1  | 33.3  | 106.7 | 240.0 | 177.8 | 153.3  |
| 13.3  | 85°   | 24.4  | 28.9  | 28.9  | 24.4  | 24.4  | 31.1  | 66.7  | 86.7  | 60.0  | 48.9   |
| 24.4  | 87.5° | 33.3  | 37.8  | 37.8  | 33.3  | 33.3  | 31.1  | 28.9  | 26.7  | 24.4  | 24.4   |
| 0.0   | 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-16

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-940-U-5WQ

Data in this report applies to families of products including GSS-SB1A-940-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-16  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-940-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3856  
 CIE  $u'$ : 0.2261  
 CIE  $v'$ : 0.5084  
 Duv: 0.0032  
 CIE x: 0.3896  
 CIE y: 0.3894  
 CIE z: 0.2211  
 Peak Wavelength (nm): 614  
 Dominant Wavelength (nm): 578  
 Purity: 33.77304  
 R<sub>f</sub>: 91.8  
 R<sub>g</sub>: 98.4

CRI (Ra): 92.1  
 R1: 91.8  
 R2: 94.1  
 R3: 95.3  
 R4: 92.8  
 R5: 91.0  
 R6: 91.6  
 R7: 95.0  
 R8: 85.2  
 R9: 60.7  
 R10: 85.2  
 R11: 92.4  
 R12: 74.5  
 R13: 92.3  
 R14: 97.0  
 R15: 88.5



### Test Conditions


Stabilization Time: 23M  
 Operation Time: 1H 23M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-16


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-16

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-16

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 492                                  | NR                             | 620               | 993                                  | NR                             | 750               | 73                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 539                                  | NR                             | 625               | 978                                  | NR                             | 755               | 62                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 583                                  | NR                             | 630               | 962                                  | NR                             | 760               | 54                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 623                                  | NR                             | 635               | 933                                  | NR                             | 765               | 46                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 661                                  | NR                             | 640               | 898                                  | NR                             | 770               | 39                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 698                                  | NR                             | 645               | 855                                  | NR                             | 775               | 34                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 733                                  | NR                             | 650               | 810                                  | NR                             | 780               | 29                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 764                                  | NR                             | 655               | 759                                  | NR                             | 785               | 25                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 794                                  | NR                             | 660               | 704                                  | NR                             | 790               | 21                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 6                                    | NR                             | 535               | 820                                  | NR                             | 665               | 651                                  | NR                             | 795               | 18                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 12                                   | NR                             | 540               | 837                                  | NR                             | 670               | 592                                  | NR                             | 800               | 16                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 22                                   | NR                             | 545               | 853                                  | NR                             | 675               | 538                                  | NR                             | 805               | 13                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 42                                   | NR                             | 550               | 864                                  | NR                             | 680               | 486                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 79                                   | NR                             | 555               | 872                                  | NR                             | 685               | 435                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 147                                  | NR                             | 560               | 876                                  | NR                             | 690               | 389                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 278                                  | NR                             | 565               | 883                                  | NR                             | 695               | 344                                  | NR                             | 825               | 7                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 515                                  | NR                             | 570               | 891                                  | NR                             | 700               | 303                                  | NR                             | 830               | 6                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 832                                  | NR                             | 575               | 900                                  | NR                             | 705               | 266                                  | NR                             | 835               | 5                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 874                                  | NR                             | 580               | 914                                  | NR                             | 710               | 233                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 659                                  | NR                             | 585               | 927                                  | NR                             | 715               | 203                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 567                                  | NR                             | 590               | 944                                  | NR                             | 720               | 178                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 485                                  | NR                             | 595               | 961                                  | NR                             | 725               | 154                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 401                                  | NR                             | 600               | 975                                  | NR                             | 730               | 133                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 393                                  | NR                             | 605               | 988                                  | NR                             | 735               | 115                                  | NR                             | 865               | 2                                    | NR                             | 995               | 1                                    | NR                             |
| 480               | 417                                  | NR                             | 610               | 996                                  | NR                             | 740               | 98                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 448                                  | NR                             | 615               | 998                                  | NR                             | 745               | 85                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-16

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.72

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 492                      | NR            | 620    | 993                      | NR            | 750    | 73                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 539                      | NR            | 625    | 978                      | NR            | 755    | 62                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 583                      | NR            | 630    | 962                      | NR            | 760    | 54                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 623                      | NR            | 635    | 933                      | NR            | 765    | 46                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 661                      | NR            | 640    | 898                      | NR            | 770    | 39                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 698                      | NR            | 645    | 855                      | NR            | 775    | 34                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 733                      | NR            | 650    | 810                      | NR            | 780    | 29                       | NR            | 910    | 1                        | NR            |
| 395    | 1                        | NR            | 525    | 764                      | NR            | 655    | 759                      | NR            | 785    | 25                       | NR            | 915    | 1                        | NR            |
| 400    | 3                        | NR            | 530    | 794                      | NR            | 660    | 704                      | NR            | 790    | 21                       | NR            | 920    | 1                        | NR            |
| 405    | 6                        | NR            | 535    | 820                      | NR            | 665    | 651                      | NR            | 795    | 18                       | NR            | 925    | 1                        | NR            |
| 410    | 12                       | NR            | 540    | 837                      | NR            | 670    | 592                      | NR            | 800    | 16                       | NR            | 930    | 1                        | NR            |
| 415    | 22                       | NR            | 545    | 853                      | NR            | 675    | 538                      | NR            | 805    | 13                       | NR            | 935    | 0                        | NR            |
| 420    | 42                       | NR            | 550    | 864                      | NR            | 680    | 486                      | NR            | 810    | 12                       | NR            | 940    | 0                        | NR            |
| 425    | 79                       | NR            | 555    | 872                      | NR            | 685    | 435                      | NR            | 815    | 10                       | NR            | 945    | 0                        | NR            |
| 430    | 147                      | NR            | 560    | 876                      | NR            | 690    | 389                      | NR            | 820    | 9                        | NR            | 950    | 0                        | NR            |
| 435    | 278                      | NR            | 565    | 883                      | NR            | 695    | 344                      | NR            | 825    | 7                        | NR            | 955    | 0                        | NR            |
| 440    | 515                      | NR            | 570    | 891                      | NR            | 700    | 303                      | NR            | 830    | 6                        | NR            | 960    | 0                        | NR            |
| 445    | 832                      | NR            | 575    | 900                      | NR            | 705    | 266                      | NR            | 835    | 5                        | NR            | 965    | 0                        | NR            |
| 450    | 874                      | NR            | 580    | 914                      | NR            | 710    | 233                      | NR            | 840    | 5                        | NR            | 970    | 0                        | NR            |
| 455    | 659                      | NR            | 585    | 927                      | NR            | 715    | 203                      | NR            | 845    | 4                        | NR            | 975    | 0                        | NR            |
| 460    | 567                      | NR            | 590    | 944                      | NR            | 720    | 178                      | NR            | 850    | 4                        | NR            | 980    | 0                        | NR            |
| 465    | 485                      | NR            | 595    | 961                      | NR            | 725    | 154                      | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 401                      | NR            | 600    | 975                      | NR            | 730    | 133                      | NR            | 860    | 3                        | NR            | 990    | 0                        | NR            |
| 475    | 393                      | NR            | 605    | 988                      | NR            | 735    | 115                      | NR            | 865    | 2                        | NR            | 995    | 1                        | NR            |
| 480    | 417                      | NR            | 610    | 996                      | NR            | 740    | 98                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 448                      | NR            | 615    | 998                      | NR            | 745    | 85                       | NR            | 875    | 2                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-16

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.52**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 492                                  | NR                             | 620               | 993                                  | NR                             | 750               | 73                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 539                                  | NR                             | 625               | 978                                  | NR                             | 755               | 62                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 583                                  | NR                             | 630               | 962                                  | NR                             | 760               | 54                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 623                                  | NR                             | 635               | 933                                  | NR                             | 765               | 46                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 661                                  | NR                             | 640               | 898                                  | NR                             | 770               | 39                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 698                                  | NR                             | 645               | 855                                  | NR                             | 775               | 34                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 733                                  | NR                             | 650               | 810                                  | NR                             | 780               | 29                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 764                                  | NR                             | 655               | 759                                  | NR                             | 785               | 25                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 794                                  | NR                             | 660               | 704                                  | NR                             | 790               | 21                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 6                                    | NR                             | 535               | 820                                  | NR                             | 665               | 651                                  | NR                             | 795               | 18                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 12                                   | NR                             | 540               | 837                                  | NR                             | 670               | 592                                  | NR                             | 800               | 16                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 22                                   | NR                             | 545               | 853                                  | NR                             | 675               | 538                                  | NR                             | 805               | 13                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 42                                   | NR                             | 550               | 864                                  | NR                             | 680               | 486                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 79                                   | NR                             | 555               | 872                                  | NR                             | 685               | 435                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 147                                  | NR                             | 560               | 876                                  | NR                             | 690               | 389                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 278                                  | NR                             | 565               | 883                                  | NR                             | 695               | 344                                  | NR                             | 825               | 7                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 515                                  | NR                             | 570               | 891                                  | NR                             | 700               | 303                                  | NR                             | 830               | 6                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 832                                  | NR                             | 575               | 900                                  | NR                             | 705               | 266                                  | NR                             | 835               | 5                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 874                                  | NR                             | 580               | 914                                  | NR                             | 710               | 233                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 659                                  | NR                             | 585               | 927                                  | NR                             | 715               | 203                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 567                                  | NR                             | 590               | 944                                  | NR                             | 720               | 178                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 485                                  | NR                             | 595               | 961                                  | NR                             | 725               | 154                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 401                                  | NR                             | 600               | 975                                  | NR                             | 730               | 133                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 393                                  | NR                             | 605               | 988                                  | NR                             | 735               | 115                                  | NR                             | 865               | 2                                    | NR                             | 995               | 1                                    | NR                             |
| 480               | 417                                  | NR                             | 610               | 996                                  | NR                             | 740               | 98                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 448                                  | NR                             | 615               | 998                                  | NR                             | 745               | 85                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-16





TM-30-18

### Summary

$R_f = 91.8$   
 $R_g = 98.4$   
 $CIE R_a = 92.1$   
 $R_9 = 60.7$




### Color Vector Graphics






Individual Sample Fidelity Index ( $R_{f,i}$ )



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 96 | CES76 = 87 |
| CES02 = 62 | CES27 = 91 | CES52 = 98 | CES77 = 90 |
| CES03 = 31 | CES28 = 96 | CES53 = 95 | CES78 = 84 |
| CES04 = 69 | CES29 = 96 | CES54 = 94 | CES79 = 96 |
| CES05 = 49 | CES30 = 93 | CES55 = 92 | CES80 = 94 |
| CES06 = 50 | CES31 = 97 | CES56 = 93 | CES81 = 89 |
| CES07 = 42 | CES32 = 92 | CES57 = 92 | CES82 = 97 |
| CES08 = 41 | CES33 = 99 | CES58 = 92 | CES83 = 98 |
| CES09 = 29 | CES34 = 94 | CES59 = 96 | CES84 = 94 |
| CES10 = 74 | CES35 = 96 | CES60 = 93 | CES85 = 85 |
| CES11 = 57 | CES36 = 82 | CES61 = 92 | CES86 = 88 |
| CES12 = 63 | CES37 = 95 | CES62 = 87 | CES87 = 92 |
| CES13 = 43 | CES38 = 88 | CES63 = 92 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 89 | CES89 = 87 |
| CES15 = 71 | CES40 = 98 | CES65 = 88 | CES90 = 96 |
| CES16 = 47 | CES41 = 97 | CES66 = 87 | CES91 = 74 |
| CES17 = 49 | CES42 = 96 | CES67 = 86 | CES92 = 80 |
| CES18 = 56 | CES43 = 96 | CES68 = 88 | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 89 | CES94 = 82 |
| CES20 = 66 | CES45 = 98 | CES70 = 86 | CES95 = 83 |
| CES21 = 85 | CES46 = 97 | CES71 = 81 | CES96 = 92 |
| CES22 = 78 | CES47 = 97 | CES72 = 94 | CES97 = 95 |
| CES23 = 91 | CES48 = 91 | CES73 = 81 | CES98 = 94 |
| CES24 = 90 | CES49 = 96 | CES74 = 93 | CES99 = 91 |
| CES25 = 71 | CES50 = 97 | CES75 = 83 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)