

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065607

Luminaire Tested: **GLAN-SA2C-935-U-LBC**

Issue Date: 08/07/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1065607  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA2C-935-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 2xLight Square PACKAGE  
90CRI 3500K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (28) 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7574.3 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2


Input Watts (W): 96.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1065607

CATALOG NUMBER: GLAN-SA2C-935-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 13.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065607  
CATALOG NUMBER: GLAN-SA2C-935-U-LBC

## Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P1065607

CATALOG NUMBER: GLAN-SA2C-935-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 51.7     | 0.0    | 51.7   |
|                    | % Fixture | 0.7      | 0.0    | 0.7    |
| <b>Street Side</b> | Lumens    | 7522.6   | 0.0    | 7522.6 |
|                    | % Fixture | 99.3     | 0.0    | 99.3   |
| <b>Total</b>       | Lumens    | 7574.3   | 0.0    | 7574.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 3.0    | 0.0       |
| 10°-20°   | 16.6   | 0.2       |
| 20°-30°   | 179.4  | 2.4       |
| 30°-40°   | 530.7  | 7.0       |
| 40°-50°   | 1581.6 | 20.9      |
| 50°-60°   | 2509.7 | 33.1      |
| 60°-70°   | 2093.4 | 27.6      |
| 70°-80°   | 645.6  | 8.5       |
| 80°-90°   | 14.3   | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7574.3 | 100.0     |
| 0°-180°   | 7574.3 | 100.0     |



REPORT NUMBER: P1065607


CATALOG NUMBER: GLAN-SA2C-935-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 193.9  | 2.6       |                         |      |         |
| FM   | (30°-60°)   | 4593.7 | 60.6      |                         |      |         |
| FH   | (60°-80°)   | 2721.4 | 35.9      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 13.6   | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 5.1    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 28.3   | 0.4       | B0/220                  |      |         |
| BH   | (60°-80°)   | 17.7   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.7    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1065607

CATALOG NUMBER: GLAN-SA2C-935-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°     | 15°    | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°    |
|-------|-------|--------|--------|---------|---------|---------|---------|---------|---------|--------|
| 0°    | 33.2  | 33.2   | 33.2   | 33.2    | 33.2    | 33.2    | 33.2    | 33.2    | 33.2    | 33.2   |
| 2.5°  | 42.9  | 42.9   | 41.2   | 38.9    | 36.6    | 34.3    | 33.8    | 32.6    | 32.0    | 31.5   |
| 5°    | 44.6  | 44.6   | 44.1   | 42.3    | 40.1    | 38.3    | 38.3    | 36.6    | 35.5    | 34.3   |
| 7.5°  | 45.8  | 46.3   | 47.5   | 46.9    | 45.8    | 44.1    | 44.1    | 42.9    | 41.2    | 38.3   |
| 10°   | 47.5  | 49.2   | 51.5   | 52.6    | 53.2    | 53.2    | 52.6    | 52.1    | 49.2    | 45.2   |
| 12.5° | 49.2  | 52.6   | 58.4   | 64.1    | 67.5    | 72.1    | 71.5    | 70.4    | 62.9    | 54.4   |
| 15°   | 52.6  | 57.8   | 69.8   | 86.4    | 112.1   | 128.2   | 134.5   | 128.7   | 104.1   | 73.2   |
| 17.5° | 56.6  | 65.2   | 101.3  | 180.8   | 296.4   | 351.3   | 384.5   | 357.6   | 236.9   | 139.0  |
| 20°   | 60.7  | 79.5   | 188.2  | 468.6   | 769.0   | 948.7   | 998.5   | 920.6   | 591.1   | 264.9  |
| 22.5° | 67.5  | 111.6  | 381.6  | 968.7   | 1657.0  | 1926.5  | 1977.4  | 1728.5  | 1116.3  | 523.0  |
| 25°   | 81.8  | 161.9  | 658.0  | 1578.6  | 2473.0  | 2927.8  | 2906.7  | 2580.5  | 1810.9  | 835.4  |
| 27.5° | 102.4 | 235.7  | 995.0  | 2242.9  | 3254.5  | 3655.6  | 3703.7  | 3300.3  | 2414.0  | 1228.5 |
| 30°   | 132.2 | 326.7  | 1356.6 | 2775.1  | 3881.1  | 4314.8  | 4322.8  | 3905.7  | 2953.6  | 1573.5 |
| 32.5° | 160.8 | 412.5  | 1673.0 | 3289.5  | 4498.5  | 4973.9  | 5009.4  | 4496.2  | 3356.4  | 1932.8 |
| 35°   | 182.5 | 468.6  | 1993.5 | 3741.5  | 5121.0  | 5776.1  | 5773.8  | 5164.5  | 3833.6  | 2253.8 |
| 37.5° | 184.2 | 524.7  | 2283.6 | 4203.8  | 5909.5  | 6643.0  | 6715.7  | 6043.9  | 4410.3  | 2650.9 |
| 40°   | 180.2 | 587.6  | 2650.9 | 4924.7  | 7330.2  | 8455.6  | 8519.7  | 7672.9  | 5567.3  | 3330.6 |
| 42.5° | 184.8 | 696.9  | 3247.1 | 6256.2  | 9689.3  | 11305.7 | 11429.3 | 10538.9 | 7694.1  | 4717.6 |
| 45°   | 208.8 | 902.3  | 4496.2 | 8483.7  | 13052.0 | 15022.5 | 14981.3 | 13699.1 | 10168.7 | 6828.9 |
| 47.5° | 288.4 | 1405.3 | 6347.7 | 10651.7 | 15201.1 | 16955.9 | 16991.4 | 15424.2 | 11612.9 | 8452.2 |
| 50°   | 443.4 | 2150.2 | 7903.5 | 11797.7 | 16125.1 | 17885.7 | 17852.5 | 16041.6 | 12161.6 | 9251.5 |
| 52.5° | 576.8 | 2689.2 | 8683.9 | 12200.0 | 16243.6 | 18345.2 | 18342.9 | 16204.1 | 12246.9 | 9320.2 |
| 55°   | 609.9 | 2729.9 | 8690.2 | 12221.7 | 16509.1 | 18946.5 | 19022.1 | 16604.0 | 12357.3 | 9020.4 |
| 57.5° | 596.8 | 2416.9 | 8327.5 | 12347.6 | 16981.7 | 19411.7 | 19415.7 | 16991.4 | 12637.7 | 8836.7 |
| 58°   | 585.3 | 2367.7 | 8254.2 | 12419.1 | 17062.9 | 19431.2 | 19421.4 | 17009.1 | 12866.0 | 8829.9 |
| 60°   | 521.3 | 2055.8 | 7968.7 | 12601.6 | 16942.2 | 19031.8 | 18940.8 | 16621.8 | 12832.2 | 8759.5 |
| 62.5° | 409.7 | 1603.8 | 7687.8 | 12390.5 | 15647.9 | 17098.4 | 17136.2 | 14715.8 | 11698.2 | 8349.2 |
| 65°   | 326.1 | 1195.3 | 7101.9 | 10868.5 | 12885.4 | 14041.2 | 14182.0 | 11966.5 | 9764.2  | 7069.8 |
| 67.5° | 259.8 | 864.0  | 5957.5 | 8653.0  | 10196.2 | 11718.8 | 11821.2 | 10046.9 | 7564.8  | 5416.8 |
| 70°   | 211.1 | 584.2  | 4112.2 | 6328.3  | 8409.9  | 10121.8 | 10128.1 | 8346.4  | 5646.3  | 3549.2 |
| 72.5° | 187.1 | 404.5  | 2387.1 | 4615.2  | 6819.2  | 8247.9  | 8081.4  | 6772.9  | 4339.4  | 2102.2 |
| 75°   | 161.9 | 268.4  | 1170.7 | 2821.4  | 4134.6  | 4162.6  | 4226.1  | 3141.8  | 2169.1  | 999.6  |
| 77.5° | 133.3 | 190.5  | 461.2  | 770.7   | 1239.9  | 1587.2  | 1646.2  | 1247.3  | 721.5   | 246.0  |
| 80°   | 91.5  | 90.4   | 124.2  | 236.3   | 354.8   | 444.6   | 414.8   | 321.0   | 188.8   | 94.4   |
| 82.5° | 39.5  | 42.9   | 56.1   | 67.5    | 54.9    | 53.2    | 50.9    | 32.6    | 25.2    | 19.5   |
| 85°   | 12.6  | 11.4   | 12.0   | 12.0    | 9.7     | 7.4     | 7.4     | 3.4     | 0.0     | 0.0    |
| 87.5° | 6.3   | 5.1    | 5.1    | 4.6     | 2.9     | 1.1     | 0.6     | 0.0     | 0.0     | 0.0    |
| 90°   | 0.0   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |

REPORT NUMBER: P1065607

CATALOG NUMBER: GLAN-SA2C-935-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°    |       | 90°    | 95°   | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° |
|--------|-------|--------|-------|------|------|------|------|------|------|------|------|
| 33.2   | 0°    | 33.2   | 33.2  | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 |
| 30.9   | 2.5°  | 30.3   | 30.3  | 29.2 | 28.0 | 27.5 | 26.3 | 25.7 | 25.2 | 24.6 | 24.0 |
| 33.2   | 5°    | 32.0   | 31.5  | 29.8 | 28.0 | 26.3 | 24.6 | 23.5 | 22.3 | 21.2 | 20.6 |
| 36.6   | 7.5°  | 34.9   | 33.8  | 30.3 | 27.5 | 25.2 | 22.9 | 21.7 | 20.0 | 18.9 | 17.2 |
| 40.6   | 10°   | 38.3   | 36.0  | 31.5 | 28.0 | 24.6 | 21.7 | 20.0 | 18.3 | 16.6 | 14.3 |
| 46.3   | 12.5° | 42.9   | 38.9  | 33.2 | 27.5 | 23.5 | 20.0 | 18.3 | 16.0 | 14.3 | 12.6 |
| 53.8   | 15°   | 46.9   | 41.8  | 33.8 | 27.5 | 22.3 | 18.3 | 16.0 | 13.7 | 12.0 | 9.7  |
| 67.5   | 17.5° | 52.6   | 44.1  | 33.2 | 25.7 | 20.6 | 16.0 | 13.7 | 12.0 | 9.2  | 5.7  |
| 100.1  | 20°   | 62.4   | 45.8  | 32.0 | 24.0 | 17.7 | 13.2 | 10.3 | 8.0  | 4.0  | 1.1  |
| 150.5  | 22.5° | 77.8   | 50.4  | 30.9 | 21.7 | 15.4 | 10.3 | 6.9  | 2.9  | 0.0  | 0.0  |
| 228.9  | 25°   | 107.6  | 58.4  | 30.9 | 20.6 | 13.7 | 7.4  | 2.3  | 0.0  | 0.0  | 0.0  |
| 325.0  | 27.5° | 143.0  | 69.2  | 30.9 | 17.7 | 10.9 | 4.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 442.9  | 30°   | 179.1  | 81.2  | 30.9 | 15.4 | 8.6  | 0.6  | 0.0  | 0.0  | 0.0  | 0.0  |
| 545.3  | 32.5° | 213.4  | 91.5  | 31.5 | 13.2 | 5.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 687.2  | 35°   | 248.3  | 93.3  | 30.9 | 11.4 | 3.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 861.1  | 37.5° | 293.0  | 89.8  | 29.2 | 10.3 | 1.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1132.9 | 40°   | 360.5  | 91.5  | 27.5 | 9.7  | 0.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1617.5 | 42.5° | 485.2  | 99.0  | 25.2 | 9.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2576.5 | 45°   | 838.8  | 132.7 | 22.9 | 10.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3867.9 | 47.5° | 1387.5 | 238.6 | 22.3 | 10.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 4659.2 | 50°   | 1770.9 | 300.4 | 23.5 | 10.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 4758.2 | 52.5° | 1768.0 | 334.7 | 24.6 | 11.4 | 2.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 4385.7 | 55°   | 1571.8 | 341.0 | 26.3 | 12.6 | 7.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3768.9 | 57.5° | 1313.7 | 311.3 | 30.3 | 15.4 | 13.7 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3672.2 | 58°   | 1267.9 | 297.5 | 31.5 | 16.0 | 14.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3185.3 | 60°   | 1039.1 | 242.6 | 40.1 | 20.0 | 20.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2611.4 | 62.5° | 717.5  | 211.7 | 45.8 | 25.7 | 20.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1925.4 | 65°   | 507.5  | 191.1 | 49.8 | 27.5 | 16.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1368.1 | 67.5° | 379.4  | 176.2 | 54.9 | 28.0 | 8.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 858.3  | 70°   | 290.7  | 165.4 | 67.5 | 29.8 | 2.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 511.5  | 72.5° | 236.9  | 152.8 | 81.8 | 30.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 306.7  | 75°   | 196.3  | 137.9 | 79.0 | 33.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 163.6  | 77.5° | 130.5  | 107.0 | 72.1 | 33.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 58.4   | 80°   | 45.8   | 42.3  | 56.1 | 29.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 12.0   | 82.5° | 6.9    | 5.7   | 8.0  | 10.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 85°   | 0.0    | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 87.5° | 0.0    | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 90°   | 0.0    | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

REPORT NUMBER: P1065607

CATALOG NUMBER: GLAN-SA2C-935-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180° |       | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° |
|------|-------|------|------|------|------|------|------|------|------|------|------|
| 33.2 | 0°    | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 |
| 23.5 | 2.5°  | 23.5 | 23.5 | 22.9 | 23.5 | 23.5 | 24.6 | 27.5 | 31.5 | 36.0 | 37.8 |
| 20.0 | 5°    | 19.5 | 18.9 | 18.3 | 18.3 | 18.3 | 20.0 | 22.3 | 26.9 | 32.0 | 34.3 |
| 16.6 | 7.5°  | 16.0 | 15.4 | 14.9 | 14.3 | 14.3 | 15.4 | 18.3 | 23.5 | 28.6 | 30.9 |
| 13.7 | 10°   | 13.2 | 12.0 | 11.4 | 10.9 | 10.9 | 12.0 | 14.9 | 20.0 | 25.7 | 28.0 |
| 11.4 | 12.5° | 10.9 | 9.2  | 8.0  | 7.4  | 6.9  | 8.6  | 11.4 | 16.0 | 22.3 | 25.2 |
| 8.6  | 15°   | 7.4  | 5.7  | 4.0  | 3.4  | 2.9  | 4.6  | 7.4  | 12.6 | 18.9 | 22.3 |
| 4.6  | 17.5° | 4.0  | 1.7  | 0.6  | 0.0  | 0.0  | 1.1  | 3.4  | 9.2  | 15.4 | 18.3 |
| 0.0  | 20°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 4.6  | 11.4 | 14.3 |
| 0.0  | 22.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.6  | 6.9  | 9.7  |
| 0.0  | 25°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 2.9  | 5.1  |
| 0.0  | 27.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.1  |
| 0.0  | 30°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 32.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 35°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 80°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 82.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 85°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.7  |
| 0.0  | 87.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 2.3  | 4.6  |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P1065607

CATALOG NUMBER: GLAN-SA2C-935-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275° |       | 285° | 295° | 305° | 315° | 316° | 325° | 335° | 345° | 355°  | 360°  |
|------|-------|------|------|------|------|------|------|------|------|-------|-------|
| 33.2 | 0°    | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2 | 33.2  | 33.2  |
| 39.5 | 2.5°  | 40.6 | 40.1 | 38.9 | 37.8 | 37.8 | 37.8 | 39.5 | 41.2 | 42.9  | 42.9  |
| 35.5 | 5°    | 37.8 | 37.8 | 37.2 | 36.0 | 36.0 | 36.6 | 38.9 | 41.8 | 44.1  | 44.6  |
| 32.6 | 7.5°  | 34.9 | 36.0 | 34.9 | 34.3 | 34.9 | 35.5 | 37.8 | 41.2 | 44.6  | 45.8  |
| 30.3 | 10°   | 33.2 | 33.8 | 33.8 | 33.2 | 33.2 | 34.3 | 36.6 | 41.2 | 45.8  | 47.5  |
| 27.5 | 12.5° | 30.9 | 32.0 | 31.5 | 31.5 | 31.5 | 32.6 | 35.5 | 40.6 | 46.9  | 49.2  |
| 24.6 | 15°   | 28.6 | 30.3 | 30.3 | 29.8 | 29.8 | 30.3 | 34.3 | 40.1 | 48.6  | 52.6  |
| 21.2 | 17.5° | 26.3 | 28.0 | 28.6 | 27.5 | 27.5 | 28.6 | 32.6 | 40.1 | 49.8  | 56.6  |
| 17.2 | 20°   | 21.7 | 24.6 | 26.3 | 24.6 | 24.6 | 25.7 | 29.8 | 37.8 | 50.4  | 60.7  |
| 12.6 | 22.5° | 17.2 | 20.0 | 22.3 | 21.7 | 21.7 | 22.3 | 27.5 | 36.0 | 50.9  | 67.5  |
| 7.4  | 25°   | 12.6 | 15.4 | 17.2 | 18.3 | 18.3 | 20.0 | 25.2 | 34.9 | 53.2  | 81.8  |
| 3.4  | 27.5° | 7.4  | 10.9 | 13.2 | 14.3 | 14.9 | 17.2 | 23.5 | 33.8 | 57.2  | 102.4 |
| 0.0  | 30°   | 3.4  | 6.3  | 9.2  | 11.4 | 11.4 | 15.4 | 21.7 | 32.6 | 62.4  | 132.2 |
| 0.0  | 32.5° | 0.0  | 2.9  | 4.6  | 8.0  | 8.6  | 12.6 | 20.0 | 31.5 | 69.8  | 160.8 |
| 0.0  | 35°   | 0.0  | 0.0  | 2.3  | 6.3  | 6.3  | 10.3 | 18.3 | 30.3 | 81.2  | 182.5 |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 4.6  | 5.1  | 9.2  | 17.7 | 29.8 | 83.5  | 184.2 |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 3.4  | 4.0  | 8.6  | 17.7 | 30.3 | 75.5  | 180.2 |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 2.3  | 2.9  | 8.6  | 17.7 | 31.5 | 68.1  | 184.8 |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 1.7  | 2.3  | 9.2  | 17.2 | 30.9 | 64.1  | 208.8 |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 2.3  | 3.4  | 9.2  | 16.6 | 30.3 | 64.7  | 288.4 |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 2.9  | 4.0  | 9.2  | 17.2 | 29.2 | 71.0  | 443.4 |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 2.3  | 3.4  | 10.3 | 18.9 | 28.6 | 77.2  | 576.8 |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.6  | 1.7  | 13.2 | 20.6 | 28.6 | 87.0  | 609.9 |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 14.9 | 23.5 | 30.3 | 103.0 | 596.8 |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 14.9 | 24.0 | 30.3 | 104.1 | 585.3 |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 14.9 | 26.3 | 33.8 | 112.1 | 521.3 |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 12.6 | 31.5 | 42.3 | 116.7 | 409.7 |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 10.3 | 37.2 | 46.3 | 120.2 | 326.1 |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 9.7  | 38.3 | 46.9 | 121.9 | 259.8 |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 10.3 | 37.8 | 50.4 | 127.6 | 211.1 |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 11.4 | 34.3 | 55.5 | 127.6 | 187.1 |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 12.0 | 32.0 | 62.4 | 116.2 | 161.9 |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 11.4 | 31.5 | 72.7 | 103.6 | 133.3 |
| 0.0  | 80°   | 1.1  | 1.7  | 1.7  | 1.1  | 1.1  | 9.7  | 30.9 | 73.8 | 88.1  | 91.5  |
| 0.6  | 82.5° | 3.4  | 4.6  | 4.0  | 2.9  | 2.9  | 8.6  | 27.5 | 61.8 | 45.8  | 39.5  |
| 3.4  | 85°   | 6.3  | 7.4  | 7.4  | 6.3  | 6.3  | 8.0  | 17.2 | 22.3 | 15.4  | 12.6  |
| 6.3  | 87.5° | 8.6  | 9.7  | 9.7  | 8.6  | 8.6  | 8.0  | 7.4  | 6.9  | 6.3   | 6.3   |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-15

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-935-U-5WQ

Data in this report applies to families of products including GSS-SB1A-935-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-15  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-935-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 3500K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3455  
 CIE  $u'$ : 0.2356  
 CIE  $v'$ : 0.5159  
 Duv: 0.0028  
 CIE x: 0.4109  
 CIE y: 0.3999  
 CIE z: 0.1892  
 Peak Wavelength (nm): 616  
 Dominant Wavelength (nm): 579  
 Purity: 43.35383  
 R<sub>f</sub>: 92.3  
 R<sub>g</sub>: 98.5

CRI (Ra): 92.2  
 R1: 92.0  
 R2: 94.4  
 R3: 95.6  
 R4: 93.2  
 R5: 91.4  
 R6: 92.5  
 R7: 94.5  
 R8: 84.2  
 R9: 59.8  
 R10: 85.8  
 R11: 93.2  
 R12: 78.0  
 R13: 92.5  
 R14: 97.0  
 R15: 88.4



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-15


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-15

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-15

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 0                             | NR                             | 490               | 410                           | NR                             | 620               | 997                           | NR                             | 750               | 74                            | NR                             | 880               | 1                             | NR                             |
| 365               | 0                             | NR                             | 495               | 454                           | NR                             | 625               | 988                           | NR                             | 755               | 64                            | NR                             | 885               | 1                             | NR                             |
| 370               | 0                             | NR                             | 500               | 493                           | NR                             | 630               | 973                           | NR                             | 760               | 54                            | NR                             | 890               | 1                             | NR                             |
| 375               | 0                             | NR                             | 505               | 530                           | NR                             | 635               | 946                           | NR                             | 765               | 47                            | NR                             | 895               | 1                             | NR                             |
| 380               | 0                             | NR                             | 510               | 564                           | NR                             | 640               | 913                           | NR                             | 770               | 40                            | NR                             | 900               | 1                             | NR                             |
| 385               | 0                             | NR                             | 515               | 599                           | NR                             | 645               | 870                           | NR                             | 775               | 34                            | NR                             | 905               | 1                             | NR                             |
| 390               | 0                             | NR                             | 520               | 634                           | NR                             | 650               | 826                           | NR                             | 780               | 29                            | NR                             | 910               | 1                             | NR                             |
| 395               | 0                             | NR                             | 525               | 664                           | NR                             | 655               | 774                           | NR                             | 785               | 25                            | NR                             | 915               | 1                             | NR                             |
| 400               | 2                             | NR                             | 530               | 695                           | NR                             | 660               | 720                           | NR                             | 790               | 21                            | NR                             | 920               | 1                             | NR                             |
| 405               | 4                             | NR                             | 535               | 722                           | NR                             | 665               | 664                           | NR                             | 795               | 18                            | NR                             | 925               | 1                             | NR                             |
| 410               | 9                             | NR                             | 540               | 741                           | NR                             | 670               | 605                           | NR                             | 800               | 16                            | NR                             | 930               | 0                             | NR                             |
| 415               | 17                            | NR                             | 545               | 762                           | NR                             | 675               | 550                           | NR                             | 805               | 13                            | NR                             | 935               | 0                             | NR                             |
| 420               | 32                            | NR                             | 550               | 777                           | NR                             | 680               | 497                           | NR                             | 810               | 12                            | NR                             | 940               | 0                             | NR                             |
| 425               | 61                            | NR                             | 555               | 789                           | NR                             | 685               | 445                           | NR                             | 815               | 10                            | NR                             | 945               | 0                             | NR                             |
| 430               | 114                           | NR                             | 560               | 800                           | NR                             | 690               | 398                           | NR                             | 820               | 9                             | NR                             | 950               | 0                             | NR                             |
| 435               | 218                           | NR                             | 565               | 813                           | NR                             | 695               | 352                           | NR                             | 825               | 7                             | NR                             | 955               | 0                             | NR                             |
| 440               | 427                           | NR                             | 570               | 828                           | NR                             | 700               | 309                           | NR                             | 830               | 6                             | NR                             | 960               | 0                             | NR                             |
| 445               | 684                           | NR                             | 575               | 846                           | NR                             | 705               | 273                           | NR                             | 835               | 5                             | NR                             | 965               | 0                             | NR                             |
| 450               | 611                           | NR                             | 580               | 866                           | NR                             | 710               | 237                           | NR                             | 840               | 5                             | NR                             | 970               | 0                             | NR                             |
| 455               | 461                           | NR                             | 585               | 888                           | NR                             | 715               | 208                           | NR                             | 845               | 4                             | NR                             | 975               | 0                             | NR                             |
| 460               | 427                           | NR                             | 590               | 913                           | NR                             | 720               | 181                           | NR                             | 850               | 4                             | NR                             | 980               | 0                             | NR                             |
| 465               | 349                           | NR                             | 595               | 936                           | NR                             | 725               | 157                           | NR                             | 855               | 3                             | NR                             | 985               | 0                             | NR                             |
| 470               | 298                           | NR                             | 600               | 957                           | NR                             | 730               | 136                           | NR                             | 860               | 3                             | NR                             | 990               | 1                             | NR                             |
| 475               | 312                           | NR                             | 605               | 976                           | NR                             | 735               | 117                           | NR                             | 865               | 2                             | NR                             | 995               | 0                             | NR                             |
| 480               | 335                           | NR                             | 610               | 990                           | NR                             | 740               | 100                           | NR                             | 870               | 2                             | NR                             | 1000              | 0                             | NR                             |
| 485               | 367                           | NR                             | 615               | 999                           | NR                             | 745               | 86                            | NR                             | 875               | 2                             | NR                             |                   |                               |                                |

REPORT NUMBER: SP1-2407-184-15

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.58

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 410                         | NR               | 620       | 997                         | NR               | 750       | 74                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 454                         | NR               | 625       | 988                         | NR               | 755       | 64                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 493                         | NR               | 630       | 973                         | NR               | 760       | 54                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 530                         | NR               | 635       | 946                         | NR               | 765       | 47                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 564                         | NR               | 640       | 913                         | NR               | 770       | 40                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 599                         | NR               | 645       | 870                         | NR               | 775       | 34                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 634                         | NR               | 650       | 826                         | NR               | 780       | 29                          | NR               | 910       | 1                           | NR               |
| 395       | 0                           | NR               | 525       | 664                         | NR               | 655       | 774                         | NR               | 785       | 25                          | NR               | 915       | 1                           | NR               |
| 400       | 2                           | NR               | 530       | 695                         | NR               | 660       | 720                         | NR               | 790       | 21                          | NR               | 920       | 1                           | NR               |
| 405       | 4                           | NR               | 535       | 722                         | NR               | 665       | 664                         | NR               | 795       | 18                          | NR               | 925       | 1                           | NR               |
| 410       | 9                           | NR               | 540       | 741                         | NR               | 670       | 605                         | NR               | 800       | 16                          | NR               | 930       | 0                           | NR               |
| 415       | 17                          | NR               | 545       | 762                         | NR               | 675       | 550                         | NR               | 805       | 13                          | NR               | 935       | 0                           | NR               |
| 420       | 32                          | NR               | 550       | 777                         | NR               | 680       | 497                         | NR               | 810       | 12                          | NR               | 940       | 0                           | NR               |
| 425       | 61                          | NR               | 555       | 789                         | NR               | 685       | 445                         | NR               | 815       | 10                          | NR               | 945       | 0                           | NR               |
| 430       | 114                         | NR               | 560       | 800                         | NR               | 690       | 398                         | NR               | 820       | 9                           | NR               | 950       | 0                           | NR               |
| 435       | 218                         | NR               | 565       | 813                         | NR               | 695       | 352                         | NR               | 825       | 7                           | NR               | 955       | 0                           | NR               |
| 440       | 427                         | NR               | 570       | 828                         | NR               | 700       | 309                         | NR               | 830       | 6                           | NR               | 960       | 0                           | NR               |
| 445       | 684                         | NR               | 575       | 846                         | NR               | 705       | 273                         | NR               | 835       | 5                           | NR               | 965       | 0                           | NR               |
| 450       | 611                         | NR               | 580       | 866                         | NR               | 710       | 237                         | NR               | 840       | 5                           | NR               | 970       | 0                           | NR               |
| 455       | 461                         | NR               | 585       | 888                         | NR               | 715       | 208                         | NR               | 845       | 4                           | NR               | 975       | 0                           | NR               |
| 460       | 427                         | NR               | 590       | 913                         | NR               | 720       | 181                         | NR               | 850       | 4                           | NR               | 980       | 0                           | NR               |
| 465       | 349                         | NR               | 595       | 936                         | NR               | 725       | 157                         | NR               | 855       | 3                           | NR               | 985       | 0                           | NR               |
| 470       | 298                         | NR               | 600       | 957                         | NR               | 730       | 136                         | NR               | 860       | 3                           | NR               | 990       | 1                           | NR               |
| 475       | 312                         | NR               | 605       | 976                         | NR               | 735       | 117                         | NR               | 865       | 2                           | NR               | 995       | 0                           | NR               |
| 480       | 335                         | NR               | 610       | 990                         | NR               | 740       | 100                         | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 367                         | NR               | 615       | 999                         | NR               | 745       | 86                          | NR               | 875       | 2                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-15

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.14**


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 410                                    | NR                             | 620               | 997                                    | NR                             | 750               | 74                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 454                                    | NR                             | 625               | 988                                    | NR                             | 755               | 64                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 493                                    | NR                             | 630               | 973                                    | NR                             | 760               | 54                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 530                                    | NR                             | 635               | 946                                    | NR                             | 765               | 47                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 564                                    | NR                             | 640               | 913                                    | NR                             | 770               | 40                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 599                                    | NR                             | 645               | 870                                    | NR                             | 775               | 34                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 634                                    | NR                             | 650               | 826                                    | NR                             | 780               | 29                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 664                                    | NR                             | 655               | 774                                    | NR                             | 785               | 25                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 695                                    | NR                             | 660               | 720                                    | NR                             | 790               | 21                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 4                                      | NR                             | 535               | 722                                    | NR                             | 665               | 664                                    | NR                             | 795               | 18                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 9                                      | NR                             | 540               | 741                                    | NR                             | 670               | 605                                    | NR                             | 800               | 16                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 17                                     | NR                             | 545               | 762                                    | NR                             | 675               | 550                                    | NR                             | 805               | 13                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 32                                     | NR                             | 550               | 777                                    | NR                             | 680               | 497                                    | NR                             | 810               | 12                                     | NR                             | 940               | 0                                      | NR                             |
| 425               | 61                                     | NR                             | 555               | 789                                    | NR                             | 685               | 445                                    | NR                             | 815               | 10                                     | NR                             | 945               | 0                                      | NR                             |
| 430               | 114                                    | NR                             | 560               | 800                                    | NR                             | 690               | 398                                    | NR                             | 820               | 9                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 218                                    | NR                             | 565               | 813                                    | NR                             | 695               | 352                                    | NR                             | 825               | 7                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 427                                    | NR                             | 570               | 828                                    | NR                             | 700               | 309                                    | NR                             | 830               | 6                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 684                                    | NR                             | 575               | 846                                    | NR                             | 705               | 273                                    | NR                             | 835               | 5                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 611                                    | NR                             | 580               | 866                                    | NR                             | 710               | 237                                    | NR                             | 840               | 5                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 461                                    | NR                             | 585               | 888                                    | NR                             | 715               | 208                                    | NR                             | 845               | 4                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 427                                    | NR                             | 590               | 913                                    | NR                             | 720               | 181                                    | NR                             | 850               | 4                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 349                                    | NR                             | 595               | 936                                    | NR                             | 725               | 157                                    | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 298                                    | NR                             | 600               | 957                                    | NR                             | 730               | 136                                    | NR                             | 860               | 3                                      | NR                             | 990               | 1                                      | NR                             |
| 475               | 312                                    | NR                             | 605               | 976                                    | NR                             | 735               | 117                                    | NR                             | 865               | 2                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 335                                    | NR                             | 610               | 990                                    | NR                             | 740               | 100                                    | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 367                                    | NR                             | 615               | 999                                    | NR                             | 745               | 86                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-15





TM-30-18

### Summary

$R_f = 92.3$   
 $R_g = 98.5$   
 $CIE R_a = 92.2$   
 $R_9 = 59.8$







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 97 | CES76 = 88 |
| CES02 = 62 | CES27 = 93 | CES52 = 98 | CES77 = 91 |
| CES03 = 31 | CES28 = 96 | CES53 = 96 | CES78 = 85 |
| CES04 = 70 | CES29 = 95 | CES54 = 95 | CES79 = 96 |
| CES05 = 50 | CES30 = 97 | CES55 = 94 | CES80 = 94 |
| CES06 = 51 | CES31 = 96 | CES56 = 94 | CES81 = 87 |
| CES07 = 42 | CES32 = 91 | CES57 = 93 | CES82 = 97 |
| CES08 = 41 | CES33 = 98 | CES58 = 94 | CES83 = 97 |
| CES09 = 29 | CES34 = 94 | CES59 = 96 | CES84 = 94 |
| CES10 = 75 | CES35 = 97 | CES60 = 94 | CES85 = 85 |
| CES11 = 58 | CES36 = 86 | CES61 = 93 | CES86 = 87 |
| CES12 = 64 | CES37 = 95 | CES62 = 91 | CES87 = 92 |
| CES13 = 43 | CES38 = 92 | CES63 = 93 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 91 | CES89 = 87 |
| CES15 = 71 | CES40 = 98 | CES65 = 89 | CES90 = 96 |
| CES16 = 47 | CES41 = 98 | CES66 = 89 | CES91 = 78 |
| CES17 = 49 | CES42 = 96 | CES67 = 88 | CES92 = 81 |
| CES18 = 56 | CES43 = 96 | CES68 = 89 | CES93 = 89 |
| CES19 = 71 | CES44 = 99 | CES69 = 91 | CES94 = 81 |
| CES20 = 66 | CES45 = 98 | CES70 = 87 | CES95 = 85 |
| CES21 = 86 | CES46 = 97 | CES71 = 84 | CES96 = 92 |
| CES22 = 78 | CES47 = 97 | CES72 = 95 | CES97 = 95 |
| CES23 = 91 | CES48 = 93 | CES73 = 83 | CES98 = 94 |
| CES24 = 90 | CES49 = 96 | CES74 = 94 | CES99 = 91 |
| CES25 = 71 | CES50 = 98 | CES75 = 85 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)