

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063173

Luminaire Tested: **GLAN-SA6A-935-U-T3BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1063173
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA6A-935-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 6xLight Square PACKAGE
90CRI 3500K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (84) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16344.6 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G3

Input Watts (W): 162.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1063173

CATALOG NUMBER: GLAN-SA6A-935-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 18.3 fc
 Type III - Short - N/A

REPORT NUMBER: P1063173

CATALOG NUMBER: GLAN-SA6A-935-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1063173

CATALOG NUMBER: GLAN-SA6A-935-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	59.7	0.0	59.7
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	16284.9	0.0	16284.9
	% Fixture	99.6	0.0	99.6
Total	Lumens	16344.6	0.0	16344.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.7	0.1
10°-20°	187.9	1.1
20°-30°	677.2	4.1
30°-40°	1549.4	9.5
40°-50°	2613.2	16.0
50°-60°	4312.4	26.4
60°-70°	4819.6	29.5
70°-80°	1989.9	12.2
80°-90°	179.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16344.6	100.0
0°-180°	16344.6	100.0



REPORT NUMBER: P1063173


CATALOG NUMBER: GLAN-SA6A-935-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	865.1	5.3			
FM	(30°-60°)	8460.6	51.8			
FH	(60°-80°)	6782.2	41.5			G3/7500
FVH	(80°-90°)	176.9	1.1			G2/225
BL	(0°-30°)	15.6	0.1	B0/110		
BM	(30°-60°)	14.3	0.1	B0/220		
BH	(60°-80°)	27.3	0.2	B0/110		G0/110
BVH	(80°-90°)	2.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G3

Type III Short



REPORT NUMBER: P1063173

CATALOG NUMBER: GLAN-SA6A-935-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9
2.5°	128.2	132.5	128.2	128.2	128.2	124.0	124.0	119.7	119.7	115.4	111.1
5°	188.1	188.1	175.3	166.7	158.2	153.9	149.6	141.1	132.5	124.0	115.4
7.5°	418.9	418.9	380.5	329.2	260.8	222.3	213.7	175.3	149.6	132.5	115.4
10°	1000.3	1000.3	914.8	773.7	598.5	444.6	397.6	252.2	179.5	141.1	119.7
12.5°	1662.9	1684.3	1577.4	1397.9	1137.1	867.8	773.7	461.7	239.4	153.9	119.7
15°	2257.1	2205.8	2175.9	2004.9	1756.9	1436.3	1316.6	778.0	346.3	175.3	119.7
17.5°	2658.9	2658.9	2616.2	2500.7	2274.2	1992.0	1893.7	1256.8	560.0	200.9	124.0
20°	3129.1	3129.1	3052.2	2971.0	2770.1	2530.7	2436.6	1786.9	867.8	256.5	124.0
22.5°	3697.7	3706.2	3620.7	3475.4	3283.0	3018.0	2936.8	2278.5	1256.8	342.0	128.2
25°	4390.2	4398.8	4274.8	4138.0	3843.0	3556.6	3432.7	2842.7	1731.3	478.8	128.2
27.5°	5155.4	5215.2	5031.4	4796.3	4484.2	4125.2	4031.1	3351.4	2201.5	675.4	136.8
30°	6108.7	6108.7	5865.0	5535.8	5198.1	4753.6	4633.9	3885.8	2701.7	936.2	145.3
32.5°	6929.4	6865.3	6553.2	6207.0	5847.9	5433.3	5305.0	4445.8	3214.6	1261.1	162.4
35°	7557.8	7502.2	7117.5	6745.6	6433.5	6053.1	5899.2	5052.8	3757.5	1628.7	188.1
37.5°	8096.4	8075.1	7553.5	7087.6	6882.4	6549.0	6412.2	5625.6	4291.9	2026.2	218.0
40°	8686.4	8618.0	8062.2	7485.1	7177.4	6908.1	6784.1	6087.3	4804.9	2492.2	260.8
42.5°	9190.8	9109.6	8609.4	8045.1	7519.3	7156.0	7036.3	6476.3	5305.0	2958.2	316.3
45°	9750.8	9708.0	9203.6	8776.1	8075.1	7493.7	7335.5	6788.4	5762.4	3513.9	389.0
47.5°	10592.9	10516.0	10045.7	9695.2	8883.0	8006.7	7780.1	7109.0	6202.7	4061.0	500.1
50°	11571.8	11520.5	11242.7	10964.8	10156.9	8883.0	8613.7	7570.6	6694.3	4710.8	645.5
52.5°	12371.2	12362.7	12396.9	12401.1	11789.9	10357.8	9956.0	8314.5	7258.6	5352.0	850.7
55°	12354.1	12392.6	12768.8	13200.5	13247.6	12371.2	11982.2	9567.0	7993.8	6142.9	1137.1
57.5°	11892.4	11862.5	12260.1	12909.8	13367.2	13461.3	13397.2	11512.0	9101.0	7096.1	1577.4
58°	11742.8	11717.2	12093.4	12756.0	13281.8	13534.0	13469.8	11952.3	9349.0	7232.9	1697.1
60°	11199.9	11204.2	11426.5	12029.2	12555.0	13153.5	13213.4	13209.1	10584.4	8147.7	2299.8
62.5°	10481.8	10447.6	10652.8	11144.4	11606.0	12007.9	12110.5	13294.6	12392.6	9310.5	3449.8
65°	9490.0	9438.7	9656.7	10212.5	10708.3	10969.1	10973.4	12148.9	13243.3	10558.7	5091.3
67.5°	7647.6	7604.8	8040.9	8754.8	9519.9	9861.9	10015.8	10541.6	12525.1	11405.1	6031.7
70°	4685.2	4774.9	5382.0	6501.9	7810.0	8438.4	8669.3	8831.7	10665.6	11276.9	5044.2
72.5°	2163.0	2056.2	2573.4	3355.7	4847.6	6245.5	6484.8	7121.8	8455.5	9789.3	3761.8
75°	1008.8	970.4	1090.1	1466.3	2197.2	3372.8	3808.8	5685.5	6484.8	6809.7	2714.5
77.5°	517.2	521.5	619.8	666.9	906.3	1560.3	1791.1	3740.4	4753.6	3800.3	1821.1
80°	226.6	235.1	239.4	260.8	367.6	602.7	679.7	1735.6	3248.8	1936.5	996.0
82.5°	145.3	149.6	149.6	149.6	175.3	239.4	273.6	696.8	1620.1	961.8	307.8
85°	76.9	76.9	85.5	106.9	124.0	145.3	153.9	222.3	534.3	286.4	72.7
87.5°	42.7	47.0	51.3	64.1	81.2	98.3	106.9	153.9	205.2	196.6	17.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1063173

CATALOG NUMBER: GLAN-SA6A-935-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9
2.5°	111.1	106.9	102.6	98.3	94.0	89.8	89.8	89.8	89.8	89.8	89.8
5°	106.9	102.6	98.3	89.8	81.2	76.9	72.7	68.4	68.4	68.4	68.4
7.5°	106.9	102.6	89.8	81.2	72.7	64.1	55.6	55.6	55.6	55.6	55.6
10°	106.9	98.3	85.5	72.7	59.8	51.3	47.0	42.7	42.7	42.7	42.7
12.5°	106.9	94.0	81.2	64.1	51.3	42.7	38.5	34.2	34.2	34.2	34.2
15°	106.9	94.0	76.9	59.8	47.0	34.2	29.9	25.6	25.6	25.6	25.6
17.5°	102.6	89.8	72.7	51.3	38.5	25.6	21.4	17.1	17.1	21.4	21.4
20°	98.3	85.5	64.1	42.7	29.9	21.4	12.8	12.8	12.8	12.8	12.8
22.5°	98.3	85.5	59.8	38.5	25.6	12.8	8.5	8.5	8.5	8.5	12.8
25°	98.3	81.2	51.3	29.9	17.1	8.5	4.3	4.3	4.3	4.3	4.3
27.5°	98.3	81.2	47.0	25.6	12.8	8.5	4.3	0.0	0.0	0.0	0.0
30°	94.0	76.9	42.7	21.4	8.5	4.3	0.0	0.0	0.0	0.0	0.0
32.5°	94.0	72.7	34.2	17.1	8.5	4.3	0.0	0.0	0.0	0.0	0.0
35°	98.3	68.4	29.9	12.8	4.3	0.0	0.0	0.0	0.0	0.0	4.3
37.5°	102.6	64.1	25.6	8.5	4.3	0.0	0.0	0.0	0.0	0.0	0.0
40°	106.9	59.8	25.6	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	115.4	59.8	21.4	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	124.0	59.8	17.1	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	141.1	64.1	17.1	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	153.9	68.4	12.8	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	171.0	64.1	12.8	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	192.4	64.1	12.8	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	209.5	59.8	12.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	218.0	55.6	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	260.8	51.3	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	406.1	42.7	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	825.0	38.5	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	1538.9	34.2	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1722.7	38.5	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1085.8	29.9	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	572.8	29.9	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	286.4	29.9	4.3	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	132.5	21.4	4.3	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	55.6	12.8	8.5	4.3	4.3	0.0	0.0	0.0	0.0	0.0	0.0
85°	25.6	12.8	8.5	8.5	4.3	4.3	0.0	0.0	0.0	0.0	0.0
87.5°	12.8	12.8	12.8	8.5	8.5	4.3	4.3	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-15

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-935-U-5WQ

Data in this report applies to families of products including GSS-SB1A-935-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-15
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-935-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI
 3500K CCT 26 LEDS

Spectral Parameters

CCT (K): 3455
 CIE u' : 0.2356
 CIE v' : 0.5159
 Duv: 0.0028
 CIE x: 0.4109
 CIE y: 0.3999
 CIE z: 0.1892
 Peak Wavelength (nm): 616
 Dominant Wavelength (nm): 579
 Purity: 43.35383
 R_f: 92.3
 R_g: 98.5

CRI (Ra): 92.2
 R1: 92.0
 R2: 94.4
 R3: 95.6
 R4: 93.2
 R5: 91.4
 R6: 92.5
 R7: 94.5
 R8: 84.2
 R9: 59.8
 R10: 85.8
 R11: 93.2
 R12: 78.0
 R13: 92.5
 R14: 97.0
 R15: 88.4



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-15

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-15

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-15

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	410	NR	620	997	NR	750	74	NR	880	1	NR
365	0	NR	495	454	NR	625	988	NR	755	64	NR	885	1	NR
370	0	NR	500	493	NR	630	973	NR	760	54	NR	890	1	NR
375	0	NR	505	530	NR	635	946	NR	765	47	NR	895	1	NR
380	0	NR	510	564	NR	640	913	NR	770	40	NR	900	1	NR
385	0	NR	515	599	NR	645	870	NR	775	34	NR	905	1	NR
390	0	NR	520	634	NR	650	826	NR	780	29	NR	910	1	NR
395	0	NR	525	664	NR	655	774	NR	785	25	NR	915	1	NR
400	2	NR	530	695	NR	660	720	NR	790	21	NR	920	1	NR
405	4	NR	535	722	NR	665	664	NR	795	18	NR	925	1	NR
410	9	NR	540	741	NR	670	605	NR	800	16	NR	930	0	NR
415	17	NR	545	762	NR	675	550	NR	805	13	NR	935	0	NR
420	32	NR	550	777	NR	680	497	NR	810	12	NR	940	0	NR
425	61	NR	555	789	NR	685	445	NR	815	10	NR	945	0	NR
430	114	NR	560	800	NR	690	398	NR	820	9	NR	950	0	NR
435	218	NR	565	813	NR	695	352	NR	825	7	NR	955	0	NR
440	427	NR	570	828	NR	700	309	NR	830	6	NR	960	0	NR
445	684	NR	575	846	NR	705	273	NR	835	5	NR	965	0	NR
450	611	NR	580	866	NR	710	237	NR	840	5	NR	970	0	NR
455	461	NR	585	888	NR	715	208	NR	845	4	NR	975	0	NR
460	427	NR	590	913	NR	720	181	NR	850	4	NR	980	0	NR
465	349	NR	595	936	NR	725	157	NR	855	3	NR	985	0	NR
470	298	NR	600	957	NR	730	136	NR	860	3	NR	990	1	NR
475	312	NR	605	976	NR	735	117	NR	865	2	NR	995	0	NR
480	335	NR	610	990	NR	740	100	NR	870	2	NR	1000	0	NR
485	367	NR	615	999	NR	745	86	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-15

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	410	NR	620	997	NR	750	74	NR	880	1	NR
365	0	NR	495	454	NR	625	988	NR	755	64	NR	885	1	NR
370	0	NR	500	493	NR	630	973	NR	760	54	NR	890	1	NR
375	0	NR	505	530	NR	635	946	NR	765	47	NR	895	1	NR
380	0	NR	510	564	NR	640	913	NR	770	40	NR	900	1	NR
385	0	NR	515	599	NR	645	870	NR	775	34	NR	905	1	NR
390	0	NR	520	634	NR	650	826	NR	780	29	NR	910	1	NR
395	0	NR	525	664	NR	655	774	NR	785	25	NR	915	1	NR
400	2	NR	530	695	NR	660	720	NR	790	21	NR	920	1	NR
405	4	NR	535	722	NR	665	664	NR	795	18	NR	925	1	NR
410	9	NR	540	741	NR	670	605	NR	800	16	NR	930	0	NR
415	17	NR	545	762	NR	675	550	NR	805	13	NR	935	0	NR
420	32	NR	550	777	NR	680	497	NR	810	12	NR	940	0	NR
425	61	NR	555	789	NR	685	445	NR	815	10	NR	945	0	NR
430	114	NR	560	800	NR	690	398	NR	820	9	NR	950	0	NR
435	218	NR	565	813	NR	695	352	NR	825	7	NR	955	0	NR
440	427	NR	570	828	NR	700	309	NR	830	6	NR	960	0	NR
445	684	NR	575	846	NR	705	273	NR	835	5	NR	965	0	NR
450	611	NR	580	866	NR	710	237	NR	840	5	NR	970	0	NR
455	461	NR	585	888	NR	715	208	NR	845	4	NR	975	0	NR
460	427	NR	590	913	NR	720	181	NR	850	4	NR	980	0	NR
465	349	NR	595	936	NR	725	157	NR	855	3	NR	985	0	NR
470	298	NR	600	957	NR	730	136	NR	860	3	NR	990	1	NR
475	312	NR	605	976	NR	735	117	NR	865	2	NR	995	0	NR
480	335	NR	610	990	NR	740	100	NR	870	2	NR	1000	0	NR
485	367	NR	615	999	NR	745	86	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-15

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.14

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	410	NR	620	997	NR	750	74	NR	880	1	NR
365	0	NR	495	454	NR	625	988	NR	755	64	NR	885	1	NR
370	0	NR	500	493	NR	630	973	NR	760	54	NR	890	1	NR
375	0	NR	505	530	NR	635	946	NR	765	47	NR	895	1	NR
380	0	NR	510	564	NR	640	913	NR	770	40	NR	900	1	NR
385	0	NR	515	599	NR	645	870	NR	775	34	NR	905	1	NR
390	0	NR	520	634	NR	650	826	NR	780	29	NR	910	1	NR
395	0	NR	525	664	NR	655	774	NR	785	25	NR	915	1	NR
400	2	NR	530	695	NR	660	720	NR	790	21	NR	920	1	NR
405	4	NR	535	722	NR	665	664	NR	795	18	NR	925	1	NR
410	9	NR	540	741	NR	670	605	NR	800	16	NR	930	0	NR
415	17	NR	545	762	NR	675	550	NR	805	13	NR	935	0	NR
420	32	NR	550	777	NR	680	497	NR	810	12	NR	940	0	NR
425	61	NR	555	789	NR	685	445	NR	815	10	NR	945	0	NR
430	114	NR	560	800	NR	690	398	NR	820	9	NR	950	0	NR
435	218	NR	565	813	NR	695	352	NR	825	7	NR	955	0	NR
440	427	NR	570	828	NR	700	309	NR	830	6	NR	960	0	NR
445	684	NR	575	846	NR	705	273	NR	835	5	NR	965	0	NR
450	611	NR	580	866	NR	710	237	NR	840	5	NR	970	0	NR
455	461	NR	585	888	NR	715	208	NR	845	4	NR	975	0	NR
460	427	NR	590	913	NR	720	181	NR	850	4	NR	980	0	NR
465	349	NR	595	936	NR	725	157	NR	855	3	NR	985	0	NR
470	298	NR	600	957	NR	730	136	NR	860	3	NR	990	1	NR
475	312	NR	605	976	NR	735	117	NR	865	2	NR	995	0	NR
480	335	NR	610	990	NR	740	100	NR	870	2	NR	1000	0	NR
485	367	NR	615	999	NR	745	86	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-15



TM-30-18

Summary

$R_f = 92.3$
 $R_g = 98.5$
 $CIE\ R_a = 92.2$
 $R_9 = 59.8$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 93	CES52 = 98	CES77 = 91
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 85
CES04 = 70	CES29 = 95	CES54 = 95	CES79 = 96
CES05 = 50	CES30 = 97	CES55 = 94	CES80 = 94
CES06 = 51	CES31 = 96	CES56 = 94	CES81 = 87
CES07 = 42	CES32 = 91	CES57 = 93	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 94
CES10 = 75	CES35 = 97	CES60 = 94	CES85 = 85
CES11 = 58	CES36 = 86	CES61 = 93	CES86 = 87
CES12 = 64	CES37 = 95	CES62 = 91	CES87 = 92
CES13 = 43	CES38 = 92	CES63 = 93	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 47	CES41 = 98	CES66 = 89	CES91 = 78
CES17 = 49	CES42 = 96	CES67 = 88	CES92 = 81
CES18 = 56	CES43 = 96	CES68 = 89	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 97	CES71 = 84	CES96 = 92
CES22 = 78	CES47 = 97	CES72 = 95	CES97 = 95
CES23 = 91	CES48 = 93	CES73 = 83	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 94	CES99 = 91
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)