

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065049

Luminaire Tested: **GLAN-SA7A-940-U-RBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065049  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA7A-940-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 7xLight Square PACKAGE  
90CRI 4000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (98) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16612 lumens  
Efficiency: N/A  
Efficacy: 86.0 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3


Input Watts (W): 193.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065049  
CATALOG NUMBER: GLAN-SA7A-940-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 83.2     | 0.0    | 83.2    |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 16528.8  | 0.0    | 16528.8 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 16612.0  | 0.0    | 16612.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 6.5     | 0.0       |
| 10°-20°   | 36.5    | 0.2       |
| 20°-30°   | 393.7   | 2.4       |
| 30°-40°   | 1164.2  | 7.0       |
| 40°-50°   | 3469.6  | 20.9      |
| 50°-60°   | 5501.5  | 33.1      |
| 60°-70°   | 4592.4  | 27.6      |
| 70°-80°   | 1416.1  | 8.5       |
| 80°-90°   | 31.5    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 16612.0 | 100.0     |
| 0°-180°   | 16612.0 | 100.0     |



REPORT NUMBER: P1065049


CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 421.4   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 10105.5 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 5977.5  | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 24.3    | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 15.3    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 29.7    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 31.0    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 7.1     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 72.8   | 72.8   | 72.8  | 72.8  | 72.8  | 72.8  | 72.8  | 72.8  | 72.8  | 72.8  |
| 2.5°   | 66.5   | 66.5   | 66.5  | 66.5  | 65.3  | 65.3  | 64.0  | 64.0  | 62.8  | 62.8  |
| 5°     | 70.3   | 70.3   | 69.0  | 67.8  | 67.8  | 66.5  | 65.3  | 64.0  | 64.0  | 62.8  |
| 7.5°   | 76.6   | 75.3   | 74.1  | 72.8  | 70.3  | 69.0  | 66.5  | 65.3  | 64.0  | 61.5  |
| 10°    | 84.1   | 81.6   | 79.1  | 76.6  | 74.1  | 71.6  | 69.0  | 67.8  | 65.3  | 64.0  |
| 12.5°  | 94.2   | 90.4   | 85.4  | 81.6  | 79.1  | 75.3  | 72.8  | 70.3  | 66.5  | 64.0  |
| 15°    | 102.9  | 97.9   | 91.6  | 86.6  | 82.9  | 77.8  | 74.1  | 70.3  | 67.8  | 64.0  |
| 17.5°  | 115.5  | 106.7  | 96.7  | 90.4  | 85.4  | 79.1  | 72.8  | 69.0  | 65.3  | 60.3  |
| 20°    | 136.8  | 119.3  | 100.4 | 92.9  | 85.4  | 77.8  | 70.3  | 65.3  | 61.5  | 56.5  |
| 22.5°  | 170.7  | 140.6  | 110.5 | 99.2  | 89.1  | 77.8  | 67.8  | 62.8  | 57.7  | 52.7  |
| 25°    | 236.0  | 182.0  | 128.0 | 113.0 | 97.9  | 82.9  | 67.8  | 61.5  | 56.5  | 50.2  |
| 27.5°  | 313.8  | 233.5  | 151.9 | 130.6 | 110.5 | 89.1  | 67.8  | 60.3  | 54.0  | 46.4  |
| 30°    | 392.9  | 286.2  | 178.3 | 150.6 | 123.0 | 95.4  | 67.8  | 59.0  | 51.5  | 42.7  |
| 32.5°  | 468.2  | 335.2  | 200.9 | 168.2 | 135.6 | 101.7 | 69.0  | 59.0  | 49.0  | 38.9  |
| 35°    | 544.8  | 375.4  | 204.6 | 170.7 | 136.8 | 101.7 | 67.8  | 56.5  | 46.4  | 35.1  |
| 37.5°  | 642.7  | 420.5  | 197.1 | 163.2 | 130.6 | 96.7  | 64.0  | 54.0  | 43.9  | 32.6  |
| 40°    | 790.9  | 495.9  | 200.9 | 165.7 | 130.6 | 95.4  | 60.3  | 50.2  | 41.4  | 31.4  |
| 42.5°  | 1064.5 | 641.5  | 217.2 | 177.0 | 136.8 | 95.4  | 55.2  | 46.4  | 38.9  | 30.1  |
| 45°    | 1840.3 | 1065.8 | 291.2 | 231.0 | 170.7 | 110.5 | 50.2  | 42.7  | 36.4  | 28.9  |
| 47.5°  | 3044.2 | 1783.9 | 523.5 | 404.2 | 286.2 | 167.0 | 49.0  | 42.7  | 36.4  | 28.9  |
| 50°    | 3885.3 | 2272.2 | 659.1 | 507.2 | 355.3 | 203.4 | 51.5  | 43.9  | 37.7  | 30.1  |
| 52.5°  | 3879.0 | 2307.3 | 734.4 | 563.7 | 394.2 | 223.5 | 54.0  | 46.4  | 40.2  | 32.6  |
| 55°    | 3448.5 | 2098.9 | 748.2 | 575.0 | 403.0 | 229.7 | 57.7  | 50.2  | 42.7  | 35.1  |
| 57.5°  | 2882.3 | 1782.6 | 682.9 | 528.5 | 375.4 | 220.9 | 66.5  | 57.7  | 50.2  | 41.4  |
| 60°    | 2279.7 | 1406.0 | 532.3 | 420.5 | 310.1 | 198.3 | 87.9  | 76.6  | 66.5  | 55.2  |
| 62.5°  | 1574.2 | 1019.3 | 464.5 | 372.8 | 282.5 | 190.8 | 100.4 | 89.1  | 79.1  | 67.8  |
| 65°    | 1113.5 | 767.0  | 419.3 | 341.5 | 264.9 | 187.0 | 109.2 | 96.7  | 85.4  | 72.8  |
| 67.5°  | 832.3  | 610.1  | 386.6 | 320.1 | 253.6 | 187.0 | 120.5 | 105.4 | 91.6  | 76.6  |
| 70°    | 637.7  | 500.9  | 362.8 | 308.8 | 256.1 | 202.1 | 148.1 | 126.8 | 106.7 | 85.4  |
| 72.5°  | 519.7  | 428.1  | 335.2 | 296.3 | 257.3 | 218.4 | 179.5 | 151.9 | 124.3 | 95.4  |
| 75°    | 430.6  | 366.6  | 302.5 | 269.9 | 238.5 | 205.9 | 173.2 | 148.1 | 124.3 | 99.2  |
| 77.5°  | 286.2  | 261.1  | 234.8 | 215.9 | 197.1 | 177.0 | 158.2 | 136.8 | 116.7 | 95.4  |
| 80°    | 100.4  | 96.7   | 92.9  | 100.4 | 108.0 | 115.5 | 123.0 | 108.0 | 94.2  | 79.1  |
| 82.5°  | 15.1   | 13.8   | 12.6  | 13.8  | 15.1  | 16.3  | 17.6  | 18.8  | 20.1  | 21.3  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 |
| 0.0 | 2.5°   | 61.5  | 61.5 | 60.3  | 60.3 | 60.3  | 59.0 | 59.0  | 57.7 | 57.7  | 57.7 |
| 0.0 | 5°     | 60.3  | 60.3 | 59.0  | 57.7 | 56.5  | 56.5 | 55.2  | 54.0 | 54.0  | 52.7 |
| 0.0 | 7.5°   | 59.0  | 57.7 | 56.5  | 55.2 | 54.0  | 52.7 | 51.5  | 50.2 | 50.2  | 49.0 |
| 0.0 | 10°    | 60.3  | 57.7 | 56.5  | 54.0 | 52.7  | 51.5 | 49.0  | 47.7 | 46.4  | 46.4 |
| 0.0 | 12.5°  | 57.7  | 56.5 | 54.0  | 51.5 | 50.2  | 47.7 | 46.4  | 43.9 | 42.7  | 42.7 |
| 0.0 | 15°    | 57.7  | 55.2 | 51.5  | 49.0 | 46.4  | 45.2 | 42.7  | 40.2 | 38.9  | 37.7 |
| 0.0 | 17.5°  | 54.0  | 51.5 | 47.7  | 45.2 | 42.7  | 40.2 | 37.7  | 35.1 | 33.9  | 32.6 |
| 0.0 | 20°    | 49.0  | 46.4 | 42.7  | 38.9 | 36.4  | 33.9 | 31.4  | 28.9 | 27.6  | 26.4 |
| 0.0 | 22.5°  | 43.9  | 41.4 | 37.7  | 33.9 | 31.4  | 28.9 | 25.1  | 22.6 | 21.3  | 18.8 |
| 0.0 | 25°    | 41.4  | 37.7 | 33.9  | 30.1 | 26.4  | 23.9 | 20.1  | 16.3 | 13.8  | 11.3 |
| 0.0 | 27.5°  | 35.1  | 31.4 | 27.6  | 23.9 | 20.1  | 16.3 | 12.6  | 8.8  | 6.3   | 5.0  |
| 0.0 | 30°    | 30.1  | 26.4 | 22.6  | 18.8 | 13.8  | 10.0 | 6.3   | 1.3  | 1.3   | 1.3  |
| 0.0 | 32.5°  | 25.1  | 21.3 | 16.3  | 12.6 | 10.0  | 6.3  | 3.8   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 20.1  | 16.3 | 11.3  | 7.5  | 6.3   | 3.8  | 2.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 17.6  | 13.8 | 8.8   | 3.8  | 2.5   | 2.5  | 1.3   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 16.3  | 11.3 | 6.3   | 1.3  | 1.3   | 1.3  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 16.3  | 11.3 | 5.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 16.3  | 11.3 | 5.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 16.3  | 11.3 | 5.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 17.6  | 12.6 | 6.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 20.1  | 15.1 | 10.0  | 5.0  | 3.8   | 2.5  | 1.3   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 25.1  | 22.6 | 18.8  | 16.3 | 12.6  | 8.8  | 3.8   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 32.6  | 32.6 | 31.4  | 30.1 | 22.6  | 15.1 | 7.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 43.9  | 43.9 | 43.9  | 43.9 | 32.6  | 22.6 | 11.3  | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 54.0  | 51.5 | 47.7  | 45.2 | 33.9  | 22.6 | 11.3  | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 54.0  | 49.0 | 42.7  | 36.4 | 27.6  | 18.8 | 8.8   | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 50.2  | 40.2 | 28.9  | 18.8 | 13.8  | 10.0 | 5.0   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 50.2  | 35.1 | 20.1  | 5.0  | 3.8   | 2.5  | 1.3   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 50.2  | 33.9 | 16.3  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 55.2  | 37.7 | 18.8  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 55.2  | 37.7 | 18.8  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 49.0  | 32.6 | 16.3  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 16.3  | 11.3 | 5.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  |
| 0.0   | 2.5°   | 56.5 | 56.5  | 56.5 | 55.2  | 55.2 | 55.2  | 55.2 | 54.0  | 54.0 | 54.0  |
| 0.0   | 5°     | 51.5 | 51.5  | 50.2 | 50.2  | 49.0 | 49.0  | 47.7 | 47.7  | 46.4 | 46.4  |
| 0.0   | 7.5°   | 47.7 | 46.4  | 46.4 | 45.2  | 43.9 | 43.9  | 42.7 | 42.7  | 41.4 | 40.2  |
| 0.0   | 10°    | 43.9 | 42.7  | 42.7 | 41.4  | 40.2 | 38.9  | 38.9 | 37.7  | 36.4 | 35.1  |
| 0.0   | 12.5°  | 40.2 | 38.9  | 37.7 | 36.4  | 35.1 | 33.9  | 33.9 | 32.6  | 31.4 | 30.1  |
| 0.0   | 15°    | 35.1 | 33.9  | 32.6 | 31.4  | 30.1 | 28.9  | 28.9 | 27.6  | 26.4 | 25.1  |
| 0.0   | 17.5°  | 30.1 | 28.9  | 28.9 | 27.6  | 26.4 | 25.1  | 23.9 | 21.3  | 20.1 | 18.8  |
| 0.0   | 20°    | 22.6 | 21.3  | 20.1 | 18.8  | 17.6 | 15.1  | 13.8 | 11.3  | 8.8  | 7.5   |
| 0.0   | 22.5°  | 15.1 | 12.6  | 11.3 | 8.8   | 6.3  | 5.0   | 3.8  | 1.3   | 0.0  | 0.0   |
| 0.0   | 25°    | 5.0  | 3.8   | 2.5  | 1.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8  | 72.8 | 72.8   | 72.8 |
| 0.0 | 2.5°   | 52.7  | 52.7 | 52.7  | 51.5 | 51.5  | 51.5 | 51.5  | 51.5 | 51.5   | 51.5 |
| 0.0 | 5°     | 45.2  | 45.2 | 45.2  | 43.9 | 43.9  | 42.7 | 42.7  | 42.7 | 41.4   | 41.4 |
| 0.0 | 7.5°   | 38.9  | 37.7 | 37.7  | 36.4 | 36.4  | 35.1 | 35.1  | 35.1 | 33.9   | 33.9 |
| 0.0 | 10°    | 32.6  | 31.4 | 31.4  | 30.1 | 30.1  | 28.9 | 28.9  | 27.6 | 27.6   | 26.4 |
| 0.0 | 12.5°  | 28.9  | 27.6 | 26.4  | 25.1 | 25.1  | 23.9 | 22.6  | 22.6 | 21.3   | 20.1 |
| 0.0 | 15°    | 22.6  | 21.3 | 20.1  | 18.8 | 17.6  | 16.3 | 15.1  | 15.1 | 13.8   | 12.6 |
| 0.0 | 17.5°  | 15.1  | 12.6 | 11.3  | 10.0 | 10.0  | 8.8  | 7.5   | 6.3  | 5.0    | 3.8  |
| 0.0 | 20°    | 3.8   | 2.5  | 1.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   |
| 0.0    | 2.5°   | 51.5 | 50.2   | 50.2 | 50.2   | 51.5 | 51.5   | 51.5 | 51.5   | 51.5 | 51.5   |
| 0.0    | 5°     | 41.4 | 40.2   | 40.2 | 40.2   | 40.2 | 40.2   | 40.2 | 40.2   | 40.2 | 40.2   |
| 0.0    | 7.5°   | 33.9 | 32.6   | 32.6 | 32.6   | 32.6 | 31.4   | 31.4 | 31.4   | 31.4 | 31.4   |
| 0.0    | 10°    | 26.4 | 25.1   | 25.1 | 25.1   | 25.1 | 23.9   | 23.9 | 23.9   | 23.9 | 23.9   |
| 0.0    | 12.5°  | 18.8 | 18.8   | 17.6 | 17.6   | 17.6 | 16.3   | 16.3 | 16.3   | 16.3 | 15.1   |
| 0.0    | 15°    | 11.3 | 10.0   | 8.8  | 8.8    | 8.8  | 7.5    | 7.5  | 7.5    | 7.5  | 6.3    |
| 0.0    | 17.5°  | 2.5  | 2.5    | 1.3  | 1.3    | 1.3  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 |
| 0.0  | 2.5°   | 52.7   | 52.7 | 54.0   | 54.0 | 55.2   | 57.7 | 59.0   | 60.3 | 62.8   | 65.3 |
| 0.0  | 5°     | 41.4   | 42.7 | 42.7   | 43.9 | 45.2   | 46.4 | 47.7   | 49.0 | 51.5   | 54.0 |
| 0.0  | 7.5°   | 32.6   | 32.6 | 33.9   | 33.9 | 35.1   | 37.7 | 38.9   | 40.2 | 42.7   | 46.4 |
| 0.0  | 10°    | 25.1   | 25.1 | 26.4   | 26.4 | 27.6   | 30.1 | 31.4   | 32.6 | 35.1   | 38.9 |
| 0.0  | 12.5°  | 16.3   | 17.6 | 17.6   | 18.8 | 20.1   | 22.6 | 23.9   | 25.1 | 27.6   | 30.1 |
| 0.0  | 15°    | 7.5    | 8.8  | 8.8    | 10.0 | 11.3   | 13.8 | 15.1   | 16.3 | 18.8   | 22.6 |
| 0.0  | 17.5°  | 1.3    | 1.3  | 2.5    | 2.5  | 3.8    | 5.0  | 6.3    | 7.5  | 11.3   | 13.8 |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 2.5    | 5.0  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 1.3  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   |
| 0.0    | 2.5°   | 69.0 | 71.6   | 74.1 | 76.6   | 79.1 | 81.6   | 82.9 | 85.4   | 86.6 | 87.9   |
| 0.0    | 5°     | 59.0 | 61.5   | 65.3 | 67.8   | 70.3 | 72.8   | 75.3 | 76.6   | 77.8 | 79.1   |
| 0.0    | 7.5°   | 51.5 | 54.0   | 57.7 | 60.3   | 62.8 | 65.3   | 67.8 | 70.3   | 71.6 | 72.8   |
| 0.0    | 10°    | 43.9 | 47.7   | 50.2 | 54.0   | 56.5 | 59.0   | 61.5 | 64.0   | 66.5 | 67.8   |
| 0.0    | 12.5°  | 35.1 | 38.9   | 42.7 | 45.2   | 49.0 | 52.7   | 55.2 | 57.7   | 60.3 | 62.8   |
| 0.0    | 15°    | 27.6 | 31.4   | 35.1 | 37.7   | 41.4 | 45.2   | 49.0 | 51.5   | 54.0 | 56.5   |
| 0.0    | 17.5°  | 20.1 | 23.9   | 27.6 | 30.1   | 33.9 | 37.7   | 40.2 | 43.9   | 46.4 | 49.0   |
| 0.0    | 20°    | 10.0 | 13.8   | 17.6 | 21.3   | 25.1 | 28.9   | 31.4 | 35.1   | 37.7 | 40.2   |
| 0.0    | 22.5°  | 1.3  | 5.0    | 8.8  | 11.3   | 15.1 | 18.8   | 21.3 | 25.1   | 27.6 | 30.1   |
| 0.0    | 25°    | 0.0  | 1.3    | 3.8  | 5.0    | 6.3  | 8.8    | 11.3 | 13.8   | 16.3 | 18.8   |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.3    | 2.5  | 5.0    | 7.5  | 10.0   |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 2.5    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.3    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.3    | 1.3  | 2.5    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 2.5    | 3.8  | 6.3    | 7.5  | 8.8    |
|        | 87.5°  | 0.0  | 1.3    | 2.5  | 3.8    | 5.0  | 7.5    | 10.0 | 12.6   | 13.8 | 15.1   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 72.8 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.9 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.3 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 74.1 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.0 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.0 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.7 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.7 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.6 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.6 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12.6 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3.8  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 1.3  |        |      |        |      |        |      |        |      |        |      |        |
| 5.0  |        |      |        |      |        |      |        |      |        |      |        |
| 11.3 |        |      |        |      |        |      |        |      |        |      |        |
| 16.3 |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 |
| 0.0  | 2.5°   | 89.1   | 89.1 | 89.1   | 89.1 | 87.9   | 87.9 | 87.9   | 86.6 | 86.6   | 85.4 |
| 0.0  | 5°     | 81.6   | 82.9 | 82.9   | 82.9 | 82.9   | 82.9 | 82.9   | 82.9 | 81.6   | 81.6 |
| 0.0  | 7.5°   | 75.3   | 76.6 | 77.8   | 77.8 | 79.1   | 79.1 | 79.1   | 77.8 | 77.8   | 76.6 |
| 0.0  | 10°    | 71.6   | 72.8 | 72.8   | 74.1 | 74.1   | 74.1 | 74.1   | 74.1 | 74.1   | 74.1 |
| 0.0  | 12.5°  | 66.5   | 67.8 | 69.0   | 69.0 | 70.3   | 70.3 | 70.3   | 70.3 | 69.0   | 69.0 |
| 0.0  | 15°    | 60.3   | 62.8 | 64.0   | 65.3 | 65.3   | 66.5 | 66.5   | 66.5 | 66.5   | 66.5 |
| 0.0  | 17.5°  | 55.2   | 57.7 | 59.0   | 60.3 | 60.3   | 61.5 | 61.5   | 62.8 | 62.8   | 62.8 |
| 0.0  | 20°    | 45.2   | 47.7 | 49.0   | 51.5 | 52.7   | 54.0 | 55.2   | 56.5 | 56.5   | 57.7 |
| 0.0  | 22.5°  | 35.1   | 37.7 | 38.9   | 41.4 | 42.7   | 43.9 | 45.2   | 46.4 | 47.7   | 49.0 |
| 0.0  | 25°    | 25.1   | 27.6 | 28.9   | 31.4 | 32.6   | 33.9 | 35.1   | 36.4 | 36.4   | 37.7 |
| 0.0  | 27.5°  | 13.8   | 16.3 | 18.8   | 20.1 | 22.6   | 23.9 | 25.1   | 26.4 | 27.6   | 28.9 |
| 0.0  | 30°    | 6.3    | 7.5  | 8.8    | 11.3 | 12.6   | 13.8 | 15.1   | 17.6 | 18.8   | 20.1 |
| 0.0  | 32.5°  | 0.0    | 0.0  | 1.3    | 3.8  | 5.0    | 6.3  | 7.5    | 8.8  | 8.8    | 10.0 |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.3    | 2.5  | 3.8    | 5.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 2.5    | 2.5  | 2.5    | 3.8  | 3.8    | 3.8  | 3.8    | 3.8  | 3.8    | 3.8  |
|      | 82.5°  | 6.3    | 7.5  | 8.8    | 8.8  | 10.0   | 10.0 | 10.0   | 10.0 | 8.8    | 8.8  |
|      | 85°    | 12.6   | 13.8 | 15.1   | 15.1 | 16.3   | 16.3 | 16.3   | 16.3 | 16.3   | 16.3 |
|      | 87.5°  | 17.6   | 18.8 | 20.1   | 20.1 | 21.3   | 21.3 | 21.3   | 21.3 | 21.3   | 21.3 |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 72.8   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85.4   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 81.6   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 76.6   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 74.1   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 69.0   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 66.5   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 62.8   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 56.5   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 49.0   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 38.9   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30.1   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 21.3   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 12.6   | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 7.5    | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.5    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.5    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.3    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.3    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.3    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.3    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.3    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 3.8    |        |        |      |        |      |        |      |        |      |        |      |
| 8.8    |        |        |      |        |      |        |      |        |      |        |      |
| 16.3   |        |        |      |        |      |        |      |        |      |        |      |
| 21.3   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   | 72.8 | 72.8   |
| 0.0    | 2.5°   | 84.1 | 84.1   | 82.9 | 82.9   | 82.9 | 82.9   | 82.9 | 84.1   | 85.4 | 85.4   |
| 0.0    | 5°     | 80.3 | 80.3   | 79.1 | 79.1   | 79.1 | 80.3   | 80.3 | 81.6   | 82.9 | 84.1   |
| 0.0    | 7.5°   | 76.6 | 75.3   | 75.3 | 76.6   | 76.6 | 77.8   | 77.8 | 79.1   | 80.3 | 81.6   |
| 0.0    | 10°    | 74.1 | 72.8   | 72.8 | 72.8   | 74.1 | 74.1   | 75.3 | 76.6   | 77.8 | 79.1   |
| 0.0    | 12.5°  | 69.0 | 69.0   | 69.0 | 69.0   | 70.3 | 70.3   | 71.6 | 72.8   | 75.3 | 76.6   |
| 0.0    | 15°    | 66.5 | 65.3   | 65.3 | 65.3   | 65.3 | 66.5   | 66.5 | 69.0   | 71.6 | 72.8   |
| 0.0    | 17.5°  | 61.5 | 61.5   | 60.3 | 60.3   | 61.5 | 61.5   | 62.8 | 65.3   | 67.8 | 69.0   |
| 0.0    | 20°    | 56.5 | 55.2   | 54.0 | 54.0   | 55.2 | 55.2   | 56.5 | 59.0   | 61.5 | 62.8   |
| 0.0    | 22.5°  | 49.0 | 47.7   | 47.7 | 47.7   | 47.7 | 49.0   | 49.0 | 51.5   | 55.2 | 57.7   |
| 0.0    | 25°    | 38.9 | 40.2   | 40.2 | 41.4   | 41.4 | 42.7   | 43.9 | 46.4   | 50.2 | 52.7   |
| 0.0    | 27.5°  | 30.1 | 31.4   | 31.4 | 33.9   | 35.1 | 36.4   | 37.7 | 41.4   | 45.2 | 47.7   |
| 0.0    | 30°    | 22.6 | 23.9   | 25.1 | 26.4   | 28.9 | 31.4   | 33.9 | 37.7   | 41.4 | 43.9   |
| 0.0    | 32.5°  | 13.8 | 16.3   | 17.6 | 20.1   | 22.6 | 25.1   | 27.6 | 31.4   | 36.4 | 40.2   |
| 0.0    | 35°    | 10.0 | 11.3   | 13.8 | 15.1   | 17.6 | 20.1   | 22.6 | 27.6   | 31.4 | 36.4   |
| 0.0    | 37.5°  | 5.0  | 7.5    | 10.0 | 12.6   | 15.1 | 17.6   | 20.1 | 25.1   | 30.1 | 33.9   |
| 0.0    | 40°    | 3.8  | 6.3    | 7.5  | 10.0   | 13.8 | 16.3   | 18.8 | 23.9   | 28.9 | 33.9   |
| 0.0    | 42.5°  | 2.5  | 3.8    | 5.0  | 8.8    | 11.3 | 15.1   | 18.8 | 23.9   | 28.9 | 33.9   |
| 0.0    | 45°    | 2.5  | 2.5    | 3.8  | 7.5    | 11.3 | 16.3   | 20.1 | 25.1   | 28.9 | 33.9   |
| 0.0    | 47.5°  | 2.5  | 3.8    | 5.0  | 10.0   | 12.6 | 16.3   | 20.1 | 23.9   | 28.9 | 32.6   |
| 0.0    | 50°    | 3.8  | 5.0    | 6.3  | 11.3   | 13.8 | 17.6   | 20.1 | 25.1   | 28.9 | 33.9   |
| 0.0    | 52.5°  | 2.5  | 3.8    | 5.0  | 10.0   | 13.8 | 18.8   | 22.6 | 27.6   | 32.6 | 36.4   |
| 0.0    | 55°    | 1.3  | 1.3    | 1.3  | 7.5    | 15.1 | 21.3   | 28.9 | 32.6   | 37.7 | 41.4   |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 5.0    | 15.1 | 23.9   | 32.6 | 37.7   | 42.7 | 46.4   |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 5.0    | 15.1 | 23.9   | 32.6 | 38.9   | 45.2 | 51.5   |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 5.0    | 12.6 | 20.1   | 27.6 | 37.7   | 49.0 | 59.0   |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 3.8    | 10.0 | 16.3   | 22.6 | 37.7   | 52.7 | 66.5   |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 3.8    | 10.0 | 15.1   | 21.3 | 37.7   | 52.7 | 69.0   |
|        | 70°    | 0.0  | 0.0    | 0.0  | 3.8    | 10.0 | 16.3   | 22.6 | 37.7   | 52.7 | 67.8   |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 3.8    | 11.3 | 17.6   | 25.1 | 37.7   | 50.2 | 62.8   |
|        | 75°    | 0.0  | 0.0    | 0.0  | 5.0    | 11.3 | 18.8   | 26.4 | 37.7   | 49.0 | 59.0   |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 3.8    | 11.3 | 17.6   | 25.1 | 36.4   | 47.7 | 57.7   |
|        | 80°    | 3.8  | 2.5    | 2.5  | 6.3    | 11.3 | 16.3   | 21.3 | 32.6   | 45.2 | 56.5   |
|        | 82.5°  | 7.5  | 7.5    | 6.3  | 8.8    | 11.3 | 15.1   | 18.8 | 28.9   | 40.2 | 50.2   |
|        | 85°    | 15.1 | 15.1   | 13.8 | 15.1   | 15.1 | 16.3   | 17.6 | 22.6   | 27.6 | 32.6   |
|        | 87.5°  | 20.1 | 20.1   | 18.8 | 18.8   | 18.8 | 17.6   | 17.6 | 17.6   | 17.6 | 16.3   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 72.8 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 86.6 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.4 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.9 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.8 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75.3 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71.6 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65.3 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60.3 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.2 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 51.5 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.7 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 43.9 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.2 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38.9 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38.9 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38.9 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.7 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 36.4 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.7 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 41.4 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45.2 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 51.5 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.7 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 69.0 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 81.6 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 84.1 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.9 |        |      |        |      |        |      |        |      |        |      |        |
| 75.3 |        |      |        |      |        |      |        |      |        |      |        |
| 70.3 |        |      |        |      |        |      |        |      |        |      |        |
| 69.0 |        |      |        |      |        |      |        |      |        |      |        |
| 67.8 |        |      |        |      |        |      |        |      |        |      |        |
| 60.3 |        |      |        |      |        |      |        |      |        |      |        |
| 37.7 |        |      |        |      |        |      |        |      |        |      |        |
| 16.3 |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 72.8   | 72.8  | 72.8   | 72.8  | 72.8   | 72.8  | 72.8   | 72.8  | 72.8   | 72.8   |
| 0.0  | 2.5°   | 87.9   | 89.1  | 89.1   | 90.4  | 91.6   | 92.9  | 92.9   | 94.2  | 94.2   | 94.2   |
| 0.0  | 5°     | 86.6   | 89.1  | 90.4   | 91.6  | 92.9   | 94.2  | 95.4   | 96.7  | 97.9   | 97.9   |
| 0.0  | 7.5°   | 85.4   | 86.6  | 89.1   | 90.4  | 92.9   | 94.2  | 96.7   | 97.9  | 99.2   | 100.4  |
| 0.0  | 10°    | 82.9   | 85.4  | 87.9   | 90.4  | 92.9   | 95.4  | 97.9   | 100.4 | 102.9  | 104.2  |
| 0.0  | 12.5°  | 80.3   | 84.1  | 86.6   | 89.1  | 92.9   | 96.7  | 99.2   | 102.9 | 105.4  | 108.0  |
| 0.0  | 15°    | 79.1   | 81.6  | 85.4   | 87.9  | 92.9   | 97.9  | 101.7  | 106.7 | 111.7  | 115.5  |
| 0.0  | 17.5°  | 75.3   | 80.3  | 84.1   | 87.9  | 92.9   | 99.2  | 104.2  | 109.2 | 116.7  | 124.3  |
| 0.0  | 20°    | 70.3   | 74.1  | 79.1   | 82.9  | 90.4   | 96.7  | 104.2  | 110.5 | 121.8  | 133.1  |
| 0.0  | 22.5°  | 65.3   | 70.3  | 74.1   | 79.1  | 87.9   | 95.4  | 104.2  | 111.7 | 130.6  | 148.1  |
| 0.0  | 25°    | 60.3   | 66.5  | 71.6   | 76.6  | 86.6   | 96.7  | 106.7  | 116.7 | 148.1  | 179.5  |
| 0.0  | 27.5°  | 57.7   | 62.8  | 69.0   | 74.1  | 86.6   | 100.4 | 113.0  | 125.5 | 175.7  | 224.7  |
| 0.0  | 30°    | 54.0   | 60.3  | 65.3   | 71.6  | 87.9   | 104.2 | 120.5  | 136.8 | 213.4  | 290.0  |
| 0.0  | 32.5°  | 50.2   | 56.5  | 62.8   | 69.0  | 90.4   | 111.7 | 131.8  | 153.2 | 253.6  | 352.8  |
| 0.0  | 35°    | 46.4   | 54.0  | 60.3   | 66.5  | 94.2   | 123.0 | 150.6  | 178.3 | 290.0  | 400.5  |
| 0.0  | 37.5°  | 45.2   | 52.7  | 59.0   | 65.3  | 95.4   | 124.3 | 154.4  | 183.3 | 293.8  | 404.2  |
| 0.0  | 40°    | 46.4   | 52.7  | 60.3   | 66.5  | 91.6   | 116.7 | 140.6  | 165.7 | 281.2  | 395.4  |
| 0.0  | 42.5°  | 46.4   | 54.0  | 61.5   | 69.0  | 89.1   | 109.2 | 129.3  | 149.4 | 277.4  | 405.5  |
| 0.0  | 45°    | 45.2   | 52.7  | 60.3   | 67.8  | 86.6   | 104.2 | 123.0  | 140.6 | 300.0  | 458.2  |
| 0.0  | 47.5°  | 43.9   | 51.5  | 59.0   | 66.5  | 85.4   | 104.2 | 123.0  | 141.9 | 387.9  | 632.7  |
| 0.0  | 50°    | 43.9   | 51.5  | 57.7   | 64.0  | 86.6   | 110.5 | 133.1  | 155.7 | 564.9  | 972.9  |
| 0.0  | 52.5°  | 46.4   | 52.7  | 57.7   | 62.8  | 89.1   | 116.7 | 143.1  | 169.5 | 718.1  | 1265.4 |
| 0.0  | 55°    | 50.2   | 54.0  | 59.0   | 62.8  | 95.4   | 126.8 | 159.4  | 190.8 | 764.5  | 1338.2 |
| 0.0  | 57.5°  | 55.2   | 59.0  | 62.8   | 66.5  | 106.7  | 146.9 | 185.8  | 226.0 | 768.3  | 1309.3 |
| 0.0  | 60°    | 61.5   | 66.5  | 70.3   | 74.1  | 116.7  | 160.7 | 203.4  | 246.0 | 695.5  | 1143.6 |
| 0.0  | 62.5°  | 75.3   | 81.6  | 86.6   | 92.9  | 134.3  | 174.5 | 215.9  | 256.1 | 577.5  | 898.8  |
| 0.0  | 65°    | 86.6   | 91.6  | 96.7   | 101.7 | 141.9  | 183.3 | 223.5  | 263.6 | 489.6  | 715.6  |
| 0.0  | 67.5°  | 89.1   | 94.2  | 97.9   | 102.9 | 144.4  | 185.8 | 226.0  | 267.4 | 419.3  | 569.9  |
|      | 70°    | 90.4   | 96.7  | 104.2  | 110.5 | 153.2  | 195.8 | 237.3  | 279.9 | 371.6  | 463.2  |
|      | 72.5°  | 86.6   | 99.2  | 110.5  | 121.8 | 161.9  | 200.9 | 241.0  | 279.9 | 345.2  | 410.5  |
|      | 75°    | 86.6   | 104.2 | 120.5  | 136.8 | 167.0  | 195.8 | 226.0  | 254.8 | 305.1  | 355.3  |
|      | 77.5°  | 91.6   | 114.2 | 136.8  | 159.4 | 177.0  | 193.3 | 210.9  | 227.2 | 259.9  | 292.5  |
|      | 80°    | 91.6   | 115.5 | 138.1  | 161.9 | 169.5  | 178.3 | 185.8  | 193.3 | 197.1  | 200.9  |
|      | 82.5°  | 79.1   | 97.9  | 116.7  | 135.6 | 126.8  | 118.0 | 109.2  | 100.4 | 94.2   | 86.6   |
|      | 85°    | 40.2   | 43.9  | 46.4   | 49.0  | 45.2   | 41.4  | 37.7   | 33.9  | 31.4   | 27.6   |
|      | 87.5°  | 16.3   | 16.3  | 15.1   | 15.1  | 15.1   | 15.1  | 13.8   | 13.8  | 13.8   | 13.8   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 72.8   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94.2   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.9   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 101.7  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106.7  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 111.7  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121.8  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 134.3  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 154.4  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 197.1  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 267.4  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 371.6  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 503.4  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 628.9  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 714.3  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 778.3  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 842.3  | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 967.9  | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1218.9 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1857.9 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2845.9 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3582.8 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3664.4 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3306.6 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2827.1 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2209.4 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1669.6 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1232.8 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 872.5  |        |        |      |        |      |        |      |        |      |        |      |
| 649.0  |        |        |      |        |      |        |      |        |      |        |      |
| 472.0  |        |        |      |        |      |        |      |        |      |        |      |
| 355.3  |        |        |      |        |      |        |      |        |      |        |      |
| 199.6  |        |        |      |        |      |        |      |        |      |        |      |
| 90.4   |        |        |      |        |      |        |      |        |      |        |      |
| 26.4   |        |        |      |        |      |        |      |        |      |        |      |
| 12.6   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5° | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 72.8   | 72.8   | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    |
| 0.0    | 2.5°   | 94.2   | 92.9   | 92.9    | 91.6    | 90.4    | 89.1    | 87.9    | 86.6    | 85.4    | 84.1    |
| 0.0    | 5°     | 97.9   | 97.9   | 97.9    | 96.7    | 96.7    | 95.4    | 95.4    | 94.2    | 92.9    | 91.6    |
| 0.0    | 7.5°   | 101.7  | 102.9  | 102.9   | 104.2   | 104.2   | 104.2   | 104.2   | 102.9   | 102.9   | 102.9   |
| 0.0    | 10°    | 108.0  | 109.2  | 110.5   | 111.7   | 113.0   | 114.2   | 114.2   | 115.5   | 115.5   | 115.5   |
| 0.0    | 12.5°  | 115.5  | 119.3  | 121.8   | 125.5   | 128.0   | 131.8   | 134.3   | 138.1   | 140.6   | 143.1   |
| 0.0    | 15°    | 126.8  | 133.1  | 140.6   | 146.9   | 153.2   | 161.9   | 172.0   | 180.8   | 189.6   | 203.4   |
| 0.0    | 17.5°  | 143.1  | 163.2  | 183.3   | 202.1   | 222.2   | 266.1   | 310.1   | 352.8   | 396.7   | 460.7   |
| 0.0    | 20°    | 174.5  | 234.8  | 293.8   | 354.0   | 413.0   | 567.4   | 720.6   | 875.0   | 1028.1  | 1192.6  |
| 0.0    | 22.5°  | 244.8  | 392.9  | 541.1   | 689.2   | 837.3   | 1159.9  | 1481.3  | 1803.9  | 2125.3  | 2503.2  |
| 0.0    | 25°    | 355.3  | 627.7  | 900.1   | 1171.2  | 1443.7  | 1948.3  | 2454.2  | 2958.9  | 3463.5  | 3954.4  |
| 0.0    | 27.5°  | 517.2  | 934.0  | 1350.8  | 1766.3  | 2183.1  | 2867.2  | 3552.6  | 4236.8  | 4921.0  | 5475.8  |
| 0.0    | 30°    | 716.8  | 1281.7 | 1846.6  | 2411.5  | 2976.4  | 3754.8  | 4533.1  | 5310.1  | 6088.5  | 6694.8  |
| 0.0    | 32.5°  | 905.1  | 1596.8 | 2288.5  | 2979.0  | 3670.7  | 4556.9  | 5444.5  | 6330.7  | 7217.0  | 7879.8  |
| 0.0    | 35°    | 1028.1 | 1864.2 | 2701.5  | 3537.6  | 4373.6  | 5332.7  | 6291.8  | 7249.7  | 8208.8  | 8965.7  |
| 0.0    | 37.5°  | 1151.2 | 2116.5 | 3080.6  | 4046.0  | 5010.1  | 6063.4  | 7116.6  | 8169.8  | 9223.1  | 10158.3 |
| 0.0    | 40°    | 1289.2 | 2421.6 | 3552.6  | 4685.0  | 5816.0  | 7063.9  | 8310.4  | 9558.3  | 10804.8 | 12124.2 |
| 0.0    | 42.5°  | 1529.0 | 2927.5 | 4327.2  | 5725.7  | 7124.1  | 8774.9  | 10425.7 | 12075.2 | 13726.0 | 15609.1 |
| 0.0    | 45°    | 1979.7 | 3950.6 | 5922.8  | 7893.7  | 9864.6  | 12051.4 | 14239.5 | 16426.3 | 18613.1 | 21118.8 |
| 0.0    | 47.5°  | 3083.1 | 5794.7 | 8505.0  | 11216.6 | 13926.9 | 16288.2 | 18648.3 | 21009.6 | 23369.6 | 25865.3 |
| 0.0    | 50°    | 4717.6 | 7873.6 | 11029.5 | 14184.2 | 17340.2 | 19476.8 | 21612.1 | 23748.8 | 25884.1 | 28258.0 |
| 0.0    | 52.5°  | 5900.2 | 9187.9 | 12476.9 | 15764.7 | 19052.5 | 20980.7 | 22910.2 | 24838.4 | 26766.6 | 28984.8 |
| 0.0    | 55°    | 5989.3 | 9258.2 | 12528.4 | 15797.4 | 19066.3 | 21003.3 | 22940.3 | 24877.3 | 26814.3 | 29165.6 |
| 0.0    | 57.5°  | 5302.6 | 8545.2 | 11786.5 | 15029.1 | 18270.4 | 20476.1 | 22680.5 | 24886.1 | 27090.5 | 29632.6 |
| 0.0    | 60°    | 4510.5 | 7754.3 | 10996.9 | 14240.7 | 17483.3 | 20024.1 | 22566.2 | 25107.1 | 27647.9 | 30029.3 |
| 0.0    | 62.5°  | 3518.8 | 6855.5 | 10193.5 | 13530.2 | 16866.9 | 19446.7 | 22026.4 | 24604.9 | 27184.7 | 28971.0 |
| 0.0    | 65°    | 2622.4 | 5862.5 | 9102.6  | 12341.4 | 15581.4 | 17647.7 | 19714.1 | 21779.1 | 23845.4 | 24951.4 |
| 0.0    | 67.5°  | 1895.6 | 4690.0 | 7483.2  | 10277.6 | 13070.7 | 14549.5 | 16028.3 | 17505.9 | 18984.7 | 19830.8 |
|        | 70°    | 1281.7 | 3217.5 | 5152.0  | 7087.7  | 9022.2  | 10237.4 | 11453.8 | 12669.0 | 13884.2 | 15026.6 |
|        | 72.5°  | 887.5  | 1974.7 | 3063.1  | 4150.2  | 5237.3  | 6460.0  | 7681.5  | 8904.2  | 10125.7 | 11334.6 |
|        | 75°    | 588.8  | 1083.4 | 1579.2  | 2073.8  | 2568.5  | 3473.6  | 4379.9  | 5285.0  | 6190.1  | 6910.7  |
|        | 77.5°  | 418.0  | 566.2  | 715.6   | 863.7   | 1011.8  | 1181.3  | 1352.0  | 1521.5  | 1691.0  | 1948.3  |
|        | 80°    | 198.3  | 217.2  | 236.0   | 253.6   | 272.4   | 333.9   | 395.4   | 456.9   | 518.5   | 583.7   |
|        | 82.5°  | 94.2   | 101.7  | 109.2   | 115.5   | 123.0   | 129.3   | 135.6   | 141.9   | 148.1   | 141.9   |
|        | 85°    | 25.1   | 25.1   | 26.4    | 26.4    | 26.4    | 26.4    | 26.4    | 26.4    | 26.4    | 25.1    |
|        | 87.5°  | 11.3   | 11.3   | 11.3    | 11.3    | 11.3    | 11.3    | 11.3    | 10.0    | 10.0    | 8.8     |
|        | 90°    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 72.8    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.9    | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 90.4    | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.7   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 116.7   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 144.4   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 218.4   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 523.5   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1358.3  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2881.0  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4445.2  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6030.7  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7302.4  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8543.9  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9722.7  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 11094.8 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13443.6 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17492.1 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23624.5 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28360.9 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30631.9 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31203.0 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31518.1 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32174.7 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32409.4 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30758.6 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26058.6 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20678.2 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16167.7 |        |      |        |      |        |      |        |      |        |      |        |
| 12543.5 |        |      |        |      |        |      |        |      |        |      |        |
| 7631.3  |        |      |        |      |        |      |        |      |        |      |        |
| 2205.7  |        |      |        |      |        |      |        |      |        |      |        |
| 649.0   |        |      |        |      |        |      |        |      |        |      |        |
| 134.3   |        |      |        |      |        |      |        |      |        |      |        |
| 23.9    |        |      |        |      |        |      |        |      |        |      |        |
| 8.8     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    |
| 0.0  | 2.5°   | 81.6    | 80.3    | 79.1    | 77.8    | 76.6    | 74.1    | 74.1    | 72.8    | 72.8    |
| 0.0  | 5°     | 89.1    | 87.9    | 86.6    | 85.4    | 85.4    | 84.1    | 82.9    | 82.9    | 81.6    |
| 0.0  | 7.5°   | 101.7   | 100.4   | 99.2    | 97.9    | 97.9    | 96.7    | 96.7    | 95.4    | 95.4    |
| 0.0  | 10°    | 116.7   | 116.7   | 116.7   | 116.7   | 116.7   | 115.5   | 115.5   | 115.5   | 114.2   |
| 0.0  | 12.5°  | 146.9   | 148.1   | 150.6   | 153.2   | 156.9   | 156.9   | 156.9   | 155.7   | 155.7   |
| 0.0  | 15°    | 232.2   | 246.0   | 256.1   | 266.1   | 274.9   | 295.0   | 292.5   | 288.7   | 286.2   |
| 0.0  | 17.5°  | 587.5   | 650.3   | 684.2   | 716.8   | 750.7   | 843.6   | 828.5   | 813.5   | 799.7   |
| 0.0  | 20°    | 1522.7  | 1687.2  | 1796.4  | 1905.6  | 2016.1  | 2190.6  | 2147.9  | 2105.2  | 2062.5  |
| 0.0  | 22.5°  | 3257.6  | 3635.5  | 3800.0  | 3964.4  | 4127.6  | 4338.5  | 4201.7  | 4064.8  | 3929.3  |
| 0.0  | 25°    | 4934.8  | 5425.6  | 5703.1  | 5980.5  | 6256.7  | 6377.2  | 6198.9  | 6019.4  | 5841.2  |
| 0.0  | 27.5°  | 6585.6  | 7140.4  | 7385.2  | 7628.8  | 7873.6  | 8125.9  | 7905.0  | 7682.8  | 7461.8  |
| 0.0  | 30°    | 7908.7  | 8515.1  | 8779.9  | 9043.6  | 9308.4  | 9484.2  | 9255.7  | 9026.0  | 8797.5  |
| 0.0  | 32.5°  | 9206.8  | 9869.6  | 10159.6 | 10449.6 | 10738.3 | 10990.6 | 10709.4 | 10427.0 | 10145.8 |
| 0.0  | 35°    | 10478.4 | 11235.4 | 11634.6 | 12033.8 | 12433.0 | 12667.8 | 12333.8 | 11998.7 | 11664.7 |
| 0.0  | 37.5°  | 12030.0 | 12965.3 | 13412.2 | 13859.1 | 14306.0 | 14734.1 | 14366.3 | 13997.2 | 13629.4 |
| 0.0  | 40°    | 14762.9 | 16082.3 | 16767.7 | 17454.4 | 18139.8 | 18692.2 | 18227.7 | 17763.2 | 17298.8 |
| 0.0  | 42.5°  | 19375.1 | 21258.1 | 22243.6 | 23227.8 | 24213.2 | 25075.7 | 24587.3 | 24099.0 | 23610.7 |
| 0.0  | 45°    | 26130.2 | 28635.8 | 29837.2 | 31037.3 | 32238.7 | 32868.9 | 32165.9 | 31461.6 | 30758.6 |
| 0.0  | 47.5°  | 30855.3 | 33351.0 | 34420.5 | 35490.1 | 36559.6 | 37278.9 | 36419.0 | 35559.1 | 34700.5 |
| 0.0  | 50°    | 33004.5 | 35378.3 | 36451.7 | 37523.7 | 38597.1 | 39168.3 | 38175.3 | 37181.0 | 36188.0 |
| 0.0  | 52.5°  | 33420.0 | 35638.2 | 36918.7 | 38200.4 | 39480.8 | 40244.1 | 39071.6 | 37897.8 | 36725.3 |
| 0.0  | 55°    | 33869.4 | 36220.7 | 37705.8 | 39192.1 | 40677.2 | 41734.2 | 40408.5 | 39081.6 | 37756.0 |
| 0.0  | 57.5°  | 34715.5 | 37257.6 | 38738.9 | 40219.0 | 41700.3 | 42597.9 | 41268.5 | 39937.8 | 38608.4 |
| 0.0  | 60°    | 34790.8 | 37171.0 | 38443.9 | 39718.1 | 40991.0 | 41555.9 | 40284.3 | 39011.3 | 37739.7 |
| 0.0  | 62.5°  | 32545.0 | 34331.4 | 35215.1 | 36098.9 | 36982.7 | 37596.6 | 36269.6 | 34941.5 | 33614.6 |
| 0.0  | 65°    | 27164.6 | 28270.5 | 28974.8 | 29679.0 | 30383.3 | 31115.2 | 29900.0 | 28684.8 | 27469.6 |
| 0.0  | 67.5°  | 21524.3 | 22370.4 | 23298.1 | 24225.8 | 25153.5 | 25935.6 | 24962.7 | 23988.5 | 23015.6 |
|      | 70°    | 17310.1 | 18451.2 | 19494.4 | 20537.6 | 21580.8 | 22221.0 | 21244.3 | 20266.4 | 19289.7 |
|      | 72.5°  | 13752.4 | 14961.3 | 15832.5 | 16702.5 | 17573.7 | 17730.6 | 17012.5 | 16294.5 | 15577.7 |
|      | 75°    | 8350.6  | 9071.2  | 9088.8  | 9105.1  | 9122.6  | 9272.0  | 8677.0  | 8082.0  | 7488.2  |
|      | 77.5°  | 2463.0  | 2720.3  | 2932.5  | 3143.4  | 3355.6  | 3611.6  | 3393.2  | 3173.5  | 2955.1  |
|      | 80°    | 713.0   | 778.3   | 833.6   | 887.5   | 942.8   | 910.1   | 858.7   | 807.2   | 755.7   |
|      | 82.5°  | 128.0   | 120.5   | 119.3   | 118.0   | 118.0   | 111.7   | 101.7   | 91.6    | 81.6    |
|      | 85°    | 22.6    | 21.3    | 20.1    | 18.8    | 17.6    | 16.3    | 13.8    | 12.6    | 10.0    |
|      | 87.5°  | 7.5     | 6.3     | 5.0     | 3.8     | 3.8     | 1.3     | 1.3     | 1.3     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    | 72.8    |
| 0.0  | 0.0    | 2.5°   | 71.6    | 70.3    | 70.3    | 70.3    | 70.3    | 69.0    | 69.0    | 69.0    | 69.0    |
| 0.0  | 0.0    | 5°     | 79.1    | 79.1    | 77.8    | 77.8    | 76.6    | 76.6    | 75.3    | 75.3    | 74.1    |
| 0.0  | 0.0    | 7.5°   | 92.9    | 91.6    | 90.4    | 89.1    | 87.9    | 85.4    | 84.1    | 82.9    | 82.9    |
| 0.0  | 0.0    | 10°    | 111.7   | 109.2   | 108.0   | 105.4   | 104.2   | 101.7   | 99.2    | 96.7    | 94.2    |
| 0.0  | 0.0    | 12.5°  | 146.9   | 141.9   | 138.1   | 133.1   | 128.0   | 124.3   | 119.3   | 115.5   | 110.5   |
| 0.0  | 0.0    | 15°    | 254.8   | 242.3   | 228.5   | 212.2   | 194.6   | 178.3   | 160.7   | 150.6   | 139.3   |
| 0.0  | 0.0    | 17.5°  | 651.5   | 586.2   | 519.7   | 465.7   | 411.8   | 359.0   | 305.1   | 266.1   | 227.2   |
| 0.0  | 0.0    | 20°    | 1658.3  | 1477.5  | 1296.8  | 1118.5  | 939.0   | 760.7   | 581.2   | 490.8   | 400.5   |
| 0.0  | 0.0    | 22.5°  | 3120.8  | 2785.6  | 2449.2  | 2124.1  | 1797.7  | 1472.5  | 1147.4  | 942.8   | 739.4   |
| 0.0  | 0.0    | 25°    | 4816.8  | 4395.0  | 3973.2  | 3438.4  | 2902.4  | 2367.6  | 1832.8  | 1500.1  | 1167.5  |
| 0.0  | 0.0    | 27.5°  | 6268.0  | 5782.2  | 5296.3  | 4646.1  | 3995.8  | 3345.5  | 2695.2  | 2199.4  | 1704.8  |
| 0.0  | 0.0    | 30°    | 7524.6  | 7002.4  | 6480.1  | 5723.2  | 4966.2  | 4209.2  | 3452.2  | 2832.1  | 2211.9  |
| 0.0  | 0.0    | 32.5°  | 8614.2  | 7989.1  | 7363.9  | 6583.1  | 5802.2  | 5021.4  | 4240.6  | 3479.8  | 2719.1  |
| 0.0  | 0.0    | 35°    | 9870.8  | 9141.5  | 8410.9  | 7544.7  | 6677.2  | 5811.0  | 4944.8  | 4086.2  | 3226.3  |
| 0.0  | 0.0    | 37.5°  | 11467.6 | 10572.6 | 9676.3  | 8710.9  | 7745.5  | 6781.4  | 5816.0  | 4834.4  | 3852.7  |
| 0.0  | 0.0    | 40°    | 14524.4 | 13369.5 | 12214.6 | 10988.1 | 9760.4  | 8533.9  | 7307.4  | 6102.3  | 4897.1  |
| 0.0  | 0.0    | 42.5°  | 20001.5 | 18441.1 | 16880.7 | 15248.8 | 13615.6 | 11983.6 | 10350.4 | 8650.6  | 6949.6  |
| 0.0  | 0.0    | 45°    | 26182.9 | 24247.1 | 22310.1 | 20478.6 | 18645.8 | 16814.2 | 14982.6 | 12650.2 | 10317.7 |
| 0.0  | 0.0    | 47.5°  | 29659.0 | 27568.8 | 25478.6 | 23745.0 | 22011.4 | 20277.7 | 18544.1 | 16029.6 | 13515.1 |
| 0.0  | 0.0    | 50°    | 30938.2 | 28810.3 | 26682.5 | 25087.0 | 23490.2 | 21894.6 | 20297.8 | 17779.6 | 15260.1 |
| 0.0  | 0.0    | 52.5°  | 31210.6 | 29040.1 | 26869.6 | 25264.0 | 23658.4 | 22054.0 | 20448.4 | 17946.5 | 15444.6 |
| 0.0  | 0.0    | 55°    | 31770.5 | 29441.8 | 27111.8 | 25281.5 | 23451.2 | 21620.9 | 19790.6 | 17248.5 | 14706.5 |
| 0.0  | 0.0    | 57.5°  | 32502.3 | 30114.7 | 27727.0 | 25641.8 | 23556.7 | 21472.8 | 19387.7 | 16608.3 | 13829.0 |
| 0.0  | 0.0    | 60°    | 32310.3 | 30232.7 | 28153.8 | 25920.5 | 23686.0 | 21452.7 | 19218.2 | 16161.4 | 13103.4 |
| 0.0  | 0.0    | 62.5°  | 28976.0 | 27321.5 | 25665.7 | 23829.1 | 21991.3 | 20154.7 | 18318.1 | 15170.9 | 12023.8 |
| 0.0  | 0.0    | 65°    | 23837.9 | 22630.2 | 21422.6 | 19945.0 | 18466.2 | 16988.7 | 15511.1 | 12689.1 | 9868.3  |
| 0.0  | 0.0    | 67.5°  | 19319.9 | 17959.1 | 16597.0 | 15419.5 | 14240.7 | 13063.2 | 11884.4 | 9663.7  | 7443.0  |
|      |        | 70°    | 15349.2 | 13869.1 | 12387.8 | 11237.9 | 10086.8 | 8936.9  | 7787.0  | 6310.7  | 4835.6  |
|      |        | 72.5°  | 12189.5 | 10855.0 | 9520.6  | 8294.1  | 7066.4  | 5839.9  | 4612.2  | 3739.7  | 2867.2  |
|      |        | 75°    | 5826.1  | 5292.6  | 4759.0  | 4117.6  | 3476.1  | 2834.6  | 2193.1  | 1812.7  | 1433.6  |
|      |        | 77.5°  | 2159.2  | 1871.7  | 1583.0  | 1321.9  | 1060.8  | 800.9   | 539.8   | 494.6   | 449.4   |
|      |        | 80°    | 558.6   | 487.1   | 414.3   | 362.8   | 310.1   | 258.6   | 207.1   | 187.0   | 168.2   |
|      |        | 82.5°  | 64.0    | 59.0    | 55.2    | 52.7    | 49.0    | 46.4    | 42.7    | 38.9    | 35.1    |
|      |        | 85°    | 3.8     | 2.5     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 72.8   | 72.8   |
| 0.0    | 0.0  | 2.5°   | 67.8   | 66.5   |
| 0.0    | 0.0  | 5°     | 71.6   | 70.3   |
| 0.0    | 0.0  | 7.5°   | 79.1   | 76.6   |
| 0.0    | 0.0  | 10°    | 86.6   | 84.1   |
| 0.0    | 0.0  | 12.5°  | 97.9   | 94.2   |
| 0.0    | 0.0  | 15°    | 110.5  | 102.9  |
| 0.0    | 0.0  | 17.5°  | 131.8  | 115.5  |
| 0.0    | 0.0  | 20°    | 178.3  | 136.8  |
| 0.0    | 0.0  | 22.5°  | 251.1  | 170.7  |
| 0.0    | 0.0  | 25°    | 369.1  | 236.0  |
| 0.0    | 0.0  | 27.5°  | 513.4  | 313.8  |
| 0.0    | 0.0  | 30°    | 682.9  | 392.9  |
| 0.0    | 0.0  | 32.5°  | 832.3  | 468.2  |
| 0.0    | 0.0  | 35°    | 1026.9 | 544.8  |
| 0.0    | 0.0  | 37.5°  | 1266.7 | 642.7  |
| 0.0    | 0.0  | 40°    | 1638.2 | 790.9  |
| 0.0    | 0.0  | 42.5°  | 2307.3 | 1064.5 |
| 0.0    | 0.0  | 45°    | 3747.2 | 1840.3 |
| 0.0    | 0.0  | 47.5°  | 5765.8 | 3044.2 |
| 0.0    | 0.0  | 50°    | 7053.8 | 3885.3 |
| 0.0    | 0.0  | 52.5°  | 7159.3 | 3879.0 |
| 0.0    | 0.0  | 55°    | 6535.4 | 3448.5 |
| 0.0    | 0.0  | 57.5°  | 5576.3 | 2882.3 |
| 0.0    | 0.0  | 60°    | 4634.8 | 2279.7 |
| 0.0    | 0.0  | 62.5°  | 3651.8 | 1574.2 |
| 0.0    | 0.0  | 65°    | 2668.9 | 1113.5 |
| 0.0    | 0.0  | 67.5°  | 1916.9 | 832.3  |
|        |      | 70°    | 1260.4 | 637.7  |
|        |      | 72.5°  | 821.0  | 519.7  |
|        |      | 75°    | 552.4  | 430.6  |
|        |      | 77.5°  | 322.6  | 286.2  |
|        |      | 80°    | 114.2  | 100.4  |
|        |      | 82.5°  | 21.3   | 15.1   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1065049

CATALOG NUMBER: GLAN-SA7A-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-16

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-940-U-5WQ

Data in this report applies to families of products including GSS-SB1A-940-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-16  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-940-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3856  
 CIE  $u'$ : 0.2261  
 CIE  $v'$ : 0.5084  
 Duv: 0.0032  
 CIE x: 0.3896  
 CIE y: 0.3894  
 CIE z: 0.2211  
 Peak Wavelength (nm): 614  
 Dominant Wavelength (nm): 578  
 Purity: 33.77304  
 R<sub>f</sub>: 91.8  
 R<sub>g</sub>: 98.4

CRI (Ra): 92.1  
 R1: 91.8  
 R2: 94.1  
 R3: 95.3  
 R4: 92.8  
 R5: 91.0  
 R6: 91.6  
 R7: 95.0  
 R8: 85.2  
 R9: 60.7  
 R10: 85.2  
 R11: 92.4  
 R12: 74.5  
 R13: 92.3  
 R14: 97.0  
 R15: 88.5



### Test Conditions

Stabilization Time: 23M  
 Operation Time: 1H 23M  
 Sphere Temperature (°C): 25.2


REPORT NUMBER: SP1-2407-184-16

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |



REPORT NUMBER: SP1-2407-184-16

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 492                                  | NR                             | 620               | 993                                  | NR                             | 750               | 73                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 539                                  | NR                             | 625               | 978                                  | NR                             | 755               | 62                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 583                                  | NR                             | 630               | 962                                  | NR                             | 760               | 54                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 623                                  | NR                             | 635               | 933                                  | NR                             | 765               | 46                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 661                                  | NR                             | 640               | 898                                  | NR                             | 770               | 39                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 698                                  | NR                             | 645               | 855                                  | NR                             | 775               | 34                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 733                                  | NR                             | 650               | 810                                  | NR                             | 780               | 29                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 764                                  | NR                             | 655               | 759                                  | NR                             | 785               | 25                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 794                                  | NR                             | 660               | 704                                  | NR                             | 790               | 21                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 6                                    | NR                             | 535               | 820                                  | NR                             | 665               | 651                                  | NR                             | 795               | 18                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 12                                   | NR                             | 540               | 837                                  | NR                             | 670               | 592                                  | NR                             | 800               | 16                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 22                                   | NR                             | 545               | 853                                  | NR                             | 675               | 538                                  | NR                             | 805               | 13                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 42                                   | NR                             | 550               | 864                                  | NR                             | 680               | 486                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 79                                   | NR                             | 555               | 872                                  | NR                             | 685               | 435                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 147                                  | NR                             | 560               | 876                                  | NR                             | 690               | 389                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 278                                  | NR                             | 565               | 883                                  | NR                             | 695               | 344                                  | NR                             | 825               | 7                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 515                                  | NR                             | 570               | 891                                  | NR                             | 700               | 303                                  | NR                             | 830               | 6                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 832                                  | NR                             | 575               | 900                                  | NR                             | 705               | 266                                  | NR                             | 835               | 5                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 874                                  | NR                             | 580               | 914                                  | NR                             | 710               | 233                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 659                                  | NR                             | 585               | 927                                  | NR                             | 715               | 203                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 567                                  | NR                             | 590               | 944                                  | NR                             | 720               | 178                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 485                                  | NR                             | 595               | 961                                  | NR                             | 725               | 154                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 401                                  | NR                             | 600               | 975                                  | NR                             | 730               | 133                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 393                                  | NR                             | 605               | 988                                  | NR                             | 735               | 115                                  | NR                             | 865               | 2                                    | NR                             | 995               | 1                                    | NR                             |
| 480               | 417                                  | NR                             | 610               | 996                                  | NR                             | 740               | 98                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 448                                  | NR                             | 615               | 998                                  | NR                             | 745               | 85                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-16

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.72

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 492                         | NR               | 620       | 993                         | NR               | 750       | 73                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 539                         | NR               | 625       | 978                         | NR               | 755       | 62                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 583                         | NR               | 630       | 962                         | NR               | 760       | 54                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 623                         | NR               | 635       | 933                         | NR               | 765       | 46                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 661                         | NR               | 640       | 898                         | NR               | 770       | 39                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 698                         | NR               | 645       | 855                         | NR               | 775       | 34                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 733                         | NR               | 650       | 810                         | NR               | 780       | 29                          | NR               | 910       | 1                           | NR               |
| 395       | 1                           | NR               | 525       | 764                         | NR               | 655       | 759                         | NR               | 785       | 25                          | NR               | 915       | 1                           | NR               |
| 400       | 3                           | NR               | 530       | 794                         | NR               | 660       | 704                         | NR               | 790       | 21                          | NR               | 920       | 1                           | NR               |
| 405       | 6                           | NR               | 535       | 820                         | NR               | 665       | 651                         | NR               | 795       | 18                          | NR               | 925       | 1                           | NR               |
| 410       | 12                          | NR               | 540       | 837                         | NR               | 670       | 592                         | NR               | 800       | 16                          | NR               | 930       | 1                           | NR               |
| 415       | 22                          | NR               | 545       | 853                         | NR               | 675       | 538                         | NR               | 805       | 13                          | NR               | 935       | 0                           | NR               |
| 420       | 42                          | NR               | 550       | 864                         | NR               | 680       | 486                         | NR               | 810       | 12                          | NR               | 940       | 0                           | NR               |
| 425       | 79                          | NR               | 555       | 872                         | NR               | 685       | 435                         | NR               | 815       | 10                          | NR               | 945       | 0                           | NR               |
| 430       | 147                         | NR               | 560       | 876                         | NR               | 690       | 389                         | NR               | 820       | 9                           | NR               | 950       | 0                           | NR               |
| 435       | 278                         | NR               | 565       | 883                         | NR               | 695       | 344                         | NR               | 825       | 7                           | NR               | 955       | 0                           | NR               |
| 440       | 515                         | NR               | 570       | 891                         | NR               | 700       | 303                         | NR               | 830       | 6                           | NR               | 960       | 0                           | NR               |
| 445       | 832                         | NR               | 575       | 900                         | NR               | 705       | 266                         | NR               | 835       | 5                           | NR               | 965       | 0                           | NR               |
| 450       | 874                         | NR               | 580       | 914                         | NR               | 710       | 233                         | NR               | 840       | 5                           | NR               | 970       | 0                           | NR               |
| 455       | 659                         | NR               | 585       | 927                         | NR               | 715       | 203                         | NR               | 845       | 4                           | NR               | 975       | 0                           | NR               |
| 460       | 567                         | NR               | 590       | 944                         | NR               | 720       | 178                         | NR               | 850       | 4                           | NR               | 980       | 0                           | NR               |
| 465       | 485                         | NR               | 595       | 961                         | NR               | 725       | 154                         | NR               | 855       | 3                           | NR               | 985       | 0                           | NR               |
| 470       | 401                         | NR               | 600       | 975                         | NR               | 730       | 133                         | NR               | 860       | 3                           | NR               | 990       | 0                           | NR               |
| 475       | 393                         | NR               | 605       | 988                         | NR               | 735       | 115                         | NR               | 865       | 2                           | NR               | 995       | 1                           | NR               |
| 480       | 417                         | NR               | 610       | 996                         | NR               | 740       | 98                          | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 448                         | NR               | 615       | 998                         | NR               | 745       | 85                          | NR               | 875       | 2                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-16

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.52


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 492                                    | NR                             | 620               | 993                                    | NR                             | 750               | 73                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 539                                    | NR                             | 625               | 978                                    | NR                             | 755               | 62                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 583                                    | NR                             | 630               | 962                                    | NR                             | 760               | 54                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 623                                    | NR                             | 635               | 933                                    | NR                             | 765               | 46                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 661                                    | NR                             | 640               | 898                                    | NR                             | 770               | 39                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 698                                    | NR                             | 645               | 855                                    | NR                             | 775               | 34                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 733                                    | NR                             | 650               | 810                                    | NR                             | 780               | 29                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 764                                    | NR                             | 655               | 759                                    | NR                             | 785               | 25                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 3                                      | NR                             | 530               | 794                                    | NR                             | 660               | 704                                    | NR                             | 790               | 21                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 6                                      | NR                             | 535               | 820                                    | NR                             | 665               | 651                                    | NR                             | 795               | 18                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 12                                     | NR                             | 540               | 837                                    | NR                             | 670               | 592                                    | NR                             | 800               | 16                                     | NR                             | 930               | 1                                      | NR                             |
| 415               | 22                                     | NR                             | 545               | 853                                    | NR                             | 675               | 538                                    | NR                             | 805               | 13                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 42                                     | NR                             | 550               | 864                                    | NR                             | 680               | 486                                    | NR                             | 810               | 12                                     | NR                             | 940               | 0                                      | NR                             |
| 425               | 79                                     | NR                             | 555               | 872                                    | NR                             | 685               | 435                                    | NR                             | 815               | 10                                     | NR                             | 945               | 0                                      | NR                             |
| 430               | 147                                    | NR                             | 560               | 876                                    | NR                             | 690               | 389                                    | NR                             | 820               | 9                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 278                                    | NR                             | 565               | 883                                    | NR                             | 695               | 344                                    | NR                             | 825               | 7                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 515                                    | NR                             | 570               | 891                                    | NR                             | 700               | 303                                    | NR                             | 830               | 6                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 832                                    | NR                             | 575               | 900                                    | NR                             | 705               | 266                                    | NR                             | 835               | 5                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 874                                    | NR                             | 580               | 914                                    | NR                             | 710               | 233                                    | NR                             | 840               | 5                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 659                                    | NR                             | 585               | 927                                    | NR                             | 715               | 203                                    | NR                             | 845               | 4                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 567                                    | NR                             | 590               | 944                                    | NR                             | 720               | 178                                    | NR                             | 850               | 4                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 485                                    | NR                             | 595               | 961                                    | NR                             | 725               | 154                                    | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 401                                    | NR                             | 600               | 975                                    | NR                             | 730               | 133                                    | NR                             | 860               | 3                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 393                                    | NR                             | 605               | 988                                    | NR                             | 735               | 115                                    | NR                             | 865               | 2                                      | NR                             | 995               | 1                                      | NR                             |
| 480               | 417                                    | NR                             | 610               | 996                                    | NR                             | 740               | 98                                     | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 448                                    | NR                             | 615               | 998                                    | NR                             | 745               | 85                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-16





TM-30-18

### Summary

$R_f = 91.8$   
 $R_g = 98.4$   
 $CIE R_a = 92.1$   
 $R_9 = 60.7$







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 96 | CES76 = 87 |
| CES02 = 62 | CES27 = 91 | CES52 = 98 | CES77 = 90 |
| CES03 = 31 | CES28 = 96 | CES53 = 95 | CES78 = 84 |
| CES04 = 69 | CES29 = 96 | CES54 = 94 | CES79 = 96 |
| CES05 = 49 | CES30 = 93 | CES55 = 92 | CES80 = 94 |
| CES06 = 50 | CES31 = 97 | CES56 = 93 | CES81 = 89 |
| CES07 = 42 | CES32 = 92 | CES57 = 92 | CES82 = 97 |
| CES08 = 41 | CES33 = 99 | CES58 = 92 | CES83 = 98 |
| CES09 = 29 | CES34 = 94 | CES59 = 96 | CES84 = 94 |
| CES10 = 74 | CES35 = 96 | CES60 = 93 | CES85 = 85 |
| CES11 = 57 | CES36 = 82 | CES61 = 92 | CES86 = 88 |
| CES12 = 63 | CES37 = 95 | CES62 = 87 | CES87 = 92 |
| CES13 = 43 | CES38 = 88 | CES63 = 92 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 89 | CES89 = 87 |
| CES15 = 71 | CES40 = 98 | CES65 = 88 | CES90 = 96 |
| CES16 = 47 | CES41 = 97 | CES66 = 87 | CES91 = 74 |
| CES17 = 49 | CES42 = 96 | CES67 = 86 | CES92 = 80 |
| CES18 = 56 | CES43 = 96 | CES68 = 88 | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 89 | CES94 = 82 |
| CES20 = 66 | CES45 = 98 | CES70 = 86 | CES95 = 83 |
| CES21 = 85 | CES46 = 97 | CES71 = 81 | CES96 = 92 |
| CES22 = 78 | CES47 = 97 | CES72 = 94 | CES97 = 95 |
| CES23 = 91 | CES48 = 91 | CES73 = 81 | CES98 = 94 |
| CES24 = 90 | CES49 = 96 | CES74 = 93 | CES99 = 91 |
| CES25 = 71 | CES50 = 97 | CES75 = 83 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)